

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031213

Luminaire Tested: S123RDIW-B560D755UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031213
REPORT IS A COMBINATION OF REPORTS P994574 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B560D755UB2750-4F0-XX-W2A-F_5000K
Description: Define 3 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4998.0 lumens
Efficiency: N/A
Efficacy: 105.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 47.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031213

CATALOG NUMBER: S123RDIW-B560D755UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1031213

CATALOG NUMBER: S123RDIW-B560D755UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	43	42	41
2	88	80	75	70	80	74	69	64	61	57	54	49	46	44	38	36	35
3	80	71	64	58	73	65	59	54	54	49	46	43	40	38	34	32	30
4	73	63	55	49	67	58	51	46	48	43	39	39	35	32	30	28	26
5	67	56	48	42	61	52	45	40	43	38	34	35	31	28	27	25	23
6	62	50	42	37	56	46	39	34	39	33	30	32	28	25	25	22	20
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18
8	53	41	34	29	49	38	31	27	32	27	23	26	22	20	21	18	16
9	50	38	30	25	45	35	28	24	29	24	21	24	20	18	19	17	15
10	46	35	27	23	42	32	26	21	27	22	19	22	19	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9734	9734	9734
5°	9750	9389	9364
10°	9673	9037	8858
15°	9547	8600	8305
20°	9383	8126	7685
25°	9213	7632	7099
30°	8996	7108	6406
35°	8771	6593	5774
40°	8559	6033	5077
45°	8288	5486	4450
50°	7991	4901	3801
55°	7681	4275	3206
60°	7385	3634	2602
65°	7003	2977	2032
70°	6523	2250	1451
75°	5831	1523	1149
80°	4978	1059	806
85°	3737	571	423

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 8288 cd/sqm

TEST NUMBER: P1031213

CATALOG NUMBER: S123RDIW-B560D755UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.0	1.7
10°-20°	236.5	4.7
20°-30°	340.5	6.8
30°-40°	383.4	7.7
40°-50°	366.8	7.3
50°-60°	300.2	6.0
60°-70°	202.4	4.1
70°-80°	101.5	2.0
80°-90°	28.5	0.6
90°-100°	34.1	0.7
100°-110°	165.2	3.3
110°-120°	404.7	8.1
120°-130°	513.8	10.3
130°-140°	548.9	11.0
140°-150°	513.2	10.3
150°-160°	414.0	8.3
160°-170°	267.2	5.3
170°-180°	92.1	1.8
0°-30°	662.0	13.2
0°-40°	1045.4	20.9
0°-60°	1712.5	34.3
0°-90°	2044.9	40.9
90°-120°	604.0	12.1
90°-150°	2179.9	43.6
90°-180°	2953.0	59.1
0°-180°	4998.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	904	904	904	904	904	
5°	904	901	892	898	897	86
15°	862	854	834	830	825	243
25°	785	766	733	717	709	361
35°	679	653	607	576	562	425
45°	558	525	469	427	409	431
55°	424	388	326	283	268	380
65°	290	249	192	156	148	287
75°	153	118	78	70	69	163
85°	39	23	20	19	19	43
90°	1	8	17	20	22	5
95°	44	14	22	27	27	52
105°	214	222	158	30	32	227
115°	402	407	413	420	423	397
125°	567	573	576	577	579	507
135°	706	710	713	715	713	544
145°	815	820	821	823	823	510
155°	897	896	897	900	896	414
165°	946	944	944	949	944	267
175°	969	965	966	971	965	92
180°	969	969	969	969	969	

TEST NUMBER: P1031213

CATALOG NUMBER: S123RDIW-B560D755UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	904.3	904.3	904.3	904.3	904.3
2.5°	908.0	905.0	896.2	904.3	902.8
5°	904.3	900.6	891.8	898.4	897.0
7.5°	897.7	894.0	883.0	887.4	885.2
10°	888.9	883.8	870.6	871.3	867.6
12.5°	876.4	870.6	853.7	853.0	848.6
15°	862.5	854.4	833.9	830.2	825.1
17.5°	845.6	836.8	811.2	803.8	796.5
20°	826.6	814.8	787.0	777.4	768.6
22.5°	805.3	791.4	761.3	748.8	740.8
25°	784.8	766.4	732.7	717.3	709.2
27.5°	759.8	740.0	703.4	682.8	670.3
30°	734.2	712.2	671.1	646.1	634.4
32.5°	708.5	682.8	638.8	610.9	598.5
35°	679.2	652.7	607.3	575.7	562.5
37.5°	649.8	621.2	573.5	538.3	522.2
40°	621.9	589.7	537.6	499.5	482.6
42.5°	590.4	558.1	503.9	461.3	446.7
45°	558.1	525.1	468.7	426.9	409.3
47.5°	526.6	489.9	434.2	388.7	373.3
50°	491.4	456.9	397.5	352.0	335.2
52.5°	459.9	421.7	363.0	315.4	300.7
55°	423.9	388.0	325.6	283.1	268.4
57.5°	391.6	352.8	289.7	249.4	236.9
60°	357.9	317.6	256.7	217.1	204.6
62.5°	324.2	283.8	223.0	186.3	173.1
65°	289.7	249.4	192.2	156.2	148.2
67.5°	255.2	214.2	158.4	131.3	122.5
70°	221.5	181.9	130.5	104.9	96.8
72.5°	187.8	148.9	103.4	83.6	81.4
75°	153.3	118.1	77.7	70.4	68.9
77.5°	121.7	89.5	60.9	56.5	55.0
80°	91.7	61.6	46.2	44.0	42.5
82.5°	63.1	38.1	33.0	30.8	30.8
85°	38.9	22.7	20.5	19.1	19.1
87.5°	17.6	9.5	9.5	8.8	8.1
90°	0.7	7.9	17.3	20.2	21.6
92.5°	16.6	12.2	18.7	23.7	24.5
95°	43.9	14.4	22.3	27.3	27.3
97.5°	79.9	59.7	23.0	28.8	29.5
100°	121.6	136.0	23.7	29.5	30.2
102.5°	169.1	178.5	53.3	29.5	30.9
105°	214.5	222.4	157.6	30.2	31.7
107.5°	262.7	269.2	279.9	169.1	74.8
110°	310.9	316.7	324.6	300.8	197.9



TEST NUMBER: P1031213

CATALOG NUMBER: S123RDIW-B560D755UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	357.0	362.0	369.9	376.4	374.9
115°	402.3	406.6	413.1	420.3	423.2
117.5°	446.9	451.9	455.5	461.3	462.0
120°	487.9	494.4	496.6	502.3	502.3
122.5°	529.7	534.7	537.6	541.2	541.9
125°	567.1	572.9	575.7	577.2	578.6
127.5°	604.5	610.3	613.9	616.0	614.6
130°	639.1	644.8	647.7	650.6	649.1
132.5°	672.2	677.9	680.1	683.0	680.8
135°	706.0	710.3	713.2	715.3	713.2
137.5°	734.8	740.5	742.0	745.6	744.1
140°	763.6	767.9	770.0	772.9	771.5
142.5°	790.2	794.5	796.7	798.8	796.7
145°	814.7	819.7	821.1	822.6	822.6
147.5°	838.4	842.0	843.4	844.9	841.3
150°	860.0	862.2	863.6	865.0	862.9
152.5°	879.4	880.1	880.9	883.7	880.1
155°	897.4	896.0	896.7	900.3	896.0
157.5°	911.8	911.8	911.1	915.4	909.7
160°	924.8	924.0	923.3	927.6	922.6
162.5°	937.0	934.8	934.1	939.2	934.8
165°	946.4	944.2	943.5	949.2	944.2
167.5°	954.3	951.4	951.4	957.2	951.4
170°	960.8	957.9	957.9	963.6	957.9
172.5°	965.1	961.5	962.2	967.9	961.5
175°	968.7	965.1	965.8	970.8	965.1
177.5°	970.1	966.5	967.2	973.0	965.8
180°	968.7	968.7	968.7	968.7	968.7

(END OF REPORT)