

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031223

Luminaire Tested: S123RDIW-B775D1030UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031223
REPORT IS A COMBINATION OF REPORTS P994618 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B775D1030UB2750-4F0-XX-W2A-F_5000K
Description: Define 3 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6841.0 lumens
Efficiency: N/A
Efficacy: 101.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031223

CATALOG NUMBER: S123RDIW-B775D1030UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1031223

CATALOG NUMBER: S123RDIW-B775D1030UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48
1	96	92	88	85	88	84	81	78	69	67	65	55	54	53	43	42	41
2	88	81	75	70	80	74	69	64	61	57	54	49	47	44	38	36	35
3	80	71	64	58	73	65	59	54	54	49	46	44	40	38	34	32	30
4	73	63	55	49	67	58	51	46	48	43	39	39	35	33	30	28	26
5	67	56	48	42	61	52	45	40	43	38	34	35	31	28	28	25	23
6	62	50	43	37	57	46	39	34	39	34	30	32	28	25	25	22	20
7	57	46	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18
8	53	41	34	29	49	38	31	27	32	27	23	26	23	20	21	18	16
9	50	38	30	25	45	35	28	24	29	24	21	24	20	18	20	17	15
10	46	35	28	23	42	32	26	21	27	22	19	22	19	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13431	13431	13431
5°	13453	12956	12921
10°	13347	12468	12223
15°	13174	11866	11459
20°	12946	11212	10605
25°	12712	10531	9795
30°	12412	9808	8839
35°	12102	9096	7968
40°	11811	8324	7005
45°	11437	7570	6140
50°	11025	6763	5245
55°	10598	5900	4424
60°	10191	5015	3590
65°	9662	4106	2802
70°	9000	3105	2003
75°	8045	2103	1587
80°	6868	1462	1113
85°	5149	788	583

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11437 cd/sqm

TEST NUMBER: P1031223

CATALOG NUMBER: S123RDIW-B775D1030UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.3	1.7
10°-20°	326.3	4.8
20°-30°	469.8	6.9
30°-40°	529.1	7.7
40°-50°	506.1	7.4
50°-60°	414.3	6.1
60°-70°	279.3	4.1
70°-80°	140.1	2.0
80°-90°	39.3	0.6
90°-100°	46.5	0.7
100°-110°	224.8	3.3
110°-120°	550.8	8.1
120°-130°	699.3	10.2
130°-140°	747.0	10.9
140°-150°	698.6	10.2
150°-160°	563.5	8.2
160°-170°	363.6	5.3
170°-180°	125.3	1.8
0°-30°	913.4	13.4
0°-40°	1442.6	21.1
0°-60°	2363.0	34.5
0°-90°	2821.6	41.2
90°-120°	822.1	12.0
90°-150°	2967.0	43.4
90°-180°	4019.0	58.7
0°-180°	6841.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1248	1248	1248	1248	1248	
5°	1248	1243	1231	1240	1238	118
15°	1190	1179	1151	1146	1138	335
25°	1083	1058	1011	990	979	498
35°	937	901	838	794	776	587
45°	770	725	647	589	565	594
55°	585	535	449	391	370	525
65°	400	344	265	216	204	396
75°	212	163	107	97	95	225
85°	54	31	28	26	26	59
90°	1	11	24	27	29	7
95°	60	20	30	37	37	71
105°	292	303	214	41	43	309
115°	548	553	562	572	576	541
125°	772	780	784	786	788	690
135°	961	967	971	974	971	740
145°	1109	1116	1118	1120	1120	694
155°	1222	1220	1220	1225	1220	563
165°	1288	1285	1284	1292	1285	364
175°	1318	1314	1314	1321	1314	125
180°	1318	1318	1318	1318	1318	

TEST NUMBER: P1031223

CATALOG NUMBER: S123RDIW-B775D1030UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1247.8	1247.8	1247.8	1247.8	1247.8
2.5°	1252.9	1248.8	1236.7	1247.8	1245.8
5°	1247.8	1242.7	1230.6	1239.7	1237.7
7.5°	1238.7	1233.6	1218.5	1224.5	1221.5
10°	1226.5	1219.5	1201.2	1202.3	1197.2
12.5°	1209.3	1201.2	1178.0	1177.0	1170.9
15°	1190.1	1179.0	1150.6	1145.6	1138.5
17.5°	1166.8	1154.7	1119.3	1109.2	1099.0
20°	1140.5	1124.3	1085.9	1072.7	1060.6
22.5°	1111.2	1092.0	1050.5	1033.3	1022.1
25°	1082.8	1057.5	1011.0	989.7	978.6
27.5°	1048.4	1021.1	970.5	942.2	925.0
30°	1013.0	982.7	926.0	891.6	875.4
32.5°	977.6	942.2	881.5	843.0	825.8
35°	937.1	900.7	837.9	794.4	776.2
37.5°	896.6	857.2	791.4	742.8	720.5
40°	858.2	813.7	741.8	689.2	665.9
42.5°	814.7	770.1	695.2	636.5	616.3
45°	770.1	724.6	646.7	589.0	564.7
47.5°	726.6	676.0	599.1	536.4	515.1
50°	678.0	630.5	548.5	485.8	462.5
52.5°	634.5	581.9	500.9	435.2	414.9
55°	584.9	535.3	449.3	390.6	370.4
57.5°	540.4	486.8	399.7	344.1	326.9
60°	493.9	438.2	354.2	299.6	282.3
62.5°	447.3	391.6	307.6	257.0	238.8
65°	399.7	344.1	265.1	215.6	204.4
67.5°	352.2	295.5	218.6	181.1	169.0
70°	305.6	251.0	180.1	144.7	133.6
72.5°	259.1	205.4	142.7	115.4	112.3
75°	211.5	162.9	107.3	97.2	95.1
77.5°	168.0	123.5	84.0	77.9	75.9
80°	126.5	85.0	63.8	60.7	58.7
82.5°	87.0	52.6	45.5	42.5	42.5
85°	53.6	31.4	28.3	26.3	26.3
87.5°	24.3	13.2	13.2	12.1	11.1
90°	1.0	10.8	23.5	27.4	29.4
92.5°	22.5	16.7	25.5	32.3	33.3
95°	59.8	19.6	30.4	37.2	37.2
97.5°	108.7	81.3	31.3	39.2	40.2
100°	165.5	185.1	32.3	40.2	41.1
102.5°	230.2	242.9	72.5	40.2	42.1
105°	291.9	302.7	214.5	41.1	43.1
107.5°	357.5	366.3	381.0	230.2	101.9
110°	423.2	431.0	441.8	409.4	269.4

TEST NUMBER: P1031223

CATALOG NUMBER: S123RDIW-B775D1030UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	485.8	492.7	503.5	512.3	510.3
115°	547.6	553.4	562.2	572.0	576.0
117.5°	608.3	615.1	620.0	627.9	628.9
120°	664.1	672.9	675.9	683.7	683.7
122.5°	720.9	727.8	731.7	736.6	737.6
125°	771.9	779.7	783.6	785.6	787.5
127.5°	822.8	830.6	835.5	838.5	836.5
130°	869.8	877.7	881.6	885.5	883.5
132.5°	914.9	922.7	925.6	929.6	926.6
135°	960.9	966.8	970.7	973.6	970.7
137.5°	1000.1	1007.9	1009.9	1014.8	1012.8
140°	1039.3	1045.2	1048.1	1052.0	1050.0
142.5°	1075.5	1081.4	1084.3	1087.3	1084.3
145°	1108.8	1115.7	1117.6	1119.6	1119.6
147.5°	1141.1	1146.0	1148.0	1150.0	1145.1
150°	1170.5	1173.5	1175.4	1177.4	1174.4
152.5°	1197.0	1198.0	1198.9	1202.9	1198.0
155°	1221.5	1219.5	1220.5	1225.4	1219.5
157.5°	1241.1	1241.1	1240.1	1246.0	1238.1
160°	1258.7	1257.7	1256.7	1262.6	1255.7
162.5°	1275.3	1272.4	1271.4	1278.3	1272.4
165°	1288.1	1285.1	1284.2	1292.0	1285.1
167.5°	1298.8	1294.9	1294.9	1302.8	1294.9
170°	1307.7	1303.7	1303.7	1311.6	1303.7
172.5°	1313.5	1308.6	1309.6	1317.5	1308.6
175°	1318.4	1313.5	1314.5	1321.4	1313.5
177.5°	1320.4	1315.5	1316.5	1324.3	1314.5
180°	1318.4	1318.4	1318.4	1318.4	1318.4

(END OF REPORT)