

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031240

Luminaire Tested: S123RDIW-B775D1535UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031240
REPORT IS A COMBINATION OF REPORTS P994702 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B775D1535UB2750-4F0-XX-W2A-F_2700K
Description: Define 3 Regressed Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9082.0 lumens
Efficiency: N/A
Efficacy: 103.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 88.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031240

CATALOG NUMBER: S123RDIW-B775D1535UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1031240

CATALOG NUMBER: S123RDIW-B775D1535UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40
1	94	90	86	83	84	81	78	75	64	62	60	49	48	47	35	35	34
2	86	79	73	68	77	71	66	62	57	53	50	44	41	39	31	30	29
3	78	69	62	57	70	63	57	52	50	46	43	39	36	33	28	26	25
4	72	61	54	48	64	56	49	44	45	40	36	34	31	29	25	23	21
5	66	55	47	41	59	50	43	38	40	35	31	31	28	25	23	20	19
6	60	49	41	36	54	44	38	33	36	31	27	28	25	22	21	18	17
7	56	44	36	31	50	40	33	29	33	28	24	25	22	19	19	17	15
8	52	40	33	27	47	36	30	25	30	25	21	23	20	17	17	15	13
9	48	36	29	24	43	33	27	23	27	22	19	21	18	15	16	14	12
10	45	33	26	22	40	30	24	20	25	20	17	20	16	14	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13851	13851	13851
5°	13874	13360	13324
10°	13764	12858	12605
15°	13586	12238	11816
20°	13350	11562	10936
25°	13109	10861	10102
30°	12799	10114	9115
35°	12480	9381	8216
40°	12180	8585	7224
45°	11795	7806	6331
50°	11370	6974	5408
55°	10930	6085	4562
60°	10509	5172	3703
65°	9964	4234	2890
70°	9282	3203	2066
75°	8296	2168	1637
80°	7079	1506	1147
85°	5312	813	601

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11795 cd/sqm

TEST NUMBER: P1031240

CATALOG NUMBER: S123RDIW-B775D1535UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.0	1.3
10°-20°	336.5	3.7
20°-30°	484.5	5.3
30°-40°	545.6	6.0
40°-50°	521.9	5.7
50°-60°	427.2	4.7
60°-70°	288.0	3.2
70°-80°	144.5	1.6
80°-90°	41.8	0.5
90°-100°	71.4	0.8
100°-110°	345.1	3.8
110°-120°	845.7	9.3
120°-130°	1073.6	11.8
130°-140°	1146.9	12.6
140°-150°	1072.5	11.8
150°-160°	865.1	9.5
160°-170°	558.3	6.1
170°-180°	192.4	2.1
0°-30°	942.0	10.4
0°-40°	1487.6	16.4
0°-60°	2436.7	26.8
0°-90°	2911.0	32.1
90°-120°	1262.2	13.9
90°-150°	4555.2	50.2
90°-180°	6171.0	67.9
0°-180°	9082.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1287	1287	1287	1287	1287	
5°	1287	1282	1269	1278	1276	122
15°	1227	1216	1187	1181	1174	346
25°	1117	1091	1043	1021	1009	514
35°	966	929	864	819	800	605
45°	794	747	667	607	582	613
55°	603	552	463	403	382	541
65°	412	355	273	222	211	408
75°	218	168	111	100	98	232
85°	55	32	29	27	27	61
90°	2	16	36	42	45	9
95°	92	30	47	57	57	110
105°	448	465	329	63	66	475
115°	841	850	863	878	884	830
125°	1185	1197	1203	1206	1209	1059
135°	1475	1484	1490	1495	1490	1136
145°	1702	1713	1716	1719	1719	1066
155°	1875	1872	1874	1881	1872	864
165°	1978	1973	1972	1984	1973	559
175°	2024	2017	2018	2029	2017	193
180°	2024	2024	2024	2024	2024	

TEST NUMBER: P1031240

CATALOG NUMBER: S123RDIW-B775D1535UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1286.8	1286.8	1286.8	1286.8	1286.8
2.5°	1292.0	1287.8	1275.3	1286.8	1284.7
5°	1286.8	1281.5	1269.0	1278.4	1276.3
7.5°	1277.4	1272.1	1256.5	1262.7	1259.6
10°	1264.8	1257.5	1238.7	1239.8	1234.6
12.5°	1247.1	1238.7	1214.7	1213.7	1207.4
15°	1227.3	1215.8	1186.6	1181.3	1174.0
17.5°	1203.3	1190.7	1154.2	1143.8	1133.3
20°	1176.1	1159.4	1119.8	1106.2	1093.7
22.5°	1145.9	1126.0	1083.3	1065.5	1054.0
25°	1116.6	1090.6	1042.6	1020.6	1009.2
27.5°	1081.2	1053.0	1000.8	971.6	953.8
30°	1044.6	1013.3	954.9	919.4	902.7
32.5°	1008.1	971.6	909.0	869.3	851.6
35°	966.4	928.8	864.1	819.2	800.4
37.5°	924.6	883.9	816.1	766.0	743.0
40°	885.0	839.0	765.0	710.7	686.7
42.5°	840.1	794.2	716.9	656.4	635.5
45°	794.2	747.2	666.9	607.4	582.3
47.5°	749.3	697.1	617.8	553.1	531.2
50°	699.2	650.2	565.6	500.9	476.9
52.5°	654.3	600.1	516.6	448.7	427.9
55°	603.2	552.1	463.4	402.8	382.0
57.5°	557.3	502.0	412.2	354.8	337.1
60°	509.3	451.9	365.3	308.9	291.2
62.5°	461.3	403.9	317.3	265.1	246.3
65°	412.2	354.8	273.4	222.3	210.8
67.5°	363.2	304.7	225.4	186.8	174.3
70°	315.2	258.8	185.8	149.2	137.8
72.5°	267.2	211.8	147.1	119.0	115.8
75°	218.1	168.0	110.6	100.2	98.1
77.5°	173.2	127.3	86.6	80.4	78.3
80°	130.4	87.7	65.7	62.6	60.5
82.5°	89.7	54.3	47.0	43.8	43.8
85°	55.3	32.4	29.2	27.1	27.1
87.5°	25.0	13.6	13.6	12.5	11.5
90°	1.5	16.5	36.1	42.1	45.1
92.5°	34.6	25.6	39.1	49.6	51.1
95°	91.7	30.1	46.6	57.1	57.1
97.5°	166.9	124.8	48.1	60.2	61.7
100°	254.2	284.2	49.6	61.7	63.2
102.5°	353.4	373.0	111.3	61.7	64.7
105°	448.2	464.7	329.3	63.2	66.2
107.5°	548.9	562.4	585.0	353.4	156.4
110°	649.7	661.7	678.2	628.6	413.6

TEST NUMBER: P1031240

CATALOG NUMBER: S123RDIW-B775D1535UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	745.9	756.4	773.0	786.5	783.5
115°	840.7	849.7	863.2	878.3	884.3
117.5°	933.9	944.4	951.9	964.0	965.5
120°	1019.6	1033.2	1037.7	1049.7	1049.7
122.5°	1106.8	1117.4	1123.4	1130.9	1132.4
125°	1185.0	1197.1	1203.1	1206.1	1209.1
127.5°	1263.2	1275.3	1282.8	1287.3	1284.3
130°	1335.4	1347.5	1353.5	1359.5	1356.5
132.5°	1404.6	1416.6	1421.2	1427.2	1422.7
135°	1475.3	1484.3	1490.3	1494.8	1490.3
137.5°	1535.4	1547.5	1550.5	1558.0	1555.0
140°	1595.6	1604.6	1609.1	1615.2	1612.1
142.5°	1651.2	1660.3	1664.8	1669.3	1664.8
145°	1702.4	1712.9	1715.9	1718.9	1718.9
147.5°	1752.0	1759.5	1762.5	1765.5	1758.0
150°	1797.1	1801.6	1804.6	1807.6	1803.1
152.5°	1837.7	1839.2	1840.7	1846.7	1839.2
155°	1875.3	1872.3	1873.8	1881.3	1872.3
157.5°	1905.4	1905.4	1903.9	1912.9	1900.9
160°	1932.5	1931.0	1929.5	1938.5	1928.0
162.5°	1958.0	1953.5	1952.0	1962.5	1953.5
165°	1977.6	1973.1	1971.6	1983.6	1973.1
167.5°	1994.1	1988.1	1988.1	2000.1	1988.1
170°	2007.7	2001.6	2001.6	2013.7	2001.6
172.5°	2016.7	2009.2	2010.7	2022.7	2009.2
175°	2024.2	2016.7	2018.2	2028.7	2016.7
177.5°	2027.2	2019.7	2021.2	2033.2	2018.2
180°	2024.2	2024.2	2024.2	2024.2	2024.2

(END OF REPORT)