

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031735

Luminaire Tested: S123DIW-B560D1320UB35-4F0-XX-W2A-A

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031735
REPORT IS A COMBINATION OF REPORTS P991614 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B560D1320UB35-4F0-XX-W2A-A
Description: Define 3 Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7691.0 lumens
Efficiency: N/A
Efficacy: 116.4 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 66.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031735

CATALOG NUMBER: S123DIW-B560D1320UB35-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1031735

CATALOG NUMBER: S123DIW-B560D1320UB35-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	39	39	31
1	94	90	86	83	84	81	78	75	64	62	60	49	47	46	34	34	33	33	33	27
2	85	78	73	68	77	71	66	62	56	53	50	43	41	39	31	29	28	28	28	22
3	78	69	62	56	70	62	56	52	50	45	42	38	35	33	27	25	24	24	24	19
4	71	61	53	48	64	55	49	44	44	39	36	34	31	28	24	22	21	21	21	17
5	65	54	46	41	59	49	42	37	39	35	31	30	27	24	22	20	18	18	18	14
6	60	49	41	35	54	44	37	32	35	30	27	27	24	21	20	18	16	16	16	13
7	56	44	36	31	50	40	33	28	32	27	24	25	21	19	18	16	14	14	14	11
8	51	40	32	27	46	36	29	25	29	24	21	23	19	17	17	14	13	13	13	10
9	48	36	29	24	43	33	26	22	27	22	19	21	17	15	15	13	11	11	11	9
10	45	33	26	21	40	30	24	20	24	20	17	19	16	13	14	12	10	10	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8509	8509	8509	8509
5°	8515	9805	8540	7317
10°	8461	11865	8469	6390
15°	8344	14071	8412	5752
20°	8243	16200	8260	5292
25°	8093	16608	8112	5053
30°	7987	13721	7987	4896
35°	7854	9177	7805	4758
40°	7696	6625	7601	4545
45°	7497	5247	7282	4281
50°	7013	4457	6765	4022
55°	6481	3916	6219	3732
60°	5943	3409	5627	3429
65°	5352	2920	5093	3024
70°	4738	2423	4420	2550
75°	4051	1827	3789	1969
80°	3203	1219	2953	1293
85°	2209	561	1767	510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 13723 cd/sqm

TEST NUMBER: P1031735

CATALOG NUMBER: S123DIW-B560D1320UB35-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.7	1.0
10°-20°	249.7	3.2
20°-30°	420.2	5.5
30°-40°	474.8	6.2
40°-50°	425.3	5.5
50°-60°	343.3	4.5
60°-70°	239.2	3.1
70°-80°	125.6	1.6
80°-90°	33.6	0.4
90°-100°	61.3	0.8
100°-110°	296.5	3.9
110°-120°	726.6	9.4
120°-130°	922.4	12.0
130°-140°	985.3	12.8
140°-150°	921.4	12.0
150°-160°	743.2	9.7
160°-170°	479.6	6.2
170°-180°	165.3	2.1
0°-30°	747.6	9.7
0°-40°	1222.5	15.9
0°-60°	1991.1	25.9
0°-90°	2389.5	31.1
90°-120°	1084.4	14.1
90°-150°	3913.4	50.9
90°-180°	5302.0	68.9
0°-180°	7691.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	790	790	790	790	790	
5°	790	939	792	701	790	75
15°	754	1398	760	572	754	213
25°	689	1659	691	505	689	318
35°	608	894	604	464	608	381
45°	505	483	490	394	505	386
55°	358	328	343	312	358	320
65°	221	213	211	221	221	220
75°	106	110	100	118	106	114
85°	23	25	18	23	23	26
90°	1	39	1	39	1	6
95°	79	49	79	49	79	94
105°	385	57	385	57	385	408
115°	722	760	722	760	722	713
125°	1018	1039	1018	1039	1018	910
135°	1267	1280	1267	1280	1267	976
145°	1462	1477	1462	1477	1462	916
155°	1611	1608	1611	1608	1611	742
165°	1699	1695	1699	1695	1699	480
175°	1739	1733	1739	1733	1739	166
180°	1739	1739	1739	1739	1739	

TEST NUMBER: P1031735

CATALOG NUMBER: S123DIW-B560D1320UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5
2.5°	792.8	799.0	802.0	806.6	811.2	818.1	820.4	824.3	822.7	825.8	827.3
5°	789.8	800.5	809.7	821.2	831.9	839.6	847.2	859.5	868.7	870.2	877.1
7.5°	784.4	799.7	815.8	831.9	852.6	864.9	878.6	895.5	909.3	931.5	939.9
10°	777.5	799.0	822.0	844.2	872.5	891.7	908.5	936.9	965.2	988.2	1009.6
12.5°	766.8	793.6	823.5	856.4	893.2	915.4	938.4	975.9	1018.8	1054.1	1077.0
15°	753.8	787.5	825.8	861.0	901.6	943.0	967.5	1009.6	1070.9	1103.9	1162.8
17.5°	743.1	777.5	815.8	871.0	926.1	967.5	985.1	1062.5	1104.6	1159.8	1226.4
20°	726.2	769.9	818.9	874.0	945.3	970.6	1006.6	1084.7	1136.8	1208.8	1290.8
22.5°	708.6	755.3	814.3	871.7	951.4	978.2	1027.3	1089.3	1172.0	1243.3	1333.7
25°	689.4	740.0	799.7	867.9	946.1	985.1	1031.1	1107.7	1197.3	1286.9	1370.4
27.5°	670.3	725.4	787.5	855.7	931.5	977.5	1023.4	1103.1	1218.0	1315.3	1421.8
30°	651.9	707.0	769.1	838.8	918.5	962.9	1006.6	1106.2	1234.1	1343.6	1450.9
32.5°	632.0	688.7	753.8	812.0	892.4	939.9	989.0	1106.2	1244.0	1360.5	1458.5
35°	608.2	666.5	722.4	780.6	860.3	913.1	968.3	1098.5	1253.2	1365.8	1426.4
37.5°	585.3	636.6	684.8	741.5	825.0	881.7	945.3	1089.3	1248.6	1342.9	1359.7
40°	559.2	610.5	649.6	702.5	790.5	856.4	920.8	1077.0	1228.7	1288.5	1239.4
42.5°	533.9	574.5	608.2	659.6	755.3	819.7	889.4	1054.8	1189.7	1201.9	1091.6
45°	504.8	533.9	563.8	622.0	717.0	782.9	860.3	1022.7	1126.8	1091.6	952.2
47.5°	467.3	493.3	526.3	579.9	676.4	744.6	818.1	981.3	1035.7	962.1	809.7
50°	431.3	453.5	484.1	536.2	633.5	700.2	778.3	916.2	943.0	827.3	697.9
52.5°	395.3	412.1	442.0	494.1	591.4	655.7	727.0	849.5	834.2	710.1	595.2
55°	357.7	372.3	400.6	452.0	542.4	603.6	671.8	767.6	727.7	609.8	517.8
57.5°	321.0	336.3	365.4	408.3	493.3	553.1	607.5	682.5	622.8	528.6	447.4
60°	288.0	301.1	323.3	365.4	442.8	491.0	540.8	592.1	542.4	451.2	389.1
62.5°	253.6	265.8	286.5	324.8	391.4	434.3	474.2	516.3	461.2	394.5	339.4
65°	221.4	231.3	250.5	285.7	340.1	375.4	407.5	436.6	392.2	330.9	289.6
67.5°	192.3	200.7	216.8	248.2	294.2	319.4	345.5	370.0	332.5	283.4	248.2
70°	160.9	167.8	182.3	205.3	242.1	268.1	287.3	305.6	271.9	232.9	209.1
72.5°	133.3	140.2	149.4	173.1	198.4	214.5	235.2	245.1	226.0	193.8	170.1
75°	106.5	111.8	120.3	135.6	159.3	170.1	183.1	190.7	173.1	151.7	137.1
77.5°	83.5	85.8	91.9	102.6	118.7	131.0	141.0	145.5	133.3	119.5	107.2
80°	59.0	62.0	66.6	75.8	88.1	91.9	98.1	103.4	95.8	83.5	75.8
82.5°	39.1	42.9	45.2	49.0	56.7	61.3	62.8	67.4	60.5	55.9	52.9
85°	23.0	24.5	25.3	27.6	31.4	33.7	36.0	36.8	35.2	34.5	31.4
87.5°	11.5	11.5	11.5	13.0	13.8	15.3	16.1	16.1	16.1	15.3	14.6
90°	1.3	4.2	7.0	9.9	12.8	14.2	16.1	19.8	23.5	27.3	31.0
92.5°	29.7	28.0	26.3	24.6	22.9	22.0	23.3	25.9	28.4	31.0	33.6
95°	78.8	67.0	55.2	43.5	31.7	25.8	27.4	30.6	33.7	36.9	40.1
97.5°	143.4	135.4	127.3	119.3	111.2	107.2	99.9	85.2	70.6	55.9	41.3
100°	218.3	224.1	229.8	235.6	241.3	244.2	221.8	177.0	132.2	87.4	42.6
102.5°	303.6	307.3	311.1	314.8	318.5	320.4	295.4	245.5	195.5	145.6	95.6
105°	385.0	388.2	391.3	394.5	397.6	399.2	386.3	360.4	334.6	308.7	282.9
107.5°	471.6	474.2	476.8	479.3	481.9	483.2	485.4	489.7	494.0	498.3	502.6
110°	558.1	560.4	562.7	565.0	567.3	568.5	570.1	573.2	576.4	579.5	582.7



TEST NUMBER: P1031735

CATALOG NUMBER: S123DIW-B560D1320UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	640.8	642.8	644.8	646.9	648.9	649.9	651.5	654.6	657.8	660.9	664.1
115°	722.2	723.9	725.7	727.4	729.1	730.0	731.3	733.9	736.4	739.0	741.6
117.5°	802.3	804.3	806.3	808.4	810.4	811.4	812.1	813.5	815.0	816.4	817.8
120°	876.0	878.6	881.2	883.7	886.3	887.6	888.0	888.9	889.8	890.6	891.5
122.5°	950.9	952.9	954.9	956.9	958.9	959.9	960.5	961.6	962.8	963.9	965.1
125°	1018.1	1020.4	1022.7	1025.0	1027.3	1028.4	1029.0	1030.1	1031.3	1032.4	1033.6
127.5°	1085.3	1087.6	1089.9	1092.2	1094.5	1095.6	1096.3	1097.8	1099.2	1100.7	1102.1
130°	1147.3	1149.6	1151.9	1154.2	1156.5	1157.6	1158.2	1159.3	1160.5	1161.6	1162.8
132.5°	1206.7	1209.0	1211.3	1213.6	1215.9	1217.1	1217.5	1218.4	1219.2	1220.1	1220.9
135°	1267.4	1269.1	1270.9	1272.6	1274.3	1275.2	1275.8	1276.9	1278.1	1279.2	1280.4
137.5°	1319.1	1321.4	1323.7	1326.0	1328.3	1329.5	1329.8	1330.3	1330.9	1331.4	1332.0
140°	1370.8	1372.5	1374.2	1375.9	1377.6	1378.5	1378.9	1379.8	1380.7	1381.5	1382.4
142.5°	1418.6	1420.3	1422.1	1423.8	1425.5	1426.4	1426.8	1427.7	1428.5	1429.4	1430.2
145°	1462.5	1464.5	1466.5	1468.6	1470.6	1471.6	1471.9	1472.5	1473.0	1473.6	1474.2
147.5°	1505.2	1506.6	1508.0	1509.5	1510.9	1511.6	1511.9	1512.5	1513.0	1513.6	1514.2
150°	1543.9	1544.8	1545.6	1546.5	1547.4	1547.8	1548.1	1548.7	1549.2	1549.8	1550.4
152.5°	1578.8	1579.1	1579.4	1579.7	1580.0	1580.1	1580.2	1580.5	1580.8	1581.1	1581.4
155°	1611.1	1610.5	1609.9	1609.4	1608.8	1608.5	1608.6	1608.9	1609.2	1609.5	1609.8
157.5°	1636.9	1636.9	1636.9	1636.9	1636.9	1636.9	1636.8	1636.5	1636.2	1636.0	1635.7
160°	1660.2	1659.9	1659.6	1659.3	1659.0	1658.9	1658.8	1658.5	1658.2	1657.9	1657.6
162.5°	1682.2	1681.3	1680.5	1679.6	1678.7	1678.3	1678.2	1677.9	1677.6	1677.3	1677.0
165°	1699.0	1698.1	1697.3	1696.4	1695.5	1695.1	1695.0	1694.7	1694.4	1694.1	1693.8
167.5°	1713.2	1712.0	1710.9	1709.7	1708.6	1708.0	1708.0	1708.0	1708.0	1708.0	1708.0
170°	1724.8	1723.6	1722.5	1721.3	1720.2	1719.6	1719.6	1719.6	1719.6	1719.6	1719.6
172.5°	1732.6	1731.2	1729.7	1728.3	1726.8	1726.1	1726.2	1726.5	1726.8	1727.1	1727.4
175°	1739.0	1737.6	1736.2	1734.7	1733.3	1732.6	1732.7	1733.0	1733.3	1733.5	1733.8
177.5°	1741.6	1740.2	1738.7	1737.3	1735.8	1735.1	1735.2	1735.5	1735.8	1736.1	1736.4
180°	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0

TEST NUMBER: P1031735

CATALOG NUMBER: S123DIW-B560D1320UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5
2.5°	832.7	834.2	839.6	843.4	851.1	850.3	850.3	849.5	847.2	851.1	853.4
5°	890.9	903.9	905.5	922.3	923.1	930.0	934.6	930.7	939.9	939.2	932.3
7.5°	962.9	980.5	989.0	1005.0	1023.4	1018.8	1036.4	1039.5	1038.0	1045.6	1051.0
10°	1041.8	1072.4	1093.9	1123.8	1131.4	1136.0	1147.5	1157.5	1177.4	1162.1	1172.0
12.5°	1132.2	1154.4	1182.8	1230.3	1254.0	1269.3	1274.7	1281.6	1295.4	1286.9	1287.7
15°	1208.0	1237.9	1286.2	1345.2	1352.1	1371.2	1366.6	1408.0	1427.9	1398.0	1414.9
17.5°	1286.9	1326.8	1384.2	1435.5	1464.7	1477.7	1489.9	1529.8	1528.2	1523.6	1527.5
20°	1337.5	1402.6	1473.9	1542.0	1550.5	1560.4	1593.4	1610.2	1607.1	1620.2	1628.6
22.5°	1408.7	1477.7	1553.5	1598.7	1617.9	1629.4	1655.4	1666.1	1670.7	1673.8	1668.4
25°	1468.5	1542.0	1597.9	1637.8	1649.3	1655.4	1663.8	1666.9	1664.6	1659.2	1663.8
27.5°	1509.1	1568.1	1606.4	1624.8	1618.6	1608.7	1592.6	1581.9	1558.1	1546.6	1560.4
30°	1525.9	1552.0	1563.5	1532.8	1502.2	1477.7	1447.0	1390.4	1345.9	1358.9	1341.3
32.5°	1499.1	1482.3	1427.1	1348.2	1324.5	1284.6	1198.1	1131.4	1133.7	1098.5	1113.0
35°	1420.2	1343.6	1239.4	1119.9	1088.5	1067.1	972.1	957.5	926.9	894.0	903.2
37.5°	1280.8	1169.0	1042.6	954.5	907.8	861.0	807.4	775.2	756.8	743.1	753.8
40°	1110.8	974.4	870.2	791.3	751.5	721.6	684.8	652.7	632.0	629.7	633.5
42.5°	943.8	828.8	733.1	658.0	645.0	609.8	586.0	560.7	554.6	544.7	550.0
45°	799.0	705.5	626.6	565.3	550.0	540.8	511.7	495.6	488.7	482.6	491.8
47.5°	694.0	596.0	538.5	501.8	486.4	471.1	455.0	444.3	438.9	439.7	438.9
50°	592.9	520.9	470.3	442.0	432.8	422.1	409.1	402.2	399.9	393.0	398.3
52.5°	510.2	458.1	422.9	396.0	389.1	381.5	370.8	366.9	361.6	360.0	360.0
55°	443.5	402.9	374.6	357.0	348.5	342.4	336.3	331.7	327.9	327.9	327.9
57.5°	391.4	356.2	335.5	320.2	317.1	311.0	304.1	304.1	298.8	298.0	300.3
60°	347.0	315.6	299.5	286.5	281.9	280.4	273.5	273.5	271.9	268.1	271.2
62.5°	301.8	278.8	265.0	255.1	250.5	250.5	245.1	241.3	241.3	242.1	240.5
65°	260.5	243.6	231.3	223.7	221.4	218.3	217.6	214.5	212.2	213.0	212.2
67.5°	223.7	210.7	202.2	196.1	192.3	190.7	188.4	188.4	186.9	187.7	183.8
70°	190.7	177.7	170.8	164.7	163.2	163.2	160.1	160.9	159.3	161.6	160.1
72.5°	157.0	147.1	141.7	139.4	137.9	137.1	135.6	134.1	133.3	134.8	134.1
75°	127.2	118.7	114.9	113.4	111.8	111.8	111.1	110.3	109.5	109.5	109.5
77.5°	98.8	93.5	88.9	90.4	88.1	88.9	86.6	86.6	87.3	86.6	86.6
80°	72.8	68.9	68.9	67.4	64.3	65.9	65.9	63.6	62.8	64.3	62.0
82.5°	48.3	47.5	46.0	45.2	43.7	44.4	43.7	42.9	42.1	43.7	42.1
85°	28.3	28.3	27.6	26.0	27.6	26.8	26.0	26.0	25.3	25.3	25.3
87.5°	14.6	13.0	13.0	12.3	13.0	11.5	12.3	11.5	10.7	11.5	10.7
90°	32.2	33.3	34.5	35.6	36.2	36.5	37.1	37.6	38.2	38.8	38.2
92.5°	35.6	37.6	39.6	41.6	42.6	42.7	43.0	43.3	43.6	43.9	43.6
95°	42.1	44.1	46.1	48.1	49.1	49.1	49.1	49.1	49.1	49.1	49.1
97.5°	43.6	45.9	48.2	50.5	51.7	51.8	52.1	52.4	52.7	53.0	52.7
100°	44.9	47.2	49.5	51.8	53.0	53.1	53.4	53.7	54.0	54.3	54.0
102.5°	86.1	76.7	67.2	57.7	53.0	53.3	53.9	54.4	55.0	55.6	55.0
105°	232.1	181.3	130.5	79.7	54.3	54.6	55.1	55.7	56.2	56.8	56.2
107.5°	458.4	414.2	369.9	325.7	303.6	284.8	247.2	209.6	172.0	134.4	172.0
110°	573.2	563.7	554.2	544.7	540.0	519.5	478.4	437.4	396.3	355.3	396.3

TEST NUMBER: P1031735

CATALOG NUMBER: S123DIW-B560D1320UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	666.7	669.3	671.8	674.4	675.7	675.4	674.8	674.3	673.7	673.1	673.7
115°	744.5	747.3	750.2	753.1	754.5	755.1	756.2	757.4	758.5	759.7	758.5
117.5°	820.1	822.4	824.7	827.0	828.2	828.3	828.6	828.9	829.2	829.5	829.2
120°	893.8	896.1	898.4	900.7	901.8	901.8	901.8	901.8	901.8	901.8	901.8
122.5°	966.5	968.0	969.4	970.9	971.6	971.7	972.0	972.3	972.6	972.9	972.6
125°	1034.2	1034.8	1035.3	1035.9	1036.2	1036.5	1037.1	1037.6	1038.2	1038.8	1038.2
127.5°	1102.9	1103.8	1104.6	1105.5	1105.9	1105.6	1105.1	1104.5	1104.0	1103.4	1104.0
130°	1164.0	1165.1	1166.3	1167.4	1168.0	1167.7	1167.1	1166.6	1166.0	1165.4	1166.0
132.5°	1222.1	1223.2	1224.4	1225.5	1226.1	1225.7	1224.8	1223.9	1223.1	1222.2	1223.1
135°	1281.2	1282.1	1282.9	1283.8	1284.2	1283.8	1282.9	1282.1	1281.2	1280.4	1281.2
137.5°	1333.4	1334.9	1336.3	1337.8	1338.5	1338.2	1337.6	1337.1	1336.5	1335.9	1336.5
140°	1383.6	1384.7	1385.9	1387.0	1387.6	1387.3	1386.7	1386.2	1385.6	1385.0	1385.6
142.5°	1431.1	1431.9	1432.8	1433.7	1434.1	1433.7	1432.8	1431.9	1431.1	1430.2	1431.1
145°	1474.8	1475.3	1475.9	1476.4	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7
147.5°	1514.8	1515.4	1515.9	1516.5	1516.8	1516.1	1514.6	1513.2	1511.7	1510.3	1511.7
150°	1551.0	1551.6	1552.1	1552.7	1553.0	1552.6	1551.7	1550.8	1550.0	1549.1	1550.0
152.5°	1582.6	1583.7	1584.9	1586.0	1586.6	1585.9	1584.4	1583.0	1581.5	1580.1	1581.5
155°	1611.2	1612.7	1614.1	1615.6	1616.3	1615.4	1613.7	1612.0	1610.2	1608.5	1610.2
157.5°	1637.4	1639.1	1640.8	1642.5	1643.4	1642.3	1640.0	1637.7	1635.4	1633.1	1635.4
160°	1659.3	1661.1	1662.8	1664.5	1665.4	1664.4	1662.4	1660.3	1658.3	1656.3	1658.3
162.5°	1679.0	1681.0	1683.0	1685.0	1686.0	1685.1	1683.4	1681.7	1680.0	1678.3	1680.0
165°	1696.1	1698.4	1700.7	1703.0	1704.1	1703.1	1701.1	1699.1	1697.1	1695.1	1697.1
167.5°	1710.3	1712.6	1714.9	1717.2	1718.3	1717.2	1714.9	1712.6	1710.3	1708.0	1710.3
170°	1721.9	1724.2	1726.5	1728.8	1730.0	1728.8	1726.5	1724.2	1721.9	1719.6	1721.9
172.5°	1729.7	1732.0	1734.3	1736.6	1737.7	1736.4	1733.8	1731.3	1728.7	1726.1	1728.7
175°	1735.8	1737.8	1739.9	1741.9	1742.9	1741.8	1739.5	1737.2	1734.9	1732.6	1734.9
177.5°	1738.7	1741.0	1743.3	1745.6	1746.8	1745.4	1742.5	1739.6	1736.7	1733.8	1736.7
180°	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0

TEST NUMBER: P1031735

CATALOG NUMBER: S123DIW-B560D1320UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5
2.5°	847.2	849.5	843.4	841.9	841.9	844.9	842.6	822.0	825.8	821.2	819.7
5°	940.7	936.1	930.0	926.9	923.1	912.3	911.6	887.8	883.2	867.9	861.0
7.5°	1043.3	1039.5	1021.1	1018.8	1017.3	1007.3	982.1	956.8	938.4	920.8	903.9
10°	1160.5	1149.1	1140.6	1123.8	1115.3	1101.6	1068.6	1044.9	1013.5	986.7	951.4
12.5°	1301.5	1288.5	1260.1	1247.9	1237.1	1198.8	1165.9	1139.1	1077.8	1059.4	1015.8
15°	1404.9	1377.3	1374.3	1347.5	1345.9	1303.8	1241.0	1211.9	1164.4	1097.0	1051.8
17.5°	1516.7	1492.2	1473.1	1440.9	1436.3	1396.5	1350.5	1279.3	1227.2	1162.8	1105.4
20°	1598.7	1585.7	1552.8	1539.7	1512.9	1479.2	1431.7	1343.6	1280.0	1215.7	1145.2
22.5°	1663.8	1650.8	1624.8	1607.1	1591.8	1548.2	1491.5	1416.4	1329.1	1244.8	1172.0
25°	1663.1	1659.2	1648.5	1640.1	1628.6	1596.4	1548.9	1476.9	1379.6	1286.9	1185.8
27.5°	1568.8	1579.6	1597.9	1607.1	1604.8	1600.2	1573.4	1512.9	1425.6	1315.3	1201.9
30°	1372.7	1411.8	1446.3	1492.2	1506.0	1539.7	1555.1	1520.6	1450.9	1348.2	1222.6
32.5°	1138.3	1195.0	1270.1	1295.4	1339.0	1404.1	1476.9	1489.9	1446.3	1367.4	1235.6
35°	933.8	980.5	1038.7	1078.6	1117.6	1223.4	1315.3	1394.9	1409.5	1357.4	1232.5
37.5°	772.9	805.9	857.2	890.9	926.9	1017.3	1146.0	1249.4	1322.2	1323.7	1224.1
40°	656.5	671.0	715.5	740.0	774.5	852.6	967.5	1102.3	1208.8	1257.8	1201.9
42.5°	556.1	575.3	612.1	630.4	652.7	720.8	796.7	924.6	1056.4	1161.3	1160.5
45°	496.4	510.2	527.0	542.4	567.6	608.2	694.8	790.5	916.9	1035.7	1082.4
47.5°	443.5	456.6	473.4	478.0	494.9	533.2	586.0	669.5	787.5	905.5	993.5
50°	399.1	409.8	421.3	429.7	437.4	468.8	508.6	579.1	673.3	787.5	897.0
52.5°	364.6	372.3	382.3	386.8	393.7	416.7	447.4	499.5	576.8	681.0	787.5
55°	332.5	337.8	343.9	351.6	354.7	371.5	395.3	439.7	497.2	590.6	691.7
57.5°	302.6	304.9	308.7	313.3	317.1	331.7	352.4	382.3	432.8	504.8	600.6
60°	268.9	275.0	277.3	281.9	284.2	295.7	311.8	337.1	376.1	438.2	510.2
62.5°	240.5	244.4	248.2	250.5	255.9	259.7	272.7	295.7	327.9	373.8	438.9
65°	215.3	216.8	219.1	221.4	222.9	227.5	239.8	255.1	279.6	320.2	370.8
67.5°	186.1	187.7	190.7	191.5	193.0	199.2	206.1	219.1	239.8	270.4	311.8
70°	157.8	160.1	161.6	163.2	165.5	167.8	175.4	186.1	202.2	223.7	255.9
72.5°	133.3	135.6	135.6	137.1	136.4	139.4	147.1	154.7	165.5	183.1	211.4
75°	108.8	108.8	110.3	111.1	111.8	114.9	118.0	124.1	132.5	146.3	163.9
77.5°	85.8	85.0	86.6	86.6	86.6	88.9	91.9	95.0	100.4	110.3	124.1
80°	62.8	62.8	64.3	65.1	63.6	64.3	65.9	68.9	72.8	79.7	87.3
82.5°	41.4	44.4	43.7	44.4	43.7	45.2	46.0	46.7	48.3	51.3	56.7
85°	25.3	25.3	25.3	26.0	25.3	26.0	26.0	26.0	26.8	28.3	30.6
87.5°	10.7	10.7	10.7	11.5	10.7	10.7	11.5	10.7	11.5	11.5	12.3
90°	37.6	37.1	36.5	36.2	35.6	34.5	33.3	32.2	31.0	27.3	23.5
92.5°	43.3	43.0	42.7	42.6	41.6	39.6	37.6	35.6	33.6	31.0	28.4
95°	49.1	49.1	49.1	49.1	48.1	46.1	44.1	42.1	40.1	36.9	33.7
97.5°	52.4	52.1	51.8	51.7	50.5	48.2	45.9	43.6	41.3	55.9	70.6
100°	53.7	53.4	53.1	53.0	51.8	49.5	47.2	44.9	42.6	87.4	132.2
102.5°	54.4	53.9	53.3	53.0	57.7	67.2	76.7	86.1	95.6	145.6	195.5
105°	55.7	55.1	54.6	54.3	79.7	130.5	181.3	232.1	282.9	308.7	334.6
107.5°	209.6	247.2	284.8	303.6	325.7	369.9	414.2	458.4	502.6	498.3	494.0
110°	437.4	478.4	519.5	540.0	544.7	554.2	563.7	573.2	582.7	579.5	576.4

TEST NUMBER: P1031735

CATALOG NUMBER: S123DIW-B560D1320UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	674.3	674.8	675.4	675.7	674.4	671.8	669.3	666.7	664.1	660.9	657.8
115°	757.4	756.2	755.1	754.5	753.1	750.2	747.3	744.5	741.6	739.0	736.4
117.5°	828.9	828.6	828.3	828.2	827.0	824.7	822.4	820.1	817.8	816.4	815.0
120°	901.8	901.8	901.8	901.8	900.7	898.4	896.1	893.8	891.5	890.6	889.8
122.5°	972.3	972.0	971.7	971.6	970.9	969.4	968.0	966.5	965.1	963.9	962.8
125°	1037.6	1037.1	1036.5	1036.2	1035.9	1035.3	1034.8	1034.2	1033.6	1032.4	1031.3
127.5°	1104.5	1105.1	1105.6	1105.9	1105.5	1104.6	1103.8	1102.9	1102.1	1100.7	1099.2
130°	1166.6	1167.1	1167.7	1168.0	1167.4	1166.3	1165.1	1164.0	1162.8	1161.6	1160.5
132.5°	1223.9	1224.8	1225.7	1226.1	1225.5	1224.4	1223.2	1222.1	1220.9	1220.1	1219.2
135°	1282.1	1282.9	1283.8	1284.2	1283.8	1282.9	1282.1	1281.2	1280.4	1279.2	1278.1
137.5°	1337.1	1337.6	1338.2	1338.5	1337.8	1336.3	1334.9	1333.4	1332.0	1331.4	1330.9
140°	1386.2	1386.7	1387.3	1387.6	1387.0	1385.9	1384.7	1383.6	1382.4	1381.5	1380.7
142.5°	1431.9	1432.8	1433.7	1434.1	1433.7	1432.8	1431.9	1431.1	1430.2	1429.4	1428.5
145°	1476.7	1476.7	1476.7	1476.7	1476.4	1475.9	1475.3	1474.8	1474.2	1473.6	1473.0
147.5°	1513.2	1514.6	1516.1	1516.8	1516.5	1515.9	1515.4	1514.8	1514.2	1513.6	1513.0
150°	1550.8	1551.7	1552.6	1553.0	1552.7	1552.1	1551.6	1551.0	1550.4	1549.8	1549.2
152.5°	1583.0	1584.4	1585.9	1586.6	1586.0	1584.9	1583.7	1582.6	1581.4	1581.1	1580.8
155°	1612.0	1613.7	1615.4	1616.3	1615.6	1614.1	1612.7	1611.2	1609.8	1609.5	1609.2
157.5°	1637.7	1640.0	1642.3	1643.4	1642.5	1640.8	1639.1	1637.4	1635.7	1636.0	1636.2
160°	1660.3	1662.4	1664.4	1665.4	1664.5	1662.8	1661.1	1659.3	1657.6	1657.9	1658.2
162.5°	1681.7	1683.4	1685.1	1686.0	1685.0	1683.0	1681.0	1679.0	1677.0	1677.3	1677.6
165°	1699.1	1701.1	1703.1	1704.1	1703.0	1700.7	1698.4	1696.1	1693.8	1694.1	1694.4
167.5°	1712.6	1714.9	1717.2	1718.3	1717.2	1714.9	1712.6	1710.3	1708.0	1708.0	1708.0
170°	1724.2	1726.5	1728.8	1730.0	1728.8	1726.5	1724.2	1721.9	1719.6	1719.6	1719.6
172.5°	1731.3	1733.8	1736.4	1737.7	1736.6	1734.3	1732.0	1729.7	1727.4	1727.1	1726.8
175°	1737.2	1739.5	1741.8	1742.9	1741.9	1739.9	1737.8	1735.8	1733.8	1733.5	1733.3
177.5°	1739.6	1742.5	1745.4	1746.8	1745.6	1743.3	1741.0	1738.7	1736.4	1736.1	1735.8
180°	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0

TEST NUMBER: P1031735

CATALOG NUMBER: S123DIW-B560D1320UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5
2.5°	812.0	809.7	809.7	808.2	803.6	795.1	794.4	795.9	791.3	786.7	779.8
5°	851.8	837.3	832.7	828.1	818.9	803.6	797.4	792.1	783.7	773.7	763.0
7.5°	885.5	864.9	858.7	850.3	831.9	810.5	796.7	785.2	773.7	759.9	746.9
10°	927.7	897.8	883.2	871.0	845.7	815.8	795.1	778.3	759.9	743.1	726.2
12.5°	975.2	926.9	922.3	892.4	863.3	818.9	793.6	769.1	744.6	723.9	706.3
15°	1015.0	962.1	943.0	923.1	867.2	812.0	787.5	759.9	731.6	709.3	683.3
17.5°	1040.3	996.6	956.0	929.2	871.0	822.0	774.5	743.1	713.2	682.5	661.1
20°	1070.9	1007.3	972.1	936.1	878.6	814.3	766.8	727.7	691.0	663.4	637.3
22.5°	1101.6	1015.8	986.7	947.6	880.2	806.6	753.0	713.9	671.8	644.2	615.9
25°	1098.5	1028.0	979.8	946.8	864.9	799.7	736.9	691.0	651.9	616.7	588.3
27.5°	1100.8	1014.2	965.2	926.9	854.1	789.8	720.1	671.8	631.2	594.4	564.6
30°	1101.6	993.5	950.6	904.7	834.2	766.0	700.9	651.9	609.0	569.2	542.4
32.5°	1099.3	976.7	923.1	881.7	802.8	743.1	678.7	626.6	583.0	546.2	520.9
35°	1093.9	956.8	894.7	842.6	770.6	710.1	658.0	604.4	557.7	524.0	494.9
37.5°	1079.3	935.3	864.9	813.5	733.1	671.8	625.9	581.4	536.2	496.4	471.9
40°	1068.6	906.2	835.0	779.1	692.5	632.7	594.4	552.3	507.9	471.9	448.1
42.5°	1044.1	878.6	804.3	737.7	652.7	591.4	555.4	521.7	483.4	448.1	426.7
45°	1004.3	848.8	766.8	699.4	609.0	550.8	517.8	490.3	456.6	422.9	401.4
47.5°	948.4	805.9	727.0	659.6	566.1	507.1	474.2	453.5	426.7	398.3	380.0
50°	887.8	759.1	686.4	619.7	524.7	467.3	435.1	416.0	398.3	372.3	354.7
52.5°	808.9	709.3	639.6	576.1	480.3	425.1	396.8	383.0	364.6	346.2	330.9
55°	732.3	645.0	587.5	527.0	436.6	385.3	357.7	343.2	332.5	317.1	304.9
57.5°	643.5	585.3	532.4	477.2	396.0	349.3	323.3	305.6	298.8	291.9	280.4
60°	561.5	517.1	474.2	428.2	353.9	311.8	286.5	272.7	265.8	261.2	253.6
62.5°	486.4	452.0	415.2	378.4	311.0	272.7	253.6	239.8	233.6	232.9	226.0
65°	414.4	389.9	360.0	324.0	271.2	237.5	219.1	210.7	203.8	203.8	198.4
67.5°	342.4	325.6	301.8	276.5	235.2	203.8	186.9	179.3	175.4	175.4	171.6
70°	285.0	273.5	252.0	229.8	193.8	170.1	157.0	150.1	147.8	148.6	145.5
72.5°	231.3	219.1	201.5	185.4	158.6	141.0	131.8	124.1	120.3	121.0	120.3
75°	179.3	173.1	157.8	145.5	124.1	111.8	103.4	99.6	96.5	97.3	95.8
77.5°	134.8	125.6	117.2	108.8	95.8	85.8	78.9	75.1	72.8	72.8	72.8
80°	91.9	90.4	83.5	78.9	68.2	60.5	55.2	54.4	52.1	52.1	52.1
82.5°	59.8	55.9	52.1	49.0	42.9	38.3	36.0	34.5	33.7	32.9	34.5
85°	32.9	30.6	29.1	26.0	23.7	21.4	19.2	18.4	17.6	18.4	17.6
87.5°	13.0	10.7	10.7	10.0	9.2	8.4	8.4	6.9	6.9	6.1	6.1
90°	19.8	16.1	14.2	12.8	9.9	7.0	4.2	1.3	4.2	7.0	9.9
92.5°	25.9	23.3	22.0	22.9	24.6	26.3	28.0	29.7	28.0	26.3	24.6
95°	30.6	27.4	25.8	31.7	43.5	55.2	67.0	78.8	67.0	55.2	43.5
97.5°	85.2	99.9	107.2	111.2	119.3	127.3	135.4	143.4	135.4	127.3	119.3
100°	177.0	221.8	244.2	241.3	235.6	229.8	224.1	218.3	224.1	229.8	235.6
102.5°	245.5	295.4	320.4	318.5	314.8	311.1	307.3	303.6	307.3	311.1	314.8
105°	360.4	386.3	399.2	397.6	394.5	391.3	388.2	385.0	388.2	391.3	394.5
107.5°	489.7	485.4	483.2	481.9	479.3	476.8	474.2	471.6	474.2	476.8	479.3
110°	573.2	570.1	568.5	567.3	565.0	562.7	560.4	558.1	560.4	562.7	565.0

TEST NUMBER: P1031735

CATALOG NUMBER: S123DIW-B560D1320UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	654.6	651.5	649.9	648.9	646.9	644.8	642.8	640.8	642.8	644.8	646.9
115°	733.9	731.3	730.0	729.1	727.4	725.7	723.9	722.2	723.9	725.7	727.4
117.5°	813.5	812.1	811.4	810.4	808.4	806.3	804.3	802.3	804.3	806.3	808.4
120°	888.9	888.0	887.6	886.3	883.7	881.2	878.6	876.0	878.6	881.2	883.7
122.5°	961.6	960.5	959.9	958.9	956.9	954.9	952.9	950.9	952.9	954.9	956.9
125°	1030.1	1029.0	1028.4	1027.3	1025.0	1022.7	1020.4	1018.1	1020.4	1022.7	1025.0
127.5°	1097.8	1096.3	1095.6	1094.5	1092.2	1089.9	1087.6	1085.3	1087.6	1089.9	1092.2
130°	1159.3	1158.2	1157.6	1156.5	1154.2	1151.9	1149.6	1147.3	1149.6	1151.9	1154.2
132.5°	1218.4	1217.5	1217.1	1215.9	1213.6	1211.3	1209.0	1206.7	1209.0	1211.3	1213.6
135°	1276.9	1275.8	1275.2	1274.3	1272.6	1270.9	1269.1	1267.4	1269.1	1270.9	1272.6
137.5°	1330.3	1329.8	1329.5	1328.3	1326.0	1323.7	1321.4	1319.1	1321.4	1323.7	1326.0
140°	1379.8	1378.9	1378.5	1377.6	1375.9	1374.2	1372.5	1370.8	1372.5	1374.2	1375.9
142.5°	1427.7	1426.8	1426.4	1425.5	1423.8	1422.1	1420.3	1418.6	1420.3	1422.1	1423.8
145°	1472.5	1471.9	1471.6	1470.6	1468.6	1466.5	1464.5	1462.5	1464.5	1466.5	1468.6
147.5°	1512.5	1511.9	1511.6	1510.9	1509.5	1508.0	1506.6	1505.2	1506.6	1508.0	1509.5
150°	1548.7	1548.1	1547.8	1547.4	1546.5	1545.6	1544.8	1543.9	1544.8	1545.6	1546.5
152.5°	1580.5	1580.2	1580.1	1580.0	1579.7	1579.4	1579.1	1578.8	1579.1	1579.4	1579.7
155°	1608.9	1608.6	1608.5	1608.8	1609.4	1609.9	1610.5	1611.1	1610.5	1609.9	1609.4
157.5°	1636.5	1636.8	1636.9	1636.9	1636.9	1636.9	1636.9	1636.9	1636.9	1636.9	1636.9
160°	1658.5	1658.8	1658.9	1659.0	1659.3	1659.6	1659.9	1660.2	1659.9	1659.6	1659.3
162.5°	1677.9	1678.2	1678.3	1678.7	1679.6	1680.5	1681.3	1682.2	1681.3	1680.5	1679.6
165°	1694.7	1695.0	1695.1	1695.5	1696.4	1697.3	1698.1	1699.0	1698.1	1697.3	1696.4
167.5°	1708.0	1708.0	1708.0	1708.6	1709.7	1710.9	1712.0	1713.2	1712.0	1710.9	1709.7
170°	1719.6	1719.6	1719.6	1720.2	1721.3	1722.5	1723.6	1724.8	1723.6	1722.5	1721.3
172.5°	1726.5	1726.2	1726.1	1726.8	1728.3	1729.7	1731.2	1732.6	1731.2	1729.7	1728.3
175°	1733.0	1732.7	1732.6	1733.3	1734.7	1736.2	1737.6	1739.0	1737.6	1736.2	1734.7
177.5°	1735.5	1735.2	1735.1	1735.8	1737.3	1738.7	1740.2	1741.6	1740.2	1738.7	1737.3
180°	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0

TEST NUMBER: P1031735

CATALOG NUMBER: S123DIW-B560D1320UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5
2.5°	778.3	777.5	779.1	774.5	766.8	763.0	752.2	749.9	749.2	749.9	750.7
5°	756.8	756.1	753.8	746.1	736.9	730.0	717.0	716.2	711.6	707.0	709.3
7.5°	736.2	733.1	728.5	718.5	706.3	698.6	687.9	680.2	674.1	670.3	667.2
10°	715.5	710.9	706.3	693.3	677.9	666.5	653.4	647.3	640.4	637.3	634.3
12.5°	688.7	684.1	675.6	660.3	651.1	636.6	623.6	617.4	613.6	607.5	603.6
15°	667.2	658.0	653.4	637.3	618.2	616.7	592.9	591.4	583.7	583.7	577.6
17.5°	642.7	635.8	627.4	611.3	597.5	583.7	571.5	566.9	560.0	558.4	555.4
20°	619.0	609.8	606.7	590.6	576.1	559.2	546.2	541.6	538.5	535.5	537.8
22.5°	594.4	586.8	579.1	564.6	553.8	537.0	529.3	524.7	520.1	518.6	519.4
25°	570.7	563.8	556.1	541.6	530.1	516.3	509.4	507.1	504.8	504.8	504.1
27.5°	547.7	540.8	533.9	520.9	509.4	499.5	494.1	491.8	489.5	491.0	492.6
30°	524.0	517.8	511.7	500.2	491.0	481.8	478.8	477.2	476.5	480.3	480.3
32.5°	502.5	497.2	492.6	481.8	472.6	465.0	462.7	463.5	464.2	466.5	468.0
35°	480.3	476.5	471.9	462.7	455.0	448.1	448.9	448.9	450.4	454.3	457.3
37.5°	460.4	455.0	451.2	443.5	437.4	431.3	433.6	435.9	437.4	442.0	443.5
40°	436.6	434.3	431.3	423.6	418.3	417.5	418.3	419.8	422.9	425.1	427.4
42.5°	417.5	414.4	410.6	404.5	399.9	400.6	401.4	402.9	404.5	408.3	410.6
45°	396.0	393.7	390.7	385.3	381.5	382.3	383.0	383.0	384.5	389.1	390.7
47.5°	372.3	373.1	369.2	363.9	361.6	361.6	361.6	363.1	366.9	368.5	369.2
50°	349.3	347.8	347.0	341.7	340.1	339.4	340.1	340.9	346.2	345.5	347.8
52.5°	324.8	324.8	324.0	321.0	318.7	318.7	317.1	321.0	322.5	324.0	326.3
55°	301.1	298.8	298.0	296.5	293.4	292.6	294.2	298.8	300.3	301.8	304.1
57.5°	275.0	275.0	273.5	271.2	271.2	271.2	271.2	274.2	276.5	278.1	282.7
60°	251.3	248.2	245.9	245.9	245.9	245.1	249.7	249.7	254.3	255.1	256.6
62.5°	222.9	221.4	219.9	220.6	219.9	221.4	222.9	226.0	226.7	229.0	231.3
65°	196.1	196.1	194.6	199.2	196.1	196.1	199.9	199.9	201.5	203.8	206.8
67.5°	170.1	170.8	169.3	169.3	170.8	171.6	172.4	175.4	176.2	179.3	183.1
70°	143.2	144.8	145.5	144.0	145.5	147.1	148.6	149.4	152.4	154.0	156.3
72.5°	119.5	121.0	118.7	119.5	120.3	121.8	122.6	124.1	125.6	130.2	131.8
75°	95.8	95.0	94.2	97.3	95.8	98.8	99.6	99.6	101.1	104.9	106.5
77.5°	73.5	73.5	74.3	72.8	75.1	74.3	75.1	77.4	79.7	79.7	85.8
80°	51.3	52.9	52.9	52.9	53.6	54.4	52.9	56.7	57.5	57.5	59.8
82.5°	32.9	33.7	32.9	34.5	34.5	36.0	35.2	36.0	37.5	39.1	39.8
85°	17.6	17.6	19.2	19.2	18.4	19.2	18.4	19.2	20.7	20.7	21.4
87.5°	6.1	6.1	6.1	6.1	6.9	6.1	6.9	6.9	6.1	6.1	8.4
90°	12.8	14.2	16.1	19.8	23.5	27.3	31.0	32.2	33.3	34.5	35.6
92.5°	22.9	22.0	23.3	25.9	28.4	31.0	33.6	35.6	37.6	39.6	41.6
95°	31.7	25.8	27.4	30.6	33.7	36.9	40.1	42.1	44.1	46.1	48.1
97.5°	111.2	107.2	99.9	85.2	70.6	55.9	41.3	43.6	45.9	48.2	50.5
100°	241.3	244.2	221.8	177.0	132.2	87.4	42.6	44.9	47.2	49.5	51.8
102.5°	318.5	320.4	295.4	245.5	195.5	145.6	95.6	86.1	76.7	67.2	57.7
105°	397.6	399.2	386.3	360.4	334.6	308.7	282.9	232.1	181.3	130.5	79.7
107.5°	481.9	483.2	485.4	489.7	494.0	498.3	502.6	458.4	414.2	369.9	325.7
110°	567.3	568.5	570.1	573.2	576.4	579.5	582.7	573.2	563.7	554.2	544.7

TEST NUMBER: P1031735

CATALOG NUMBER: S123DIW-B560D1320UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	648.9	649.9	651.5	654.6	657.8	660.9	664.1	666.7	669.3	671.8	674.4
115°	729.1	730.0	731.3	733.9	736.4	739.0	741.6	744.5	747.3	750.2	753.1
117.5°	810.4	811.4	812.1	813.5	815.0	816.4	817.8	820.1	822.4	824.7	827.0
120°	886.3	887.6	888.0	888.9	889.8	890.6	891.5	893.8	896.1	898.4	900.7
122.5°	958.9	959.9	960.5	961.6	962.8	963.9	965.1	966.5	968.0	969.4	970.9
125°	1027.3	1028.4	1029.0	1030.1	1031.3	1032.4	1033.6	1034.2	1034.8	1035.3	1035.9
127.5°	1094.5	1095.6	1096.3	1097.8	1099.2	1100.7	1102.1	1102.9	1103.8	1104.6	1105.5
130°	1156.5	1157.6	1158.2	1159.3	1160.5	1161.6	1162.8	1164.0	1165.1	1166.3	1167.4
132.5°	1215.9	1217.1	1217.5	1218.4	1219.2	1220.1	1220.9	1222.1	1223.2	1224.4	1225.5
135°	1274.3	1275.2	1275.8	1276.9	1278.1	1279.2	1280.4	1281.2	1282.1	1282.9	1283.8
137.5°	1328.3	1329.5	1329.8	1330.3	1330.9	1331.4	1332.0	1333.4	1334.9	1336.3	1337.8
140°	1377.6	1378.5	1378.9	1379.8	1380.7	1381.5	1382.4	1383.6	1384.7	1385.9	1387.0
142.5°	1425.5	1426.4	1426.8	1427.7	1428.5	1429.4	1430.2	1431.1	1431.9	1432.8	1433.7
145°	1470.6	1471.6	1471.9	1472.5	1473.0	1473.6	1474.2	1474.8	1475.3	1475.9	1476.4
147.5°	1510.9	1511.6	1511.9	1512.5	1513.0	1513.6	1514.2	1514.8	1515.4	1515.9	1516.5
150°	1547.4	1547.8	1548.1	1548.7	1549.2	1549.8	1550.4	1551.0	1551.6	1552.1	1552.7
152.5°	1580.0	1580.1	1580.2	1580.5	1580.8	1581.1	1581.4	1582.6	1583.7	1584.9	1586.0
155°	1608.8	1608.5	1608.6	1608.9	1609.2	1609.5	1609.8	1611.2	1612.7	1614.1	1615.6
157.5°	1636.9	1636.9	1636.8	1636.5	1636.2	1636.0	1635.7	1637.4	1639.1	1640.8	1642.5
160°	1659.0	1658.9	1658.8	1658.5	1658.2	1657.9	1657.6	1659.3	1661.1	1662.8	1664.5
162.5°	1678.7	1678.3	1678.2	1677.9	1677.6	1677.3	1677.0	1679.0	1681.0	1683.0	1685.0
165°	1695.5	1695.1	1695.0	1694.7	1694.4	1694.1	1693.8	1696.1	1698.4	1700.7	1703.0
167.5°	1708.6	1708.0	1708.0	1708.0	1708.0	1708.0	1708.0	1710.3	1712.6	1714.9	1717.2
170°	1720.2	1719.6	1719.6	1719.6	1719.6	1719.6	1719.6	1721.9	1724.2	1726.5	1728.8
172.5°	1726.8	1726.1	1726.2	1726.5	1726.8	1727.1	1727.4	1729.7	1732.0	1734.3	1736.6
175°	1733.3	1732.6	1732.7	1733.0	1733.3	1733.5	1733.8	1735.8	1737.8	1739.9	1741.9
177.5°	1735.8	1735.1	1735.2	1735.5	1735.8	1736.1	1736.4	1738.7	1741.0	1743.3	1745.6
180°	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0

TEST NUMBER: P1031735

CATALOG NUMBER: S123DIW-B560D1320UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5
2.5°	749.9	750.7	747.6	745.4	751.5	747.6	747.6	748.4	746.9	749.2	748.4
5°	707.8	708.6	703.2	704.8	701.7	700.9	700.2	704.8	704.0	703.2	704.8
7.5°	666.5	666.5	664.2	662.6	662.6	660.3	663.4	662.6	664.2	664.2	666.5
10°	632.0	633.5	629.7	625.9	625.1	625.9	625.9	626.6	627.4	632.7	632.0
12.5°	603.6	601.3	600.6	598.3	594.4	592.9	591.4	599.8	597.5	597.5	597.5
15°	572.2	577.6	576.8	569.9	568.4	571.5	569.9	569.9	577.6	576.8	576.1
17.5°	555.4	553.8	552.3	548.5	549.2	548.5	549.2	549.2	553.8	553.8	553.8
20°	536.2	533.2	533.2	531.6	531.6	529.3	532.4	533.2	536.2	536.2	537.0
22.5°	519.4	517.1	517.1	516.3	517.8	514.8	517.8	518.6	518.6	520.9	520.9
25°	504.8	503.3	503.3	504.8	504.8	504.8	504.8	507.9	505.6	506.3	505.6
27.5°	491.8	492.6	493.3	494.1	493.3	494.1	494.9	496.4	497.2	496.4	494.9
30°	479.5	481.8	482.6	482.6	484.1	484.9	485.7	485.7	486.4	484.1	485.7
32.5°	470.3	470.3	471.9	472.6	474.2	474.9	474.9	476.5	475.7	473.4	474.2
35°	457.3	457.3	460.4	461.9	464.2	463.5	464.2	464.2	465.0	463.5	461.2
37.5°	444.3	445.8	445.8	448.9	449.7	450.4	449.7	451.2	450.4	448.9	448.1
40°	429.0	428.2	429.0	431.3	432.0	432.0	432.0	433.6	433.6	433.6	432.8
42.5°	409.8	412.1	411.4	413.7	412.9	412.9	414.4	416.0	416.7	414.4	415.2
45°	391.4	391.4	393.0	393.0	393.7	393.7	396.8	395.3	396.8	395.3	396.0
47.5°	371.5	372.3	372.3	373.1	374.6	376.1	374.6	375.4	375.4	376.1	374.6
50°	349.3	349.3	350.8	353.1	356.2	354.7	353.9	357.0	354.7	354.7	353.1
52.5°	326.3	328.6	329.4	331.7	334.0	334.8	335.5	334.0	334.8	332.5	333.2
55°	304.1	304.9	307.9	310.2	312.5	312.5	311.8	312.5	313.3	310.2	310.2
57.5°	281.9	284.2	287.3	287.3	290.3	290.3	289.6	289.6	290.3	288.0	287.3
60°	258.2	260.5	264.3	264.3	268.9	269.6	268.1	266.6	266.6	264.3	265.0
62.5°	232.9	235.2	237.5	241.3	244.4	242.8	245.9	242.8	243.6	239.0	239.0
65°	210.7	211.4	215.3	219.1	219.1	220.6	219.1	219.9	217.6	217.6	214.5
67.5°	184.6	184.6	188.4	192.3	196.1	196.1	196.1	193.8	193.8	191.5	191.5
70°	161.6	160.9	164.7	167.0	169.3	170.1	168.5	167.8	166.2	163.9	163.2
72.5°	133.3	134.8	138.7	140.2	144.0	143.2	147.1	142.5	142.5	138.7	137.9
75°	108.0	109.5	113.4	115.7	118.0	118.0	120.3	118.0	114.9	113.4	112.6
77.5°	85.8	85.0	88.1	91.9	92.7	91.9	93.5	92.7	89.6	89.6	88.1
80°	61.3	63.6	66.6	65.9	68.9	68.2	68.2	66.6	66.6	64.3	65.9
82.5°	40.6	42.9	43.7	42.9	43.7	45.2	46.0	45.2	45.2	43.7	44.4
85°	21.4	21.4	23.0	23.7	23.0	23.0	23.7	26.0	24.5	23.0	24.5
87.5°	6.9	6.1	6.1	6.9	6.1	6.1	6.9	6.9	7.7	7.7	7.7
90°	36.2	36.5	37.1	37.6	38.2	38.8	38.2	37.6	37.1	36.5	36.2
92.5°	42.6	42.7	43.0	43.3	43.6	43.9	43.6	43.3	43.0	42.7	42.6
95°	49.1	49.1	49.1	49.1	49.1	49.1	49.1	49.1	49.1	49.1	49.1
97.5°	51.7	51.8	52.1	52.4	52.7	53.0	52.7	52.4	52.1	51.8	51.7
100°	53.0	53.1	53.4	53.7	54.0	54.3	54.0	53.7	53.4	53.1	53.0
102.5°	53.0	53.3	53.9	54.4	55.0	55.6	55.0	54.4	53.9	53.3	53.0
105°	54.3	54.6	55.1	55.7	56.2	56.8	56.2	55.7	55.1	54.6	54.3
107.5°	303.6	284.8	247.2	209.6	172.0	134.4	172.0	209.6	247.2	284.8	303.6
110°	540.0	519.5	478.4	437.4	396.3	355.3	396.3	437.4	478.4	519.5	540.0

TEST NUMBER: P1031735

CATALOG NUMBER: S123DIW-B560D1320UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	675.7	675.4	674.8	674.3	673.7	673.1	673.7	674.3	674.8	675.4	675.7
115°	754.5	755.1	756.2	757.4	758.5	759.7	758.5	757.4	756.2	755.1	754.5
117.5°	828.2	828.3	828.6	828.9	829.2	829.5	829.2	828.9	828.6	828.3	828.2
120°	901.8	901.8	901.8	901.8	901.8	901.8	901.8	901.8	901.8	901.8	901.8
122.5°	971.6	971.7	972.0	972.3	972.6	972.9	972.6	972.3	972.0	971.7	971.6
125°	1036.2	1036.5	1037.1	1037.6	1038.2	1038.8	1038.2	1037.6	1037.1	1036.5	1036.2
127.5°	1105.9	1105.6	1105.1	1104.5	1104.0	1103.4	1104.0	1104.5	1105.1	1105.6	1105.9
130°	1168.0	1167.7	1167.1	1166.6	1166.0	1165.4	1166.0	1166.6	1167.1	1167.7	1168.0
132.5°	1226.1	1225.7	1224.8	1223.9	1223.1	1222.2	1223.1	1223.9	1224.8	1225.7	1226.1
135°	1284.2	1283.8	1282.9	1282.1	1281.2	1280.4	1281.2	1282.1	1282.9	1283.8	1284.2
137.5°	1338.5	1338.2	1337.6	1337.1	1336.5	1335.9	1336.5	1337.1	1337.6	1338.2	1338.5
140°	1387.6	1387.3	1386.7	1386.2	1385.6	1385.0	1385.6	1386.2	1386.7	1387.3	1387.6
142.5°	1434.1	1433.7	1432.8	1431.9	1431.1	1430.2	1431.1	1431.9	1432.8	1433.7	1434.1
145°	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7
147.5°	1516.8	1516.1	1514.6	1513.2	1511.7	1510.3	1511.7	1513.2	1514.6	1516.1	1516.8
150°	1553.0	1552.6	1551.7	1550.8	1550.0	1549.1	1550.0	1550.8	1551.7	1552.6	1553.0
152.5°	1586.6	1585.9	1584.4	1583.0	1581.5	1580.1	1581.5	1583.0	1584.4	1585.9	1586.6
155°	1616.3	1615.4	1613.7	1612.0	1610.2	1608.5	1610.2	1612.0	1613.7	1615.4	1616.3
157.5°	1643.4	1642.3	1640.0	1637.7	1635.4	1633.1	1635.4	1637.7	1640.0	1642.3	1643.4
160°	1665.4	1664.4	1662.4	1660.3	1658.3	1656.3	1658.3	1660.3	1662.4	1664.4	1665.4
162.5°	1686.0	1685.1	1683.4	1681.7	1680.0	1678.3	1680.0	1681.7	1683.4	1685.1	1686.0
165°	1704.1	1703.1	1701.1	1699.1	1697.1	1695.1	1697.1	1699.1	1701.1	1703.1	1704.1
167.5°	1718.3	1717.2	1714.9	1712.6	1710.3	1708.0	1710.3	1712.6	1714.9	1717.2	1718.3
170°	1730.0	1728.8	1726.5	1724.2	1721.9	1719.6	1721.9	1724.2	1726.5	1728.8	1730.0
172.5°	1737.7	1736.4	1733.8	1731.3	1728.7	1726.1	1728.7	1731.3	1733.8	1736.4	1737.7
175°	1742.9	1741.8	1739.5	1737.2	1734.9	1732.6	1734.9	1737.2	1739.5	1741.8	1742.9
177.5°	1746.8	1745.4	1742.5	1739.6	1736.7	1733.8	1736.7	1739.6	1742.5	1745.4	1746.8
180°	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0

TEST NUMBER: P1031735

CATALOG NUMBER: S123DIW-B560D1320UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5
2.5°	750.7	752.2	753.0	749.9	747.6	751.5	756.8	760.7	763.7	767.6	769.9
5°	706.3	711.6	711.6	713.2	715.5	719.3	729.3	736.2	742.3	746.9	750.7
7.5°	668.7	672.6	674.9	678.7	682.5	687.9	699.4	709.3	718.5	723.9	730.0
10°	635.0	638.1	641.9	644.2	651.1	658.8	673.3	681.8	692.5	700.9	708.6
12.5°	602.9	613.6	615.9	615.1	621.3	629.7	644.2	657.3	668.7	677.2	685.6
15°	579.9	583.7	588.3	587.5	600.6	602.9	615.1	630.4	645.8	651.1	658.8
17.5°	554.6	560.7	565.3	567.6	571.5	579.9	591.4	602.9	622.8	623.6	643.5
20°	534.7	540.8	543.9	546.9	549.2	559.2	569.2	582.2	598.3	606.7	617.4
22.5°	521.7	524.7	527.0	529.3	532.4	537.8	550.0	564.6	575.3	584.5	591.4
25°	506.3	509.4	512.5	514.0	516.3	519.4	528.6	540.1	555.4	561.5	568.4
27.5°	495.6	495.6	497.2	497.2	500.2	503.3	510.2	520.9	533.2	540.8	550.0
30°	484.1	483.4	484.1	483.4	482.6	487.2	493.3	502.5	510.9	520.1	526.3
32.5°	472.6	471.9	471.9	472.6	469.6	471.9	474.9	483.4	492.6	497.2	504.1
35°	460.4	458.9	458.9	458.9	457.3	455.8	458.9	466.5	472.6	478.8	484.1
37.5°	448.1	445.8	445.8	444.3	442.8	440.5	440.5	446.6	455.0	457.3	464.2
40°	431.3	431.3	429.7	429.0	427.4	425.9	423.6	429.0	436.6	438.9	444.3
42.5°	414.4	412.1	411.4	411.4	411.4	409.1	407.5	411.4	416.0	419.8	422.9
45°	395.3	393.7	394.5	393.7	392.2	391.4	390.7	392.2	397.6	399.1	402.9
47.5°	374.6	373.8	373.8	373.1	372.3	373.1	370.0	373.8	375.4	376.9	380.0
50°	353.1	352.4	351.6	350.8	350.8	351.6	350.8	350.8	353.9	355.4	358.5
52.5°	331.7	329.4	329.4	328.6	328.6	327.1	328.6	329.4	330.9	332.5	334.0
55°	308.7	308.7	306.4	306.4	304.9	304.9	305.6	304.9	307.9	309.5	309.5
57.5°	286.5	283.4	284.2	282.7	281.1	280.4	280.4	281.9	283.4	283.4	285.0
60°	262.7	259.7	258.9	255.9	257.4	255.1	255.9	255.9	258.9	257.4	258.9
62.5°	239.0	235.2	232.9	231.3	231.3	232.1	230.6	229.8	231.3	232.9	235.9
65°	213.7	211.4	209.1	206.8	206.8	206.1	207.6	205.3	204.5	205.3	206.8
67.5°	187.7	185.4	183.1	180.8	181.6	179.3	177.7	180.0	178.5	179.3	180.8
70°	162.4	160.9	156.3	154.7	154.0	154.7	154.0	152.4	154.7	154.0	154.7
72.5°	137.1	135.6	133.3	129.5	129.5	128.7	127.9	127.9	127.2	127.2	127.2
75°	112.6	109.5	107.2	106.5	104.9	104.2	103.4	101.9	102.6	103.4	101.9
77.5°	87.3	83.5	82.7	82.7	80.4	80.4	81.2	80.4	79.7	79.7	79.7
80°	64.3	61.3	61.3	59.8	58.2	58.2	58.2	58.2	57.5	56.7	57.5
82.5°	41.4	40.6	39.8	39.8	41.4	38.3	39.8	39.1	38.3	38.3	37.5
85°	23.0	23.7	23.0	23.7	22.2	23.0	23.0	23.0	22.2	23.0	21.4
87.5°	8.4	8.4	8.4	9.2	9.2	9.2	9.2	9.2	10.0	9.2	9.2
90°	35.6	34.5	33.3	32.2	31.0	27.3	23.5	19.8	16.1	14.2	12.8
92.5°	41.6	39.6	37.6	35.6	33.6	31.0	28.4	25.9	23.3	22.0	22.9
95°	48.1	46.1	44.1	42.1	40.1	36.9	33.7	30.6	27.4	25.8	31.7
97.5°	50.5	48.2	45.9	43.6	41.3	55.9	70.6	85.2	99.9	107.2	111.2
100°	51.8	49.5	47.2	44.9	42.6	87.4	132.2	177.0	221.8	244.2	241.3
102.5°	57.7	67.2	76.7	86.1	95.6	145.6	195.5	245.5	295.4	320.4	318.5
105°	79.7	130.5	181.3	232.1	282.9	308.7	334.6	360.4	386.3	399.2	397.6
107.5°	325.7	369.9	414.2	458.4	502.6	498.3	494.0	489.7	485.4	483.2	481.9
110°	544.7	554.2	563.7	573.2	582.7	579.5	576.4	573.2	570.1	568.5	567.3

TEST NUMBER: P1031735

CATALOG NUMBER: S123DIW-B560D1320UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	674.4	671.8	669.3	666.7	664.1	660.9	657.8	654.6	651.5	649.9	648.9
115°	753.1	750.2	747.3	744.5	741.6	739.0	736.4	733.9	731.3	730.0	729.1
117.5°	827.0	824.7	822.4	820.1	817.8	816.4	815.0	813.5	812.1	811.4	810.4
120°	900.7	898.4	896.1	893.8	891.5	890.6	889.8	888.9	888.0	887.6	886.3
122.5°	970.9	969.4	968.0	966.5	965.1	963.9	962.8	961.6	960.5	959.9	958.9
125°	1035.9	1035.3	1034.8	1034.2	1033.6	1032.4	1031.3	1030.1	1029.0	1028.4	1027.3
127.5°	1105.5	1104.6	1103.8	1102.9	1102.1	1100.7	1099.2	1097.8	1096.3	1095.6	1094.5
130°	1167.4	1166.3	1165.1	1164.0	1162.8	1161.6	1160.5	1159.3	1158.2	1157.6	1156.5
132.5°	1225.5	1224.4	1223.2	1222.1	1220.9	1220.1	1219.2	1218.4	1217.5	1217.1	1215.9
135°	1283.8	1282.9	1282.1	1281.2	1280.4	1279.2	1278.1	1276.9	1275.8	1275.2	1274.3
137.5°	1337.8	1336.3	1334.9	1333.4	1332.0	1331.4	1330.9	1330.3	1329.8	1329.5	1328.3
140°	1387.0	1385.9	1384.7	1383.6	1382.4	1381.5	1380.7	1379.8	1378.9	1378.5	1377.6
142.5°	1433.7	1432.8	1431.9	1431.1	1430.2	1429.4	1428.5	1427.7	1426.8	1426.4	1425.5
145°	1476.4	1475.9	1475.3	1474.8	1474.2	1473.6	1473.0	1472.5	1471.9	1471.6	1470.6
147.5°	1516.5	1515.9	1515.4	1514.8	1514.2	1513.6	1513.0	1512.5	1511.9	1511.6	1510.9
150°	1552.7	1552.1	1551.6	1551.0	1550.4	1549.8	1549.2	1548.7	1548.1	1547.8	1547.4
152.5°	1586.0	1584.9	1583.7	1582.6	1581.4	1581.1	1580.8	1580.5	1580.2	1580.1	1580.0
155°	1615.6	1614.1	1612.7	1611.2	1609.8	1609.5	1609.2	1608.9	1608.6	1608.5	1608.8
157.5°	1642.5	1640.8	1639.1	1637.4	1635.7	1636.0	1636.2	1636.5	1636.8	1636.9	1636.9
160°	1664.5	1662.8	1661.1	1659.3	1657.6	1657.9	1658.2	1658.5	1658.8	1658.9	1659.0
162.5°	1685.0	1683.0	1681.0	1679.0	1677.0	1677.3	1677.6	1677.9	1678.2	1678.3	1678.7
165°	1703.0	1700.7	1698.4	1696.1	1693.8	1694.1	1694.4	1694.7	1695.0	1695.1	1695.5
167.5°	1717.2	1714.9	1712.6	1710.3	1708.0	1708.0	1708.0	1708.0	1708.0	1708.0	1708.6
170°	1728.8	1726.5	1724.2	1721.9	1719.6	1719.6	1719.6	1719.6	1719.6	1719.6	1720.2
172.5°	1736.6	1734.3	1732.0	1729.7	1727.4	1727.1	1726.8	1726.5	1726.2	1726.1	1726.8
175°	1741.9	1739.9	1737.8	1735.8	1733.8	1733.5	1733.3	1733.0	1732.7	1732.6	1733.3
177.5°	1745.6	1743.3	1741.0	1738.7	1736.4	1736.1	1735.8	1735.5	1735.2	1735.1	1735.8
180°	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0

TEST NUMBER: P1031735

CATALOG NUMBER: S123DIW-B560D1320UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	790.5	790.5	790.5	790.5
2.5°	773.7	776.0	783.7	792.8
5°	758.4	764.5	775.2	789.8
7.5°	741.5	750.7	766.0	784.4
10°	722.4	735.4	754.5	777.5
12.5°	701.7	718.5	743.1	766.8
15°	688.7	705.5	727.7	753.8
17.5°	663.4	683.3	706.3	743.1
20°	637.3	659.6	689.4	726.2
22.5°	617.4	641.2	669.5	708.6
25°	593.7	618.2	648.8	689.4
27.5°	568.4	592.9	627.4	670.3
30°	549.2	573.0	605.9	651.9
32.5°	526.3	549.2	583.7	632.0
35°	500.2	526.3	559.2	608.2
37.5°	480.3	504.1	538.5	585.3
40°	458.9	479.5	513.2	559.2
42.5°	435.9	458.9	488.0	533.9
45°	414.4	431.3	461.2	504.8
47.5°	391.4	410.6	433.6	467.3
50°	366.9	383.0	408.3	431.3
52.5°	343.2	356.2	377.7	395.3
55°	317.9	330.9	347.0	357.7
57.5°	294.2	303.3	314.1	321.0
60°	265.0	274.2	281.1	288.0
62.5°	239.0	245.9	249.7	253.6
65°	212.2	216.0	218.3	221.4
67.5°	183.1	186.9	187.7	192.3
70°	156.3	157.0	158.6	160.9
72.5°	131.0	132.5	131.8	133.3
75°	104.9	106.5	104.9	106.5
77.5°	79.7	81.2	81.2	83.5
80°	57.5	58.2	59.0	59.0
82.5°	37.5	39.8	38.3	39.1
85°	21.4	22.2	22.2	23.0
87.5°	10.0	10.7	10.0	11.5
90°	9.9	7.0	4.2	1.3
92.5°	24.6	26.3	28.0	29.7
95°	43.5	55.2	67.0	78.8
97.5°	119.3	127.3	135.4	143.4
100°	235.6	229.8	224.1	218.3
102.5°	314.8	311.1	307.3	303.6
105°	394.5	391.3	388.2	385.0
107.5°	479.3	476.8	474.2	471.6
110°	565.0	562.7	560.4	558.1

TEST NUMBER: P1031735

CATALOG NUMBER: S123DIW-B560D1320UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	646.9	644.8	642.8	640.8
115°	727.4	725.7	723.9	722.2
117.5°	808.4	806.3	804.3	802.3
120°	883.7	881.2	878.6	876.0
122.5°	956.9	954.9	952.9	950.9
125°	1025.0	1022.7	1020.4	1018.1
127.5°	1092.2	1089.9	1087.6	1085.3
130°	1154.2	1151.9	1149.6	1147.3
132.5°	1213.6	1211.3	1209.0	1206.7
135°	1272.6	1270.9	1269.1	1267.4
137.5°	1326.0	1323.7	1321.4	1319.1
140°	1375.9	1374.2	1372.5	1370.8
142.5°	1423.8	1422.1	1420.3	1418.6
145°	1468.6	1466.5	1464.5	1462.5
147.5°	1509.5	1508.0	1506.6	1505.2
150°	1546.5	1545.6	1544.8	1543.9
152.5°	1579.7	1579.4	1579.1	1578.8
155°	1609.4	1609.9	1610.5	1611.1
157.5°	1636.9	1636.9	1636.9	1636.9
160°	1659.3	1659.6	1659.9	1660.2
162.5°	1679.6	1680.5	1681.3	1682.2
165°	1696.4	1697.3	1698.1	1699.0
167.5°	1709.7	1710.9	1712.0	1713.2
170°	1721.3	1722.5	1723.6	1724.8
172.5°	1728.3	1729.7	1731.2	1732.6
175°	1734.7	1736.2	1737.6	1739.0
177.5°	1737.3	1738.7	1740.2	1741.6
180°	1739.0	1739.0	1739.0	1739.0

(END OF REPORT)