

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031746

Luminaire Tested: S123DIW-B560D1320UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031746
REPORT IS A COMBINATION OF REPORTS P991630 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B560D1320UB40-4F0-XX-W2A-F1
Description: Define 3 Direct/Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6850.0 lumens
Efficiency: N/A
Efficacy: 103.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 66.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031746

CATALOG NUMBER: S123DIW-B560D1320UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1031746

CATALOG NUMBER: S123DIW-B560D1320UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41
1	94	90	86	83	85	81	78	75	65	63	61	50	49	47	36	35	35
2	86	78	72	67	77	71	66	61	57	53	50	44	41	39	32	30	29
3	78	69	62	56	70	62	56	51	50	46	42	39	36	33	28	26	25
4	71	61	53	47	64	55	48	43	44	40	36	34	31	28	25	23	21
5	65	54	46	40	59	49	42	37	40	35	31	31	27	25	23	20	18
6	60	48	40	35	54	44	37	32	36	30	27	28	24	21	20	18	16
7	55	44	36	30	50	40	33	28	32	27	23	25	22	19	19	16	14
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	15	13
9	48	36	29	24	43	33	26	22	27	22	18	21	18	15	16	13	12
10	45	33	26	21	40	30	24	20	25	20	17	19	16	13	15	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9496	9496	9496
5°	9520	9168	9155
10°	9435	8858	8767
15°	9304	8535	8345
20°	9154	8177	7926
25°	8959	7799	7479
30°	8746	7408	7008
35°	8523	7008	6541
40°	8289	6588	6081
45°	8033	6180	5601
50°	7771	5723	5118
55°	7436	5250	4629
60°	7090	4726	4109
65°	6766	4159	3567
70°	6299	3530	2934
75°	5626	2795	2277
80°	4859	1964	1612
85°	3785	1055	807

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8033 cd/sqm

TEST NUMBER: P1031746

CATALOG NUMBER: S123DIW-B560D1320UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.2	1.2
10°-20°	234.8	3.4
20°-30°	346.8	5.1
30°-40°	405.1	5.9
40°-50°	407.2	5.9
50°-60°	357.7	5.2
60°-70°	266.4	3.9
70°-80°	151.6	2.2
80°-90°	46.6	0.7
90°-100°	105.7	1.5
100°-110°	320.0	4.7
110°-120°	544.7	8.0
120°-130°	716.6	10.5
130°-140°	805.5	11.8
140°-150°	791.9	11.6
150°-160°	666.7	9.7
160°-170°	443.9	6.5
170°-180°	155.4	2.3
0°-30°	664.8	9.7
0°-40°	1069.9	15.6
0°-60°	1834.9	26.8
0°-90°	2299.4	33.6
90°-120°	970.4	14.2
90°-150°	3284.5	47.9
90°-180°	4551.0	66.4
0°-180°	6850.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	882	882	882	882	882	
5°	883	879	871	878	877	84
15°	840	838	828	834	829	237
25°	763	759	749	750	747	352
35°	660	655	646	641	637	413
45°	541	538	528	519	515	418
55°	410	410	400	391	388	368
65°	280	276	268	262	260	276
75°	148	145	143	139	136	158
85°	39	38	38	36	36	42
90°	1	14	31	36	39	8
95°	76	85	96	101	101	84
105°	290	293	304	304	307	311
115°	548	552	550	551	550	543
125°	802	806	804	799	793	716
135°	1041	1049	1048	1042	1040	802
145°	1263	1266	1270	1268	1263	789
155°	1446	1446	1448	1453	1444	666
165°	1575	1571	1571	1579	1570	444
175°	1638	1633	1633	1641	1632	156
180°	1642	1642	1642	1642	1642	

TEST NUMBER: P1031746

CATALOG NUMBER: S123DIW-B560D1320UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	882.2	882.2	882.2	882.2	882.2
2.5°	886.0	883.0	874.6	882.2	881.5
5°	883.0	879.2	870.8	878.4	876.9
7.5°	876.1	872.3	864.0	870.8	870.1
10°	867.0	863.2	853.4	860.2	858.7
12.5°	854.9	851.9	842.8	847.3	846.6
15°	840.5	837.5	827.6	833.7	829.1
17.5°	824.6	820.8	810.9	815.5	813.9
20°	806.4	801.8	791.9	795.0	792.7
22.5°	785.9	781.3	771.5	773.7	770.7
25°	763.1	758.6	748.7	749.5	747.2
27.5°	739.6	735.0	724.4	725.2	722.9
30°	713.8	710.0	699.4	699.4	694.1
32.5°	688.0	682.7	675.1	669.8	667.5
35°	660.0	655.4	645.5	641.0	637.2
37.5°	631.9	625.8	616.0	610.6	608.4
40°	602.3	597.7	587.1	581.1	578.0
42.5°	572.7	567.4	556.8	550.7	547.7
45°	540.9	537.8	528.0	518.9	515.1
47.5°	509.8	505.2	496.1	487.0	484.0
50°	477.9	474.1	464.2	455.9	451.3
52.5°	444.5	442.2	431.6	424.8	420.2
55°	410.4	409.6	399.8	391.4	387.6
57.5°	378.5	375.5	367.9	360.3	355.8
60°	343.6	342.9	333.8	326.9	323.1
62.5°	312.5	310.3	301.1	294.3	292.0
65°	279.9	276.1	268.5	262.5	260.2
67.5°	245.0	242.0	235.9	230.6	227.6
70°	213.9	209.4	204.8	199.5	195.7
72.5°	181.3	178.3	173.0	168.4	166.9
75°	147.9	144.9	142.6	138.8	136.5
77.5°	118.3	116.8	113.8	110.8	110.8
80°	89.5	87.2	85.7	85.0	85.0
82.5°	61.4	61.4	61.4	59.9	59.2
85°	39.4	37.9	37.9	36.4	36.4
87.5°	19.7	17.4	16.7	15.9	15.9
90°	1.3	14.2	31.0	36.1	38.7
92.5°	38.7	46.4	54.2	58.1	55.5
95°	76.1	85.1	95.5	100.6	100.6
97.5°	125.1	131.6	139.3	145.8	144.5
100°	175.5	183.2	189.6	193.5	196.1
102.5°	233.5	237.4	246.4	250.3	249.0
105°	290.3	292.9	304.5	304.5	307.0
107.5°	357.4	358.6	363.8	367.7	366.4
110°	419.3	421.9	424.4	429.6	427.0

TEST NUMBER: P1031746

CATALOG NUMBER: S123DIW-B560D1320UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	483.8	485.1	485.1	491.5	491.5
115°	548.3	552.2	549.6	550.9	549.6
117.5°	614.1	615.4	612.8	612.8	608.9
120°	674.7	682.5	676.0	674.7	672.1
122.5°	737.9	743.1	740.5	736.7	732.8
125°	802.4	806.3	803.7	798.6	793.4
127.5°	861.8	869.5	867.0	859.2	854.1
130°	921.1	931.5	927.6	922.4	913.4
132.5°	980.5	990.8	988.2	981.8	975.3
135°	1041.1	1048.9	1047.6	1042.4	1039.8
137.5°	1096.6	1103.0	1106.9	1100.5	1096.6
140°	1154.6	1161.1	1162.4	1161.1	1152.1
142.5°	1207.5	1214.0	1216.6	1215.3	1208.8
145°	1263.0	1265.6	1269.5	1268.2	1263.0
147.5°	1310.7	1315.9	1319.8	1319.8	1312.0
150°	1361.1	1363.6	1366.2	1366.2	1358.5
152.5°	1402.3	1406.2	1407.5	1410.1	1403.6
155°	1446.2	1446.2	1447.5	1452.7	1443.6
157.5°	1483.6	1482.3	1483.6	1488.8	1481.0
160°	1518.5	1515.9	1515.9	1522.3	1517.2
162.5°	1549.4	1545.5	1546.8	1553.3	1544.3
165°	1575.2	1571.3	1571.3	1579.1	1570.1
167.5°	1597.2	1592.0	1593.3	1601.0	1593.3
170°	1615.2	1610.1	1610.1	1619.1	1610.1
172.5°	1629.4	1624.2	1624.2	1632.0	1623.0
175°	1638.4	1633.3	1633.3	1641.0	1632.0
177.5°	1643.6	1638.4	1638.4	1646.2	1637.1
180°	1642.3	1642.3	1642.3	1642.3	1642.3

(END OF REPORT)