

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031281

Luminaire Tested: S123DIW-B1000D1030UB35-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031281
REPORT IS A COMBINATION OF REPORTS P990565 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B1000D1030UB35-4F0-XX-W2A-F1
Description: Define 3 Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7756.0 lumens
Efficiency: N/A
Efficacy: 99.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 78.3
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031281

CATALOG NUMBER: S123DIW-B1000D1030UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1031281

CATALOG NUMBER: S123DIW-B1000D1030UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59
1	98	94	90	87	91	87	84	81	74	72	70	63	61	59	52	51	50
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42
3	82	72	65	59	75	67	61	55	58	53	48	49	45	42	40	38	36
4	75	64	56	50	69	59	52	47	51	46	41	43	39	36	36	33	31
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	29	27
6	63	51	43	37	58	48	40	35	41	35	31	35	31	27	30	26	23
7	58	46	38	32	54	43	36	31	37	32	27	32	27	24	27	23	21
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	25	21	19
9	51	38	31	26	47	36	29	24	31	26	22	27	22	19	23	19	17
10	47	35	28	23	44	33	26	22	29	23	20	25	21	17	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17011	17011	17011
5°	17053	16424	16400
10°	16902	15868	15705
15°	16666	15289	14948
20°	16397	14649	14199
25°	16048	13971	13398
30°	15667	13270	12555
35°	15267	12554	11718
40°	14848	11803	10894
45°	14389	11071	10033
50°	13921	10253	9168
55°	13321	9403	8294
60°	12702	8465	7362
65°	12121	7450	6390
70°	11285	6325	5257
75°	10080	5009	4081
80°	8703	3521	2886
85°	6791	1891	1445

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14389 cd/sqm

TEST NUMBER: P1031281

CATALOG NUMBER: S123DIW-B1000D1030UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.0	1.9
10°-20°	420.7	5.4
20°-30°	621.3	8.0
30°-40°	725.6	9.4
40°-50°	729.5	9.4
50°-60°	640.8	8.3
60°-70°	477.3	6.2
70°-80°	271.6	3.5
80°-90°	80.0	1.0
90°-100°	84.6	1.1
100°-110°	256.0	3.3
110°-120°	435.8	5.6
120°-130°	573.3	7.4
130°-140°	644.4	8.3
140°-150°	633.5	8.2
150°-160°	533.3	6.9
160°-170°	355.1	4.6
170°-180°	124.3	1.6
0°-30°	1191.0	15.4
0°-40°	1916.6	24.7
0°-60°	3286.9	42.4
0°-90°	4115.8	53.1
90°-120°	776.3	10.0
90°-150°	2627.5	33.9
90°-180°	3640.0	46.9
0°-180°	7756.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1580	1580	1580	1580	1580	
5°	1582	1575	1560	1574	1571	150
15°	1506	1500	1482	1493	1485	425
25°	1367	1359	1341	1343	1338	630
35°	1182	1174	1156	1148	1142	740
45°	969	963	946	930	923	748
55°	735	734	716	701	694	659
65°	501	495	481	470	466	495
75°	265	260	256	249	245	283
85°	71	68	68	65	65	76
90°	1	11	25	29	31	9
95°	61	68	76	80	80	67
105°	232	234	244	244	246	249
115°	439	442	440	441	440	434
125°	642	645	643	639	635	572
135°	833	839	838	834	832	642
145°	1010	1012	1016	1014	1010	631
155°	1157	1157	1158	1162	1155	533
165°	1260	1257	1257	1263	1256	355
175°	1311	1306	1306	1313	1306	125
180°	1314	1314	1314	1314	1314	

TEST NUMBER: P1031281

CATALOG NUMBER: S123DIW-B1000D1030UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1580.4	1580.4	1580.4	1580.4	1580.4
2.5°	1587.2	1581.7	1566.8	1580.4	1579.0
5°	1581.7	1574.9	1560.0	1573.6	1570.9
7.5°	1569.5	1562.7	1547.8	1560.0	1558.6
10°	1553.2	1546.4	1528.7	1541.0	1538.2
12.5°	1531.4	1526.0	1509.7	1517.9	1516.5
15°	1505.6	1500.2	1482.5	1493.4	1485.2
17.5°	1477.1	1470.3	1452.6	1460.8	1458.1
20°	1444.5	1436.3	1418.7	1424.1	1420.0
22.5°	1407.8	1399.6	1382.0	1386.1	1380.6
25°	1367.0	1358.9	1341.2	1342.6	1338.5
27.5°	1324.9	1316.7	1297.7	1299.1	1295.0
30°	1278.7	1271.9	1252.9	1252.9	1243.4
32.5°	1232.5	1223.0	1209.4	1199.9	1195.8
35°	1182.2	1174.1	1156.4	1148.2	1141.5
37.5°	1131.9	1121.1	1103.4	1093.9	1089.8
40°	1078.9	1070.8	1051.8	1040.9	1035.5
42.5°	1025.9	1016.4	997.4	986.5	981.1
45°	968.9	963.4	945.8	929.5	922.7
47.5°	913.2	905.0	888.7	872.4	867.0
50°	856.1	849.3	831.6	816.7	808.5
52.5°	796.3	792.2	773.2	761.0	752.8
55°	735.2	733.8	716.1	701.2	694.4
57.5°	678.1	672.6	659.1	645.5	637.3
60°	615.6	614.2	597.9	585.7	578.9
62.5°	559.9	555.8	539.5	527.2	523.2
65°	501.4	494.6	481.0	470.2	466.1
67.5°	438.9	433.5	422.6	413.1	407.7
70°	383.2	375.0	366.9	357.4	350.6
72.5°	324.8	319.3	309.8	301.7	299.0
75°	265.0	259.5	255.5	248.7	244.6
77.5°	212.0	209.3	203.8	198.4	198.4
80°	160.3	156.3	153.6	152.2	152.2
82.5°	110.1	110.1	110.1	107.4	106.0
85°	70.7	67.9	67.9	65.2	65.2
87.5°	35.3	31.3	29.9	28.5	28.5
90°	1.0	11.4	24.8	28.9	31.0
92.5°	31.0	37.2	43.3	46.4	44.4
95°	60.9	68.1	76.4	80.5	80.5
97.5°	100.1	105.3	111.5	116.6	115.6
100°	140.4	146.5	151.7	154.8	156.9
102.5°	186.8	189.9	197.1	200.2	199.2
105°	232.2	234.3	243.6	243.6	245.6
107.5°	285.9	286.9	291.0	294.1	293.1
110°	335.4	337.5	339.5	343.7	341.6

TEST NUMBER: P1031281

CATALOG NUMBER: S123DIW-B1000D1030UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	387.0	388.0	388.0	393.2	393.2
115°	438.6	441.7	439.6	440.7	439.6
117.5°	491.2	492.3	490.2	490.2	487.1
120°	539.8	545.9	540.8	539.8	537.7
122.5°	590.3	594.4	592.4	589.3	586.2
125°	641.9	645.0	643.0	638.8	634.7
127.5°	689.4	695.6	693.5	687.3	683.2
130°	736.9	745.1	742.0	737.9	730.7
132.5°	784.3	792.6	790.5	785.4	780.2
135°	832.8	839.0	838.0	833.9	831.8
137.5°	877.2	882.4	885.5	880.3	877.2
140°	923.7	928.8	929.9	928.8	921.6
142.5°	966.0	971.1	973.2	972.2	967.0
145°	1010.4	1012.4	1015.5	1014.5	1010.4
147.5°	1048.5	1052.7	1055.8	1055.8	1049.6
150°	1088.8	1090.9	1092.9	1092.9	1086.7
152.5°	1121.8	1124.9	1125.9	1128.0	1122.8
155°	1156.9	1156.9	1157.9	1162.1	1154.8
157.5°	1186.8	1185.8	1186.8	1191.0	1184.8
160°	1214.7	1212.6	1212.6	1217.8	1213.7
162.5°	1239.5	1236.4	1237.4	1242.6	1235.3
165°	1260.1	1257.0	1257.0	1263.2	1256.0
167.5°	1277.7	1273.5	1274.6	1280.7	1274.6
170°	1292.1	1288.0	1288.0	1295.2	1288.0
172.5°	1303.5	1299.3	1299.3	1305.5	1298.3
175°	1310.7	1306.5	1306.5	1312.7	1305.5
177.5°	1314.8	1310.7	1310.7	1316.9	1309.6
180°	1313.8	1313.8	1313.8	1313.8	1313.8

(END OF REPORT)