

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031371

Luminaire Tested: S123DIW-B1000D460UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031371
REPORT IS A COMBINATION OF REPORTS P990772 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B1000D460UB40-4F0-XX-W2A-F1
Description: Define 3 Direct/Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5680.0 lumens
Efficiency: N/A
Efficacy: 94.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 60
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031371

CATALOG NUMBER: S123DIW-B1000D460UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1031371

CATALOG NUMBER: S123DIW-B1000D460UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76
1	103	98	94	90	97	93	89	86	84	81	78	75	73	71	67	66	64
2	93	86	79	74	88	81	76	71	73	69	65	66	62	59	59	56	54
3	85	75	68	62	80	72	65	59	65	59	55	58	54	50	52	49	46
4	78	67	58	52	74	64	56	50	58	51	47	52	47	43	47	43	40
5	72	60	51	45	68	57	49	43	52	45	40	47	41	37	42	38	34
6	66	54	45	39	62	51	43	38	47	40	35	42	37	33	38	34	30
7	61	48	40	34	58	46	39	33	42	36	31	39	33	29	35	30	27
8	57	44	36	31	54	42	35	30	39	32	28	35	30	26	32	28	24
9	53	40	33	27	50	39	32	27	36	29	25	33	27	23	30	25	22
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	28	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16841	16841	16841
5°	16884	16260	16236
10°	16733	15710	15549
15°	16500	15138	14799
20°	16234	14502	14058
25°	15889	13832	13264
30°	15511	13138	12430
35°	15115	12429	11601
40°	14701	11685	10784
45°	14245	10959	9933
50°	13783	10151	9078
55°	13187	9310	8211
60°	12575	8380	7288
65°	12000	7375	6326
70°	11173	6261	5204
75°	9978	4958	4041
80°	8616	3484	2858
85°	6724	1874	1432

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14245 cd/sqm

TEST NUMBER: P1031371

CATALOG NUMBER: S123DIW-B1000D460UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.5	2.6
10°-20°	416.5	7.3
20°-30°	615.1	10.8
30°-40°	718.4	12.6
40°-50°	722.2	12.7
50°-60°	634.4	11.2
60°-70°	472.5	8.3
70°-80°	268.9	4.7
80°-90°	77.7	1.4
90°-100°	37.3	0.7
100°-110°	113.0	2.0
110°-120°	192.4	3.4
120°-130°	253.0	4.5
130°-140°	284.4	5.0
140°-150°	279.6	4.9
150°-160°	235.4	4.1
160°-170°	156.7	2.8
170°-180°	54.9	1.0
0°-30°	1179.1	20.8
0°-40°	1897.5	33.4
0°-60°	3254.2	57.3
0°-90°	4073.2	71.7
90°-120°	342.7	6.0
90°-150°	1159.8	20.4
90°-180°	1607.0	28.3
0°-180°	5680.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1565	1565	1565	1565	1565	
5°	1566	1559	1544	1558	1555	149
15°	1491	1485	1468	1478	1470	420
25°	1353	1345	1328	1329	1325	623
35°	1170	1162	1145	1137	1130	732
45°	959	954	936	920	914	741
55°	728	726	709	694	688	652
65°	496	490	476	466	461	490
75°	262	257	253	246	242	280
85°	70	67	67	65	65	75
90°	0	5	11	13	14	7
95°	27	30	34	36	36	30
105°	102	103	108	108	108	110
115°	194	195	194	194	194	192
125°	283	285	284	282	280	253
135°	368	370	370	368	367	283
145°	446	447	448	448	446	279
155°	511	511	511	513	510	235
165°	556	555	555	558	554	157
175°	578	577	577	579	576	55
180°	580	580	580	580	580	

TEST NUMBER: P1031371

CATALOG NUMBER: S123DIW-B1000D460UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1564.6	1564.6	1564.6	1564.6	1564.6
2.5°	1571.3	1566.0	1551.2	1564.6	1563.3
5°	1566.0	1559.2	1544.4	1557.9	1555.2
7.5°	1553.9	1547.1	1532.3	1544.4	1543.1
10°	1537.7	1531.0	1513.5	1525.6	1522.9
12.5°	1516.2	1510.8	1494.7	1502.7	1501.4
15°	1490.6	1485.2	1467.8	1478.5	1470.4
17.5°	1462.4	1455.6	1438.2	1446.2	1443.5
20°	1430.1	1422.0	1404.5	1409.9	1405.9
22.5°	1393.8	1385.7	1368.2	1372.2	1366.9
25°	1353.4	1345.3	1327.8	1329.2	1325.1
27.5°	1311.7	1303.6	1284.8	1286.1	1282.1
30°	1266.0	1259.2	1240.4	1240.4	1231.0
32.5°	1220.2	1210.8	1197.3	1187.9	1183.9
35°	1170.4	1162.4	1144.9	1136.8	1130.1
37.5°	1120.7	1109.9	1092.4	1083.0	1079.0
40°	1068.2	1060.1	1041.3	1030.5	1025.1
42.5°	1015.7	1006.3	987.5	976.7	971.3
45°	959.2	953.8	936.3	920.2	913.5
47.5°	904.1	896.0	879.8	863.7	858.3
50°	847.6	840.8	823.3	808.5	800.5
52.5°	788.4	784.3	765.5	753.4	745.3
55°	727.8	726.5	709.0	694.2	687.5
57.5°	671.3	665.9	652.5	639.0	631.0
60°	609.4	608.1	591.9	579.8	573.1
62.5°	554.3	550.2	534.1	522.0	518.0
65°	496.4	489.7	476.2	465.5	461.4
67.5°	434.5	429.2	418.4	409.0	403.6
70°	379.4	371.3	363.2	353.8	347.1
72.5°	321.5	316.2	306.7	298.7	296.0
75°	262.3	257.0	252.9	246.2	242.2
77.5°	209.9	207.2	201.8	196.4	196.4
80°	158.7	154.7	152.0	150.7	150.7
82.5°	109.0	109.0	109.0	106.3	104.9
85°	70.0	67.3	67.3	64.6	64.6
87.5°	35.0	30.9	29.6	28.3	28.3
90°	0.5	5.0	10.9	12.8	13.7
92.5°	13.7	16.4	19.1	20.5	19.6
95°	26.9	30.1	33.7	35.5	35.5
97.5°	44.2	46.5	49.2	51.5	51.0
100°	62.0	64.7	67.0	68.3	69.2
102.5°	82.5	83.8	87.0	88.4	87.9
105°	102.5	103.4	107.5	107.5	108.4
107.5°	126.2	126.6	128.5	129.8	129.4
110°	148.0	149.0	149.9	151.7	150.8



TEST NUMBER: P1031371

CATALOG NUMBER: S123DIW-B1000D460UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	170.8	171.3	171.3	173.6	173.6
115°	193.6	195.0	194.1	194.5	194.1
117.5°	216.8	217.3	216.4	216.4	215.0
120°	238.2	241.0	238.7	238.2	237.3
122.5°	260.6	262.4	261.5	260.1	258.7
125°	283.3	284.7	283.8	282.0	280.2
127.5°	304.3	307.0	306.1	303.4	301.6
130°	325.2	328.9	327.5	325.7	322.5
132.5°	346.2	349.8	348.9	346.7	344.4
135°	367.6	370.3	369.9	368.1	367.2
137.5°	387.2	389.5	390.8	388.6	387.2
140°	407.7	410.0	410.4	410.0	406.8
142.5°	426.4	428.7	429.6	429.1	426.8
145°	446.0	446.9	448.2	447.8	446.0
147.5°	462.8	464.6	466.0	466.0	463.3
150°	480.6	481.5	482.4	482.4	479.7
152.5°	495.2	496.5	497.0	497.9	495.6
155°	510.7	510.7	511.1	512.9	509.7
157.5°	523.9	523.4	523.9	525.7	523.0
160°	536.2	535.2	535.2	537.5	535.7
162.5°	547.1	545.7	546.2	548.5	545.3
165°	556.2	554.8	554.8	557.6	554.4
167.5°	563.9	562.1	562.6	565.3	562.6
170°	570.3	568.5	568.5	571.7	568.5
172.5°	575.3	573.5	573.5	576.2	573.1
175°	578.5	576.7	576.7	579.4	576.2
177.5°	580.3	578.5	578.5	581.3	578.1
180°	579.9	579.9	579.9	579.9	579.9

(END OF REPORT)