

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031428

Luminaire Tested: S123DIW-B1165D1030UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031428
REPORT IS A COMBINATION OF REPORTS P990904 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B1165D1030UB40-4F0-XX-W2A-F1
Description: Define 3 Direct/Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8347.0 lumens
Efficiency: N/A
Efficacy: 89.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 92.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031428

CATALOG NUMBER: S123DIW-B1165D1030UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1031428

CATALOG NUMBER: S123DIW-B1165D1030UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62
1	99	95	91	87	92	88	85	82	76	74	71	65	63	62	55	54	53
2	90	83	77	71	84	77	72	67	67	63	59	57	54	52	48	46	44
3	82	73	65	59	76	68	61	56	59	54	50	51	47	44	43	40	38
4	75	64	56	50	70	60	53	48	52	47	42	45	41	37	38	35	32
5	69	57	49	43	64	54	46	41	47	41	37	40	36	32	35	31	28
6	64	52	43	37	59	48	41	36	42	36	32	37	32	28	31	28	25
7	59	47	38	33	55	44	36	31	38	32	28	33	29	25	29	25	22
8	55	42	34	29	51	40	33	28	35	29	25	31	26	22	26	23	20
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	21	18
10	48	35	28	23	44	33	27	22	30	24	20	26	21	18	23	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19609	19609	19609
5°	19657	18932	18903
10°	19482	18290	18103
15°	19211	17624	17231
20°	18900	16885	16366
25°	18500	16105	15444
30°	18059	15296	14471
35°	17598	14471	13506
40°	17117	13605	12557
45°	16586	12761	11565
50°	16047	11819	10569
55°	15354	10839	9560
60°	14642	9758	8486
65°	13972	8588	7366
70°	13008	7290	6059
75°	11617	5773	4703
80°	10033	4057	3326
85°	7828	2180	1667

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16586 cd/sqm

TEST NUMBER: P1031428

CATALOG NUMBER: S123DIW-B1165D1030UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.7	2.1
10°-20°	484.9	5.8
20°-30°	716.2	8.6
30°-40°	836.4	10.0
40°-50°	840.9	10.1
50°-60°	738.7	8.8
60°-70°	550.1	6.6
70°-80°	313.1	3.8
80°-90°	91.7	1.1
90°-100°	83.7	1.0
100°-110°	253.4	3.0
110°-120°	431.3	5.2
120°-130°	567.5	6.8
130°-140°	637.8	7.6
140°-150°	627.1	7.5
150°-160°	527.9	6.3
160°-170°	351.5	4.2
170°-180°	123.1	1.5
0°-30°	1372.8	16.4
0°-40°	2209.3	26.5
0°-60°	3788.8	45.4
0°-90°	4743.7	56.8
90°-120°	768.4	9.2
90°-150°	2600.8	31.2
90°-180°	3603.0	43.2
0°-180°	8347.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1822	1822	1822	1822	1822	
5°	1823	1815	1798	1814	1811	173
15°	1736	1729	1709	1721	1712	489
25°	1576	1566	1546	1548	1543	726
35°	1363	1353	1333	1324	1316	853
45°	1117	1110	1090	1071	1064	862
55°	847	846	826	808	800	759
65°	578	570	554	542	537	570
75°	305	299	294	287	282	326
85°	82	78	78	75	75	87
90°	1	11	24	29	31	10
95°	60	67	76	80	80	66
105°	230	232	241	241	243	246
115°	434	437	435	436	435	430
125°	635	638	636	632	628	567
135°	824	830	830	825	823	635
145°	1000	1002	1005	1004	1000	625
155°	1145	1145	1146	1150	1143	527
165°	1247	1244	1244	1250	1243	352
175°	1297	1293	1293	1299	1292	123
180°	1300	1300	1300	1300	1300	

TEST NUMBER: P1031428

CATALOG NUMBER: S123DIW-B1165D1030UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1821.7	1821.7	1821.7	1821.7	1821.7
2.5°	1829.5	1823.2	1806.0	1821.7	1820.1
5°	1823.2	1815.4	1798.2	1813.8	1810.7
7.5°	1809.1	1801.3	1784.1	1798.2	1796.6
10°	1790.3	1782.5	1762.1	1776.2	1773.1
12.5°	1765.3	1759.0	1740.2	1749.6	1748.1
15°	1735.5	1729.3	1708.9	1721.4	1712.0
17.5°	1702.6	1694.8	1674.4	1683.8	1680.7
20°	1665.0	1655.6	1635.3	1641.5	1636.8
22.5°	1622.7	1613.3	1593.0	1597.7	1591.4
25°	1575.8	1566.4	1546.0	1547.6	1542.9
27.5°	1527.2	1517.8	1495.9	1497.4	1492.7
30°	1473.9	1466.1	1444.2	1444.2	1433.2
32.5°	1420.7	1409.7	1394.1	1383.1	1378.4
35°	1362.7	1353.3	1333.0	1323.6	1315.7
37.5°	1304.8	1292.2	1271.9	1260.9	1256.2
40°	1243.7	1234.3	1212.4	1199.8	1193.6
42.5°	1182.6	1171.6	1149.7	1137.2	1130.9
45°	1116.8	1110.5	1090.2	1071.4	1063.6
47.5°	1052.6	1043.2	1024.4	1005.6	999.3
50°	986.8	979.0	958.6	941.4	932.0
52.5°	917.9	913.2	891.3	877.2	867.8
55°	847.4	845.8	825.5	808.2	800.4
57.5°	781.6	775.3	759.7	744.0	734.6
60°	709.6	708.0	689.2	675.1	667.3
62.5°	645.3	640.6	621.8	607.7	603.0
65°	578.0	570.2	554.5	542.0	537.3
67.5°	505.9	499.7	487.1	476.2	469.9
70°	441.7	432.3	422.9	412.0	404.1
72.5°	374.4	368.1	357.1	347.7	344.6
75°	305.4	299.2	294.5	286.6	281.9
77.5°	244.4	241.2	235.0	228.7	228.7
80°	184.8	180.1	177.0	175.4	175.4
82.5°	126.9	126.9	126.9	123.7	122.2
85°	81.5	78.3	78.3	75.2	75.2
87.5°	40.7	36.0	34.5	32.9	32.9
90°	1.0	11.2	24.5	28.6	30.6
92.5°	30.6	36.8	42.9	46.0	43.9
95°	60.3	67.4	75.6	79.7	79.7
97.5°	99.1	104.2	110.3	115.4	114.4
100°	138.9	145.1	150.2	153.2	155.3
102.5°	184.9	188.0	195.1	198.2	197.2
105°	229.8	231.9	241.1	241.1	243.1
107.5°	283.0	284.0	288.1	291.1	290.1
110°	332.0	334.0	336.1	340.2	338.1

TEST NUMBER: P1031428

CATALOG NUMBER: S123DIW-B1165D1030UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	383.1	384.1	384.1	389.2	389.2
115°	434.2	437.2	435.2	436.2	435.2
117.5°	486.3	487.3	485.2	485.2	482.2
120°	534.3	540.4	535.3	534.3	532.2
122.5°	584.3	588.4	586.4	583.3	580.2
125°	635.4	638.5	636.4	632.3	628.3
127.5°	682.4	688.5	686.5	680.3	676.3
130°	729.4	737.6	734.5	730.4	723.3
132.5°	776.4	784.5	782.5	777.4	772.3
135°	824.4	830.5	829.5	825.4	823.4
137.5°	868.3	873.4	876.5	871.4	868.3
140°	914.3	919.4	920.4	919.4	912.2
142.5°	956.2	961.3	963.3	962.3	957.2
145°	1000.1	1002.1	1005.2	1004.2	1000.1
147.5°	1037.9	1042.0	1045.0	1045.0	1038.9
150°	1077.7	1079.8	1081.8	1081.8	1075.7
152.5°	1110.4	1113.5	1114.5	1116.6	1111.4
155°	1145.2	1145.2	1146.2	1150.3	1143.1
157.5°	1174.8	1173.8	1174.8	1178.9	1172.7
160°	1202.4	1200.3	1200.3	1205.4	1201.3
162.5°	1226.9	1223.8	1224.8	1229.9	1222.8
165°	1247.3	1244.2	1244.2	1250.4	1243.2
167.5°	1264.7	1260.6	1261.6	1267.7	1261.6
170°	1279.0	1274.9	1274.9	1282.0	1274.9
172.5°	1290.2	1286.1	1286.1	1292.3	1285.1
175°	1297.4	1293.3	1293.3	1299.4	1292.3
177.5°	1301.4	1297.4	1297.4	1303.5	1296.3
180°	1300.4	1300.4	1300.4	1300.4	1300.4

(END OF REPORT)