

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031445

Luminaire Tested: S123DIW-B1165D1320UB30-4F0-XX-W2A-F

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031445
REPORT IS A COMBINATION OF REPORTS P990951 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B1165D1320UB30-4F0-XX-W2A-F
Description: Define 3 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10050.0 lumens
Efficiency: N/A
Efficacy: 97.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 103.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031445

CATALOG NUMBER: S123DIW-B1165D1320UB30-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1031445

CATALOG NUMBER: S123DIW-B1165D1320UB30-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54
1	97	93	89	85	89	85	82	79	72	69	67	59	57	56	47	46	45
2	88	81	75	70	81	75	69	65	63	59	56	52	49	47	42	40	38
3	81	71	64	58	74	66	59	54	55	51	47	46	42	39	37	35	32
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	30	28
5	68	56	48	42	62	52	45	39	44	38	34	37	32	29	30	27	24
6	62	50	42	36	57	47	39	34	40	34	30	33	29	26	27	24	21
7	58	45	37	32	53	42	35	30	36	30	26	30	26	23	25	21	19
8	53	41	33	28	49	38	31	26	33	27	23	27	23	20	23	19	17
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15
10	46	34	27	22	43	32	26	21	28	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19719	19719	19719
5°	19769	19039	19011
10°	19593	18395	18206
15°	19321	17724	17330
20°	19008	16981	16460
25°	18604	16196	15531
30°	18162	15383	14554
35°	17699	14553	13583
40°	17214	13682	12629
45°	16681	12833	11630
50°	16138	11887	10629
55°	15441	10901	9615
60°	14725	9813	8534
65°	14052	8636	7407
70°	13081	7331	6093
75°	11686	5806	4730
80°	10092	4080	3345
85°	7867	2194	1676

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16681 cd/sqm

TEST NUMBER: P1031445

CATALOG NUMBER: S123DIW-B1165D1320UB30-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.7	1.7
10°-20°	487.7	4.9
20°-30°	720.3	7.2
30°-40°	841.2	8.4
40°-50°	845.7	8.4
50°-60°	742.9	7.4
60°-70°	553.3	5.5
70°-80°	314.9	3.1
80°-90°	93.0	0.9
90°-100°	61.1	0.6
100°-110°	295.2	2.9
110°-120°	723.4	7.2
120°-130°	918.4	9.1
130°-140°	981.1	9.8
140°-150°	917.4	9.1
150°-160°	740.0	7.4
160°-170°	477.5	4.8
170°-180°	164.6	1.6
0°-30°	1380.7	13.7
0°-40°	2221.8	22.1
0°-60°	3810.4	37.9
0°-90°	4771.5	47.5
90°-120°	1079.7	10.7
90°-150°	3896.5	38.8
90°-180°	5279.0	52.5
0°-180°	10050.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1832	1832	1832	1832	1832	
5°	1834	1826	1808	1824	1821	174
15°	1745	1739	1719	1731	1722	492
25°	1585	1575	1555	1556	1552	730
35°	1370	1361	1341	1331	1323	857
45°	1123	1117	1096	1078	1070	867
55°	852	851	830	813	805	763
65°	581	573	558	545	540	573
75°	307	301	296	288	284	328
85°	82	79	79	76	76	88
90°	1	14	31	36	39	10
95°	78	26	40	49	49	94
105°	383	398	282	54	57	406
115°	719	727	738	751	756	710
125°	1014	1024	1029	1032	1034	906
135°	1262	1270	1275	1279	1275	972
145°	1456	1465	1468	1470	1470	912
155°	1604	1602	1603	1609	1602	739
165°	1692	1688	1686	1697	1688	478
175°	1732	1725	1726	1735	1725	165
180°	1732	1732	1732	1732	1732	

TEST NUMBER: P1031445

CATALOG NUMBER: S123DIW-B1165D1320UB30-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1832.0	1832.0	1832.0	1832.0	1832.0
2.5°	1839.9	1833.6	1816.3	1832.0	1830.5
5°	1833.6	1825.7	1808.4	1824.2	1821.0
7.5°	1819.4	1811.6	1794.2	1808.4	1806.8
10°	1800.5	1792.7	1772.2	1786.4	1783.2
12.5°	1775.3	1769.0	1750.1	1759.6	1758.0
15°	1745.4	1739.1	1718.6	1731.2	1721.8
17.5°	1712.3	1704.4	1684.0	1693.4	1690.3
20°	1674.5	1665.1	1644.6	1650.9	1646.2
22.5°	1632.0	1622.5	1602.1	1606.8	1600.5
25°	1584.7	1575.3	1554.8	1556.4	1551.6
27.5°	1535.9	1526.4	1504.4	1506.0	1501.2
30°	1482.3	1474.5	1452.4	1452.4	1441.4
32.5°	1428.8	1417.7	1402.0	1391.0	1386.2
35°	1370.5	1361.0	1340.6	1331.1	1323.2
37.5°	1312.2	1299.6	1279.1	1268.1	1263.4
40°	1250.8	1241.3	1219.3	1206.7	1200.4
42.5°	1189.3	1178.3	1156.3	1143.6	1137.3
45°	1123.2	1116.9	1096.4	1077.5	1069.6
47.5°	1058.6	1049.1	1030.2	1011.3	1005.0
50°	992.4	984.5	964.1	946.7	937.3
52.5°	923.1	918.4	896.3	882.2	872.7
55°	852.2	850.6	830.2	812.8	805.0
57.5°	786.1	779.8	764.0	748.3	738.8
60°	713.6	712.0	693.1	678.9	671.1
62.5°	649.0	644.3	625.4	611.2	606.5
65°	581.3	573.4	557.6	545.0	540.3
67.5°	508.8	502.5	489.9	478.9	472.6
70°	444.2	434.8	425.3	414.3	406.4
72.5°	376.5	370.2	359.2	349.7	346.6
75°	307.2	300.9	296.2	288.3	283.5
77.5°	245.7	242.6	236.3	230.0	230.0
80°	185.9	181.2	178.0	176.4	176.4
82.5°	127.6	127.6	127.6	124.4	122.9
85°	81.9	78.8	78.8	75.6	75.6
87.5°	41.0	36.2	34.7	33.1	33.1
90°	1.3	14.2	30.9	36.0	38.6
92.5°	29.6	21.9	33.4	42.5	43.7
95°	78.5	25.7	39.9	48.9	48.9
97.5°	142.8	106.8	41.2	51.5	52.7
100°	217.4	243.1	42.5	52.7	54.0
102.5°	302.3	319.0	95.2	52.7	55.3
105°	383.3	397.5	281.7	54.0	56.6
107.5°	469.5	481.1	500.4	302.3	133.8
110°	555.7	566.0	580.2	537.7	353.8



TEST NUMBER: P1031445

CATALOG NUMBER: S123DIW-B1165D1320UB30-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	638.0	647.1	661.2	672.8	670.2
115°	719.1	726.8	738.4	751.2	756.4
117.5°	798.8	807.8	814.3	824.6	825.9
120°	872.2	883.7	887.6	897.9	897.9
122.5°	946.8	955.8	960.9	967.4	968.6
125°	1013.7	1024.0	1029.1	1031.7	1034.3
127.5°	1080.6	1090.9	1097.3	1101.1	1098.6
130°	1142.3	1152.6	1157.7	1162.9	1160.3
132.5°	1201.5	1211.8	1215.6	1220.8	1216.9
135°	1261.9	1269.7	1274.8	1278.7	1274.8
137.5°	1313.4	1323.7	1326.3	1332.7	1330.1
140°	1364.9	1372.6	1376.4	1381.6	1379.0
142.5°	1412.4	1420.2	1424.0	1427.9	1424.0
145°	1456.2	1465.2	1467.8	1470.3	1470.3
147.5°	1498.6	1505.1	1507.6	1510.2	1503.8
150°	1537.2	1541.1	1543.7	1546.2	1542.4
152.5°	1572.0	1573.2	1574.5	1579.7	1573.2
155°	1604.1	1601.5	1602.8	1609.3	1601.5
157.5°	1629.8	1629.8	1628.6	1636.3	1626.0
160°	1653.0	1651.7	1650.4	1658.1	1649.1
162.5°	1674.9	1671.0	1669.7	1678.7	1671.0
165°	1691.6	1687.7	1686.4	1696.7	1687.7
167.5°	1705.7	1700.6	1700.6	1710.9	1700.6
170°	1717.3	1712.2	1712.2	1722.5	1712.2
172.5°	1725.0	1718.6	1719.9	1730.2	1718.6
175°	1731.5	1725.0	1726.3	1735.3	1725.0
177.5°	1734.0	1727.6	1728.9	1739.2	1726.3
180°	1731.5	1731.5	1731.5	1731.5	1731.5

(END OF REPORT)