

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031483

Luminaire Tested: S123DIW-B1165D1535UB40-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031483
REPORT IS A COMBINATION OF REPORTS P991030 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B1165D1535UB40-4F0-XX-W2A-A1
Description: Define 3 Direct/Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10249.0 lumens
Efficiency: N/A
Efficacy: 90.3 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 113.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031483

CATALOG NUMBER: S123DIW-B1165D1535UB40-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1031483

CATALOG NUMBER: S123DIW-B1165D1535UB40-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	48	48	48
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41	41	41
2	89	82	76	71	82	75	70	66	64	60	57	53	50	48	43	41	39	34	34	34
3	81	72	65	59	75	67	60	55	56	52	48	47	43	41	38	36	34	29	29	29
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29	25	25	25
5	68	57	49	43	63	53	46	40	45	40	35	38	34	30	31	28	25	22	22	22
6	63	51	43	37	58	47	40	35	41	35	31	34	30	27	28	25	22	20	20	20
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	22	20	17	17	17
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18	16	16	16
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	18	16	14	14	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	13	13	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	17400	17400	17400	17400
5°	17412	20048	17463	14963
10°	17301	24262	17319	13067
15°	17062	28772	17201	11762
20°	16857	33127	16892	10823
25°	16551	33962	16587	10333
30°	16332	28058	16332	10011
35°	16061	18765	15961	9728
40°	15738	13546	15543	9295
45°	15331	10730	14888	8754
50°	14341	9113	13832	8225
55°	13254	8007	12716	7633
60°	12154	6972	11506	7012
65°	10943	5970	10414	6184
70°	9686	4955	9041	5213
75°	8281	3737	7745	4024
80°	6547	2496	6037	2644
85°	4515	1146	3612	1042

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 28063 cd/sqm

TEST NUMBER: P1031483

CATALOG NUMBER: S123DIW-B1165D1535UB40-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.0	1.6
10°-20°	510.6	5.0
20°-30°	859.2	8.4
30°-40°	971.0	9.5
40°-50°	869.7	8.5
50°-60°	702.0	6.8
60°-70°	489.2	4.8
70°-80°	256.8	2.5
80°-90°	65.6	0.6
90°-100°	124.7	1.2
100°-110°	377.3	3.7
110°-120°	642.3	6.3
120°-130°	845.1	8.2
130°-140°	949.9	9.3
140°-150°	933.8	9.1
150°-160°	786.2	7.7
160°-170°	523.4	5.1
170°-180°	183.3	1.8
0°-30°	1528.8	14.9
0°-40°	2499.8	24.4
0°-60°	4071.5	39.7
0°-90°	4883.1	47.6
90°-120°	1144.3	11.2
90°-150°	3873.1	37.8
90°-180°	5366.0	52.4
0°-180°	10249.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1616	1616	1616	1616	1616	
5°	1615	1920	1620	1433	1615	153
15°	1541	2859	1554	1169	1541	436
25°	1410	3393	1413	1032	1410	650
35°	1244	1828	1236	948	1244	778
45°	1032	987	1002	805	1032	790
55°	732	670	702	639	732	655
65°	453	436	431	451	453	451
75°	218	224	204	241	218	233
85°	47	52	38	47	47	54
90°	2	46	2	46	2	10
95°	90	119	90	119	90	99
105°	342	362	342	362	342	366
115°	646	648	646	648	646	640
125°	946	936	946	936	946	844
135°	1228	1226	1228	1226	1228	946
145°	1489	1489	1489	1489	1489	930
155°	1705	1702	1705	1702	1705	785
165°	1858	1851	1858	1851	1858	524
175°	1932	1924	1932	1924	1932	184
180°	1937	1937	1937	1937	1937	

TEST NUMBER: P1031483

CATALOG NUMBER: S123DIW-B1165D1535UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5
2.5°	1621.2	1633.8	1640.0	1649.4	1658.8	1672.9	1677.6	1685.5	1682.3	1688.6	1691.7
5°	1615.0	1636.9	1655.7	1679.2	1701.1	1716.8	1732.5	1757.5	1776.3	1779.5	1793.6
7.5°	1604.0	1635.3	1668.2	1701.1	1743.4	1768.5	1796.7	1831.1	1859.3	1904.8	1922.0
10°	1589.9	1633.8	1680.8	1726.2	1784.2	1823.3	1857.8	1915.7	1973.7	2020.7	2064.5
12.5°	1568.0	1622.8	1683.9	1751.3	1826.4	1871.9	1918.9	1995.6	2083.3	2155.4	2202.4
15°	1541.4	1610.3	1688.6	1760.7	1843.7	1928.3	1978.4	2064.5	2189.9	2257.2	2377.8
17.5°	1519.4	1589.9	1668.2	1781.0	1893.8	1978.4	2014.4	2172.6	2258.8	2371.6	2507.8
20°	1485.0	1574.3	1674.5	1787.3	1933.0	1984.7	2058.3	2218.1	2324.6	2471.8	2639.4
22.5°	1448.9	1544.5	1665.1	1782.6	1945.5	2000.3	2100.6	2227.5	2396.6	2542.3	2727.1
25°	1409.8	1513.2	1635.3	1774.8	1934.5	2014.4	2108.4	2265.0	2448.3	2631.6	2802.3
27.5°	1370.6	1483.4	1610.3	1749.7	1904.8	1998.8	2092.7	2255.6	2490.6	2689.5	2907.3
30°	1333.0	1445.8	1572.7	1715.2	1878.1	1969.0	2058.3	2261.9	2523.5	2747.5	2966.8
32.5°	1292.3	1408.2	1541.4	1660.4	1824.9	1922.0	2022.3	2261.9	2543.9	2782.0	2982.5
35°	1243.7	1362.8	1477.1	1596.2	1759.1	1867.2	1980.0	2246.2	2562.7	2792.9	2916.7
37.5°	1196.7	1301.7	1400.4	1516.3	1687.0	1803.0	1933.0	2227.5	2553.3	2745.9	2780.4
40°	1143.5	1248.4	1328.3	1436.4	1616.5	1751.3	1882.8	2202.4	2512.5	2634.7	2534.5
42.5°	1091.8	1174.8	1243.7	1348.7	1544.5	1676.1	1818.6	2157.0	2432.7	2457.7	2232.2
45°	1032.3	1091.8	1152.9	1271.9	1466.2	1600.9	1759.1	2091.2	2304.2	2232.2	1947.1
47.5°	955.5	1008.8	1076.1	1185.8	1383.2	1522.6	1672.9	2006.6	2117.8	1967.4	1655.7
50°	881.9	927.3	990.0	1096.5	1295.4	1431.7	1591.5	1873.4	1928.3	1691.7	1427.0
52.5°	808.3	842.7	903.8	1010.3	1209.3	1340.9	1486.5	1737.2	1705.8	1452.1	1217.1
55°	731.5	761.3	819.2	924.2	1109.0	1234.3	1373.8	1569.6	1488.1	1246.9	1058.9
57.5°	656.3	687.7	747.2	834.9	1008.8	1131.0	1242.2	1395.7	1273.5	1080.8	914.8
60°	589.0	615.6	661.0	747.2	905.4	1004.1	1105.9	1210.8	1109.0	922.6	795.7
62.5°	518.5	543.5	585.8	664.2	800.4	888.2	969.6	1055.8	943.0	806.7	693.9
65°	452.7	473.1	512.2	584.3	695.5	767.5	833.3	892.9	802.0	676.7	592.1
67.5°	393.2	410.4	443.3	507.5	601.5	653.2	706.5	756.6	679.8	579.6	507.5
70°	328.9	343.0	372.8	419.8	495.0	548.2	587.4	625.0	556.1	476.2	427.6
72.5°	272.6	286.7	305.5	354.0	405.7	438.6	480.9	501.3	462.1	396.3	347.7
75°	217.7	228.7	245.9	277.3	325.8	347.7	374.4	390.0	354.0	310.2	280.4
77.5°	170.7	175.4	188.0	209.9	242.8	267.9	288.2	297.6	272.6	244.4	219.3
80°	120.6	126.9	136.3	155.1	180.1	188.0	200.5	211.5	195.8	170.7	155.1
82.5°	79.9	87.7	92.4	100.3	115.9	125.3	128.4	137.8	123.7	114.3	108.1
85°	47.0	50.1	51.7	56.4	64.2	68.9	73.6	75.2	72.1	70.5	64.2
87.5°	23.5	23.5	23.5	26.6	28.2	31.3	32.9	32.9	32.9	31.3	29.8
90°	1.5	4.9	8.3	11.6	15.0	16.7	18.9	23.3	27.7	32.1	36.5
92.5°	45.6	47.6	49.7	51.7	53.8	54.8	55.8	57.8	59.9	61.9	63.9
95°	89.8	92.2	94.5	96.9	99.2	100.4	101.8	104.5	107.2	109.9	112.6
97.5°	147.6	149.3	151.0	152.7	154.4	155.2	156.2	158.2	160.3	162.3	164.3
100°	206.9	208.9	210.9	213.0	215.0	216.0	216.8	218.5	220.2	221.9	223.6
102.5°	275.4	276.4	277.4	278.4	279.4	279.9	281.1	283.5	285.8	288.2	290.6
105°	342.3	343.0	343.6	344.3	345.0	345.3	346.8	349.9	352.9	356.0	359.0
107.5°	421.4	421.7	422.1	422.4	422.7	422.9	423.6	424.9	426.3	427.6	429.0
110°	494.4	495.1	495.8	496.5	497.2	497.5	497.8	498.5	499.2	499.8	500.5

TEST NUMBER: P1031483

CATALOG NUMBER: S123DIW-B1165D1535UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	570.5	570.8	571.2	571.5	571.8	572.0	572.0	572.0	572.0	572.0	572.0
115°	646.5	647.5	648.5	649.6	650.6	651.1	650.8	650.1	649.4	648.8	648.1
117.5°	724.1	724.4	724.8	725.1	725.4	725.6	725.3	724.6	723.9	723.3	722.6
120°	795.6	797.6	799.7	801.7	803.8	804.8	803.9	802.2	800.5	798.8	797.1
122.5°	870.2	871.6	872.9	874.3	875.6	876.3	876.0	875.3	874.6	873.9	873.2
125°	946.2	947.2	948.2	949.3	950.3	950.8	950.5	949.8	949.1	948.5	947.8
127.5°	1016.2	1018.2	1020.2	1022.3	1024.3	1025.3	1025.0	1024.3	1023.6	1023.0	1022.3
130°	1086.2	1088.9	1091.6	1094.3	1097.0	1098.4	1097.9	1096.9	1095.8	1094.8	1093.8
132.5°	1156.2	1158.9	1161.6	1164.3	1167.0	1168.3	1168.0	1167.3	1166.6	1166.0	1165.3
135°	1227.7	1229.7	1231.7	1233.8	1235.8	1236.8	1236.6	1236.3	1236.0	1235.6	1235.3
137.5°	1293.1	1294.8	1296.5	1298.2	1299.9	1300.7	1301.2	1302.2	1303.3	1304.3	1305.3
140°	1361.5	1363.2	1364.9	1366.6	1368.3	1369.1	1369.3	1369.6	1370.0	1370.3	1370.7
142.5°	1423.9	1425.6	1427.3	1429.0	1430.7	1431.5	1431.8	1432.5	1433.2	1433.9	1434.6
145°	1489.3	1490.0	1490.7	1491.4	1492.1	1492.4	1492.9	1493.9	1494.9	1495.9	1496.9
147.5°	1545.6	1547.0	1548.3	1549.7	1551.0	1551.7	1552.2	1553.2	1554.3	1555.3	1556.3
150°	1604.9	1605.6	1606.3	1607.0	1607.7	1608.0	1608.3	1609.0	1609.7	1610.3	1611.0
152.5°	1653.6	1654.6	1655.6	1656.7	1657.7	1658.2	1658.4	1658.7	1659.0	1659.4	1659.7
155°	1705.3	1705.3	1705.3	1705.3	1705.3	1705.3	1705.5	1705.8	1706.2	1706.5	1706.9
157.5°	1749.5	1749.1	1748.8	1748.4	1748.1	1747.9	1748.1	1748.4	1748.8	1749.1	1749.5
160°	1790.5	1789.8	1789.2	1788.5	1787.8	1787.5	1787.5	1787.5	1787.5	1787.5	1787.5
162.5°	1827.0	1826.0	1825.0	1824.0	1823.0	1822.5	1822.7	1823.0	1823.3	1823.7	1824.0
165°	1857.5	1856.5	1855.5	1854.4	1853.4	1852.9	1852.9	1852.9	1852.9	1852.9	1852.9
167.5°	1883.3	1881.9	1880.6	1879.2	1877.9	1877.2	1877.4	1877.7	1878.1	1878.4	1878.8
170°	1904.6	1903.2	1901.9	1900.5	1899.2	1898.5	1898.5	1898.5	1898.5	1898.5	1898.5
172.5°	1921.4	1920.0	1918.7	1917.3	1916.0	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3
175°	1932.0	1930.6	1929.3	1927.9	1926.6	1925.9	1925.9	1925.9	1925.9	1925.9	1925.9
177.5°	1938.1	1936.7	1935.4	1934.0	1932.7	1932.0	1932.0	1932.0	1932.0	1932.0	1932.0
180°	1936.6	1936.6	1936.6	1936.6	1936.6	1936.6	1936.6	1936.6	1936.6	1936.6	1936.6

TEST NUMBER: P1031483

CATALOG NUMBER: S123DIW-B1165D1535UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5
2.5°	1702.7	1705.8	1716.8	1724.6	1740.3	1738.7	1738.7	1737.2	1732.5	1740.3	1745.0
5°	1821.7	1848.4	1851.5	1886.0	1887.5	1901.6	1911.0	1903.2	1922.0	1920.4	1906.3
7.5°	1969.0	2005.0	2022.3	2055.1	2092.7	2083.3	2119.4	2125.6	2122.5	2138.2	2149.1
10°	2130.3	2193.0	2236.9	2297.9	2313.6	2323.0	2346.5	2366.9	2407.6	2376.3	2396.6
12.5°	2315.2	2360.6	2418.6	2515.7	2564.2	2595.6	2606.5	2620.6	2648.8	2631.6	2633.2
15°	2470.2	2531.3	2630.0	2750.6	2764.7	2803.9	2794.5	2879.1	2919.8	2858.7	2893.2
17.5°	2631.6	2713.0	2830.5	2935.5	2995.0	3021.6	3046.7	3128.1	3125.0	3115.6	3123.4
20°	2735.0	2868.1	3013.8	3153.2	3170.4	3190.8	3258.2	3292.6	3286.4	3313.0	3330.2
22.5°	2880.7	3021.6	3176.7	3269.1	3308.3	3331.8	3385.0	3407.0	3416.4	3422.6	3411.7
25°	3002.8	3153.2	3267.6	3349.0	3372.5	3385.0	3402.3	3408.5	3403.8	3392.9	3402.3
27.5°	3085.9	3206.5	3284.8	3322.4	3309.8	3289.5	3256.6	3234.7	3186.1	3162.6	3190.8
30°	3120.3	3173.6	3197.1	3134.4	3071.8	3021.6	2959.0	2843.1	2752.2	2778.8	2742.8
32.5°	3065.5	3031.0	2918.2	2756.9	2708.3	2626.9	2449.9	2313.6	2318.3	2246.2	2276.0
35°	2904.1	2747.5	2534.5	2290.1	2225.9	2182.0	1987.8	1958.0	1895.4	1828.0	1846.8
37.5°	2619.1	2390.4	2131.9	1951.8	1856.2	1760.7	1651.0	1585.2	1547.6	1519.4	1541.4
40°	2271.3	1992.5	1779.5	1618.1	1536.7	1475.6	1400.4	1334.6	1292.3	1287.6	1295.4
42.5°	1929.8	1694.9	1499.1	1345.6	1318.9	1246.9	1198.3	1146.6	1134.1	1113.7	1124.7
45°	1633.8	1442.7	1281.3	1156.0	1124.7	1105.9	1046.4	1013.5	999.4	986.8	1005.6
47.5°	1419.2	1218.7	1101.2	1026.0	994.7	963.3	930.5	908.5	897.6	899.1	897.6
50°	1212.4	1065.2	961.8	903.8	885.0	863.1	836.5	822.4	817.7	803.6	814.5
52.5°	1043.2	936.7	864.7	809.8	795.7	780.1	758.1	750.3	739.4	736.2	736.2
55°	907.0	823.9	766.0	730.0	712.7	700.2	687.7	678.3	670.4	670.4	670.4
57.5°	800.4	728.4	686.1	654.8	648.5	636.0	621.9	621.9	610.9	609.3	614.0
60°	709.6	645.4	612.5	585.8	576.4	573.3	559.2	559.2	556.1	548.2	554.5
62.5°	617.2	570.2	542.0	521.6	512.2	512.2	501.3	493.4	493.4	495.0	491.9
65°	532.6	498.1	473.1	457.4	452.7	446.4	444.9	438.6	433.9	435.5	433.9
67.5°	457.4	430.8	413.5	401.0	393.2	390.0	385.3	385.3	382.2	383.8	375.9
70°	390.0	363.4	349.3	336.8	333.6	333.6	327.4	328.9	325.8	330.5	327.4
72.5°	321.1	300.8	289.8	285.1	282.0	280.4	277.3	274.1	272.6	275.7	274.1
75°	260.0	242.8	235.0	231.8	228.7	228.7	227.1	225.6	224.0	224.0	224.0
77.5°	202.1	191.1	181.7	184.8	180.1	181.7	177.0	177.0	178.6	177.0	177.0
80°	148.8	141.0	141.0	137.8	131.6	134.7	134.7	130.0	128.4	131.6	126.9
82.5°	98.7	97.1	94.0	92.4	89.3	90.9	89.3	87.7	86.2	89.3	86.2
85°	58.0	58.0	56.4	53.3	56.4	54.8	53.3	53.3	51.7	51.7	51.7
87.5°	29.8	26.6	26.6	25.1	26.6	23.5	25.1	23.5	21.9	23.5	21.9
90°	37.9	39.2	40.6	41.9	42.6	42.9	43.6	44.3	44.9	45.6	44.9
92.5°	64.9	65.9	67.0	68.0	68.5	68.2	67.5	66.8	66.1	65.4	66.1
95°	114.0	115.3	116.7	118.0	118.7	118.7	118.7	118.7	118.7	118.7	118.7
97.5°	166.0	167.7	169.4	171.1	171.9	171.7	171.4	171.1	170.7	170.4	170.7
100°	224.6	225.6	226.7	227.7	228.2	228.5	229.2	229.9	230.5	231.2	230.5
102.5°	291.6	292.6	293.6	294.6	295.1	294.9	294.6	294.3	293.9	293.6	293.9
105°	359.0	359.0	359.0	359.0	359.0	359.3	360.0	360.7	361.4	362.1	361.4
107.5°	430.0	431.0	432.1	433.1	433.6	433.4	433.1	432.7	432.4	432.0	432.4
110°	501.9	503.2	504.6	505.9	506.6	506.3	505.6	504.9	504.2	503.5	504.2

TEST NUMBER: P1031483

CATALOG NUMBER: S123DIW-B1165D1535UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	573.7	575.4	577.1	578.8	579.6	579.6	579.6	579.6	579.6	579.6	579.6
115°	648.4	648.8	649.1	649.4	649.6	649.4	649.1	648.8	648.4	648.1	648.4
117.5°	722.6	722.6	722.6	722.6	722.6	722.1	721.1	720.0	719.0	718.0	719.0
120°	796.8	796.4	796.1	795.8	795.6	795.3	794.6	793.9	793.3	792.6	793.3
122.5°	872.2	871.2	870.1	869.1	868.6	868.1	867.1	866.1	865.1	864.1	865.1
125°	946.4	945.1	943.7	942.4	941.7	941.0	939.7	938.3	937.0	935.6	937.0
127.5°	1020.3	1018.3	1016.2	1014.2	1013.2	1012.5	1011.2	1009.8	1008.5	1007.1	1008.5
130°	1092.4	1091.1	1089.7	1088.4	1087.7	1086.5	1084.2	1081.8	1079.5	1077.1	1079.5
132.5°	1163.6	1161.9	1160.2	1158.5	1157.7	1156.9	1155.2	1153.5	1151.8	1150.1	1151.8
135°	1233.9	1232.6	1231.2	1229.9	1229.2	1228.9	1228.2	1227.5	1226.8	1226.1	1226.8
137.5°	1303.6	1301.9	1300.2	1298.5	1297.6	1297.1	1296.1	1295.1	1294.1	1293.1	1294.1
140°	1370.3	1370.0	1369.6	1369.3	1369.1	1367.9	1365.6	1363.2	1360.9	1358.5	1360.9
142.5°	1434.2	1433.9	1433.5	1433.2	1433.0	1432.2	1430.5	1428.8	1427.1	1425.4	1427.1
145°	1496.6	1496.2	1495.9	1495.6	1495.4	1494.7	1493.4	1492.0	1490.7	1489.3	1490.7
147.5°	1556.3	1556.3	1556.3	1556.3	1556.3	1555.3	1553.2	1551.2	1549.1	1547.1	1549.1
150°	1611.0	1611.0	1611.0	1611.0	1611.0	1610.0	1608.0	1605.9	1603.9	1601.9	1603.9
152.5°	1660.4	1661.0	1661.7	1662.4	1662.7	1661.9	1660.2	1658.5	1656.8	1655.1	1656.8
155°	1708.3	1709.6	1711.0	1712.3	1713.0	1711.8	1709.4	1707.1	1704.7	1702.3	1704.7
157.5°	1750.8	1752.2	1753.5	1754.8	1755.5	1754.5	1752.5	1750.4	1748.4	1746.4	1748.4
160°	1789.2	1790.9	1792.6	1794.3	1795.1	1794.4	1793.1	1791.7	1790.4	1789.0	1790.4
162.5°	1825.7	1827.4	1829.1	1830.8	1831.6	1830.4	1828.1	1825.7	1823.4	1821.0	1823.4
165°	1854.9	1856.9	1859.0	1861.0	1862.0	1860.8	1858.5	1856.1	1853.8	1851.4	1853.8
167.5°	1880.8	1882.8	1884.9	1886.9	1887.9	1886.9	1884.9	1882.8	1880.8	1878.8	1880.8
170°	1900.9	1903.3	1905.6	1908.0	1909.2	1908.0	1905.6	1903.3	1900.9	1898.5	1900.9
172.5°	1917.3	1919.3	1921.4	1923.4	1924.4	1923.2	1920.9	1918.5	1916.2	1913.8	1916.2
175°	1927.9	1930.0	1932.0	1934.1	1935.1	1933.9	1931.5	1929.2	1926.8	1924.4	1926.8
177.5°	1934.0	1936.0	1938.1	1940.1	1941.1	1939.9	1937.6	1935.2	1932.9	1930.5	1932.9
180°	1936.6	1936.6	1936.6	1936.6	1936.6	1936.6	1936.6	1936.6	1936.6	1936.6	1936.6

TEST NUMBER: P1031483

CATALOG NUMBER: S123DIW-B1165D1535UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5
2.5°	1732.5	1737.2	1724.6	1721.5	1721.5	1727.8	1723.1	1680.8	1688.6	1679.2	1676.1
5°	1923.6	1914.2	1901.6	1895.4	1887.5	1865.6	1864.0	1815.5	1806.1	1774.8	1760.7
7.5°	2133.5	2125.6	2088.0	2083.3	2080.2	2059.8	2008.2	1956.5	1918.9	1882.8	1848.4
10°	2373.1	2349.6	2332.4	2297.9	2280.7	2252.5	2185.2	2136.6	2072.4	2017.6	1945.5
12.5°	2661.4	2634.7	2576.8	2551.7	2529.8	2451.5	2384.1	2329.3	2204.0	2166.4	2077.1
15°	2872.8	2816.4	2810.2	2755.3	2752.2	2666.1	2537.6	2478.1	2381.0	2243.1	2150.7
17.5°	3101.5	3051.4	3012.2	2946.4	2937.0	2855.6	2761.6	2615.9	2509.4	2377.8	2260.3
20°	3269.1	3242.5	3175.1	3148.5	3093.7	3024.8	2927.6	2747.5	2617.5	2485.9	2341.8
22.5°	3402.3	3375.6	3322.4	3286.4	3255.0	3165.7	3049.8	2896.3	2717.7	2545.4	2396.6
25°	3400.7	3392.9	3370.9	3353.7	3330.2	3264.4	3167.3	3020.1	2821.1	2631.6	2424.8
27.5°	3208.0	3230.0	3267.6	3286.4	3281.7	3272.3	3217.4	3093.7	2915.1	2689.5	2457.7
30°	2807.0	2886.9	2957.4	3051.4	3079.6	3148.5	3179.8	3109.3	2966.8	2756.9	2500.0
32.5°	2327.7	2443.6	2597.1	2648.8	2738.1	2871.3	3020.1	3046.7	2957.4	2796.1	2526.6
35°	1909.5	2005.0	2124.1	2205.5	2285.4	2501.6	2689.5	2852.5	2882.2	2775.7	2520.4
37.5°	1580.5	1647.9	1752.8	1821.7	1895.4	2080.2	2343.4	2554.8	2703.6	2706.8	2503.1
40°	1342.4	1372.2	1463.0	1513.2	1583.7	1743.4	1978.4	2254.1	2471.8	2572.1	2457.7
42.5°	1137.2	1176.4	1251.6	1289.2	1334.6	1474.0	1629.1	1890.7	2160.1	2374.7	2373.1
45°	1015.0	1043.2	1077.7	1109.0	1160.7	1243.7	1420.7	1616.5	1875.0	2117.8	2213.4
47.5°	907.0	933.6	968.0	977.4	1011.9	1090.2	1198.3	1369.1	1610.3	1851.5	2031.6
50°	816.1	838.0	861.5	878.8	894.4	958.7	1040.1	1184.2	1376.9	1610.3	1834.3
52.5°	745.6	761.3	781.6	791.0	805.1	852.1	914.8	1021.3	1179.5	1392.5	1610.3
55°	679.8	690.8	703.3	719.0	725.3	759.7	808.3	899.1	1016.6	1207.7	1414.5
57.5°	618.7	623.4	631.3	640.7	648.5	678.3	720.6	781.6	885.0	1032.3	1228.1
60°	549.8	562.3	567.0	576.4	581.1	604.6	637.5	689.2	769.1	896.0	1043.2
62.5°	491.9	499.7	507.5	512.2	523.2	531.0	557.6	604.6	670.4	764.4	897.6
65°	440.2	443.3	448.0	452.7	455.8	465.2	490.3	521.6	571.7	654.8	758.1
67.5°	380.6	383.8	390.0	391.6	394.7	407.3	421.4	448.0	490.3	552.9	637.5
70°	322.7	327.4	330.5	333.6	338.3	343.0	358.7	380.6	413.5	457.4	523.2
72.5°	272.6	277.3	277.3	280.4	278.8	285.1	300.8	316.4	338.3	374.4	432.3
75°	222.4	222.4	225.6	227.1	228.7	235.0	241.2	253.8	271.0	299.2	335.2
77.5°	175.4	173.9	177.0	177.0	177.0	181.7	188.0	194.2	205.2	225.6	253.8
80°	128.4	128.4	131.6	133.1	130.0	131.6	134.7	141.0	148.8	162.9	178.6
82.5°	84.6	90.9	89.3	90.9	89.3	92.4	94.0	95.6	98.7	105.0	115.9
85°	51.7	51.7	51.7	53.3	51.7	53.3	53.3	53.3	54.8	58.0	62.7
87.5°	21.9	21.9	21.9	23.5	21.9	21.9	23.5	21.9	23.5	23.5	25.1
90°	44.3	43.6	42.9	42.6	41.9	40.6	39.2	37.9	36.5	32.1	27.7
92.5°	66.8	67.5	68.2	68.5	68.0	67.0	65.9	64.9	63.9	61.9	59.9
95°	118.7	118.7	118.7	118.7	118.0	116.7	115.3	114.0	112.6	109.9	107.2
97.5°	171.1	171.4	171.7	171.9	171.1	169.4	167.7	166.0	164.3	162.3	160.3
100°	229.9	229.2	228.5	228.2	227.7	226.7	225.6	224.6	223.6	221.9	220.2
102.5°	294.3	294.6	294.9	295.1	294.6	293.6	292.6	291.6	290.6	288.2	285.8
105°	360.7	360.0	359.3	359.0	359.0	359.0	359.0	359.0	359.0	356.0	352.9
107.5°	432.7	433.1	433.4	433.6	433.1	432.1	431.0	430.0	429.0	427.6	426.3
110°	504.9	505.6	506.3	506.6	505.9	504.6	503.2	501.9	500.5	499.8	499.2

TEST NUMBER: P1031483

CATALOG NUMBER: S123DIW-B1165D1535UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	579.6	579.6	579.6	579.6	578.8	577.1	575.4	573.7	572.0	572.0	572.0
115°	648.8	649.1	649.4	649.6	649.4	649.1	648.8	648.4	648.1	648.8	649.4
117.5°	720.0	721.1	722.1	722.6	722.6	722.6	722.6	722.6	722.6	723.3	723.9
120°	793.9	794.6	795.3	795.6	795.8	796.1	796.4	796.8	797.1	798.8	800.5
122.5°	866.1	867.1	868.1	868.6	869.1	870.1	871.2	872.2	873.2	873.9	874.6
125°	938.3	939.7	941.0	941.7	942.4	943.7	945.1	946.4	947.8	948.5	949.1
127.5°	1009.8	1011.2	1012.5	1013.2	1014.2	1016.2	1018.3	1020.3	1022.3	1023.0	1023.6
130°	1081.8	1084.2	1086.5	1087.7	1088.4	1089.7	1091.1	1092.4	1093.8	1094.8	1095.8
132.5°	1153.5	1155.2	1156.9	1157.7	1158.5	1160.2	1161.9	1163.6	1165.3	1166.0	1166.6
135°	1227.5	1228.2	1228.9	1229.2	1229.9	1231.2	1232.6	1233.9	1235.3	1235.6	1236.0
137.5°	1295.1	1296.1	1297.1	1297.6	1298.5	1300.2	1301.9	1303.6	1305.3	1304.3	1303.3
140°	1363.2	1365.6	1367.9	1369.1	1369.3	1369.6	1370.0	1370.3	1370.7	1370.3	1370.0
142.5°	1428.8	1430.5	1432.2	1433.0	1433.2	1433.5	1433.9	1434.2	1434.6	1433.9	1433.2
145°	1492.0	1493.4	1494.7	1495.4	1495.6	1495.9	1496.2	1496.6	1496.9	1495.9	1494.9
147.5°	1551.2	1553.2	1555.3	1556.3	1556.3	1556.3	1556.3	1556.3	1556.3	1555.3	1554.3
150°	1605.9	1608.0	1610.0	1611.0	1611.0	1611.0	1611.0	1611.0	1611.0	1610.3	1609.7
152.5°	1658.5	1660.2	1661.9	1662.7	1662.4	1661.7	1661.0	1660.4	1659.7	1659.4	1659.0
155°	1707.1	1709.4	1711.8	1713.0	1712.3	1711.0	1709.6	1708.3	1706.9	1706.5	1706.2
157.5°	1750.4	1752.5	1754.5	1755.5	1754.8	1753.5	1752.2	1750.8	1749.5	1749.1	1748.8
160°	1791.7	1793.1	1794.4	1795.1	1794.3	1792.6	1790.9	1789.2	1787.5	1787.5	1787.5
162.5°	1825.7	1828.1	1830.4	1831.6	1830.8	1829.1	1827.4	1825.7	1824.0	1823.7	1823.3
165°	1856.1	1858.5	1860.8	1862.0	1861.0	1859.0	1856.9	1854.9	1852.9	1852.9	1852.9
167.5°	1882.8	1884.9	1886.9	1887.9	1886.9	1884.9	1882.8	1880.8	1878.8	1878.4	1878.1
170°	1903.3	1905.6	1908.0	1909.2	1908.0	1905.6	1903.3	1900.9	1898.5	1898.5	1898.5
172.5°	1918.5	1920.9	1923.2	1924.4	1923.4	1921.4	1919.3	1917.3	1915.3	1915.3	1915.3
175°	1929.2	1931.5	1933.9	1935.1	1934.1	1932.0	1930.0	1927.9	1925.9	1925.9	1925.9
177.5°	1935.2	1937.6	1939.9	1941.1	1940.1	1938.1	1936.0	1934.0	1932.0	1932.0	1932.0
180°	1936.6	1936.6	1936.6	1936.6	1936.6	1936.6	1936.6	1936.6	1936.6	1936.6	1936.6

TEST NUMBER: P1031483

CATALOG NUMBER: S123DIW-B1165D1535UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5
2.5°	1660.4	1655.7	1655.7	1652.6	1643.2	1625.9	1624.4	1627.5	1618.1	1608.7	1594.6
5°	1741.9	1712.1	1702.7	1693.3	1674.5	1643.2	1630.6	1619.7	1602.4	1582.1	1560.2
7.5°	1810.8	1768.5	1756.0	1738.7	1701.1	1657.3	1629.1	1605.6	1582.1	1553.9	1527.3
10°	1896.9	1835.8	1806.1	1781.0	1729.3	1668.2	1625.9	1591.5	1553.9	1519.4	1485.0
12.5°	1994.1	1895.4	1886.0	1824.9	1765.4	1674.5	1622.8	1572.7	1522.6	1480.3	1444.2
15°	2075.5	1967.4	1928.3	1887.5	1773.2	1660.4	1610.3	1553.9	1495.9	1450.5	1397.2
17.5°	2127.2	2037.9	1954.9	1900.1	1781.0	1680.8	1583.7	1519.4	1458.3	1395.7	1351.8
20°	2189.9	2059.8	1987.8	1914.2	1796.7	1665.1	1568.0	1488.1	1412.9	1356.5	1303.3
22.5°	2252.5	2077.1	2017.6	1937.7	1799.8	1649.4	1539.8	1459.9	1373.8	1317.4	1259.4
25°	2246.2	2102.1	2003.5	1936.1	1768.5	1635.3	1506.9	1412.9	1333.0	1261.0	1203.0
27.5°	2250.9	2073.9	1973.7	1895.4	1746.6	1615.0	1472.4	1373.8	1290.7	1215.5	1154.5
30°	2252.5	2031.6	1943.9	1849.9	1705.8	1566.4	1433.3	1333.0	1245.3	1163.9	1109.0
32.5°	2247.8	1997.2	1887.5	1803.0	1641.6	1519.4	1387.8	1281.3	1192.0	1116.9	1065.2
35°	2236.9	1956.5	1829.6	1723.1	1575.8	1452.1	1345.6	1235.9	1140.4	1071.4	1011.9
37.5°	2207.1	1912.6	1768.5	1663.5	1499.1	1373.8	1279.8	1188.9	1096.5	1015.0	964.9
40°	2185.2	1853.1	1707.4	1593.1	1416.0	1293.9	1215.5	1129.4	1038.5	964.9	916.4
42.5°	2135.0	1796.7	1644.7	1508.5	1334.6	1209.3	1135.7	1066.7	988.4	916.4	872.5
45°	2053.6	1735.6	1568.0	1430.1	1245.3	1126.3	1058.9	1002.5	933.6	864.7	820.8
47.5°	1939.2	1647.9	1486.5	1348.7	1157.6	1037.0	969.6	927.3	872.5	814.5	776.9
50°	1815.5	1552.3	1403.5	1267.2	1073.0	955.5	889.7	850.6	814.5	761.3	725.3
52.5°	1654.1	1450.5	1308.0	1177.9	982.1	869.4	811.4	783.2	745.6	708.0	676.7
55°	1497.5	1318.9	1201.4	1077.7	892.9	787.9	731.5	701.8	679.8	648.5	623.4
57.5°	1315.8	1196.7	1088.7	975.9	809.8	714.3	661.0	625.0	610.9	596.8	573.3
60°	1148.2	1057.3	969.6	875.6	723.7	637.5	585.8	557.6	543.5	534.1	518.5
62.5°	994.7	924.2	849.0	773.8	636.0	557.6	518.5	490.3	477.8	476.2	462.1
65°	847.4	797.3	736.2	662.6	554.5	485.6	448.0	430.8	416.7	416.7	405.7
67.5°	700.2	665.7	617.2	565.5	480.9	416.7	382.2	366.5	358.7	358.7	350.9
70°	582.7	559.2	515.4	469.9	396.3	347.7	321.1	307.0	302.3	303.9	297.6
72.5°	473.1	448.0	412.0	379.1	324.2	288.2	269.4	253.8	245.9	247.5	245.9
75°	366.5	354.0	322.7	297.6	253.8	228.7	211.5	203.6	197.4	198.9	195.8
77.5°	275.7	256.9	239.7	222.4	195.8	175.4	161.3	153.5	148.8	148.8	148.8
80°	188.0	184.8	170.7	161.3	139.4	123.7	112.8	111.2	106.5	106.5	106.5
82.5°	122.2	114.3	106.5	100.3	87.7	78.3	73.6	70.5	68.9	67.4	70.5
85°	67.4	62.7	59.5	53.3	48.6	43.9	39.2	37.6	36.0	37.6	36.0
87.5°	26.6	21.9	21.9	20.4	18.8	17.2	17.2	14.1	14.1	12.5	12.5
90°	23.3	18.9	16.7	15.0	11.6	8.3	4.9	1.5	4.9	8.3	11.6
92.5°	57.8	55.8	54.8	53.8	51.7	49.7	47.6	45.6	47.6	49.7	51.7
95°	104.5	101.8	100.4	99.2	96.9	94.5	92.2	89.8	92.2	94.5	96.9
97.5°	158.2	156.2	155.2	154.4	152.7	151.0	149.3	147.6	149.3	151.0	152.7
100°	218.5	216.8	216.0	215.0	213.0	210.9	208.9	206.9	208.9	210.9	213.0
102.5°	283.5	281.1	279.9	279.4	278.4	277.4	276.4	275.4	276.4	277.4	278.4
105°	349.9	346.8	345.3	345.0	344.3	343.6	343.0	342.3	343.0	343.6	344.3
107.5°	424.9	423.6	422.9	422.7	422.4	422.1	421.7	421.4	421.7	422.1	422.4
110°	498.5	497.8	497.5	497.2	496.5	495.8	495.1	494.4	495.1	495.8	496.5

TEST NUMBER: P1031483

CATALOG NUMBER: S123DIW-B1165D1535UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	572.0	572.0	572.0	571.8	571.5	571.2	570.8	570.5	570.8	571.2	571.5
115°	650.1	650.8	651.1	650.6	649.6	648.5	647.5	646.5	647.5	648.5	649.6
117.5°	724.6	725.3	725.6	725.4	725.1	724.8	724.4	724.1	724.4	724.8	725.1
120°	802.2	803.9	804.8	803.8	801.7	799.7	797.6	795.6	797.6	799.7	801.7
122.5°	875.3	876.0	876.3	875.6	874.3	872.9	871.6	870.2	871.6	872.9	874.3
125°	949.8	950.5	950.8	950.3	949.3	948.2	947.2	946.2	947.2	948.2	949.3
127.5°	1024.3	1025.0	1025.3	1024.3	1022.3	1020.2	1018.2	1016.2	1018.2	1020.2	1022.3
130°	1096.9	1097.9	1098.4	1097.0	1094.3	1091.6	1088.9	1086.2	1088.9	1091.6	1094.3
132.5°	1167.3	1168.0	1168.3	1167.0	1164.3	1161.6	1158.9	1156.2	1158.9	1161.6	1164.3
135°	1236.3	1236.6	1236.8	1235.8	1233.8	1231.7	1229.7	1227.7	1229.7	1231.7	1233.8
137.5°	1302.2	1301.2	1300.7	1299.9	1298.2	1296.5	1294.8	1293.1	1294.8	1296.5	1298.2
140°	1369.6	1369.3	1369.1	1368.3	1366.6	1364.9	1363.2	1361.5	1363.2	1364.9	1366.6
142.5°	1432.5	1431.8	1431.5	1430.7	1429.0	1427.3	1425.6	1423.9	1425.6	1427.3	1429.0
145°	1493.9	1492.9	1492.4	1492.1	1491.4	1490.7	1490.0	1489.3	1490.0	1490.7	1491.4
147.5°	1553.2	1552.2	1551.7	1551.0	1549.7	1548.3	1547.0	1545.6	1547.0	1548.3	1549.7
150°	1609.0	1608.3	1608.0	1607.7	1607.0	1606.3	1605.6	1604.9	1605.6	1606.3	1607.0
152.5°	1658.7	1658.4	1658.2	1657.7	1656.7	1655.6	1654.6	1653.6	1654.6	1655.6	1656.7
155°	1705.8	1705.5	1705.3	1705.3	1705.3	1705.3	1705.3	1705.3	1705.3	1705.3	1705.3
157.5°	1748.4	1748.1	1747.9	1748.1	1748.4	1748.8	1749.1	1749.5	1749.1	1748.8	1748.4
160°	1787.5	1787.5	1787.5	1787.8	1788.5	1789.2	1789.8	1790.5	1789.8	1789.2	1788.5
162.5°	1823.0	1822.7	1822.5	1823.0	1824.0	1825.0	1826.0	1827.0	1826.0	1825.0	1824.0
165°	1852.9	1852.9	1852.9	1853.4	1854.4	1855.5	1856.5	1857.5	1856.5	1855.5	1854.4
167.5°	1877.7	1877.4	1877.2	1877.9	1879.2	1880.6	1881.9	1883.3	1881.9	1880.6	1879.2
170°	1898.5	1898.5	1898.5	1899.2	1900.5	1901.9	1903.2	1904.6	1903.2	1901.9	1900.5
172.5°	1915.3	1915.3	1915.3	1916.0	1917.3	1918.7	1920.0	1921.4	1920.0	1918.7	1917.3
175°	1925.9	1925.9	1925.9	1926.6	1927.9	1929.3	1930.6	1932.0	1930.6	1929.3	1927.9
177.5°	1932.0	1932.0	1932.0	1932.7	1934.0	1935.4	1936.7	1938.1	1936.7	1935.4	1934.0
180°	1936.6	1936.6	1936.6	1936.6	1936.6	1936.6	1936.6	1936.6	1936.6	1936.6	1936.6

TEST NUMBER: P1031483

CATALOG NUMBER: S123DIW-B1165D1535UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5
2.5°	1591.5	1589.9	1593.1	1583.7	1568.0	1560.2	1538.2	1533.5	1532.0	1533.5	1535.1
5°	1547.6	1546.1	1541.4	1525.7	1506.9	1492.8	1466.2	1464.6	1455.2	1445.8	1450.5
7.5°	1505.3	1499.1	1489.7	1469.3	1444.2	1428.6	1406.6	1391.0	1378.5	1370.6	1364.4
10°	1463.0	1453.6	1444.2	1417.6	1386.3	1362.8	1336.2	1323.6	1309.5	1303.3	1297.0
12.5°	1408.2	1398.8	1381.6	1350.3	1331.5	1301.7	1275.1	1262.5	1254.7	1242.2	1234.3
15°	1364.4	1345.6	1336.2	1303.3	1264.1	1261.0	1212.4	1209.3	1193.6	1193.6	1181.1
17.5°	1314.2	1300.1	1282.9	1250.0	1221.8	1193.6	1168.6	1159.2	1145.1	1141.9	1135.7
20°	1265.7	1246.9	1240.6	1207.7	1177.9	1143.5	1116.9	1107.5	1101.2	1094.9	1099.6
22.5°	1215.5	1199.9	1184.2	1154.5	1132.5	1098.1	1082.4	1073.0	1063.6	1060.5	1062.0
25°	1167.0	1152.9	1137.2	1107.5	1084.0	1055.8	1041.7	1037.0	1032.3	1032.3	1030.7
27.5°	1120.0	1105.9	1091.8	1065.2	1041.7	1021.3	1010.3	1005.6	1000.9	1004.1	1007.2
30°	1071.4	1058.9	1046.4	1022.9	1004.1	985.3	979.0	975.9	974.3	982.1	982.1
32.5°	1027.6	1016.6	1007.2	985.3	966.5	950.8	946.1	947.7	949.3	954.0	957.1
35°	982.1	974.3	964.9	946.1	930.5	916.4	917.9	917.9	921.1	928.9	935.2
37.5°	941.4	930.5	922.6	907.0	894.4	881.9	886.6	891.3	894.4	903.8	907.0
40°	892.9	888.2	881.9	866.2	855.3	853.7	855.3	858.4	864.7	869.4	874.1
42.5°	853.7	847.4	839.6	827.1	817.7	819.2	820.8	823.9	827.1	834.9	839.6
45°	809.8	805.1	798.9	787.9	780.1	781.6	783.2	783.2	786.3	795.7	798.9
47.5°	761.3	762.8	755.0	744.1	739.4	739.4	739.4	742.5	750.3	753.4	755.0
50°	714.3	711.2	709.6	698.6	695.5	693.9	695.5	697.1	708.0	706.5	711.2
52.5°	664.2	664.2	662.6	656.3	651.6	651.6	648.5	656.3	659.5	662.6	667.3
55°	615.6	610.9	609.3	606.2	599.9	598.4	601.5	610.9	614.0	617.2	621.9
57.5°	562.3	562.3	559.2	554.5	554.5	554.5	554.5	560.8	565.5	568.6	578.0
60°	513.8	507.5	502.8	502.8	502.8	501.3	510.7	510.7	520.1	521.6	524.8
62.5°	455.8	452.7	449.6	451.1	449.6	452.7	455.8	462.1	463.7	468.4	473.1
65°	401.0	401.0	397.9	407.3	401.0	401.0	408.8	408.8	412.0	416.7	422.9
67.5°	347.7	349.3	346.2	346.2	349.3	350.9	352.4	358.7	360.3	366.5	374.4
70°	292.9	296.1	297.6	294.5	297.6	300.8	303.9	305.5	311.7	314.9	319.6
72.5°	244.4	247.5	242.8	244.4	245.9	249.1	250.6	253.8	256.9	266.3	269.4
75°	195.8	194.2	192.7	198.9	195.8	202.1	203.6	203.6	206.8	214.6	217.7
77.5°	150.4	150.4	151.9	148.8	153.5	151.9	153.5	158.2	162.9	162.9	175.4
80°	105.0	108.1	108.1	108.1	109.6	111.2	108.1	115.9	117.5	117.5	122.2
82.5°	67.4	68.9	67.4	70.5	70.5	73.6	72.1	73.6	76.8	79.9	81.5
85°	36.0	36.0	39.2	39.2	37.6	39.2	37.6	39.2	42.3	42.3	43.9
87.5°	12.5	12.5	12.5	12.5	14.1	12.5	14.1	14.1	12.5	12.5	17.2
90°	15.0	16.7	18.9	23.3	27.7	32.1	36.5	37.9	39.2	40.6	41.9
92.5°	53.8	54.8	55.8	57.8	59.9	61.9	63.9	64.9	65.9	67.0	68.0
95°	99.2	100.4	101.8	104.5	107.2	109.9	112.6	114.0	115.3	116.7	118.0
97.5°	154.4	155.2	156.2	158.2	160.3	162.3	164.3	166.0	167.7	169.4	171.1
100°	215.0	216.0	216.8	218.5	220.2	221.9	223.6	224.6	225.6	226.7	227.7
102.5°	279.4	279.9	281.1	283.5	285.8	288.2	290.6	291.6	292.6	293.6	294.6
105°	345.0	345.3	346.8	349.9	352.9	356.0	359.0	359.0	359.0	359.0	359.0
107.5°	422.7	422.9	423.6	424.9	426.3	427.6	429.0	430.0	431.0	432.1	433.1
110°	497.2	497.5	497.8	498.5	499.2	499.8	500.5	501.9	503.2	504.6	505.9

TEST NUMBER: P1031483

CATALOG NUMBER: S123DIW-B1165D1535UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	571.8	572.0	572.0	572.0	572.0	572.0	572.0	573.7	575.4	577.1	578.8
115°	650.6	651.1	650.8	650.1	649.4	648.8	648.1	648.4	648.8	649.1	649.4
117.5°	725.4	725.6	725.3	724.6	723.9	723.3	722.6	722.6	722.6	722.6	722.6
120°	803.8	804.8	803.9	802.2	800.5	798.8	797.1	796.8	796.4	796.1	795.8
122.5°	875.6	876.3	876.0	875.3	874.6	873.9	873.2	872.2	871.2	870.1	869.1
125°	950.3	950.8	950.5	949.8	949.1	948.5	947.8	946.4	945.1	943.7	942.4
127.5°	1024.3	1025.3	1025.0	1024.3	1023.6	1023.0	1022.3	1020.3	1018.3	1016.2	1014.2
130°	1097.0	1098.4	1097.9	1096.9	1095.8	1094.8	1093.8	1092.4	1091.1	1089.7	1088.4
132.5°	1167.0	1168.3	1168.0	1167.3	1166.6	1166.0	1165.3	1163.6	1161.9	1160.2	1158.5
135°	1235.8	1236.8	1236.6	1236.3	1236.0	1235.6	1235.3	1233.9	1232.6	1231.2	1229.9
137.5°	1299.9	1300.7	1301.2	1302.2	1303.3	1304.3	1305.3	1303.6	1301.9	1300.2	1298.5
140°	1368.3	1369.1	1369.3	1369.6	1370.0	1370.3	1370.7	1370.3	1370.0	1369.6	1369.3
142.5°	1430.7	1431.5	1431.8	1432.5	1433.2	1433.9	1434.6	1434.2	1433.9	1433.5	1433.2
145°	1492.1	1492.4	1492.9	1493.9	1494.9	1495.9	1496.9	1496.6	1496.2	1495.9	1495.6
147.5°	1551.0	1551.7	1552.2	1553.2	1554.3	1555.3	1556.3	1556.3	1556.3	1556.3	1556.3
150°	1607.7	1608.0	1608.3	1609.0	1609.7	1610.3	1611.0	1611.0	1611.0	1611.0	1611.0
152.5°	1657.7	1658.2	1658.4	1658.7	1659.0	1659.4	1659.7	1660.4	1661.0	1661.7	1662.4
155°	1705.3	1705.3	1705.5	1705.8	1706.2	1706.5	1706.9	1708.3	1709.6	1711.0	1712.3
157.5°	1748.1	1747.9	1748.1	1748.4	1748.8	1749.1	1749.5	1750.8	1752.2	1753.5	1754.8
160°	1787.8	1787.5	1787.5	1787.5	1787.5	1787.5	1787.5	1789.2	1790.9	1792.6	1794.3
162.5°	1823.0	1822.5	1822.7	1823.0	1823.3	1823.7	1824.0	1825.7	1827.4	1829.1	1830.8
165°	1853.4	1852.9	1852.9	1852.9	1852.9	1852.9	1852.9	1854.9	1856.9	1859.0	1861.0
167.5°	1877.9	1877.2	1877.4	1877.7	1878.1	1878.4	1878.8	1880.8	1882.8	1884.9	1886.9
170°	1899.2	1898.5	1898.5	1898.5	1898.5	1898.5	1898.5	1900.9	1903.3	1905.6	1908.0
172.5°	1916.0	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1917.3	1919.3	1921.4	1923.4
175°	1926.6	1925.9	1925.9	1925.9	1925.9	1925.9	1925.9	1927.9	1930.0	1932.0	1934.1
177.5°	1932.7	1932.0	1932.0	1932.0	1932.0	1932.0	1932.0	1934.0	1936.0	1938.1	1940.1
180°	1936.6	1936.6	1936.6	1936.6	1936.6	1936.6	1936.6	1936.6	1936.6	1936.6	1936.6

TEST NUMBER: P1031483

CATALOG NUMBER: S123DIW-B1165D1535UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5
2.5°	1533.5	1535.1	1528.8	1524.1	1536.7	1528.8	1528.8	1530.4	1527.3	1532.0	1530.4
5°	1447.4	1448.9	1438.0	1441.1	1434.8	1433.3	1431.7	1441.1	1439.5	1438.0	1441.1
7.5°	1362.8	1362.8	1358.1	1355.0	1355.0	1350.3	1356.5	1355.0	1358.1	1358.1	1362.8
10°	1292.3	1295.4	1287.6	1279.8	1278.2	1279.8	1279.8	1281.3	1282.9	1293.9	1292.3
12.5°	1234.3	1229.6	1228.1	1223.4	1215.5	1212.4	1209.3	1226.5	1221.8	1221.8	1221.8
15°	1170.1	1181.1	1179.5	1165.4	1162.3	1168.6	1165.4	1165.4	1181.1	1179.5	1177.9
17.5°	1135.7	1132.5	1129.4	1121.6	1123.1	1121.6	1123.1	1123.1	1132.5	1132.5	1132.5
20°	1096.5	1090.2	1090.2	1087.1	1087.1	1082.4	1088.7	1090.2	1096.5	1096.5	1098.1
22.5°	1062.0	1057.3	1057.3	1055.8	1058.9	1052.6	1058.9	1060.5	1060.5	1065.2	1065.2
25°	1032.3	1029.1	1029.1	1032.3	1032.3	1032.3	1032.3	1038.5	1033.8	1035.4	1033.8
27.5°	1005.6	1007.2	1008.8	1010.3	1008.8	1010.3	1011.9	1015.0	1016.6	1015.0	1011.9
30°	980.6	985.3	986.8	986.8	990.0	991.5	993.1	993.1	994.7	990.0	993.1
32.5°	961.8	961.8	964.9	966.5	969.6	971.2	971.2	974.3	972.7	968.0	969.6
35°	935.2	935.2	941.4	944.6	949.3	947.7	949.3	949.3	950.8	947.7	943.0
37.5°	908.5	911.7	911.7	917.9	919.5	921.1	919.5	922.6	921.1	917.9	916.4
40°	877.2	875.6	877.2	881.9	883.5	883.5	883.5	886.6	886.6	886.6	885.0
42.5°	838.0	842.7	841.2	845.9	844.3	844.3	847.4	850.6	852.1	847.4	849.0
45°	800.4	800.4	803.6	803.6	805.1	805.1	811.4	808.3	811.4	808.3	809.8
47.5°	759.7	761.3	761.3	762.8	766.0	769.1	766.0	767.5	767.5	769.1	766.0
50°	714.3	714.3	717.4	722.1	728.4	725.3	723.7	730.0	725.3	725.3	722.1
52.5°	667.3	672.0	673.6	678.3	683.0	684.5	686.1	683.0	684.5	679.8	681.4
55°	621.9	623.4	629.7	634.4	639.1	639.1	637.5	639.1	640.7	634.4	634.4
57.5°	576.4	581.1	587.4	587.4	593.7	593.7	592.1	592.1	593.7	589.0	587.4
60°	527.9	532.6	540.4	540.4	549.8	551.4	548.2	545.1	545.1	540.4	542.0
62.5°	476.2	480.9	485.6	493.4	499.7	496.6	502.8	496.6	498.1	488.7	488.7
65°	430.8	432.3	440.2	448.0	448.0	451.1	448.0	449.6	444.9	444.9	438.6
67.5°	377.5	377.5	385.3	393.2	401.0	401.0	401.0	396.3	396.3	391.6	391.6
70°	330.5	328.9	336.8	341.5	346.2	347.7	344.6	343.0	339.9	335.2	333.6
72.5°	272.6	275.7	283.5	286.7	294.5	292.9	300.8	291.4	291.4	283.5	282.0
75°	220.9	224.0	231.8	236.5	241.2	241.2	245.9	241.2	235.0	231.8	230.3
77.5°	175.4	173.9	180.1	188.0	189.5	188.0	191.1	189.5	183.3	183.3	180.1
80°	125.3	130.0	136.3	134.7	141.0	139.4	139.4	136.3	136.3	131.6	134.7
82.5°	83.0	87.7	89.3	87.7	89.3	92.4	94.0	92.4	92.4	89.3	90.9
85°	43.9	43.9	47.0	48.6	47.0	47.0	48.6	53.3	50.1	47.0	50.1
87.5°	14.1	12.5	12.5	14.1	12.5	12.5	14.1	14.1	15.7	15.7	15.7
90°	42.6	42.9	43.6	44.3	44.9	45.6	44.9	44.3	43.6	42.9	42.6
92.5°	68.5	68.2	67.5	66.8	66.1	65.4	66.1	66.8	67.5	68.2	68.5
95°	118.7	118.7	118.7	118.7	118.7	118.7	118.7	118.7	118.7	118.7	118.7
97.5°	171.9	171.7	171.4	171.1	170.7	170.4	170.7	171.1	171.4	171.7	171.9
100°	228.2	228.5	229.2	229.9	230.5	231.2	230.5	229.9	229.2	228.5	228.2
102.5°	295.1	294.9	294.6	294.3	293.9	293.6	293.9	294.3	294.6	294.9	295.1
105°	359.0	359.3	360.0	360.7	361.4	362.1	361.4	360.7	360.0	359.3	359.0
107.5°	433.6	433.4	433.1	432.7	432.4	432.0	432.4	432.7	433.1	433.4	433.6
110°	506.6	506.3	505.6	504.9	504.2	503.5	504.2	504.9	505.6	506.3	506.6

TEST NUMBER: P1031483

CATALOG NUMBER: S123DIW-B1165D1535UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	579.6	579.6	579.6	579.6	579.6	579.6	579.6	579.6	579.6	579.6	579.6
115°	649.6	649.4	649.1	648.8	648.4	648.1	648.4	648.8	649.1	649.4	649.6
117.5°	722.6	722.1	721.1	720.0	719.0	718.0	719.0	720.0	721.1	722.1	722.6
120°	795.6	795.3	794.6	793.9	793.3	792.6	793.3	793.9	794.6	795.3	795.6
122.5°	868.6	868.1	867.1	866.1	865.1	864.1	865.1	866.1	867.1	868.1	868.6
125°	941.7	941.0	939.7	938.3	937.0	935.6	937.0	938.3	939.7	941.0	941.7
127.5°	1013.2	1012.5	1011.2	1009.8	1008.5	1007.1	1008.5	1009.8	1011.2	1012.5	1013.2
130°	1087.7	1086.5	1084.2	1081.8	1079.5	1077.1	1079.5	1081.8	1084.2	1086.5	1087.7
132.5°	1157.7	1156.9	1155.2	1153.5	1151.8	1150.1	1151.8	1153.5	1155.2	1156.9	1157.7
135°	1229.2	1228.9	1228.2	1227.5	1226.8	1226.1	1226.8	1227.5	1228.2	1228.9	1229.2
137.5°	1297.6	1297.1	1296.1	1295.1	1294.1	1293.1	1294.1	1295.1	1296.1	1297.1	1297.6
140°	1369.1	1367.9	1365.6	1363.2	1360.9	1358.5	1360.9	1363.2	1365.6	1367.9	1369.1
142.5°	1433.0	1432.2	1430.5	1428.8	1427.1	1425.4	1427.1	1428.8	1430.5	1432.2	1433.0
145°	1495.4	1494.7	1493.4	1492.0	1490.7	1489.3	1490.7	1492.0	1493.4	1494.7	1495.4
147.5°	1556.3	1555.3	1553.2	1551.2	1549.1	1547.1	1549.1	1551.2	1553.2	1555.3	1556.3
150°	1611.0	1610.0	1608.0	1605.9	1603.9	1601.9	1603.9	1605.9	1608.0	1610.0	1611.0
152.5°	1662.7	1661.9	1660.2	1658.5	1656.8	1655.1	1656.8	1658.5	1660.2	1661.9	1662.7
155°	1713.0	1711.8	1709.4	1707.1	1704.7	1702.3	1704.7	1707.1	1709.4	1711.8	1713.0
157.5°	1755.5	1754.5	1752.5	1750.4	1748.4	1746.4	1748.4	1750.4	1752.5	1754.5	1755.5
160°	1795.1	1794.4	1793.1	1791.7	1790.4	1789.0	1790.4	1791.7	1793.1	1794.4	1795.1
162.5°	1831.6	1830.4	1828.1	1825.7	1823.4	1821.0	1823.4	1825.7	1828.1	1830.4	1831.6
165°	1862.0	1860.8	1858.5	1856.1	1853.8	1851.4	1853.8	1856.1	1858.5	1860.8	1862.0
167.5°	1887.9	1886.9	1884.9	1882.8	1880.8	1878.8	1880.8	1882.8	1884.9	1886.9	1887.9
170°	1909.2	1908.0	1905.6	1903.3	1900.9	1898.5	1900.9	1903.3	1905.6	1908.0	1909.2
172.5°	1924.4	1923.2	1920.9	1918.5	1916.2	1913.8	1916.2	1918.5	1920.9	1923.2	1924.4
175°	1935.1	1933.9	1931.5	1929.2	1926.8	1924.4	1926.8	1929.2	1931.5	1933.9	1935.1
177.5°	1941.1	1939.9	1937.6	1935.2	1932.9	1930.5	1932.9	1935.2	1937.6	1939.9	1941.1
180°	1936.6	1936.6	1936.6	1936.6	1936.6	1936.6	1936.6	1936.6	1936.6	1936.6	1936.6

TEST NUMBER: P1031483

CATALOG NUMBER: S123DIW-B1165D1535UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5	1616.5
2.5°	1535.1	1538.2	1539.8	1533.5	1528.8	1536.7	1547.6	1555.5	1561.7	1569.6	1574.3
5°	1444.2	1455.2	1455.2	1458.3	1463.0	1470.9	1491.2	1505.3	1517.9	1527.3	1535.1
7.5°	1367.5	1375.3	1380.0	1387.8	1395.7	1406.6	1430.1	1450.5	1469.3	1480.3	1492.8
10°	1298.6	1304.8	1312.7	1317.4	1331.5	1347.1	1376.9	1394.1	1416.0	1433.3	1448.9
12.5°	1232.8	1254.7	1259.4	1257.8	1270.4	1287.6	1317.4	1344.0	1367.5	1384.7	1401.9
15°	1185.8	1193.6	1203.0	1201.4	1228.1	1232.8	1257.8	1289.2	1320.5	1331.5	1347.1
17.5°	1134.1	1146.6	1156.0	1160.7	1168.6	1185.8	1209.3	1232.8	1273.5	1275.1	1315.8
20°	1093.4	1105.9	1112.2	1118.4	1123.1	1143.5	1163.9	1190.5	1223.4	1240.6	1262.5
22.5°	1066.7	1073.0	1077.7	1082.4	1088.7	1099.6	1124.7	1154.5	1176.4	1195.2	1209.3
25°	1035.4	1041.7	1047.9	1051.1	1055.8	1062.0	1080.8	1104.3	1135.7	1148.2	1162.3
27.5°	1013.5	1013.5	1016.6	1016.6	1022.9	1029.1	1043.2	1065.2	1090.2	1105.9	1124.7
30°	990.0	988.4	990.0	988.4	986.8	996.2	1008.8	1027.6	1044.8	1063.6	1076.1
32.5°	966.5	964.9	964.9	966.5	960.2	964.9	971.2	988.4	1007.2	1016.6	1030.7
35°	941.4	938.3	938.3	938.3	935.2	932.0	938.3	954.0	966.5	979.0	990.0
37.5°	916.4	911.7	911.7	908.5	905.4	900.7	900.7	913.2	930.5	935.2	949.3
40°	881.9	881.9	878.8	877.2	874.1	870.9	866.2	877.2	892.9	897.6	908.5
42.5°	847.4	842.7	841.2	841.2	841.2	836.5	833.3	841.2	850.6	858.4	864.7
45°	808.3	805.1	806.7	805.1	802.0	800.4	798.9	802.0	813.0	816.1	823.9
47.5°	766.0	764.4	764.4	762.8	761.3	762.8	756.6	764.4	767.5	770.7	776.9
50°	722.1	720.6	719.0	717.4	717.4	719.0	717.4	717.4	723.7	726.8	733.1
52.5°	678.3	673.6	673.6	672.0	672.0	668.9	672.0	673.6	676.7	679.8	683.0
55°	631.3	631.3	626.6	626.6	623.4	623.4	625.0	623.4	629.7	632.8	632.8
57.5°	585.8	579.6	581.1	578.0	574.9	573.3	573.3	576.4	579.6	579.6	582.7
60°	537.3	531.0	529.5	523.2	526.3	521.6	523.2	523.2	529.5	526.3	529.5
62.5°	488.7	480.9	476.2	473.1	473.1	474.6	471.5	469.9	473.1	476.2	482.5
65°	437.0	432.3	427.6	422.9	422.9	421.4	424.5	419.8	418.2	419.8	422.9
67.5°	383.8	379.1	374.4	369.7	371.2	366.5	363.4	368.1	365.0	366.5	369.7
70°	332.1	328.9	319.6	316.4	314.9	316.4	314.9	311.7	316.4	314.9	316.4
72.5°	280.4	277.3	272.6	264.7	264.7	263.2	261.6	261.6	260.0	260.0	260.0
75°	230.3	224.0	219.3	217.7	214.6	213.0	211.5	208.3	209.9	211.5	208.3
77.5°	178.6	170.7	169.2	169.2	164.5	164.5	166.0	164.5	162.9	162.9	162.9
80°	131.6	125.3	125.3	122.2	119.0	119.0	119.0	119.0	117.5	115.9	117.5
82.5°	84.6	83.0	81.5	81.5	84.6	78.3	81.5	79.9	78.3	78.3	76.8
85°	47.0	48.6	47.0	48.6	45.4	47.0	47.0	47.0	45.4	47.0	43.9
87.5°	17.2	17.2	17.2	18.8	18.8	18.8	18.8	18.8	20.4	18.8	18.8
90°	41.9	40.6	39.2	37.9	36.5	32.1	27.7	23.3	18.9	16.7	15.0
92.5°	68.0	67.0	65.9	64.9	63.9	61.9	59.9	57.8	55.8	54.8	53.8
95°	118.0	116.7	115.3	114.0	112.6	109.9	107.2	104.5	101.8	100.4	99.2
97.5°	171.1	169.4	167.7	166.0	164.3	162.3	160.3	158.2	156.2	155.2	154.4
100°	227.7	226.7	225.6	224.6	223.6	221.9	220.2	218.5	216.8	216.0	215.0
102.5°	294.6	293.6	292.6	291.6	290.6	288.2	285.8	283.5	281.1	279.9	279.4
105°	359.0	359.0	359.0	359.0	359.0	356.0	352.9	349.9	346.8	345.3	345.0
107.5°	433.1	432.1	431.0	430.0	429.0	427.6	426.3	424.9	423.6	422.9	422.7
110°	505.9	504.6	503.2	501.9	500.5	499.8	499.2	498.5	497.8	497.5	497.2

TEST NUMBER: P1031483

CATALOG NUMBER: S123DIW-B1165D1535UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	578.8	577.1	575.4	573.7	572.0	572.0	572.0	572.0	572.0	572.0	571.8
115°	649.4	649.1	648.8	648.4	648.1	648.8	649.4	650.1	650.8	651.1	650.6
117.5°	722.6	722.6	722.6	722.6	722.6	723.3	723.9	724.6	725.3	725.6	725.4
120°	795.8	796.1	796.4	796.8	797.1	798.8	800.5	802.2	803.9	804.8	803.8
122.5°	869.1	870.1	871.2	872.2	873.2	873.9	874.6	875.3	876.0	876.3	875.6
125°	942.4	943.7	945.1	946.4	947.8	948.5	949.1	949.8	950.5	950.8	950.3
127.5°	1014.2	1016.2	1018.3	1020.3	1022.3	1023.0	1023.6	1024.3	1025.0	1025.3	1024.3
130°	1088.4	1089.7	1091.1	1092.4	1093.8	1094.8	1095.8	1096.9	1097.9	1098.4	1097.0
132.5°	1158.5	1160.2	1161.9	1163.6	1165.3	1166.0	1166.6	1167.3	1168.0	1168.3	1167.0
135°	1229.9	1231.2	1232.6	1233.9	1235.3	1235.6	1236.0	1236.3	1236.6	1236.8	1235.8
137.5°	1298.5	1300.2	1301.9	1303.6	1305.3	1304.3	1303.3	1302.2	1301.2	1300.7	1299.9
140°	1369.3	1369.6	1370.0	1370.3	1370.7	1370.3	1370.0	1369.6	1369.3	1369.1	1368.3
142.5°	1433.2	1433.5	1433.9	1434.2	1434.6	1433.9	1433.2	1432.5	1431.8	1431.5	1430.7
145°	1495.6	1495.9	1496.2	1496.6	1496.9	1495.9	1494.9	1493.9	1492.9	1492.4	1492.1
147.5°	1556.3	1556.3	1556.3	1556.3	1556.3	1555.3	1554.3	1553.2	1552.2	1551.7	1551.0
150°	1611.0	1611.0	1611.0	1611.0	1611.0	1610.3	1609.7	1609.0	1608.3	1608.0	1607.7
152.5°	1662.4	1661.7	1661.0	1660.4	1659.7	1659.4	1659.0	1658.7	1658.4	1658.2	1657.7
155°	1712.3	1711.0	1709.6	1708.3	1706.9	1706.5	1706.2	1705.8	1705.5	1705.3	1705.3
157.5°	1754.8	1753.5	1752.2	1750.8	1749.5	1749.1	1748.8	1748.4	1748.1	1747.9	1748.1
160°	1794.3	1792.6	1790.9	1789.2	1787.5	1787.5	1787.5	1787.5	1787.5	1787.5	1787.8
162.5°	1830.8	1829.1	1827.4	1825.7	1824.0	1823.7	1823.3	1823.0	1822.7	1822.5	1823.0
165°	1861.0	1859.0	1856.9	1854.9	1852.9	1852.9	1852.9	1852.9	1852.9	1852.9	1853.4
167.5°	1886.9	1884.9	1882.8	1880.8	1878.8	1878.4	1878.1	1877.7	1877.4	1877.2	1877.9
170°	1908.0	1905.6	1903.3	1900.9	1898.5	1898.5	1898.5	1898.5	1898.5	1898.5	1899.2
172.5°	1923.4	1921.4	1919.3	1917.3	1915.3	1915.3	1915.3	1915.3	1915.3	1915.3	1916.0
175°	1934.1	1932.0	1930.0	1927.9	1925.9	1925.9	1925.9	1925.9	1925.9	1925.9	1926.6
177.5°	1940.1	1938.1	1936.0	1934.0	1932.0	1932.0	1932.0	1932.0	1932.0	1932.0	1932.7
180°	1936.6	1936.6	1936.6	1936.6	1936.6	1936.6	1936.6	1936.6	1936.6	1936.6	1936.6

TEST NUMBER: P1031483

CATALOG NUMBER: S123DIW-B1165D1535UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1616.5	1616.5	1616.5	1616.5
2.5°	1582.1	1586.8	1602.4	1621.2
5°	1550.8	1563.3	1585.2	1615.0
7.5°	1516.3	1535.1	1566.4	1604.0
10°	1477.1	1503.8	1542.9	1589.9
12.5°	1434.8	1469.3	1519.4	1568.0
15°	1408.2	1442.7	1488.1	1541.4
17.5°	1356.5	1397.2	1444.2	1519.4
20°	1303.3	1348.7	1409.8	1485.0
22.5°	1262.5	1311.1	1369.1	1448.9
25°	1214.0	1264.1	1326.8	1409.8
27.5°	1162.3	1212.4	1282.9	1370.6
30°	1123.1	1171.7	1239.0	1333.0
32.5°	1076.1	1123.1	1193.6	1292.3
35°	1022.9	1076.1	1143.5	1243.7
37.5°	982.1	1030.7	1101.2	1196.7
40°	938.3	980.6	1049.5	1143.5
42.5°	891.3	938.3	997.8	1091.8
45°	847.4	881.9	943.0	1032.3
47.5°	800.4	839.6	886.6	955.5
50°	750.3	783.2	834.9	881.9
52.5°	701.8	728.4	772.2	808.3
55°	650.1	676.7	709.6	731.5
57.5°	601.5	620.3	642.2	656.3
60°	542.0	560.8	574.9	589.0
62.5°	488.7	502.8	510.7	518.5
65°	433.9	441.7	446.4	452.7
67.5°	374.4	382.2	383.8	393.2
70°	319.6	321.1	324.2	328.9
72.5°	267.9	271.0	269.4	272.6
75°	214.6	217.7	214.6	217.7
77.5°	162.9	166.0	166.0	170.7
80°	117.5	119.0	120.6	120.6
82.5°	76.8	81.5	78.3	79.9
85°	43.9	45.4	45.4	47.0
87.5°	20.4	21.9	20.4	23.5
90°	11.6	8.3	4.9	1.5
92.5°	51.7	49.7	47.6	45.6
95°	96.9	94.5	92.2	89.8
97.5°	152.7	151.0	149.3	147.6
100°	213.0	210.9	208.9	206.9
102.5°	278.4	277.4	276.4	275.4
105°	344.3	343.6	343.0	342.3
107.5°	422.4	422.1	421.7	421.4
110°	496.5	495.8	495.1	494.4

TEST NUMBER: P1031483

CATALOG NUMBER: S123DIW-B1165D1535UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	571.5	571.2	570.8	570.5
115°	649.6	648.5	647.5	646.5
117.5°	725.1	724.8	724.4	724.1
120°	801.7	799.7	797.6	795.6
122.5°	874.3	872.9	871.6	870.2
125°	949.3	948.2	947.2	946.2
127.5°	1022.3	1020.2	1018.2	1016.2
130°	1094.3	1091.6	1088.9	1086.2
132.5°	1164.3	1161.6	1158.9	1156.2
135°	1233.8	1231.7	1229.7	1227.7
137.5°	1298.2	1296.5	1294.8	1293.1
140°	1366.6	1364.9	1363.2	1361.5
142.5°	1429.0	1427.3	1425.6	1423.9
145°	1491.4	1490.7	1490.0	1489.3
147.5°	1549.7	1548.3	1547.0	1545.6
150°	1607.0	1606.3	1605.6	1604.9
152.5°	1656.7	1655.6	1654.6	1653.6
155°	1705.3	1705.3	1705.3	1705.3
157.5°	1748.4	1748.8	1749.1	1749.5
160°	1788.5	1789.2	1789.8	1790.5
162.5°	1824.0	1825.0	1826.0	1827.0
165°	1854.4	1855.5	1856.5	1857.5
167.5°	1879.2	1880.6	1881.9	1883.3
170°	1900.5	1901.9	1903.2	1904.6
172.5°	1917.3	1918.7	1920.0	1921.4
175°	1927.9	1929.3	1930.6	1932.0
177.5°	1934.0	1935.4	1936.7	1938.1
180°	1936.6	1936.6	1936.6	1936.6

(END OF REPORT)