

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032033

Luminaire Tested: S123RDIW-B1000D1535UB35-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032033
REPORT IS A COMBINATION OF REPORTS P993837 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B1000D1535UB35-4F0-XX-W2A-F1
Description: Define 3 Regressed Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9209.0 lumens
Efficiency: N/A
Efficacy: 93.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 99
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032033

CATALOG NUMBER: S123RDIW-B1000D1535UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1032033

CATALOG NUMBER: S123RDIW-B1000D1535UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48
1	96	92	88	85	87	84	81	78	69	67	65	55	54	53	43	42	41
2	88	81	75	70	80	74	69	64	61	57	54	49	46	44	38	36	35
3	80	71	64	58	73	65	59	54	54	49	46	43	40	38	34	32	30
4	73	63	55	49	67	58	51	46	48	43	39	39	35	33	30	28	26
5	67	56	48	42	61	52	45	40	43	38	34	35	31	28	28	25	23
6	62	50	42	37	56	46	39	34	39	34	30	32	28	25	25	22	20
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18
8	53	41	34	29	49	38	31	27	32	27	23	26	23	20	21	18	16
9	50	38	30	25	45	35	28	24	29	24	21	24	20	18	19	17	15
10	46	35	28	23	42	32	26	21	27	22	19	22	19	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18034	18034	18034
5°	18063	17396	17349
10°	17922	16742	16411
15°	17688	15933	15385
20°	17384	15054	14239
25°	17069	14140	13153
30°	16664	13168	11868
35°	16249	12214	10698
40°	15859	11177	9406
45°	15356	10163	8244
50°	14804	9081	7042
55°	14231	7922	5939
60°	13683	6734	4821
65°	12974	5514	3763
70°	12086	4170	2690
75°	10803	2823	2130
80°	9218	1962	1494
85°	6916	1058	782

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15356 cd/sqm

TEST NUMBER: P1032033

CATALOG NUMBER: S123RDIW-B1000D1535UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.5	1.7
10°-20°	438.1	4.8
20°-30°	630.8	6.9
30°-40°	710.4	7.7
40°-50°	679.5	7.4
50°-60°	556.3	6.0
60°-70°	375.0	4.1
70°-80°	188.1	2.0
80°-90°	53.3	0.6
90°-100°	125.9	1.4
100°-110°	381.1	4.1
110°-120°	648.8	7.0
120°-130°	853.5	9.3
130°-140°	959.4	10.4
140°-150°	943.2	10.2
150°-160°	794.1	8.6
160°-170°	528.7	5.7
170°-180°	185.1	2.0
0°-30°	1226.5	13.3
0°-40°	1936.9	21.0
0°-60°	3172.7	34.5
0°-90°	3789.1	41.1
90°-120°	1155.8	12.6
90°-150°	3912.0	42.5
90°-180°	5420.0	58.9
0°-180°	9209.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1675	1675	1675	1675	1675	
5°	1675	1669	1652	1664	1662	159
15°	1598	1583	1545	1538	1529	450
25°	1454	1420	1357	1329	1314	669
35°	1258	1209	1125	1067	1042	788
45°	1034	973	868	791	758	798
55°	785	719	603	524	497	704
65°	537	462	356	289	274	531
75°	284	219	144	130	128	303
85°	72	42	38	35	35	79
90°	2	17	37	43	46	11
95°	91	101	114	120	120	100
105°	346	349	363	363	366	370
115°	653	658	655	656	655	646
125°	956	960	957	951	945	852
135°	1240	1249	1248	1242	1238	955
145°	1504	1507	1512	1510	1504	940
155°	1722	1722	1724	1730	1719	793
165°	1876	1872	1872	1881	1870	529
175°	1951	1945	1945	1954	1944	185
180°	1956	1956	1956	1956	1956	

TEST NUMBER: P1032033

CATALOG NUMBER: S123RDIW-B1000D1535UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1675.4	1675.4	1675.4	1675.4	1675.4
2.5°	1682.2	1676.7	1660.4	1675.4	1672.7
5°	1675.4	1668.6	1652.3	1664.5	1661.8
7.5°	1663.2	1656.4	1636.0	1644.1	1640.1
10°	1646.9	1637.3	1612.9	1614.2	1607.4
12.5°	1623.8	1612.9	1581.6	1580.3	1572.1
15°	1597.9	1583.0	1544.9	1538.2	1528.6
17.5°	1566.7	1550.4	1502.8	1489.2	1475.6
20°	1531.4	1509.6	1458.0	1440.3	1424.0
22.5°	1492.0	1466.1	1410.4	1387.3	1372.4
25°	1453.9	1419.9	1357.4	1328.9	1314.0
27.5°	1407.7	1371.0	1303.1	1265.0	1241.9
30°	1360.1	1319.4	1243.3	1197.1	1175.4
32.5°	1312.6	1265.0	1183.5	1131.9	1108.8
35°	1258.2	1209.3	1125.1	1066.7	1042.2
37.5°	1203.9	1150.9	1062.6	997.4	967.5
40°	1152.3	1092.5	996.0	925.3	894.1
42.5°	1093.8	1034.0	933.5	854.7	827.5
45°	1034.0	972.9	868.3	790.8	758.2
47.5°	975.6	907.7	804.4	720.2	691.6
50°	910.4	846.5	736.5	652.2	621.0
52.5°	852.0	781.3	672.6	584.3	557.1
55°	785.4	718.8	603.3	524.5	497.3
57.5°	725.6	653.6	536.7	462.0	438.9
60°	663.1	588.4	475.6	402.2	379.1
62.5°	600.6	525.9	413.1	345.1	320.7
65°	536.7	462.0	356.0	289.4	274.5
67.5°	472.9	396.8	293.5	243.2	226.9
70°	410.4	337.0	241.9	194.3	179.4
72.5°	347.9	275.8	191.6	154.9	150.8
75°	284.0	218.8	144.0	130.4	127.7
77.5°	225.6	165.8	112.8	104.6	101.9
80°	169.8	114.1	85.6	81.5	78.8
82.5°	116.9	70.7	61.1	57.1	57.1
85°	72.0	42.1	38.0	35.3	35.3
87.5°	32.6	17.7	17.7	16.3	14.9
90°	1.5	16.9	36.9	43.0	46.1
92.5°	46.1	55.3	64.5	69.1	66.1
95°	90.7	101.4	113.7	119.9	119.9
97.5°	149.0	156.7	165.9	173.6	172.1
100°	209.0	218.2	225.9	230.5	233.6
102.5°	278.1	282.7	293.5	298.1	296.6
105°	345.7	348.8	362.6	362.6	365.7
107.5°	425.6	427.2	433.3	437.9	436.4
110°	499.4	502.5	505.5	511.7	508.6

TEST NUMBER: P1032033

CATALOG NUMBER: S123RDIW-B1000D1535UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	576.2	577.7	577.7	585.4	585.4
115°	653.0	657.7	654.6	656.1	654.6
117.5°	731.4	732.9	729.9	729.9	725.3
120°	803.6	812.8	805.2	803.6	800.6
122.5°	878.9	885.1	882.0	877.4	872.8
125°	955.7	960.4	957.3	951.1	945.0
127.5°	1026.4	1035.6	1032.6	1023.4	1017.2
130°	1097.1	1109.4	1104.8	1098.6	1087.9
132.5°	1167.8	1180.1	1177.0	1169.3	1161.6
135°	1240.0	1249.2	1247.7	1241.5	1238.5
137.5°	1306.1	1313.8	1318.4	1310.7	1306.1
140°	1375.2	1382.9	1384.4	1382.9	1372.2
142.5°	1438.2	1445.9	1449.0	1447.4	1439.8
145°	1504.3	1507.4	1512.0	1510.4	1504.3
147.5°	1561.2	1567.3	1571.9	1571.9	1562.7
150°	1621.1	1624.2	1627.2	1627.2	1618.0
152.5°	1670.3	1674.9	1676.4	1679.5	1671.8
155°	1722.5	1722.5	1724.0	1730.2	1719.4
157.5°	1767.1	1765.5	1767.1	1773.2	1764.0
160°	1808.5	1805.5	1805.5	1813.2	1807.0
162.5°	1845.4	1840.8	1842.3	1850.0	1839.3
165°	1876.2	1871.5	1871.5	1880.8	1870.0
167.5°	1902.3	1896.1	1897.7	1906.9	1897.7
170°	1923.8	1917.6	1917.6	1928.4	1917.6
172.5°	1940.7	1934.5	1934.5	1943.8	1933.0
175°	1951.4	1945.3	1945.3	1954.5	1943.8
177.5°	1957.6	1951.4	1951.4	1960.7	1949.9
180°	1956.1	1956.1	1956.1	1956.1	1956.1

(END OF REPORT)