

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032062

Luminaire Tested: S123RDIW-B1000D755UB27-4F0-XX-W2A-F

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032062
REPORT IS A COMBINATION OF REPORTS P993898 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B1000D755UB27-4F0-XX-W2A-F
Description: Define 3 Regressed Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6783.0 lumens
Efficiency: N/A
Efficacy: 96.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032062

CATALOG NUMBER: S123RDIW-B1000D755UB27-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1032062

CATALOG NUMBER: S123RDIW-B1000D755UB27-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	99	95	91	88	92	88	85	82	76	74	72	65	63	62	54	53	52
2	91	83	77	72	84	78	73	68	67	63	60	57	54	52	48	46	44
3	83	74	66	61	77	69	62	57	60	55	51	51	47	44	43	40	38
4	76	65	58	52	70	61	54	49	53	48	44	46	42	38	39	36	33
5	70	58	50	45	65	55	48	42	48	42	38	41	37	33	35	32	29
6	65	53	45	39	60	49	42	37	43	37	33	37	33	29	32	28	26
7	60	48	40	34	55	45	38	33	39	33	29	34	30	26	29	26	23
8	56	43	36	30	52	41	34	29	36	30	26	31	27	23	27	23	21
9	52	40	32	27	48	37	31	26	33	27	24	29	24	21	25	21	19
10	48	36	29	24	45	34	28	23	30	25	21	27	22	19	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17800	17800	17800
5°	17829	17170	17124
10°	17689	16525	16199
15°	17460	15727	15186
20°	17158	14859	14055
25°	16848	13958	12981
30°	16449	12998	11714
35°	16039	12056	10560
40°	15652	11032	9284
45°	15159	10031	8138
50°	14612	8963	6950
55°	14046	7819	5863
60°	13505	6646	4759
65°	12807	5442	3714
70°	11927	4115	2654
75°	10662	2788	2104
80°	9099	1937	1475
85°	6829	1047	774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15159 cd/sqm

TEST NUMBER: P1032062

CATALOG NUMBER: S123RDIW-B1000D755UB27-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.5	2.3
10°-20°	432.5	6.4
20°-30°	622.7	9.2
30°-40°	701.2	10.3
40°-50°	670.7	9.9
50°-60°	549.1	8.1
60°-70°	370.2	5.5
70°-80°	185.7	2.7
80°-90°	50.5	0.7
90°-100°	35.2	0.5
100°-110°	170.3	2.5
110°-120°	417.3	6.2
120°-130°	529.8	7.8
130°-140°	565.9	8.3
140°-150°	529.2	7.8
150°-160°	426.9	6.3
160°-170°	275.5	4.1
170°-180°	94.9	1.4
0°-30°	1210.6	17.8
0°-40°	1911.8	28.2
0°-60°	3131.6	46.2
0°-90°	3738.0	55.1
90°-120°	622.8	9.2
90°-150°	2247.8	33.1
90°-180°	3045.0	44.9
0°-180°	6783.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1654	1654	1654	1654	1654	
5°	1654	1647	1631	1643	1640	157
15°	1577	1562	1525	1518	1509	444
25°	1435	1402	1340	1312	1297	660
35°	1242	1194	1110	1053	1029	777
45°	1021	960	857	781	748	788
55°	775	710	596	518	491	695
65°	530	456	351	286	271	524
75°	280	216	142	129	126	299
85°	71	42	38	35	35	78
90°	1	8	18	21	22	7
95°	45	15	23	28	28	54
105°	221	229	162	31	33	234
115°	415	419	426	433	436	410
125°	585	591	594	595	597	522
135°	728	732	735	738	735	560
145°	840	845	847	848	848	526
155°	925	924	925	928	924	426
165°	976	974	973	979	974	276
175°	999	995	996	1001	995	95
180°	999	999	999	999	999	

TEST NUMBER: P1032062

CATALOG NUMBER: S123RDIW-B1000D755UB27-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1653.7	1653.7	1653.7	1653.7	1653.7
2.5°	1660.4	1655.0	1638.9	1653.7	1651.0
5°	1653.7	1647.0	1630.9	1643.0	1640.3
7.5°	1641.6	1634.9	1614.8	1622.9	1618.8
10°	1625.5	1616.1	1592.0	1593.3	1586.6
12.5°	1602.7	1592.0	1561.2	1559.8	1551.8
15°	1577.3	1562.5	1524.9	1518.2	1508.8
17.5°	1546.4	1530.3	1483.4	1470.0	1456.5
20°	1511.5	1490.1	1439.1	1421.7	1405.6
22.5°	1472.6	1447.2	1392.2	1369.4	1354.6
25°	1435.1	1401.6	1339.9	1311.7	1296.9
27.5°	1389.5	1353.3	1286.2	1248.7	1225.9
30°	1342.5	1302.3	1227.2	1181.6	1160.1
32.5°	1295.6	1248.7	1168.2	1117.2	1094.4
35°	1242.0	1193.7	1110.5	1052.8	1028.7
37.5°	1188.3	1136.0	1048.8	984.4	954.9
40°	1137.3	1078.3	983.1	913.4	882.5
42.5°	1079.7	1020.7	921.4	843.6	816.8
45°	1020.7	960.3	857.0	780.6	748.4
47.5°	963.0	895.9	794.0	710.8	682.7
50°	898.6	835.6	726.9	643.8	612.9
52.5°	840.9	771.2	663.9	576.7	549.9
55°	775.2	709.5	595.5	517.7	490.9
57.5°	716.2	645.1	529.8	456.0	433.2
60°	654.5	580.7	469.4	397.0	374.2
62.5°	592.8	519.0	407.7	340.7	316.5
65°	529.8	456.0	351.4	285.7	270.9
67.5°	466.7	391.6	289.7	240.1	224.0
70°	405.0	332.6	238.7	191.8	177.0
72.5°	343.3	272.3	189.1	152.9	148.9
75°	280.3	215.9	142.2	128.8	126.1
77.5°	222.6	163.6	111.3	103.3	100.6
80°	167.6	112.7	84.5	80.5	77.8
82.5°	115.3	69.7	60.4	56.3	56.3
85°	71.1	41.6	37.6	34.9	34.9
87.5°	32.2	17.4	17.4	16.1	14.8
90°	0.7	8.2	17.8	20.8	22.3
92.5°	17.1	12.6	19.3	24.5	25.2
95°	45.3	14.8	23.0	28.2	28.2
97.5°	82.4	61.6	23.7	29.7	30.4
100°	125.4	140.3	24.5	30.4	31.2
102.5°	174.4	184.0	54.9	30.4	31.9
105°	221.1	229.3	162.5	31.2	32.7
107.5°	270.9	277.5	288.7	174.4	77.2
110°	320.6	326.5	334.7	310.2	204.1

TEST NUMBER: P1032062

CATALOG NUMBER: S123RDIW-B1000D755UB27-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	368.1	373.3	381.4	388.1	386.6
115°	414.8	419.3	425.9	433.4	436.3
117.5°	460.8	466.0	469.7	475.7	476.4
120°	503.1	509.8	512.0	518.0	518.0
122.5°	546.2	551.4	554.3	558.0	558.8
125°	584.8	590.7	593.7	595.1	596.6
127.5°	623.3	629.3	633.0	635.2	633.7
130°	659.0	664.9	667.9	670.8	669.3
132.5°	693.1	699.0	701.3	704.2	702.0
135°	728.0	732.4	735.4	737.6	735.4
137.5°	757.7	763.6	765.1	768.8	767.3
140°	787.3	791.8	794.0	797.0	795.5
142.5°	814.8	819.2	821.5	823.7	821.5
145°	840.0	845.2	846.7	848.2	848.2
147.5°	864.5	868.2	869.7	871.2	867.5
150°	886.8	889.0	890.5	892.0	889.7
152.5°	906.8	907.6	908.3	911.3	907.6
155°	925.4	923.9	924.6	928.3	923.9
157.5°	940.2	940.2	939.5	943.9	938.0
160°	953.6	952.8	952.1	956.5	951.3
162.5°	966.2	963.9	963.2	968.4	963.9
165°	975.8	973.6	972.9	978.8	973.6
167.5°	984.0	981.0	981.0	987.0	981.0
170°	990.7	987.7	987.7	993.6	987.7
172.5°	995.1	991.4	992.1	998.1	991.4
175°	998.8	995.1	995.9	1001.1	995.1
177.5°	1000.3	996.6	997.3	1003.3	995.9
180°	998.8	998.8	998.8	998.8	998.8

(END OF REPORT)