

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031546

Luminaire Tested: S123DIW-B1165D755UB50-4F0-XX-W2A-A

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031546
REPORT IS A COMBINATION OF REPORTS P991170 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B1165D755UB50-4F0-XX-W2A-A
Description: Define 3 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7673.0 lumens
Efficiency: N/A
Efficacy: 90.8 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 84.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031546

CATALOG NUMBER: S123DIW-B1165D755UB50-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1031546

CATALOG NUMBER: S123DIW-B1165D755UB50-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67
1	101	96	93	89	94	90	87	84	79	77	75	69	67	66	60	58	57
2	92	85	79	73	86	79	74	70	70	66	62	61	58	55	53	51	49
3	84	75	67	62	78	70	64	59	62	57	53	54	50	47	47	44	42
4	77	66	58	52	72	62	55	50	55	50	45	48	44	41	42	39	36
5	71	59	51	45	66	56	49	43	50	44	39	44	39	35	38	35	32
6	65	53	45	39	61	50	43	38	45	39	34	40	35	31	35	31	28
7	61	48	40	35	57	46	38	33	41	35	30	36	31	28	32	28	25
8	56	44	36	31	53	42	34	29	37	31	27	33	28	25	29	25	22
9	52	40	33	27	49	38	31	26	34	28	24	30	26	22	27	23	20
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16826	16826	16826	16826
5°	16837	19388	16886	14469
10°	16731	23460	16747	12635
15°	16499	27823	16633	11373
20°	16301	32034	16335	10466
25°	16005	32841	16040	9992
30°	15793	27132	15793	9681
35°	15532	18146	15434	9407
40°	15219	13099	15030	8987
45°	14824	10376	14397	8466
50°	13868	8812	13375	7953
55°	12818	7743	12296	7381
60°	11751	6743	11126	6781
65°	10583	5773	10071	5980
70°	9368	4792	8743	5042
75°	8007	3614	7490	3892
80°	6330	2412	5836	2556
85°	4361	1108	3496	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 27137 cd/sqm

TEST NUMBER: P1031546

CATALOG NUMBER: S123DIW-B1165D755UB50-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.7	2.0
10°-20°	493.8	6.4
20°-30°	830.9	10.8
30°-40°	938.9	12.2
40°-50°	841.0	11.0
50°-60°	678.9	8.8
60°-70°	473.1	6.2
70°-80°	248.3	3.2
80°-90°	61.5	0.8
90°-100°	34.1	0.4
100°-110°	165.2	2.2
110°-120°	404.7	5.3
120°-130°	513.8	6.7
130°-140°	548.9	7.2
140°-150°	513.2	6.7
150°-160°	414.0	5.4
160°-170°	267.2	3.5
170°-180°	92.1	1.2
0°-30°	1478.4	19.3
0°-40°	2417.3	31.5
0°-60°	3937.1	51.3
0°-90°	4719.9	61.5
90°-120°	604.0	7.9
90°-150°	2179.9	28.4
90°-180°	2953.0	38.5
0°-180°	7673.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1563	1563	1563	1563	1563	
5°	1562	1857	1566	1386	1562	148
15°	1490	2764	1503	1130	1490	421
25°	1363	3281	1366	998	1363	629
35°	1203	1768	1195	916	1203	753
45°	998	954	969	779	998	763
55°	707	648	679	618	707	633
65°	438	421	417	436	438	436
75°	210	217	197	233	210	226
85°	45	50	36	45	45	52
90°	1	22	1	22	1	6
95°	44	27	44	27	44	52
105°	214	32	214	32	214	227
115°	402	423	402	423	402	397
125°	567	579	567	579	567	507
135°	706	713	706	713	706	544
145°	815	823	815	823	815	510
155°	897	896	897	896	897	414
165°	946	944	946	944	946	267
175°	969	965	969	965	969	92
180°	969	969	969	969	969	

TEST NUMBER: P1031546

CATALOG NUMBER: S123DIW-B1165D755UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2
2.5°	1567.7	1579.9	1585.9	1595.0	1604.1	1617.7	1622.3	1629.9	1626.8	1632.9	1635.9
5°	1561.7	1582.9	1601.1	1623.8	1645.0	1660.1	1675.3	1699.5	1717.7	1720.7	1734.4
7.5°	1551.1	1581.4	1613.2	1645.0	1685.9	1710.1	1737.4	1770.7	1798.0	1841.9	1858.6
10°	1537.5	1579.9	1625.3	1669.2	1725.3	1763.1	1796.5	1852.5	1908.6	1954.0	1996.4
12.5°	1516.2	1569.3	1628.3	1693.5	1766.2	1810.1	1855.5	1929.8	2014.6	2084.3	2129.7
15°	1490.5	1557.1	1632.9	1702.6	1782.8	1864.6	1913.1	1996.4	2117.6	2182.7	2299.4
17.5°	1469.3	1537.5	1613.2	1722.3	1831.3	1913.1	1947.9	2100.9	2184.2	2293.3	2425.1
20°	1436.0	1522.3	1619.2	1728.3	1869.2	1919.2	1990.4	2144.9	2247.9	2390.2	2552.3
22.5°	1401.1	1493.5	1610.2	1723.8	1881.3	1934.3	2031.3	2153.9	2317.5	2458.4	2637.1
25°	1363.3	1463.2	1581.4	1716.2	1870.7	1947.9	2038.8	2190.3	2367.5	2544.8	2709.9
27.5°	1325.4	1434.5	1557.1	1692.0	1841.9	1932.8	2023.7	2181.2	2408.4	2600.8	2811.3
30°	1289.0	1398.1	1520.8	1658.6	1816.2	1904.0	1990.4	2187.3	2440.2	2656.8	2868.9
32.5°	1249.7	1361.7	1490.5	1605.6	1764.7	1858.6	1955.5	2187.3	2459.9	2690.2	2884.1
35°	1202.7	1317.8	1428.4	1543.5	1701.0	1805.6	1914.6	2172.1	2478.1	2700.8	2820.4
37.5°	1157.3	1258.7	1354.2	1466.3	1631.4	1743.5	1869.2	2153.9	2469.0	2655.3	2688.6
40°	1105.8	1207.2	1284.5	1389.0	1563.2	1693.5	1820.7	2129.7	2429.6	2547.8	2450.8
42.5°	1055.8	1136.0	1202.7	1304.2	1493.5	1620.8	1758.6	2085.8	2352.4	2376.6	2158.5
45°	998.2	1055.8	1114.8	1230.0	1417.8	1548.1	1701.0	2022.2	2228.2	2158.5	1882.8
47.5°	924.0	975.5	1040.6	1146.7	1337.5	1472.3	1617.7	1940.4	2047.9	1902.5	1601.1
50°	852.8	896.7	957.3	1060.3	1252.7	1384.5	1539.0	1811.6	1864.6	1635.9	1379.9
52.5°	781.6	814.9	874.0	977.0	1169.4	1296.6	1437.5	1679.8	1649.5	1404.2	1176.9
55°	707.4	736.2	792.2	893.7	1072.4	1193.6	1328.4	1517.8	1439.0	1205.7	1024.0
57.5°	634.7	665.0	722.5	807.4	975.5	1093.6	1201.2	1349.6	1231.5	1045.2	884.6
60°	569.5	595.3	639.2	722.5	875.5	970.9	1069.4	1170.9	1072.4	892.2	769.5
62.5°	501.4	525.6	566.5	642.2	774.0	858.9	937.6	1020.9	911.9	780.1	671.0
65°	437.8	457.4	495.3	565.0	672.5	742.2	805.8	863.4	775.5	654.4	572.6
67.5°	380.2	396.9	428.7	490.8	581.7	631.6	683.1	731.6	657.4	560.5	490.8
70°	318.1	331.7	360.5	405.9	478.7	530.2	568.0	604.4	537.7	460.5	413.5
72.5°	263.6	277.2	295.4	342.3	392.3	424.1	465.0	484.7	446.8	383.2	336.3
75°	210.5	221.2	237.8	268.1	315.1	336.3	362.0	377.2	342.3	299.9	271.1
77.5°	165.1	169.7	181.8	203.0	234.8	259.0	278.7	287.8	263.6	236.3	212.1
80°	116.6	122.7	131.8	150.0	174.2	181.8	193.9	204.5	189.3	165.1	150.0
82.5°	77.3	84.8	89.4	96.9	112.1	121.2	124.2	133.3	119.7	110.6	104.5
85°	45.4	48.5	50.0	54.5	62.1	66.6	71.2	72.7	69.7	68.2	62.1
87.5°	22.7	22.7	22.7	25.8	27.3	30.3	31.8	31.8	31.8	30.3	28.8
90°	0.7	2.3	3.9	5.5	7.1	7.9	8.9	11.0	13.1	15.2	17.3
92.5°	16.6	15.6	14.6	13.7	12.7	12.2	12.9	14.4	15.8	17.3	18.7
95°	43.9	37.3	30.8	24.2	17.7	14.4	15.3	17.0	18.8	20.5	22.3
97.5°	79.9	75.4	70.9	66.4	61.9	59.7	55.6	47.5	39.3	31.2	23.0
100°	121.6	124.8	128.0	131.2	134.4	136.0	123.5	98.6	73.6	48.7	23.7
102.5°	169.1	171.2	173.3	175.4	177.5	178.5	164.6	136.8	108.9	81.1	53.3
105°	214.5	216.3	218.0	219.8	221.5	222.4	215.2	200.8	186.4	172.0	157.6
107.5°	262.7	264.1	265.6	267.0	268.5	269.2	270.4	272.8	275.1	277.5	279.9
110°	310.9	312.2	313.5	314.8	316.1	316.7	317.6	319.3	321.1	322.8	324.6

TEST NUMBER: P1031546

CATALOG NUMBER: S123DIW-B1165D755UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	357.0	358.1	359.2	360.3	361.4	362.0	362.9	364.6	366.4	368.1	369.9
115°	402.3	403.3	404.2	405.2	406.1	406.6	407.3	408.8	410.2	411.7	413.1
117.5°	446.9	448.0	449.1	450.2	451.3	451.9	452.3	453.1	453.9	454.7	455.5
120°	487.9	489.3	490.8	492.2	493.7	494.4	494.6	495.1	495.6	496.1	496.6
122.5°	529.7	530.8	531.9	533.0	534.1	534.7	535.0	535.7	536.3	537.0	537.6
125°	567.1	568.4	569.7	571.0	572.3	572.9	573.2	573.8	574.5	575.1	575.7
127.5°	604.5	605.8	607.1	608.4	609.7	610.3	610.7	611.5	612.3	613.1	613.9
130°	639.1	640.4	641.6	642.9	644.2	644.8	645.1	645.8	646.4	647.1	647.7
132.5°	672.2	673.5	674.7	676.0	677.3	677.9	678.1	678.6	679.1	679.6	680.1
135°	706.0	707.0	707.9	708.9	709.8	710.3	710.6	711.3	711.9	712.6	713.2
137.5°	734.8	736.1	737.3	738.6	739.9	740.5	740.7	741.0	741.3	741.7	742.0
140°	763.6	764.6	765.5	766.5	767.4	767.9	768.1	768.6	769.1	769.5	770.0
142.5°	790.2	791.2	792.1	793.1	794.0	794.5	794.7	795.2	795.7	796.2	796.7
145°	814.7	815.8	816.9	818.0	819.1	819.7	819.9	820.2	820.5	820.8	821.1
147.5°	838.4	839.2	840.0	840.8	841.6	842.0	842.2	842.5	842.8	843.1	843.4
150°	860.0	860.5	861.0	861.5	862.0	862.2	862.4	862.7	863.0	863.3	863.6
152.5°	879.4	879.6	879.7	879.9	880.0	880.1	880.2	880.4	880.5	880.7	880.9
155°	897.4	897.1	896.8	896.5	896.2	896.0	896.1	896.2	896.4	896.5	896.7
157.5°	911.8	911.8	911.8	911.8	911.8	911.8	911.7	911.6	911.4	911.3	911.1
160°	924.8	924.6	924.4	924.3	924.1	924.0	923.9	923.8	923.6	923.5	923.3
162.5°	937.0	936.5	936.0	935.5	935.0	934.8	934.7	934.6	934.4	934.3	934.1
165°	946.4	945.9	945.4	944.9	944.4	944.2	944.1	944.0	943.8	943.7	943.5
167.5°	954.3	953.7	953.0	952.4	951.7	951.4	951.4	951.4	951.4	951.4	951.4
170°	960.8	960.2	959.5	958.9	958.2	957.9	957.9	957.9	957.9	957.9	957.9
172.5°	965.1	964.3	963.5	962.7	961.9	961.5	961.6	961.7	961.9	962.0	962.2
175°	968.7	967.9	967.1	966.3	965.5	965.1	965.2	965.3	965.5	965.6	965.8
177.5°	970.1	969.3	968.5	967.7	966.9	966.5	966.6	966.7	966.9	967.0	967.2
180°	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7

TEST NUMBER: P1031546

CATALOG NUMBER: S123DIW-B1165D755UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2
2.5°	1646.5	1649.5	1660.1	1667.7	1682.9	1681.4	1681.4	1679.8	1675.3	1682.9	1687.4
5°	1761.6	1787.4	1790.4	1823.7	1825.3	1838.9	1848.0	1840.4	1858.6	1857.1	1843.4
7.5°	1904.0	1938.9	1955.5	1987.3	2023.7	2014.6	2049.4	2055.5	2052.5	2067.6	2078.2
10°	2060.0	2120.6	2163.0	2222.1	2237.3	2246.3	2269.1	2288.8	2328.1	2297.8	2317.5
12.5°	2238.8	2282.7	2338.7	2432.7	2479.6	2509.9	2520.5	2534.1	2561.4	2544.8	2546.3
15°	2388.7	2447.8	2543.2	2659.9	2673.5	2711.4	2702.3	2784.1	2823.5	2764.4	2797.7
17.5°	2544.8	2623.5	2737.1	2838.6	2896.2	2921.9	2946.2	3024.9	3021.9	3012.8	3020.4
20°	2644.7	2773.5	2914.3	3049.2	3065.8	3085.5	3150.6	3184.0	3177.9	3203.7	3220.3
22.5°	2785.6	2921.9	3071.9	3161.2	3199.1	3221.8	3273.3	3294.5	3303.6	3309.7	3299.1
25°	2903.7	3049.2	3159.7	3238.5	3261.2	3273.3	3290.0	3296.1	3291.5	3280.9	3290.0
27.5°	2984.0	3100.7	3176.4	3212.7	3200.6	3180.9	3149.1	3127.9	3081.0	3058.2	3085.5
30°	3017.3	3068.8	3091.6	3031.0	2970.4	2921.9	2861.3	2749.2	2661.4	2687.1	2652.3
32.5°	2964.3	2931.0	2821.9	2665.9	2619.0	2540.2	2369.0	2237.3	2241.8	2172.1	2200.9
35°	2808.3	2656.8	2450.8	2214.5	2152.4	2110.0	1922.2	1893.4	1832.8	1767.7	1785.9
37.5°	2532.6	2311.5	2061.6	1887.4	1795.0	1702.6	1596.5	1532.9	1496.6	1469.3	1490.5
40°	2196.4	1926.7	1720.7	1564.7	1486.0	1426.9	1354.2	1290.6	1249.7	1245.1	1252.7
42.5°	1866.2	1638.9	1449.6	1301.2	1275.4	1205.7	1158.8	1108.8	1096.7	1077.0	1087.6
45°	1579.9	1395.1	1239.1	1117.9	1087.6	1069.4	1011.8	980.0	966.4	954.3	972.5
47.5°	1372.3	1178.5	1064.9	992.1	961.9	931.6	899.8	878.5	867.9	869.5	867.9
50°	1172.4	1030.0	930.0	874.0	855.8	834.6	808.9	795.2	790.7	777.1	787.7
52.5°	1008.8	905.8	836.1	783.1	769.5	754.3	733.1	725.6	715.0	711.9	711.9
55°	877.0	796.7	740.7	705.9	689.2	677.1	665.0	655.9	648.3	648.3	648.3
57.5°	774.0	704.4	663.5	633.2	627.1	615.0	601.3	601.3	590.7	589.2	593.8
60°	686.2	624.1	592.3	566.5	557.4	554.4	540.8	540.8	537.7	530.2	536.2
62.5°	596.8	551.4	524.1	504.4	495.3	495.3	484.7	477.1	477.1	478.7	475.6
65°	515.0	481.7	457.4	442.3	437.8	431.7	430.2	424.1	419.6	421.1	419.6
67.5°	442.3	416.6	399.9	387.8	380.2	377.2	372.6	372.6	369.6	371.1	363.5
70°	377.2	351.4	337.8	325.7	322.6	322.6	316.6	318.1	315.1	319.6	316.6
72.5°	310.5	290.8	280.2	275.7	272.7	271.1	268.1	265.1	263.6	266.6	265.1
75°	251.4	234.8	227.2	224.2	221.2	221.2	219.6	218.1	216.6	216.6	216.6
77.5°	195.4	184.8	175.7	178.7	174.2	175.7	171.2	171.2	172.7	171.2	171.2
80°	143.9	136.3	136.3	133.3	127.2	130.3	130.3	125.7	124.2	127.2	122.7
82.5°	95.4	93.9	90.9	89.4	86.3	87.9	86.3	84.8	83.3	86.3	83.3
85°	56.0	56.0	54.5	51.5	54.5	53.0	51.5	51.5	50.0	50.0	50.0
87.5°	28.8	25.8	25.8	24.2	25.8	22.7	24.2	22.7	21.2	22.7	21.2
90°	17.9	18.6	19.2	19.9	20.2	20.4	20.7	21.0	21.3	21.6	21.3
92.5°	19.8	20.9	22.0	23.1	23.7	23.8	24.0	24.1	24.3	24.5	24.3
95°	23.4	24.5	25.6	26.7	27.3	27.3	27.3	27.3	27.3	27.3	27.3
97.5°	24.3	25.6	26.9	28.2	28.8	28.9	29.0	29.2	29.3	29.5	29.3
100°	25.0	26.3	27.6	28.9	29.5	29.6	29.7	29.9	30.0	30.2	30.0
102.5°	48.0	42.7	37.4	32.1	29.5	29.7	30.0	30.3	30.6	30.9	30.6
105°	129.3	101.0	72.7	44.4	30.2	30.4	30.7	31.0	31.4	31.7	31.4
107.5°	255.3	230.7	206.0	181.4	169.1	158.6	137.7	116.7	95.8	74.8	95.8
110°	319.3	314.0	308.7	303.4	300.8	289.4	266.5	243.6	220.8	197.9	220.8

TEST NUMBER: P1031546

CATALOG NUMBER: S123DIW-B1165D755UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	371.3	372.8	374.2	375.7	376.4	376.2	375.9	375.6	375.2	374.9	375.2
115°	414.7	416.3	417.9	419.5	420.3	420.6	421.3	421.9	422.6	423.2	422.6
117.5°	456.8	458.1	459.4	460.7	461.3	461.4	461.5	461.7	461.8	462.0	461.8
120°	497.9	499.1	500.4	501.7	502.3	502.3	502.3	502.3	502.3	502.3	502.3
122.5°	538.4	539.2	540.0	540.8	541.2	541.3	541.4	541.6	541.7	541.9	541.7
125°	576.0	576.4	576.7	577.0	577.2	577.4	577.7	578.0	578.3	578.6	578.3
127.5°	614.4	614.8	615.3	615.8	616.0	615.8	615.5	615.2	614.9	614.6	614.9
130°	648.3	649.0	649.6	650.3	650.6	650.4	650.1	649.8	649.4	649.1	649.4
132.5°	680.7	681.4	682.0	682.7	683.0	682.8	682.3	681.8	681.3	680.8	681.3
135°	713.7	714.1	714.6	715.1	715.3	715.1	714.6	714.1	713.7	713.2	713.7
137.5°	742.8	743.6	744.4	745.2	745.6	745.4	745.1	744.8	744.4	744.1	744.4
140°	770.6	771.3	771.9	772.6	772.9	772.7	772.4	772.1	771.8	771.5	771.8
142.5°	797.2	797.6	798.1	798.6	798.8	798.6	798.1	797.6	797.2	796.7	797.2
145°	821.4	821.8	822.1	822.4	822.6	822.6	822.6	822.6	822.6	822.6	822.6
147.5°	843.7	844.1	844.4	844.7	844.9	844.5	843.7	842.9	842.1	841.3	842.1
150°	863.9	864.2	864.5	864.8	865.0	864.8	864.3	863.8	863.4	862.9	863.4
152.5°	881.5	882.1	882.8	883.4	883.7	883.3	882.5	881.7	880.9	880.1	880.9
155°	897.5	898.3	899.1	899.9	900.3	899.8	898.9	897.9	897.0	896.0	897.0
157.5°	912.1	913.0	914.0	914.9	915.4	914.8	913.5	912.2	911.0	909.7	911.0
160°	924.3	925.2	926.2	927.1	927.6	927.0	925.9	924.8	923.7	922.6	923.7
162.5°	935.2	936.4	937.5	938.6	939.2	938.7	937.7	936.8	935.8	934.8	935.8
165°	944.8	946.0	947.3	948.6	949.2	948.6	947.5	946.4	945.3	944.2	945.3
167.5°	952.7	954.0	955.3	956.6	957.2	956.6	955.3	954.0	952.7	951.4	952.7
170°	959.2	960.4	961.7	963.0	963.6	963.0	961.7	960.4	959.2	957.9	959.2
172.5°	963.5	964.7	966.0	967.3	967.9	967.2	965.8	964.3	962.9	961.5	962.9
175°	966.9	968.0	969.1	970.2	970.8	970.2	968.9	967.6	966.4	965.1	966.4
177.5°	968.5	969.8	971.1	972.4	973.0	972.2	970.6	969.0	967.4	965.8	967.4
180°	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7

TEST NUMBER: P1031546

CATALOG NUMBER: S123DIW-B1165D755UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2
2.5°	1675.3	1679.8	1667.7	1664.7	1664.7	1670.7	1666.2	1625.3	1632.9	1623.8	1620.8
5°	1860.1	1851.0	1838.9	1832.8	1825.3	1804.0	1802.5	1755.6	1746.5	1716.2	1702.6
7.5°	2063.1	2055.5	2019.1	2014.6	2011.6	1991.9	1941.9	1891.9	1855.5	1820.7	1787.4
10°	2294.8	2272.1	2255.4	2222.1	2205.5	2178.2	2113.1	2066.1	2004.0	1951.0	1881.3
12.5°	2573.5	2547.8	2491.7	2467.5	2446.3	2370.6	2305.4	2252.4	2131.2	2094.9	2008.5
15°	2778.0	2723.5	2717.4	2664.4	2661.4	2578.1	2453.9	2396.3	2302.4	2169.1	2079.7
17.5°	2999.2	2950.7	2912.8	2849.2	2840.1	2761.4	2670.5	2529.6	2426.6	2299.4	2185.8
20°	3161.2	3135.5	3070.4	3044.6	2991.6	2924.9	2831.0	2656.8	2531.1	2403.9	2264.5
22.5°	3290.0	3264.2	3212.7	3177.9	3147.6	3061.3	2949.2	2800.7	2628.1	2461.4	2317.5
25°	3288.5	3280.9	3259.7	3243.0	3220.3	3156.7	3062.8	2920.4	2728.0	2544.8	2344.8
27.5°	3102.2	3123.4	3159.7	3177.9	3173.4	3164.3	3111.3	2991.6	2818.9	2600.8	2376.6
30°	2714.4	2791.7	2859.8	2950.7	2978.0	3044.6	3074.9	3006.7	2868.9	2665.9	2417.5
32.5°	2250.9	2363.0	2511.4	2561.4	2647.8	2776.5	2920.4	2946.2	2859.8	2703.8	2443.3
35°	1846.5	1938.9	2054.0	2132.7	2210.0	2419.0	2600.8	2758.3	2787.1	2684.1	2437.2
37.5°	1528.4	1593.5	1695.0	1761.6	1832.8	2011.6	2266.0	2470.5	2614.4	2617.5	2420.5
40°	1298.1	1326.9	1414.8	1463.2	1531.4	1685.9	1913.1	2179.7	2390.2	2487.2	2376.6
42.5°	1099.7	1137.6	1210.3	1246.6	1290.6	1425.4	1575.3	1828.3	2088.8	2296.3	2294.8
45°	981.5	1008.8	1042.1	1072.4	1122.4	1202.7	1373.9	1563.2	1813.1	2047.9	2140.3
47.5°	877.0	902.8	936.1	945.2	978.5	1054.3	1158.8	1323.9	1557.1	1790.4	1964.6
50°	789.2	810.4	833.1	849.8	864.9	927.0	1005.8	1145.1	1331.4	1557.1	1773.8
52.5°	721.0	736.2	755.9	764.9	778.6	824.0	884.6	987.6	1140.6	1346.6	1557.1
55°	657.4	668.0	680.1	695.3	701.3	734.6	781.6	869.5	983.1	1167.9	1367.8
57.5°	598.3	602.9	610.4	619.5	627.1	655.9	696.8	755.9	855.8	998.2	1187.6
60°	531.7	543.8	548.3	557.4	562.0	584.7	616.5	666.5	743.7	866.4	1008.8
62.5°	475.6	483.2	490.8	495.3	505.9	513.5	539.2	584.7	648.3	739.2	867.9
65°	425.6	428.7	433.2	437.8	440.8	449.9	474.1	504.4	552.9	633.2	733.1
67.5°	368.1	371.1	377.2	378.7	381.7	393.8	407.5	433.2	474.1	534.7	616.5
70°	312.0	316.6	319.6	322.6	327.2	331.7	346.9	368.1	399.9	442.3	505.9
72.5°	263.6	268.1	268.1	271.1	269.6	275.7	290.8	306.0	327.2	362.0	418.1
75°	215.1	215.1	218.1	219.6	221.2	227.2	233.3	245.4	262.0	289.3	324.2
77.5°	169.7	168.1	171.2	171.2	171.2	175.7	181.8	187.8	198.4	218.1	245.4
80°	124.2	124.2	127.2	128.8	125.7	127.2	130.3	136.3	143.9	157.5	172.7
82.5°	81.8	87.9	86.3	87.9	86.3	89.4	90.9	92.4	95.4	101.5	112.1
85°	50.0	50.0	50.0	51.5	50.0	51.5	51.5	51.5	53.0	56.0	60.6
87.5°	21.2	21.2	21.2	22.7	21.2	21.2	22.7	21.2	22.7	22.7	24.2
90°	21.0	20.7	20.4	20.2	19.9	19.2	18.6	17.9	17.3	15.2	13.1
92.5°	24.1	24.0	23.8	23.7	23.1	22.0	20.9	19.8	18.7	17.3	15.8
95°	27.3	27.3	27.3	27.3	26.7	25.6	24.5	23.4	22.3	20.5	18.8
97.5°	29.2	29.0	28.9	28.8	28.2	26.9	25.6	24.3	23.0	31.2	39.3
100°	29.9	29.7	29.6	29.5	28.9	27.6	26.3	25.0	23.7	48.7	73.6
102.5°	30.3	30.0	29.7	29.5	32.1	37.4	42.7	48.0	53.3	81.1	108.9
105°	31.0	30.7	30.4	30.2	44.4	72.7	101.0	129.3	157.6	172.0	186.4
107.5°	116.7	137.7	158.6	169.1	181.4	206.0	230.7	255.3	279.9	277.5	275.1
110°	243.6	266.5	289.4	300.8	303.4	308.7	314.0	319.3	324.6	322.8	321.1

TEST NUMBER: P1031546

CATALOG NUMBER: S123DIW-B1165D755UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	375.6	375.9	376.2	376.4	375.7	374.2	372.8	371.3	369.9	368.1	366.4
115°	421.9	421.3	420.6	420.3	419.5	417.9	416.3	414.7	413.1	411.7	410.2
117.5°	461.7	461.5	461.4	461.3	460.7	459.4	458.1	456.8	455.5	454.7	453.9
120°	502.3	502.3	502.3	502.3	501.7	500.4	499.1	497.9	496.6	496.1	495.6
122.5°	541.6	541.4	541.3	541.2	540.8	540.0	539.2	538.4	537.6	537.0	536.3
125°	578.0	577.7	577.4	577.2	577.0	576.7	576.4	576.0	575.7	575.1	574.5
127.5°	615.2	615.5	615.8	616.0	615.8	615.3	614.8	614.4	613.9	613.1	612.3
130°	649.8	650.1	650.4	650.6	650.3	649.6	649.0	648.3	647.7	647.1	646.4
132.5°	681.8	682.3	682.8	683.0	682.7	682.0	681.4	680.7	680.1	679.6	679.1
135°	714.1	714.6	715.1	715.3	715.1	714.6	714.1	713.7	713.2	712.6	711.9
137.5°	744.8	745.1	745.4	745.6	745.2	744.4	743.6	742.8	742.0	741.7	741.3
140°	772.1	772.4	772.7	772.9	772.6	771.9	771.3	770.6	770.0	769.5	769.1
142.5°	797.6	798.1	798.6	798.8	798.6	798.1	797.6	797.2	796.7	796.2	795.7
145°	822.6	822.6	822.6	822.6	822.4	822.1	821.8	821.4	821.1	820.8	820.5
147.5°	842.9	843.7	844.5	844.9	844.7	844.4	844.1	843.7	843.4	843.1	842.8
150°	863.8	864.3	864.8	865.0	864.8	864.5	864.2	863.9	863.6	863.3	863.0
152.5°	881.7	882.5	883.3	883.7	883.4	882.8	882.1	881.5	880.9	880.7	880.5
155°	897.9	898.9	899.8	900.3	899.9	899.1	898.3	897.5	896.7	896.5	896.4
157.5°	912.2	913.5	914.8	915.4	914.9	914.0	913.0	912.1	911.1	911.3	911.4
160°	924.8	925.9	927.0	927.6	927.1	926.2	925.2	924.3	923.3	923.5	923.6
162.5°	936.8	937.7	938.7	939.2	938.6	937.5	936.4	935.2	934.1	934.3	934.4
165°	946.4	947.5	948.6	949.2	948.6	947.3	946.0	944.8	943.5	943.7	943.8
167.5°	954.0	955.3	956.6	957.2	956.6	955.3	954.0	952.7	951.4	951.4	951.4
170°	960.4	961.7	963.0	963.6	963.0	961.7	960.4	959.2	957.9	957.9	957.9
172.5°	964.3	965.8	967.2	967.9	967.3	966.0	964.7	963.5	962.2	962.0	961.9
175°	967.6	968.9	970.2	970.8	970.2	969.1	968.0	966.9	965.8	965.6	965.5
177.5°	969.0	970.6	972.2	973.0	972.4	971.1	969.8	968.5	967.2	967.0	966.9
180°	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7

TEST NUMBER: P1031546

CATALOG NUMBER: S123DIW-B1165D755UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2
2.5°	1605.6	1601.1	1601.1	1598.0	1589.0	1572.3	1570.8	1573.8	1564.7	1555.6	1542.0
5°	1684.4	1655.6	1646.5	1637.4	1619.2	1589.0	1576.8	1566.2	1549.6	1529.9	1508.7
7.5°	1751.0	1710.1	1698.0	1681.4	1645.0	1602.6	1575.3	1552.6	1529.9	1502.6	1476.9
10°	1834.3	1775.3	1746.5	1722.3	1672.3	1613.2	1572.3	1539.0	1502.6	1469.3	1436.0
12.5°	1928.3	1832.8	1823.7	1764.7	1707.1	1619.2	1569.3	1520.8	1472.3	1431.4	1396.6
15°	2007.0	1902.5	1864.6	1825.3	1714.7	1605.6	1557.1	1502.6	1446.6	1402.6	1351.1
17.5°	2057.0	1970.7	1890.4	1837.4	1722.3	1625.3	1531.4	1469.3	1410.2	1349.6	1307.2
20°	2117.6	1991.9	1922.2	1851.0	1737.4	1610.2	1516.2	1439.0	1366.3	1311.8	1260.3
22.5°	2178.2	2008.5	1951.0	1873.7	1740.4	1595.0	1489.0	1411.7	1328.4	1273.9	1217.8
25°	2172.1	2032.8	1937.3	1872.2	1710.1	1581.4	1457.2	1366.3	1289.0	1219.4	1163.3
27.5°	2176.7	2005.5	1908.6	1832.8	1688.9	1561.7	1423.8	1328.4	1248.1	1175.4	1116.4
30°	2178.2	1964.6	1879.8	1788.9	1649.5	1514.7	1386.0	1289.0	1204.2	1125.4	1072.4
32.5°	2173.6	1931.3	1825.3	1743.5	1587.4	1469.3	1342.1	1239.1	1152.7	1080.0	1030.0
35°	2163.0	1891.9	1769.2	1666.2	1523.8	1404.2	1301.2	1195.1	1102.7	1036.1	978.5
37.5°	2134.3	1849.5	1710.1	1608.6	1449.6	1328.4	1237.5	1149.7	1060.3	981.5	933.1
40°	2113.1	1791.9	1651.1	1540.5	1369.3	1251.2	1175.4	1092.1	1004.3	933.1	886.1
42.5°	2064.6	1737.4	1590.5	1458.7	1290.6	1169.4	1098.2	1031.5	955.8	886.1	843.7
45°	1985.8	1678.3	1516.2	1383.0	1204.2	1089.1	1024.0	969.4	902.8	836.1	793.7
47.5°	1875.2	1593.5	1437.5	1304.2	1119.4	1002.8	937.6	896.7	843.7	787.7	751.3
50°	1755.6	1501.1	1357.2	1225.4	1037.6	924.0	860.4	822.5	787.7	736.2	701.3
52.5°	1599.6	1402.6	1264.8	1139.1	949.7	840.7	784.6	757.4	721.0	684.7	654.4
55°	1448.1	1275.4	1161.8	1042.1	863.4	761.9	707.4	678.6	657.4	627.1	602.9
57.5°	1272.4	1157.3	1052.7	943.7	783.1	690.7	639.2	604.4	590.7	577.1	554.4
60°	1110.3	1022.4	937.6	846.7	699.8	616.5	566.5	539.2	525.6	516.5	501.4
62.5°	961.9	893.7	821.0	748.3	615.0	539.2	501.4	474.1	462.0	460.5	446.8
65°	819.5	771.0	711.9	640.7	536.2	469.6	433.2	416.6	402.9	402.9	392.3
67.5°	677.1	643.8	596.8	546.8	465.0	402.9	369.6	354.4	346.9	346.9	339.3
70°	563.5	540.8	498.3	454.4	383.2	336.3	310.5	296.9	292.3	293.9	287.8
72.5°	457.4	433.2	398.4	366.6	313.5	278.7	260.5	245.4	237.8	239.3	237.8
75°	354.4	342.3	312.0	287.8	245.4	221.2	204.5	196.9	190.9	192.4	189.3
77.5°	266.6	248.4	231.8	215.1	189.3	169.7	156.0	148.4	143.9	143.9	143.9
80°	181.8	178.7	165.1	156.0	134.8	119.7	109.1	107.5	103.0	103.0	103.0
82.5°	118.1	110.6	103.0	96.9	84.8	75.7	71.2	68.2	66.6	65.1	68.2
85°	65.1	60.6	57.6	51.5	47.0	42.4	37.9	36.4	34.8	36.4	34.8
87.5°	25.8	21.2	21.2	19.7	18.2	16.7	16.7	13.6	13.6	12.1	12.1
90°	11.0	8.9	7.9	7.1	5.5	3.9	2.3	0.7	2.3	3.9	5.5
92.5°	14.4	12.9	12.2	12.7	13.7	14.6	15.6	16.6	15.6	14.6	13.7
95°	17.0	15.3	14.4	17.7	24.2	30.8	37.3	43.9	37.3	30.8	24.2
97.5°	47.5	55.6	59.7	61.9	66.4	70.9	75.4	79.9	75.4	70.9	66.4
100°	98.6	123.5	136.0	134.4	131.2	128.0	124.8	121.6	124.8	128.0	131.2
102.5°	136.8	164.6	178.5	177.5	175.4	173.3	171.2	169.1	171.2	173.3	175.4
105°	200.8	215.2	222.4	221.5	219.8	218.0	216.3	214.5	216.3	218.0	219.8
107.5°	272.8	270.4	269.2	268.5	267.0	265.6	264.1	262.7	264.1	265.6	267.0
110°	319.3	317.6	316.7	316.1	314.8	313.5	312.2	310.9	312.2	313.5	314.8

TEST NUMBER: P1031546

CATALOG NUMBER: S123DIW-B1165D755UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	364.6	362.9	362.0	361.4	360.3	359.2	358.1	357.0	358.1	359.2	360.3
115°	408.8	407.3	406.6	406.1	405.2	404.2	403.3	402.3	403.3	404.2	405.2
117.5°	453.1	452.3	451.9	451.3	450.2	449.1	448.0	446.9	448.0	449.1	450.2
120°	495.1	494.6	494.4	493.7	492.2	490.8	489.3	487.9	489.3	490.8	492.2
122.5°	535.7	535.0	534.7	534.1	533.0	531.9	530.8	529.7	530.8	531.9	533.0
125°	573.8	573.2	572.9	572.3	571.0	569.7	568.4	567.1	568.4	569.7	571.0
127.5°	611.5	610.7	610.3	609.7	608.4	607.1	605.8	604.5	605.8	607.1	608.4
130°	645.8	645.1	644.8	644.2	642.9	641.6	640.4	639.1	640.4	641.6	642.9
132.5°	678.6	678.1	677.9	677.3	676.0	674.7	673.5	672.2	673.5	674.7	676.0
135°	711.3	710.6	710.3	709.8	708.9	707.9	707.0	706.0	707.0	707.9	708.9
137.5°	741.0	740.7	740.5	739.9	738.6	737.3	736.1	734.8	736.1	737.3	738.6
140°	768.6	768.1	767.9	767.4	766.5	765.5	764.6	763.6	764.6	765.5	766.5
142.5°	795.2	794.7	794.5	794.0	793.1	792.1	791.2	790.2	791.2	792.1	793.1
145°	820.2	819.9	819.7	819.1	818.0	816.9	815.8	814.7	815.8	816.9	818.0
147.5°	842.5	842.2	842.0	841.6	840.8	840.0	839.2	838.4	839.2	840.0	840.8
150°	862.7	862.4	862.2	862.0	861.5	861.0	860.5	860.0	860.5	861.0	861.5
152.5°	880.4	880.2	880.1	880.0	879.9	879.7	879.6	879.4	879.6	879.7	879.9
155°	896.2	896.1	896.0	896.2	896.5	896.8	897.1	897.4	897.1	896.8	896.5
157.5°	911.6	911.7	911.8	911.8	911.8	911.8	911.8	911.8	911.8	911.8	911.8
160°	923.8	923.9	924.0	924.1	924.3	924.4	924.6	924.8	924.6	924.4	924.3
162.5°	934.6	934.7	934.8	935.0	935.5	936.0	936.5	937.0	936.5	936.0	935.5
165°	944.0	944.1	944.2	944.4	944.9	945.4	945.9	946.4	945.9	945.4	944.9
167.5°	951.4	951.4	951.4	951.7	952.4	953.0	953.7	954.3	953.7	953.0	952.4
170°	957.9	957.9	957.9	958.2	958.9	959.5	960.2	960.8	960.2	959.5	958.9
172.5°	961.7	961.6	961.5	961.9	962.7	963.5	964.3	965.1	964.3	963.5	962.7
175°	965.3	965.2	965.1	965.5	966.3	967.1	967.9	968.7	967.9	967.1	966.3
177.5°	966.7	966.6	966.5	966.9	967.7	968.5	969.3	970.1	969.3	968.5	967.7
180°	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7

TEST NUMBER: P1031546

CATALOG NUMBER: S123DIW-B1165D755UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2
2.5°	1539.0	1537.5	1540.5	1531.4	1516.2	1508.7	1487.5	1482.9	1481.4	1482.9	1484.4
5°	1496.6	1495.0	1490.5	1475.3	1457.2	1443.5	1417.8	1416.3	1407.2	1398.1	1402.6
7.5°	1455.7	1449.6	1440.5	1420.8	1396.6	1381.4	1360.2	1345.1	1333.0	1325.4	1319.3
10°	1414.8	1405.7	1396.6	1370.8	1340.5	1317.8	1292.1	1279.9	1266.3	1260.3	1254.2
12.5°	1361.7	1352.7	1336.0	1305.7	1287.5	1258.7	1233.0	1220.9	1213.3	1201.2	1193.6
15°	1319.3	1301.2	1292.1	1260.3	1222.4	1219.4	1172.4	1169.4	1154.2	1154.2	1142.1
17.5°	1270.9	1257.2	1240.6	1208.8	1181.5	1154.2	1130.0	1120.9	1107.3	1104.2	1098.2
20°	1223.9	1205.7	1199.7	1167.9	1139.1	1105.8	1080.0	1070.9	1064.9	1058.8	1063.3
22.5°	1175.4	1160.3	1145.1	1116.4	1095.2	1061.8	1046.7	1037.6	1028.5	1025.5	1027.0
25°	1128.5	1114.8	1099.7	1070.9	1048.2	1020.9	1007.3	1002.8	998.2	998.2	996.7
27.5°	1083.0	1069.4	1055.8	1030.0	1007.3	987.6	977.0	972.5	967.9	970.9	974.0
30°	1036.1	1024.0	1011.8	989.1	970.9	952.8	946.7	943.7	942.2	949.7	949.7
32.5°	993.7	983.1	974.0	952.8	934.6	919.4	914.9	916.4	917.9	922.5	925.5
35°	949.7	942.2	933.1	914.9	899.8	886.1	887.6	887.6	890.7	898.2	904.3
37.5°	910.4	899.8	892.2	877.0	864.9	852.8	857.3	861.9	864.9	874.0	877.0
40°	863.4	858.9	852.8	837.6	827.0	825.5	827.0	830.1	836.1	840.7	845.2
42.5°	825.5	819.5	811.9	799.8	790.7	792.2	793.7	796.7	799.8	807.4	811.9
45°	783.1	778.6	772.5	761.9	754.3	755.9	757.4	757.4	760.4	769.5	772.5
47.5°	736.2	737.7	730.1	719.5	715.0	715.0	715.0	718.0	725.6	728.6	730.1
50°	690.7	687.7	686.2	675.6	672.5	671.0	672.5	674.1	684.7	683.1	687.7
52.5°	642.2	642.2	640.7	634.7	630.1	630.1	627.1	634.7	637.7	640.7	645.3
55°	595.3	590.7	589.2	586.2	580.1	578.6	581.7	590.7	593.8	596.8	601.3
57.5°	543.8	543.8	540.8	536.2	536.2	536.2	536.2	542.3	546.8	549.8	558.9
60°	496.8	490.8	486.2	486.2	486.2	484.7	493.8	493.8	502.9	504.4	507.4
62.5°	440.8	437.8	434.7	436.2	434.7	437.8	440.8	446.8	448.4	452.9	457.4
65°	387.8	387.8	384.7	393.8	387.8	387.8	395.3	395.3	398.4	402.9	409.0
67.5°	336.3	337.8	334.8	334.8	337.8	339.3	340.8	346.9	348.4	354.4	362.0
70°	283.3	286.3	287.8	284.8	287.8	290.8	293.9	295.4	301.4	304.5	309.0
72.5°	236.3	239.3	234.8	236.3	237.8	240.8	242.4	245.4	248.4	257.5	260.5
75°	189.3	187.8	186.3	192.4	189.3	195.4	196.9	196.9	199.9	207.5	210.5
77.5°	145.4	145.4	146.9	143.9	148.4	146.9	148.4	153.0	157.5	157.5	169.7
80°	101.5	104.5	104.5	104.5	106.0	107.5	104.5	112.1	113.6	113.6	118.1
82.5°	65.1	66.6	65.1	68.2	68.2	71.2	69.7	71.2	74.2	77.3	78.8
85°	34.8	34.8	37.9	37.9	36.4	37.9	36.4	37.9	40.9	40.9	42.4
87.5°	12.1	12.1	12.1	12.1	13.6	12.1	13.6	13.6	12.1	12.1	16.7
90°	7.1	7.9	8.9	11.0	13.1	15.2	17.3	17.9	18.6	19.2	19.9
92.5°	12.7	12.2	12.9	14.4	15.8	17.3	18.7	19.8	20.9	22.0	23.1
95°	17.7	14.4	15.3	17.0	18.8	20.5	22.3	23.4	24.5	25.6	26.7
97.5°	61.9	59.7	55.6	47.5	39.3	31.2	23.0	24.3	25.6	26.9	28.2
100°	134.4	136.0	123.5	98.6	73.6	48.7	23.7	25.0	26.3	27.6	28.9
102.5°	177.5	178.5	164.6	136.8	108.9	81.1	53.3	48.0	42.7	37.4	32.1
105°	221.5	222.4	215.2	200.8	186.4	172.0	157.6	129.3	101.0	72.7	44.4
107.5°	268.5	269.2	270.4	272.8	275.1	277.5	279.9	255.3	230.7	206.0	181.4
110°	316.1	316.7	317.6	319.3	321.1	322.8	324.6	319.3	314.0	308.7	303.4

TEST NUMBER: P1031546

CATALOG NUMBER: S123DIW-B1165D755UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	361.4	362.0	362.9	364.6	366.4	368.1	369.9	371.3	372.8	374.2	375.7
115°	406.1	406.6	407.3	408.8	410.2	411.7	413.1	414.7	416.3	417.9	419.5
117.5°	451.3	451.9	452.3	453.1	453.9	454.7	455.5	456.8	458.1	459.4	460.7
120°	493.7	494.4	494.6	495.1	495.6	496.1	496.6	497.9	499.1	500.4	501.7
122.5°	534.1	534.7	535.0	535.7	536.3	537.0	537.6	538.4	539.2	540.0	540.8
125°	572.3	572.9	573.2	573.8	574.5	575.1	575.7	576.0	576.4	576.7	577.0
127.5°	609.7	610.3	610.7	611.5	612.3	613.1	613.9	614.4	614.8	615.3	615.8
130°	644.2	644.8	645.1	645.8	646.4	647.1	647.7	648.3	649.0	649.6	650.3
132.5°	677.3	677.9	678.1	678.6	679.1	679.6	680.1	680.7	681.4	682.0	682.7
135°	709.8	710.3	710.6	711.3	711.9	712.6	713.2	713.7	714.1	714.6	715.1
137.5°	739.9	740.5	740.7	741.0	741.3	741.7	742.0	742.8	743.6	744.4	745.2
140°	767.4	767.9	768.1	768.6	769.1	769.5	770.0	770.6	771.3	771.9	772.6
142.5°	794.0	794.5	794.7	795.2	795.7	796.2	796.7	797.2	797.6	798.1	798.6
145°	819.1	819.7	819.9	820.2	820.5	820.8	821.1	821.4	821.8	822.1	822.4
147.5°	841.6	842.0	842.2	842.5	842.8	843.1	843.4	843.7	844.1	844.4	844.7
150°	862.0	862.2	862.4	862.7	863.0	863.3	863.6	863.9	864.2	864.5	864.8
152.5°	880.0	880.1	880.2	880.4	880.5	880.7	880.9	881.5	882.1	882.8	883.4
155°	896.2	896.0	896.1	896.2	896.4	896.5	896.7	897.5	898.3	899.1	899.9
157.5°	911.8	911.8	911.7	911.6	911.4	911.3	911.1	912.1	913.0	914.0	914.9
160°	924.1	924.0	923.9	923.8	923.6	923.5	923.3	924.3	925.2	926.2	927.1
162.5°	935.0	934.8	934.7	934.6	934.4	934.3	934.1	935.2	936.4	937.5	938.6
165°	944.4	944.2	944.1	944.0	943.8	943.7	943.5	944.8	946.0	947.3	948.6
167.5°	951.7	951.4	951.4	951.4	951.4	951.4	951.4	952.7	954.0	955.3	956.6
170°	958.2	957.9	957.9	957.9	957.9	957.9	957.9	959.2	960.4	961.7	963.0
172.5°	961.9	961.5	961.6	961.7	961.9	962.0	962.2	963.5	964.7	966.0	967.3
175°	965.5	965.1	965.2	965.3	965.5	965.6	965.8	966.9	968.0	969.1	970.2
177.5°	966.9	966.5	966.6	966.7	966.9	967.0	967.2	968.5	969.8	971.1	972.4
180°	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7

TEST NUMBER: P1031546

CATALOG NUMBER: S123DIW-B1165D755UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2
2.5°	1482.9	1484.4	1478.4	1473.8	1486.0	1478.4	1478.4	1479.9	1476.9	1481.4	1479.9
5°	1399.6	1401.1	1390.5	1393.6	1387.5	1386.0	1384.5	1393.6	1392.0	1390.5	1393.6
7.5°	1317.8	1317.8	1313.3	1310.2	1310.2	1305.7	1311.8	1310.2	1313.3	1313.3	1317.8
10°	1249.7	1252.7	1245.1	1237.5	1236.0	1237.5	1237.5	1239.1	1240.6	1251.2	1249.7
12.5°	1193.6	1189.1	1187.6	1183.0	1175.4	1172.4	1169.4	1186.0	1181.5	1181.5	1181.5
15°	1131.5	1142.1	1140.6	1127.0	1123.9	1130.0	1127.0	1127.0	1142.1	1140.6	1139.1
17.5°	1098.2	1095.2	1092.1	1084.5	1086.1	1084.5	1086.1	1086.1	1095.2	1095.2	1095.2
20°	1060.3	1054.3	1054.3	1051.2	1051.2	1046.7	1052.7	1054.3	1060.3	1060.3	1061.8
22.5°	1027.0	1022.4	1022.4	1020.9	1024.0	1017.9	1024.0	1025.5	1025.5	1030.0	1030.0
25°	998.2	995.2	995.2	998.2	998.2	998.2	998.2	1004.3	999.7	1001.2	999.7
27.5°	972.5	974.0	975.5	977.0	975.5	977.0	978.5	981.5	983.1	981.5	978.5
30°	948.2	952.8	954.3	954.3	957.3	958.8	960.3	960.3	961.9	957.3	960.3
32.5°	930.0	930.0	933.1	934.6	937.6	939.1	939.1	942.2	940.6	936.1	937.6
35°	904.3	904.3	910.4	913.4	917.9	916.4	917.9	917.9	919.4	916.4	911.9
37.5°	878.5	881.6	881.6	887.6	889.1	890.7	889.1	892.2	890.7	887.6	886.1
40°	848.3	846.7	848.3	852.8	854.3	854.3	854.3	857.3	857.3	857.3	855.8
42.5°	810.4	814.9	813.4	818.0	816.4	816.4	819.5	822.5	824.0	819.5	821.0
45°	774.0	774.0	777.1	777.1	778.6	778.6	784.6	781.6	784.6	781.6	783.1
47.5°	734.6	736.2	736.2	737.7	740.7	743.7	740.7	742.2	742.2	743.7	740.7
50°	690.7	690.7	693.7	698.3	704.4	701.3	699.8	705.9	701.3	701.3	698.3
52.5°	645.3	649.8	651.3	655.9	660.4	661.9	663.5	660.4	661.9	657.4	658.9
55°	601.3	602.9	608.9	613.5	618.0	618.0	616.5	618.0	619.5	613.5	613.5
57.5°	557.4	562.0	568.0	568.0	574.1	574.1	572.6	572.6	574.1	569.5	568.0
60°	510.5	515.0	522.6	522.6	531.7	533.2	530.2	527.1	527.1	522.6	524.1
62.5°	460.5	465.0	469.6	477.1	483.2	480.2	486.2	480.2	481.7	472.6	472.6
65°	416.6	418.1	425.6	433.2	433.2	436.2	433.2	434.7	430.2	430.2	424.1
67.5°	365.1	365.1	372.6	380.2	387.8	387.8	387.8	383.2	383.2	378.7	378.7
70°	319.6	318.1	325.7	330.2	334.8	336.3	333.2	331.7	328.7	324.2	322.6
72.5°	263.6	266.6	274.2	277.2	284.8	283.3	290.8	281.7	281.7	274.2	272.7
75°	213.6	216.6	224.2	228.7	233.3	233.3	237.8	233.3	227.2	224.2	222.7
77.5°	169.7	168.1	174.2	181.8	183.3	181.8	184.8	183.3	177.2	177.2	174.2
80°	121.2	125.7	131.8	130.3	136.3	134.8	134.8	131.8	131.8	127.2	130.3
82.5°	80.3	84.8	86.3	84.8	86.3	89.4	90.9	89.4	89.4	86.3	87.9
85°	42.4	42.4	45.4	47.0	45.4	45.4	47.0	51.5	48.5	45.4	48.5
87.5°	13.6	12.1	12.1	13.6	12.1	12.1	13.6	13.6	15.1	15.1	15.1
90°	20.2	20.4	20.7	21.0	21.3	21.6	21.3	21.0	20.7	20.4	20.2
92.5°	23.7	23.8	24.0	24.1	24.3	24.5	24.3	24.1	24.0	23.8	23.7
95°	27.3	27.3	27.3	27.3	27.3	27.3	27.3	27.3	27.3	27.3	27.3
97.5°	28.8	28.9	29.0	29.2	29.3	29.5	29.3	29.2	29.0	28.9	28.8
100°	29.5	29.6	29.7	29.9	30.0	30.2	30.0	29.9	29.7	29.6	29.5
102.5°	29.5	29.7	30.0	30.3	30.6	30.9	30.6	30.3	30.0	29.7	29.5
105°	30.2	30.4	30.7	31.0	31.4	31.7	31.4	31.0	30.7	30.4	30.2
107.5°	169.1	158.6	137.7	116.7	95.8	74.8	95.8	116.7	137.7	158.6	169.1
110°	300.8	289.4	266.5	243.6	220.8	197.9	220.8	243.6	266.5	289.4	300.8

TEST NUMBER: P1031546

CATALOG NUMBER: S123DIW-B1165D755UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	376.4	376.2	375.9	375.6	375.2	374.9	375.2	375.6	375.9	376.2	376.4
115°	420.3	420.6	421.3	421.9	422.6	423.2	422.6	421.9	421.3	420.6	420.3
117.5°	461.3	461.4	461.5	461.7	461.8	462.0	461.8	461.7	461.5	461.4	461.3
120°	502.3	502.3	502.3	502.3	502.3	502.3	502.3	502.3	502.3	502.3	502.3
122.5°	541.2	541.3	541.4	541.6	541.7	541.9	541.7	541.6	541.4	541.3	541.2
125°	577.2	577.4	577.7	578.0	578.3	578.6	578.3	578.0	577.7	577.4	577.2
127.5°	616.0	615.8	615.5	615.2	614.9	614.6	614.9	615.2	615.5	615.8	616.0
130°	650.6	650.4	650.1	649.8	649.4	649.1	649.4	649.8	650.1	650.4	650.6
132.5°	683.0	682.8	682.3	681.8	681.3	680.8	681.3	681.8	682.3	682.8	683.0
135°	715.3	715.1	714.6	714.1	713.7	713.2	713.7	714.1	714.6	715.1	715.3
137.5°	745.6	745.4	745.1	744.8	744.4	744.1	744.4	744.8	745.1	745.4	745.6
140°	772.9	772.7	772.4	772.1	771.8	771.5	771.8	772.1	772.4	772.7	772.9
142.5°	798.8	798.6	798.1	797.6	797.2	796.7	797.2	797.6	798.1	798.6	798.8
145°	822.6	822.6	822.6	822.6	822.6	822.6	822.6	822.6	822.6	822.6	822.6
147.5°	844.9	844.5	843.7	842.9	842.1	841.3	842.1	842.9	843.7	844.5	844.9
150°	865.0	864.8	864.3	863.8	863.4	862.9	863.4	863.8	864.3	864.8	865.0
152.5°	883.7	883.3	882.5	881.7	880.9	880.1	880.9	881.7	882.5	883.3	883.7
155°	900.3	899.8	898.9	897.9	897.0	896.0	897.0	897.9	898.9	899.8	900.3
157.5°	915.4	914.8	913.5	912.2	911.0	909.7	911.0	912.2	913.5	914.8	915.4
160°	927.6	927.0	925.9	924.8	923.7	922.6	923.7	924.8	925.9	927.0	927.6
162.5°	939.2	938.7	937.7	936.8	935.8	934.8	935.8	936.8	937.7	938.7	939.2
165°	949.2	948.6	947.5	946.4	945.3	944.2	945.3	946.4	947.5	948.6	949.2
167.5°	957.2	956.6	955.3	954.0	952.7	951.4	952.7	954.0	955.3	956.6	957.2
170°	963.6	963.0	961.7	960.4	959.2	957.9	959.2	960.4	961.7	963.0	963.6
172.5°	967.9	967.2	965.8	964.3	962.9	961.5	962.9	964.3	965.8	967.2	967.9
175°	970.8	970.2	968.9	967.6	966.4	965.1	966.4	967.6	968.9	970.2	970.8
177.5°	973.0	972.2	970.6	969.0	967.4	965.8	967.4	969.0	970.6	972.2	973.0
180°	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7

TEST NUMBER: P1031546

CATALOG NUMBER: S123DIW-B1165D755UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2	1563.2
2.5°	1484.4	1487.5	1489.0	1482.9	1478.4	1486.0	1496.6	1504.1	1510.2	1517.8	1522.3
5°	1396.6	1407.2	1407.2	1410.2	1414.8	1422.3	1442.0	1455.7	1467.8	1476.9	1484.4
7.5°	1322.4	1329.9	1334.5	1342.1	1349.6	1360.2	1383.0	1402.6	1420.8	1431.4	1443.5
10°	1255.7	1261.8	1269.3	1273.9	1287.5	1302.7	1331.4	1348.1	1369.3	1386.0	1401.1
12.5°	1192.1	1213.3	1217.8	1216.3	1228.4	1245.1	1273.9	1299.6	1322.4	1339.0	1355.7
15°	1146.7	1154.2	1163.3	1161.8	1187.6	1192.1	1216.3	1246.6	1276.9	1287.5	1302.7
17.5°	1096.7	1108.8	1117.9	1122.4	1130.0	1146.7	1169.4	1192.1	1231.5	1233.0	1272.4
20°	1057.3	1069.4	1075.5	1081.5	1086.1	1105.8	1125.4	1151.2	1183.0	1199.7	1220.9
22.5°	1031.5	1037.6	1042.1	1046.7	1052.7	1063.3	1087.6	1116.4	1137.6	1155.7	1169.4
25°	1001.2	1007.3	1013.4	1016.4	1020.9	1027.0	1045.2	1067.9	1098.2	1110.3	1123.9
27.5°	980.0	980.0	983.1	983.1	989.1	995.2	1008.8	1030.0	1054.3	1069.4	1087.6
30°	957.3	955.8	957.3	955.8	954.3	963.4	975.5	993.7	1010.3	1028.5	1040.6
32.5°	934.6	933.1	933.1	934.6	928.5	933.1	939.1	955.8	974.0	983.1	996.7
35°	910.4	907.3	907.3	907.3	904.3	901.3	907.3	922.5	934.6	946.7	957.3
37.5°	886.1	881.6	881.6	878.5	875.5	871.0	871.0	883.1	899.8	904.3	917.9
40°	852.8	852.8	849.8	848.3	845.2	842.2	837.6	848.3	863.4	867.9	878.5
42.5°	819.5	814.9	813.4	813.4	813.4	808.9	805.8	813.4	822.5	830.1	836.1
45°	781.6	778.6	780.1	778.6	775.5	774.0	772.5	775.5	786.1	789.2	796.7
47.5°	740.7	739.2	739.2	737.7	736.2	737.7	731.6	739.2	742.2	745.2	751.3
50°	698.3	696.8	695.3	693.7	693.7	695.3	693.7	693.7	699.8	702.8	708.9
52.5°	655.9	651.3	651.3	649.8	649.8	646.8	649.8	651.3	654.4	657.4	660.4
55°	610.4	610.4	605.9	605.9	602.9	602.9	604.4	602.9	608.9	612.0	612.0
57.5°	566.5	560.5	562.0	558.9	555.9	554.4	554.4	557.4	560.5	560.5	563.5
60°	519.6	513.5	512.0	505.9	509.0	504.4	505.9	505.9	512.0	509.0	512.0
62.5°	472.6	465.0	460.5	457.4	457.4	459.0	455.9	454.4	457.4	460.5	466.5
65°	422.6	418.1	413.5	409.0	409.0	407.5	410.5	405.9	404.4	405.9	409.0
67.5°	371.1	366.6	362.0	357.5	359.0	354.4	351.4	356.0	352.9	354.4	357.5
70°	321.1	318.1	309.0	306.0	304.5	306.0	304.5	301.4	306.0	304.5	306.0
72.5°	271.1	268.1	263.6	256.0	256.0	254.5	253.0	253.0	251.4	251.4	251.4
75°	222.7	216.6	212.1	210.5	207.5	206.0	204.5	201.5	203.0	204.5	201.5
77.5°	172.7	165.1	163.6	163.6	159.0	159.0	160.6	159.0	157.5	157.5	157.5
80°	127.2	121.2	121.2	118.1	115.1	115.1	115.1	115.1	113.6	112.1	113.6
82.5°	81.8	80.3	78.8	78.8	81.8	75.7	78.8	77.3	75.7	75.7	74.2
85°	45.4	47.0	45.4	47.0	43.9	45.4	45.4	45.4	43.9	45.4	42.4
87.5°	16.7	16.7	16.7	18.2	18.2	18.2	18.2	18.2	19.7	18.2	18.2
90°	19.9	19.2	18.6	17.9	17.3	15.2	13.1	11.0	8.9	7.9	7.1
92.5°	23.1	22.0	20.9	19.8	18.7	17.3	15.8	14.4	12.9	12.2	12.7
95°	26.7	25.6	24.5	23.4	22.3	20.5	18.8	17.0	15.3	14.4	17.7
97.5°	28.2	26.9	25.6	24.3	23.0	31.2	39.3	47.5	55.6	59.7	61.9
100°	28.9	27.6	26.3	25.0	23.7	48.7	73.6	98.6	123.5	136.0	134.4
102.5°	32.1	37.4	42.7	48.0	53.3	81.1	108.9	136.8	164.6	178.5	177.5
105°	44.4	72.7	101.0	129.3	157.6	172.0	186.4	200.8	215.2	222.4	221.5
107.5°	181.4	206.0	230.7	255.3	279.9	277.5	275.1	272.8	270.4	269.2	268.5
110°	303.4	308.7	314.0	319.3	324.6	322.8	321.1	319.3	317.6	316.7	316.1

TEST NUMBER: P1031546

CATALOG NUMBER: S123DIW-B1165D755UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	375.7	374.2	372.8	371.3	369.9	368.1	366.4	364.6	362.9	362.0	361.4
115°	419.5	417.9	416.3	414.7	413.1	411.7	410.2	408.8	407.3	406.6	406.1
117.5°	460.7	459.4	458.1	456.8	455.5	454.7	453.9	453.1	452.3	451.9	451.3
120°	501.7	500.4	499.1	497.9	496.6	496.1	495.6	495.1	494.6	494.4	493.7
122.5°	540.8	540.0	539.2	538.4	537.6	537.0	536.3	535.7	535.0	534.7	534.1
125°	577.0	576.7	576.4	576.0	575.7	575.1	574.5	573.8	573.2	572.9	572.3
127.5°	615.8	615.3	614.8	614.4	613.9	613.1	612.3	611.5	610.7	610.3	609.7
130°	650.3	649.6	649.0	648.3	647.7	647.1	646.4	645.8	645.1	644.8	644.2
132.5°	682.7	682.0	681.4	680.7	680.1	679.6	679.1	678.6	678.1	677.9	677.3
135°	715.1	714.6	714.1	713.7	713.2	712.6	711.9	711.3	710.6	710.3	709.8
137.5°	745.2	744.4	743.6	742.8	742.0	741.7	741.3	741.0	740.7	740.5	739.9
140°	772.6	771.9	771.3	770.6	770.0	769.5	769.1	768.6	768.1	767.9	767.4
142.5°	798.6	798.1	797.6	797.2	796.7	796.2	795.7	795.2	794.7	794.5	794.0
145°	822.4	822.1	821.8	821.4	821.1	820.8	820.5	820.2	819.9	819.7	819.1
147.5°	844.7	844.4	844.1	843.7	843.4	843.1	842.8	842.5	842.2	842.0	841.6
150°	864.8	864.5	864.2	863.9	863.6	863.3	863.0	862.7	862.4	862.2	862.0
152.5°	883.4	882.8	882.1	881.5	880.9	880.7	880.5	880.4	880.2	880.1	880.0
155°	899.9	899.1	898.3	897.5	896.7	896.5	896.4	896.2	896.1	896.0	896.2
157.5°	914.9	914.0	913.0	912.1	911.1	911.3	911.4	911.6	911.7	911.8	911.8
160°	927.1	926.2	925.2	924.3	923.3	923.5	923.6	923.8	923.9	924.0	924.1
162.5°	938.6	937.5	936.4	935.2	934.1	934.3	934.4	934.6	934.7	934.8	935.0
165°	948.6	947.3	946.0	944.8	943.5	943.7	943.8	944.0	944.1	944.2	944.4
167.5°	956.6	955.3	954.0	952.7	951.4	951.4	951.4	951.4	951.4	951.4	951.7
170°	963.0	961.7	960.4	959.2	957.9	957.9	957.9	957.9	957.9	957.9	958.2
172.5°	967.3	966.0	964.7	963.5	962.2	962.0	961.9	961.7	961.6	961.5	961.9
175°	970.2	969.1	968.0	966.9	965.8	965.6	965.5	965.3	965.2	965.1	965.5
177.5°	972.4	971.1	969.8	968.5	967.2	967.0	966.9	966.7	966.6	966.5	966.9
180°	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7

TEST NUMBER: P1031546

CATALOG NUMBER: S123DIW-B1165D755UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1563.2	1563.2	1563.2	1563.2
2.5°	1529.9	1534.4	1549.6	1567.7
5°	1499.6	1511.7	1532.9	1561.7
7.5°	1466.3	1484.4	1514.7	1551.1
10°	1428.4	1454.1	1492.0	1537.5
12.5°	1387.5	1420.8	1469.3	1516.2
15°	1361.7	1395.1	1439.0	1490.5
17.5°	1311.8	1351.1	1396.6	1469.3
20°	1260.3	1304.2	1363.3	1436.0
22.5°	1220.9	1267.8	1323.9	1401.1
25°	1173.9	1222.4	1283.0	1363.3
27.5°	1123.9	1172.4	1240.6	1325.4
30°	1086.1	1133.0	1198.2	1289.0
32.5°	1040.6	1086.1	1154.2	1249.7
35°	989.1	1040.6	1105.8	1202.7
37.5°	949.7	996.7	1064.9	1157.3
40°	907.3	948.2	1014.9	1105.8
42.5°	861.9	907.3	964.9	1055.8
45°	819.5	852.8	911.9	998.2
47.5°	774.0	811.9	857.3	924.0
50°	725.6	757.4	807.4	852.8
52.5°	678.6	704.4	746.8	781.6
55°	628.6	654.4	686.2	707.4
57.5°	581.7	599.8	621.0	634.7
60°	524.1	542.3	555.9	569.5
62.5°	472.6	486.2	493.8	501.4
65°	419.6	427.2	431.7	437.8
67.5°	362.0	369.6	371.1	380.2
70°	309.0	310.5	313.5	318.1
72.5°	259.0	262.0	260.5	263.6
75°	207.5	210.5	207.5	210.5
77.5°	157.5	160.6	160.6	165.1
80°	113.6	115.1	116.6	116.6
82.5°	74.2	78.8	75.7	77.3
85°	42.4	43.9	43.9	45.4
87.5°	19.7	21.2	19.7	22.7
90°	5.5	3.9	2.3	0.7
92.5°	13.7	14.6	15.6	16.6
95°	24.2	30.8	37.3	43.9
97.5°	66.4	70.9	75.4	79.9
100°	131.2	128.0	124.8	121.6
102.5°	175.4	173.3	171.2	169.1
105°	219.8	218.0	216.3	214.5
107.5°	267.0	265.6	264.1	262.7
110°	314.8	313.5	312.2	310.9

TEST NUMBER: P1031546

CATALOG NUMBER: S123DIW-B1165D755UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	360.3	359.2	358.1	357.0
115°	405.2	404.2	403.3	402.3
117.5°	450.2	449.1	448.0	446.9
120°	492.2	490.8	489.3	487.9
122.5°	533.0	531.9	530.8	529.7
125°	571.0	569.7	568.4	567.1
127.5°	608.4	607.1	605.8	604.5
130°	642.9	641.6	640.4	639.1
132.5°	676.0	674.7	673.5	672.2
135°	708.9	707.9	707.0	706.0
137.5°	738.6	737.3	736.1	734.8
140°	766.5	765.5	764.6	763.6
142.5°	793.1	792.1	791.2	790.2
145°	818.0	816.9	815.8	814.7
147.5°	840.8	840.0	839.2	838.4
150°	861.5	861.0	860.5	860.0
152.5°	879.9	879.7	879.6	879.4
155°	896.5	896.8	897.1	897.4
157.5°	911.8	911.8	911.8	911.8
160°	924.3	924.4	924.6	924.8
162.5°	935.5	936.0	936.5	937.0
165°	944.9	945.4	945.9	946.4
167.5°	952.4	953.0	953.7	954.3
170°	958.9	959.5	960.2	960.8
172.5°	962.7	963.5	964.3	965.1
175°	966.3	967.1	967.9	968.7
177.5°	967.7	968.5	969.3	970.1
180°	968.7	968.7	968.7	968.7

(END OF REPORT)