

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032089

Luminaire Tested: S123RDIW-B1165D1030UB35-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032089
REPORT IS A COMBINATION OF REPORTS P993966 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B1165D1030UB35-4F0-XX-W2A-A1
Description: Define 3 Regressed Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8245.0 lumens
Efficiency: N/A
Efficacy: 88.8 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 92.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032089

CATALOG NUMBER: S123RDIW-B1165D1030UB35-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1032089

CATALOG NUMBER: S123RDIW-B1165D1030UB35-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	61	61	61
1	100	96	92	89	93	89	86	83	77	75	73	66	64	63	55	54	53
2	91	84	78	74	85	79	74	69	68	64	61	59	56	53	50	48	46
3	84	75	68	62	78	70	64	59	61	56	52	52	49	46	44	42	40
4	77	67	59	53	71	62	56	50	54	49	45	47	43	40	40	37	35
5	71	60	52	46	66	56	49	44	49	43	39	43	38	35	36	33	31
6	66	54	46	40	61	51	43	38	44	39	35	39	34	31	33	30	27
7	61	49	41	35	56	46	39	34	40	35	31	35	31	28	31	27	25
8	56	44	37	32	53	42	35	30	37	31	27	32	28	25	28	25	22
9	53	41	33	28	49	38	32	27	34	29	25	30	26	22	26	23	20
10	49	37	30	26	46	35	29	25	31	26	22	28	23	20	24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	19894	19894	19894	19894
5°	19909	22912	19960	16998
10°	19732	27657	19819	14847
15°	19530	31390	19530	13091
20°	19129	33859	19237	11613
25°	18837	32168	18799	10596
30°	18495	22288	18457	9602
35°	18085	14310	18002	8853
40°	17573	10105	17487	8107
45°	16684	8086	16662	7381
50°	15593	6764	15541	6532
55°	14363	5575	14249	5537
60°	13159	4609	13026	4709
65°	11744	3688	11818	3991
70°	10437	2562	10716	3227
75°	8848	1900	9209	2481
80°	7047	1261	7644	1860
85°	5014	596	5475	1157

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 26558 cd/sqm

TEST NUMBER: P1032089

CATALOG NUMBER: S123RDIW-B1165D1030UB35-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.5	2.2
10°-20°	568.1	6.9
20°-30°	894.8	10.9
30°-40°	930.5	11.3
40°-50°	796.0	9.7
50°-60°	606.9	7.4
60°-70°	388.8	4.7
70°-80°	186.3	2.3
80°-90°	51.8	0.6
90°-100°	84.6	1.0
100°-110°	256.0	3.1
110°-120°	435.8	5.3
120°-130°	573.3	7.0
130°-140°	644.4	7.8
140°-150°	633.5	7.7
150°-160°	533.3	6.5
160°-170°	355.1	4.3
170°-180°	124.3	1.5
0°-30°	1644.5	19.9
0°-40°	2574.9	31.2
0°-60°	3977.9	48.2
0°-90°	4604.8	55.8
90°-120°	776.3	9.4
90°-150°	2627.5	31.9
90°-180°	3640.0	44.1
0°-180°	8245.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1848	1848	1848	1848	1848	
5°	1847	2195	1851	1628	1847	175
15°	1764	3119	1764	1301	1764	496
25°	1604	3214	1601	1059	1604	739
35°	1400	1394	1394	862	1400	876
45°	1123	744	1122	679	1123	865
55°	793	467	786	464	793	710
65°	486	269	489	291	486	485
75°	233	114	242	149	233	251
85°	52	27	57	52	52	58
90°	1	31	1	31	1	7
95°	61	80	61	80	61	67
105°	232	246	232	246	232	249
115°	439	440	439	440	439	434
125°	642	635	642	635	642	572
135°	833	832	833	832	833	642
145°	1010	1010	1010	1010	1010	631
155°	1157	1155	1157	1155	1157	533
165°	1260	1256	1260	1256	1260	355
175°	1311	1306	1311	1306	1311	125
180°	1314	1314	1314	1314	1314	

TEST NUMBER: P1032089

CATALOG NUMBER: S123RDIW-B1165D1030UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2
2.5°	1852.9	1865.6	1875.1	1881.4	1897.2	1906.7	1914.6	1928.9	1928.9	1932.0	1938.3
5°	1846.6	1873.5	1892.5	1917.8	1951.0	1966.8	1989.0	2008.0	2034.9	2049.1	2063.3
7.5°	1832.3	1870.3	1909.9	1947.8	1996.9	2028.5	2050.7	2099.7	2134.6	2177.3	2210.5
10°	1813.3	1865.6	1916.2	1974.7	2041.2	2088.7	2121.9	2186.8	2253.2	2313.4	2364.0
12.5°	1789.6	1852.9	1925.7	1996.9	2090.2	2137.7	2191.5	2272.2	2367.2	2443.1	2511.1
15°	1764.3	1837.1	1919.4	2006.4	2123.5	2189.9	2267.5	2365.6	2471.6	2580.8	2674.1
17.5°	1724.7	1816.5	1908.3	2034.9	2172.5	2212.1	2278.5	2413.0	2544.4	2642.5	2756.4
20°	1685.2	1788.0	1903.5	2017.5	2166.2	2258.0	2319.7	2462.1	2602.9	2721.6	2830.8
22.5°	1648.8	1756.4	1876.6	2020.6	2159.9	2251.6	2329.2	2477.9	2640.9	2773.8	2908.3
25°	1604.5	1721.6	1854.5	1990.6	2159.9	2229.5	2314.9	2487.4	2659.9	2813.4	2979.5
27.5°	1557.0	1675.7	1807.0	1946.3	2101.3	2204.2	2288.0	2473.2	2683.6	2848.2	3019.1
30°	1509.5	1631.4	1758.0	1883.0	2057.0	2155.1	2251.6	2455.8	2696.3	2884.6	3015.9
32.5°	1463.6	1566.5	1691.5	1813.3	1985.8	2093.4	2202.6	2438.4	2701.0	2859.3	2922.5
35°	1400.4	1508.0	1609.2	1739.0	1913.0	2019.0	2147.2	2436.8	2680.5	2778.6	2746.9
37.5°	1341.8	1432.0	1528.5	1644.0	1822.8	1960.5	2093.4	2395.6	2612.4	2618.7	2439.9
40°	1276.9	1351.3	1432.0	1553.8	1746.9	1883.0	2027.0	2332.3	2489.0	2395.6	2080.8
42.5°	1202.6	1269.0	1332.3	1451.0	1661.4	1813.3	1968.4	2253.2	2310.2	2095.0	1767.5
45°	1123.4	1177.2	1235.8	1360.8	1571.2	1721.6	1876.6	2131.4	2072.8	1769.0	1457.3
47.5°	1041.2	1087.1	1144.0	1257.9	1474.7	1628.2	1775.4	1957.3	1808.6	1482.6	1221.6
50°	958.9	995.3	1050.7	1167.8	1376.6	1515.9	1651.9	1770.6	1561.8	1272.2	1009.5
52.5°	878.2	906.7	963.6	1063.3	1265.9	1398.8	1496.9	1542.8	1330.7	1050.7	876.6
55°	792.7	824.4	862.4	963.6	1164.6	1262.7	1327.6	1326.0	1107.6	890.8	724.7
57.5°	710.5	738.9	772.2	873.4	1036.4	1102.9	1158.3	1131.4	924.1	729.5	621.9
60°	637.7	653.5	689.9	775.3	898.8	955.7	987.4	941.5	754.8	615.5	514.3
62.5°	558.6	574.4	604.4	685.1	761.1	791.2	818.1	759.5	623.4	501.6	439.9
65°	485.8	506.3	525.3	590.2	631.3	667.7	664.6	615.5	487.4	408.2	357.6
67.5°	422.5	430.4	446.2	485.8	504.8	531.7	533.2	477.9	392.4	332.3	302.2
70°	354.4	362.4	373.4	392.4	405.1	411.4	408.2	359.2	295.9	259.5	232.6
72.5°	295.9	294.3	302.2	302.2	314.9	313.3	303.8	265.8	224.7	194.6	178.8
75°	232.6	234.2	235.8	232.6	227.9	221.5	213.6	185.1	158.2	144.0	129.8
77.5°	182.0	178.8	180.4	169.3	163.0	156.6	145.6	131.3	109.2	106.0	99.7
80°	129.8	128.2	126.6	121.8	107.6	101.3	93.4	85.4	80.7	77.5	76.0
82.5°	87.0	87.0	83.9	74.4	66.5	61.7	60.1	57.0	52.2	52.2	50.6
85°	52.2	50.6	47.5	38.0	33.2	33.2	33.2	33.2	30.1	30.1	28.5
87.5°	20.6	19.0	14.2	14.2	12.7	12.7	12.7	11.1	11.1	9.5	9.5
90°	1.0	3.3	5.6	7.9	10.2	11.4	12.9	15.9	18.8	21.8	24.8
92.5°	31.0	32.4	33.8	35.1	36.5	37.2	37.9	39.2	40.6	41.9	43.3
95°	60.9	62.5	64.1	65.7	67.3	68.1	69.0	70.9	72.7	74.6	76.4
97.5°	100.1	101.3	102.4	103.6	104.7	105.3	106.0	107.4	108.7	110.1	111.5
100°	140.4	141.8	143.1	144.5	145.8	146.5	147.1	148.2	149.4	150.5	151.7
102.5°	186.8	187.5	188.2	188.9	189.6	189.9	190.7	192.3	193.9	195.5	197.1
105°	232.2	232.7	233.1	233.6	234.1	234.3	235.3	237.4	239.5	241.5	243.6
107.5°	285.9	286.1	286.3	286.6	286.8	286.9	287.4	288.3	289.2	290.1	291.0
110°	335.4	335.9	336.3	336.8	337.3	337.5	337.7	338.2	338.6	339.1	339.5

TEST NUMBER: P1032089

CATALOG NUMBER: S123RDIW-B1165D1030UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	387.0	387.2	387.4	387.7	387.9	388.0	388.0	388.0	388.0	388.0	388.0
115°	438.6	439.3	440.0	440.7	441.4	441.7	441.5	441.0	440.5	440.1	439.6
117.5°	491.2	491.4	491.7	491.9	492.2	492.3	492.1	491.6	491.1	490.7	490.2
120°	539.8	541.2	542.5	543.9	545.2	545.9	545.3	544.2	543.1	541.9	540.8
122.5°	590.3	591.2	592.1	593.0	593.9	594.4	594.2	593.7	593.3	592.8	592.4
125°	641.9	642.6	643.3	644.0	644.7	645.0	644.8	644.3	643.9	643.4	643.0
127.5°	689.4	690.8	692.2	693.5	694.9	695.6	695.4	694.9	694.4	694.0	693.5
130°	736.9	738.7	740.5	742.4	744.2	745.1	744.8	744.1	743.4	742.7	742.0
132.5°	784.3	786.1	788.0	789.8	791.7	792.6	792.4	791.9	791.4	791.0	790.5
135°	832.8	834.2	835.6	836.9	838.3	839.0	838.9	838.7	838.4	838.2	838.0
137.5°	877.2	878.4	879.5	880.7	881.8	882.4	882.7	883.4	884.1	884.8	885.5
140°	923.7	924.8	926.0	927.1	928.2	928.8	928.9	929.2	929.4	929.7	929.9
142.5°	966.0	967.1	968.3	969.4	970.5	971.1	971.3	971.8	972.3	972.7	973.2
145°	1010.4	1010.8	1011.3	1011.7	1012.2	1012.4	1012.7	1013.4	1014.1	1014.8	1015.5
147.5°	1048.5	1049.4	1050.4	1051.3	1052.2	1052.7	1053.0	1053.7	1054.4	1055.1	1055.8
150°	1088.8	1089.3	1089.7	1090.2	1090.7	1090.9	1091.1	1091.6	1092.0	1092.5	1092.9
152.5°	1121.8	1122.5	1123.2	1123.9	1124.6	1124.9	1125.0	1125.2	1125.5	1125.7	1125.9
155°	1156.9	1156.9	1156.9	1156.9	1156.9	1156.9	1157.0	1157.2	1157.5	1157.7	1157.9
157.5°	1186.8	1186.6	1186.4	1186.1	1185.9	1185.8	1185.9	1186.1	1186.4	1186.6	1186.8
160°	1214.7	1214.2	1213.8	1213.3	1212.8	1212.6	1212.6	1212.6	1212.6	1212.6	1212.6
162.5°	1239.5	1238.8	1238.1	1237.4	1236.7	1236.4	1236.5	1236.7	1237.0	1237.2	1237.4
165°	1260.1	1259.4	1258.7	1258.0	1257.3	1257.0	1257.0	1257.0	1257.0	1257.0	1257.0
167.5°	1277.7	1276.8	1275.8	1274.9	1274.0	1273.5	1273.6	1273.9	1274.1	1274.4	1274.6
170°	1292.1	1291.2	1290.3	1289.4	1288.5	1288.0	1288.0	1288.0	1288.0	1288.0	1288.0
172.5°	1303.5	1302.6	1301.6	1300.7	1299.8	1299.3	1299.3	1299.3	1299.3	1299.3	1299.3
175°	1310.7	1309.8	1308.8	1307.9	1307.0	1306.5	1306.5	1306.5	1306.5	1306.5	1306.5
177.5°	1314.8	1313.9	1313.0	1312.1	1311.2	1310.7	1310.7	1310.7	1310.7	1310.7	1310.7
180°	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8

TEST NUMBER: P1032089

CATALOG NUMBER: S123RDIW-B1165D1030UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2
2.5°	1951.0	1951.0	1965.2	1979.5	1971.6	1976.3	1993.7	1987.4	2000.1	1998.5	2003.2
5°	2098.2	2115.6	2129.8	2159.9	2164.6	2159.9	2189.9	2197.8	2212.1	2194.7	2202.6
7.5°	2264.3	2300.7	2335.5	2379.8	2394.1	2397.2	2413.0	2435.2	2454.2	2419.4	2436.8
10°	2425.7	2481.1	2552.3	2591.8	2626.7	2639.3	2652.0	2666.2	2688.4	2708.9	2693.1
12.5°	2599.8	2680.5	2748.5	2819.7	2862.4	2857.7	2894.1	2903.6	2921.0	2925.7	2932.0
15°	2742.2	2856.1	2898.8	3004.8	3014.3	3046.0	3087.1	3123.5	3128.3	3118.8	3118.8
17.5°	2878.2	2976.3	3052.3	3137.7	3155.1	3182.0	3234.3	3251.7	3258.0	3256.4	3256.4
20°	2989.0	3053.9	3182.0	3253.3	3281.7	3316.5	3352.9	3375.1	3379.8	3386.2	3376.7
22.5°	3061.8	3159.9	3264.3	3322.9	3346.6	3359.3	3383.0	3389.3	3381.4	3383.0	3384.6
25°	3118.8	3215.3	3278.6	3294.4	3292.8	3277.0	3259.6	3229.5	3226.4	3213.7	3188.4
27.5°	3134.6	3171.0	3163.1	3098.2	3033.3	3027.0	2922.5	2865.6	2800.7	2810.2	2773.8
30°	3049.1	3001.7	2889.3	2724.8	2656.7	2546.0	2428.9	2307.0	2259.6	2207.3	2303.9
32.5°	2840.3	2671.0	2471.6	2258.0	2144.0	2045.9	1920.9	1832.3	1781.7	1739.0	1821.3
35°	2525.4	2261.1	1996.9	1794.4	1701.0	1612.4	1495.3	1451.0	1387.7	1394.0	1401.9
37.5°	2120.3	1829.2	1629.8	1430.4	1368.7	1332.3	1246.9	1178.8	1156.7	1150.3	1150.3
40°	1740.6	1501.6	1324.4	1167.8	1120.3	1090.2	1022.2	990.5	966.8	960.5	968.4
42.5°	1439.9	1235.8	1098.1	993.7	960.5	922.5	894.0	854.5	849.7	838.6	852.9
45°	1208.9	1031.7	928.8	852.9	824.4	810.1	778.5	754.8	745.3	743.7	754.8
47.5°	1025.3	887.7	797.5	750.0	727.9	713.6	686.7	677.2	667.7	670.9	666.2
50°	860.8	757.9	699.4	656.7	642.4	628.2	610.8	601.3	596.5	596.5	595.0
52.5°	738.9	653.5	615.5	576.0	569.6	561.7	542.7	536.4	528.5	526.9	533.2
55°	632.9	574.4	536.4	512.7	506.3	490.5	482.6	474.7	469.9	466.8	468.4
57.5°	541.2	496.8	471.5	451.0	439.9	433.6	419.3	417.7	414.6	414.6	413.0
60°	465.2	433.6	403.5	390.8	382.9	375.0	373.4	363.9	359.2	362.4	360.8
62.5°	394.0	368.7	351.3	337.0	332.3	326.0	321.2	318.0	313.3	314.9	314.9
65°	329.1	308.6	295.9	283.2	281.7	275.3	273.7	270.6	270.6	269.0	272.2
67.5°	270.6	256.3	245.3	237.3	232.6	234.2	227.9	223.1	223.1	221.5	226.3
70°	215.2	207.3	196.2	186.7	180.4	180.4	172.5	170.9	170.9	170.9	169.3
72.5°	166.1	151.9	147.2	144.0	144.0	144.0	140.8	140.8	139.2	140.8	139.2
75°	123.4	121.8	118.7	117.1	117.1	115.5	113.9	113.9	113.9	113.9	113.9
77.5°	96.5	96.5	93.4	91.8	91.8	91.8	90.2	90.2	88.6	88.6	88.6
80°	71.2	71.2	68.0	68.0	68.0	66.5	66.5	66.5	68.0	66.5	66.5
82.5°	49.1	49.1	47.5	49.1	47.5	45.9	45.9	45.9	44.3	45.9	45.9
85°	28.5	28.5	26.9	25.3	26.9	26.9	25.3	26.9	25.3	26.9	25.3
87.5°	11.1	9.5	9.5	9.5	7.9	9.5	7.9	7.9	9.5	7.9	9.5
90°	25.7	26.6	27.5	28.4	28.9	29.1	29.6	30.1	30.5	31.0	30.5
92.5°	44.0	44.7	45.4	46.1	46.4	46.2	45.7	45.3	44.8	44.4	44.8
95°	77.3	78.2	79.1	80.0	80.5	80.5	80.5	80.5	80.5	80.5	80.5
97.5°	112.6	113.8	114.9	116.0	116.6	116.5	116.3	116.0	115.8	115.6	115.8
100°	152.4	153.1	153.8	154.5	154.8	155.0	155.5	156.0	156.4	156.9	156.4
102.5°	197.8	198.5	199.2	199.9	200.2	200.1	199.9	199.6	199.4	199.2	199.4
105°	243.6	243.6	243.6	243.6	243.6	243.8	244.3	244.7	245.2	245.6	245.2
107.5°	291.7	292.4	293.1	293.8	294.1	294.0	293.8	293.5	293.3	293.1	293.3
110°	340.4	341.4	342.3	343.2	343.7	343.5	343.0	342.5	342.1	341.6	342.1

TEST NUMBER: P1032089

CATALOG NUMBER: S123RDIW-B1165D1030UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	389.2	390.3	391.5	392.6	393.2	393.2	393.2	393.2	393.2	393.2	393.2
115°	439.8	440.1	440.3	440.6	440.7	440.6	440.3	440.1	439.8	439.6	439.8
117.5°	490.2	490.2	490.2	490.2	490.2	489.9	489.2	488.5	487.8	487.1	487.8
120°	540.6	540.4	540.1	539.9	539.8	539.6	539.1	538.6	538.2	537.7	538.2
122.5°	591.7	591.0	590.3	589.6	589.3	589.0	588.3	587.6	586.9	586.2	586.9
125°	642.1	641.1	640.2	639.3	638.8	638.3	637.4	636.5	635.6	634.7	635.6
127.5°	692.1	690.7	689.4	688.0	687.3	686.8	685.9	685.0	684.1	683.2	684.1
130°	741.1	740.2	739.3	738.4	737.9	737.1	735.5	733.9	732.3	730.7	732.3
132.5°	789.4	788.2	787.1	786.0	785.4	784.8	783.7	782.5	781.4	780.2	781.4
135°	837.1	836.2	835.3	834.4	833.9	833.7	833.2	832.7	832.3	831.8	832.3
137.5°	884.3	883.2	882.0	880.9	880.3	880.0	879.3	878.6	877.9	877.2	877.9
140°	929.7	929.4	929.2	928.9	928.8	928.0	926.4	924.8	923.2	921.6	923.2
142.5°	973.0	972.8	972.5	972.3	972.2	971.6	970.5	969.3	968.2	967.0	968.2
145°	1015.3	1015.1	1014.8	1014.6	1014.5	1014.0	1013.1	1012.2	1011.3	1010.4	1011.3
147.5°	1055.8	1055.8	1055.8	1055.8	1055.8	1055.1	1053.7	1052.4	1051.0	1049.6	1051.0
150°	1092.9	1092.9	1092.9	1092.9	1092.9	1092.2	1090.8	1089.5	1088.1	1086.7	1088.1
152.5°	1126.4	1126.8	1127.3	1127.8	1128.0	1127.4	1126.3	1125.1	1124.0	1122.8	1124.0
155°	1158.8	1159.8	1160.7	1161.6	1162.1	1161.3	1159.7	1158.0	1156.4	1154.8	1156.4
157.5°	1187.7	1188.7	1189.6	1190.5	1191.0	1190.3	1188.9	1187.6	1186.2	1184.8	1186.2
160°	1213.8	1214.9	1216.1	1217.2	1217.8	1217.3	1216.4	1215.5	1214.6	1213.7	1214.6
162.5°	1238.6	1239.7	1240.9	1242.0	1242.6	1241.8	1240.2	1238.5	1236.9	1235.3	1236.9
165°	1258.4	1259.8	1261.1	1262.5	1263.2	1262.4	1260.8	1259.2	1257.6	1256.0	1257.6
167.5°	1276.0	1277.3	1278.7	1280.0	1280.7	1280.0	1278.7	1277.3	1276.0	1274.6	1276.0
170°	1289.6	1291.2	1292.8	1294.4	1295.2	1294.4	1292.8	1291.2	1289.6	1288.0	1289.6
172.5°	1300.7	1302.1	1303.4	1304.8	1305.5	1304.7	1303.1	1301.5	1299.9	1298.3	1299.9
175°	1307.9	1309.3	1310.6	1312.0	1312.7	1311.9	1310.3	1308.7	1307.1	1305.5	1307.1
177.5°	1312.1	1313.5	1314.8	1316.2	1316.9	1316.1	1314.5	1312.8	1311.2	1309.6	1311.2
180°	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8

TEST NUMBER: P1032089

CATALOG NUMBER: S123RDIW-B1165D1030UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2
2.5°	1995.3	1985.8	1979.5	1974.7	1970.0	1984.2	1965.2	1944.7	1930.4	1920.9	1917.8
5°	2204.2	2183.6	2166.2	2152.0	2155.1	2155.1	2121.9	2085.5	2053.9	2036.4	2017.5
7.5°	2446.3	2424.1	2389.3	2381.4	2375.1	2335.5	2302.3	2235.8	2196.3	2156.7	2121.9
10°	2686.8	2658.3	2625.1	2614.0	2598.2	2549.1	2498.5	2413.0	2364.0	2291.2	2245.3
12.5°	2911.5	2876.7	2843.4	2835.5	2811.8	2769.1	2682.0	2593.4	2509.6	2432.0	2351.3
15°	3099.8	3090.3	3039.6	3008.0	2955.8	2897.2	2878.2	2758.0	2652.0	2571.3	2425.7
17.5°	3258.0	3213.7	3166.2	3145.7	3125.1	3057.0	2989.0	2865.6	2751.7	2633.0	2539.6
20°	3384.6	3335.5	3302.3	3272.2	3262.7	3185.2	3077.6	2968.4	2843.4	2710.5	2588.7
22.5°	3390.9	3384.6	3362.4	3345.0	3326.0	3275.4	3190.0	3053.9	2921.0	2775.4	2615.6
25°	3259.6	3250.1	3313.4	3297.6	3310.2	3291.2	3245.3	3131.4	2976.3	2805.5	2644.1
27.5°	2864.0	2960.5	3060.2	3095.0	3118.8	3186.8	3208.9	3145.7	3020.7	2838.7	2658.3
30°	2326.0	2454.2	2615.6	2702.6	2769.1	2895.6	3060.2	3080.8	3022.2	2876.7	2655.1
32.5°	1826.0	1943.1	2072.8	2175.7	2264.3	2523.8	2745.3	2905.1	2933.6	2857.7	2663.0
35°	1471.6	1522.2	1645.6	1743.7	1864.0	2085.5	2346.6	2604.5	2778.6	2788.1	2639.3
37.5°	1213.6	1240.5	1348.1	1403.5	1474.7	1669.3	1913.0	2250.1	2520.6	2648.8	2572.9
40°	1004.8	1066.5	1128.2	1159.8	1210.5	1345.0	1579.2	1843.4	2178.9	2416.2	2470.0
42.5°	871.9	898.8	938.3	982.6	1014.3	1131.4	1288.0	1530.1	1832.3	2163.0	2311.8
45°	769.0	778.5	819.6	848.1	881.4	963.6	1074.4	1276.9	1542.8	1868.7	2121.9
47.5°	683.6	702.6	724.7	742.1	764.3	827.6	922.5	1069.6	1303.8	1595.0	1867.1
50°	607.6	618.7	647.2	655.1	670.9	715.2	788.0	900.3	1093.4	1326.0	1607.6
52.5°	536.4	557.0	568.1	579.1	593.4	629.8	677.2	769.0	914.6	1132.9	1371.9
55°	481.0	487.4	503.2	512.7	523.7	549.1	590.2	658.2	772.2	946.2	1172.5
57.5°	427.2	427.2	443.1	451.0	462.0	481.0	517.4	569.6	651.9	781.7	989.0
60°	370.3	371.8	384.5	394.0	397.2	416.2	446.2	487.4	550.6	645.6	814.9
62.5°	319.6	327.5	333.9	337.0	348.1	359.2	384.5	413.0	457.3	541.2	661.4
65°	276.9	278.5	283.2	286.4	291.1	303.8	322.8	341.8	379.8	441.5	539.6
67.5°	227.9	234.2	240.5	240.5	245.3	251.6	270.6	286.4	314.9	351.3	417.7
70°	170.9	174.1	183.5	188.3	194.6	205.7	215.2	224.7	246.8	273.7	324.4
72.5°	142.4	142.4	145.6	147.2	147.2	155.1	169.3	178.8	189.9	208.9	243.7
75°	113.9	113.9	118.7	117.1	120.3	123.4	125.0	131.3	137.7	151.9	172.5
77.5°	90.2	91.8	91.8	93.4	93.4	94.9	96.5	99.7	102.9	110.8	120.3
80°	66.5	68.0	68.0	69.6	69.6	71.2	72.8	74.4	77.5	80.7	85.4
82.5°	45.9	47.5	47.5	49.1	47.5	49.1	50.6	50.6	52.2	55.4	57.0
85°	26.9	26.9	28.5	26.9	26.9	26.9	28.5	28.5	30.1	34.8	34.8
87.5°	7.9	9.5	7.9	9.5	9.5	9.5	9.5	11.1	11.1	12.7	14.2
90°	30.1	29.6	29.1	28.9	28.4	27.5	26.6	25.7	24.8	21.8	18.8
92.5°	45.3	45.7	46.2	46.4	46.1	45.4	44.7	44.0	43.3	41.9	40.6
95°	80.5	80.5	80.5	80.5	80.0	79.1	78.2	77.3	76.4	74.6	72.7
97.5°	116.0	116.3	116.5	116.6	116.0	114.9	113.8	112.6	111.5	110.1	108.7
100°	156.0	155.5	155.0	154.8	154.5	153.8	153.1	152.4	151.7	150.5	149.4
102.5°	199.6	199.9	200.1	200.2	199.9	199.2	198.5	197.8	197.1	195.5	193.9
105°	244.7	244.3	243.8	243.6	243.6	243.6	243.6	243.6	243.6	241.5	239.5
107.5°	293.5	293.8	294.0	294.1	293.8	293.1	292.4	291.7	291.0	290.1	289.2
110°	342.5	343.0	343.5	343.7	343.2	342.3	341.4	340.4	339.5	339.1	338.6

TEST NUMBER: P1032089

CATALOG NUMBER: S123RDIW-B1165D1030UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	393.2	393.2	393.2	393.2	392.6	391.5	390.3	389.2	388.0	388.0	388.0
115°	440.1	440.3	440.6	440.7	440.6	440.3	440.1	439.8	439.6	440.1	440.5
117.5°	488.5	489.2	489.9	490.2	490.2	490.2	490.2	490.2	490.2	490.7	491.1
120°	538.6	539.1	539.6	539.8	539.9	540.1	540.4	540.6	540.8	541.9	543.1
122.5°	587.6	588.3	589.0	589.3	589.6	590.3	591.0	591.7	592.4	592.8	593.3
125°	636.5	637.4	638.3	638.8	639.3	640.2	641.1	642.1	643.0	643.4	643.9
127.5°	685.0	685.9	686.8	687.3	688.0	689.4	690.7	692.1	693.5	694.0	694.4
130°	733.9	735.5	737.1	737.9	738.4	739.3	740.2	741.1	742.0	742.7	743.4
132.5°	782.5	783.7	784.8	785.4	786.0	787.1	788.2	789.4	790.5	791.0	791.4
135°	832.7	833.2	833.7	833.9	834.4	835.3	836.2	837.1	838.0	838.2	838.4
137.5°	878.6	879.3	880.0	880.3	880.9	882.0	883.2	884.3	885.5	884.8	884.1
140°	924.8	926.4	928.0	928.8	928.9	929.2	929.4	929.7	929.9	929.7	929.4
142.5°	969.3	970.5	971.6	972.2	972.3	972.5	972.8	973.0	973.2	972.7	972.3
145°	1012.2	1013.1	1014.0	1014.5	1014.6	1014.8	1015.1	1015.3	1015.5	1014.8	1014.1
147.5°	1052.4	1053.7	1055.1	1055.8	1055.8	1055.8	1055.8	1055.8	1055.8	1055.1	1054.4
150°	1089.5	1090.8	1092.2	1092.9	1092.9	1092.9	1092.9	1092.9	1092.9	1092.5	1092.0
152.5°	1125.1	1126.3	1127.4	1128.0	1127.8	1127.3	1126.8	1126.4	1125.9	1125.7	1125.5
155°	1158.0	1159.7	1161.3	1162.1	1161.6	1160.7	1159.8	1158.8	1157.9	1157.7	1157.5
157.5°	1187.6	1188.9	1190.3	1191.0	1190.5	1189.6	1188.7	1187.7	1186.8	1186.6	1186.4
160°	1215.5	1216.4	1217.3	1217.8	1217.2	1216.1	1214.9	1213.8	1212.6	1212.6	1212.6
162.5°	1238.5	1240.2	1241.8	1242.6	1242.0	1240.9	1239.7	1238.6	1237.4	1237.2	1237.0
165°	1259.2	1260.8	1262.4	1263.2	1262.5	1261.1	1259.8	1258.4	1257.0	1257.0	1257.0
167.5°	1277.3	1278.7	1280.0	1280.7	1280.0	1278.7	1277.3	1276.0	1274.6	1274.4	1274.1
170°	1291.2	1292.8	1294.4	1295.2	1294.4	1292.8	1291.2	1289.6	1288.0	1288.0	1288.0
172.5°	1301.5	1303.1	1304.7	1305.5	1304.8	1303.4	1302.1	1300.7	1299.3	1299.3	1299.3
175°	1308.7	1310.3	1311.9	1312.7	1312.0	1310.6	1309.3	1307.9	1306.5	1306.5	1306.5
177.5°	1312.8	1314.5	1316.1	1316.9	1316.2	1314.8	1313.5	1312.1	1310.7	1310.7	1310.7
180°	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8

TEST NUMBER: P1032089

CATALOG NUMBER: S123RDIW-B1165D1030UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2
2.5°	1913.0	1905.1	1897.2	1897.2	1879.8	1864.0	1856.1	1859.2	1849.7	1837.1	1824.4
5°	1996.9	1965.2	1958.9	1941.5	1917.8	1884.5	1867.1	1851.3	1832.3	1807.0	1783.3
7.5°	2074.4	2033.3	2011.1	1993.7	1947.8	1902.0	1864.0	1838.7	1805.4	1767.5	1739.0
10°	2175.7	2099.7	2076.0	2036.4	1971.6	1906.7	1862.4	1821.3	1775.4	1731.1	1693.1
12.5°	2256.4	2169.4	2125.1	2085.5	2001.6	1919.4	1845.0	1794.4	1739.0	1689.9	1640.9
15°	2348.2	2250.1	2172.5	2125.1	2019.0	1919.4	1835.5	1764.3	1702.6	1642.4	1599.7
17.5°	2392.5	2269.0	2234.2	2166.2	2012.7	1913.0	1810.2	1734.2	1659.9	1590.2	1539.6
20°	2462.1	2318.1	2231.1	2185.2	2049.1	1902.0	1781.7	1694.7	1617.1	1542.8	1489.0
22.5°	2466.8	2310.2	2253.2	2166.2	1998.5	1868.7	1756.4	1650.4	1560.2	1490.5	1435.2
25°	2455.8	2295.9	2216.8	2147.2	2008.0	1849.7	1705.7	1601.3	1512.7	1432.0	1367.1
27.5°	2451.0	2254.8	2180.4	2110.8	1954.2	1794.4	1675.7	1557.0	1455.7	1384.5	1318.1
30°	2444.7	2210.5	2120.3	2039.6	1895.6	1751.6	1609.2	1506.4	1409.8	1319.7	1253.2
32.5°	2403.5	2150.4	2058.6	1973.2	1818.1	1674.1	1561.8	1452.6	1348.1	1264.3	1204.1
35°	2390.9	2095.0	1974.7	1883.0	1731.1	1602.9	1484.2	1394.0	1295.9	1212.1	1140.9
37.5°	2354.5	2038.0	1908.3	1791.2	1633.0	1511.1	1424.1	1333.9	1239.0	1148.8	1091.8
40°	2291.2	1971.6	1824.4	1704.2	1541.2	1417.8	1337.1	1270.6	1177.2	1096.5	1026.9
42.5°	2197.8	1903.5	1745.3	1618.7	1438.3	1322.8	1256.4	1193.1	1114.0	1030.1	973.1
45°	2090.2	1813.3	1666.2	1525.4	1341.8	1229.5	1159.8	1121.9	1049.1	977.9	911.4
47.5°	1943.1	1720.0	1574.4	1428.8	1242.1	1132.9	1077.6	1039.6	989.0	911.4	857.6
50°	1758.0	1599.7	1462.1	1332.3	1144.0	1039.6	984.2	955.7	913.0	857.6	805.4
52.5°	1552.3	1460.5	1346.6	1226.3	1044.3	946.2	895.6	873.4	841.8	789.6	745.3
55°	1345.0	1305.4	1227.9	1109.2	939.9	859.2	814.9	786.4	762.7	724.7	686.7
57.5°	1159.8	1140.9	1087.1	995.3	852.9	769.0	731.0	712.0	693.1	664.6	626.6
60°	968.4	989.0	933.6	887.7	757.9	685.1	651.9	631.3	621.9	596.5	572.8
62.5°	802.2	821.2	789.6	754.8	663.0	598.1	577.5	558.6	552.2	530.1	506.3
65°	651.9	675.7	651.9	632.9	577.5	523.7	498.4	488.9	482.6	468.4	449.4
67.5°	519.0	542.7	531.7	507.9	490.5	446.2	432.0	422.5	419.3	408.2	392.4
70°	390.8	424.1	427.2	413.0	397.2	376.6	367.1	363.9	356.0	346.5	337.0
72.5°	281.7	319.6	321.2	321.2	311.7	311.7	302.2	297.5	297.5	288.0	276.9
75°	207.3	232.6	235.8	238.9	243.7	248.4	242.1	242.1	240.5	231.0	226.3
77.5°	137.7	159.8	167.7	178.8	185.1	185.1	188.3	191.5	188.3	183.5	180.4
80°	88.6	104.4	113.9	120.3	129.8	134.5	139.2	140.8	137.7	136.1	131.3
82.5°	58.5	63.3	68.0	76.0	87.0	94.9	94.9	93.4	96.5	94.9	93.4
85°	33.2	36.4	38.0	39.6	45.9	53.8	55.4	57.0	60.1	57.0	53.8
87.5°	12.7	14.2	14.2	14.2	17.4	19.0	23.7	30.1	28.5	25.3	25.3
90°	15.9	12.9	11.4	10.2	7.9	5.6	3.3	1.0	3.3	5.6	7.9
92.5°	39.2	37.9	37.2	36.5	35.1	33.8	32.4	31.0	32.4	33.8	35.1
95°	70.9	69.0	68.1	67.3	65.7	64.1	62.5	60.9	62.5	64.1	65.7
97.5°	107.4	106.0	105.3	104.7	103.6	102.4	101.3	100.1	101.3	102.4	103.6
100°	148.2	147.1	146.5	145.8	144.5	143.1	141.8	140.4	141.8	143.1	144.5
102.5°	192.3	190.7	189.9	189.6	188.9	188.2	187.5	186.8	187.5	188.2	188.9
105°	237.4	235.3	234.3	234.1	233.6	233.1	232.7	232.2	232.7	233.1	233.6
107.5°	288.3	287.4	286.9	286.8	286.6	286.3	286.1	285.9	286.1	286.3	286.6
110°	338.2	337.7	337.5	337.3	336.8	336.3	335.9	335.4	335.9	336.3	336.8

TEST NUMBER: P1032089

CATALOG NUMBER: S123RDIW-B1165D1030UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	388.0	388.0	388.0	387.9	387.7	387.4	387.2	387.0	387.2	387.4	387.7
115°	441.0	441.5	441.7	441.4	440.7	440.0	439.3	438.6	439.3	440.0	440.7
117.5°	491.6	492.1	492.3	492.2	491.9	491.7	491.4	491.2	491.4	491.7	491.9
120°	544.2	545.3	545.9	545.2	543.9	542.5	541.2	539.8	541.2	542.5	543.9
122.5°	593.7	594.2	594.4	593.9	593.0	592.1	591.2	590.3	591.2	592.1	593.0
125°	644.3	644.8	645.0	644.7	644.0	643.3	642.6	641.9	642.6	643.3	644.0
127.5°	694.9	695.4	695.6	694.9	693.5	692.2	690.8	689.4	690.8	692.2	693.5
130°	744.1	744.8	745.1	744.2	742.4	740.5	738.7	736.9	738.7	740.5	742.4
132.5°	791.9	792.4	792.6	791.7	789.8	788.0	786.1	784.3	786.1	788.0	789.8
135°	838.7	838.9	839.0	838.3	836.9	835.6	834.2	832.8	834.2	835.6	836.9
137.5°	883.4	882.7	882.4	881.8	880.7	879.5	878.4	877.2	878.4	879.5	880.7
140°	929.2	928.9	928.8	928.2	927.1	926.0	924.8	923.7	924.8	926.0	927.1
142.5°	971.8	971.3	971.1	970.5	969.4	968.3	967.1	966.0	967.1	968.3	969.4
145°	1013.4	1012.7	1012.4	1012.2	1011.7	1011.3	1010.8	1010.4	1010.8	1011.3	1011.7
147.5°	1053.7	1053.0	1052.7	1052.2	1051.3	1050.4	1049.4	1048.5	1049.4	1050.4	1051.3
150°	1091.6	1091.1	1090.9	1090.7	1090.2	1089.7	1089.3	1088.8	1089.3	1089.7	1090.2
152.5°	1125.2	1125.0	1124.9	1124.6	1123.9	1123.2	1122.5	1121.8	1122.5	1123.2	1123.9
155°	1157.2	1157.0	1156.9	1156.9	1156.9	1156.9	1156.9	1156.9	1156.9	1156.9	1156.9
157.5°	1186.1	1185.9	1185.8	1185.9	1186.1	1186.4	1186.6	1186.8	1186.6	1186.4	1186.1
160°	1212.6	1212.6	1212.6	1212.8	1213.3	1213.8	1214.2	1214.7	1214.2	1213.8	1213.3
162.5°	1236.7	1236.5	1236.4	1236.7	1237.4	1238.1	1238.8	1239.5	1238.8	1238.1	1237.4
165°	1257.0	1257.0	1257.0	1257.3	1258.0	1258.7	1259.4	1260.1	1259.4	1258.7	1258.0
167.5°	1273.9	1273.6	1273.5	1274.0	1274.9	1275.8	1276.8	1277.7	1276.8	1275.8	1274.9
170°	1288.0	1288.0	1288.0	1288.5	1289.4	1290.3	1291.2	1292.1	1291.2	1290.3	1289.4
172.5°	1299.3	1299.3	1299.3	1299.8	1300.7	1301.6	1302.6	1303.5	1302.6	1301.6	1300.7
175°	1306.5	1306.5	1306.5	1307.0	1307.9	1308.8	1309.8	1310.7	1309.8	1308.8	1307.9
177.5°	1310.7	1310.7	1310.7	1311.2	1312.1	1313.0	1313.9	1314.8	1313.9	1313.0	1312.1
180°	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8

TEST NUMBER: P1032089

CATALOG NUMBER: S123RDIW-B1165D1030UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2
2.5°	1824.4	1816.5	1813.3	1805.4	1786.4	1773.8	1759.5	1750.0	1751.6	1743.7	1748.5
5°	1767.5	1765.9	1754.8	1739.0	1712.1	1697.8	1672.5	1659.9	1653.5	1655.1	1645.6
7.5°	1720.0	1705.7	1697.8	1672.5	1647.2	1617.1	1596.6	1585.5	1576.0	1566.5	1560.2
10°	1666.2	1653.5	1640.9	1614.0	1579.2	1550.7	1522.2	1511.1	1496.9	1490.5	1485.8
12.5°	1609.2	1601.3	1585.5	1553.8	1514.3	1487.4	1454.2	1447.8	1428.8	1416.2	1413.0
15°	1557.0	1552.3	1523.8	1487.4	1447.8	1420.9	1392.4	1373.5	1341.8	1348.1	1337.1
17.5°	1501.6	1481.1	1463.6	1414.6	1395.6	1354.5	1321.2	1311.7	1289.6	1275.4	1261.1
20°	1439.9	1427.3	1405.1	1373.5	1327.6	1280.1	1254.8	1239.0	1226.3	1204.1	1197.8
22.5°	1381.4	1365.5	1346.6	1305.4	1265.9	1226.3	1191.5	1177.2	1161.4	1145.6	1136.1
25°	1335.5	1311.7	1291.2	1240.5	1201.0	1167.8	1145.6	1121.9	1099.7	1090.2	1087.1
27.5°	1264.3	1250.0	1229.5	1182.0	1145.6	1109.2	1088.6	1072.8	1049.1	1038.0	1028.5
30°	1218.4	1189.9	1166.2	1128.2	1091.8	1052.2	1033.3	1014.3	1000.0	985.8	974.7
32.5°	1156.7	1134.5	1115.5	1077.6	1041.2	1004.8	984.2	955.7	947.8	936.7	924.1
35°	1096.5	1082.3	1061.7	1020.6	981.0	955.7	933.6	906.7	897.2	889.3	878.2
37.5°	1039.6	1019.0	1004.8	965.2	930.4	900.3	882.9	860.8	854.5	845.0	837.0
40°	990.5	970.0	955.7	916.2	879.8	848.1	837.0	814.9	805.4	794.3	789.6
42.5°	935.2	917.7	898.8	870.3	832.3	800.7	778.5	765.8	753.2	748.4	738.9
45°	876.6	860.8	846.5	814.9	775.3	753.2	734.2	716.8	707.3	699.4	693.1
47.5°	826.0	811.7	792.7	757.9	726.3	705.7	686.7	669.3	659.8	650.3	642.4
50°	767.4	759.5	738.9	705.7	675.7	651.9	634.5	618.7	612.4	601.3	588.6
52.5°	715.2	701.0	683.6	656.7	629.8	601.3	577.5	568.1	557.0	550.6	539.6
55°	653.5	644.0	625.0	601.3	572.8	549.1	531.7	519.0	504.8	498.4	484.2
57.5°	601.3	583.9	574.4	544.3	517.4	493.7	481.0	468.4	452.5	443.1	436.7
60°	544.3	528.5	514.3	488.9	469.9	444.6	425.6	414.6	403.5	390.8	384.5
62.5°	488.9	476.3	458.9	438.3	414.6	394.0	379.8	363.9	357.6	344.9	340.2
65°	428.8	419.3	405.1	381.3	362.4	344.9	330.7	318.0	311.7	307.0	303.8
67.5°	375.0	362.4	352.9	332.3	311.7	297.5	289.6	281.7	273.7	269.0	264.2
70°	319.6	310.1	300.6	281.7	267.4	254.8	248.4	242.1	237.3	232.6	227.9
72.5°	262.7	257.9	248.4	235.8	224.7	215.2	210.4	202.5	197.8	189.9	186.7
75°	216.8	208.9	204.1	193.0	183.5	175.6	169.3	159.8	153.5	150.3	148.7
77.5°	170.9	167.7	161.4	151.9	147.2	139.2	129.8	126.6	123.4	123.4	121.8
80°	128.2	123.4	118.7	110.8	106.0	99.7	99.7	99.7	98.1	99.7	98.1
82.5°	87.0	83.9	80.7	76.0	74.4	74.4	76.0	76.0	76.0	76.0	76.0
85°	50.6	50.6	50.6	52.2	50.6	50.6	52.2	53.8	52.2	52.2	50.6
87.5°	23.7	23.7	25.3	25.3	26.9	26.9	26.9	26.9	26.9	26.9	28.5
90°	10.2	11.4	12.9	15.9	18.8	21.8	24.8	25.7	26.6	27.5	28.4
92.5°	36.5	37.2	37.9	39.2	40.6	41.9	43.3	44.0	44.7	45.4	46.1
95°	67.3	68.1	69.0	70.9	72.7	74.6	76.4	77.3	78.2	79.1	80.0
97.5°	104.7	105.3	106.0	107.4	108.7	110.1	111.5	112.6	113.8	114.9	116.0
100°	145.8	146.5	147.1	148.2	149.4	150.5	151.7	152.4	153.1	153.8	154.5
102.5°	189.6	189.9	190.7	192.3	193.9	195.5	197.1	197.8	198.5	199.2	199.9
105°	234.1	234.3	235.3	237.4	239.5	241.5	243.6	243.6	243.6	243.6	243.6
107.5°	286.8	286.9	287.4	288.3	289.2	290.1	291.0	291.7	292.4	293.1	293.8
110°	337.3	337.5	337.7	338.2	338.6	339.1	339.5	340.4	341.4	342.3	343.2

TEST NUMBER: P1032089

CATALOG NUMBER: S123RDIW-B1165D1030UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	387.9	388.0	388.0	388.0	388.0	388.0	388.0	389.2	390.3	391.5	392.6
115°	441.4	441.7	441.5	441.0	440.5	440.1	439.6	439.8	440.1	440.3	440.6
117.5°	492.2	492.3	492.1	491.6	491.1	490.7	490.2	490.2	490.2	490.2	490.2
120°	545.2	545.9	545.3	544.2	543.1	541.9	540.8	540.6	540.4	540.1	539.9
122.5°	593.9	594.4	594.2	593.7	593.3	592.8	592.4	591.7	591.0	590.3	589.6
125°	644.7	645.0	644.8	644.3	643.9	643.4	643.0	642.1	641.1	640.2	639.3
127.5°	694.9	695.6	695.4	694.9	694.4	694.0	693.5	692.1	690.7	689.4	688.0
130°	744.2	745.1	744.8	744.1	743.4	742.7	742.0	741.1	740.2	739.3	738.4
132.5°	791.7	792.6	792.4	791.9	791.4	791.0	790.5	789.4	788.2	787.1	786.0
135°	838.3	839.0	838.9	838.7	838.4	838.2	838.0	837.1	836.2	835.3	834.4
137.5°	881.8	882.4	882.7	883.4	884.1	884.8	885.5	884.3	883.2	882.0	880.9
140°	928.2	928.8	928.9	929.2	929.4	929.7	929.9	929.7	929.4	929.2	928.9
142.5°	970.5	971.1	971.3	971.8	972.3	972.7	973.2	973.0	972.8	972.5	972.3
145°	1012.2	1012.4	1012.7	1013.4	1014.1	1014.8	1015.5	1015.3	1015.1	1014.8	1014.6
147.5°	1052.2	1052.7	1053.0	1053.7	1054.4	1055.1	1055.8	1055.8	1055.8	1055.8	1055.8
150°	1090.7	1090.9	1091.1	1091.6	1092.0	1092.5	1092.9	1092.9	1092.9	1092.9	1092.9
152.5°	1124.6	1124.9	1125.0	1125.2	1125.5	1125.7	1125.9	1126.4	1126.8	1127.3	1127.8
155°	1156.9	1156.9	1157.0	1157.2	1157.5	1157.7	1157.9	1158.8	1159.8	1160.7	1161.6
157.5°	1185.9	1185.8	1185.9	1186.1	1186.4	1186.6	1186.8	1187.7	1188.7	1189.6	1190.5
160°	1212.8	1212.6	1212.6	1212.6	1212.6	1212.6	1212.6	1213.8	1214.9	1216.1	1217.2
162.5°	1236.7	1236.4	1236.5	1236.7	1237.0	1237.2	1237.4	1238.6	1239.7	1240.9	1242.0
165°	1257.3	1257.0	1257.0	1257.0	1257.0	1257.0	1257.0	1258.4	1259.8	1261.1	1262.5
167.5°	1274.0	1273.5	1273.6	1273.9	1274.1	1274.4	1274.6	1276.0	1277.3	1278.7	1280.0
170°	1288.5	1288.0	1288.0	1288.0	1288.0	1288.0	1288.0	1289.6	1291.2	1292.8	1294.4
172.5°	1299.8	1299.3	1299.3	1299.3	1299.3	1299.3	1299.3	1300.7	1302.1	1303.4	1304.8
175°	1307.0	1306.5	1306.5	1306.5	1306.5	1306.5	1306.5	1307.9	1309.3	1310.6	1312.0
177.5°	1311.2	1310.7	1310.7	1310.7	1310.7	1310.7	1310.7	1312.1	1313.5	1314.8	1316.2
180°	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8

TEST NUMBER: P1032089

CATALOG NUMBER: S123RDIW-B1165D1030UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2
2.5°	1746.9	1748.5	1743.7	1734.2	1732.6	1735.8	1745.3	1742.1	1734.2	1748.5	1735.8
5°	1650.4	1642.4	1639.3	1642.4	1633.0	1628.2	1637.7	1633.0	1637.7	1639.3	1644.0
7.5°	1557.0	1558.6	1549.1	1550.7	1538.0	1541.2	1541.2	1541.2	1545.9	1549.1	1555.4
10°	1476.3	1479.5	1468.4	1470.0	1460.5	1454.2	1458.9	1468.4	1468.4	1468.4	1471.6
12.5°	1411.4	1397.2	1389.3	1387.7	1376.6	1373.5	1382.9	1386.1	1394.0	1394.0	1398.8
15°	1330.7	1327.6	1321.2	1321.2	1294.3	1300.7	1303.8	1314.9	1330.7	1318.1	1321.2
17.5°	1257.9	1250.0	1242.1	1239.0	1235.8	1226.3	1239.0	1237.4	1246.9	1248.5	1253.2
20°	1193.1	1186.7	1170.9	1172.5	1175.7	1161.4	1169.3	1169.3	1178.8	1188.3	1199.4
22.5°	1129.8	1123.4	1115.5	1118.7	1109.2	1106.0	1106.0	1114.0	1125.0	1132.9	1131.4
25°	1080.7	1069.6	1064.9	1060.2	1055.4	1058.6	1053.8	1061.7	1069.6	1074.4	1069.6
27.5°	1025.3	1020.6	1011.1	1006.4	998.4	1001.6	1004.8	1011.1	1015.9	1015.9	1020.6
30°	971.5	965.2	962.1	957.3	957.3	951.0	952.6	958.9	963.6	968.4	974.7
32.5°	919.3	914.6	909.8	909.8	906.7	905.1	903.5	913.0	913.0	922.5	922.5
35°	876.6	868.7	868.7	860.8	863.9	862.4	859.2	865.5	867.1	873.4	871.9
37.5°	829.1	829.1	826.0	818.1	811.7	813.3	821.2	821.2	826.0	824.4	829.1
40°	781.7	778.5	778.5	773.8	772.2	770.6	772.2	773.8	781.7	780.1	781.7
42.5°	734.2	735.8	727.9	727.9	727.9	723.1	724.7	726.3	729.5	732.6	737.4
45°	688.3	685.1	683.6	680.4	677.2	678.8	677.2	683.6	682.0	685.1	689.9
47.5°	639.3	634.5	632.9	626.6	626.6	629.8	628.2	632.9	634.5	639.3	636.1
50°	591.8	585.5	580.7	582.3	572.8	576.0	576.0	580.7	585.5	587.0	590.2
52.5°	536.4	534.8	533.2	525.3	523.7	522.2	523.7	525.3	531.7	536.4	538.0
55°	482.6	481.0	471.5	468.4	463.6	463.6	466.8	468.4	479.4	481.0	487.4
57.5°	433.6	428.8	417.7	416.2	416.2	416.2	411.4	417.7	420.9	428.8	428.8
60°	379.8	379.8	370.3	370.3	371.8	370.3	370.3	371.8	371.8	378.2	381.3
62.5°	337.0	335.5	335.5	332.3	330.7	332.3	330.7	330.7	332.3	337.0	341.8
65°	299.1	297.5	295.9	294.3	291.1	291.1	292.7	295.9	295.9	299.1	300.6
67.5°	262.7	262.7	259.5	259.5	257.9	256.3	257.9	256.3	262.7	262.7	264.2
70°	226.3	224.7	219.9	218.4	213.6	215.2	215.2	219.9	221.5	224.7	227.9
72.5°	182.0	182.0	178.8	175.6	177.2	174.1	174.1	175.6	175.6	180.4	182.0
75°	150.3	147.2	145.6	147.2	145.6	148.7	145.6	145.6	148.7	148.7	148.7
77.5°	123.4	123.4	121.8	121.8	123.4	121.8	123.4	123.4	123.4	121.8	123.4
80°	101.3	99.7	99.7	99.7	98.1	98.1	98.1	98.1	98.1	98.1	98.1
82.5°	76.0	76.0	74.4	76.0	76.0	74.4	76.0	74.4	74.4	76.0	76.0
85°	50.6	53.8	50.6	50.6	52.2	52.2	53.8	52.2	53.8	50.6	52.2
87.5°	26.9	28.5	28.5	26.9	26.9	28.5	28.5	28.5	30.1	26.9	28.5
90°	28.9	29.1	29.6	30.1	30.5	31.0	30.5	30.1	29.6	29.1	28.9
92.5°	46.4	46.2	45.7	45.3	44.8	44.4	44.8	45.3	45.7	46.2	46.4
95°	80.5	80.5	80.5	80.5	80.5	80.5	80.5	80.5	80.5	80.5	80.5
97.5°	116.6	116.5	116.3	116.0	115.8	115.6	115.8	116.0	116.3	116.5	116.6
100°	154.8	155.0	155.5	156.0	156.4	156.9	156.4	156.0	155.5	155.0	154.8
102.5°	200.2	200.1	199.9	199.6	199.4	199.2	199.4	199.6	199.9	200.1	200.2
105°	243.6	243.8	244.3	244.7	245.2	245.6	245.2	244.7	244.3	243.8	243.6
107.5°	294.1	294.0	293.8	293.5	293.3	293.1	293.3	293.5	293.8	294.0	294.1
110°	343.7	343.5	343.0	342.5	342.1	341.6	342.1	342.5	343.0	343.5	343.7

TEST NUMBER: P1032089

CATALOG NUMBER: S123RDIW-B1165D1030UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	393.2	393.2	393.2	393.2	393.2	393.2	393.2	393.2	393.2	393.2	393.2
115°	440.7	440.6	440.3	440.1	439.8	439.6	439.8	440.1	440.3	440.6	440.7
117.5°	490.2	489.9	489.2	488.5	487.8	487.1	487.8	488.5	489.2	489.9	490.2
120°	539.8	539.6	539.1	538.6	538.2	537.7	538.2	538.6	539.1	539.6	539.8
122.5°	589.3	589.0	588.3	587.6	586.9	586.2	586.9	587.6	588.3	589.0	589.3
125°	638.8	638.3	637.4	636.5	635.6	634.7	635.6	636.5	637.4	638.3	638.8
127.5°	687.3	686.8	685.9	685.0	684.1	683.2	684.1	685.0	685.9	686.8	687.3
130°	737.9	737.1	735.5	733.9	732.3	730.7	732.3	733.9	735.5	737.1	737.9
132.5°	785.4	784.8	783.7	782.5	781.4	780.2	781.4	782.5	783.7	784.8	785.4
135°	833.9	833.7	833.2	832.7	832.3	831.8	832.3	832.7	833.2	833.7	833.9
137.5°	880.3	880.0	879.3	878.6	877.9	877.2	877.9	878.6	879.3	880.0	880.3
140°	928.8	928.0	926.4	924.8	923.2	921.6	923.2	924.8	926.4	928.0	928.8
142.5°	972.2	971.6	970.5	969.3	968.2	967.0	968.2	969.3	970.5	971.6	972.2
145°	1014.5	1014.0	1013.1	1012.2	1011.3	1010.4	1011.3	1012.2	1013.1	1014.0	1014.5
147.5°	1055.8	1055.1	1053.7	1052.4	1051.0	1049.6	1051.0	1052.4	1053.7	1055.1	1055.8
150°	1092.9	1092.2	1090.8	1089.5	1088.1	1086.7	1088.1	1089.5	1090.8	1092.2	1092.9
152.5°	1128.0	1127.4	1126.3	1125.1	1124.0	1122.8	1124.0	1125.1	1126.3	1127.4	1128.0
155°	1162.1	1161.3	1159.7	1158.0	1156.4	1154.8	1156.4	1158.0	1159.7	1161.3	1162.1
157.5°	1191.0	1190.3	1188.9	1187.6	1186.2	1184.8	1186.2	1187.6	1188.9	1190.3	1191.0
160°	1217.8	1217.3	1216.4	1215.5	1214.6	1213.7	1214.6	1215.5	1216.4	1217.3	1217.8
162.5°	1242.6	1241.8	1240.2	1238.5	1236.9	1235.3	1236.9	1238.5	1240.2	1241.8	1242.6
165°	1263.2	1262.4	1260.8	1259.2	1257.6	1256.0	1257.6	1259.2	1260.8	1262.4	1263.2
167.5°	1280.7	1280.0	1278.7	1277.3	1276.0	1274.6	1276.0	1277.3	1278.7	1280.0	1280.7
170°	1295.2	1294.4	1292.8	1291.2	1289.6	1288.0	1289.6	1291.2	1292.8	1294.4	1295.2
172.5°	1305.5	1304.7	1303.1	1301.5	1299.9	1298.3	1299.9	1301.5	1303.1	1304.7	1305.5
175°	1312.7	1311.9	1310.3	1308.7	1307.1	1305.5	1307.1	1308.7	1310.3	1311.9	1312.7
177.5°	1316.9	1316.1	1314.5	1312.8	1311.2	1309.6	1311.2	1312.8	1314.5	1316.1	1316.9
180°	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8

TEST NUMBER: P1032089

CATALOG NUMBER: S123RDIW-B1165D1030UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2
2.5°	1748.5	1754.8	1748.5	1735.8	1748.5	1756.4	1764.3	1776.9	1783.3	1783.3	1792.8
5°	1648.8	1661.4	1656.7	1653.5	1666.2	1674.1	1686.8	1702.6	1720.0	1731.1	1743.7
7.5°	1560.2	1568.1	1576.0	1576.0	1588.7	1606.1	1625.0	1644.0	1666.2	1682.0	1691.5
10°	1482.6	1489.0	1493.7	1500.0	1519.0	1538.0	1563.3	1587.1	1606.1	1623.5	1639.3
12.5°	1408.3	1417.8	1428.8	1433.6	1447.8	1471.6	1495.3	1523.8	1553.8	1571.2	1587.1
15°	1337.1	1341.8	1354.5	1368.7	1381.4	1406.7	1436.7	1466.8	1492.1	1519.0	1533.3
17.5°	1264.3	1265.9	1299.1	1291.2	1332.3	1356.0	1371.9	1400.4	1441.5	1463.6	1485.8
20°	1193.1	1208.9	1223.1	1231.0	1253.2	1280.1	1326.0	1348.1	1381.4	1401.9	1420.9
22.5°	1137.7	1161.4	1161.4	1180.4	1191.5	1216.8	1250.0	1292.8	1329.2	1343.4	1370.3
25°	1088.6	1099.7	1118.7	1125.0	1145.6	1167.8	1189.9	1235.8	1275.4	1294.3	1313.3
27.5°	1025.3	1039.6	1064.9	1064.9	1091.8	1115.5	1142.4	1172.5	1212.1	1239.0	1259.5
30°	976.3	990.5	1001.6	1019.0	1030.1	1052.2	1099.7	1121.9	1156.7	1180.4	1205.7
32.5°	930.4	941.5	951.0	970.0	982.6	1007.9	1033.3	1072.8	1102.9	1125.0	1151.9
35°	879.8	890.8	903.5	917.7	936.7	960.5	984.2	1017.4	1047.5	1068.1	1090.2
37.5°	832.3	840.2	859.2	868.7	884.5	906.7	936.7	971.5	998.4	1014.3	1036.4
40°	786.4	792.7	807.0	824.4	835.5	852.9	884.5	914.6	947.8	966.8	984.2
42.5°	737.4	745.3	757.9	775.3	792.7	811.7	829.1	863.9	894.0	909.8	928.8
45°	694.6	699.4	708.9	726.3	743.7	757.9	784.8	816.5	845.0	857.6	878.2
47.5°	644.0	648.8	663.0	670.9	689.9	708.9	735.8	767.4	792.7	805.4	824.4
50°	591.8	596.5	606.0	623.4	636.1	656.7	680.4	707.3	738.9	756.3	767.4
52.5°	541.2	550.6	558.6	572.8	588.6	609.2	631.3	656.7	683.6	701.0	713.6
55°	490.5	498.4	507.9	515.8	534.8	553.8	579.1	602.9	626.6	642.4	656.7
57.5°	433.6	444.6	454.1	469.9	484.2	500.0	528.5	547.5	576.0	587.0	599.7
60°	384.5	395.6	403.5	416.2	428.8	449.4	468.4	492.1	515.8	530.1	545.9
62.5°	343.4	348.1	352.9	365.5	378.2	397.2	416.2	439.9	465.2	473.1	485.8
65°	302.2	307.0	314.9	326.0	335.5	346.5	367.1	386.1	409.8	422.5	427.2
67.5°	267.4	272.2	273.7	281.7	289.6	302.2	313.3	332.3	354.4	362.4	371.8
70°	227.9	235.8	237.3	243.7	246.8	254.8	267.4	281.7	299.1	313.3	321.2
72.5°	182.0	193.0	196.2	205.7	210.4	218.4	227.9	238.9	250.0	256.3	262.7
75°	148.7	151.9	153.5	161.4	169.3	180.4	185.1	191.5	201.0	208.9	215.2
77.5°	123.4	125.0	126.6	126.6	128.2	134.5	144.0	151.9	158.2	161.4	166.1
80°	99.7	98.1	98.1	99.7	99.7	99.7	102.9	113.9	117.1	125.0	123.4
82.5°	77.5	74.4	76.0	74.4	74.4	74.4	74.4	76.0	76.0	80.7	83.9
85°	50.6	52.2	50.6	50.6	49.1	50.6	49.1	49.1	47.5	47.5	45.9
87.5°	26.9	28.5	26.9	26.9	25.3	26.9	25.3	25.3	23.7	23.7	20.6
90°	28.4	27.5	26.6	25.7	24.8	21.8	18.8	15.9	12.9	11.4	10.2
92.5°	46.1	45.4	44.7	44.0	43.3	41.9	40.6	39.2	37.9	37.2	36.5
95°	80.0	79.1	78.2	77.3	76.4	74.6	72.7	70.9	69.0	68.1	67.3
97.5°	116.0	114.9	113.8	112.6	111.5	110.1	108.7	107.4	106.0	105.3	104.7
100°	154.5	153.8	153.1	152.4	151.7	150.5	149.4	148.2	147.1	146.5	145.8
102.5°	199.9	199.2	198.5	197.8	197.1	195.5	193.9	192.3	190.7	189.9	189.6
105°	243.6	243.6	243.6	243.6	243.6	241.5	239.5	237.4	235.3	234.3	234.1
107.5°	293.8	293.1	292.4	291.7	291.0	290.1	289.2	288.3	287.4	286.9	286.8
110°	343.2	342.3	341.4	340.4	339.5	339.1	338.6	338.2	337.7	337.5	337.3

TEST NUMBER: P1032089

CATALOG NUMBER: S123RDIW-B1165D1030UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	392.6	391.5	390.3	389.2	388.0	388.0	388.0	388.0	388.0	388.0	387.9
115°	440.6	440.3	440.1	439.8	439.6	440.1	440.5	441.0	441.5	441.7	441.4
117.5°	490.2	490.2	490.2	490.2	490.2	490.7	491.1	491.6	492.1	492.3	492.2
120°	539.9	540.1	540.4	540.6	540.8	541.9	543.1	544.2	545.3	545.9	545.2
122.5°	589.6	590.3	591.0	591.7	592.4	592.8	593.3	593.7	594.2	594.4	593.9
125°	639.3	640.2	641.1	642.1	643.0	643.4	643.9	644.3	644.8	645.0	644.7
127.5°	688.0	689.4	690.7	692.1	693.5	694.0	694.4	694.9	695.4	695.6	694.9
130°	738.4	739.3	740.2	741.1	742.0	742.7	743.4	744.1	744.8	745.1	744.2
132.5°	786.0	787.1	788.2	789.4	790.5	791.0	791.4	791.9	792.4	792.6	791.7
135°	834.4	835.3	836.2	837.1	838.0	838.2	838.4	838.7	838.9	839.0	838.3
137.5°	880.9	882.0	883.2	884.3	885.5	884.8	884.1	883.4	882.7	882.4	881.8
140°	928.9	929.2	929.4	929.7	929.9	929.7	929.4	929.2	928.9	928.8	928.2
142.5°	972.3	972.5	972.8	973.0	973.2	972.7	972.3	971.8	971.3	971.1	970.5
145°	1014.6	1014.8	1015.1	1015.3	1015.5	1014.8	1014.1	1013.4	1012.7	1012.4	1012.2
147.5°	1055.8	1055.8	1055.8	1055.8	1055.8	1055.1	1054.4	1053.7	1053.0	1052.7	1052.2
150°	1092.9	1092.9	1092.9	1092.9	1092.9	1092.5	1092.0	1091.6	1091.1	1090.9	1090.7
152.5°	1127.8	1127.3	1126.8	1126.4	1125.9	1125.7	1125.5	1125.2	1125.0	1124.9	1124.6
155°	1161.6	1160.7	1159.8	1158.8	1157.9	1157.7	1157.5	1157.2	1157.0	1156.9	1156.9
157.5°	1190.5	1189.6	1188.7	1187.7	1186.8	1186.6	1186.4	1186.1	1185.9	1185.8	1185.9
160°	1217.2	1216.1	1214.9	1213.8	1212.6	1212.6	1212.6	1212.6	1212.6	1212.6	1212.8
162.5°	1242.0	1240.9	1239.7	1238.6	1237.4	1237.2	1237.0	1236.7	1236.5	1236.4	1236.7
165°	1262.5	1261.1	1259.8	1258.4	1257.0	1257.0	1257.0	1257.0	1257.0	1257.0	1257.3
167.5°	1280.0	1278.7	1277.3	1276.0	1274.6	1274.4	1274.1	1273.9	1273.6	1273.5	1274.0
170°	1294.4	1292.8	1291.2	1289.6	1288.0	1288.0	1288.0	1288.0	1288.0	1288.0	1288.5
172.5°	1304.8	1303.4	1302.1	1300.7	1299.3	1299.3	1299.3	1299.3	1299.3	1299.3	1299.8
175°	1312.0	1310.6	1309.3	1307.9	1306.5	1306.5	1306.5	1306.5	1306.5	1306.5	1307.0
177.5°	1316.2	1314.8	1313.5	1312.1	1310.7	1310.7	1310.7	1310.7	1310.7	1310.7	1311.2
180°	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8

TEST NUMBER: P1032089

CATALOG NUMBER: S123RDIW-B1165D1030UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1848.2	1848.2	1848.2	1848.2
2.5°	1800.7	1811.8	1833.9	1852.9
5°	1762.7	1780.1	1813.3	1846.6
7.5°	1716.8	1743.7	1786.4	1832.3
10°	1672.5	1707.3	1759.5	1813.3
12.5°	1628.2	1664.6	1720.0	1789.6
15°	1576.0	1614.0	1680.4	1764.3
17.5°	1530.1	1580.7	1640.9	1724.7
20°	1481.1	1519.0	1596.6	1685.2
22.5°	1419.3	1482.6	1555.4	1648.8
25°	1370.3	1425.7	1498.5	1604.5
27.5°	1310.2	1375.0	1463.6	1557.0
30°	1261.1	1314.9	1397.2	1509.5
32.5°	1204.1	1267.4	1352.9	1463.6
35°	1153.5	1207.3	1288.0	1400.4
37.5°	1093.4	1151.9	1242.1	1341.8
40°	1041.2	1098.1	1183.6	1276.9
42.5°	977.9	1038.0	1123.4	1202.6
45°	927.2	982.6	1050.7	1123.4
47.5°	865.5	924.1	990.5	1041.2
50°	810.1	863.9	916.2	958.9
52.5°	750.0	799.1	846.5	878.2
55°	694.6	732.6	770.6	792.7
57.5°	629.8	666.2	697.8	710.5
60°	572.8	602.9	623.4	637.7
62.5°	512.7	534.8	550.6	558.6
65°	454.1	469.9	477.9	485.8
67.5°	394.0	408.2	413.0	422.5
70°	330.7	346.5	349.7	354.4
72.5°	283.2	283.2	289.6	295.9
75°	226.3	229.4	232.6	232.6
77.5°	177.2	177.2	180.4	182.0
80°	129.8	131.3	131.3	129.8
82.5°	88.6	91.8	88.6	87.0
85°	49.1	55.4	52.2	52.2
87.5°	20.6	20.6	23.7	20.6
90°	7.9	5.6	3.3	1.0
92.5°	35.1	33.8	32.4	31.0
95°	65.7	64.1	62.5	60.9
97.5°	103.6	102.4	101.3	100.1
100°	144.5	143.1	141.8	140.4
102.5°	188.9	188.2	187.5	186.8
105°	233.6	233.1	232.7	232.2
107.5°	286.6	286.3	286.1	285.9
110°	336.8	336.3	335.9	335.4

TEST NUMBER: P1032089

CATALOG NUMBER: S123RDIW-B1165D1030UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	387.7	387.4	387.2	387.0
115°	440.7	440.0	439.3	438.6
117.5°	491.9	491.7	491.4	491.2
120°	543.9	542.5	541.2	539.8
122.5°	593.0	592.1	591.2	590.3
125°	644.0	643.3	642.6	641.9
127.5°	693.5	692.2	690.8	689.4
130°	742.4	740.5	738.7	736.9
132.5°	789.8	788.0	786.1	784.3
135°	836.9	835.6	834.2	832.8
137.5°	880.7	879.5	878.4	877.2
140°	927.1	926.0	924.8	923.7
142.5°	969.4	968.3	967.1	966.0
145°	1011.7	1011.3	1010.8	1010.4
147.5°	1051.3	1050.4	1049.4	1048.5
150°	1090.2	1089.7	1089.3	1088.8
152.5°	1123.9	1123.2	1122.5	1121.8
155°	1156.9	1156.9	1156.9	1156.9
157.5°	1186.1	1186.4	1186.6	1186.8
160°	1213.3	1213.8	1214.2	1214.7
162.5°	1237.4	1238.1	1238.8	1239.5
165°	1258.0	1258.7	1259.4	1260.1
167.5°	1274.9	1275.8	1276.8	1277.7
170°	1289.4	1290.3	1291.2	1292.1
172.5°	1300.7	1301.6	1302.6	1303.5
175°	1307.9	1308.8	1309.8	1310.7
177.5°	1312.1	1313.0	1313.9	1314.8
180°	1313.8	1313.8	1313.8	1313.8

(END OF REPORT)