

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031592

Luminaire Tested: S123DIW-B340D1320UB35-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031592
REPORT IS A COMBINATION OF REPORTS P991285 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B340D1320UB35-4F0-XX-W2A-A1
Description: Define 3 Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6019.0 lumens
Efficiency: N/A
Efficacy: 109.2 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 55.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031592

CATALOG NUMBER: S123DIW-B340D1320UB35-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1031592

CATALOG NUMBER: S123DIW-B340D1320UB35-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32
1	92	88	84	81	82	78	75	72	60	58	56	44	42	41	28	28	27
2	84	77	71	66	74	68	64	60	53	50	47	38	36	35	25	24	23
3	76	68	61	55	68	60	54	50	47	43	39	34	31	29	22	21	20
4	70	60	52	47	62	53	47	42	41	37	34	30	27	25	20	18	17
5	64	53	45	40	57	47	41	36	37	32	29	27	24	22	18	16	15
6	59	47	40	34	52	43	36	31	33	28	25	24	21	19	16	14	13
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12
8	50	39	31	26	45	35	28	24	27	23	19	20	17	15	14	12	10
9	47	35	28	23	41	32	25	21	25	20	17	18	15	13	13	11	9
10	43	32	25	21	39	29	23	19	23	18	15	17	14	12	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5061	5061	5061	5061
5°	5064	5831	5079	4352
10°	5032	7056	5037	3800
15°	4962	8368	5002	3421
20°	4903	9634	4913	3148
25°	4813	9878	4824	3005
30°	4750	8161	4750	2912
35°	4671	5458	4641	2829
40°	4577	3940	4521	2703
45°	4458	3121	4331	2547
50°	4171	2650	4023	2392
55°	3856	2329	3698	2220
60°	3535	2028	3347	2040
65°	3184	1736	3029	1799
70°	2818	1441	2630	1516
75°	2408	1086	2252	1171
80°	1906	726	1754	768
85°	1316	332	1047	304

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 8162 cd/sqm

TEST NUMBER: P1031592

CATALOG NUMBER: S123DIW-B340D1320UB35-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.2	0.8
10°-20°	148.5	2.5
20°-30°	249.9	4.2
30°-40°	282.4	4.7
40°-50°	252.9	4.2
50°-60°	204.2	3.4
60°-70°	142.3	2.4
70°-80°	74.7	1.2
80°-90°	21.4	0.4
90°-100°	106.8	1.8
100°-110°	323.2	5.4
110°-120°	550.2	9.1
120°-130°	723.9	12.0
130°-140°	813.7	13.5
140°-150°	799.9	13.3
150°-160°	673.4	11.2
160°-170°	448.3	7.4
170°-180°	157.0	2.6
0°-30°	444.6	7.4
0°-40°	727.0	12.1
0°-60°	1184.1	19.7
0°-90°	1422.5	23.6
90°-120°	980.2	16.3
90°-150°	3317.7	55.1
90°-180°	4596.0	76.4
0°-180°	6019.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	470	470	470	470	470	
5°	470	558	471	417	470	45
15°	448	831	452	340	448	127
25°	410	987	411	300	410	189
35°	362	532	359	276	362	226
45°	300	287	292	234	300	230
55°	213	195	204	186	213	191
65°	132	127	125	131	132	131
75°	63	65	59	70	63	68
85°	14	15	11	14	14	16
90°	1	39	1	39	1	7
95°	77	102	77	102	77	85
105°	293	310	293	310	293	314
115°	554	555	554	555	554	548
125°	811	801	811	801	811	723
135°	1052	1050	1052	1050	1052	810
145°	1276	1276	1276	1276	1276	797
155°	1461	1458	1461	1458	1461	672
165°	1591	1586	1591	1586	1591	449
175°	1655	1648	1655	1648	1655	157
180°	1659	1659	1659	1659	1659	

TEST NUMBER: P1031592

CATALOG NUMBER: S123DIW-B340D1320UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	471.5	475.2	477.0	479.7	482.5	486.6	487.9	490.2	489.3	491.1	492.0
5°	469.7	476.1	481.5	488.4	494.8	499.3	503.9	511.2	516.6	517.5	521.6
7.5°	466.5	475.6	485.2	494.8	507.1	514.3	522.5	532.6	540.8	554.0	559.0
10°	462.4	475.2	488.8	502.0	518.9	530.3	540.3	557.2	574.0	587.7	600.4
12.5°	456.0	472.0	489.7	509.3	531.2	544.4	558.1	580.4	605.9	626.9	640.5
15°	448.3	468.3	491.1	512.1	536.2	560.8	575.4	600.4	636.9	656.5	691.6
17.5°	441.9	462.4	485.2	518.0	550.8	575.4	585.9	631.9	656.9	689.7	729.4
20°	431.9	457.9	487.0	519.8	562.2	577.2	598.6	645.1	676.1	718.9	767.6
22.5°	421.4	449.2	484.3	518.4	565.8	581.8	610.9	647.8	697.0	739.4	793.2
25°	410.0	440.1	475.6	516.2	562.6	585.9	613.2	658.8	712.1	765.4	815.0
27.5°	398.6	431.4	468.3	508.9	554.0	581.3	608.6	656.0	724.4	782.2	845.5
30°	387.7	420.5	457.4	498.9	546.2	572.7	598.6	657.9	733.9	799.1	862.9
32.5°	375.8	409.6	448.3	482.9	530.7	559.0	588.1	657.9	739.9	809.1	867.4
35°	361.7	396.4	429.6	464.2	511.6	543.0	575.8	653.3	745.3	812.3	848.3
37.5°	348.1	378.6	407.3	441.0	490.7	524.4	562.2	647.8	742.6	798.6	808.6
40°	332.6	363.1	386.3	417.8	470.2	509.3	547.6	640.5	730.7	766.3	737.1
42.5°	317.5	341.7	361.7	392.3	449.2	487.5	528.9	627.3	707.5	714.8	649.2
45°	300.2	317.5	335.3	369.9	426.4	465.6	511.6	608.2	670.2	649.2	566.3
47.5°	277.9	293.4	313.0	344.9	402.3	442.8	486.6	583.6	615.9	572.2	481.5
50°	256.5	269.7	287.9	318.9	376.8	416.4	462.9	544.9	560.8	492.0	415.0
52.5°	235.1	245.1	262.9	293.8	351.7	390.0	432.3	505.2	496.1	422.3	354.0
55°	212.8	221.4	238.3	268.8	322.5	359.0	399.5	456.5	432.8	362.6	308.0
57.5°	190.9	200.0	217.3	242.8	293.4	328.9	361.3	405.9	370.4	314.3	266.1
60°	171.3	179.0	192.3	217.3	263.3	292.0	321.6	352.2	322.5	268.3	231.4
62.5°	150.8	158.1	170.4	193.2	232.8	258.3	282.0	307.1	274.3	234.6	201.8
65°	131.7	137.6	149.0	169.9	202.3	223.2	242.4	259.7	233.3	196.8	172.2
67.5°	114.3	119.4	128.9	147.6	174.9	190.0	205.5	220.0	197.7	168.6	147.6
70°	95.7	99.8	108.4	122.1	144.0	159.5	170.8	181.8	161.7	138.5	124.4
72.5°	79.3	83.4	88.8	103.0	118.0	127.6	139.9	145.8	134.4	115.3	101.1
75°	63.3	66.5	71.5	80.6	94.8	101.1	108.9	113.4	103.0	90.2	81.5
77.5°	49.7	51.0	54.7	61.0	70.6	77.9	83.8	86.6	79.3	71.1	63.8
80°	35.1	36.9	39.6	45.1	52.4	54.7	58.3	61.5	56.9	49.7	45.1
82.5°	23.2	25.5	26.9	29.2	33.7	36.4	37.4	40.1	36.0	33.3	31.4
85°	13.7	14.6	15.0	16.4	18.7	20.0	21.4	21.9	21.0	20.5	18.7
87.5°	6.8	6.8	6.8	7.7	8.2	9.1	9.6	9.6	9.6	9.1	8.7
90°	1.3	4.2	7.1	10.0	12.9	14.3	16.2	20.0	23.7	27.5	31.3
92.5°	39.1	40.8	42.6	44.3	46.0	46.9	47.8	49.5	51.2	53.0	54.7
95°	76.9	78.9	80.9	83.0	85.0	86.0	87.2	89.5	91.8	94.1	96.4
97.5°	126.4	127.8	129.3	130.7	132.2	132.9	133.8	135.5	137.2	139.0	140.7
100°	177.2	178.9	180.7	182.4	184.1	185.0	185.7	187.2	188.7	190.1	191.6
102.5°	235.9	236.8	237.6	238.5	239.4	239.8	240.8	242.8	244.9	246.9	248.9
105°	293.2	293.8	294.4	294.9	295.5	295.8	297.1	299.7	302.3	304.9	307.5
107.5°	361.0	361.3	361.6	361.9	362.2	362.3	362.9	364.0	365.2	366.3	367.5
110°	423.5	424.1	424.7	425.2	425.8	426.1	426.4	427.0	427.5	428.1	428.7

TEST NUMBER: P1031592

CATALOG NUMBER: S123DIW-B340D1320UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	488.7	489.0	489.3	489.6	489.9	490.0	490.0	490.0	490.0	490.0	490.0
115°	553.8	554.7	555.5	556.4	557.3	557.7	557.4	556.8	556.3	555.7	555.1
117.5°	620.3	620.6	620.9	621.2	621.5	621.6	621.3	620.7	620.2	619.6	619.0
120°	681.5	683.3	685.0	686.8	688.5	689.4	688.7	687.2	685.7	684.3	682.8
122.5°	745.4	746.6	747.7	748.9	750.0	750.6	750.3	749.7	749.2	748.6	748.0
125°	810.6	811.5	812.3	813.2	814.1	814.5	814.2	813.6	813.1	812.5	811.9
127.5°	870.5	872.2	874.0	875.7	877.4	878.3	878.0	877.4	876.9	876.3	875.7
130°	930.4	932.7	935.1	937.4	939.7	940.9	940.5	939.6	938.7	937.9	937.0
132.5°	990.4	992.7	995.0	997.3	999.6	1000.8	1000.5	999.9	999.4	998.8	998.2
135°	1051.6	1053.4	1055.1	1056.9	1058.6	1059.5	1059.3	1059.0	1058.7	1058.4	1058.1
137.5°	1107.7	1109.1	1110.6	1112.0	1113.5	1114.2	1114.6	1115.5	1116.4	1117.2	1118.1
140°	1166.3	1167.7	1169.2	1170.6	1172.1	1172.8	1172.9	1173.2	1173.5	1173.8	1174.1
142.5°	1219.7	1221.2	1222.6	1224.1	1225.6	1226.3	1226.6	1227.2	1227.7	1228.3	1228.9
145°	1275.8	1276.4	1277.0	1277.5	1278.1	1278.4	1278.8	1279.7	1280.6	1281.4	1282.3
147.5°	1324.0	1325.2	1326.3	1327.5	1328.6	1329.2	1329.6	1330.5	1331.4	1332.2	1333.1
150°	1374.8	1375.4	1376.0	1376.5	1377.1	1377.4	1377.7	1378.3	1378.8	1379.4	1380.0
152.5°	1416.5	1417.4	1418.2	1419.1	1420.0	1420.4	1420.5	1420.8	1421.1	1421.4	1421.7
155°	1460.8	1460.8	1460.8	1460.8	1460.8	1460.8	1460.9	1461.2	1461.5	1461.8	1462.1
157.5°	1498.6	1498.3	1498.0	1497.7	1497.4	1497.3	1497.4	1497.7	1498.0	1498.3	1498.6
160°	1533.8	1533.2	1532.6	1532.1	1531.5	1531.2	1531.2	1531.2	1531.2	1531.2	1531.2
162.5°	1565.1	1564.2	1563.4	1562.5	1561.6	1561.2	1561.3	1561.6	1561.9	1562.2	1562.5
165°	1591.1	1590.2	1589.4	1588.5	1587.6	1587.2	1587.2	1587.2	1587.2	1587.2	1587.2
167.5°	1613.3	1612.1	1611.0	1609.8	1608.7	1608.1	1608.2	1608.5	1608.8	1609.1	1609.4
170°	1631.5	1630.3	1629.2	1628.0	1626.9	1626.3	1626.3	1626.3	1626.3	1626.3	1626.3
172.5°	1645.9	1644.7	1643.5	1642.4	1641.2	1640.6	1640.6	1640.6	1640.6	1640.6	1640.6
175°	1655.0	1653.8	1652.7	1651.5	1650.4	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8
177.5°	1660.2	1659.0	1657.9	1656.7	1655.6	1655.0	1655.0	1655.0	1655.0	1655.0	1655.0
180°	1658.9	1658.9	1658.9	1658.9	1658.9	1658.9	1658.9	1658.9	1658.9	1658.9	1658.9

TEST NUMBER: P1031592

CATALOG NUMBER: S123DIW-B340D1320UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	495.2	496.1	499.3	501.6	506.1	505.7	505.7	505.2	503.9	506.1	507.5
5°	529.8	537.6	538.5	548.5	549.0	553.1	555.8	553.5	559.0	558.5	554.4
7.5°	572.7	583.1	588.1	597.7	608.6	605.9	616.4	618.2	617.3	621.9	625.0
10°	619.6	637.8	650.6	668.3	672.9	675.6	682.5	688.4	700.2	691.1	697.0
12.5°	673.3	686.6	703.4	731.7	745.8	754.9	758.1	762.2	770.4	765.4	765.8
15°	718.4	736.2	764.9	800.0	804.1	815.5	812.7	837.3	849.2	831.4	841.4
17.5°	765.4	789.1	823.2	853.7	871.1	878.8	886.1	909.8	908.9	906.1	908.4
20°	795.4	834.2	876.5	917.1	922.1	928.0	947.6	957.6	955.8	963.5	968.6
22.5°	837.8	878.8	923.9	950.8	962.2	969.0	984.5	990.9	993.6	995.4	992.2
25°	873.3	917.1	950.3	974.0	980.9	984.5	989.5	991.3	990.0	986.8	989.5
27.5°	897.5	932.6	955.3	966.3	962.6	956.7	947.1	940.8	926.6	919.8	928.0
30°	907.5	923.0	929.8	911.6	893.4	878.8	860.6	826.9	800.4	808.2	797.7
32.5°	891.6	881.5	848.7	801.8	787.7	764.0	712.5	672.9	674.3	653.3	662.0
35°	844.6	799.1	737.1	666.1	647.4	634.6	578.1	569.5	551.2	531.7	537.1
37.5°	761.7	695.2	620.0	567.6	539.9	512.1	480.2	461.0	450.1	441.9	448.3
40°	660.6	579.5	517.5	470.6	446.9	429.2	407.3	388.2	375.8	374.5	376.8
42.5°	561.3	492.9	436.0	391.3	383.6	362.6	348.5	333.5	329.8	323.9	327.1
45°	475.2	419.6	372.7	336.2	327.1	321.6	304.3	294.8	290.7	287.0	292.5
47.5°	412.8	354.4	320.3	298.4	289.3	280.2	270.6	264.2	261.0	261.5	261.0
50°	352.6	309.8	279.7	262.9	257.4	251.0	243.3	239.2	237.8	233.7	236.9
52.5°	303.4	272.4	251.5	235.5	231.4	226.9	220.5	218.2	215.0	214.1	214.1
55°	263.8	239.6	222.8	212.3	207.3	203.6	200.0	197.3	195.0	195.0	195.0
57.5°	232.8	211.8	199.5	190.4	188.6	185.0	180.9	180.9	177.7	177.2	178.6
60°	206.4	187.7	178.1	170.4	167.7	166.7	162.6	162.6	161.7	159.5	161.3
62.5°	179.5	165.8	157.6	151.7	149.0	149.0	145.8	143.5	143.5	144.0	143.1
65°	154.9	144.9	137.6	133.0	131.7	129.8	129.4	127.6	126.2	126.6	126.2
67.5°	133.0	125.3	120.3	116.6	114.3	113.4	112.1	112.1	111.2	111.6	109.3
70°	113.4	105.7	101.6	97.9	97.0	97.0	95.2	95.7	94.8	96.1	95.2
72.5°	93.4	87.5	84.3	82.9	82.0	81.5	80.6	79.7	79.3	80.2	79.7
75°	75.6	70.6	68.3	67.4	66.5	66.5	66.1	65.6	65.1	65.1	65.1
77.5°	58.8	55.6	52.8	53.8	52.4	52.8	51.5	51.5	51.9	51.5	51.5
80°	43.3	41.0	41.0	40.1	38.3	39.2	39.2	37.8	37.4	38.3	36.9
82.5°	28.7	28.2	27.3	26.9	26.0	26.4	26.0	25.5	25.1	26.0	25.1
85°	16.9	16.9	16.4	15.5	16.4	15.9	15.5	15.5	15.0	15.0	15.0
87.5°	8.7	7.7	7.7	7.3	7.7	6.8	7.3	6.8	6.4	6.8	6.4
90°	32.5	33.6	34.8	35.9	36.5	36.8	37.4	37.9	38.5	39.1	38.5
92.5°	55.6	56.4	57.3	58.2	58.6	58.3	57.7	57.2	56.6	56.0	56.6
95°	97.6	98.7	99.9	101.0	101.6	101.6	101.6	101.6	101.6	101.6	101.6
97.5°	142.2	143.6	145.1	146.6	147.3	147.2	146.9	146.6	146.3	146.0	146.3
100°	192.5	193.3	194.2	195.1	195.5	195.8	196.4	196.9	197.5	198.1	197.5
102.5°	249.8	250.6	251.5	252.4	252.8	252.7	252.4	252.1	251.8	251.5	251.8
105°	307.5	307.5	307.5	307.5	307.5	307.8	308.4	308.9	309.5	310.1	309.5
107.5°	368.4	369.2	370.1	371.0	371.4	371.3	371.0	370.7	370.4	370.1	370.4
110°	429.9	431.0	432.2	433.3	433.9	433.6	433.0	432.5	431.9	431.3	431.9

TEST NUMBER: P1031592

CATALOG NUMBER: S123DIW-B340D1320UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	491.4	492.9	494.3	495.8	496.5	496.5	496.5	496.5	496.5	496.5	496.5
115°	555.4	555.7	556.0	556.3	556.4	556.3	556.0	555.7	555.4	555.1	555.4
117.5°	619.0	619.0	619.0	619.0	619.0	618.6	617.7	616.8	616.0	615.1	616.0
120°	682.5	682.2	681.9	681.6	681.5	681.2	680.6	680.1	679.5	678.9	679.5
122.5°	747.1	746.3	745.4	744.5	744.1	743.7	742.8	741.9	741.1	740.2	741.1
125°	810.7	809.5	808.4	807.2	806.6	806.0	804.9	803.7	802.6	801.4	802.6
127.5°	874.0	872.2	870.5	868.8	867.9	867.3	866.2	865.0	863.9	862.7	863.9
130°	935.8	934.6	933.5	932.3	931.7	930.7	928.7	926.6	924.6	922.6	924.6
132.5°	996.8	995.3	993.9	992.4	991.7	991.0	989.5	988.1	986.6	985.2	986.6
135°	1056.9	1055.8	1054.6	1053.5	1052.9	1052.6	1052.0	1051.5	1050.9	1050.3	1050.9
137.5°	1116.7	1115.2	1113.8	1112.3	1111.6	1111.2	1110.3	1109.4	1108.6	1107.7	1108.6
140°	1173.8	1173.5	1173.2	1172.9	1172.8	1171.8	1169.8	1167.7	1165.7	1163.7	1165.7
142.5°	1228.6	1228.3	1228.0	1227.7	1227.6	1226.9	1225.4	1223.9	1222.5	1221.0	1222.5
145°	1282.0	1281.7	1281.4	1281.1	1281.0	1280.4	1279.3	1278.1	1277.0	1275.8	1277.0
147.5°	1333.1	1333.1	1333.1	1333.1	1333.1	1332.2	1330.5	1328.8	1327.0	1325.3	1327.0
150°	1380.0	1380.0	1380.0	1380.0	1380.0	1379.1	1377.4	1375.7	1373.9	1372.2	1373.9
152.5°	1422.3	1422.9	1423.4	1424.0	1424.3	1423.6	1422.1	1420.7	1419.2	1417.8	1419.2
155°	1463.3	1464.4	1465.6	1466.7	1467.3	1466.3	1464.3	1462.2	1460.2	1458.2	1460.2
157.5°	1499.8	1500.9	1502.1	1503.2	1503.8	1502.9	1501.2	1499.5	1497.7	1496.0	1497.7
160°	1532.6	1534.1	1535.5	1537.0	1537.7	1537.1	1536.0	1534.8	1533.7	1532.5	1533.7
162.5°	1563.9	1565.4	1566.8	1568.3	1569.0	1568.0	1566.0	1563.9	1561.9	1559.9	1561.9
165°	1588.9	1590.7	1592.4	1594.1	1595.0	1594.0	1592.0	1589.9	1587.9	1585.9	1587.9
167.5°	1611.1	1612.9	1614.6	1616.3	1617.2	1616.3	1614.6	1612.9	1611.1	1609.4	1611.1
170°	1628.3	1630.3	1632.4	1634.4	1635.4	1634.4	1632.4	1630.3	1628.3	1626.3	1628.3
172.5°	1642.4	1644.1	1645.9	1647.6	1648.5	1647.5	1645.4	1643.4	1641.3	1639.3	1641.3
175°	1651.5	1653.3	1655.0	1656.7	1657.6	1656.6	1654.6	1652.5	1650.5	1648.5	1650.5
177.5°	1656.7	1658.5	1660.2	1661.9	1662.8	1661.8	1659.8	1657.7	1655.7	1653.7	1655.7
180°	1658.9	1658.9	1658.9	1658.9	1658.9	1658.9	1658.9	1658.9	1658.9	1658.9	1658.9

TEST NUMBER: P1031592

CATALOG NUMBER: S123DIW-B340D1320UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	503.9	505.2	501.6	500.7	500.7	502.5	501.1	488.8	491.1	488.4	487.5
5°	559.4	556.7	553.1	551.2	549.0	542.6	542.1	528.0	525.3	516.2	512.1
7.5°	620.5	618.2	607.3	605.9	605.0	599.1	584.0	569.0	558.1	547.6	537.6
10°	690.2	683.4	678.4	668.3	663.3	655.1	635.5	621.4	602.7	586.8	565.8
12.5°	774.0	766.3	749.4	742.1	735.8	713.0	693.4	677.4	641.0	630.1	604.1
15°	835.5	819.1	817.3	801.4	800.4	775.4	738.0	720.7	692.5	652.4	625.5
17.5°	902.0	887.5	876.1	856.9	854.2	830.5	803.2	760.8	729.8	691.6	657.4
20°	950.8	943.0	923.5	915.7	899.8	879.7	851.5	799.1	761.3	723.0	681.1
22.5°	989.5	981.8	966.3	955.8	946.7	920.7	887.0	842.4	790.4	740.3	697.0
25°	989.1	986.8	980.4	975.4	968.6	949.4	921.2	878.3	820.5	765.4	705.2
27.5°	933.0	939.4	950.3	955.8	954.4	951.7	935.8	899.8	847.8	782.2	714.8
30°	816.4	839.6	860.1	887.5	895.7	915.7	924.8	904.3	862.9	801.8	727.1
32.5°	677.0	710.7	755.3	770.4	796.3	835.1	878.3	886.1	860.1	813.2	734.8
35°	555.3	583.1	617.8	641.5	664.7	727.6	782.2	829.6	838.3	807.3	733.0
37.5°	459.7	479.3	509.8	529.8	551.2	605.0	681.5	743.0	786.3	787.2	728.0
40°	390.4	399.1	425.5	440.1	460.6	507.1	575.4	655.6	718.9	748.1	714.8
42.5°	330.7	342.1	364.0	374.9	388.2	428.7	473.8	549.9	628.2	690.7	690.2
45°	295.2	303.4	313.4	322.5	337.6	361.7	413.2	470.2	545.3	615.9	643.7
47.5°	263.8	271.5	281.5	284.3	294.3	317.1	348.5	398.2	468.3	538.5	590.9
50°	237.4	243.7	250.6	255.6	260.1	278.8	302.5	344.4	400.5	468.3	533.5
52.5°	216.9	221.4	227.3	230.1	234.2	247.8	266.1	297.0	343.0	405.0	468.3
55°	197.7	200.9	204.6	209.1	210.9	221.0	235.1	261.5	295.7	351.2	411.4
57.5°	180.0	181.3	183.6	186.3	188.6	197.3	209.6	227.3	257.4	300.2	357.2
60°	159.9	163.6	164.9	167.7	169.0	175.9	185.4	200.5	223.7	260.6	303.4
62.5°	143.1	145.3	147.6	149.0	152.2	154.4	162.2	175.9	195.0	222.3	261.0
65°	128.0	128.9	130.3	131.7	132.6	135.3	142.6	151.7	166.3	190.4	220.5
67.5°	110.7	111.6	113.4	113.9	114.8	118.4	122.5	130.3	142.6	160.8	185.4
70°	93.8	95.2	96.1	97.0	98.4	99.8	104.3	110.7	120.3	133.0	152.2
72.5°	79.3	80.6	80.6	81.5	81.1	82.9	87.5	92.0	98.4	108.9	125.7
75°	64.7	64.7	65.6	66.1	66.5	68.3	70.2	73.8	78.8	87.0	97.5
77.5°	51.0	50.6	51.5	51.5	51.5	52.8	54.7	56.5	59.7	65.6	73.8
80°	37.4	37.4	38.3	38.7	37.8	38.3	39.2	41.0	43.3	47.4	51.9
82.5°	24.6	26.4	26.0	26.4	26.0	26.9	27.3	27.8	28.7	30.5	33.7
85°	15.0	15.0	15.0	15.5	15.0	15.5	15.5	15.5	15.9	16.9	18.2
87.5°	6.4	6.4	6.4	6.8	6.4	6.4	6.8	6.4	6.8	6.8	7.3
90°	37.9	37.4	36.8	36.5	35.9	34.8	33.6	32.5	31.3	27.5	23.7
92.5°	57.2	57.7	58.3	58.6	58.2	57.3	56.4	55.6	54.7	53.0	51.2
95°	101.6	101.6	101.6	101.6	101.0	99.9	98.7	97.6	96.4	94.1	91.8
97.5°	146.6	146.9	147.2	147.3	146.6	145.1	143.6	142.2	140.7	139.0	137.2
100°	196.9	196.4	195.8	195.5	195.1	194.2	193.3	192.5	191.6	190.1	188.7
102.5°	252.1	252.4	252.7	252.8	252.4	251.5	250.6	249.8	248.9	246.9	244.9
105°	308.9	308.4	307.8	307.5	307.5	307.5	307.5	307.5	307.5	304.9	302.3
107.5°	370.7	371.0	371.3	371.4	371.0	370.1	369.2	368.4	367.5	366.3	365.2
110°	432.5	433.0	433.6	433.9	433.3	432.2	431.0	429.9	428.7	428.1	427.5

TEST NUMBER: P1031592

CATALOG NUMBER: S123DIW-B340D1320UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	496.5	496.5	496.5	496.5	495.8	494.3	492.9	491.4	490.0	490.0	490.0
115°	555.7	556.0	556.3	556.4	556.3	556.0	555.7	555.4	555.1	555.7	556.3
117.5°	616.8	617.7	618.6	619.0	619.0	619.0	619.0	619.0	619.0	619.6	620.2
120°	680.1	680.6	681.2	681.5	681.6	681.9	682.2	682.5	682.8	684.3	685.7
122.5°	741.9	742.8	743.7	744.1	744.5	745.4	746.3	747.1	748.0	748.6	749.2
125°	803.7	804.9	806.0	806.6	807.2	808.4	809.5	810.7	811.9	812.5	813.1
127.5°	865.0	866.2	867.3	867.9	868.8	870.5	872.2	874.0	875.7	876.3	876.9
130°	926.6	928.7	930.7	931.7	932.3	933.5	934.6	935.8	937.0	937.9	938.7
132.5°	988.1	989.5	991.0	991.7	992.4	993.9	995.3	996.8	998.2	998.8	999.4
135°	1051.5	1052.0	1052.6	1052.9	1053.5	1054.6	1055.8	1056.9	1058.1	1058.4	1058.7
137.5°	1109.4	1110.3	1111.2	1111.6	1112.3	1113.8	1115.2	1116.7	1118.1	1117.2	1116.4
140°	1167.7	1169.8	1171.8	1172.8	1172.9	1173.2	1173.5	1173.8	1174.1	1173.8	1173.5
142.5°	1223.9	1225.4	1226.9	1227.6	1227.7	1228.0	1228.3	1228.6	1228.9	1228.3	1227.7
145°	1278.1	1279.3	1280.4	1281.0	1281.1	1281.4	1281.7	1282.0	1282.3	1281.4	1280.6
147.5°	1328.8	1330.5	1332.2	1333.1	1333.1	1333.1	1333.1	1333.1	1333.1	1332.2	1331.4
150°	1375.7	1377.4	1379.1	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0	1379.4	1378.8
152.5°	1420.7	1422.1	1423.6	1424.3	1424.0	1423.4	1422.9	1422.3	1421.7	1421.4	1421.1
155°	1462.2	1464.3	1466.3	1467.3	1466.7	1465.6	1464.4	1463.3	1462.1	1461.8	1461.5
157.5°	1499.5	1501.2	1502.9	1503.8	1503.2	1502.1	1500.9	1499.8	1498.6	1498.3	1498.0
160°	1534.8	1536.0	1537.1	1537.7	1537.0	1535.5	1534.1	1532.6	1531.2	1531.2	1531.2
162.5°	1563.9	1566.0	1568.0	1569.0	1568.3	1566.8	1565.4	1563.9	1562.5	1562.2	1561.9
165°	1589.9	1592.0	1594.0	1595.0	1594.1	1592.4	1590.7	1588.9	1587.2	1587.2	1587.2
167.5°	1612.9	1614.6	1616.3	1617.2	1616.3	1614.6	1612.9	1611.1	1609.4	1609.1	1608.8
170°	1630.3	1632.4	1634.4	1635.4	1634.4	1632.4	1630.3	1628.3	1626.3	1626.3	1626.3
172.5°	1643.4	1645.4	1647.5	1648.5	1647.6	1645.9	1644.1	1642.4	1640.6	1640.6	1640.6
175°	1652.5	1654.6	1656.6	1657.6	1656.7	1655.0	1653.3	1651.5	1649.8	1649.8	1649.8
177.5°	1657.7	1659.8	1661.8	1662.8	1661.9	1660.2	1658.5	1656.7	1655.0	1655.0	1655.0
180°	1658.9	1658.9	1658.9	1658.9	1658.9	1658.9	1658.9	1658.9	1658.9	1658.9	1658.9

TEST NUMBER: P1031592

CATALOG NUMBER: S123DIW-B340D1320UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	482.9	481.5	481.5	480.6	477.9	472.9	472.4	473.3	470.6	467.9	463.8
5°	506.6	497.9	495.2	492.5	487.0	477.9	474.3	471.1	466.1	460.1	453.8
7.5°	526.6	514.3	510.7	505.7	494.8	482.0	473.8	467.0	460.1	451.9	444.2
10°	551.7	533.9	525.3	518.0	503.0	485.2	472.9	462.9	451.9	441.9	431.9
12.5°	579.9	551.2	548.5	530.7	513.4	487.0	472.0	457.4	442.8	430.5	420.0
15°	603.6	572.2	560.8	549.0	515.7	482.9	468.3	451.9	435.1	421.9	406.4
17.5°	618.7	592.7	568.6	552.6	518.0	488.8	460.6	441.9	424.1	405.9	393.2
20°	636.9	599.1	578.1	556.7	522.5	484.3	456.0	432.8	410.9	394.5	379.0
22.5°	655.1	604.1	586.8	563.5	523.5	479.7	447.8	424.6	399.5	383.1	366.3
25°	653.3	611.4	582.7	563.1	514.3	475.6	438.3	410.9	387.7	366.7	349.9
27.5°	654.7	603.2	574.0	551.2	508.0	469.7	428.2	399.5	375.4	353.5	335.8
30°	655.1	590.9	565.4	538.0	496.1	455.6	416.9	387.7	362.2	338.5	322.5
32.5°	653.8	580.9	549.0	524.4	477.4	441.9	403.6	372.7	346.7	324.8	309.8
35°	650.6	569.0	532.1	501.1	458.3	422.3	391.3	359.4	331.7	311.6	294.3
37.5°	641.9	556.3	514.3	483.8	436.0	399.5	372.2	345.8	318.9	295.2	280.6
40°	635.5	538.9	496.6	463.3	411.8	376.3	353.5	328.5	302.0	280.6	266.5
42.5°	620.9	522.5	478.4	438.7	388.2	351.7	330.3	310.2	287.5	266.5	253.8
45°	597.3	504.8	456.0	415.9	362.2	327.6	308.0	291.6	271.5	251.5	238.7
47.5°	564.0	479.3	432.3	392.3	336.7	301.6	282.0	269.7	253.8	236.9	226.0
50°	528.0	451.5	408.2	368.6	312.1	277.9	258.8	247.4	236.9	221.4	210.9
52.5°	481.1	421.9	380.4	342.6	285.6	252.8	236.0	227.8	216.9	205.9	196.8
55°	435.5	383.6	349.4	313.4	259.7	229.2	212.8	204.1	197.7	188.6	181.3
57.5°	382.7	348.1	316.6	283.8	235.5	207.7	192.3	181.8	177.7	173.6	166.7
60°	333.9	307.5	282.0	254.7	210.5	185.4	170.4	162.2	158.1	155.4	150.8
62.5°	289.3	268.8	246.9	225.1	185.0	162.2	150.8	142.6	139.0	138.5	134.4
65°	246.5	231.9	214.1	192.7	161.3	141.2	130.3	125.3	121.2	121.2	118.0
67.5°	203.6	193.6	179.5	164.5	139.9	121.2	111.2	106.6	104.3	104.3	102.0
70°	169.5	162.6	149.9	136.7	115.3	101.1	93.4	89.3	87.9	88.4	86.6
72.5°	137.6	130.3	119.8	110.2	94.3	83.8	78.4	73.8	71.5	72.0	71.5
75°	106.6	103.0	93.8	86.6	73.8	66.5	61.5	59.2	57.4	57.9	56.9
77.5°	80.2	74.7	69.7	64.7	56.9	51.0	46.9	44.6	43.3	43.3	43.3
80°	54.7	53.8	49.7	46.9	40.5	36.0	32.8	32.3	31.0	31.0	31.0
82.5°	35.5	33.3	31.0	29.2	25.5	22.8	21.4	20.5	20.0	19.6	20.5
85°	19.6	18.2	17.3	15.5	14.1	12.8	11.4	10.9	10.5	10.9	10.5
87.5°	7.7	6.4	6.4	5.9	5.5	5.0	5.0	4.1	4.1	3.6	3.6
90°	20.0	16.2	14.3	12.9	10.0	7.1	4.2	1.3	4.2	7.1	10.0
92.5°	49.5	47.8	46.9	46.0	44.3	42.6	40.8	39.1	40.8	42.6	44.3
95°	89.5	87.2	86.0	85.0	83.0	80.9	78.9	76.9	78.9	80.9	83.0
97.5°	135.5	133.8	132.9	132.2	130.7	129.3	127.8	126.4	127.8	129.3	130.7
100°	187.2	185.7	185.0	184.1	182.4	180.7	178.9	177.2	178.9	180.7	182.4
102.5°	242.8	240.8	239.8	239.4	238.5	237.6	236.8	235.9	236.8	237.6	238.5
105°	299.7	297.1	295.8	295.5	294.9	294.4	293.8	293.2	293.8	294.4	294.9
107.5°	364.0	362.9	362.3	362.2	361.9	361.6	361.3	361.0	361.3	361.6	361.9
110°	427.0	426.4	426.1	425.8	425.2	424.7	424.1	423.5	424.1	424.7	425.2

TEST NUMBER: P1031592

CATALOG NUMBER: S123DIW-B340D1320UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	490.0	490.0	490.0	489.9	489.6	489.3	489.0	488.7	489.0	489.3	489.6
115°	556.8	557.4	557.7	557.3	556.4	555.5	554.7	553.8	554.7	555.5	556.4
117.5°	620.7	621.3	621.6	621.5	621.2	620.9	620.6	620.3	620.6	620.9	621.2
120°	687.2	688.7	689.4	688.5	686.8	685.0	683.3	681.5	683.3	685.0	686.8
122.5°	749.7	750.3	750.6	750.0	748.9	747.7	746.6	745.4	746.6	747.7	748.9
125°	813.6	814.2	814.5	814.1	813.2	812.3	811.5	810.6	811.5	812.3	813.2
127.5°	877.4	878.0	878.3	877.4	875.7	874.0	872.2	870.5	872.2	874.0	875.7
130°	939.6	940.5	940.9	939.7	937.4	935.1	932.7	930.4	932.7	935.1	937.4
132.5°	999.9	1000.5	1000.8	999.6	997.3	995.0	992.7	990.4	992.7	995.0	997.3
135°	1059.0	1059.3	1059.5	1058.6	1056.9	1055.1	1053.4	1051.6	1053.4	1055.1	1056.9
137.5°	1115.5	1114.6	1114.2	1113.5	1112.0	1110.6	1109.1	1107.7	1109.1	1110.6	1112.0
140°	1173.2	1172.9	1172.8	1172.1	1170.6	1169.2	1167.7	1166.3	1167.7	1169.2	1170.6
142.5°	1227.2	1226.6	1226.3	1225.6	1224.1	1222.6	1221.2	1219.7	1221.2	1222.6	1224.1
145°	1279.7	1278.8	1278.4	1278.1	1277.5	1277.0	1276.4	1275.8	1276.4	1277.0	1277.5
147.5°	1330.5	1329.6	1329.2	1328.6	1327.5	1326.3	1325.2	1324.0	1325.2	1326.3	1327.5
150°	1378.3	1377.7	1377.4	1377.1	1376.5	1376.0	1375.4	1374.8	1375.4	1376.0	1376.5
152.5°	1420.8	1420.5	1420.4	1420.0	1419.1	1418.2	1417.4	1416.5	1417.4	1418.2	1419.1
155°	1461.2	1460.9	1460.8	1460.8	1460.8	1460.8	1460.8	1460.8	1460.8	1460.8	1460.8
157.5°	1497.7	1497.4	1497.3	1497.4	1497.7	1498.0	1498.3	1498.6	1498.3	1498.0	1497.7
160°	1531.2	1531.2	1531.2	1531.5	1532.1	1532.6	1533.2	1533.8	1533.2	1532.6	1532.1
162.5°	1561.6	1561.3	1561.2	1561.6	1562.5	1563.4	1564.2	1565.1	1564.2	1563.4	1562.5
165°	1587.2	1587.2	1587.2	1587.6	1588.5	1589.4	1590.2	1591.1	1590.2	1589.4	1588.5
167.5°	1608.5	1608.2	1608.1	1608.7	1609.8	1611.0	1612.1	1613.3	1612.1	1611.0	1609.8
170°	1626.3	1626.3	1626.3	1626.9	1628.0	1629.2	1630.3	1631.5	1630.3	1629.2	1628.0
172.5°	1640.6	1640.6	1640.6	1641.2	1642.4	1643.5	1644.7	1645.9	1644.7	1643.5	1642.4
175°	1649.8	1649.8	1649.8	1650.4	1651.5	1652.7	1653.8	1655.0	1653.8	1652.7	1651.5
177.5°	1655.0	1655.0	1655.0	1655.6	1656.7	1657.9	1659.0	1660.2	1659.0	1657.9	1656.7
180°	1658.9	1658.9	1658.9	1658.9	1658.9	1658.9	1658.9	1658.9	1658.9	1658.9	1658.9

TEST NUMBER: P1031592

CATALOG NUMBER: S123DIW-B340D1320UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	462.9	462.4	463.3	460.6	456.0	453.8	447.4	446.0	445.6	446.0	446.5
5°	450.1	449.7	448.3	443.7	438.3	434.2	426.4	426.0	423.2	420.5	421.9
7.5°	437.8	436.0	433.3	427.3	420.0	415.5	409.1	404.6	400.9	398.6	396.8
10°	425.5	422.8	420.0	412.3	403.2	396.4	388.6	385.0	380.9	379.0	377.2
12.5°	409.6	406.8	401.8	392.7	387.2	378.6	370.8	367.2	364.9	361.3	359.0
15°	396.8	391.3	388.6	379.0	367.6	366.7	352.6	351.7	347.1	347.1	343.5
17.5°	382.2	378.1	373.1	363.5	355.3	347.1	339.9	337.1	333.0	332.1	330.3
20°	368.1	362.6	360.8	351.2	342.6	332.6	324.8	322.1	320.3	318.4	319.8
22.5°	353.5	349.0	344.4	335.8	329.4	319.4	314.8	312.1	309.3	308.4	308.9
25°	339.4	335.3	330.7	322.1	315.3	307.1	303.0	301.6	300.2	300.2	299.8
27.5°	325.7	321.6	317.5	309.8	303.0	297.0	293.8	292.5	291.1	292.0	292.9
30°	311.6	308.0	304.3	297.5	292.0	286.6	284.7	283.8	283.4	285.6	285.6
32.5°	298.9	295.7	292.9	286.6	281.1	276.5	275.2	275.6	276.1	277.4	278.4
35°	285.6	283.4	280.6	275.2	270.6	266.5	267.0	267.0	267.9	270.2	272.0
37.5°	273.8	270.6	268.3	263.8	260.1	256.5	257.9	259.2	260.1	262.9	263.8
40°	259.7	258.3	256.5	251.9	248.7	248.3	248.7	249.7	251.5	252.8	254.2
42.5°	248.3	246.5	244.2	240.5	237.8	238.3	238.7	239.6	240.5	242.8	244.2
45°	235.5	234.2	232.3	229.2	226.9	227.3	227.8	227.8	228.7	231.4	232.3
47.5°	221.4	221.9	219.6	216.4	215.0	215.0	215.0	215.9	218.2	219.1	219.6
50°	207.7	206.8	206.4	203.2	202.3	201.8	202.3	202.7	205.9	205.5	206.8
52.5°	193.2	193.2	192.7	190.9	189.5	189.5	188.6	190.9	191.8	192.7	194.1
55°	179.0	177.7	177.2	176.3	174.5	174.0	174.9	177.7	178.6	179.5	180.9
57.5°	163.6	163.6	162.6	161.3	161.3	161.3	161.3	163.1	164.5	165.4	168.1
60°	149.4	147.6	146.2	146.2	146.2	145.8	148.5	148.5	151.3	151.7	152.6
62.5°	132.6	131.7	130.8	131.2	130.8	131.7	132.6	134.4	134.9	136.2	137.6
65°	116.6	116.6	115.7	118.4	116.6	116.6	118.9	118.9	119.8	121.2	123.0
67.5°	101.1	101.6	100.7	100.7	101.6	102.0	102.5	104.3	104.8	106.6	108.9
70°	85.2	86.1	86.6	85.6	86.6	87.5	88.4	88.8	90.7	91.6	92.9
72.5°	71.1	72.0	70.6	71.1	71.5	72.4	72.9	73.8	74.7	77.4	78.4
75°	56.9	56.5	56.0	57.9	56.9	58.8	59.2	59.2	60.1	62.4	63.3
77.5°	43.7	43.7	44.2	43.3	44.6	44.2	44.6	46.0	47.4	47.4	51.0
80°	30.5	31.4	31.4	31.4	31.9	32.3	31.4	33.7	34.2	34.2	35.5
82.5°	19.6	20.0	19.6	20.5	20.5	21.4	21.0	21.4	22.3	23.2	23.7
85°	10.5	10.5	11.4	11.4	10.9	11.4	10.9	11.4	12.3	12.3	12.8
87.5°	3.6	3.6	3.6	3.6	4.1	3.6	4.1	4.1	3.6	3.6	5.0
90°	12.9	14.3	16.2	20.0	23.7	27.5	31.3	32.5	33.6	34.8	35.9
92.5°	46.0	46.9	47.8	49.5	51.2	53.0	54.7	55.6	56.4	57.3	58.2
95°	85.0	86.0	87.2	89.5	91.8	94.1	96.4	97.6	98.7	99.9	101.0
97.5°	132.2	132.9	133.8	135.5	137.2	139.0	140.7	142.2	143.6	145.1	146.6
100°	184.1	185.0	185.7	187.2	188.7	190.1	191.6	192.5	193.3	194.2	195.1
102.5°	239.4	239.8	240.8	242.8	244.9	246.9	248.9	249.8	250.6	251.5	252.4
105°	295.5	295.8	297.1	299.7	302.3	304.9	307.5	307.5	307.5	307.5	307.5
107.5°	362.2	362.3	362.9	364.0	365.2	366.3	367.5	368.4	369.2	370.1	371.0
110°	425.8	426.1	426.4	427.0	427.5	428.1	428.7	429.9	431.0	432.2	433.3

TEST NUMBER: P1031592

CATALOG NUMBER: S123DIW-B340D1320UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	489.9	490.0	490.0	490.0	490.0	490.0	490.0	491.4	492.9	494.3	495.8
115°	557.3	557.7	557.4	556.8	556.3	555.7	555.1	555.4	555.7	556.0	556.3
117.5°	621.5	621.6	621.3	620.7	620.2	619.6	619.0	619.0	619.0	619.0	619.0
120°	688.5	689.4	688.7	687.2	685.7	684.3	682.8	682.5	682.2	681.9	681.6
122.5°	750.0	750.6	750.3	749.7	749.2	748.6	748.0	747.1	746.3	745.4	744.5
125°	814.1	814.5	814.2	813.6	813.1	812.5	811.9	810.7	809.5	808.4	807.2
127.5°	877.4	878.3	878.0	877.4	876.9	876.3	875.7	874.0	872.2	870.5	868.8
130°	939.7	940.9	940.5	939.6	938.7	937.9	937.0	935.8	934.6	933.5	932.3
132.5°	999.6	1000.8	1000.5	999.9	999.4	998.8	998.2	996.8	995.3	993.9	992.4
135°	1058.6	1059.5	1059.3	1059.0	1058.7	1058.4	1058.1	1056.9	1055.8	1054.6	1053.5
137.5°	1113.5	1114.2	1114.6	1115.5	1116.4	1117.2	1118.1	1116.7	1115.2	1113.8	1112.3
140°	1172.1	1172.8	1172.9	1173.2	1173.5	1173.8	1174.1	1173.8	1173.5	1173.2	1172.9
142.5°	1225.6	1226.3	1226.6	1227.2	1227.7	1228.3	1228.9	1228.6	1228.3	1228.0	1227.7
145°	1278.1	1278.4	1278.8	1279.7	1280.6	1281.4	1282.3	1282.0	1281.7	1281.4	1281.1
147.5°	1328.6	1329.2	1329.6	1330.5	1331.4	1332.2	1333.1	1333.1	1333.1	1333.1	1333.1
150°	1377.1	1377.4	1377.7	1378.3	1378.8	1379.4	1380.0	1380.0	1380.0	1380.0	1380.0
152.5°	1420.0	1420.4	1420.5	1420.8	1421.1	1421.4	1421.7	1422.3	1422.9	1423.4	1424.0
155°	1460.8	1460.8	1460.9	1461.2	1461.5	1461.8	1462.1	1463.3	1464.4	1465.6	1466.7
157.5°	1497.4	1497.3	1497.4	1497.7	1498.0	1498.3	1498.6	1499.8	1500.9	1502.1	1503.2
160°	1531.5	1531.2	1531.2	1531.2	1531.2	1531.2	1531.2	1532.6	1534.1	1535.5	1537.0
162.5°	1561.6	1561.2	1561.3	1561.6	1561.9	1562.2	1562.5	1563.9	1565.4	1566.8	1568.3
165°	1587.6	1587.2	1587.2	1587.2	1587.2	1587.2	1587.2	1588.9	1590.7	1592.4	1594.1
167.5°	1608.7	1608.1	1608.2	1608.5	1608.8	1609.1	1609.4	1611.1	1612.9	1614.6	1616.3
170°	1626.9	1626.3	1626.3	1626.3	1626.3	1626.3	1626.3	1628.3	1630.3	1632.4	1634.4
172.5°	1641.2	1640.6	1640.6	1640.6	1640.6	1640.6	1640.6	1642.4	1644.1	1645.9	1647.6
175°	1650.4	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1651.5	1653.3	1655.0	1656.7
177.5°	1655.6	1655.0	1655.0	1655.0	1655.0	1655.0	1655.0	1656.7	1658.5	1660.2	1661.9
180°	1658.9	1658.9	1658.9	1658.9	1658.9	1658.9	1658.9	1658.9	1658.9	1658.9	1658.9

TEST NUMBER: P1031592

CATALOG NUMBER: S123DIW-B340D1320UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	446.0	446.5	444.6	443.3	446.9	444.6	444.6	445.1	444.2	445.6	445.1
5°	421.0	421.4	418.2	419.1	417.3	416.9	416.4	419.1	418.7	418.2	419.1
7.5°	396.4	396.4	395.0	394.1	394.1	392.7	394.5	394.1	395.0	395.0	396.4
10°	375.8	376.8	374.5	372.2	371.7	372.2	372.2	372.7	373.1	376.3	375.8
12.5°	359.0	357.6	357.2	355.8	353.5	352.6	351.7	356.7	355.3	355.3	355.3
15°	340.3	343.5	343.0	338.9	338.0	339.9	338.9	338.9	343.5	343.0	342.6
17.5°	330.3	329.4	328.5	326.2	326.6	326.2	326.6	326.6	329.4	329.4	329.4
20°	318.9	317.1	317.1	316.2	316.2	314.8	316.6	317.1	318.9	318.9	319.4
22.5°	308.9	307.5	307.5	307.1	308.0	306.1	308.0	308.4	308.4	309.8	309.8
25°	300.2	299.3	299.3	300.2	300.2	300.2	300.2	302.0	300.7	301.1	300.7
27.5°	292.5	292.9	293.4	293.8	293.4	293.8	294.3	295.2	295.7	295.2	294.3
30°	285.2	286.6	287.0	287.0	287.9	288.4	288.8	288.8	289.3	287.9	288.8
32.5°	279.7	279.7	280.6	281.1	282.0	282.5	282.5	283.4	282.9	281.5	282.0
35°	272.0	272.0	273.8	274.7	276.1	275.6	276.1	276.1	276.5	275.6	274.3
37.5°	264.2	265.1	265.1	267.0	267.4	267.9	267.4	268.3	267.9	267.0	266.5
40°	255.1	254.7	255.1	256.5	256.9	256.9	256.9	257.9	257.9	257.9	257.4
42.5°	243.7	245.1	244.6	246.0	245.6	245.6	246.5	247.4	247.8	246.5	246.9
45°	232.8	232.8	233.7	233.7	234.2	234.2	236.0	235.1	236.0	235.1	235.5
47.5°	221.0	221.4	221.4	221.9	222.8	223.7	222.8	223.2	223.2	223.7	222.8
50°	207.7	207.7	208.7	210.0	211.8	210.9	210.5	212.3	210.9	210.9	210.0
52.5°	194.1	195.4	195.9	197.3	198.6	199.1	199.5	198.6	199.1	197.7	198.2
55°	180.9	181.3	183.1	184.5	185.9	185.9	185.4	185.9	186.3	184.5	184.5
57.5°	167.7	169.0	170.8	170.8	172.7	172.7	172.2	172.2	172.7	171.3	170.8
60°	153.5	154.9	157.2	157.2	159.9	160.4	159.5	158.5	158.5	157.2	157.6
62.5°	138.5	139.9	141.2	143.5	145.3	144.4	146.2	144.4	144.9	142.1	142.1
65°	125.3	125.7	128.0	130.3	130.3	131.2	130.3	130.8	129.4	129.4	127.6
67.5°	109.8	109.8	112.1	114.3	116.6	116.6	116.6	115.3	115.3	113.9	113.9
70°	96.1	95.7	97.9	99.3	100.7	101.1	100.2	99.8	98.9	97.5	97.0
72.5°	79.3	80.2	82.5	83.4	85.6	85.2	87.5	84.7	84.7	82.5	82.0
75°	64.2	65.1	67.4	68.8	70.2	70.2	71.5	70.2	68.3	67.4	67.0
77.5°	51.0	50.6	52.4	54.7	55.1	54.7	55.6	55.1	53.3	53.3	52.4
80°	36.4	37.8	39.6	39.2	41.0	40.5	40.5	39.6	39.6	38.3	39.2
82.5°	24.1	25.5	26.0	25.5	26.0	26.9	27.3	26.9	26.9	26.0	26.4
85°	12.8	12.8	13.7	14.1	13.7	13.7	14.1	15.5	14.6	13.7	14.6
87.5°	4.1	3.6	3.6	4.1	3.6	3.6	4.1	4.1	4.6	4.6	4.6
90°	36.5	36.8	37.4	37.9	38.5	39.1	38.5	37.9	37.4	36.8	36.5
92.5°	58.6	58.3	57.7	57.2	56.6	56.0	56.6	57.2	57.7	58.3	58.6
95°	101.6	101.6	101.6	101.6	101.6	101.6	101.6	101.6	101.6	101.6	101.6
97.5°	147.3	147.2	146.9	146.6	146.3	146.0	146.3	146.6	146.9	147.2	147.3
100°	195.5	195.8	196.4	196.9	197.5	198.1	197.5	196.9	196.4	195.8	195.5
102.5°	252.8	252.7	252.4	252.1	251.8	251.5	251.8	252.1	252.4	252.7	252.8
105°	307.5	307.8	308.4	308.9	309.5	310.1	309.5	308.9	308.4	307.8	307.5
107.5°	371.4	371.3	371.0	370.7	370.4	370.1	370.4	370.7	371.0	371.3	371.4
110°	433.9	433.6	433.0	432.5	431.9	431.3	431.9	432.5	433.0	433.6	433.9

TEST NUMBER: P1031592

CATALOG NUMBER: S123DIW-B340D1320UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	496.5	496.5	496.5	496.5	496.5	496.5	496.5	496.5	496.5	496.5	496.5
115°	556.4	556.3	556.0	555.7	555.4	555.1	555.4	555.7	556.0	556.3	556.4
117.5°	619.0	618.6	617.7	616.8	616.0	615.1	616.0	616.8	617.7	618.6	619.0
120°	681.5	681.2	680.6	680.1	679.5	678.9	679.5	680.1	680.6	681.2	681.5
122.5°	744.1	743.7	742.8	741.9	741.1	740.2	741.1	741.9	742.8	743.7	744.1
125°	806.6	806.0	804.9	803.7	802.6	801.4	802.6	803.7	804.9	806.0	806.6
127.5°	867.9	867.3	866.2	865.0	863.9	862.7	863.9	865.0	866.2	867.3	867.9
130°	931.7	930.7	928.7	926.6	924.6	922.6	924.6	926.6	928.7	930.7	931.7
132.5°	991.7	991.0	989.5	988.1	986.6	985.2	986.6	988.1	989.5	991.0	991.7
135°	1052.9	1052.6	1052.0	1051.5	1050.9	1050.3	1050.9	1051.5	1052.0	1052.6	1052.9
137.5°	1111.6	1111.2	1110.3	1109.4	1108.6	1107.7	1108.6	1109.4	1110.3	1111.2	1111.6
140°	1172.8	1171.8	1169.8	1167.7	1165.7	1163.7	1165.7	1167.7	1169.8	1171.8	1172.8
142.5°	1227.6	1226.9	1225.4	1223.9	1222.5	1221.0	1222.5	1223.9	1225.4	1226.9	1227.6
145°	1281.0	1280.4	1279.3	1278.1	1277.0	1275.8	1277.0	1278.1	1279.3	1280.4	1281.0
147.5°	1333.1	1332.2	1330.5	1328.8	1327.0	1325.3	1327.0	1328.8	1330.5	1332.2	1333.1
150°	1380.0	1379.1	1377.4	1375.7	1373.9	1372.2	1373.9	1375.7	1377.4	1379.1	1380.0
152.5°	1424.3	1423.6	1422.1	1420.7	1419.2	1417.8	1419.2	1420.7	1422.1	1423.6	1424.3
155°	1467.3	1466.3	1464.3	1462.2	1460.2	1458.2	1460.2	1462.2	1464.3	1466.3	1467.3
157.5°	1503.8	1502.9	1501.2	1499.5	1497.7	1496.0	1497.7	1499.5	1501.2	1502.9	1503.8
160°	1537.7	1537.1	1536.0	1534.8	1533.7	1532.5	1533.7	1534.8	1536.0	1537.1	1537.7
162.5°	1569.0	1568.0	1566.0	1563.9	1561.9	1559.9	1561.9	1563.9	1566.0	1568.0	1569.0
165°	1595.0	1594.0	1592.0	1589.9	1587.9	1585.9	1587.9	1589.9	1592.0	1594.0	1595.0
167.5°	1617.2	1616.3	1614.6	1612.9	1611.1	1609.4	1611.1	1612.9	1614.6	1616.3	1617.2
170°	1635.4	1634.4	1632.4	1630.3	1628.3	1626.3	1628.3	1630.3	1632.4	1634.4	1635.4
172.5°	1648.5	1647.5	1645.4	1643.4	1641.3	1639.3	1641.3	1643.4	1645.4	1647.5	1648.5
175°	1657.6	1656.6	1654.6	1652.5	1650.5	1648.5	1650.5	1652.5	1654.6	1656.6	1657.6
177.5°	1662.8	1661.8	1659.8	1657.7	1655.7	1653.7	1655.7	1657.7	1659.8	1661.8	1662.8
180°	1658.9	1658.9	1658.9	1658.9	1658.9	1658.9	1658.9	1658.9	1658.9	1658.9	1658.9

TEST NUMBER: P1031592

CATALOG NUMBER: S123DIW-B340D1320UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	446.5	447.4	447.8	446.0	444.6	446.9	450.1	452.4	454.2	456.5	457.9
5°	420.0	423.2	423.2	424.1	425.5	427.8	433.7	437.8	441.5	444.2	446.5
7.5°	397.7	400.0	401.4	403.6	405.9	409.1	415.9	421.9	427.3	430.5	434.2
10°	377.7	379.5	381.8	383.1	387.2	391.8	400.5	405.5	411.8	416.9	421.4
12.5°	358.5	364.9	366.3	365.8	369.5	374.5	383.1	390.9	397.7	402.7	407.7
15°	344.9	347.1	349.9	349.4	357.2	358.5	365.8	374.9	384.1	387.2	391.8
17.5°	329.8	333.5	336.2	337.6	339.9	344.9	351.7	358.5	370.4	370.8	382.7
20°	318.0	321.6	323.5	325.3	326.6	332.6	338.5	346.2	355.8	360.8	367.2
22.5°	310.2	312.1	313.4	314.8	316.6	319.8	327.1	335.8	342.1	347.6	351.7
25°	301.1	303.0	304.8	305.7	307.1	308.9	314.3	321.2	330.3	333.9	338.0
27.5°	294.8	294.8	295.7	295.7	297.5	299.3	303.4	309.8	317.1	321.6	327.1
30°	287.9	287.5	287.9	287.5	287.0	289.7	293.4	298.9	303.9	309.3	313.0
32.5°	281.1	280.6	280.6	281.1	279.3	280.6	282.5	287.5	292.9	295.7	299.8
35°	273.8	272.9	272.9	272.9	272.0	271.1	272.9	277.4	281.1	284.7	287.9
37.5°	266.5	265.1	265.1	264.2	263.3	262.0	262.0	265.6	270.6	272.0	276.1
40°	256.5	256.5	255.6	255.1	254.2	253.3	251.9	255.1	259.7	261.0	264.2
42.5°	246.5	245.1	244.6	244.6	244.6	243.3	242.4	244.6	247.4	249.7	251.5
45°	235.1	234.2	234.6	234.2	233.3	232.8	232.3	233.3	236.4	237.4	239.6
47.5°	222.8	222.3	222.3	221.9	221.4	221.9	220.0	222.3	223.2	224.1	226.0
50°	210.0	209.6	209.1	208.7	208.7	209.1	208.7	208.7	210.5	211.4	213.2
52.5°	197.3	195.9	195.9	195.4	195.4	194.5	195.4	195.9	196.8	197.7	198.6
55°	183.6	183.6	182.2	182.2	181.3	181.3	181.8	181.3	183.1	184.1	184.1
57.5°	170.4	168.6	169.0	168.1	167.2	166.7	166.7	167.7	168.6	168.6	169.5
60°	156.3	154.4	154.0	152.2	153.1	151.7	152.2	152.2	154.0	153.1	154.0
62.5°	142.1	139.9	138.5	137.6	137.6	138.0	137.1	136.7	137.6	138.5	140.3
65°	127.1	125.7	124.4	123.0	123.0	122.5	123.5	122.1	121.6	122.1	123.0
67.5°	111.6	110.2	108.9	107.5	108.0	106.6	105.7	107.1	106.1	106.6	107.5
70°	96.6	95.7	92.9	92.0	91.6	92.0	91.6	90.7	92.0	91.6	92.0
72.5°	81.5	80.6	79.3	77.0	77.0	76.5	76.1	76.1	75.6	75.6	75.6
75°	67.0	65.1	63.8	63.3	62.4	62.0	61.5	60.6	61.0	61.5	60.6
77.5°	51.9	49.7	49.2	49.2	47.8	47.8	48.3	47.8	47.4	47.4	47.4
80°	38.3	36.4	36.4	35.5	34.6	34.6	34.6	34.6	34.2	33.7	34.2
82.5°	24.6	24.1	23.7	23.7	24.6	22.8	23.7	23.2	22.8	22.8	22.3
85°	13.7	14.1	13.7	14.1	13.2	13.7	13.7	13.7	13.2	13.7	12.8
87.5°	5.0	5.0	5.0	5.5	5.5	5.5	5.5	5.5	5.9	5.5	5.5
90°	35.9	34.8	33.6	32.5	31.3	27.5	23.7	20.0	16.2	14.3	12.9
92.5°	58.2	57.3	56.4	55.6	54.7	53.0	51.2	49.5	47.8	46.9	46.0
95°	101.0	99.9	98.7	97.6	96.4	94.1	91.8	89.5	87.2	86.0	85.0
97.5°	146.6	145.1	143.6	142.2	140.7	139.0	137.2	135.5	133.8	132.9	132.2
100°	195.1	194.2	193.3	192.5	191.6	190.1	188.7	187.2	185.7	185.0	184.1
102.5°	252.4	251.5	250.6	249.8	248.9	246.9	244.9	242.8	240.8	239.8	239.4
105°	307.5	307.5	307.5	307.5	307.5	304.9	302.3	299.7	297.1	295.8	295.5
107.5°	371.0	370.1	369.2	368.4	367.5	366.3	365.2	364.0	362.9	362.3	362.2
110°	433.3	432.2	431.0	429.9	428.7	428.1	427.5	427.0	426.4	426.1	425.8

TEST NUMBER: P1031592

CATALOG NUMBER: S123DIW-B340D1320UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	495.8	494.3	492.9	491.4	490.0	490.0	490.0	490.0	490.0	490.0	489.9
115°	556.3	556.0	555.7	555.4	555.1	555.7	556.3	556.8	557.4	557.7	557.3
117.5°	619.0	619.0	619.0	619.0	619.0	619.6	620.2	620.7	621.3	621.6	621.5
120°	681.6	681.9	682.2	682.5	682.8	684.3	685.7	687.2	688.7	689.4	688.5
122.5°	744.5	745.4	746.3	747.1	748.0	748.6	749.2	749.7	750.3	750.6	750.0
125°	807.2	808.4	809.5	810.7	811.9	812.5	813.1	813.6	814.2	814.5	814.1
127.5°	868.8	870.5	872.2	874.0	875.7	876.3	876.9	877.4	878.0	878.3	877.4
130°	932.3	933.5	934.6	935.8	937.0	937.9	938.7	939.6	940.5	940.9	939.7
132.5°	992.4	993.9	995.3	996.8	998.2	998.8	999.4	999.9	1000.5	1000.8	999.6
135°	1053.5	1054.6	1055.8	1056.9	1058.1	1058.4	1058.7	1059.0	1059.3	1059.5	1058.6
137.5°	1112.3	1113.8	1115.2	1116.7	1118.1	1117.2	1116.4	1115.5	1114.6	1114.2	1113.5
140°	1172.9	1173.2	1173.5	1173.8	1174.1	1173.8	1173.5	1173.2	1172.9	1172.8	1172.1
142.5°	1227.7	1228.0	1228.3	1228.6	1228.9	1228.3	1227.7	1227.2	1226.6	1226.3	1225.6
145°	1281.1	1281.4	1281.7	1282.0	1282.3	1281.4	1280.6	1279.7	1278.8	1278.4	1278.1
147.5°	1333.1	1333.1	1333.1	1333.1	1333.1	1332.2	1331.4	1330.5	1329.6	1329.2	1328.6
150°	1380.0	1380.0	1380.0	1380.0	1380.0	1379.4	1378.8	1378.3	1377.7	1377.4	1377.1
152.5°	1424.0	1423.4	1422.9	1422.3	1421.7	1421.4	1421.1	1420.8	1420.5	1420.4	1420.0
155°	1466.7	1465.6	1464.4	1463.3	1462.1	1461.8	1461.5	1461.2	1460.9	1460.8	1460.8
157.5°	1503.2	1502.1	1500.9	1499.8	1498.6	1498.3	1498.0	1497.7	1497.4	1497.3	1497.4
160°	1537.0	1535.5	1534.1	1532.6	1531.2	1531.2	1531.2	1531.2	1531.2	1531.2	1531.5
162.5°	1568.3	1566.8	1565.4	1563.9	1562.5	1562.2	1561.9	1561.6	1561.3	1561.2	1561.6
165°	1594.1	1592.4	1590.7	1588.9	1587.2	1587.2	1587.2	1587.2	1587.2	1587.2	1587.6
167.5°	1616.3	1614.6	1612.9	1611.1	1609.4	1609.1	1608.8	1608.5	1608.2	1608.1	1608.7
170°	1634.4	1632.4	1630.3	1628.3	1626.3	1626.3	1626.3	1626.3	1626.3	1626.3	1626.9
172.5°	1647.6	1645.9	1644.1	1642.4	1640.6	1640.6	1640.6	1640.6	1640.6	1640.6	1641.2
175°	1656.7	1655.0	1653.3	1651.5	1649.8	1649.8	1649.8	1649.8	1649.8	1649.8	1650.4
177.5°	1661.9	1660.2	1658.5	1656.7	1655.0	1655.0	1655.0	1655.0	1655.0	1655.0	1655.6
180°	1658.9	1658.9	1658.9	1658.9	1658.9	1658.9	1658.9	1658.9	1658.9	1658.9	1658.9

TEST NUMBER: P1031592

CATALOG NUMBER: S123DIW-B340D1320UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	470.2	470.2	470.2	470.2
2.5°	460.1	461.5	466.1	471.5
5°	451.0	454.7	461.0	469.7
7.5°	441.0	446.5	455.6	466.5
10°	429.6	437.4	448.7	462.4
12.5°	417.3	427.3	441.9	456.0
15°	409.6	419.6	432.8	448.3
17.5°	394.5	406.4	420.0	441.9
20°	379.0	392.3	410.0	431.9
22.5°	367.2	381.3	398.2	421.4
25°	353.1	367.6	385.9	410.0
27.5°	338.0	352.6	373.1	398.6
30°	326.6	340.8	360.4	387.7
32.5°	313.0	326.6	347.1	375.8
35°	297.5	313.0	332.6	361.7
37.5°	285.6	299.8	320.3	348.1
40°	272.9	285.2	305.2	332.6
42.5°	259.2	272.9	290.2	317.5
45°	246.5	256.5	274.3	300.2
47.5°	232.8	244.2	257.9	277.9
50°	218.2	227.8	242.8	256.5
52.5°	204.1	211.8	224.6	235.1
55°	189.1	196.8	206.4	212.8
57.5°	174.9	180.4	186.8	190.9
60°	157.6	163.1	167.2	171.3
62.5°	142.1	146.2	148.5	150.8
65°	126.2	128.5	129.8	131.7
67.5°	108.9	111.2	111.6	114.3
70°	92.9	93.4	94.3	95.7
72.5°	77.9	78.8	78.4	79.3
75°	62.4	63.3	62.4	63.3
77.5°	47.4	48.3	48.3	49.7
80°	34.2	34.6	35.1	35.1
82.5°	22.3	23.7	22.8	23.2
85°	12.8	13.2	13.2	13.7
87.5°	5.9	6.4	5.9	6.8
90°	10.0	7.1	4.2	1.3
92.5°	44.3	42.6	40.8	39.1
95°	83.0	80.9	78.9	76.9
97.5°	130.7	129.3	127.8	126.4
100°	182.4	180.7	178.9	177.2
102.5°	238.5	237.6	236.8	235.9
105°	294.9	294.4	293.8	293.2
107.5°	361.9	361.6	361.3	361.0
110°	425.2	424.7	424.1	423.5

TEST NUMBER: P1031592

CATALOG NUMBER: S123DIW-B340D1320UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	489.6	489.3	489.0	488.7
115°	556.4	555.5	554.7	553.8
117.5°	621.2	620.9	620.6	620.3
120°	686.8	685.0	683.3	681.5
122.5°	748.9	747.7	746.6	745.4
125°	813.2	812.3	811.5	810.6
127.5°	875.7	874.0	872.2	870.5
130°	937.4	935.1	932.7	930.4
132.5°	997.3	995.0	992.7	990.4
135°	1056.9	1055.1	1053.4	1051.6
137.5°	1112.0	1110.6	1109.1	1107.7
140°	1170.6	1169.2	1167.7	1166.3
142.5°	1224.1	1222.6	1221.2	1219.7
145°	1277.5	1277.0	1276.4	1275.8
147.5°	1327.5	1326.3	1325.2	1324.0
150°	1376.5	1376.0	1375.4	1374.8
152.5°	1419.1	1418.2	1417.4	1416.5
155°	1460.8	1460.8	1460.8	1460.8
157.5°	1497.7	1498.0	1498.3	1498.6
160°	1532.1	1532.6	1533.2	1533.8
162.5°	1562.5	1563.4	1564.2	1565.1
165°	1588.5	1589.4	1590.2	1591.1
167.5°	1609.8	1611.0	1612.1	1613.3
170°	1628.0	1629.2	1630.3	1631.5
172.5°	1642.4	1643.5	1644.7	1645.9
175°	1651.5	1652.7	1653.8	1655.0
177.5°	1656.7	1657.9	1659.0	1660.2
180°	1658.9	1658.9	1658.9	1658.9

(END OF REPORT)