

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032139

Luminaire Tested: S123RDIW-B1165D460UB27-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032139
REPORT IS A COMBINATION OF REPORTS P994075 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B1165D460UB27-4F0-XX-W2A-F1
Description: Define 3 Regressed Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5954.0 lumens
Efficiency: N/A
Efficacy: 79.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 74.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032139

CATALOG NUMBER: S123RDIW-B1165D460UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1032139

CATALOG NUMBER: S123RDIW-B1165D460UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	77	77	73
1	103	99	95	92	98	94	91	88	85	83	80	77	75	73	69	68	66	66	66	63
2	95	87	81	76	90	83	78	73	75	71	67	68	65	62	61	59	57	57	57	53
3	87	77	70	64	82	74	67	62	67	62	57	61	56	53	55	52	49	49	49	46
4	80	69	61	55	75	66	58	53	60	54	49	54	50	46	49	46	42	42	42	39
5	73	62	53	47	69	59	51	46	54	48	43	49	44	40	45	41	37	37	37	35
6	68	55	47	41	64	53	46	40	49	42	38	45	39	35	41	36	33	33	33	31
7	63	50	42	37	60	48	41	36	44	38	34	41	35	31	37	33	30	30	30	27
8	59	46	38	33	56	44	37	32	41	34	30	37	32	28	34	30	27	27	27	24
9	55	42	35	29	52	41	33	29	37	31	27	35	29	26	32	27	24	24	24	22
10	51	39	32	27	49	37	31	26	35	29	25	32	27	23	30	25	22	22	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20730	20730	20730
5°	20764	19997	19943
10°	20601	19245	18866
15°	20334	18316	17686
20°	19983	17305	16368
25°	19621	16255	15119
30°	19156	15137	13642
35°	18679	14040	12298
40°	18230	12848	10813
45°	17654	11683	9477
50°	17017	10438	8094
55°	16358	9106	6828
60°	15727	7740	5542
65°	14915	6338	4325
70°	13891	4792	3092
75°	12420	3246	2449
80°	10597	2255	1718
85°	7953	1217	900

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17654 cd/sqm

TEST NUMBER: P1032139

CATALOG NUMBER: S123RDIW-B1165D460UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.0	3.0
10°-20°	503.7	8.5
20°-30°	725.2	12.2
30°-40°	816.6	13.7
40°-50°	781.2	13.1
50°-60°	639.4	10.7
60°-70°	431.1	7.2
70°-80°	216.2	3.6
80°-90°	57.7	1.0
90°-100°	37.2	0.6
100°-110°	112.6	1.9
110°-120°	191.7	3.2
120°-130°	252.3	4.2
130°-140°	283.5	4.8
140°-150°	278.8	4.7
150°-160°	234.7	3.9
160°-170°	156.2	2.6
170°-180°	54.7	0.9
0°-30°	1409.9	23.7
0°-40°	2226.5	37.4
0°-60°	3647.1	61.3
0°-90°	4352.2	73.1
90°-120°	341.6	5.7
90°-150°	1156.2	19.4
90°-180°	1602.0	26.9
0°-180°	5954.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1926	1926	1926	1926	1926	
5°	1926	1918	1899	1913	1910	183
15°	1837	1820	1776	1768	1757	518
25°	1671	1632	1560	1528	1510	769
35°	1446	1390	1293	1226	1198	905
45°	1189	1118	998	909	872	917
55°	903	826	694	603	572	810
65°	617	531	409	333	316	611
75°	326	252	166	150	147	348
85°	83	48	44	41	41	91
90°	0	5	11	13	14	7
95°	27	30	34	35	35	30
105°	102	103	107	107	108	109
115°	193	194	194	194	194	191
125°	282	284	283	281	279	252
135°	366	369	369	367	366	282
145°	445	446	447	446	445	278
155°	509	509	510	511	508	234
165°	554	553	553	556	553	156
175°	577	575	575	578	574	55
180°	578	578	578	578	578	

TEST NUMBER: P1032139

CATALOG NUMBER: S123RDIW-B1165D460UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1925.9	1925.9	1925.9	1925.9	1925.9
2.5°	1933.7	1927.5	1908.7	1925.9	1922.8
5°	1925.9	1918.1	1899.4	1913.4	1910.3
7.5°	1911.9	1904.1	1880.6	1890.0	1885.3
10°	1893.1	1882.2	1854.1	1855.6	1847.8
12.5°	1866.6	1854.1	1818.1	1816.6	1807.2
15°	1836.9	1819.7	1776.0	1768.2	1757.2
17.5°	1801.0	1782.2	1727.6	1711.9	1696.3
20°	1760.4	1735.4	1676.0	1655.7	1637.0
22.5°	1715.1	1685.4	1621.3	1594.8	1577.6
25°	1671.3	1632.3	1560.4	1527.6	1510.4
27.5°	1618.2	1576.0	1497.9	1454.2	1427.7
30°	1563.5	1516.7	1429.2	1376.1	1351.1
32.5°	1508.9	1454.2	1360.5	1301.1	1274.6
35°	1446.4	1390.2	1293.3	1226.2	1198.0
37.5°	1383.9	1323.0	1221.5	1146.5	1112.1
40°	1324.6	1255.8	1144.9	1063.7	1027.8
42.5°	1257.4	1188.7	1073.1	982.5	951.2
45°	1188.7	1118.4	998.1	909.1	871.6
47.5°	1121.5	1043.4	924.7	827.8	795.0
50°	1046.5	973.1	846.6	749.8	713.8
52.5°	979.4	898.1	773.2	671.7	640.4
55°	902.8	826.3	693.5	602.9	571.7
57.5°	834.1	751.3	617.0	531.1	504.5
60°	762.2	676.3	546.7	462.3	435.8
62.5°	690.4	604.5	474.8	396.7	368.6
65°	617.0	531.1	409.2	332.7	315.5
67.5°	543.6	456.1	337.4	279.6	260.9
70°	471.7	387.4	278.0	223.4	206.2
72.5°	399.9	317.1	220.2	178.1	173.4
75°	326.5	251.5	165.6	150.0	146.8
77.5°	259.3	190.6	129.6	120.3	117.1
80°	195.2	131.2	98.4	93.7	90.6
82.5°	134.3	81.2	70.3	65.6	65.6
85°	82.8	48.4	43.7	40.6	40.6
87.5°	37.5	20.3	20.3	18.7	17.2
90°	0.5	5.0	10.9	12.7	13.6
92.5°	13.6	16.3	19.1	20.4	19.5
95°	26.8	30.0	33.6	35.4	35.4
97.5°	44.0	46.3	49.0	51.3	50.9
100°	61.8	64.5	66.8	68.1	69.0
102.5°	82.2	83.6	86.7	88.1	87.6
105°	102.2	103.1	107.2	107.2	108.1
107.5°	125.8	126.2	128.1	129.4	129.0
110°	147.6	148.5	149.4	151.2	150.3

TEST NUMBER: P1032139

CATALOG NUMBER: S123RDIW-B1165D460UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	170.3	170.7	170.7	173.0	173.0
115°	193.0	194.4	193.5	193.9	193.5
117.5°	216.2	216.6	215.7	215.7	214.3
120°	237.5	240.2	238.0	237.5	236.6
122.5°	259.8	261.6	260.7	259.3	257.9
125°	282.5	283.8	282.9	281.1	279.3
127.5°	303.3	306.1	305.2	302.4	300.6
130°	324.2	327.9	326.5	324.7	321.5
132.5°	345.1	348.8	347.9	345.6	343.3
135°	366.5	369.2	368.7	366.9	366.0
137.5°	386.0	388.3	389.6	387.4	386.0
140°	406.4	408.7	409.2	408.7	405.5
142.5°	425.1	427.3	428.2	427.8	425.5
145°	444.6	445.5	446.8	446.4	444.6
147.5°	461.4	463.2	464.6	464.6	461.8
150°	479.1	480.0	480.9	480.9	478.2
152.5°	493.6	495.0	495.4	496.3	494.1
155°	509.1	509.1	509.5	511.3	508.2
157.5°	522.2	521.8	522.2	524.0	521.3
160°	534.5	533.6	533.6	535.9	534.0
162.5°	545.4	544.0	544.5	546.8	543.6
165°	554.5	553.1	553.1	555.8	552.7
167.5°	562.2	560.4	560.8	563.6	560.8
170°	568.6	566.7	566.7	569.9	566.7
172.5°	573.5	571.7	571.7	574.5	571.3
175°	576.7	574.9	574.9	577.6	574.5
177.5°	578.5	576.7	576.7	579.5	576.3
180°	578.1	578.1	578.1	578.1	578.1

(END OF REPORT)