

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032176

Luminaire Tested: S123RDIW-B340D1030UB27-4F0-XX-W2A-A

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032176
REPORT IS A COMBINATION OF REPORTS P994159 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B340D1030UB27-4F0-XX-W2A-A
Description: Define 3 Regressed Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5455.0 lumens
Efficiency: N/A
Efficacy: 122.6 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 44.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032176

CATALOG NUMBER: S123RDIW-B340D1030UB27-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1032176

CATALOG NUMBER: S123RDIW-B340D1030UB27-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32	24		
1	92	88	85	81	82	79	76	73	61	59	57	44	43	42	29	28	28	21		
2	84	77	72	67	75	69	64	60	53	50	47	39	37	35	26	25	24	18		
3	77	68	61	56	68	61	55	51	47	43	40	35	32	30	23	22	21	15		
4	70	60	53	47	62	54	48	43	42	38	34	31	28	26	21	19	18	13		
5	65	54	46	40	57	48	42	37	38	33	30	28	25	23	19	17	16	12		
6	59	48	40	35	53	43	37	32	34	29	26	25	22	20	17	15	14	11		
7	55	43	36	31	49	39	32	28	31	26	23	23	20	17	16	14	12	9		
8	51	39	32	27	45	35	29	25	28	23	20	21	18	16	14	13	11	9		
9	47	36	29	24	42	32	26	22	25	21	18	19	16	14	13	11	10	8		
10	44	33	26	21	39	29	23	19	23	19	16	18	15	13	12	10	9	7		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5654	5654	5654	5654
5°	5658	6512	5673	4831
10°	5609	7861	5633	4220
15°	5551	8922	5551	3721
20°	5437	9623	5468	3301
25°	5353	9143	5343	3012
30°	5256	6335	5245	2729
35°	5140	4067	5117	2516
40°	4994	2872	4970	2304
45°	4742	2299	4736	2097
50°	4431	1922	4417	1856
55°	4082	1585	4050	1574
60°	3739	1310	3702	1338
65°	3338	1049	3360	1135
70°	2965	729	3045	918
75°	2514	541	2617	706
80°	2003	358	2172	529
85°	1422	168	1556	328

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 7549 cd/sqm

TEST NUMBER: P1032176

CATALOG NUMBER: S123RDIW-B340D1030UB27-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.6	0.9
10°-20°	161.5	3.0
20°-30°	254.3	4.7
30°-40°	264.5	4.8
40°-50°	226.3	4.1
50°-60°	172.5	3.2
60°-70°	110.5	2.0
70°-80°	52.9	1.0
80°-90°	16.6	0.3
90°-100°	47.9	0.9
100°-110°	231.8	4.2
110°-120°	568.0	10.4
120°-130°	721.0	13.2
130°-140°	770.3	14.1
140°-150°	720.3	13.2
150°-160°	581.0	10.7
160°-170°	374.9	6.9
170°-180°	129.2	2.4
0°-30°	467.4	8.6
0°-40°	731.9	13.4
0°-60°	1130.6	20.7
0°-90°	1310.7	24.0
90°-120°	847.7	15.5
90°-150°	3059.2	56.1
90°-180°	4144.0	76.0
0°-180°	5455.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	525	525	525	525	525	
5°	525	624	526	463	525	50
15°	502	886	502	370	502	141
25°	456	913	455	301	456	210
35°	398	396	396	245	398	249
45°	319	211	319	193	319	246
55°	225	133	224	132	225	202
65°	138	76	139	83	138	138
75°	66	32	69	42	66	71
85°	15	8	16	15	15	17
90°	1	30	1	30	1	4
95°	62	38	62	38	62	74
105°	301	44	301	44	301	319
115°	565	594	565	594	565	558
125°	796	812	796	812	796	711
135°	991	1001	991	1001	991	763
145°	1143	1154	1143	1154	1143	716
155°	1259	1257	1259	1257	1259	580
165°	1328	1325	1328	1325	1328	375
175°	1359	1354	1359	1354	1359	129
180°	1359	1359	1359	1359	1359	

TEST NUMBER: P1032176

CATALOG NUMBER: S123RDIW-B340D1030UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3
2.5°	526.6	530.2	532.9	534.7	539.2	541.9	544.2	548.2	548.2	549.1	550.9
5°	524.8	532.5	537.9	545.1	554.5	559.0	565.3	570.7	578.4	582.4	586.5
7.5°	520.8	531.6	542.8	553.6	567.6	576.6	582.9	596.8	606.7	618.8	628.3
10°	515.4	530.2	544.6	561.3	580.2	593.6	603.1	621.5	640.4	657.5	671.9
12.5°	508.6	526.6	547.3	567.6	594.1	607.6	622.9	645.8	672.8	694.4	713.7
15°	501.5	522.1	545.5	570.3	603.5	622.4	644.5	672.4	702.5	733.5	760.1
17.5°	490.2	516.3	542.4	578.4	617.5	628.7	647.6	685.8	723.2	751.1	783.4
20°	479.0	508.2	541.0	573.4	615.7	641.8	659.3	699.8	739.8	773.5	804.6
22.5°	468.6	499.2	533.4	574.3	613.9	640.0	662.0	704.3	750.6	788.4	826.6
25°	456.0	489.3	527.1	565.8	613.9	633.7	658.0	707.0	756.0	799.6	846.8
27.5°	442.5	476.3	513.6	553.2	597.2	626.5	650.3	702.9	762.7	809.5	858.1
30°	429.0	463.7	499.7	535.2	584.7	612.5	640.0	698.0	766.3	819.9	857.2
32.5°	416.0	445.2	480.8	515.4	564.4	595.0	626.0	693.0	767.7	812.7	830.7
35°	398.0	428.6	457.4	494.3	543.7	573.9	610.3	692.6	761.8	789.7	780.7
37.5°	381.4	407.0	434.4	467.3	518.1	557.2	595.0	680.9	742.5	744.3	693.5
40°	362.9	384.1	407.0	441.6	496.5	535.2	576.1	662.9	707.4	680.9	591.4
42.5°	341.8	360.7	378.7	412.4	472.2	515.4	559.5	640.4	656.6	595.4	502.4
45°	319.3	334.6	351.2	386.8	446.6	489.3	533.4	605.8	589.2	502.8	414.2
47.5°	295.9	309.0	325.2	357.5	419.2	462.8	504.6	556.3	514.0	421.4	347.2
50°	272.5	282.9	298.6	331.9	391.3	430.8	469.5	503.3	443.9	361.6	286.9
52.5°	249.6	257.7	273.9	302.2	359.8	397.6	425.4	438.5	378.2	298.6	249.2
55°	225.3	234.3	245.1	273.9	331.0	358.9	377.3	376.9	314.8	253.2	206.0
57.5°	201.9	210.0	219.5	248.3	294.6	313.5	329.2	321.6	262.6	207.3	176.7
60°	181.2	185.7	196.1	220.4	255.4	271.6	280.6	267.6	214.5	174.9	146.2
62.5°	158.8	163.3	171.8	194.7	216.3	224.9	232.5	215.9	177.2	142.6	125.0
65°	138.1	143.9	149.3	167.8	179.4	189.8	188.9	174.9	138.5	116.0	101.6
67.5°	120.1	122.3	126.8	138.1	143.5	151.1	151.6	135.8	111.5	94.4	85.9
70°	100.7	103.0	106.1	111.5	115.1	116.9	116.0	102.1	84.1	73.8	66.1
72.5°	84.1	83.7	85.9	85.9	89.5	89.0	86.3	75.6	63.9	55.3	50.8
75°	66.1	66.6	67.0	66.1	64.8	63.0	60.7	52.6	45.0	40.9	36.9
77.5°	51.7	50.8	51.3	48.1	46.3	44.5	41.4	37.3	31.0	30.1	28.3
80°	36.9	36.4	36.0	34.6	30.6	28.8	26.5	24.3	22.9	22.0	21.6
82.5°	24.7	24.7	23.8	21.1	18.9	17.5	17.1	16.2	14.8	14.8	14.4
85°	14.8	14.4	13.5	10.8	9.4	9.4	9.4	9.4	8.5	8.5	8.1
87.5°	5.8	5.4	4.0	4.0	3.6	3.6	3.6	3.1	3.1	2.7	2.7
90°	1.0	3.2	5.5	7.7	10.0	11.1	12.6	15.5	18.4	21.3	24.2
92.5°	23.2	21.9	20.5	19.2	17.9	17.2	18.2	20.2	22.3	24.3	26.3
95°	61.6	52.4	43.2	34.0	24.8	20.2	21.4	23.9	26.4	28.8	31.3
97.5°	112.1	105.8	99.5	93.2	86.9	83.8	78.1	66.6	55.2	43.7	32.3
100°	170.7	175.2	179.7	184.2	188.7	190.9	173.4	138.4	103.3	68.3	33.3
102.5°	237.3	240.2	243.2	246.1	249.0	250.5	231.0	191.9	152.8	113.8	74.7
105°	301.0	303.5	305.9	308.4	310.9	312.1	302.0	281.8	261.6	241.4	221.2
107.5°	368.6	370.6	372.6	374.7	376.7	377.7	379.4	382.8	386.1	389.5	392.9
110°	436.3	438.1	439.9	441.7	443.5	444.4	445.6	448.1	450.6	453.0	455.5

TEST NUMBER: P1032176

CATALOG NUMBER: S123RDIW-B340D1030UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	500.9	502.5	504.1	505.6	507.2	508.0	509.2	511.7	514.2	516.6	519.1
115°	564.6	565.9	567.3	568.6	569.9	570.6	571.6	573.6	575.7	577.7	579.7
117.5°	627.2	628.8	630.4	631.9	633.5	634.3	634.9	636.0	637.1	638.2	639.3
120°	684.8	686.8	688.8	690.8	692.8	693.8	694.1	694.8	695.5	696.2	696.9
122.5°	743.3	744.9	746.5	748.0	749.6	750.4	750.8	751.7	752.6	753.5	754.4
125°	795.9	797.7	799.5	801.2	803.0	803.9	804.4	805.3	806.2	807.1	808.0
127.5°	848.4	850.2	852.0	853.8	855.6	856.5	857.1	858.2	859.3	860.4	861.5
130°	896.8	898.6	900.4	902.2	904.0	904.9	905.4	906.3	907.2	908.1	909.0
132.5°	943.3	945.1	946.9	948.7	950.5	951.4	951.7	952.4	953.1	953.7	954.4
135°	990.8	992.1	993.5	994.8	996.1	996.8	997.3	998.2	999.1	1000.0	1000.9
137.5°	1031.2	1033.0	1034.8	1036.6	1038.4	1039.3	1039.5	1040.0	1040.4	1040.9	1041.3
140°	1071.6	1072.9	1074.3	1075.6	1076.9	1077.6	1077.9	1078.6	1079.3	1080.0	1080.7
142.5°	1108.9	1110.3	1111.6	1113.0	1114.3	1115.0	1115.3	1116.0	1116.7	1117.3	1118.0
145°	1143.3	1144.9	1146.5	1148.0	1149.6	1150.4	1150.6	1151.1	1151.5	1152.0	1152.4
147.5°	1176.6	1177.7	1178.9	1180.0	1181.1	1181.7	1181.9	1182.4	1182.8	1183.3	1183.7
150°	1206.9	1207.6	1208.2	1208.9	1209.6	1209.9	1210.1	1210.6	1211.1	1211.5	1212.0
152.5°	1234.2	1234.4	1234.6	1234.9	1235.1	1235.2	1235.3	1235.5	1235.8	1236.0	1236.2
155°	1259.4	1259.0	1258.5	1258.1	1257.6	1257.4	1257.5	1257.7	1258.0	1258.2	1258.4
157.5°	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.5	1279.3	1279.0	1278.8	1278.6
160°	1297.8	1297.6	1297.4	1297.1	1296.9	1296.8	1296.7	1296.5	1296.2	1296.0	1295.8
162.5°	1315.0	1314.3	1313.6	1312.9	1312.2	1311.9	1311.8	1311.6	1311.3	1311.1	1310.9
165°	1328.1	1327.4	1326.8	1326.1	1325.4	1325.1	1325.0	1324.8	1324.5	1324.3	1324.1
167.5°	1339.2	1338.3	1337.4	1336.5	1335.6	1335.2	1335.2	1335.2	1335.2	1335.2	1335.2
170°	1348.3	1347.4	1346.5	1345.6	1344.7	1344.3	1344.3	1344.3	1344.3	1344.3	1344.3
172.5°	1354.4	1353.3	1352.1	1351.0	1349.9	1349.3	1349.4	1349.6	1349.9	1350.1	1350.3
175°	1359.4	1358.3	1357.2	1356.1	1355.0	1354.4	1354.5	1354.7	1355.0	1355.2	1355.4
177.5°	1361.4	1360.3	1359.2	1358.1	1357.0	1356.4	1356.5	1356.7	1357.0	1357.2	1357.4
180°	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4

TEST NUMBER: P1032176

CATALOG NUMBER: S123RDIW-B340D1030UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3
2.5°	554.5	554.5	558.6	562.6	560.4	561.7	566.7	564.9	568.5	568.0	569.4
5°	596.3	601.3	605.3	613.9	615.2	613.9	622.4	624.7	628.7	623.8	626.0
7.5°	643.6	653.9	663.8	676.4	680.4	681.3	685.8	692.1	697.5	687.6	692.6
10°	689.4	705.2	725.4	736.7	746.6	750.2	753.8	757.8	764.1	769.9	765.4
12.5°	738.9	761.8	781.2	801.4	813.6	812.2	822.6	825.3	830.2	831.6	833.4
15°	779.4	811.8	823.9	854.0	856.7	865.7	877.4	887.8	889.1	886.4	886.4
17.5°	818.1	846.0	867.5	891.8	896.8	904.4	919.3	924.2	926.0	925.6	925.6
20°	849.5	868.0	904.4	924.7	932.7	942.6	953.0	959.3	960.6	962.4	959.7
22.5°	870.2	898.1	927.8	944.4	951.2	954.8	961.5	963.3	961.1	961.5	962.0
25°	886.4	913.9	931.8	936.3	935.9	931.4	926.5	917.9	917.0	913.4	906.2
27.5°	890.9	901.3	899.0	880.6	862.1	860.3	830.7	814.5	796.0	798.7	788.4
30°	866.6	853.1	821.2	774.4	755.1	723.6	690.3	655.7	642.2	627.4	654.8
32.5°	807.3	759.2	702.5	641.8	609.4	581.5	546.0	520.8	506.4	494.3	517.6
35°	717.8	642.7	567.6	510.0	483.5	458.3	425.0	412.4	394.4	396.2	398.5
37.5°	602.6	519.9	463.2	406.6	389.0	378.7	354.4	335.1	328.8	327.0	327.0
40°	494.7	426.8	376.4	331.9	318.4	309.9	290.5	281.5	274.8	273.0	275.2
42.5°	409.3	351.2	312.1	282.4	273.0	262.2	254.1	242.9	241.5	238.4	242.4
45°	343.6	293.2	264.0	242.4	234.3	230.3	221.3	214.5	211.8	211.4	214.5
47.5°	291.4	252.3	226.7	213.2	206.9	202.8	195.2	192.5	189.8	190.7	189.3
50°	244.7	215.4	198.8	186.6	182.6	178.5	173.6	170.9	169.5	169.5	169.1
52.5°	210.0	185.7	174.9	163.7	161.9	159.7	154.3	152.5	150.2	149.8	151.6
55°	179.9	163.3	152.5	145.7	143.9	139.4	137.2	134.9	133.6	132.7	133.1
57.5°	153.8	141.2	134.0	128.2	125.0	123.2	119.2	118.7	117.8	117.8	117.4
60°	132.2	123.2	114.7	111.1	108.8	106.6	106.1	103.4	102.1	103.0	102.5
62.5°	112.0	104.8	99.8	95.8	94.4	92.6	91.3	90.4	89.0	89.5	89.5
65°	93.5	87.7	84.1	80.5	80.1	78.3	77.8	76.9	76.9	76.5	77.4
67.5°	76.9	72.9	69.7	67.5	66.1	66.6	64.8	63.4	63.4	63.0	64.3
70°	61.2	58.9	55.8	53.1	51.3	51.3	49.0	48.6	48.6	48.6	48.1
72.5°	47.2	43.2	41.8	40.9	40.9	40.9	40.0	40.0	39.6	40.0	39.6
75°	35.1	34.6	33.7	33.3	33.3	32.8	32.4	32.4	32.4	32.4	32.4
77.5°	27.4	27.4	26.5	26.1	26.1	26.1	25.6	25.6	25.2	25.2	25.2
80°	20.2	20.2	19.3	19.3	19.3	18.9	18.9	18.9	19.3	18.9	18.9
82.5°	13.9	13.9	13.5	13.9	13.5	13.0	13.0	13.0	12.6	13.0	13.0
85°	8.1	8.1	7.6	7.2	7.6	7.6	7.2	7.6	7.2	7.6	7.2
87.5°	3.1	2.7	2.7	2.7	2.2	2.7	2.2	2.2	2.7	2.2	2.7
90°	25.1	26.0	26.9	27.8	28.3	28.5	29.0	29.4	29.9	30.3	29.9
92.5°	27.9	29.4	31.0	32.5	33.3	33.4	33.6	33.9	34.1	34.3	34.1
95°	32.9	34.5	36.0	37.6	38.4	38.4	38.4	38.4	38.4	38.4	38.4
97.5°	34.1	35.9	37.7	39.5	40.4	40.5	40.7	41.0	41.2	41.4	41.2
100°	35.1	36.9	38.7	40.5	41.4	41.5	41.7	42.0	42.2	42.4	42.2
102.5°	67.3	59.9	52.5	45.1	41.4	41.6	42.1	42.5	43.0	43.4	43.0
105°	181.5	141.7	102.0	62.3	42.4	42.6	43.1	43.5	44.0	44.4	44.0
107.5°	358.3	323.7	289.2	254.6	237.3	222.6	193.2	163.8	134.4	105.0	134.4
110°	448.1	440.7	433.3	425.9	422.2	406.1	374.0	341.9	309.8	277.7	309.8

TEST NUMBER: P1032176

CATALOG NUMBER: S123RDIW-B340D1030UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	521.1	523.1	525.2	527.2	528.2	528.0	527.5	527.1	526.6	526.2	526.6
115°	581.9	584.2	586.4	588.7	589.8	590.3	591.2	592.1	593.0	593.9	593.0
117.5°	641.1	642.9	644.7	646.5	647.4	647.5	647.7	648.0	648.2	648.4	648.2
120°	698.7	700.5	702.3	704.1	705.0	705.0	705.0	705.0	705.0	705.0	705.0
122.5°	755.5	756.7	757.8	758.9	759.5	759.6	759.8	760.1	760.3	760.5	760.3
125°	808.4	808.9	809.3	809.8	810.0	810.2	810.7	811.1	811.6	812.0	811.6
127.5°	862.2	862.8	863.5	864.2	864.5	864.3	863.8	863.4	862.9	862.5	862.9
130°	909.9	910.8	911.7	912.6	913.0	912.8	912.3	911.9	911.4	911.0	911.4
132.5°	955.3	956.2	957.1	958.0	958.5	958.2	957.5	956.8	956.1	955.4	956.1
135°	1001.6	1002.2	1002.9	1003.6	1003.9	1003.6	1002.9	1002.2	1001.6	1000.9	1001.6
137.5°	1042.4	1043.5	1044.6	1045.7	1046.3	1046.1	1045.6	1045.2	1044.7	1044.3	1044.7
140°	1081.6	1082.5	1083.4	1084.3	1084.7	1084.5	1084.0	1083.6	1083.1	1082.7	1083.1
142.5°	1118.7	1119.4	1120.1	1120.8	1121.1	1120.8	1120.1	1119.4	1118.7	1118.0	1118.7
145°	1152.8	1153.3	1153.7	1154.2	1154.4	1154.4	1154.4	1154.4	1154.4	1154.4	1154.4
147.5°	1184.1	1184.6	1185.0	1185.5	1185.7	1185.1	1184.0	1182.9	1181.7	1180.6	1181.7
150°	1212.4	1212.9	1213.3	1213.8	1214.0	1213.7	1213.0	1212.3	1211.6	1210.9	1211.6
152.5°	1237.1	1238.0	1238.9	1239.8	1240.2	1239.6	1238.5	1237.4	1236.3	1235.2	1236.3
155°	1259.5	1260.7	1261.8	1262.9	1263.5	1262.8	1261.5	1260.1	1258.8	1257.4	1258.8
157.5°	1280.0	1281.3	1282.7	1284.0	1284.7	1283.8	1282.0	1280.2	1278.4	1276.6	1278.4
160°	1297.1	1298.5	1299.8	1301.1	1301.8	1301.0	1299.5	1297.9	1296.4	1294.8	1296.4
162.5°	1312.5	1314.1	1315.6	1317.2	1318.0	1317.3	1316.0	1314.6	1313.3	1311.9	1313.3
165°	1325.9	1327.7	1329.4	1331.2	1332.1	1331.3	1329.8	1328.2	1326.7	1325.1	1326.7
167.5°	1337.0	1338.8	1340.6	1342.4	1343.3	1342.4	1340.6	1338.8	1337.0	1335.2	1337.0
170°	1346.1	1347.9	1349.6	1351.4	1352.3	1351.4	1349.6	1347.9	1346.1	1344.3	1346.1
172.5°	1352.1	1353.9	1355.7	1357.5	1358.4	1357.4	1355.4	1353.3	1351.3	1349.3	1351.3
175°	1357.0	1358.5	1360.1	1361.6	1362.4	1361.5	1359.7	1358.0	1356.2	1354.4	1356.2
177.5°	1359.2	1361.0	1362.8	1364.6	1365.5	1364.4	1362.1	1359.9	1357.6	1355.4	1357.6
180°	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4

TEST NUMBER: P1032176

CATALOG NUMBER: S123RDIW-B340D1030UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3
2.5°	567.1	564.4	562.6	561.3	559.9	564.0	558.6	552.7	548.7	546.0	545.1
5°	626.5	620.6	615.7	611.6	612.5	612.5	603.1	592.7	583.8	578.8	573.4
7.5°	695.3	689.0	679.1	676.8	675.1	663.8	654.4	635.5	624.2	613.0	603.1
10°	763.6	755.6	746.1	743.0	738.5	724.5	710.1	685.8	671.9	651.2	638.2
12.5°	827.5	817.6	808.2	805.9	799.2	787.0	762.3	737.1	713.3	691.2	668.3
15°	881.0	878.3	863.9	854.9	840.1	823.5	818.1	783.9	753.8	730.8	689.4
17.5°	926.0	913.4	899.9	894.1	888.2	868.9	849.5	814.5	782.1	748.4	721.8
20°	962.0	948.0	938.6	930.1	927.4	905.3	874.7	843.7	808.2	770.4	735.8
22.5°	963.8	962.0	955.7	950.7	945.3	930.9	906.7	868.0	830.2	788.8	743.4
25°	926.5	923.8	941.7	937.2	940.8	935.4	922.4	890.0	846.0	797.4	751.5
27.5°	814.0	841.5	869.8	879.7	886.4	905.8	912.1	894.1	858.5	806.8	755.6
30°	661.1	697.5	743.4	768.1	787.0	823.0	869.8	875.6	859.0	817.6	754.7
32.5°	519.0	552.3	589.2	618.4	643.6	717.3	780.3	825.7	833.8	812.2	756.9
35°	418.3	432.6	467.7	495.6	529.8	592.7	667.0	740.3	789.7	792.4	750.2
37.5°	344.9	352.6	383.2	398.9	419.2	474.5	543.7	639.5	716.4	752.9	731.3
40°	285.6	303.1	320.7	329.7	344.0	382.3	448.8	523.9	619.3	686.7	702.0
42.5°	247.8	255.4	266.7	279.3	288.3	321.6	366.1	434.9	520.8	614.8	657.1
45°	218.6	221.3	233.0	241.1	250.5	273.9	305.4	362.9	438.5	531.1	603.1
47.5°	194.3	199.7	206.0	210.9	217.2	235.2	262.2	304.0	370.6	453.3	530.7
50°	172.7	175.8	183.9	186.2	190.7	203.3	224.0	255.9	310.8	376.9	456.9
52.5°	152.5	158.3	161.5	164.6	168.7	179.0	192.5	218.6	259.9	322.0	389.9
55°	136.7	138.5	143.0	145.7	148.9	156.1	167.8	187.1	219.5	268.9	333.3
57.5°	121.4	121.4	125.9	128.2	131.3	136.7	147.1	161.9	185.3	222.2	281.1
60°	105.2	105.7	109.3	112.0	112.9	118.3	126.8	138.5	156.5	183.5	231.6
62.5°	90.8	93.1	94.9	95.8	98.9	102.1	109.3	117.4	130.0	153.8	188.0
65°	78.7	79.2	80.5	81.4	82.8	86.3	91.7	97.1	107.9	125.5	153.4
67.5°	64.8	66.6	68.4	68.4	69.7	71.5	76.9	81.4	89.5	99.8	118.7
70°	48.6	49.5	52.2	53.5	55.3	58.5	61.2	63.9	70.2	77.8	92.2
72.5°	40.5	40.5	41.4	41.8	41.8	44.1	48.1	50.8	54.0	59.4	69.3
75°	32.4	32.4	33.7	33.3	34.2	35.1	35.5	37.3	39.1	43.2	49.0
77.5°	25.6	26.1	26.1	26.5	26.5	27.0	27.4	28.3	29.2	31.5	34.2
80°	18.9	19.3	19.3	19.8	19.8	20.2	20.7	21.1	22.0	22.9	24.3
82.5°	13.0	13.5	13.5	13.9	13.5	13.9	14.4	14.4	14.8	15.7	16.2
85°	7.6	7.6	8.1	7.6	7.6	7.6	8.1	8.1	8.5	9.9	9.9
87.5°	2.2	2.7	2.2	2.7	2.7	2.7	2.7	3.1	3.1	3.6	4.0
90°	29.4	29.0	28.5	28.3	27.8	26.9	26.0	25.1	24.2	21.3	18.4
92.5°	33.9	33.6	33.4	33.3	32.5	31.0	29.4	27.9	26.3	24.3	22.3
95°	38.4	38.4	38.4	38.4	37.6	36.0	34.5	32.9	31.3	28.8	26.4
97.5°	41.0	40.7	40.5	40.4	39.5	37.7	35.9	34.1	32.3	43.7	55.2
100°	42.0	41.7	41.5	41.4	40.5	38.7	36.9	35.1	33.3	68.3	103.3
102.5°	42.5	42.1	41.6	41.4	45.1	52.5	59.9	67.3	74.7	113.8	152.8
105°	43.5	43.1	42.6	42.4	62.3	102.0	141.7	181.5	221.2	241.4	261.6
107.5°	163.8	193.2	222.6	237.3	254.6	289.2	323.7	358.3	392.9	389.5	386.1
110°	341.9	374.0	406.1	422.2	425.9	433.3	440.7	448.1	455.5	453.0	450.6

TEST NUMBER: P1032176

CATALOG NUMBER: S123RDIW-B340D1030UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	527.1	527.5	528.0	528.2	527.2	525.2	523.1	521.1	519.1	516.6	514.2
115°	592.1	591.2	590.3	589.8	588.7	586.4	584.2	581.9	579.7	577.7	575.7
117.5°	648.0	647.7	647.5	647.4	646.5	644.7	642.9	641.1	639.3	638.2	637.1
120°	705.0	705.0	705.0	705.0	704.1	702.3	700.5	698.7	696.9	696.2	695.5
122.5°	760.1	759.8	759.6	759.5	758.9	757.8	756.7	755.5	754.4	753.5	752.6
125°	811.1	810.7	810.2	810.0	809.8	809.3	808.9	808.4	808.0	807.1	806.2
127.5°	863.4	863.8	864.3	864.5	864.2	863.5	862.8	862.2	861.5	860.4	859.3
130°	911.9	912.3	912.8	913.0	912.6	911.7	910.8	909.9	909.0	908.1	907.2
132.5°	956.8	957.5	958.2	958.5	958.0	957.1	956.2	955.3	954.4	953.7	953.1
135°	1002.2	1002.9	1003.6	1003.9	1003.6	1002.9	1002.2	1001.6	1000.9	1000.0	999.1
137.5°	1045.2	1045.6	1046.1	1046.3	1045.7	1044.6	1043.5	1042.4	1041.3	1040.9	1040.4
140°	1083.6	1084.0	1084.5	1084.7	1084.3	1083.4	1082.5	1081.6	1080.7	1080.0	1079.3
142.5°	1119.4	1120.1	1120.8	1121.1	1120.8	1120.1	1119.4	1118.7	1118.0	1117.3	1116.7
145°	1154.4	1154.4	1154.4	1154.4	1154.2	1153.7	1153.3	1152.8	1152.4	1152.0	1151.5
147.5°	1182.9	1184.0	1185.1	1185.7	1185.5	1185.0	1184.6	1184.1	1183.7	1183.3	1182.8
150°	1212.3	1213.0	1213.7	1214.0	1213.8	1213.3	1212.9	1212.4	1212.0	1211.5	1211.1
152.5°	1237.4	1238.5	1239.6	1240.2	1239.8	1238.9	1238.0	1237.1	1236.2	1236.0	1235.8
155°	1260.1	1261.5	1262.8	1263.5	1262.9	1261.8	1260.7	1259.5	1258.4	1258.2	1258.0
157.5°	1280.2	1282.0	1283.8	1284.7	1284.0	1282.7	1281.3	1280.0	1278.6	1278.8	1279.0
160°	1297.9	1299.5	1301.0	1301.8	1301.1	1299.8	1298.5	1297.1	1295.8	1296.0	1296.2
162.5°	1314.6	1316.0	1317.3	1318.0	1317.2	1315.6	1314.1	1312.5	1310.9	1311.1	1311.3
165°	1328.2	1329.8	1331.3	1332.1	1331.2	1329.4	1327.7	1325.9	1324.1	1324.3	1324.5
167.5°	1338.8	1340.6	1342.4	1343.3	1342.4	1340.6	1338.8	1337.0	1335.2	1335.2	1335.2
170°	1347.9	1349.6	1351.4	1352.3	1351.4	1349.6	1347.9	1346.1	1344.3	1344.3	1344.3
172.5°	1353.3	1355.4	1357.4	1358.4	1357.5	1355.7	1353.9	1352.1	1350.3	1350.1	1349.9
175°	1358.0	1359.7	1361.5	1362.4	1361.6	1360.1	1358.5	1357.0	1355.4	1355.2	1355.0
177.5°	1359.9	1362.1	1364.4	1365.5	1364.6	1362.8	1361.0	1359.2	1357.4	1357.2	1357.0
180°	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4

TEST NUMBER: P1032176

CATALOG NUMBER: S123RDIW-B340D1030UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3
2.5°	543.7	541.5	539.2	539.2	534.3	529.8	527.5	528.4	525.7	522.1	518.5
5°	567.6	558.6	556.8	551.8	545.1	535.6	530.7	526.2	520.8	513.6	506.9
7.5°	589.6	577.9	571.6	566.7	553.6	540.6	529.8	522.6	513.1	502.4	494.3
10°	618.4	596.8	590.1	578.8	560.4	541.9	529.3	517.6	504.6	492.0	481.2
12.5°	641.3	616.6	604.0	592.7	568.9	545.5	524.4	510.0	494.3	480.3	466.4
15°	667.4	639.5	617.5	604.0	573.9	545.5	521.7	501.5	483.9	466.8	454.7
17.5°	680.0	644.9	635.0	615.7	572.1	543.7	514.5	492.9	471.8	452.0	437.6
20°	699.8	658.9	634.1	621.1	582.4	540.6	506.4	481.7	459.6	438.5	423.2
22.5°	701.1	656.6	640.4	615.7	568.0	531.1	499.2	469.1	443.4	423.6	407.9
25°	698.0	652.6	630.1	610.3	570.7	525.7	484.8	455.1	429.9	407.0	388.6
27.5°	696.6	640.9	619.7	599.9	555.4	510.0	476.3	442.5	413.8	393.5	374.6
30°	694.8	628.3	602.6	579.7	538.8	497.9	457.4	428.1	400.7	375.1	356.2
32.5°	683.1	611.2	585.1	560.8	516.7	475.8	443.9	412.9	383.2	359.3	342.2
35°	679.5	595.4	561.3	535.2	492.0	455.6	421.9	396.2	368.3	344.5	324.3
37.5°	669.2	579.3	542.4	509.1	464.1	429.5	404.8	379.1	352.1	326.5	310.3
40°	651.2	560.4	518.5	484.4	438.0	403.0	380.0	361.1	334.6	311.7	291.9
42.5°	624.7	541.0	496.1	460.1	408.8	376.0	357.1	339.1	316.6	292.8	276.6
45°	594.1	515.4	473.6	433.5	381.4	349.4	329.7	318.9	298.2	277.9	259.0
47.5°	552.3	488.9	447.5	406.1	353.0	322.0	306.3	295.5	281.1	259.0	243.8
50°	499.7	454.7	415.6	378.7	325.2	295.5	279.7	271.6	259.5	243.8	228.9
52.5°	441.2	415.1	382.7	348.5	296.8	268.9	254.5	248.3	239.3	224.4	211.8
55°	382.3	371.0	349.0	315.3	267.1	244.2	231.6	223.5	216.8	206.0	195.2
57.5°	329.7	324.3	309.0	282.9	242.4	218.6	207.8	202.4	197.0	188.9	178.1
60°	275.2	281.1	265.3	252.3	215.4	194.7	185.3	179.4	176.7	169.5	162.8
62.5°	228.0	233.4	224.4	214.5	188.4	170.0	164.2	158.8	157.0	150.7	143.9
65°	185.3	192.0	185.3	179.9	164.2	148.9	141.7	139.0	137.2	133.1	127.7
67.5°	147.5	154.3	151.1	144.4	139.4	126.8	122.8	120.1	119.2	116.0	111.5
70°	111.1	120.5	121.4	117.4	112.9	107.0	104.3	103.4	101.2	98.5	95.8
72.5°	80.1	90.8	91.3	91.3	88.6	88.6	85.9	84.6	84.6	81.9	78.7
75°	58.9	66.1	67.0	67.9	69.3	70.6	68.8	68.8	68.4	65.7	64.3
77.5°	39.1	45.4	47.7	50.8	52.6	52.6	53.5	54.4	53.5	52.2	51.3
80°	25.2	29.7	32.4	34.2	36.9	38.2	39.6	40.0	39.1	38.7	37.3
82.5°	16.6	18.0	19.3	21.6	24.7	27.0	27.0	26.5	27.4	27.0	26.5
85°	9.4	10.3	10.8	11.2	13.0	15.3	15.7	16.2	17.1	16.2	15.3
87.5°	3.6	4.0	4.0	4.0	4.9	5.4	6.7	8.5	8.1	7.2	7.2
90°	15.5	12.6	11.1	10.0	7.7	5.5	3.2	1.0	3.2	5.5	7.7
92.5°	20.2	18.2	17.2	17.9	19.2	20.5	21.9	23.2	21.9	20.5	19.2
95°	23.9	21.4	20.2	24.8	34.0	43.2	52.4	61.6	52.4	43.2	34.0
97.5°	66.6	78.1	83.8	86.9	93.2	99.5	105.8	112.1	105.8	99.5	93.2
100°	138.4	173.4	190.9	188.7	184.2	179.7	175.2	170.7	175.2	179.7	184.2
102.5°	191.9	231.0	250.5	249.0	246.1	243.2	240.2	237.3	240.2	243.2	246.1
105°	281.8	302.0	312.1	310.9	308.4	305.9	303.5	301.0	303.5	305.9	308.4
107.5°	382.8	379.4	377.7	376.7	374.7	372.6	370.6	368.6	370.6	372.6	374.7
110°	448.1	445.6	444.4	443.5	441.7	439.9	438.1	436.3	438.1	439.9	441.7

TEST NUMBER: P1032176

CATALOG NUMBER: S123RDIW-B340D1030UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	511.7	509.2	508.0	507.2	505.6	504.1	502.5	500.9	502.5	504.1	505.6
115°	573.6	571.6	570.6	569.9	568.6	567.3	565.9	564.6	565.9	567.3	568.6
117.5°	636.0	634.9	634.3	633.5	631.9	630.4	628.8	627.2	628.8	630.4	631.9
120°	694.8	694.1	693.8	692.8	690.8	688.8	686.8	684.8	686.8	688.8	690.8
122.5°	751.7	750.8	750.4	749.6	748.0	746.5	744.9	743.3	744.9	746.5	748.0
125°	805.3	804.4	803.9	803.0	801.2	799.5	797.7	795.9	797.7	799.5	801.2
127.5°	858.2	857.1	856.5	855.6	853.8	852.0	850.2	848.4	850.2	852.0	853.8
130°	906.3	905.4	904.9	904.0	902.2	900.4	898.6	896.8	898.6	900.4	902.2
132.5°	952.4	951.7	951.4	950.5	948.7	946.9	945.1	943.3	945.1	946.9	948.7
135°	998.2	997.3	996.8	996.1	994.8	993.5	992.1	990.8	992.1	993.5	994.8
137.5°	1040.0	1039.5	1039.3	1038.4	1036.6	1034.8	1033.0	1031.2	1033.0	1034.8	1036.6
140°	1078.6	1077.9	1077.6	1076.9	1075.6	1074.3	1072.9	1071.6	1072.9	1074.3	1075.6
142.5°	1116.0	1115.3	1115.0	1114.3	1113.0	1111.6	1110.3	1108.9	1110.3	1111.6	1113.0
145°	1151.1	1150.6	1150.4	1149.6	1148.0	1146.5	1144.9	1143.3	1144.9	1146.5	1148.0
147.5°	1182.4	1181.9	1181.7	1181.1	1180.0	1178.9	1177.7	1176.6	1177.7	1178.9	1180.0
150°	1210.6	1210.1	1209.9	1209.6	1208.9	1208.2	1207.6	1206.9	1207.6	1208.2	1208.9
152.5°	1235.5	1235.3	1235.2	1235.1	1234.9	1234.6	1234.4	1234.2	1234.4	1234.6	1234.9
155°	1257.7	1257.5	1257.4	1257.6	1258.1	1258.5	1259.0	1259.4	1259.0	1258.5	1258.1
157.5°	1279.3	1279.5	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6
160°	1296.5	1296.7	1296.8	1296.9	1297.1	1297.4	1297.6	1297.8	1297.6	1297.4	1297.1
162.5°	1311.6	1311.8	1311.9	1312.2	1312.9	1313.6	1314.3	1315.0	1314.3	1313.6	1312.9
165°	1324.8	1325.0	1325.1	1325.4	1326.1	1326.8	1327.4	1328.1	1327.4	1326.8	1326.1
167.5°	1335.2	1335.2	1335.2	1335.6	1336.5	1337.4	1338.3	1339.2	1338.3	1337.4	1336.5
170°	1344.3	1344.3	1344.3	1344.7	1345.6	1346.5	1347.4	1348.3	1347.4	1346.5	1345.6
172.5°	1349.6	1349.4	1349.3	1349.9	1351.0	1352.1	1353.3	1354.4	1353.3	1352.1	1351.0
175°	1354.7	1354.5	1354.4	1355.0	1356.1	1357.2	1358.3	1359.4	1358.3	1357.2	1356.1
177.5°	1356.7	1356.5	1356.4	1357.0	1358.1	1359.2	1360.3	1361.4	1360.3	1359.2	1358.1
180°	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4

TEST NUMBER: P1032176

CATALOG NUMBER: S123RDIW-B340D1030UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3
2.5°	518.5	516.3	515.4	513.1	507.7	504.2	500.1	497.4	497.9	495.6	497.0
5°	502.4	501.9	498.8	494.3	486.6	482.6	475.4	471.8	470.0	470.4	467.7
7.5°	488.9	484.8	482.6	475.4	468.2	459.6	453.8	450.6	447.9	445.2	443.4
10°	473.6	470.0	466.4	458.7	448.8	440.7	432.6	429.5	425.4	423.6	422.3
12.5°	457.4	455.1	450.6	441.6	430.4	422.8	413.3	411.5	406.1	402.5	401.6
15°	442.5	441.2	433.1	422.8	411.5	403.9	395.8	390.4	381.4	383.2	380.0
17.5°	426.8	421.0	416.0	402.1	396.7	385.0	375.5	372.8	366.5	362.5	358.4
20°	409.3	405.7	399.4	390.4	377.3	363.8	356.6	352.1	348.5	342.2	340.4
22.5°	392.6	388.1	382.7	371.0	359.8	348.5	338.6	334.6	330.1	325.6	322.9
25°	379.6	372.8	367.0	352.6	341.3	331.9	325.6	318.9	312.6	309.9	309.0
27.5°	359.3	355.3	349.4	336.0	325.6	315.3	309.4	304.9	298.2	295.0	292.3
30°	346.3	338.2	331.5	320.7	310.3	299.1	293.7	288.3	284.2	280.2	277.0
32.5°	328.8	322.5	317.1	306.3	295.9	285.6	279.7	271.6	269.4	266.2	262.6
35°	311.7	307.6	301.8	290.1	278.8	271.6	265.3	257.7	255.0	252.8	249.6
37.5°	295.5	289.6	285.6	274.3	264.4	255.9	251.0	244.7	242.9	240.2	237.9
40°	281.5	275.7	271.6	260.4	250.1	241.1	237.9	231.6	228.9	225.8	224.4
42.5°	265.8	260.8	255.4	247.4	236.6	227.6	221.3	217.7	214.1	212.7	210.0
45°	249.2	244.7	240.6	231.6	220.4	214.1	208.7	203.7	201.0	198.8	197.0
47.5°	234.8	230.7	225.3	215.4	206.4	200.6	195.2	190.2	187.5	184.8	182.6
50°	218.1	215.9	210.0	200.6	192.0	185.3	180.3	175.8	174.0	170.9	167.3
52.5°	203.3	199.2	194.3	186.6	179.0	170.9	164.2	161.5	158.3	156.5	153.4
55°	185.7	183.0	177.6	170.9	162.8	156.1	151.1	147.5	143.5	141.7	137.6
57.5°	170.9	166.0	163.3	154.7	147.1	140.3	136.7	133.1	128.6	125.9	124.1
60°	154.7	150.2	146.2	139.0	133.6	126.4	121.0	117.8	114.7	111.1	109.3
62.5°	139.0	135.4	130.4	124.6	117.8	112.0	107.9	103.4	101.6	98.0	96.7
65°	121.9	119.2	115.1	108.4	103.0	98.0	94.0	90.4	88.6	87.2	86.3
67.5°	106.6	103.0	100.3	94.4	88.6	84.6	82.3	80.1	77.8	76.5	75.1
70°	90.8	88.1	85.4	80.1	76.0	72.4	70.6	68.8	67.5	66.1	64.8
72.5°	74.7	73.3	70.6	67.0	63.9	61.2	59.8	57.6	56.2	54.0	53.1
75°	61.6	59.4	58.0	54.9	52.2	49.9	48.1	45.4	43.6	42.7	42.3
77.5°	48.6	47.7	45.9	43.2	41.8	39.6	36.9	36.0	35.1	35.1	34.6
80°	36.4	35.1	33.7	31.5	30.1	28.3	28.3	28.3	27.9	28.3	27.9
82.5°	24.7	23.8	22.9	21.6	21.1	21.1	21.6	21.6	21.6	21.6	21.6
85°	14.4	14.4	14.4	14.8	14.4	14.4	14.8	15.3	14.8	14.8	14.4
87.5°	6.7	6.7	7.2	7.2	7.6	7.6	7.6	7.6	7.6	7.6	8.1
90°	10.0	11.1	12.6	15.5	18.4	21.3	24.2	25.1	26.0	26.9	27.8
92.5°	17.9	17.2	18.2	20.2	22.3	24.3	26.3	27.9	29.4	31.0	32.5
95°	24.8	20.2	21.4	23.9	26.4	28.8	31.3	32.9	34.5	36.0	37.6
97.5°	86.9	83.8	78.1	66.6	55.2	43.7	32.3	34.1	35.9	37.7	39.5
100°	188.7	190.9	173.4	138.4	103.3	68.3	33.3	35.1	36.9	38.7	40.5
102.5°	249.0	250.5	231.0	191.9	152.8	113.8	74.7	67.3	59.9	52.5	45.1
105°	310.9	312.1	302.0	281.8	261.6	241.4	221.2	181.5	141.7	102.0	62.3
107.5°	376.7	377.7	379.4	382.8	386.1	389.5	392.9	358.3	323.7	289.2	254.6
110°	443.5	444.4	445.6	448.1	450.6	453.0	455.5	448.1	440.7	433.3	425.9

TEST NUMBER: P1032176

CATALOG NUMBER: S123RDIW-B340D1030UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	507.2	508.0	509.2	511.7	514.2	516.6	519.1	521.1	523.1	525.2	527.2
115°	569.9	570.6	571.6	573.6	575.7	577.7	579.7	581.9	584.2	586.4	588.7
117.5°	633.5	634.3	634.9	636.0	637.1	638.2	639.3	641.1	642.9	644.7	646.5
120°	692.8	693.8	694.1	694.8	695.5	696.2	696.9	698.7	700.5	702.3	704.1
122.5°	749.6	750.4	750.8	751.7	752.6	753.5	754.4	755.5	756.7	757.8	758.9
125°	803.0	803.9	804.4	805.3	806.2	807.1	808.0	808.4	808.9	809.3	809.8
127.5°	855.6	856.5	857.1	858.2	859.3	860.4	861.5	862.2	862.8	863.5	864.2
130°	904.0	904.9	905.4	906.3	907.2	908.1	909.0	909.9	910.8	911.7	912.6
132.5°	950.5	951.4	951.7	952.4	953.1	953.7	954.4	955.3	956.2	957.1	958.0
135°	996.1	996.8	997.3	998.2	999.1	1000.0	1000.9	1001.6	1002.2	1002.9	1003.6
137.5°	1038.4	1039.3	1039.5	1040.0	1040.4	1040.9	1041.3	1042.4	1043.5	1044.6	1045.7
140°	1076.9	1077.6	1077.9	1078.6	1079.3	1080.0	1080.7	1081.6	1082.5	1083.4	1084.3
142.5°	1114.3	1115.0	1115.3	1116.0	1116.7	1117.3	1118.0	1118.7	1119.4	1120.1	1120.8
145°	1149.6	1150.4	1150.6	1151.1	1151.5	1152.0	1152.4	1152.8	1153.3	1153.7	1154.2
147.5°	1181.1	1181.7	1181.9	1182.4	1182.8	1183.3	1183.7	1184.1	1184.6	1185.0	1185.5
150°	1209.6	1209.9	1210.1	1210.6	1211.1	1211.5	1212.0	1212.4	1212.9	1213.3	1213.8
152.5°	1235.1	1235.2	1235.3	1235.5	1235.8	1236.0	1236.2	1237.1	1238.0	1238.9	1239.8
155°	1257.6	1257.4	1257.5	1257.7	1258.0	1258.2	1258.4	1259.5	1260.7	1261.8	1262.9
157.5°	1279.6	1279.6	1279.5	1279.3	1279.0	1278.8	1278.6	1280.0	1281.3	1282.7	1284.0
160°	1296.9	1296.8	1296.7	1296.5	1296.2	1296.0	1295.8	1297.1	1298.5	1299.8	1301.1
162.5°	1312.2	1311.9	1311.8	1311.6	1311.3	1311.1	1310.9	1312.5	1314.1	1315.6	1317.2
165°	1325.4	1325.1	1325.0	1324.8	1324.5	1324.3	1324.1	1325.9	1327.7	1329.4	1331.2
167.5°	1335.6	1335.2	1335.2	1335.2	1335.2	1335.2	1335.2	1337.0	1338.8	1340.6	1342.4
170°	1344.7	1344.3	1344.3	1344.3	1344.3	1344.3	1344.3	1346.1	1347.9	1349.6	1351.4
172.5°	1349.9	1349.3	1349.4	1349.6	1349.9	1350.1	1350.3	1352.1	1353.9	1355.7	1357.5
175°	1355.0	1354.4	1354.5	1354.7	1355.0	1355.2	1355.4	1357.0	1358.5	1360.1	1361.6
177.5°	1357.0	1356.4	1356.5	1356.7	1357.0	1357.2	1357.4	1359.2	1361.0	1362.8	1364.6
180°	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4

TEST NUMBER: P1032176

CATALOG NUMBER: S123RDIW-B340D1030UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3
2.5°	496.5	497.0	495.6	492.9	492.5	493.4	496.1	495.2	492.9	497.0	493.4
5°	469.1	466.8	465.9	466.8	464.1	462.8	465.5	464.1	465.5	465.9	467.3
7.5°	442.5	443.0	440.3	440.7	437.1	438.0	438.0	438.0	439.4	440.3	442.1
10°	419.6	420.5	417.4	417.8	415.1	413.3	414.7	417.4	417.4	417.4	418.3
12.5°	401.2	397.1	394.9	394.4	391.3	390.4	393.1	394.0	396.2	396.2	397.6
15°	378.2	377.3	375.5	375.5	367.9	369.7	370.6	373.7	378.2	374.6	375.5
17.5°	357.5	355.3	353.0	352.1	351.2	348.5	352.1	351.7	354.4	354.8	356.2
20°	339.1	337.3	332.8	333.3	334.2	330.1	332.4	332.4	335.1	337.8	340.9
22.5°	321.1	319.3	317.1	318.0	315.3	314.4	314.4	316.6	319.8	322.0	321.6
25°	307.2	304.0	302.7	301.3	300.0	300.9	299.5	301.8	304.0	305.4	304.0
27.5°	291.4	290.1	287.4	286.0	283.8	284.7	285.6	287.4	288.7	288.7	290.1
30°	276.1	274.3	273.4	272.1	272.1	270.3	270.7	272.5	273.9	275.2	277.0
32.5°	261.3	259.9	258.6	258.6	257.7	257.2	256.8	259.5	259.5	262.2	262.2
35°	249.2	246.9	246.9	244.7	245.6	245.1	244.2	246.0	246.5	248.3	247.8
37.5°	235.7	235.7	234.8	232.5	230.7	231.2	233.4	233.4	234.8	234.3	235.7
40°	222.2	221.3	221.3	219.9	219.5	219.0	219.5	219.9	222.2	221.7	222.2
42.5°	208.7	209.1	206.9	206.9	206.9	205.5	206.0	206.4	207.3	208.2	209.6
45°	195.6	194.7	194.3	193.4	192.5	192.9	192.5	194.3	193.8	194.7	196.1
47.5°	181.7	180.3	179.9	178.1	178.1	179.0	178.5	179.9	180.3	181.7	180.8
50°	168.2	166.4	165.1	165.5	162.8	163.7	163.7	165.1	166.4	166.9	167.8
52.5°	152.5	152.0	151.6	149.3	148.9	148.4	148.9	149.3	151.1	152.5	152.9
55°	137.2	136.7	134.0	133.1	131.8	131.8	132.7	133.1	136.3	136.7	138.5
57.5°	123.2	121.9	118.7	118.3	118.3	118.3	116.9	118.7	119.6	121.9	121.9
60°	107.9	107.9	105.2	105.2	105.7	105.2	105.2	105.7	105.7	107.5	108.4
62.5°	95.8	95.3	95.3	94.4	94.0	94.4	94.0	94.0	94.4	95.8	97.1
65°	85.0	84.6	84.1	83.7	82.8	82.8	83.2	84.1	84.1	85.0	85.4
67.5°	74.7	74.7	73.8	73.8	73.3	72.9	73.3	72.9	74.7	74.7	75.1
70°	64.3	63.9	62.5	62.1	60.7	61.2	61.2	62.5	63.0	63.9	64.8
72.5°	51.7	51.7	50.8	49.9	50.4	49.5	49.5	49.9	49.9	51.3	51.7
75°	42.7	41.8	41.4	41.8	41.4	42.3	41.4	41.4	42.3	42.3	42.3
77.5°	35.1	35.1	34.6	34.6	35.1	34.6	35.1	35.1	35.1	34.6	35.1
80°	28.8	28.3	28.3	28.3	27.9	27.9	27.9	27.9	27.9	27.9	27.9
82.5°	21.6	21.6	21.1	21.6	21.6	21.1	21.6	21.1	21.1	21.6	21.6
85°	14.4	15.3	14.4	14.4	14.8	14.8	15.3	14.8	15.3	14.4	14.8
87.5°	7.6	8.1	8.1	7.6	7.6	8.1	8.1	8.1	8.5	7.6	8.1
90°	28.3	28.5	29.0	29.4	29.9	30.3	29.9	29.4	29.0	28.5	28.3
92.5°	33.3	33.4	33.6	33.9	34.1	34.3	34.1	33.9	33.6	33.4	33.3
95°	38.4	38.4	38.4	38.4	38.4	38.4	38.4	38.4	38.4	38.4	38.4
97.5°	40.4	40.5	40.7	41.0	41.2	41.4	41.2	41.0	40.7	40.5	40.4
100°	41.4	41.5	41.7	42.0	42.2	42.4	42.2	42.0	41.7	41.5	41.4
102.5°	41.4	41.6	42.1	42.5	43.0	43.4	43.0	42.5	42.1	41.6	41.4
105°	42.4	42.6	43.1	43.5	44.0	44.4	44.0	43.5	43.1	42.6	42.4
107.5°	237.3	222.6	193.2	163.8	134.4	105.0	134.4	163.8	193.2	222.6	237.3
110°	422.2	406.1	374.0	341.9	309.8	277.7	309.8	341.9	374.0	406.1	422.2

TEST NUMBER: P1032176

CATALOG NUMBER: S123RDIW-B340D1030UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	528.2	528.0	527.5	527.1	526.6	526.2	526.6	527.1	527.5	528.0	528.2
115°	589.8	590.3	591.2	592.1	593.0	593.9	593.0	592.1	591.2	590.3	589.8
117.5°	647.4	647.5	647.7	648.0	648.2	648.4	648.2	648.0	647.7	647.5	647.4
120°	705.0	705.0	705.0	705.0	705.0	705.0	705.0	705.0	705.0	705.0	705.0
122.5°	759.5	759.6	759.8	760.1	760.3	760.5	760.3	760.1	759.8	759.6	759.5
125°	810.0	810.2	810.7	811.1	811.6	812.0	811.6	811.1	810.7	810.2	810.0
127.5°	864.5	864.3	863.8	863.4	862.9	862.5	862.9	863.4	863.8	864.3	864.5
130°	913.0	912.8	912.3	911.9	911.4	911.0	911.4	911.9	912.3	912.8	913.0
132.5°	958.5	958.2	957.5	956.8	956.1	955.4	956.1	956.8	957.5	958.2	958.5
135°	1003.9	1003.6	1002.9	1002.2	1001.6	1000.9	1001.6	1002.2	1002.9	1003.6	1003.9
137.5°	1046.3	1046.1	1045.6	1045.2	1044.7	1044.3	1044.7	1045.2	1045.6	1046.1	1046.3
140°	1084.7	1084.5	1084.0	1083.6	1083.1	1082.7	1083.1	1083.6	1084.0	1084.5	1084.7
142.5°	1121.1	1120.8	1120.1	1119.4	1118.7	1118.0	1118.7	1119.4	1120.1	1120.8	1121.1
145°	1154.4	1154.4	1154.4	1154.4	1154.4	1154.4	1154.4	1154.4	1154.4	1154.4	1154.4
147.5°	1185.7	1185.1	1184.0	1182.9	1181.7	1180.6	1181.7	1182.9	1184.0	1185.1	1185.7
150°	1214.0	1213.7	1213.0	1212.3	1211.6	1210.9	1211.6	1212.3	1213.0	1213.7	1214.0
152.5°	1240.2	1239.6	1238.5	1237.4	1236.3	1235.2	1236.3	1237.4	1238.5	1239.6	1240.2
155°	1263.5	1262.8	1261.5	1260.1	1258.8	1257.4	1258.8	1260.1	1261.5	1262.8	1263.5
157.5°	1284.7	1283.8	1282.0	1280.2	1278.4	1276.6	1278.4	1280.2	1282.0	1283.8	1284.7
160°	1301.8	1301.0	1299.5	1297.9	1296.4	1294.8	1296.4	1297.9	1299.5	1301.0	1301.8
162.5°	1318.0	1317.3	1316.0	1314.6	1313.3	1311.9	1313.3	1314.6	1316.0	1317.3	1318.0
165°	1332.1	1331.3	1329.8	1328.2	1326.7	1325.1	1326.7	1328.2	1329.8	1331.3	1332.1
167.5°	1343.3	1342.4	1340.6	1338.8	1337.0	1335.2	1337.0	1338.8	1340.6	1342.4	1343.3
170°	1352.3	1351.4	1349.6	1347.9	1346.1	1344.3	1346.1	1347.9	1349.6	1351.4	1352.3
172.5°	1358.4	1357.4	1355.4	1353.3	1351.3	1349.3	1351.3	1353.3	1355.4	1357.4	1358.4
175°	1362.4	1361.5	1359.7	1358.0	1356.2	1354.4	1356.2	1358.0	1359.7	1361.5	1362.4
177.5°	1365.5	1364.4	1362.1	1359.9	1357.6	1355.4	1357.6	1359.9	1362.1	1364.4	1365.5
180°	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4

TEST NUMBER: P1032176

CATALOG NUMBER: S123RDIW-B340D1030UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3
2.5°	497.0	498.8	497.0	493.4	497.0	499.2	501.5	505.1	506.9	506.9	509.5
5°	468.6	472.2	470.9	470.0	473.6	475.8	479.4	483.9	488.9	492.0	495.6
7.5°	443.4	445.7	447.9	447.9	451.5	456.5	461.9	467.3	473.6	478.1	480.8
10°	421.4	423.2	424.5	426.3	431.7	437.1	444.3	451.1	456.5	461.4	465.9
12.5°	400.3	403.0	406.1	407.5	411.5	418.3	425.0	433.1	441.6	446.6	451.1
15°	380.0	381.4	385.0	389.0	392.6	399.8	408.4	416.9	424.1	431.7	435.8
17.5°	359.3	359.8	369.2	367.0	378.7	385.4	389.9	398.0	409.7	416.0	422.3
20°	339.1	343.6	347.6	349.9	356.2	363.8	376.9	383.2	392.6	398.5	403.9
22.5°	323.4	330.1	330.1	335.5	338.6	345.8	355.3	367.4	377.8	381.8	389.5
25°	309.4	312.6	318.0	319.8	325.6	331.9	338.2	351.2	362.5	367.9	373.3
27.5°	291.4	295.5	302.7	302.7	310.3	317.1	324.7	333.3	344.5	352.1	358.0
30°	277.5	281.5	284.7	289.6	292.8	299.1	312.6	318.9	328.8	335.5	342.7
32.5°	264.4	267.6	270.3	275.7	279.3	286.5	293.7	304.9	313.5	319.8	327.4
35°	250.1	253.2	256.8	260.8	266.2	273.0	279.7	289.2	297.7	303.6	309.9
37.5°	236.6	238.8	244.2	246.9	251.4	257.7	266.2	276.1	283.8	288.3	294.6
40°	223.5	225.3	229.4	234.3	237.5	242.4	251.4	259.9	269.4	274.8	279.7
42.5°	209.6	211.8	215.4	220.4	225.3	230.7	235.7	245.6	254.1	258.6	264.0
45°	197.4	198.8	201.5	206.4	211.4	215.4	223.1	232.1	240.2	243.8	249.6
47.5°	183.0	184.4	188.4	190.7	196.1	201.5	209.1	218.1	225.3	228.9	234.3
50°	168.2	169.5	172.2	177.2	180.8	186.6	193.4	201.0	210.0	215.0	218.1
52.5°	153.8	156.5	158.8	162.8	167.3	173.1	179.4	186.6	194.3	199.2	202.8
55°	139.4	141.7	144.4	146.6	152.0	157.4	164.6	171.3	178.1	182.6	186.6
57.5°	123.2	126.4	129.1	133.6	137.6	142.1	150.2	155.6	163.7	166.9	170.4
60°	109.3	112.4	114.7	118.3	121.9	127.7	133.1	139.9	146.6	150.7	155.2
62.5°	97.6	98.9	100.3	103.9	107.5	112.9	118.3	125.0	132.2	134.5	138.1
65°	85.9	87.2	89.5	92.6	95.3	98.5	104.3	109.7	116.5	120.1	121.4
67.5°	76.0	77.4	77.8	80.1	82.3	85.9	89.0	94.4	100.7	103.0	105.7
70°	64.8	67.0	67.5	69.3	70.2	72.4	76.0	80.1	85.0	89.0	91.3
72.5°	51.7	54.9	55.8	58.5	59.8	62.1	64.8	67.9	71.1	72.9	74.7
75°	42.3	43.2	43.6	45.9	48.1	51.3	52.6	54.4	57.1	59.4	61.2
77.5°	35.1	35.5	36.0	36.0	36.4	38.2	40.9	43.2	45.0	45.9	47.2
80°	28.3	27.9	27.9	28.3	28.3	28.3	29.2	32.4	33.3	35.5	35.1
82.5°	22.0	21.1	21.6	21.1	21.1	21.1	21.1	21.6	21.6	22.9	23.8
85°	14.4	14.8	14.4	14.4	13.9	14.4	13.9	13.9	13.5	13.5	13.0
87.5°	7.6	8.1	7.6	7.6	7.2	7.6	7.2	7.2	6.7	6.7	5.8
90°	27.8	26.9	26.0	25.1	24.2	21.3	18.4	15.5	12.6	11.1	10.0
92.5°	32.5	31.0	29.4	27.9	26.3	24.3	22.3	20.2	18.2	17.2	17.9
95°	37.6	36.0	34.5	32.9	31.3	28.8	26.4	23.9	21.4	20.2	24.8
97.5°	39.5	37.7	35.9	34.1	32.3	43.7	55.2	66.6	78.1	83.8	86.9
100°	40.5	38.7	36.9	35.1	33.3	68.3	103.3	138.4	173.4	190.9	188.7
102.5°	45.1	52.5	59.9	67.3	74.7	113.8	152.8	191.9	231.0	250.5	249.0
105°	62.3	102.0	141.7	181.5	221.2	241.4	261.6	281.8	302.0	312.1	310.9
107.5°	254.6	289.2	323.7	358.3	392.9	389.5	386.1	382.8	379.4	377.7	376.7
110°	425.9	433.3	440.7	448.1	455.5	453.0	450.6	448.1	445.6	444.4	443.5

TEST NUMBER: P1032176

CATALOG NUMBER: S123RDIW-B340D1030UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	527.2	525.2	523.1	521.1	519.1	516.6	514.2	511.7	509.2	508.0	507.2
115°	588.7	586.4	584.2	581.9	579.7	577.7	575.7	573.6	571.6	570.6	569.9
117.5°	646.5	644.7	642.9	641.1	639.3	638.2	637.1	636.0	634.9	634.3	633.5
120°	704.1	702.3	700.5	698.7	696.9	696.2	695.5	694.8	694.1	693.8	692.8
122.5°	758.9	757.8	756.7	755.5	754.4	753.5	752.6	751.7	750.8	750.4	749.6
125°	809.8	809.3	808.9	808.4	808.0	807.1	806.2	805.3	804.4	803.9	803.0
127.5°	864.2	863.5	862.8	862.2	861.5	860.4	859.3	858.2	857.1	856.5	855.6
130°	912.6	911.7	910.8	909.9	909.0	908.1	907.2	906.3	905.4	904.9	904.0
132.5°	958.0	957.1	956.2	955.3	954.4	953.7	953.1	952.4	951.7	951.4	950.5
135°	1003.6	1002.9	1002.2	1001.6	1000.9	1000.0	999.1	998.2	997.3	996.8	996.1
137.5°	1045.7	1044.6	1043.5	1042.4	1041.3	1040.9	1040.4	1040.0	1039.5	1039.3	1038.4
140°	1084.3	1083.4	1082.5	1081.6	1080.7	1080.0	1079.3	1078.6	1077.9	1077.6	1076.9
142.5°	1120.8	1120.1	1119.4	1118.7	1118.0	1117.3	1116.7	1116.0	1115.3	1115.0	1114.3
145°	1154.2	1153.7	1153.3	1152.8	1152.4	1152.0	1151.5	1151.1	1150.6	1150.4	1149.6
147.5°	1185.5	1185.0	1184.6	1184.1	1183.7	1183.3	1182.8	1182.4	1181.9	1181.7	1181.1
150°	1213.8	1213.3	1212.9	1212.4	1212.0	1211.5	1211.1	1210.6	1210.1	1209.9	1209.6
152.5°	1239.8	1238.9	1238.0	1237.1	1236.2	1236.0	1235.8	1235.5	1235.3	1235.2	1235.1
155°	1262.9	1261.8	1260.7	1259.5	1258.4	1258.2	1258.0	1257.7	1257.5	1257.4	1257.6
157.5°	1284.0	1282.7	1281.3	1280.0	1278.6	1278.8	1279.0	1279.3	1279.5	1279.6	1279.6
160°	1301.1	1299.8	1298.5	1297.1	1295.8	1296.0	1296.2	1296.5	1296.7	1296.8	1296.9
162.5°	1317.2	1315.6	1314.1	1312.5	1310.9	1311.1	1311.3	1311.6	1311.8	1311.9	1312.2
165°	1331.2	1329.4	1327.7	1325.9	1324.1	1324.3	1324.5	1324.8	1325.0	1325.1	1325.4
167.5°	1342.4	1340.6	1338.8	1337.0	1335.2	1335.2	1335.2	1335.2	1335.2	1335.2	1335.6
170°	1351.4	1349.6	1347.9	1346.1	1344.3	1344.3	1344.3	1344.3	1344.3	1344.3	1344.7
172.5°	1357.5	1355.7	1353.9	1352.1	1350.3	1350.1	1349.9	1349.6	1349.4	1349.3	1349.9
175°	1361.6	1360.1	1358.5	1357.0	1355.4	1355.2	1355.0	1354.7	1354.5	1354.4	1355.0
177.5°	1364.6	1362.8	1361.0	1359.2	1357.4	1357.2	1357.0	1356.7	1356.5	1356.4	1357.0
180°	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4

TEST NUMBER: P1032176

CATALOG NUMBER: S123RDIW-B340D1030UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	525.3	525.3	525.3	525.3
2.5°	511.8	514.9	521.2	526.6
5°	501.0	506.0	515.4	524.8
7.5°	488.0	495.6	507.7	520.8
10°	475.4	485.3	500.1	515.4
12.5°	462.8	473.1	488.9	508.6
15°	447.9	458.7	477.6	501.5
17.5°	434.9	449.3	466.4	490.2
20°	421.0	431.7	453.8	479.0
22.5°	403.4	421.4	442.1	468.6
25°	389.5	405.2	425.9	456.0
27.5°	372.4	390.8	416.0	442.5
30°	358.4	373.7	397.1	429.0
32.5°	342.2	360.2	384.5	416.0
35°	327.9	343.1	366.1	398.0
37.5°	310.8	327.4	353.0	381.4
40°	295.9	312.1	336.4	362.9
42.5°	277.9	295.0	319.3	341.8
45°	263.5	279.3	298.6	319.3
47.5°	246.0	262.6	281.5	295.9
50°	230.3	245.6	260.4	272.5
52.5°	213.2	227.1	240.6	249.6
55°	197.4	208.2	219.0	225.3
57.5°	179.0	189.3	198.3	201.9
60°	162.8	171.3	177.2	181.2
62.5°	145.7	152.0	156.5	158.8
65°	129.1	133.6	135.8	138.1
67.5°	112.0	116.0	117.4	120.1
70°	94.0	98.5	99.4	100.7
72.5°	80.5	80.5	82.3	84.1
75°	64.3	65.2	66.1	66.1
77.5°	50.4	50.4	51.3	51.7
80°	36.9	37.3	37.3	36.9
82.5°	25.2	26.1	25.2	24.7
85°	13.9	15.7	14.8	14.8
87.5°	5.8	5.8	6.7	5.8
90°	7.7	5.5	3.2	1.0
92.5°	19.2	20.5	21.9	23.2
95°	34.0	43.2	52.4	61.6
97.5°	93.2	99.5	105.8	112.1
100°	184.2	179.7	175.2	170.7
102.5°	246.1	243.2	240.2	237.3
105°	308.4	305.9	303.5	301.0
107.5°	374.7	372.6	370.6	368.6
110°	441.7	439.9	438.1	436.3

TEST NUMBER: P1032176

CATALOG NUMBER: S123RDIW-B340D1030UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	505.6	504.1	502.5	500.9
115°	568.6	567.3	565.9	564.6
117.5°	631.9	630.4	628.8	627.2
120°	690.8	688.8	686.8	684.8
122.5°	748.0	746.5	744.9	743.3
125°	801.2	799.5	797.7	795.9
127.5°	853.8	852.0	850.2	848.4
130°	902.2	900.4	898.6	896.8
132.5°	948.7	946.9	945.1	943.3
135°	994.8	993.5	992.1	990.8
137.5°	1036.6	1034.8	1033.0	1031.2
140°	1075.6	1074.3	1072.9	1071.6
142.5°	1113.0	1111.6	1110.3	1108.9
145°	1148.0	1146.5	1144.9	1143.3
147.5°	1180.0	1178.9	1177.7	1176.6
150°	1208.9	1208.2	1207.6	1206.9
152.5°	1234.9	1234.6	1234.4	1234.2
155°	1258.1	1258.5	1259.0	1259.4
157.5°	1279.6	1279.6	1279.6	1279.6
160°	1297.1	1297.4	1297.6	1297.8
162.5°	1312.9	1313.6	1314.3	1315.0
165°	1326.1	1326.8	1327.4	1328.1
167.5°	1336.5	1337.4	1338.3	1339.2
170°	1345.6	1346.5	1347.4	1348.3
172.5°	1351.0	1352.1	1353.3	1354.4
175°	1356.1	1357.2	1358.3	1359.4
177.5°	1358.1	1359.2	1360.3	1361.4
180°	1359.4	1359.4	1359.4	1359.4

(END OF REPORT)