

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032194

Luminaire Tested: S123RDIW-B340D1320UB27-4F0-XX-W2A-A

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032194
REPORT IS A COMBINATION OF REPORTS P994203 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B340D1320UB27-4F0-XX-W2A-A
Description: Define 3 Regressed Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6545.0 lumens
Efficiency: N/A
Efficacy: 118.8 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 55.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032194

CATALOG NUMBER: S123RDIW-B340D1320UB27-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1032194

CATALOG NUMBER: S123RDIW-B340D1320UB27-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	100	100	100	100	88	88	88	88	67	67	67	47	47	47	29	29	29
1	91	87	84	80	81	77	74	72	59	57	55	41	40	39	26	25	25
2	83	76	71	66	73	68	63	59	52	48	46	37	35	33	23	22	21
3	76	67	60	55	67	60	54	49	46	42	39	33	30	28	20	19	18
4	70	60	52	47	61	53	47	42	41	36	33	29	26	24	18	17	16
5	64	53	45	40	56	47	41	36	36	32	28	26	23	21	17	15	14
6	59	47	40	34	52	42	36	31	33	28	25	24	21	18	15	13	12
7	54	43	35	30	48	38	32	27	29	25	22	21	18	16	14	12	11
8	50	39	31	26	44	34	28	24	27	22	19	19	17	14	13	11	10
9	47	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9
10	43	32	25	21	38	29	23	19	22	18	15	16	14	12	11	9	8

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5654	5654	5654	5654
5°	5658	6512	5673	4831
10°	5609	7861	5633	4220
15°	5551	8922	5551	3721
20°	5437	9623	5468	3301
25°	5353	9143	5343	3012
30°	5256	6335	5245	2729
35°	5140	4067	5117	2516
40°	4994	2872	4970	2304
45°	4742	2299	4736	2097
50°	4431	1922	4417	1856
55°	4082	1585	4050	1574
60°	3739	1310	3702	1338
65°	3338	1049	3360	1135
70°	2965	729	3045	918
75°	2514	541	2617	706
80°	2003	358	2172	529
85°	1422	168	1556	328

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 7549 cd/sqm

TEST NUMBER: P1032194

CATALOG NUMBER: S123RDIW-B340D1320UB27-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.6	0.8
10°-20°	161.5	2.5
20°-30°	254.3	3.9
30°-40°	264.5	4.0
40°-50°	226.3	3.5
50°-60°	172.5	2.6
60°-70°	110.5	1.7
70°-80°	52.9	0.8
80°-90°	17.3	0.3
90°-100°	60.5	0.9
100°-110°	292.7	4.5
110°-120°	717.2	11.0
120°-130°	910.5	13.9
130°-140°	972.7	14.9
140°-150°	909.6	13.9
150°-160°	733.7	11.2
160°-170°	473.5	7.2
170°-180°	163.2	2.5
0°-30°	467.4	7.1
0°-40°	731.9	11.2
0°-60°	1130.6	17.3
0°-90°	1311.4	20.0
90°-120°	1070.5	16.4
90°-150°	3863.3	59.0
90°-180°	5234.0	80.0
0°-180°	6545.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	525	525	525	525	525	
5°	525	624	526	463	525	50
15°	502	886	502	370	502	141
25°	456	913	455	301	456	210
35°	398	396	396	245	398	249
45°	319	211	319	193	319	246
55°	225	133	224	132	225	202
65°	138	76	139	83	138	138
75°	66	32	69	42	66	71
85°	15	8	16	15	15	17
90°	1	38	1	38	1	5
95°	78	48	78	48	78	93
105°	380	56	380	56	380	403
115°	713	750	713	750	713	704
125°	1005	1025	1005	1025	1005	898
135°	1251	1264	1251	1264	1251	963
145°	1444	1458	1444	1458	1444	904
155°	1590	1588	1590	1588	1590	733
165°	1677	1673	1677	1673	1677	474
175°	1717	1710	1717	1710	1717	163
180°	1717	1717	1717	1717	1717	

TEST NUMBER: P1032194

CATALOG NUMBER: S123RDIW-B340D1320UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3
2.5°	526.6	530.2	532.9	534.7	539.2	541.9	544.2	548.2	548.2	549.1	550.9
5°	524.8	532.5	537.9	545.1	554.5	559.0	565.3	570.7	578.4	582.4	586.5
7.5°	520.8	531.6	542.8	553.6	567.6	576.6	582.9	596.8	606.7	618.8	628.3
10°	515.4	530.2	544.6	561.3	580.2	593.6	603.1	621.5	640.4	657.5	671.9
12.5°	508.6	526.6	547.3	567.6	594.1	607.6	622.9	645.8	672.8	694.4	713.7
15°	501.5	522.1	545.5	570.3	603.5	622.4	644.5	672.4	702.5	733.5	760.1
17.5°	490.2	516.3	542.4	578.4	617.5	628.7	647.6	685.8	723.2	751.1	783.4
20°	479.0	508.2	541.0	573.4	615.7	641.8	659.3	699.8	739.8	773.5	804.6
22.5°	468.6	499.2	533.4	574.3	613.9	640.0	662.0	704.3	750.6	788.4	826.6
25°	456.0	489.3	527.1	565.8	613.9	633.7	658.0	707.0	756.0	799.6	846.8
27.5°	442.5	476.3	513.6	553.2	597.2	626.5	650.3	702.9	762.7	809.5	858.1
30°	429.0	463.7	499.7	535.2	584.7	612.5	640.0	698.0	766.3	819.9	857.2
32.5°	416.0	445.2	480.8	515.4	564.4	595.0	626.0	693.0	767.7	812.7	830.7
35°	398.0	428.6	457.4	494.3	543.7	573.9	610.3	692.6	761.8	789.7	780.7
37.5°	381.4	407.0	434.4	467.3	518.1	557.2	595.0	680.9	742.5	744.3	693.5
40°	362.9	384.1	407.0	441.6	496.5	535.2	576.1	662.9	707.4	680.9	591.4
42.5°	341.8	360.7	378.7	412.4	472.2	515.4	559.5	640.4	656.6	595.4	502.4
45°	319.3	334.6	351.2	386.8	446.6	489.3	533.4	605.8	589.2	502.8	414.2
47.5°	295.9	309.0	325.2	357.5	419.2	462.8	504.6	556.3	514.0	421.4	347.2
50°	272.5	282.9	298.6	331.9	391.3	430.8	469.5	503.3	443.9	361.6	286.9
52.5°	249.6	257.7	273.9	302.2	359.8	397.6	425.4	438.5	378.2	298.6	249.2
55°	225.3	234.3	245.1	273.9	331.0	358.9	377.3	376.9	314.8	253.2	206.0
57.5°	201.9	210.0	219.5	248.3	294.6	313.5	329.2	321.6	262.6	207.3	176.7
60°	181.2	185.7	196.1	220.4	255.4	271.6	280.6	267.6	214.5	174.9	146.2
62.5°	158.8	163.3	171.8	194.7	216.3	224.9	232.5	215.9	177.2	142.6	125.0
65°	138.1	143.9	149.3	167.8	179.4	189.8	188.9	174.9	138.5	116.0	101.6
67.5°	120.1	122.3	126.8	138.1	143.5	151.1	151.6	135.8	111.5	94.4	85.9
70°	100.7	103.0	106.1	111.5	115.1	116.9	116.0	102.1	84.1	73.8	66.1
72.5°	84.1	83.7	85.9	85.9	89.5	89.0	86.3	75.6	63.9	55.3	50.8
75°	66.1	66.6	67.0	66.1	64.8	63.0	60.7	52.6	45.0	40.9	36.9
77.5°	51.7	50.8	51.3	48.1	46.3	44.5	41.4	37.3	31.0	30.1	28.3
80°	36.9	36.4	36.0	34.6	30.6	28.8	26.5	24.3	22.9	22.0	21.6
82.5°	24.7	24.7	23.8	21.1	18.9	17.5	17.1	16.2	14.8	14.8	14.4
85°	14.8	14.4	13.5	10.8	9.4	9.4	9.4	9.4	8.5	8.5	8.1
87.5°	5.8	5.4	4.0	4.0	3.6	3.6	3.6	3.1	3.1	2.7	2.7
90°	1.3	4.1	6.9	9.8	12.6	14.0	15.8	19.5	23.2	26.9	30.6
92.5°	29.3	27.6	25.9	24.2	22.5	21.7	23.0	25.5	28.1	30.6	33.2
95°	77.8	66.2	54.6	42.9	31.3	25.5	27.1	30.2	33.3	36.4	39.5
97.5°	141.6	133.7	125.7	117.8	109.9	105.9	98.7	84.2	69.7	55.3	40.8
100°	215.5	221.2	226.9	232.6	238.3	241.1	219.0	174.8	130.5	86.3	42.1
102.5°	299.7	303.4	307.1	310.8	314.5	316.3	291.6	242.3	193.0	143.7	94.4
105°	380.1	383.2	386.3	389.4	392.5	394.1	381.3	355.8	330.3	304.8	279.3
107.5°	465.5	468.1	470.6	473.2	475.7	477.0	479.1	483.4	487.6	491.9	496.1
110°	551.0	553.3	555.5	557.8	560.1	561.2	562.8	565.9	569.0	572.1	575.2

TEST NUMBER: P1032194

CATALOG NUMBER: S123RDIW-B340D1320UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	632.6	634.6	636.6	638.5	640.5	641.5	643.1	646.2	649.3	652.5	655.6
115°	713.0	714.7	716.4	718.1	719.8	720.6	721.9	724.4	727.0	729.5	732.1
117.5°	792.0	794.0	796.0	798.0	800.0	801.0	801.7	803.1	804.5	805.9	807.3
120°	864.7	867.3	869.8	872.4	874.9	876.2	876.6	877.5	878.3	879.2	880.0
122.5°	938.7	940.7	942.7	944.6	946.6	947.6	948.2	949.3	950.4	951.6	952.7
125°	1005.0	1007.3	1009.5	1011.8	1014.1	1015.2	1015.8	1016.9	1018.0	1019.2	1020.3
127.5°	1071.4	1073.7	1075.9	1078.2	1080.5	1081.6	1082.3	1083.7	1085.1	1086.5	1087.9
130°	1132.6	1134.9	1137.1	1139.4	1141.7	1142.8	1143.4	1144.5	1145.6	1146.8	1147.9
132.5°	1191.2	1193.5	1195.8	1198.1	1200.4	1201.5	1201.9	1202.8	1203.6	1204.5	1205.3
135°	1251.2	1252.9	1254.6	1256.3	1258.0	1258.8	1259.4	1260.5	1261.6	1262.8	1263.9
137.5°	1302.2	1304.5	1306.7	1309.0	1311.3	1312.4	1312.7	1313.3	1313.8	1314.4	1315.0
140°	1353.2	1354.9	1356.6	1358.3	1360.0	1360.9	1361.3	1362.2	1363.0	1363.9	1364.7
142.5°	1400.4	1402.1	1403.8	1405.5	1407.2	1408.1	1408.5	1409.4	1410.2	1411.1	1411.9
145°	1443.8	1445.8	1447.8	1449.7	1451.7	1452.7	1453.0	1453.6	1454.1	1454.7	1455.3
147.5°	1485.9	1487.3	1488.7	1490.1	1491.5	1492.2	1492.5	1493.1	1493.6	1494.2	1494.8
150°	1524.1	1525.0	1525.8	1526.7	1527.6	1528.0	1528.3	1528.8	1529.4	1529.9	1530.5
152.5°	1558.6	1558.9	1559.1	1559.4	1559.7	1559.8	1559.9	1560.2	1560.5	1560.8	1561.1
155°	1590.5	1589.9	1589.3	1588.8	1588.2	1587.9	1588.0	1588.3	1588.6	1588.9	1589.2
157.5°	1616.0	1616.0	1616.0	1616.0	1616.0	1616.0	1615.9	1615.6	1615.3	1615.0	1614.7
160°	1638.9	1638.6	1638.3	1638.0	1637.7	1637.6	1637.5	1637.2	1636.9	1636.7	1636.4
162.5°	1660.6	1659.8	1658.9	1658.1	1657.2	1656.8	1656.7	1656.4	1656.1	1655.8	1655.5
165°	1677.2	1676.4	1675.5	1674.7	1673.8	1673.4	1673.3	1673.0	1672.7	1672.4	1672.1
167.5°	1691.2	1690.1	1688.9	1687.8	1686.7	1686.1	1686.1	1686.1	1686.1	1686.1	1686.1
170°	1702.7	1701.6	1700.4	1699.3	1698.2	1697.6	1697.6	1697.6	1697.6	1697.6	1697.6
172.5°	1710.3	1708.9	1707.5	1706.1	1704.7	1704.0	1704.1	1704.4	1704.7	1704.9	1705.2
175°	1716.7	1715.3	1713.9	1712.4	1711.0	1710.3	1710.4	1710.7	1711.0	1711.3	1711.6
177.5°	1719.3	1717.9	1716.5	1715.0	1713.6	1712.9	1713.0	1713.3	1713.6	1713.9	1714.2
180°	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7

TEST NUMBER: P1032194

CATALOG NUMBER: S123RDIW-B340D1320UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3
2.5°	554.5	554.5	558.6	562.6	560.4	561.7	566.7	564.9	568.5	568.0	569.4
5°	596.3	601.3	605.3	613.9	615.2	613.9	622.4	624.7	628.7	623.8	626.0
7.5°	643.6	653.9	663.8	676.4	680.4	681.3	685.8	692.1	697.5	687.6	692.6
10°	689.4	705.2	725.4	736.7	746.6	750.2	753.8	757.8	764.1	769.9	765.4
12.5°	738.9	761.8	781.2	801.4	813.6	812.2	822.6	825.3	830.2	831.6	833.4
15°	779.4	811.8	823.9	854.0	856.7	865.7	877.4	887.8	889.1	886.4	886.4
17.5°	818.1	846.0	867.5	891.8	896.8	904.4	919.3	924.2	926.0	925.6	925.6
20°	849.5	868.0	904.4	924.7	932.7	942.6	953.0	959.3	960.6	962.4	959.7
22.5°	870.2	898.1	927.8	944.4	951.2	954.8	961.5	963.3	961.1	961.5	962.0
25°	886.4	913.9	931.8	936.3	935.9	931.4	926.5	917.9	917.0	913.4	906.2
27.5°	890.9	901.3	899.0	880.6	862.1	860.3	830.7	814.5	796.0	798.7	788.4
30°	866.6	853.1	821.2	774.4	755.1	723.6	690.3	655.7	642.2	627.4	654.8
32.5°	807.3	759.2	702.5	641.8	609.4	581.5	546.0	520.8	506.4	494.3	517.6
35°	717.8	642.7	567.6	510.0	483.5	458.3	425.0	412.4	394.4	396.2	398.5
37.5°	602.6	519.9	463.2	406.6	389.0	378.7	354.4	335.1	328.8	327.0	327.0
40°	494.7	426.8	376.4	331.9	318.4	309.9	290.5	281.5	274.8	273.0	275.2
42.5°	409.3	351.2	312.1	282.4	273.0	262.2	254.1	242.9	241.5	238.4	242.4
45°	343.6	293.2	264.0	242.4	234.3	230.3	221.3	214.5	211.8	211.4	214.5
47.5°	291.4	252.3	226.7	213.2	206.9	202.8	195.2	192.5	189.8	190.7	189.3
50°	244.7	215.4	198.8	186.6	182.6	178.5	173.6	170.9	169.5	169.5	169.1
52.5°	210.0	185.7	174.9	163.7	161.9	159.7	154.3	152.5	150.2	149.8	151.6
55°	179.9	163.3	152.5	145.7	143.9	139.4	137.2	134.9	133.6	132.7	133.1
57.5°	153.8	141.2	134.0	128.2	125.0	123.2	119.2	118.7	117.8	117.8	117.4
60°	132.2	123.2	114.7	111.1	108.8	106.6	106.1	103.4	102.1	103.0	102.5
62.5°	112.0	104.8	99.8	95.8	94.4	92.6	91.3	90.4	89.0	89.5	89.5
65°	93.5	87.7	84.1	80.5	80.1	78.3	77.8	76.9	76.9	76.5	77.4
67.5°	76.9	72.9	69.7	67.5	66.1	66.6	64.8	63.4	63.4	63.0	64.3
70°	61.2	58.9	55.8	53.1	51.3	51.3	49.0	48.6	48.6	48.6	48.1
72.5°	47.2	43.2	41.8	40.9	40.9	40.9	40.0	40.0	39.6	40.0	39.6
75°	35.1	34.6	33.7	33.3	33.3	32.8	32.4	32.4	32.4	32.4	32.4
77.5°	27.4	27.4	26.5	26.1	26.1	26.1	25.6	25.6	25.2	25.2	25.2
80°	20.2	20.2	19.3	19.3	19.3	18.9	18.9	18.9	19.3	18.9	18.9
82.5°	13.9	13.9	13.5	13.9	13.5	13.0	13.0	13.0	12.6	13.0	13.0
85°	8.1	8.1	7.6	7.2	7.6	7.6	7.2	7.6	7.2	7.6	7.2
87.5°	3.1	2.7	2.7	2.7	2.2	2.7	2.2	2.2	2.7	2.2	2.7
90°	31.7	32.9	34.0	35.1	35.7	36.0	36.6	37.1	37.7	38.3	37.7
92.5°	35.2	37.2	39.1	41.1	42.1	42.2	42.5	42.8	43.1	43.4	43.1
95°	41.5	43.5	45.5	47.5	48.5	48.5	48.5	48.5	48.5	48.5	48.5
97.5°	43.1	45.3	47.6	49.9	51.0	51.1	51.4	51.7	52.0	52.3	52.0
100°	44.4	46.6	48.9	51.2	52.3	52.4	52.7	53.0	53.3	53.6	53.3
102.5°	85.0	75.7	66.3	57.0	52.3	52.6	53.1	53.7	54.2	54.8	54.2
105°	229.1	179.0	128.8	78.7	53.6	53.9	54.4	55.0	55.5	56.1	55.5
107.5°	452.5	408.8	365.2	321.5	299.7	281.1	244.0	206.9	169.7	132.6	169.7
110°	565.8	556.5	547.1	537.8	533.1	512.8	472.3	431.8	391.2	350.7	391.2

TEST NUMBER: P1032194

CATALOG NUMBER: S123RDIW-B340D1320UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	658.1	660.7	663.2	665.7	667.0	666.7	666.2	665.6	665.1	664.5	665.1
115°	734.9	737.7	740.6	743.4	744.8	745.4	746.5	747.6	748.8	749.9	748.8
117.5°	809.6	811.8	814.1	816.4	817.5	817.6	817.9	818.2	818.5	818.8	818.5
120°	882.3	884.5	886.8	889.1	890.2	890.2	890.2	890.2	890.2	890.2	890.2
122.5°	954.1	955.5	957.0	958.4	959.1	959.2	959.5	959.8	960.1	960.4	960.1
125°	1020.9	1021.5	1022.0	1022.6	1022.9	1023.2	1023.7	1024.3	1024.8	1025.4	1024.8
127.5°	1088.8	1089.6	1090.5	1091.4	1091.8	1091.5	1090.9	1090.4	1089.8	1089.2	1089.8
130°	1149.0	1150.2	1151.3	1152.4	1153.0	1152.7	1152.1	1151.6	1151.0	1150.4	1151.0
132.5°	1206.4	1207.6	1208.7	1209.8	1210.4	1210.0	1209.1	1208.3	1207.4	1206.6	1207.4
135°	1264.8	1265.6	1266.5	1267.4	1267.8	1267.4	1266.5	1265.6	1264.8	1263.9	1264.8
137.5°	1316.4	1317.8	1319.2	1320.6	1321.3	1321.0	1320.5	1319.9	1319.4	1318.8	1319.4
140°	1365.8	1367.0	1368.1	1369.2	1369.8	1369.5	1369.0	1368.4	1367.9	1367.3	1367.9
142.5°	1412.7	1413.6	1414.4	1415.3	1415.7	1415.3	1414.4	1413.6	1412.7	1411.9	1412.7
145°	1455.9	1456.4	1457.0	1457.5	1457.8	1457.8	1457.8	1457.8	1457.8	1457.8	1457.8
147.5°	1495.4	1495.9	1496.5	1497.0	1497.3	1496.6	1495.2	1493.8	1492.4	1491.0	1492.4
150°	1531.1	1531.7	1532.2	1532.8	1533.1	1532.7	1531.8	1530.9	1530.1	1529.2	1530.1
152.5°	1562.2	1563.4	1564.5	1565.6	1566.2	1565.5	1564.1	1562.6	1561.2	1559.8	1561.2
155°	1590.6	1592.0	1593.5	1594.9	1595.6	1594.7	1593.0	1591.3	1589.6	1587.9	1589.6
157.5°	1616.4	1618.1	1619.8	1621.5	1622.3	1621.2	1618.9	1616.6	1614.4	1612.1	1614.4
160°	1638.1	1639.8	1641.5	1643.2	1644.0	1643.0	1641.0	1639.1	1637.1	1635.1	1637.1
162.5°	1657.5	1659.5	1661.4	1663.4	1664.4	1663.6	1661.9	1660.2	1658.5	1656.8	1658.5
165°	1674.4	1676.6	1678.9	1681.2	1682.3	1681.3	1679.3	1677.4	1675.4	1673.4	1675.4
167.5°	1688.4	1690.6	1692.9	1695.2	1696.3	1695.2	1692.9	1690.6	1688.4	1686.1	1688.4
170°	1699.9	1702.1	1704.4	1706.7	1707.8	1706.7	1704.4	1702.1	1699.9	1697.6	1699.9
172.5°	1707.5	1709.7	1712.0	1714.3	1715.4	1714.1	1711.6	1709.1	1706.5	1704.0	1706.5
175°	1713.6	1715.6	1717.5	1719.5	1720.5	1719.4	1717.1	1714.8	1712.6	1710.3	1712.6
177.5°	1716.5	1718.7	1721.0	1723.3	1724.4	1723.0	1720.1	1717.3	1714.4	1711.6	1714.4
180°	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7

TEST NUMBER: P1032194

CATALOG NUMBER: S123RDIW-B340D1320UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3
2.5°	567.1	564.4	562.6	561.3	559.9	564.0	558.6	552.7	548.7	546.0	545.1
5°	626.5	620.6	615.7	611.6	612.5	612.5	603.1	592.7	583.8	578.8	573.4
7.5°	695.3	689.0	679.1	676.8	675.1	663.8	654.4	635.5	624.2	613.0	603.1
10°	763.6	755.6	746.1	743.0	738.5	724.5	710.1	685.8	671.9	651.2	638.2
12.5°	827.5	817.6	808.2	805.9	799.2	787.0	762.3	737.1	713.3	691.2	668.3
15°	881.0	878.3	863.9	854.9	840.1	823.5	818.1	783.9	753.8	730.8	689.4
17.5°	926.0	913.4	899.9	894.1	888.2	868.9	849.5	814.5	782.1	748.4	721.8
20°	962.0	948.0	938.6	930.1	927.4	905.3	874.7	843.7	808.2	770.4	735.8
22.5°	963.8	962.0	955.7	950.7	945.3	930.9	906.7	868.0	830.2	788.8	743.4
25°	926.5	923.8	941.7	937.2	940.8	935.4	922.4	890.0	846.0	797.4	751.5
27.5°	814.0	841.5	869.8	879.7	886.4	905.8	912.1	894.1	858.5	806.8	755.6
30°	661.1	697.5	743.4	768.1	787.0	823.0	869.8	875.6	859.0	817.6	754.7
32.5°	519.0	552.3	589.2	618.4	643.6	717.3	780.3	825.7	833.8	812.2	756.9
35°	418.3	432.6	467.7	495.6	529.8	592.7	667.0	740.3	789.7	792.4	750.2
37.5°	344.9	352.6	383.2	398.9	419.2	474.5	543.7	639.5	716.4	752.9	731.3
40°	285.6	303.1	320.7	329.7	344.0	382.3	448.8	523.9	619.3	686.7	702.0
42.5°	247.8	255.4	266.7	279.3	288.3	321.6	366.1	434.9	520.8	614.8	657.1
45°	218.6	221.3	233.0	241.1	250.5	273.9	305.4	362.9	438.5	531.1	603.1
47.5°	194.3	199.7	206.0	210.9	217.2	235.2	262.2	304.0	370.6	453.3	530.7
50°	172.7	175.8	183.9	186.2	190.7	203.3	224.0	255.9	310.8	376.9	456.9
52.5°	152.5	158.3	161.5	164.6	168.7	179.0	192.5	218.6	259.9	322.0	389.9
55°	136.7	138.5	143.0	145.7	148.9	156.1	167.8	187.1	219.5	268.9	333.3
57.5°	121.4	121.4	125.9	128.2	131.3	136.7	147.1	161.9	185.3	222.2	281.1
60°	105.2	105.7	109.3	112.0	112.9	118.3	126.8	138.5	156.5	183.5	231.6
62.5°	90.8	93.1	94.9	95.8	98.9	102.1	109.3	117.4	130.0	153.8	188.0
65°	78.7	79.2	80.5	81.4	82.8	86.3	91.7	97.1	107.9	125.5	153.4
67.5°	64.8	66.6	68.4	68.4	69.7	71.5	76.9	81.4	89.5	99.8	118.7
70°	48.6	49.5	52.2	53.5	55.3	58.5	61.2	63.9	70.2	77.8	92.2
72.5°	40.5	40.5	41.4	41.8	41.8	44.1	48.1	50.8	54.0	59.4	69.3
75°	32.4	32.4	33.7	33.3	34.2	35.1	35.5	37.3	39.1	43.2	49.0
77.5°	25.6	26.1	26.1	26.5	26.5	27.0	27.4	28.3	29.2	31.5	34.2
80°	18.9	19.3	19.3	19.8	19.8	20.2	20.7	21.1	22.0	22.9	24.3
82.5°	13.0	13.5	13.5	13.9	13.5	13.9	14.4	14.4	14.8	15.7	16.2
85°	7.6	7.6	8.1	7.6	7.6	7.6	8.1	8.1	8.5	9.9	9.9
87.5°	2.2	2.7	2.2	2.7	2.7	2.7	2.7	3.1	3.1	3.6	4.0
90°	37.1	36.6	36.0	35.7	35.1	34.0	32.9	31.7	30.6	26.9	23.2
92.5°	42.8	42.5	42.2	42.1	41.1	39.1	37.2	35.2	33.2	30.6	28.1
95°	48.5	48.5	48.5	48.5	47.5	45.5	43.5	41.5	39.5	36.4	33.3
97.5°	51.7	51.4	51.1	51.0	49.9	47.6	45.3	43.1	40.8	55.3	69.7
100°	53.0	52.7	52.4	52.3	51.2	48.9	46.6	44.4	42.1	86.3	130.5
102.5°	53.7	53.1	52.6	52.3	57.0	66.3	75.7	85.0	94.4	143.7	193.0
105°	55.0	54.4	53.9	53.6	78.7	128.8	179.0	229.1	279.3	304.8	330.3
107.5°	206.9	244.0	281.1	299.7	321.5	365.2	408.8	452.5	496.1	491.9	487.6
110°	431.8	472.3	512.8	533.1	537.8	547.1	556.5	565.8	575.2	572.1	569.0

TEST NUMBER: P1032194

CATALOG NUMBER: S123RDIW-B340D1320UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	665.6	666.2	666.7	667.0	665.7	663.2	660.7	658.1	655.6	652.5	649.3
115°	747.6	746.5	745.4	744.8	743.4	740.6	737.7	734.9	732.1	729.5	727.0
117.5°	818.2	817.9	817.6	817.5	816.4	814.1	811.8	809.6	807.3	805.9	804.5
120°	890.2	890.2	890.2	890.2	889.1	886.8	884.5	882.3	880.0	879.2	878.3
122.5°	959.8	959.5	959.2	959.1	958.4	957.0	955.5	954.1	952.7	951.6	950.4
125°	1024.3	1023.7	1023.2	1022.9	1022.6	1022.0	1021.5	1020.9	1020.3	1019.2	1018.0
127.5°	1090.4	1090.9	1091.5	1091.8	1091.4	1090.5	1089.6	1088.8	1087.9	1086.5	1085.1
130°	1151.6	1152.1	1152.7	1153.0	1152.4	1151.3	1150.2	1149.0	1147.9	1146.8	1145.6
132.5°	1208.3	1209.1	1210.0	1210.4	1209.8	1208.7	1207.6	1206.4	1205.3	1204.5	1203.6
135°	1265.6	1266.5	1267.4	1267.8	1267.4	1266.5	1265.6	1264.8	1263.9	1262.8	1261.6
137.5°	1319.9	1320.5	1321.0	1321.3	1320.6	1319.2	1317.8	1316.4	1315.0	1314.4	1313.8
140°	1368.4	1369.0	1369.5	1369.8	1369.2	1368.1	1367.0	1365.8	1364.7	1363.9	1363.0
142.5°	1413.6	1414.4	1415.3	1415.7	1415.3	1414.4	1413.6	1412.7	1411.9	1411.1	1410.2
145°	1457.8	1457.8	1457.8	1457.8	1457.5	1457.0	1456.4	1455.9	1455.3	1454.7	1454.1
147.5°	1493.8	1495.2	1496.6	1497.3	1497.0	1496.5	1495.9	1495.4	1494.8	1494.2	1493.6
150°	1530.9	1531.8	1532.7	1533.1	1532.8	1532.2	1531.7	1531.1	1530.5	1529.9	1529.4
152.5°	1562.6	1564.1	1565.5	1566.2	1565.6	1564.5	1563.4	1562.2	1561.1	1560.8	1560.5
155°	1591.3	1593.0	1594.7	1595.6	1594.9	1593.5	1592.0	1590.6	1589.2	1588.9	1588.6
157.5°	1616.6	1618.9	1621.2	1622.3	1621.5	1619.8	1618.1	1616.4	1614.7	1615.0	1615.3
160°	1639.1	1641.0	1643.0	1644.0	1643.2	1641.5	1639.8	1638.1	1636.4	1636.7	1636.9
162.5°	1660.2	1661.9	1663.6	1664.4	1663.4	1661.4	1659.5	1657.5	1655.5	1655.8	1656.1
165°	1677.4	1679.3	1681.3	1682.3	1681.2	1678.9	1676.6	1674.4	1672.1	1672.4	1672.7
167.5°	1690.6	1692.9	1695.2	1696.3	1695.2	1692.9	1690.6	1688.4	1686.1	1686.1	1686.1
170°	1702.1	1704.4	1706.7	1707.8	1706.7	1704.4	1702.1	1699.9	1697.6	1697.6	1697.6
172.5°	1709.1	1711.6	1714.1	1715.4	1714.3	1712.0	1709.7	1707.5	1705.2	1704.9	1704.7
175°	1714.8	1717.1	1719.4	1720.5	1719.5	1717.5	1715.6	1713.6	1711.6	1711.3	1711.0
177.5°	1717.3	1720.1	1723.0	1724.4	1723.3	1721.0	1718.7	1716.5	1714.2	1713.9	1713.6
180°	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7

TEST NUMBER: P1032194

CATALOG NUMBER: S123RDIW-B340D1320UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3
2.5°	543.7	541.5	539.2	539.2	534.3	529.8	527.5	528.4	525.7	522.1	518.5
5°	567.6	558.6	556.8	551.8	545.1	535.6	530.7	526.2	520.8	513.6	506.9
7.5°	589.6	577.9	571.6	566.7	553.6	540.6	529.8	522.6	513.1	502.4	494.3
10°	618.4	596.8	590.1	578.8	560.4	541.9	529.3	517.6	504.6	492.0	481.2
12.5°	641.3	616.6	604.0	592.7	568.9	545.5	524.4	510.0	494.3	480.3	466.4
15°	667.4	639.5	617.5	604.0	573.9	545.5	521.7	501.5	483.9	466.8	454.7
17.5°	680.0	644.9	635.0	615.7	572.1	543.7	514.5	492.9	471.8	452.0	437.6
20°	699.8	658.9	634.1	621.1	582.4	540.6	506.4	481.7	459.6	438.5	423.2
22.5°	701.1	656.6	640.4	615.7	568.0	531.1	499.2	469.1	443.4	423.6	407.9
25°	698.0	652.6	630.1	610.3	570.7	525.7	484.8	455.1	429.9	407.0	388.6
27.5°	696.6	640.9	619.7	599.9	555.4	510.0	476.3	442.5	413.8	393.5	374.6
30°	694.8	628.3	602.6	579.7	538.8	497.9	457.4	428.1	400.7	375.1	356.2
32.5°	683.1	611.2	585.1	560.8	516.7	475.8	443.9	412.9	383.2	359.3	342.2
35°	679.5	595.4	561.3	535.2	492.0	455.6	421.9	396.2	368.3	344.5	324.3
37.5°	669.2	579.3	542.4	509.1	464.1	429.5	404.8	379.1	352.1	326.5	310.3
40°	651.2	560.4	518.5	484.4	438.0	403.0	380.0	361.1	334.6	311.7	291.9
42.5°	624.7	541.0	496.1	460.1	408.8	376.0	357.1	339.1	316.6	292.8	276.6
45°	594.1	515.4	473.6	433.5	381.4	349.4	329.7	318.9	298.2	277.9	259.0
47.5°	552.3	488.9	447.5	406.1	353.0	322.0	306.3	295.5	281.1	259.0	243.8
50°	499.7	454.7	415.6	378.7	325.2	295.5	279.7	271.6	259.5	243.8	228.9
52.5°	441.2	415.1	382.7	348.5	296.8	268.9	254.5	248.3	239.3	224.4	211.8
55°	382.3	371.0	349.0	315.3	267.1	244.2	231.6	223.5	216.8	206.0	195.2
57.5°	329.7	324.3	309.0	282.9	242.4	218.6	207.8	202.4	197.0	188.9	178.1
60°	275.2	281.1	265.3	252.3	215.4	194.7	185.3	179.4	176.7	169.5	162.8
62.5°	228.0	233.4	224.4	214.5	188.4	170.0	164.2	158.8	157.0	150.7	143.9
65°	185.3	192.0	185.3	179.9	164.2	148.9	141.7	139.0	137.2	133.1	127.7
67.5°	147.5	154.3	151.1	144.4	139.4	126.8	122.8	120.1	119.2	116.0	111.5
70°	111.1	120.5	121.4	117.4	112.9	107.0	104.3	103.4	101.2	98.5	95.8
72.5°	80.1	90.8	91.3	91.3	88.6	88.6	85.9	84.6	84.6	81.9	78.7
75°	58.9	66.1	67.0	67.9	69.3	70.6	68.8	68.8	68.4	65.7	64.3
77.5°	39.1	45.4	47.7	50.8	52.6	52.6	53.5	54.4	53.5	52.2	51.3
80°	25.2	29.7	32.4	34.2	36.9	38.2	39.6	40.0	39.1	38.7	37.3
82.5°	16.6	18.0	19.3	21.6	24.7	27.0	27.0	26.5	27.4	27.0	26.5
85°	9.4	10.3	10.8	11.2	13.0	15.3	15.7	16.2	17.1	16.2	15.3
87.5°	3.6	4.0	4.0	4.0	4.9	5.4	6.7	8.5	8.1	7.2	7.2
90°	19.5	15.8	14.0	12.6	9.8	6.9	4.1	1.3	4.1	6.9	9.8
92.5°	25.5	23.0	21.7	22.5	24.2	25.9	27.6	29.3	27.6	25.9	24.2
95°	30.2	27.1	25.5	31.3	42.9	54.6	66.2	77.8	66.2	54.6	42.9
97.5°	84.2	98.7	105.9	109.9	117.8	125.7	133.7	141.6	133.7	125.7	117.8
100°	174.8	219.0	241.1	238.3	232.6	226.9	221.2	215.5	221.2	226.9	232.6
102.5°	242.3	291.6	316.3	314.5	310.8	307.1	303.4	299.7	303.4	307.1	310.8
105°	355.8	381.3	394.1	392.5	389.4	386.3	383.2	380.1	383.2	386.3	389.4
107.5°	483.4	479.1	477.0	475.7	473.2	470.6	468.1	465.5	468.1	470.6	473.2
110°	565.9	562.8	561.2	560.1	557.8	555.5	553.3	551.0	553.3	555.5	557.8

TEST NUMBER: P1032194

CATALOG NUMBER: S123RDIW-B340D1320UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	646.2	643.1	641.5	640.5	638.5	636.6	634.6	632.6	634.6	636.6	638.5
115°	724.4	721.9	720.6	719.8	718.1	716.4	714.7	713.0	714.7	716.4	718.1
117.5°	803.1	801.7	801.0	800.0	798.0	796.0	794.0	792.0	794.0	796.0	798.0
120°	877.5	876.6	876.2	874.9	872.4	869.8	867.3	864.7	867.3	869.8	872.4
122.5°	949.3	948.2	947.6	946.6	944.6	942.7	940.7	938.7	940.7	942.7	944.6
125°	1016.9	1015.8	1015.2	1014.1	1011.8	1009.5	1007.3	1005.0	1007.3	1009.5	1011.8
127.5°	1083.7	1082.3	1081.6	1080.5	1078.2	1075.9	1073.7	1071.4	1073.7	1075.9	1078.2
130°	1144.5	1143.4	1142.8	1141.7	1139.4	1137.1	1134.9	1132.6	1134.9	1137.1	1139.4
132.5°	1202.8	1201.9	1201.5	1200.4	1198.1	1195.8	1193.5	1191.2	1193.5	1195.8	1198.1
135°	1260.5	1259.4	1258.8	1258.0	1256.3	1254.6	1252.9	1251.2	1252.9	1254.6	1256.3
137.5°	1313.3	1312.7	1312.4	1311.3	1309.0	1306.7	1304.5	1302.2	1304.5	1306.7	1309.0
140°	1362.2	1361.3	1360.9	1360.0	1358.3	1356.6	1354.9	1353.2	1354.9	1356.6	1358.3
142.5°	1409.4	1408.5	1408.1	1407.2	1405.5	1403.8	1402.1	1400.4	1402.1	1403.8	1405.5
145°	1453.6	1453.0	1452.7	1451.7	1449.7	1447.8	1445.8	1443.8	1445.8	1447.8	1449.7
147.5°	1493.1	1492.5	1492.2	1491.5	1490.1	1488.7	1487.3	1485.9	1487.3	1488.7	1490.1
150°	1528.8	1528.3	1528.0	1527.6	1526.7	1525.8	1525.0	1524.1	1525.0	1525.8	1526.7
152.5°	1560.2	1559.9	1559.8	1559.7	1559.4	1559.1	1558.9	1558.6	1558.9	1559.1	1559.4
155°	1588.3	1588.0	1587.9	1588.2	1588.8	1589.3	1589.9	1590.5	1589.9	1589.3	1588.8
157.5°	1615.6	1615.9	1616.0	1616.0	1616.0	1616.0	1616.0	1616.0	1616.0	1616.0	1616.0
160°	1637.2	1637.5	1637.6	1637.7	1638.0	1638.3	1638.6	1638.9	1638.6	1638.3	1638.0
162.5°	1656.4	1656.7	1656.8	1657.2	1658.1	1658.9	1659.8	1660.6	1659.8	1658.9	1658.1
165°	1673.0	1673.3	1673.4	1673.8	1674.7	1675.5	1676.4	1677.2	1676.4	1675.5	1674.7
167.5°	1686.1	1686.1	1686.1	1686.7	1687.8	1688.9	1690.1	1691.2	1690.1	1688.9	1687.8
170°	1697.6	1697.6	1697.6	1698.2	1699.3	1700.4	1701.6	1702.7	1701.6	1700.4	1699.3
172.5°	1704.4	1704.1	1704.0	1704.7	1706.1	1707.5	1708.9	1710.3	1708.9	1707.5	1706.1
175°	1710.7	1710.4	1710.3	1711.0	1712.4	1713.9	1715.3	1716.7	1715.3	1713.9	1712.4
177.5°	1713.3	1713.0	1712.9	1713.6	1715.0	1716.5	1717.9	1719.3	1717.9	1716.5	1715.0
180°	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7

TEST NUMBER: P1032194

CATALOG NUMBER: S123RDIW-B340D1320UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3
2.5°	518.5	516.3	515.4	513.1	507.7	504.2	500.1	497.4	497.9	495.6	497.0
5°	502.4	501.9	498.8	494.3	486.6	482.6	475.4	471.8	470.0	470.4	467.7
7.5°	488.9	484.8	482.6	475.4	468.2	459.6	453.8	450.6	447.9	445.2	443.4
10°	473.6	470.0	466.4	458.7	448.8	440.7	432.6	429.5	425.4	423.6	422.3
12.5°	457.4	455.1	450.6	441.6	430.4	422.8	413.3	411.5	406.1	402.5	401.6
15°	442.5	441.2	433.1	422.8	411.5	403.9	395.8	390.4	381.4	383.2	380.0
17.5°	426.8	421.0	416.0	402.1	396.7	385.0	375.5	372.8	366.5	362.5	358.4
20°	409.3	405.7	399.4	390.4	377.3	363.8	356.6	352.1	348.5	342.2	340.4
22.5°	392.6	388.1	382.7	371.0	359.8	348.5	338.6	334.6	330.1	325.6	322.9
25°	379.6	372.8	367.0	352.6	341.3	331.9	325.6	318.9	312.6	309.9	309.0
27.5°	359.3	355.3	349.4	336.0	325.6	315.3	309.4	304.9	298.2	295.0	292.3
30°	346.3	338.2	331.5	320.7	310.3	299.1	293.7	288.3	284.2	280.2	277.0
32.5°	328.8	322.5	317.1	306.3	295.9	285.6	279.7	271.6	269.4	266.2	262.6
35°	311.7	307.6	301.8	290.1	278.8	271.6	265.3	257.7	255.0	252.8	249.6
37.5°	295.5	289.6	285.6	274.3	264.4	255.9	251.0	244.7	242.9	240.2	237.9
40°	281.5	275.7	271.6	260.4	250.1	241.1	237.9	231.6	228.9	225.8	224.4
42.5°	265.8	260.8	255.4	247.4	236.6	227.6	221.3	217.7	214.1	212.7	210.0
45°	249.2	244.7	240.6	231.6	220.4	214.1	208.7	203.7	201.0	198.8	197.0
47.5°	234.8	230.7	225.3	215.4	206.4	200.6	195.2	190.2	187.5	184.8	182.6
50°	218.1	215.9	210.0	200.6	192.0	185.3	180.3	175.8	174.0	170.9	167.3
52.5°	203.3	199.2	194.3	186.6	179.0	170.9	164.2	161.5	158.3	156.5	153.4
55°	185.7	183.0	177.6	170.9	162.8	156.1	151.1	147.5	143.5	141.7	137.6
57.5°	170.9	166.0	163.3	154.7	147.1	140.3	136.7	133.1	128.6	125.9	124.1
60°	154.7	150.2	146.2	139.0	133.6	126.4	121.0	117.8	114.7	111.1	109.3
62.5°	139.0	135.4	130.4	124.6	117.8	112.0	107.9	103.4	101.6	98.0	96.7
65°	121.9	119.2	115.1	108.4	103.0	98.0	94.0	90.4	88.6	87.2	86.3
67.5°	106.6	103.0	100.3	94.4	88.6	84.6	82.3	80.1	77.8	76.5	75.1
70°	90.8	88.1	85.4	80.1	76.0	72.4	70.6	68.8	67.5	66.1	64.8
72.5°	74.7	73.3	70.6	67.0	63.9	61.2	59.8	57.6	56.2	54.0	53.1
75°	61.6	59.4	58.0	54.9	52.2	49.9	48.1	45.4	43.6	42.7	42.3
77.5°	48.6	47.7	45.9	43.2	41.8	39.6	36.9	36.0	35.1	35.1	34.6
80°	36.4	35.1	33.7	31.5	30.1	28.3	28.3	28.3	27.9	28.3	27.9
82.5°	24.7	23.8	22.9	21.6	21.1	21.1	21.6	21.6	21.6	21.6	21.6
85°	14.4	14.4	14.4	14.8	14.4	14.4	14.8	15.3	14.8	14.8	14.4
87.5°	6.7	6.7	7.2	7.2	7.6	7.6	7.6	7.6	7.6	7.6	8.1
90°	12.6	14.0	15.8	19.5	23.2	26.9	30.6	31.7	32.9	34.0	35.1
92.5°	22.5	21.7	23.0	25.5	28.1	30.6	33.2	35.2	37.2	39.1	41.1
95°	31.3	25.5	27.1	30.2	33.3	36.4	39.5	41.5	43.5	45.5	47.5
97.5°	109.9	105.9	98.7	84.2	69.7	55.3	40.8	43.1	45.3	47.6	49.9
100°	238.3	241.1	219.0	174.8	130.5	86.3	42.1	44.4	46.6	48.9	51.2
102.5°	314.5	316.3	291.6	242.3	193.0	143.7	94.4	85.0	75.7	66.3	57.0
105°	392.5	394.1	381.3	355.8	330.3	304.8	279.3	229.1	179.0	128.8	78.7
107.5°	475.7	477.0	479.1	483.4	487.6	491.9	496.1	452.5	408.8	365.2	321.5
110°	560.1	561.2	562.8	565.9	569.0	572.1	575.2	565.8	556.5	547.1	537.8

TEST NUMBER: P1032194

CATALOG NUMBER: S123RDIW-B340D1320UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	640.5	641.5	643.1	646.2	649.3	652.5	655.6	658.1	660.7	663.2	665.7
115°	719.8	720.6	721.9	724.4	727.0	729.5	732.1	734.9	737.7	740.6	743.4
117.5°	800.0	801.0	801.7	803.1	804.5	805.9	807.3	809.6	811.8	814.1	816.4
120°	874.9	876.2	876.6	877.5	878.3	879.2	880.0	882.3	884.5	886.8	889.1
122.5°	946.6	947.6	948.2	949.3	950.4	951.6	952.7	954.1	955.5	957.0	958.4
125°	1014.1	1015.2	1015.8	1016.9	1018.0	1019.2	1020.3	1020.9	1021.5	1022.0	1022.6
127.5°	1080.5	1081.6	1082.3	1083.7	1085.1	1086.5	1087.9	1088.8	1089.6	1090.5	1091.4
130°	1141.7	1142.8	1143.4	1144.5	1145.6	1146.8	1147.9	1149.0	1150.2	1151.3	1152.4
132.5°	1200.4	1201.5	1201.9	1202.8	1203.6	1204.5	1205.3	1206.4	1207.6	1208.7	1209.8
135°	1258.0	1258.8	1259.4	1260.5	1261.6	1262.8	1263.9	1264.8	1265.6	1266.5	1267.4
137.5°	1311.3	1312.4	1312.7	1313.3	1313.8	1314.4	1315.0	1316.4	1317.8	1319.2	1320.6
140°	1360.0	1360.9	1361.3	1362.2	1363.0	1363.9	1364.7	1365.8	1367.0	1368.1	1369.2
142.5°	1407.2	1408.1	1408.5	1409.4	1410.2	1411.1	1411.9	1412.7	1413.6	1414.4	1415.3
145°	1451.7	1452.7	1453.0	1453.6	1454.1	1454.7	1455.3	1455.9	1456.4	1457.0	1457.5
147.5°	1491.5	1492.2	1492.5	1493.1	1493.6	1494.2	1494.8	1495.4	1495.9	1496.5	1497.0
150°	1527.6	1528.0	1528.3	1528.8	1529.4	1529.9	1530.5	1531.1	1531.7	1532.2	1532.8
152.5°	1559.7	1559.8	1559.9	1560.2	1560.5	1560.8	1561.1	1562.2	1563.4	1564.5	1565.6
155°	1588.2	1587.9	1588.0	1588.3	1588.6	1588.9	1589.2	1590.6	1592.0	1593.5	1594.9
157.5°	1616.0	1616.0	1615.9	1615.6	1615.3	1615.0	1614.7	1616.4	1618.1	1619.8	1621.5
160°	1637.7	1637.6	1637.5	1637.2	1636.9	1636.7	1636.4	1638.1	1639.8	1641.5	1643.2
162.5°	1657.2	1656.8	1656.7	1656.4	1656.1	1655.8	1655.5	1657.5	1659.5	1661.4	1663.4
165°	1673.8	1673.4	1673.3	1673.0	1672.7	1672.4	1672.1	1674.4	1676.6	1678.9	1681.2
167.5°	1686.7	1686.1	1686.1	1686.1	1686.1	1686.1	1686.1	1688.4	1690.6	1692.9	1695.2
170°	1698.2	1697.6	1697.6	1697.6	1697.6	1697.6	1697.6	1699.9	1702.1	1704.4	1706.7
172.5°	1704.7	1704.0	1704.1	1704.4	1704.7	1704.9	1705.2	1707.5	1709.7	1712.0	1714.3
175°	1711.0	1710.3	1710.4	1710.7	1711.0	1711.3	1711.6	1713.6	1715.6	1717.5	1719.5
177.5°	1713.6	1712.9	1713.0	1713.3	1713.6	1713.9	1714.2	1716.5	1718.7	1721.0	1723.3
180°	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7

TEST NUMBER: P1032194

CATALOG NUMBER: S123RDIW-B340D1320UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3
2.5°	496.5	497.0	495.6	492.9	492.5	493.4	496.1	495.2	492.9	497.0	493.4
5°	469.1	466.8	465.9	466.8	464.1	462.8	465.5	464.1	465.5	465.9	467.3
7.5°	442.5	443.0	440.3	440.7	437.1	438.0	438.0	438.0	439.4	440.3	442.1
10°	419.6	420.5	417.4	417.8	415.1	413.3	414.7	417.4	417.4	417.4	418.3
12.5°	401.2	397.1	394.9	394.4	391.3	390.4	393.1	394.0	396.2	396.2	397.6
15°	378.2	377.3	375.5	375.5	367.9	369.7	370.6	373.7	378.2	374.6	375.5
17.5°	357.5	355.3	353.0	352.1	351.2	348.5	352.1	351.7	354.4	354.8	356.2
20°	339.1	337.3	332.8	333.3	334.2	330.1	332.4	332.4	335.1	337.8	340.9
22.5°	321.1	319.3	317.1	318.0	315.3	314.4	314.4	316.6	319.8	322.0	321.6
25°	307.2	304.0	302.7	301.3	300.0	300.9	299.5	301.8	304.0	305.4	304.0
27.5°	291.4	290.1	287.4	286.0	283.8	284.7	285.6	287.4	288.7	288.7	290.1
30°	276.1	274.3	273.4	272.1	272.1	270.3	270.7	272.5	273.9	275.2	277.0
32.5°	261.3	259.9	258.6	258.6	257.7	257.2	256.8	259.5	259.5	262.2	262.2
35°	249.2	246.9	246.9	244.7	245.6	245.1	244.2	246.0	246.5	248.3	247.8
37.5°	235.7	235.7	234.8	232.5	230.7	231.2	233.4	233.4	234.8	234.3	235.7
40°	222.2	221.3	221.3	219.9	219.5	219.0	219.5	219.9	222.2	221.7	222.2
42.5°	208.7	209.1	206.9	206.9	206.9	205.5	206.0	206.4	207.3	208.2	209.6
45°	195.6	194.7	194.3	193.4	192.5	192.9	192.5	194.3	193.8	194.7	196.1
47.5°	181.7	180.3	179.9	178.1	178.1	179.0	178.5	179.9	180.3	181.7	180.8
50°	168.2	166.4	165.1	165.5	162.8	163.7	163.7	165.1	166.4	166.9	167.8
52.5°	152.5	152.0	151.6	149.3	148.9	148.4	148.9	149.3	151.1	152.5	152.9
55°	137.2	136.7	134.0	133.1	131.8	131.8	132.7	133.1	136.3	136.7	138.5
57.5°	123.2	121.9	118.7	118.3	118.3	118.3	116.9	118.7	119.6	121.9	121.9
60°	107.9	107.9	105.2	105.2	105.7	105.2	105.2	105.7	105.7	107.5	108.4
62.5°	95.8	95.3	95.3	94.4	94.0	94.4	94.0	94.0	94.4	95.8	97.1
65°	85.0	84.6	84.1	83.7	82.8	82.8	83.2	84.1	84.1	85.0	85.4
67.5°	74.7	74.7	73.8	73.8	73.3	72.9	73.3	72.9	74.7	74.7	75.1
70°	64.3	63.9	62.5	62.1	60.7	61.2	61.2	62.5	63.0	63.9	64.8
72.5°	51.7	51.7	50.8	49.9	50.4	49.5	49.5	49.9	49.9	51.3	51.7
75°	42.7	41.8	41.4	41.8	41.4	42.3	41.4	41.4	42.3	42.3	42.3
77.5°	35.1	35.1	34.6	34.6	35.1	34.6	35.1	35.1	35.1	34.6	35.1
80°	28.8	28.3	28.3	28.3	27.9	27.9	27.9	27.9	27.9	27.9	27.9
82.5°	21.6	21.6	21.1	21.6	21.6	21.1	21.6	21.1	21.1	21.6	21.6
85°	14.4	15.3	14.4	14.4	14.8	14.8	15.3	14.8	15.3	14.4	14.8
87.5°	7.6	8.1	8.1	7.6	7.6	8.1	8.1	8.1	8.5	7.6	8.1
90°	35.7	36.0	36.6	37.1	37.7	38.3	37.7	37.1	36.6	36.0	35.7
92.5°	42.1	42.2	42.5	42.8	43.1	43.4	43.1	42.8	42.5	42.2	42.1
95°	48.5	48.5	48.5	48.5	48.5	48.5	48.5	48.5	48.5	48.5	48.5
97.5°	51.0	51.1	51.4	51.7	52.0	52.3	52.0	51.7	51.4	51.1	51.0
100°	52.3	52.4	52.7	53.0	53.3	53.6	53.3	53.0	52.7	52.4	52.3
102.5°	52.3	52.6	53.1	53.7	54.2	54.8	54.2	53.7	53.1	52.6	52.3
105°	53.6	53.9	54.4	55.0	55.5	56.1	55.5	55.0	54.4	53.9	53.6
107.5°	299.7	281.1	244.0	206.9	169.7	132.6	169.7	206.9	244.0	281.1	299.7
110°	533.1	512.8	472.3	431.8	391.2	350.7	391.2	431.8	472.3	512.8	533.1



TEST NUMBER: P1032194

CATALOG NUMBER: S123RDIW-B340D1320UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	667.0	666.7	666.2	665.6	665.1	664.5	665.1	665.6	666.2	666.7	667.0
115°	744.8	745.4	746.5	747.6	748.8	749.9	748.8	747.6	746.5	745.4	744.8
117.5°	817.5	817.6	817.9	818.2	818.5	818.8	818.5	818.2	817.9	817.6	817.5
120°	890.2	890.2	890.2	890.2	890.2	890.2	890.2	890.2	890.2	890.2	890.2
122.5°	959.1	959.2	959.5	959.8	960.1	960.4	960.1	959.8	959.5	959.2	959.1
125°	1022.9	1023.2	1023.7	1024.3	1024.8	1025.4	1024.8	1024.3	1023.7	1023.2	1022.9
127.5°	1091.8	1091.5	1090.9	1090.4	1089.8	1089.2	1089.8	1090.4	1090.9	1091.5	1091.8
130°	1153.0	1152.7	1152.1	1151.6	1151.0	1150.4	1151.0	1151.6	1152.1	1152.7	1153.0
132.5°	1210.4	1210.0	1209.1	1208.3	1207.4	1206.6	1207.4	1208.3	1209.1	1210.0	1210.4
135°	1267.8	1267.4	1266.5	1265.6	1264.8	1263.9	1264.8	1265.6	1266.5	1267.4	1267.8
137.5°	1321.3	1321.0	1320.5	1319.9	1319.4	1318.8	1319.4	1319.9	1320.5	1321.0	1321.3
140°	1369.8	1369.5	1369.0	1368.4	1367.9	1367.3	1367.9	1368.4	1369.0	1369.5	1369.8
142.5°	1415.7	1415.3	1414.4	1413.6	1412.7	1411.9	1412.7	1413.6	1414.4	1415.3	1415.7
145°	1457.8	1457.8	1457.8	1457.8	1457.8	1457.8	1457.8	1457.8	1457.8	1457.8	1457.8
147.5°	1497.3	1496.6	1495.2	1493.8	1492.4	1491.0	1492.4	1493.8	1495.2	1496.6	1497.3
150°	1533.1	1532.7	1531.8	1530.9	1530.1	1529.2	1530.1	1530.9	1531.8	1532.7	1533.1
152.5°	1566.2	1565.5	1564.1	1562.6	1561.2	1559.8	1561.2	1562.6	1564.1	1565.5	1566.2
155°	1595.6	1594.7	1593.0	1591.3	1589.6	1587.9	1589.6	1591.3	1593.0	1594.7	1595.6
157.5°	1622.3	1621.2	1618.9	1616.6	1614.4	1612.1	1614.4	1616.6	1618.9	1621.2	1622.3
160°	1644.0	1643.0	1641.0	1639.1	1637.1	1635.1	1637.1	1639.1	1641.0	1643.0	1644.0
162.5°	1664.4	1663.6	1661.9	1660.2	1658.5	1656.8	1658.5	1660.2	1661.9	1663.6	1664.4
165°	1682.3	1681.3	1679.3	1677.4	1675.4	1673.4	1675.4	1677.4	1679.3	1681.3	1682.3
167.5°	1696.3	1695.2	1692.9	1690.6	1688.4	1686.1	1688.4	1690.6	1692.9	1695.2	1696.3
170°	1707.8	1706.7	1704.4	1702.1	1699.9	1697.6	1699.9	1702.1	1704.4	1706.7	1707.8
172.5°	1715.4	1714.1	1711.6	1709.1	1706.5	1704.0	1706.5	1709.1	1711.6	1714.1	1715.4
175°	1720.5	1719.4	1717.1	1714.8	1712.6	1710.3	1712.6	1714.8	1717.1	1719.4	1720.5
177.5°	1724.4	1723.0	1720.1	1717.3	1714.4	1711.6	1714.4	1717.3	1720.1	1723.0	1724.4
180°	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7

TEST NUMBER: P1032194

CATALOG NUMBER: S123RDIW-B340D1320UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3
2.5°	497.0	498.8	497.0	493.4	497.0	499.2	501.5	505.1	506.9	506.9	509.5
5°	468.6	472.2	470.9	470.0	473.6	475.8	479.4	483.9	488.9	492.0	495.6
7.5°	443.4	445.7	447.9	447.9	451.5	456.5	461.9	467.3	473.6	478.1	480.8
10°	421.4	423.2	424.5	426.3	431.7	437.1	444.3	451.1	456.5	461.4	465.9
12.5°	400.3	403.0	406.1	407.5	411.5	418.3	425.0	433.1	441.6	446.6	451.1
15°	380.0	381.4	385.0	389.0	392.6	399.8	408.4	416.9	424.1	431.7	435.8
17.5°	359.3	359.8	369.2	367.0	378.7	385.4	389.9	398.0	409.7	416.0	422.3
20°	339.1	343.6	347.6	349.9	356.2	363.8	376.9	383.2	392.6	398.5	403.9
22.5°	323.4	330.1	330.1	335.5	338.6	345.8	355.3	367.4	377.8	381.8	389.5
25°	309.4	312.6	318.0	319.8	325.6	331.9	338.2	351.2	362.5	367.9	373.3
27.5°	291.4	295.5	302.7	302.7	310.3	317.1	324.7	333.3	344.5	352.1	358.0
30°	277.5	281.5	284.7	289.6	292.8	299.1	312.6	318.9	328.8	335.5	342.7
32.5°	264.4	267.6	270.3	275.7	279.3	286.5	293.7	304.9	313.5	319.8	327.4
35°	250.1	253.2	256.8	260.8	266.2	273.0	279.7	289.2	297.7	303.6	309.9
37.5°	236.6	238.8	244.2	246.9	251.4	257.7	266.2	276.1	283.8	288.3	294.6
40°	223.5	225.3	229.4	234.3	237.5	242.4	251.4	259.9	269.4	274.8	279.7
42.5°	209.6	211.8	215.4	220.4	225.3	230.7	235.7	245.6	254.1	258.6	264.0
45°	197.4	198.8	201.5	206.4	211.4	215.4	223.1	232.1	240.2	243.8	249.6
47.5°	183.0	184.4	188.4	190.7	196.1	201.5	209.1	218.1	225.3	228.9	234.3
50°	168.2	169.5	172.2	177.2	180.8	186.6	193.4	201.0	210.0	215.0	218.1
52.5°	153.8	156.5	158.8	162.8	167.3	173.1	179.4	186.6	194.3	199.2	202.8
55°	139.4	141.7	144.4	146.6	152.0	157.4	164.6	171.3	178.1	182.6	186.6
57.5°	123.2	126.4	129.1	133.6	137.6	142.1	150.2	155.6	163.7	166.9	170.4
60°	109.3	112.4	114.7	118.3	121.9	127.7	133.1	139.9	146.6	150.7	155.2
62.5°	97.6	98.9	100.3	103.9	107.5	112.9	118.3	125.0	132.2	134.5	138.1
65°	85.9	87.2	89.5	92.6	95.3	98.5	104.3	109.7	116.5	120.1	121.4
67.5°	76.0	77.4	77.8	80.1	82.3	85.9	89.0	94.4	100.7	103.0	105.7
70°	64.8	67.0	67.5	69.3	70.2	72.4	76.0	80.1	85.0	89.0	91.3
72.5°	51.7	54.9	55.8	58.5	59.8	62.1	64.8	67.9	71.1	72.9	74.7
75°	42.3	43.2	43.6	45.9	48.1	51.3	52.6	54.4	57.1	59.4	61.2
77.5°	35.1	35.5	36.0	36.0	36.4	38.2	40.9	43.2	45.0	45.9	47.2
80°	28.3	27.9	27.9	28.3	28.3	28.3	29.2	32.4	33.3	35.5	35.1
82.5°	22.0	21.1	21.6	21.1	21.1	21.1	21.1	21.6	21.6	22.9	23.8
85°	14.4	14.8	14.4	14.4	13.9	14.4	13.9	13.9	13.5	13.5	13.0
87.5°	7.6	8.1	7.6	7.6	7.2	7.6	7.2	7.2	6.7	6.7	5.8
90°	35.1	34.0	32.9	31.7	30.6	26.9	23.2	19.5	15.8	14.0	12.6
92.5°	41.1	39.1	37.2	35.2	33.2	30.6	28.1	25.5	23.0	21.7	22.5
95°	47.5	45.5	43.5	41.5	39.5	36.4	33.3	30.2	27.1	25.5	31.3
97.5°	49.9	47.6	45.3	43.1	40.8	55.3	69.7	84.2	98.7	105.9	109.9
100°	51.2	48.9	46.6	44.4	42.1	86.3	130.5	174.8	219.0	241.1	238.3
102.5°	57.0	66.3	75.7	85.0	94.4	143.7	193.0	242.3	291.6	316.3	314.5
105°	78.7	128.8	179.0	229.1	279.3	304.8	330.3	355.8	381.3	394.1	392.5
107.5°	321.5	365.2	408.8	452.5	496.1	491.9	487.6	483.4	479.1	477.0	475.7
110°	537.8	547.1	556.5	565.8	575.2	572.1	569.0	565.9	562.8	561.2	560.1

TEST NUMBER: P1032194

CATALOG NUMBER: S123RDIW-B340D1320UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	665.7	663.2	660.7	658.1	655.6	652.5	649.3	646.2	643.1	641.5	640.5
115°	743.4	740.6	737.7	734.9	732.1	729.5	727.0	724.4	721.9	720.6	719.8
117.5°	816.4	814.1	811.8	809.6	807.3	805.9	804.5	803.1	801.7	801.0	800.0
120°	889.1	886.8	884.5	882.3	880.0	879.2	878.3	877.5	876.6	876.2	874.9
122.5°	958.4	957.0	955.5	954.1	952.7	951.6	950.4	949.3	948.2	947.6	946.6
125°	1022.6	1022.0	1021.5	1020.9	1020.3	1019.2	1018.0	1016.9	1015.8	1015.2	1014.1
127.5°	1091.4	1090.5	1089.6	1088.8	1087.9	1086.5	1085.1	1083.7	1082.3	1081.6	1080.5
130°	1152.4	1151.3	1150.2	1149.0	1147.9	1146.8	1145.6	1144.5	1143.4	1142.8	1141.7
132.5°	1209.8	1208.7	1207.6	1206.4	1205.3	1204.5	1203.6	1202.8	1201.9	1201.5	1200.4
135°	1267.4	1266.5	1265.6	1264.8	1263.9	1262.8	1261.6	1260.5	1259.4	1258.8	1258.0
137.5°	1320.6	1319.2	1317.8	1316.4	1315.0	1314.4	1313.8	1313.3	1312.7	1312.4	1311.3
140°	1369.2	1368.1	1367.0	1365.8	1364.7	1363.9	1363.0	1362.2	1361.3	1360.9	1360.0
142.5°	1415.3	1414.4	1413.6	1412.7	1411.9	1411.1	1410.2	1409.4	1408.5	1408.1	1407.2
145°	1457.5	1457.0	1456.4	1455.9	1455.3	1454.7	1454.1	1453.6	1453.0	1452.7	1451.7
147.5°	1497.0	1496.5	1495.9	1495.4	1494.8	1494.2	1493.6	1493.1	1492.5	1492.2	1491.5
150°	1532.8	1532.2	1531.7	1531.1	1530.5	1529.9	1529.4	1528.8	1528.3	1528.0	1527.6
152.5°	1565.6	1564.5	1563.4	1562.2	1561.1	1560.8	1560.5	1560.2	1559.9	1559.8	1559.7
155°	1594.9	1593.5	1592.0	1590.6	1589.2	1588.9	1588.6	1588.3	1588.0	1587.9	1588.2
157.5°	1621.5	1619.8	1618.1	1616.4	1614.7	1615.0	1615.3	1615.6	1615.9	1616.0	1616.0
160°	1643.2	1641.5	1639.8	1638.1	1636.4	1636.7	1636.9	1637.2	1637.5	1637.6	1637.7
162.5°	1663.4	1661.4	1659.5	1657.5	1655.5	1655.8	1656.1	1656.4	1656.7	1656.8	1657.2
165°	1681.2	1678.9	1676.6	1674.4	1672.1	1672.4	1672.7	1673.0	1673.3	1673.4	1673.8
167.5°	1695.2	1692.9	1690.6	1688.4	1686.1	1686.1	1686.1	1686.1	1686.1	1686.1	1686.7
170°	1706.7	1704.4	1702.1	1699.9	1697.6	1697.6	1697.6	1697.6	1697.6	1697.6	1698.2
172.5°	1714.3	1712.0	1709.7	1707.5	1705.2	1704.9	1704.7	1704.4	1704.1	1704.0	1704.7
175°	1719.5	1717.5	1715.6	1713.6	1711.6	1711.3	1711.0	1710.7	1710.4	1710.3	1711.0
177.5°	1723.3	1721.0	1718.7	1716.5	1714.2	1713.9	1713.6	1713.3	1713.0	1712.9	1713.6
180°	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7

TEST NUMBER: P1032194

CATALOG NUMBER: S123RDIW-B340D1320UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	525.3	525.3	525.3	525.3
2.5°	511.8	514.9	521.2	526.6
5°	501.0	506.0	515.4	524.8
7.5°	488.0	495.6	507.7	520.8
10°	475.4	485.3	500.1	515.4
12.5°	462.8	473.1	488.9	508.6
15°	447.9	458.7	477.6	501.5
17.5°	434.9	449.3	466.4	490.2
20°	421.0	431.7	453.8	479.0
22.5°	403.4	421.4	442.1	468.6
25°	389.5	405.2	425.9	456.0
27.5°	372.4	390.8	416.0	442.5
30°	358.4	373.7	397.1	429.0
32.5°	342.2	360.2	384.5	416.0
35°	327.9	343.1	366.1	398.0
37.5°	310.8	327.4	353.0	381.4
40°	295.9	312.1	336.4	362.9
42.5°	277.9	295.0	319.3	341.8
45°	263.5	279.3	298.6	319.3
47.5°	246.0	262.6	281.5	295.9
50°	230.3	245.6	260.4	272.5
52.5°	213.2	227.1	240.6	249.6
55°	197.4	208.2	219.0	225.3
57.5°	179.0	189.3	198.3	201.9
60°	162.8	171.3	177.2	181.2
62.5°	145.7	152.0	156.5	158.8
65°	129.1	133.6	135.8	138.1
67.5°	112.0	116.0	117.4	120.1
70°	94.0	98.5	99.4	100.7
72.5°	80.5	80.5	82.3	84.1
75°	64.3	65.2	66.1	66.1
77.5°	50.4	50.4	51.3	51.7
80°	36.9	37.3	37.3	36.9
82.5°	25.2	26.1	25.2	24.7
85°	13.9	15.7	14.8	14.8
87.5°	5.8	5.8	6.7	5.8
90°	9.8	6.9	4.1	1.3
92.5°	24.2	25.9	27.6	29.3
95°	42.9	54.6	66.2	77.8
97.5°	117.8	125.7	133.7	141.6
100°	232.6	226.9	221.2	215.5
102.5°	310.8	307.1	303.4	299.7
105°	389.4	386.3	383.2	380.1
107.5°	473.2	470.6	468.1	465.5
110°	557.8	555.5	553.3	551.0



TEST NUMBER: P1032194

CATALOG NUMBER: S123RDIW-B340D1320UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	638.5	636.6	634.6	632.6
115°	718.1	716.4	714.7	713.0
117.5°	798.0	796.0	794.0	792.0
120°	872.4	869.8	867.3	864.7
122.5°	944.6	942.7	940.7	938.7
125°	1011.8	1009.5	1007.3	1005.0
127.5°	1078.2	1075.9	1073.7	1071.4
130°	1139.4	1137.1	1134.9	1132.6
132.5°	1198.1	1195.8	1193.5	1191.2
135°	1256.3	1254.6	1252.9	1251.2
137.5°	1309.0	1306.7	1304.5	1302.2
140°	1358.3	1356.6	1354.9	1353.2
142.5°	1405.5	1403.8	1402.1	1400.4
145°	1449.7	1447.8	1445.8	1443.8
147.5°	1490.1	1488.7	1487.3	1485.9
150°	1526.7	1525.8	1525.0	1524.1
152.5°	1559.4	1559.1	1558.9	1558.6
155°	1588.8	1589.3	1589.9	1590.5
157.5°	1616.0	1616.0	1616.0	1616.0
160°	1638.0	1638.3	1638.6	1638.9
162.5°	1658.1	1658.9	1659.8	1660.6
165°	1674.7	1675.5	1676.4	1677.2
167.5°	1687.8	1688.9	1690.1	1691.2
170°	1699.3	1700.4	1701.6	1702.7
172.5°	1706.1	1707.5	1708.9	1710.3
175°	1712.4	1713.9	1715.3	1716.7
177.5°	1715.0	1716.5	1717.9	1719.3
180°	1716.7	1716.7	1716.7	1716.7

(END OF REPORT)