

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031659

Luminaire Tested: S123DIW-B340D460UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031659
REPORT IS A COMBINATION OF REPORTS P991432 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B340D460UB40-4F0-XX-W2A-F1
Description: Define 3 Direct/Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2973.0 lumens
Efficiency: N/A
Efficacy: 113.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 26.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031659

CATALOG NUMBER: S123DIW-B340D460UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1031659

CATALOG NUMBER: S123DIW-B340D460UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52
1	97	92	89	85	89	85	82	79	71	69	66	58	56	55	46	45	44
2	88	81	75	69	81	74	69	64	62	58	55	51	48	46	41	39	37
3	80	71	64	58	73	65	59	54	55	50	46	45	42	39	36	34	32
4	73	63	55	49	67	58	51	46	49	43	39	40	36	33	32	29	27
5	67	56	48	42	62	52	44	39	43	38	34	36	32	29	29	26	24
6	62	50	42	36	57	46	39	34	39	34	29	32	28	25	26	23	21
7	57	45	37	32	52	42	35	30	35	30	26	30	25	22	24	21	18
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	17
9	50	37	30	25	45	35	28	23	30	24	21	25	21	18	20	17	15
10	46	34	27	22	42	32	25	21	27	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5646	5646	5646
5°	5659	5450	5442
10°	5610	5266	5212
15°	5531	5074	4961
20°	5442	4861	4713
25°	5326	4637	4446
30°	5200	4404	4166
35°	5066	4167	3888
40°	4928	3917	3615
45°	4775	3674	3329
50°	4620	3403	3043
55°	4421	3121	2752
60°	4216	2809	2443
65°	4022	2472	2121
70°	3746	2100	1745
75°	3344	1662	1355
80°	2888	1169	958
85°	2257	627	479

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4775 cd/sqm

TEST NUMBER: P1031659

CATALOG NUMBER: S123DIW-B340D460UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.4	1.7
10°-20°	139.6	4.7
20°-30°	206.2	6.9
30°-40°	240.8	8.1
40°-50°	242.1	8.1
50°-60°	212.7	7.2
60°-70°	158.4	5.3
70°-80°	90.1	3.0
80°-90°	26.8	0.9
90°-100°	37.3	1.3
100°-110°	113.0	3.8
110°-120°	192.4	6.5
120°-130°	253.0	8.5
130°-140°	284.4	9.6
140°-150°	279.6	9.4
150°-160°	235.4	7.9
160°-170°	156.7	5.3
170°-180°	54.9	1.8
0°-30°	395.3	13.3
0°-40°	636.1	21.4
0°-60°	1090.8	36.7
0°-90°	1366.2	46.0
90°-120°	342.7	11.5
90°-150°	1159.8	39.0
90°-180°	1607.0	54.1
0°-180°	2973.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	524	524	524	524	524	
5°	525	523	518	522	521	50
15°	500	498	492	496	493	141
25°	454	451	445	446	444	209
35°	392	390	384	381	379	245
45°	322	320	314	308	306	248
55°	244	244	238	233	230	219
65°	166	164	160	156	155	164
75°	88	86	85	82	81	94
85°	24	22	22	22	22	25
90°	0	5	11	13	14	4
95°	27	30	34	36	36	30
105°	102	103	108	108	108	110
115°	194	195	194	194	194	192
125°	283	285	284	282	280	253
135°	368	370	370	368	367	283
145°	446	447	448	448	446	279
155°	511	511	511	513	510	235
165°	556	555	555	558	554	157
175°	578	577	577	579	576	55
180°	580	580	580	580	580	

TEST NUMBER: P1031659

CATALOG NUMBER: S123DIW-B340D460UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	524.5	524.5	524.5	524.5	524.5
2.5°	526.7	524.9	520.0	524.5	524.0
5°	524.9	522.7	517.7	522.2	521.3
7.5°	520.9	518.6	513.7	517.7	517.3
10°	515.5	513.2	507.3	511.4	510.5
12.5°	508.2	506.4	501.0	503.7	503.3
15°	499.7	497.9	492.0	495.6	492.9
17.5°	490.2	488.0	482.1	484.8	483.9
20°	479.4	476.7	470.8	472.6	471.3
22.5°	467.2	464.5	458.6	460.0	458.2
25°	453.7	451.0	445.1	445.6	444.2
27.5°	439.7	437.0	430.7	431.1	429.8
30°	424.4	422.1	415.8	415.8	412.6
32.5°	409.0	405.9	401.4	398.2	396.9
35°	392.3	389.6	383.8	381.1	378.8
37.5°	375.7	372.1	366.2	363.0	361.7
40°	358.1	355.4	349.1	345.4	343.6
42.5°	340.5	337.3	331.0	327.4	325.6
45°	321.5	319.7	313.9	308.5	306.2
47.5°	303.1	300.3	294.9	289.5	287.7
50°	284.1	281.9	276.0	271.0	268.3
52.5°	264.3	262.9	256.6	252.5	249.8
55°	244.0	243.5	237.7	232.7	230.4
57.5°	225.0	223.2	218.7	214.2	211.5
60°	204.3	203.8	198.4	194.4	192.1
62.5°	185.8	184.4	179.0	175.0	173.6
65°	166.4	164.2	159.6	156.0	154.7
67.5°	145.7	143.9	140.3	137.1	135.3
70°	127.2	124.5	121.8	118.6	116.4
72.5°	107.8	106.0	102.8	100.1	99.2
75°	87.9	86.1	84.8	82.5	81.2
77.5°	70.4	69.5	67.6	65.8	65.8
80°	53.2	51.9	51.0	50.5	50.5
82.5°	36.5	36.5	36.5	35.6	35.2
85°	23.5	22.5	22.5	21.6	21.6
87.5°	11.7	10.4	9.9	9.5	9.5
90°	0.5	5.0	10.9	12.8	13.7
92.5°	13.7	16.4	19.1	20.5	19.6
95°	26.9	30.1	33.7	35.5	35.5
97.5°	44.2	46.5	49.2	51.5	51.0
100°	62.0	64.7	67.0	68.3	69.2
102.5°	82.5	83.8	87.0	88.4	87.9
105°	102.5	103.4	107.5	107.5	108.4
107.5°	126.2	126.6	128.5	129.8	129.4
110°	148.0	149.0	149.9	151.7	150.8

TEST NUMBER: P1031659

CATALOG NUMBER: S123DIW-B340D460UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	170.8	171.3	171.3	173.6	173.6
115°	193.6	195.0	194.1	194.5	194.1
117.5°	216.8	217.3	216.4	216.4	215.0
120°	238.2	241.0	238.7	238.2	237.3
122.5°	260.6	262.4	261.5	260.1	258.7
125°	283.3	284.7	283.8	282.0	280.2
127.5°	304.3	307.0	306.1	303.4	301.6
130°	325.2	328.9	327.5	325.7	322.5
132.5°	346.2	349.8	348.9	346.7	344.4
135°	367.6	370.3	369.9	368.1	367.2
137.5°	387.2	389.5	390.8	388.6	387.2
140°	407.7	410.0	410.4	410.0	406.8
142.5°	426.4	428.7	429.6	429.1	426.8
145°	446.0	446.9	448.2	447.8	446.0
147.5°	462.8	464.6	466.0	466.0	463.3
150°	480.6	481.5	482.4	482.4	479.7
152.5°	495.2	496.5	497.0	497.9	495.6
155°	510.7	510.7	511.1	512.9	509.7
157.5°	523.9	523.4	523.9	525.7	523.0
160°	536.2	535.2	535.2	537.5	535.7
162.5°	547.1	545.7	546.2	548.5	545.3
165°	556.2	554.8	554.8	557.6	554.4
167.5°	563.9	562.1	562.6	565.3	562.6
170°	570.3	568.5	568.5	571.7	568.5
172.5°	575.3	573.5	573.5	576.2	573.1
175°	578.5	576.7	576.7	579.4	576.2
177.5°	580.3	578.5	578.5	581.3	578.1
180°	579.9	579.9	579.9	579.9	579.9

(END OF REPORT)