

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032253

Luminaire Tested: S123RDIW-B340D755UB27-4F0-XX-W2A-A1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032253
REPORT IS A COMBINATION OF REPORTS P994336 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B340D755UB27-4F0-XX-W2A-A1
Description: Define 3 Regressed Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3950.0 lumens
Efficiency: N/A
Efficacy: 109.1 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 36.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032253

CATALOG NUMBER: S123RDIW-B340D755UB27-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1032253

CATALOG NUMBER: S123RDIW-B340D755UB27-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41
1	94	90	87	83	85	82	79	76	65	63	61	50	49	48	36	36	35
2	86	79	74	69	78	72	67	63	58	54	51	45	42	40	33	31	30
3	79	70	63	58	71	63	58	53	51	47	44	40	37	35	29	27	26
4	72	62	55	49	65	56	50	45	46	41	37	36	32	30	26	24	23
5	66	55	48	42	60	50	44	39	41	36	32	32	29	26	24	22	20
6	61	50	42	36	55	45	39	34	37	32	28	29	26	23	22	20	18
7	57	45	37	32	51	41	34	30	33	29	25	26	23	20	20	18	16
8	52	41	33	28	47	37	31	26	31	26	22	24	21	18	18	16	14
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13
10	46	34	27	22	41	31	25	21	26	21	18	21	17	15	16	13	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5654	5654	5654	5654
5°	5658	6512	5673	4831
10°	5609	7861	5633	4220
15°	5551	8922	5551	3721
20°	5437	9623	5468	3301
25°	5353	9143	5343	3012
30°	5256	6335	5245	2729
35°	5140	4067	5117	2516
40°	4994	2872	4970	2304
45°	4742	2299	4736	2097
50°	4431	1922	4417	1856
55°	4082	1585	4050	1574
60°	3739	1310	3702	1338
65°	3338	1049	3360	1135
70°	2965	729	3045	918
75°	2514	541	2617	706
80°	2003	358	2172	529
85°	1422	168	1556	328

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 7549 cd/sqm

TEST NUMBER: P1032253

CATALOG NUMBER: S123RDIW-B340D755UB27-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.6	1.3
10°-20°	161.5	4.1
20°-30°	254.3	6.4
30°-40°	264.5	6.7
40°-50°	226.3	5.7
50°-60°	172.5	4.4
60°-70°	110.5	2.8
70°-80°	52.9	1.3
80°-90°	15.9	0.4
90°-100°	61.3	1.6
100°-110°	185.6	4.7
110°-120°	316.0	8.0
120°-130°	415.8	10.5
130°-140°	467.3	11.8
140°-150°	459.4	11.6
150°-160°	386.8	9.8
160°-170°	257.5	6.5
170°-180°	90.2	2.3
0°-30°	467.4	11.8
0°-40°	731.9	18.5
0°-60°	1130.6	28.6
0°-90°	1310.0	33.2
90°-120°	563.0	14.3
90°-150°	1905.5	48.2
90°-180°	2640.0	66.8
0°-180°	3950.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	525	525	525	525	525	
5°	525	624	526	463	525	50
15°	502	886	502	370	502	141
25°	456	913	455	301	456	210
35°	398	396	396	245	398	249
45°	319	211	319	193	319	246
55°	225	133	224	132	225	202
65°	138	76	139	83	138	138
75°	66	32	69	42	66	71
85°	15	8	16	15	15	17
90°	1	22	1	22	1	4
95°	44	58	44	58	44	49
105°	168	178	168	178	168	180
115°	318	319	318	319	318	315
125°	466	460	466	460	466	415
135°	604	603	604	603	604	465
145°	733	733	733	733	733	458
155°	839	838	839	838	839	386
165°	914	911	914	911	914	258
175°	950	947	950	947	950	90
180°	953	953	953	953	953	

TEST NUMBER: P1032253

CATALOG NUMBER: S123RDIW-B340D755UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3
2.5°	526.6	530.2	532.9	534.7	539.2	541.9	544.2	548.2	548.2	549.1	550.9
5°	524.8	532.5	537.9	545.1	554.5	559.0	565.3	570.7	578.4	582.4	586.5
7.5°	520.8	531.6	542.8	553.6	567.6	576.6	582.9	596.8	606.7	618.8	628.3
10°	515.4	530.2	544.6	561.3	580.2	593.6	603.1	621.5	640.4	657.5	671.9
12.5°	508.6	526.6	547.3	567.6	594.1	607.6	622.9	645.8	672.8	694.4	713.7
15°	501.5	522.1	545.5	570.3	603.5	622.4	644.5	672.4	702.5	733.5	760.1
17.5°	490.2	516.3	542.4	578.4	617.5	628.7	647.6	685.8	723.2	751.1	783.4
20°	479.0	508.2	541.0	573.4	615.7	641.8	659.3	699.8	739.8	773.5	804.6
22.5°	468.6	499.2	533.4	574.3	613.9	640.0	662.0	704.3	750.6	788.4	826.6
25°	456.0	489.3	527.1	565.8	613.9	633.7	658.0	707.0	756.0	799.6	846.8
27.5°	442.5	476.3	513.6	553.2	597.2	626.5	650.3	702.9	762.7	809.5	858.1
30°	429.0	463.7	499.7	535.2	584.7	612.5	640.0	698.0	766.3	819.9	857.2
32.5°	416.0	445.2	480.8	515.4	564.4	595.0	626.0	693.0	767.7	812.7	830.7
35°	398.0	428.6	457.4	494.3	543.7	573.9	610.3	692.6	761.8	789.7	780.7
37.5°	381.4	407.0	434.4	467.3	518.1	557.2	595.0	680.9	742.5	744.3	693.5
40°	362.9	384.1	407.0	441.6	496.5	535.2	576.1	662.9	707.4	680.9	591.4
42.5°	341.8	360.7	378.7	412.4	472.2	515.4	559.5	640.4	656.6	595.4	502.4
45°	319.3	334.6	351.2	386.8	446.6	489.3	533.4	605.8	589.2	502.8	414.2
47.5°	295.9	309.0	325.2	357.5	419.2	462.8	504.6	556.3	514.0	421.4	347.2
50°	272.5	282.9	298.6	331.9	391.3	430.8	469.5	503.3	443.9	361.6	286.9
52.5°	249.6	257.7	273.9	302.2	359.8	397.6	425.4	438.5	378.2	298.6	249.2
55°	225.3	234.3	245.1	273.9	331.0	358.9	377.3	376.9	314.8	253.2	206.0
57.5°	201.9	210.0	219.5	248.3	294.6	313.5	329.2	321.6	262.6	207.3	176.7
60°	181.2	185.7	196.1	220.4	255.4	271.6	280.6	267.6	214.5	174.9	146.2
62.5°	158.8	163.3	171.8	194.7	216.3	224.9	232.5	215.9	177.2	142.6	125.0
65°	138.1	143.9	149.3	167.8	179.4	189.8	188.9	174.9	138.5	116.0	101.6
67.5°	120.1	122.3	126.8	138.1	143.5	151.1	151.6	135.8	111.5	94.4	85.9
70°	100.7	103.0	106.1	111.5	115.1	116.9	116.0	102.1	84.1	73.8	66.1
72.5°	84.1	83.7	85.9	85.9	89.5	89.0	86.3	75.6	63.9	55.3	50.8
75°	66.1	66.6	67.0	66.1	64.8	63.0	60.7	52.6	45.0	40.9	36.9
77.5°	51.7	50.8	51.3	48.1	46.3	44.5	41.4	37.3	31.0	30.1	28.3
80°	36.9	36.4	36.0	34.6	30.6	28.8	26.5	24.3	22.9	22.0	21.6
82.5°	24.7	24.7	23.8	21.1	18.9	17.5	17.1	16.2	14.8	14.8	14.4
85°	14.8	14.4	13.5	10.8	9.4	9.4	9.4	9.4	8.5	8.5	8.1
87.5°	5.8	5.4	4.0	4.0	3.6	3.6	3.6	3.1	3.1	2.7	2.7
90°	0.7	2.4	4.0	5.7	7.4	8.2	9.3	11.5	13.6	15.8	18.0
92.5°	22.5	23.5	24.5	25.4	26.4	26.9	27.4	28.4	29.4	30.4	31.4
95°	44.2	45.4	46.5	47.7	48.8	49.4	50.1	51.4	52.7	54.1	55.4
97.5°	72.6	73.4	74.2	75.1	75.9	76.3	76.8	77.8	78.8	79.8	80.8
100°	101.8	102.8	103.8	104.8	105.8	106.3	106.7	107.5	108.4	109.2	110.0
102.5°	135.5	136.0	136.5	137.0	137.5	137.7	138.3	139.5	140.6	141.8	143.0
105°	168.4	168.7	169.1	169.4	169.7	169.9	170.6	172.1	173.6	175.1	176.6
107.5°	207.3	207.5	207.7	207.8	208.0	208.1	208.4	209.1	209.8	210.4	211.1
110°	243.2	243.5	243.9	244.2	244.5	244.7	244.9	245.2	245.5	245.9	246.2



TEST NUMBER: P1032253

CATALOG NUMBER: S123RDIW-B340D755UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	280.7	280.9	281.0	281.2	281.3	281.4	281.4	281.4	281.4	281.4	281.4
115°	318.1	318.6	319.1	319.6	320.1	320.3	320.1	319.8	319.5	319.1	318.8
117.5°	356.3	356.5	356.6	356.8	356.9	357.0	356.8	356.5	356.2	355.8	355.5
120°	391.4	392.4	393.4	394.4	395.4	395.9	395.5	394.7	393.8	393.0	392.2
122.5°	428.1	428.8	429.4	430.1	430.8	431.1	430.9	430.6	430.3	429.9	429.6
125°	465.5	466.0	466.5	467.0	467.5	467.8	467.6	467.3	467.0	466.6	466.3
127.5°	500.0	501.0	502.0	503.0	504.0	504.5	504.3	504.0	503.7	503.3	503.0
130°	534.4	535.7	537.1	538.4	539.7	540.4	540.1	539.6	539.1	538.6	538.1
132.5°	568.8	570.1	571.5	572.8	574.1	574.8	574.6	574.3	574.0	573.6	573.3
135°	604.0	605.0	606.0	607.0	608.0	608.5	608.4	608.2	608.1	607.9	607.7
137.5°	636.2	637.0	637.8	638.7	639.5	639.9	640.2	640.7	641.2	641.7	642.2
140°	669.9	670.7	671.5	672.4	673.2	673.6	673.7	673.9	674.0	674.2	674.4
142.5°	700.6	701.4	702.2	703.1	703.9	704.3	704.5	704.8	705.1	705.5	705.8
145°	732.7	733.0	733.4	733.7	734.0	734.2	734.5	735.0	735.5	736.0	736.5
147.5°	760.4	761.1	761.7	762.4	763.1	763.4	763.7	764.2	764.7	765.2	765.7
150°	789.6	789.9	790.3	790.6	790.9	791.1	791.3	791.6	791.9	792.3	792.6
152.5°	813.6	814.1	814.6	815.1	815.6	815.8	815.9	816.1	816.2	816.4	816.6
155°	839.0	839.0	839.0	839.0	839.0	839.0	839.1	839.3	839.4	839.6	839.8
157.5°	860.7	860.5	860.4	860.2	860.1	860.0	860.1	860.2	860.4	860.5	860.7
160°	880.9	880.6	880.2	879.9	879.6	879.4	879.4	879.4	879.4	879.4	879.4
162.5°	898.9	898.4	897.9	897.4	896.9	896.6	896.7	896.9	897.0	897.2	897.4
165°	913.9	913.4	912.9	912.4	911.9	911.6	911.6	911.6	911.6	911.6	911.6
167.5°	926.6	925.9	925.3	924.6	923.9	923.6	923.7	923.8	924.0	924.1	924.3
170°	937.1	936.4	935.8	935.1	934.4	934.1	934.1	934.1	934.1	934.1	934.1
172.5°	945.3	944.6	944.0	943.3	942.6	942.3	942.3	942.3	942.3	942.3	942.3
175°	950.5	949.8	949.2	948.5	947.8	947.5	947.5	947.5	947.5	947.5	947.5
177.5°	953.5	952.8	952.2	951.5	950.8	950.5	950.5	950.5	950.5	950.5	950.5
180°	952.8	952.8	952.8	952.8	952.8	952.8	952.8	952.8	952.8	952.8	952.8

TEST NUMBER: P1032253

CATALOG NUMBER: S123RDIW-B340D755UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3
2.5°	554.5	554.5	558.6	562.6	560.4	561.7	566.7	564.9	568.5	568.0	569.4
5°	596.3	601.3	605.3	613.9	615.2	613.9	622.4	624.7	628.7	623.8	626.0
7.5°	643.6	653.9	663.8	676.4	680.4	681.3	685.8	692.1	697.5	687.6	692.6
10°	689.4	705.2	725.4	736.7	746.6	750.2	753.8	757.8	764.1	769.9	765.4
12.5°	738.9	761.8	781.2	801.4	813.6	812.2	822.6	825.3	830.2	831.6	833.4
15°	779.4	811.8	823.9	854.0	856.7	865.7	877.4	887.8	889.1	886.4	886.4
17.5°	818.1	846.0	867.5	891.8	896.8	904.4	919.3	924.2	926.0	925.6	925.6
20°	849.5	868.0	904.4	924.7	932.7	942.6	953.0	959.3	960.6	962.4	959.7
22.5°	870.2	898.1	927.8	944.4	951.2	954.8	961.5	963.3	961.1	961.5	962.0
25°	886.4	913.9	931.8	936.3	935.9	931.4	926.5	917.9	917.0	913.4	906.2
27.5°	890.9	901.3	899.0	880.6	862.1	860.3	830.7	814.5	796.0	798.7	788.4
30°	866.6	853.1	821.2	774.4	755.1	723.6	690.3	655.7	642.2	627.4	654.8
32.5°	807.3	759.2	702.5	641.8	609.4	581.5	546.0	520.8	506.4	494.3	517.6
35°	717.8	642.7	567.6	510.0	483.5	458.3	425.0	412.4	394.4	396.2	398.5
37.5°	602.6	519.9	463.2	406.6	389.0	378.7	354.4	335.1	328.8	327.0	327.0
40°	494.7	426.8	376.4	331.9	318.4	309.9	290.5	281.5	274.8	273.0	275.2
42.5°	409.3	351.2	312.1	282.4	273.0	262.2	254.1	242.9	241.5	238.4	242.4
45°	343.6	293.2	264.0	242.4	234.3	230.3	221.3	214.5	211.8	211.4	214.5
47.5°	291.4	252.3	226.7	213.2	206.9	202.8	195.2	192.5	189.8	190.7	189.3
50°	244.7	215.4	198.8	186.6	182.6	178.5	173.6	170.9	169.5	169.5	169.1
52.5°	210.0	185.7	174.9	163.7	161.9	159.7	154.3	152.5	150.2	149.8	151.6
55°	179.9	163.3	152.5	145.7	143.9	139.4	137.2	134.9	133.6	132.7	133.1
57.5°	153.8	141.2	134.0	128.2	125.0	123.2	119.2	118.7	117.8	117.8	117.4
60°	132.2	123.2	114.7	111.1	108.8	106.6	106.1	103.4	102.1	103.0	102.5
62.5°	112.0	104.8	99.8	95.8	94.4	92.6	91.3	90.4	89.0	89.5	89.5
65°	93.5	87.7	84.1	80.5	80.1	78.3	77.8	76.9	76.9	76.5	77.4
67.5°	76.9	72.9	69.7	67.5	66.1	66.6	64.8	63.4	63.4	63.0	64.3
70°	61.2	58.9	55.8	53.1	51.3	51.3	49.0	48.6	48.6	48.6	48.1
72.5°	47.2	43.2	41.8	40.9	40.9	40.9	40.0	40.0	39.6	40.0	39.6
75°	35.1	34.6	33.7	33.3	33.3	32.8	32.4	32.4	32.4	32.4	32.4
77.5°	27.4	27.4	26.5	26.1	26.1	26.1	25.6	25.6	25.2	25.2	25.2
80°	20.2	20.2	19.3	19.3	19.3	18.9	18.9	18.9	19.3	18.9	18.9
82.5°	13.9	13.9	13.5	13.9	13.5	13.0	13.0	13.0	12.6	13.0	13.0
85°	8.1	8.1	7.6	7.2	7.6	7.6	7.2	7.6	7.2	7.6	7.2
87.5°	3.1	2.7	2.7	2.7	2.2	2.7	2.2	2.2	2.7	2.2	2.7
90°	18.7	19.3	20.0	20.7	21.0	21.2	21.5	21.8	22.2	22.5	22.2
92.5°	31.9	32.4	32.9	33.4	33.7	33.5	33.2	32.9	32.5	32.2	32.5
95°	56.1	56.7	57.4	58.1	58.4	58.4	58.4	58.4	58.4	58.4	58.4
97.5°	81.6	82.5	83.3	84.2	84.6	84.5	84.3	84.2	84.0	83.8	84.0
100°	110.5	111.0	111.5	112.0	112.3	112.5	112.8	113.1	113.5	113.8	113.5
102.5°	143.5	144.0	144.5	145.0	145.2	145.1	145.0	144.8	144.7	144.5	144.7
105°	176.6	176.6	176.6	176.6	176.6	176.8	177.1	177.4	177.8	178.1	177.8
107.5°	211.6	212.1	212.6	213.1	213.3	213.2	213.1	212.9	212.8	212.6	212.8
110°	246.9	247.5	248.2	248.9	249.2	249.0	248.7	248.4	248.0	247.7	248.0

TEST NUMBER: P1032253

CATALOG NUMBER: S123RDIW-B340D755UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	282.2	283.1	283.9	284.8	285.2	285.2	285.2	285.2	285.2	285.2	285.2
115°	319.0	319.2	319.3	319.5	319.6	319.5	319.3	319.2	319.0	318.8	319.0
117.5°	355.5	355.5	355.5	355.5	355.5	355.3	354.8	354.3	353.8	353.3	353.8
120°	392.0	391.8	391.7	391.5	391.4	391.2	390.9	390.6	390.2	389.9	390.2
122.5°	429.1	428.6	428.1	427.6	427.4	427.1	426.6	426.1	425.6	425.1	425.6
125°	465.6	465.0	464.3	463.6	463.3	463.0	462.3	461.6	461.0	460.3	461.0
127.5°	502.0	501.0	500.0	499.0	498.5	498.2	497.5	496.8	496.2	495.5	496.2
130°	537.4	536.8	536.1	535.4	535.1	534.5	533.4	532.2	531.1	529.9	531.1
132.5°	572.5	571.7	570.8	570.0	569.6	569.2	568.3	567.5	566.6	565.8	566.6
135°	607.1	606.4	605.8	605.1	604.8	604.6	604.3	604.0	603.6	603.3	603.6
137.5°	641.4	640.5	639.7	638.8	638.4	638.2	637.7	637.2	636.7	636.2	636.7
140°	674.2	674.0	673.9	673.7	673.6	673.0	671.9	670.7	669.6	668.4	669.6
142.5°	705.6	705.4	705.3	705.1	705.0	704.6	703.8	702.9	702.1	701.3	702.1
145°	736.3	736.1	736.0	735.8	735.7	735.4	734.7	734.0	733.4	732.7	733.4
147.5°	765.7	765.7	765.7	765.7	765.7	765.2	764.2	763.2	762.2	761.2	762.2
150°	792.6	792.6	792.6	792.6	792.6	792.1	791.1	790.1	789.1	788.1	789.1
152.5°	816.9	817.3	817.6	817.9	818.1	817.7	816.8	816.0	815.1	814.3	815.1
155°	840.5	841.1	841.8	842.5	842.8	842.2	841.0	839.9	838.7	837.5	838.7
157.5°	861.4	862.0	862.7	863.4	863.7	863.2	862.2	861.2	860.2	859.2	860.2
160°	880.2	881.1	881.9	882.8	883.2	882.9	882.2	881.5	880.9	880.2	880.9
162.5°	898.2	899.0	899.9	900.7	901.1	900.5	899.4	898.2	897.1	895.9	897.1
165°	912.6	913.6	914.6	915.6	916.1	915.5	914.4	913.2	912.1	910.9	912.1
167.5°	925.3	926.3	927.3	928.3	928.8	928.3	927.3	926.3	925.3	924.3	925.3
170°	935.3	936.4	937.6	938.7	939.3	938.7	937.6	936.4	935.3	934.1	935.3
172.5°	943.3	944.3	945.3	946.3	946.8	946.2	945.1	943.9	942.8	941.6	942.8
175°	948.5	949.5	950.5	951.5	952.0	951.4	950.3	949.1	948.0	946.8	948.0
177.5°	951.5	952.5	953.5	954.5	955.0	954.4	953.3	952.1	951.0	949.8	951.0
180°	952.8	952.8	952.8	952.8	952.8	952.8	952.8	952.8	952.8	952.8	952.8

TEST NUMBER: P1032253

CATALOG NUMBER: S123RDIW-B340D755UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3
2.5°	567.1	564.4	562.6	561.3	559.9	564.0	558.6	552.7	548.7	546.0	545.1
5°	626.5	620.6	615.7	611.6	612.5	612.5	603.1	592.7	583.8	578.8	573.4
7.5°	695.3	689.0	679.1	676.8	675.1	663.8	654.4	635.5	624.2	613.0	603.1
10°	763.6	755.6	746.1	743.0	738.5	724.5	710.1	685.8	671.9	651.2	638.2
12.5°	827.5	817.6	808.2	805.9	799.2	787.0	762.3	737.1	713.3	691.2	668.3
15°	881.0	878.3	863.9	854.9	840.1	823.5	818.1	783.9	753.8	730.8	689.4
17.5°	926.0	913.4	899.9	894.1	888.2	868.9	849.5	814.5	782.1	748.4	721.8
20°	962.0	948.0	938.6	930.1	927.4	905.3	874.7	843.7	808.2	770.4	735.8
22.5°	963.8	962.0	955.7	950.7	945.3	930.9	906.7	868.0	830.2	788.8	743.4
25°	926.5	923.8	941.7	937.2	940.8	935.4	922.4	890.0	846.0	797.4	751.5
27.5°	814.0	841.5	869.8	879.7	886.4	905.8	912.1	894.1	858.5	806.8	755.6
30°	661.1	697.5	743.4	768.1	787.0	823.0	869.8	875.6	859.0	817.6	754.7
32.5°	519.0	552.3	589.2	618.4	643.6	717.3	780.3	825.7	833.8	812.2	756.9
35°	418.3	432.6	467.7	495.6	529.8	592.7	667.0	740.3	789.7	792.4	750.2
37.5°	344.9	352.6	383.2	398.9	419.2	474.5	543.7	639.5	716.4	752.9	731.3
40°	285.6	303.1	320.7	329.7	344.0	382.3	448.8	523.9	619.3	686.7	702.0
42.5°	247.8	255.4	266.7	279.3	288.3	321.6	366.1	434.9	520.8	614.8	657.1
45°	218.6	221.3	233.0	241.1	250.5	273.9	305.4	362.9	438.5	531.1	603.1
47.5°	194.3	199.7	206.0	210.9	217.2	235.2	262.2	304.0	370.6	453.3	530.7
50°	172.7	175.8	183.9	186.2	190.7	203.3	224.0	255.9	310.8	376.9	456.9
52.5°	152.5	158.3	161.5	164.6	168.7	179.0	192.5	218.6	259.9	322.0	389.9
55°	136.7	138.5	143.0	145.7	148.9	156.1	167.8	187.1	219.5	268.9	333.3
57.5°	121.4	121.4	125.9	128.2	131.3	136.7	147.1	161.9	185.3	222.2	281.1
60°	105.2	105.7	109.3	112.0	112.9	118.3	126.8	138.5	156.5	183.5	231.6
62.5°	90.8	93.1	94.9	95.8	98.9	102.1	109.3	117.4	130.0	153.8	188.0
65°	78.7	79.2	80.5	81.4	82.8	86.3	91.7	97.1	107.9	125.5	153.4
67.5°	64.8	66.6	68.4	68.4	69.7	71.5	76.9	81.4	89.5	99.8	118.7
70°	48.6	49.5	52.2	53.5	55.3	58.5	61.2	63.9	70.2	77.8	92.2
72.5°	40.5	40.5	41.4	41.8	41.8	44.1	48.1	50.8	54.0	59.4	69.3
75°	32.4	32.4	33.7	33.3	34.2	35.1	35.5	37.3	39.1	43.2	49.0
77.5°	25.6	26.1	26.1	26.5	26.5	27.0	27.4	28.3	29.2	31.5	34.2
80°	18.9	19.3	19.3	19.8	19.8	20.2	20.7	21.1	22.0	22.9	24.3
82.5°	13.0	13.5	13.5	13.9	13.5	13.9	14.4	14.4	14.8	15.7	16.2
85°	7.6	7.6	8.1	7.6	7.6	7.6	8.1	8.1	8.5	9.9	9.9
87.5°	2.2	2.7	2.2	2.7	2.7	2.7	2.7	3.1	3.1	3.6	4.0
90°	21.8	21.5	21.2	21.0	20.7	20.0	19.3	18.7	18.0	15.8	13.6
92.5°	32.9	33.2	33.5	33.7	33.4	32.9	32.4	31.9	31.4	30.4	29.4
95°	58.4	58.4	58.4	58.4	58.1	57.4	56.7	56.1	55.4	54.1	52.7
97.5°	84.2	84.3	84.5	84.6	84.2	83.3	82.5	81.6	80.8	79.8	78.8
100°	113.1	112.8	112.5	112.3	112.0	111.5	111.0	110.5	110.0	109.2	108.4
102.5°	144.8	145.0	145.1	145.2	145.0	144.5	144.0	143.5	143.0	141.8	140.6
105°	177.4	177.1	176.8	176.6	176.6	176.6	176.6	176.6	176.6	175.1	173.6
107.5°	212.9	213.1	213.2	213.3	213.1	212.6	212.1	211.6	211.1	210.4	209.8
110°	248.4	248.7	249.0	249.2	248.9	248.2	247.5	246.9	246.2	245.9	245.5

TEST NUMBER: P1032253

CATALOG NUMBER: S123RDIW-B340D755UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	285.2	285.2	285.2	285.2	284.8	283.9	283.1	282.2	281.4	281.4	281.4
115°	319.2	319.3	319.5	319.6	319.5	319.3	319.2	319.0	318.8	319.1	319.5
117.5°	354.3	354.8	355.3	355.5	355.5	355.5	355.5	355.5	355.5	355.8	356.2
120°	390.6	390.9	391.2	391.4	391.5	391.7	391.8	392.0	392.2	393.0	393.8
122.5°	426.1	426.6	427.1	427.4	427.6	428.1	428.6	429.1	429.6	429.9	430.3
125°	461.6	462.3	463.0	463.3	463.6	464.3	465.0	465.6	466.3	466.6	467.0
127.5°	496.8	497.5	498.2	498.5	499.0	500.0	501.0	502.0	503.0	503.3	503.7
130°	532.2	533.4	534.5	535.1	535.4	536.1	536.8	537.4	538.1	538.6	539.1
132.5°	567.5	568.3	569.2	569.6	570.0	570.8	571.7	572.5	573.3	573.6	574.0
135°	604.0	604.3	604.6	604.8	605.1	605.8	606.4	607.1	607.7	607.9	608.1
137.5°	637.2	637.7	638.2	638.4	638.8	639.7	640.5	641.4	642.2	641.7	641.2
140°	670.7	671.9	673.0	673.6	673.7	673.9	674.0	674.2	674.4	674.2	674.0
142.5°	702.9	703.8	704.6	705.0	705.1	705.3	705.4	705.6	705.8	705.5	705.1
145°	734.0	734.7	735.4	735.7	735.8	736.0	736.1	736.3	736.5	736.0	735.5
147.5°	763.2	764.2	765.2	765.7	765.7	765.7	765.7	765.7	765.7	765.2	764.7
150°	790.1	791.1	792.1	792.6	792.6	792.6	792.6	792.6	792.6	792.3	791.9
152.5°	816.0	816.8	817.7	818.1	817.9	817.6	817.3	816.9	816.6	816.4	816.2
155°	839.9	841.0	842.2	842.8	842.5	841.8	841.1	840.5	839.8	839.6	839.4
157.5°	861.2	862.2	863.2	863.7	863.4	862.7	862.0	861.4	860.7	860.5	860.4
160°	881.5	882.2	882.9	883.2	882.8	881.9	881.1	880.2	879.4	879.4	879.4
162.5°	898.2	899.4	900.5	901.1	900.7	899.9	899.0	898.2	897.4	897.2	897.0
165°	913.2	914.4	915.5	916.1	915.6	914.6	913.6	912.6	911.6	911.6	911.6
167.5°	926.3	927.3	928.3	928.8	928.3	927.3	926.3	925.3	924.3	924.1	924.0
170°	936.4	937.6	938.7	939.3	938.7	937.6	936.4	935.3	934.1	934.1	934.1
172.5°	943.9	945.1	946.2	946.8	946.3	945.3	944.3	943.3	942.3	942.3	942.3
175°	949.1	950.3	951.4	952.0	951.5	950.5	949.5	948.5	947.5	947.5	947.5
177.5°	952.1	953.3	954.4	955.0	954.5	953.5	952.5	951.5	950.5	950.5	950.5
180°	952.8	952.8	952.8	952.8	952.8	952.8	952.8	952.8	952.8	952.8	952.8

TEST NUMBER: P1032253

CATALOG NUMBER: S123RDIW-B340D755UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3
2.5°	543.7	541.5	539.2	539.2	534.3	529.8	527.5	528.4	525.7	522.1	518.5
5°	567.6	558.6	556.8	551.8	545.1	535.6	530.7	526.2	520.8	513.6	506.9
7.5°	589.6	577.9	571.6	566.7	553.6	540.6	529.8	522.6	513.1	502.4	494.3
10°	618.4	596.8	590.1	578.8	560.4	541.9	529.3	517.6	504.6	492.0	481.2
12.5°	641.3	616.6	604.0	592.7	568.9	545.5	524.4	510.0	494.3	480.3	466.4
15°	667.4	639.5	617.5	604.0	573.9	545.5	521.7	501.5	483.9	466.8	454.7
17.5°	680.0	644.9	635.0	615.7	572.1	543.7	514.5	492.9	471.8	452.0	437.6
20°	699.8	658.9	634.1	621.1	582.4	540.6	506.4	481.7	459.6	438.5	423.2
22.5°	701.1	656.6	640.4	615.7	568.0	531.1	499.2	469.1	443.4	423.6	407.9
25°	698.0	652.6	630.1	610.3	570.7	525.7	484.8	455.1	429.9	407.0	388.6
27.5°	696.6	640.9	619.7	599.9	555.4	510.0	476.3	442.5	413.8	393.5	374.6
30°	694.8	628.3	602.6	579.7	538.8	497.9	457.4	428.1	400.7	375.1	356.2
32.5°	683.1	611.2	585.1	560.8	516.7	475.8	443.9	412.9	383.2	359.3	342.2
35°	679.5	595.4	561.3	535.2	492.0	455.6	421.9	396.2	368.3	344.5	324.3
37.5°	669.2	579.3	542.4	509.1	464.1	429.5	404.8	379.1	352.1	326.5	310.3
40°	651.2	560.4	518.5	484.4	438.0	403.0	380.0	361.1	334.6	311.7	291.9
42.5°	624.7	541.0	496.1	460.1	408.8	376.0	357.1	339.1	316.6	292.8	276.6
45°	594.1	515.4	473.6	433.5	381.4	349.4	329.7	318.9	298.2	277.9	259.0
47.5°	552.3	488.9	447.5	406.1	353.0	322.0	306.3	295.5	281.1	259.0	243.8
50°	499.7	454.7	415.6	378.7	325.2	295.5	279.7	271.6	259.5	243.8	228.9
52.5°	441.2	415.1	382.7	348.5	296.8	268.9	254.5	248.3	239.3	224.4	211.8
55°	382.3	371.0	349.0	315.3	267.1	244.2	231.6	223.5	216.8	206.0	195.2
57.5°	329.7	324.3	309.0	282.9	242.4	218.6	207.8	202.4	197.0	188.9	178.1
60°	275.2	281.1	265.3	252.3	215.4	194.7	185.3	179.4	176.7	169.5	162.8
62.5°	228.0	233.4	224.4	214.5	188.4	170.0	164.2	158.8	157.0	150.7	143.9
65°	185.3	192.0	185.3	179.9	164.2	148.9	141.7	139.0	137.2	133.1	127.7
67.5°	147.5	154.3	151.1	144.4	139.4	126.8	122.8	120.1	119.2	116.0	111.5
70°	111.1	120.5	121.4	117.4	112.9	107.0	104.3	103.4	101.2	98.5	95.8
72.5°	80.1	90.8	91.3	91.3	88.6	88.6	85.9	84.6	84.6	81.9	78.7
75°	58.9	66.1	67.0	67.9	69.3	70.6	68.8	68.8	68.4	65.7	64.3
77.5°	39.1	45.4	47.7	50.8	52.6	52.6	53.5	54.4	53.5	52.2	51.3
80°	25.2	29.7	32.4	34.2	36.9	38.2	39.6	40.0	39.1	38.7	37.3
82.5°	16.6	18.0	19.3	21.6	24.7	27.0	27.0	26.5	27.4	27.0	26.5
85°	9.4	10.3	10.8	11.2	13.0	15.3	15.7	16.2	17.1	16.2	15.3
87.5°	3.6	4.0	4.0	4.0	4.9	5.4	6.7	8.5	8.1	7.2	7.2
90°	11.5	9.3	8.2	7.4	5.7	4.0	2.4	0.7	2.4	4.0	5.7
92.5°	28.4	27.4	26.9	26.4	25.4	24.5	23.5	22.5	23.5	24.5	25.4
95°	51.4	50.1	49.4	48.8	47.7	46.5	45.4	44.2	45.4	46.5	47.7
97.5°	77.8	76.8	76.3	75.9	75.1	74.2	73.4	72.6	73.4	74.2	75.1
100°	107.5	106.7	106.3	105.8	104.8	103.8	102.8	101.8	102.8	103.8	104.8
102.5°	139.5	138.3	137.7	137.5	137.0	136.5	136.0	135.5	136.0	136.5	137.0
105°	172.1	170.6	169.9	169.7	169.4	169.1	168.7	168.4	168.7	169.1	169.4
107.5°	209.1	208.4	208.1	208.0	207.8	207.7	207.5	207.3	207.5	207.7	207.8
110°	245.2	244.9	244.7	244.5	244.2	243.9	243.5	243.2	243.5	243.9	244.2

TEST NUMBER: P1032253

CATALOG NUMBER: S123RDIW-B340D755UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	281.4	281.4	281.4	281.3	281.2	281.0	280.9	280.7	280.9	281.0	281.2
115°	319.8	320.1	320.3	320.1	319.6	319.1	318.6	318.1	318.6	319.1	319.6
117.5°	356.5	356.8	357.0	356.9	356.8	356.6	356.5	356.3	356.5	356.6	356.8
120°	394.7	395.5	395.9	395.4	394.4	393.4	392.4	391.4	392.4	393.4	394.4
122.5°	430.6	430.9	431.1	430.8	430.1	429.4	428.8	428.1	428.8	429.4	430.1
125°	467.3	467.6	467.8	467.5	467.0	466.5	466.0	465.5	466.0	466.5	467.0
127.5°	504.0	504.3	504.5	504.0	503.0	502.0	501.0	500.0	501.0	502.0	503.0
130°	539.6	540.1	540.4	539.7	538.4	537.1	535.7	534.4	535.7	537.1	538.4
132.5°	574.3	574.6	574.8	574.1	572.8	571.5	570.1	568.8	570.1	571.5	572.8
135°	608.2	608.4	608.5	608.0	607.0	606.0	605.0	604.0	605.0	606.0	607.0
137.5°	640.7	640.2	639.9	639.5	638.7	637.8	637.0	636.2	637.0	637.8	638.7
140°	673.9	673.7	673.6	673.2	672.4	671.5	670.7	669.9	670.7	671.5	672.4
142.5°	704.8	704.5	704.3	703.9	703.1	702.2	701.4	700.6	701.4	702.2	703.1
145°	735.0	734.5	734.2	734.0	733.7	733.4	733.0	732.7	733.0	733.4	733.7
147.5°	764.2	763.7	763.4	763.1	762.4	761.7	761.1	760.4	761.1	761.7	762.4
150°	791.6	791.3	791.1	790.9	790.6	790.3	789.9	789.6	789.9	790.3	790.6
152.5°	816.1	815.9	815.8	815.6	815.1	814.6	814.1	813.6	814.1	814.6	815.1
155°	839.3	839.1	839.0	839.0	839.0	839.0	839.0	839.0	839.0	839.0	839.0
157.5°	860.2	860.1	860.0	860.1	860.2	860.4	860.5	860.7	860.5	860.4	860.2
160°	879.4	879.4	879.4	879.6	879.9	880.2	880.6	880.9	880.6	880.2	879.9
162.5°	896.9	896.7	896.6	896.9	897.4	897.9	898.4	898.9	898.4	897.9	897.4
165°	911.6	911.6	911.6	911.9	912.4	912.9	913.4	913.9	913.4	912.9	912.4
167.5°	923.8	923.7	923.6	923.9	924.6	925.3	925.9	926.6	925.9	925.3	924.6
170°	934.1	934.1	934.1	934.4	935.1	935.8	936.4	937.1	936.4	935.8	935.1
172.5°	942.3	942.3	942.3	942.6	943.3	944.0	944.6	945.3	944.6	944.0	943.3
175°	947.5	947.5	947.5	947.8	948.5	949.2	949.8	950.5	949.8	949.2	948.5
177.5°	950.5	950.5	950.5	950.8	951.5	952.2	952.8	953.5	952.8	952.2	951.5
180°	952.8	952.8	952.8	952.8	952.8	952.8	952.8	952.8	952.8	952.8	952.8

TEST NUMBER: P1032253

CATALOG NUMBER: S123RDIW-B340D755UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3
2.5°	518.5	516.3	515.4	513.1	507.7	504.2	500.1	497.4	497.9	495.6	497.0
5°	502.4	501.9	498.8	494.3	486.6	482.6	475.4	471.8	470.0	470.4	467.7
7.5°	488.9	484.8	482.6	475.4	468.2	459.6	453.8	450.6	447.9	445.2	443.4
10°	473.6	470.0	466.4	458.7	448.8	440.7	432.6	429.5	425.4	423.6	422.3
12.5°	457.4	455.1	450.6	441.6	430.4	422.8	413.3	411.5	406.1	402.5	401.6
15°	442.5	441.2	433.1	422.8	411.5	403.9	395.8	390.4	381.4	383.2	380.0
17.5°	426.8	421.0	416.0	402.1	396.7	385.0	375.5	372.8	366.5	362.5	358.4
20°	409.3	405.7	399.4	390.4	377.3	363.8	356.6	352.1	348.5	342.2	340.4
22.5°	392.6	388.1	382.7	371.0	359.8	348.5	338.6	334.6	330.1	325.6	322.9
25°	379.6	372.8	367.0	352.6	341.3	331.9	325.6	318.9	312.6	309.9	309.0
27.5°	359.3	355.3	349.4	336.0	325.6	315.3	309.4	304.9	298.2	295.0	292.3
30°	346.3	338.2	331.5	320.7	310.3	299.1	293.7	288.3	284.2	280.2	277.0
32.5°	328.8	322.5	317.1	306.3	295.9	285.6	279.7	271.6	269.4	266.2	262.6
35°	311.7	307.6	301.8	290.1	278.8	271.6	265.3	257.7	255.0	252.8	249.6
37.5°	295.5	289.6	285.6	274.3	264.4	255.9	251.0	244.7	242.9	240.2	237.9
40°	281.5	275.7	271.6	260.4	250.1	241.1	237.9	231.6	228.9	225.8	224.4
42.5°	265.8	260.8	255.4	247.4	236.6	227.6	221.3	217.7	214.1	212.7	210.0
45°	249.2	244.7	240.6	231.6	220.4	214.1	208.7	203.7	201.0	198.8	197.0
47.5°	234.8	230.7	225.3	215.4	206.4	200.6	195.2	190.2	187.5	184.8	182.6
50°	218.1	215.9	210.0	200.6	192.0	185.3	180.3	175.8	174.0	170.9	167.3
52.5°	203.3	199.2	194.3	186.6	179.0	170.9	164.2	161.5	158.3	156.5	153.4
55°	185.7	183.0	177.6	170.9	162.8	156.1	151.1	147.5	143.5	141.7	137.6
57.5°	170.9	166.0	163.3	154.7	147.1	140.3	136.7	133.1	128.6	125.9	124.1
60°	154.7	150.2	146.2	139.0	133.6	126.4	121.0	117.8	114.7	111.1	109.3
62.5°	139.0	135.4	130.4	124.6	117.8	112.0	107.9	103.4	101.6	98.0	96.7
65°	121.9	119.2	115.1	108.4	103.0	98.0	94.0	90.4	88.6	87.2	86.3
67.5°	106.6	103.0	100.3	94.4	88.6	84.6	82.3	80.1	77.8	76.5	75.1
70°	90.8	88.1	85.4	80.1	76.0	72.4	70.6	68.8	67.5	66.1	64.8
72.5°	74.7	73.3	70.6	67.0	63.9	61.2	59.8	57.6	56.2	54.0	53.1
75°	61.6	59.4	58.0	54.9	52.2	49.9	48.1	45.4	43.6	42.7	42.3
77.5°	48.6	47.7	45.9	43.2	41.8	39.6	36.9	36.0	35.1	35.1	34.6
80°	36.4	35.1	33.7	31.5	30.1	28.3	28.3	28.3	27.9	28.3	27.9
82.5°	24.7	23.8	22.9	21.6	21.1	21.1	21.6	21.6	21.6	21.6	21.6
85°	14.4	14.4	14.4	14.8	14.4	14.4	14.8	15.3	14.8	14.8	14.4
87.5°	6.7	6.7	7.2	7.2	7.6	7.6	7.6	7.6	7.6	7.6	8.1
90°	7.4	8.2	9.3	11.5	13.6	15.8	18.0	18.7	19.3	20.0	20.7
92.5°	26.4	26.9	27.4	28.4	29.4	30.4	31.4	31.9	32.4	32.9	33.4
95°	48.8	49.4	50.1	51.4	52.7	54.1	55.4	56.1	56.7	57.4	58.1
97.5°	75.9	76.3	76.8	77.8	78.8	79.8	80.8	81.6	82.5	83.3	84.2
100°	105.8	106.3	106.7	107.5	108.4	109.2	110.0	110.5	111.0	111.5	112.0
102.5°	137.5	137.7	138.3	139.5	140.6	141.8	143.0	143.5	144.0	144.5	145.0
105°	169.7	169.9	170.6	172.1	173.6	175.1	176.6	176.6	176.6	176.6	176.6
107.5°	208.0	208.1	208.4	209.1	209.8	210.4	211.1	211.6	212.1	212.6	213.1
110°	244.5	244.7	244.9	245.2	245.5	245.9	246.2	246.9	247.5	248.2	248.9

TEST NUMBER: P1032253

CATALOG NUMBER: S123RDIW-B340D755UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	281.3	281.4	281.4	281.4	281.4	281.4	281.4	282.2	283.1	283.9	284.8
115°	320.1	320.3	320.1	319.8	319.5	319.1	318.8	319.0	319.2	319.3	319.5
117.5°	356.9	357.0	356.8	356.5	356.2	355.8	355.5	355.5	355.5	355.5	355.5
120°	395.4	395.9	395.5	394.7	393.8	393.0	392.2	392.0	391.8	391.7	391.5
122.5°	430.8	431.1	430.9	430.6	430.3	429.9	429.6	429.1	428.6	428.1	427.6
125°	467.5	467.8	467.6	467.3	467.0	466.6	466.3	465.6	465.0	464.3	463.6
127.5°	504.0	504.5	504.3	504.0	503.7	503.3	503.0	502.0	501.0	500.0	499.0
130°	539.7	540.4	540.1	539.6	539.1	538.6	538.1	537.4	536.8	536.1	535.4
132.5°	574.1	574.8	574.6	574.3	574.0	573.6	573.3	572.5	571.7	570.8	570.0
135°	608.0	608.5	608.4	608.2	608.1	607.9	607.7	607.1	606.4	605.8	605.1
137.5°	639.5	639.9	640.2	640.7	641.2	641.7	642.2	641.4	640.5	639.7	638.8
140°	673.2	673.6	673.7	673.9	674.0	674.2	674.4	674.2	674.0	673.9	673.7
142.5°	703.9	704.3	704.5	704.8	705.1	705.5	705.8	705.6	705.4	705.3	705.1
145°	734.0	734.2	734.5	735.0	735.5	736.0	736.5	736.3	736.1	736.0	735.8
147.5°	763.1	763.4	763.7	764.2	764.7	765.2	765.7	765.7	765.7	765.7	765.7
150°	790.9	791.1	791.3	791.6	791.9	792.3	792.6	792.6	792.6	792.6	792.6
152.5°	815.6	815.8	815.9	816.1	816.2	816.4	816.6	816.9	817.3	817.6	817.9
155°	839.0	839.0	839.1	839.3	839.4	839.6	839.8	840.5	841.1	841.8	842.5
157.5°	860.1	860.0	860.1	860.2	860.4	860.5	860.7	861.4	862.0	862.7	863.4
160°	879.6	879.4	879.4	879.4	879.4	879.4	879.4	880.2	881.1	881.9	882.8
162.5°	896.9	896.6	896.7	896.9	897.0	897.2	897.4	898.2	899.0	899.9	900.7
165°	911.9	911.6	911.6	911.6	911.6	911.6	911.6	912.6	913.6	914.6	915.6
167.5°	923.9	923.6	923.7	923.8	924.0	924.1	924.3	925.3	926.3	927.3	928.3
170°	934.4	934.1	934.1	934.1	934.1	934.1	934.1	935.3	936.4	937.6	938.7
172.5°	942.6	942.3	942.3	942.3	942.3	942.3	942.3	943.3	944.3	945.3	946.3
175°	947.8	947.5	947.5	947.5	947.5	947.5	947.5	948.5	949.5	950.5	951.5
177.5°	950.8	950.5	950.5	950.5	950.5	950.5	950.5	951.5	952.5	953.5	954.5
180°	952.8	952.8	952.8	952.8	952.8	952.8	952.8	952.8	952.8	952.8	952.8

TEST NUMBER: P1032253

CATALOG NUMBER: S123RDIW-B340D755UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3
2.5°	496.5	497.0	495.6	492.9	492.5	493.4	496.1	495.2	492.9	497.0	493.4
5°	469.1	466.8	465.9	466.8	464.1	462.8	465.5	464.1	465.5	465.9	467.3
7.5°	442.5	443.0	440.3	440.7	437.1	438.0	438.0	438.0	439.4	440.3	442.1
10°	419.6	420.5	417.4	417.8	415.1	413.3	414.7	417.4	417.4	417.4	418.3
12.5°	401.2	397.1	394.9	394.4	391.3	390.4	393.1	394.0	396.2	396.2	397.6
15°	378.2	377.3	375.5	375.5	367.9	369.7	370.6	373.7	378.2	374.6	375.5
17.5°	357.5	355.3	353.0	352.1	351.2	348.5	352.1	351.7	354.4	354.8	356.2
20°	339.1	337.3	332.8	333.3	334.2	330.1	332.4	332.4	335.1	337.8	340.9
22.5°	321.1	319.3	317.1	318.0	315.3	314.4	314.4	316.6	319.8	322.0	321.6
25°	307.2	304.0	302.7	301.3	300.0	300.9	299.5	301.8	304.0	305.4	304.0
27.5°	291.4	290.1	287.4	286.0	283.8	284.7	285.6	287.4	288.7	288.7	290.1
30°	276.1	274.3	273.4	272.1	272.1	270.3	270.7	272.5	273.9	275.2	277.0
32.5°	261.3	259.9	258.6	258.6	257.7	257.2	256.8	259.5	259.5	262.2	262.2
35°	249.2	246.9	246.9	244.7	245.6	245.1	244.2	246.0	246.5	248.3	247.8
37.5°	235.7	235.7	234.8	232.5	230.7	231.2	233.4	233.4	234.8	234.3	235.7
40°	222.2	221.3	221.3	219.9	219.5	219.0	219.5	219.9	222.2	221.7	222.2
42.5°	208.7	209.1	206.9	206.9	206.9	205.5	206.0	206.4	207.3	208.2	209.6
45°	195.6	194.7	194.3	193.4	192.5	192.9	192.5	194.3	193.8	194.7	196.1
47.5°	181.7	180.3	179.9	178.1	178.1	179.0	178.5	179.9	180.3	181.7	180.8
50°	168.2	166.4	165.1	165.5	162.8	163.7	163.7	165.1	166.4	166.9	167.8
52.5°	152.5	152.0	151.6	149.3	148.9	148.4	148.9	149.3	151.1	152.5	152.9
55°	137.2	136.7	134.0	133.1	131.8	131.8	132.7	133.1	136.3	136.7	138.5
57.5°	123.2	121.9	118.7	118.3	118.3	118.3	116.9	118.7	119.6	121.9	121.9
60°	107.9	107.9	105.2	105.2	105.7	105.2	105.2	105.7	105.7	107.5	108.4
62.5°	95.8	95.3	95.3	94.4	94.0	94.4	94.0	94.0	94.4	95.8	97.1
65°	85.0	84.6	84.1	83.7	82.8	82.8	83.2	84.1	84.1	85.0	85.4
67.5°	74.7	74.7	73.8	73.8	73.3	72.9	73.3	72.9	74.7	74.7	75.1
70°	64.3	63.9	62.5	62.1	60.7	61.2	61.2	62.5	63.0	63.9	64.8
72.5°	51.7	51.7	50.8	49.9	50.4	49.5	49.5	49.9	49.9	51.3	51.7
75°	42.7	41.8	41.4	41.8	41.4	42.3	41.4	41.4	42.3	42.3	42.3
77.5°	35.1	35.1	34.6	34.6	35.1	34.6	35.1	35.1	35.1	34.6	35.1
80°	28.8	28.3	28.3	28.3	27.9	27.9	27.9	27.9	27.9	27.9	27.9
82.5°	21.6	21.6	21.1	21.6	21.6	21.1	21.6	21.1	21.1	21.6	21.6
85°	14.4	15.3	14.4	14.4	14.8	14.8	15.3	14.8	15.3	14.4	14.8
87.5°	7.6	8.1	8.1	7.6	7.6	8.1	8.1	8.1	8.5	7.6	8.1
90°	21.0	21.2	21.5	21.8	22.2	22.5	22.2	21.8	21.5	21.2	21.0
92.5°	33.7	33.5	33.2	32.9	32.5	32.2	32.5	32.9	33.2	33.5	33.7
95°	58.4	58.4	58.4	58.4	58.4	58.4	58.4	58.4	58.4	58.4	58.4
97.5°	84.6	84.5	84.3	84.2	84.0	83.8	84.0	84.2	84.3	84.5	84.6
100°	112.3	112.5	112.8	113.1	113.5	113.8	113.5	113.1	112.8	112.5	112.3
102.5°	145.2	145.1	145.0	144.8	144.7	144.5	144.7	144.8	145.0	145.1	145.2
105°	176.6	176.8	177.1	177.4	177.8	178.1	177.8	177.4	177.1	176.8	176.6
107.5°	213.3	213.2	213.1	212.9	212.8	212.6	212.8	212.9	213.1	213.2	213.3
110°	249.2	249.0	248.7	248.4	248.0	247.7	248.0	248.4	248.7	249.0	249.2

TEST NUMBER: P1032253

CATALOG NUMBER: S123RDIW-B340D755UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	285.2	285.2	285.2	285.2	285.2	285.2	285.2	285.2	285.2	285.2	285.2
115°	319.6	319.5	319.3	319.2	319.0	318.8	319.0	319.2	319.3	319.5	319.6
117.5°	355.5	355.3	354.8	354.3	353.8	353.3	353.8	354.3	354.8	355.3	355.5
120°	391.4	391.2	390.9	390.6	390.2	389.9	390.2	390.6	390.9	391.2	391.4
122.5°	427.4	427.1	426.6	426.1	425.6	425.1	425.6	426.1	426.6	427.1	427.4
125°	463.3	463.0	462.3	461.6	461.0	460.3	461.0	461.6	462.3	463.0	463.3
127.5°	498.5	498.2	497.5	496.8	496.2	495.5	496.2	496.8	497.5	498.2	498.5
130°	535.1	534.5	533.4	532.2	531.1	529.9	531.1	532.2	533.4	534.5	535.1
132.5°	569.6	569.2	568.3	567.5	566.6	565.8	566.6	567.5	568.3	569.2	569.6
135°	604.8	604.6	604.3	604.0	603.6	603.3	603.6	604.0	604.3	604.6	604.8
137.5°	638.4	638.2	637.7	637.2	636.7	636.2	636.7	637.2	637.7	638.2	638.4
140°	673.6	673.0	671.9	670.7	669.6	668.4	669.6	670.7	671.9	673.0	673.6
142.5°	705.0	704.6	703.8	702.9	702.1	701.3	702.1	702.9	703.8	704.6	705.0
145°	735.7	735.4	734.7	734.0	733.4	732.7	733.4	734.0	734.7	735.4	735.7
147.5°	765.7	765.2	764.2	763.2	762.2	761.2	762.2	763.2	764.2	765.2	765.7
150°	792.6	792.1	791.1	790.1	789.1	788.1	789.1	790.1	791.1	792.1	792.6
152.5°	818.1	817.7	816.8	816.0	815.1	814.3	815.1	816.0	816.8	817.7	818.1
155°	842.8	842.2	841.0	839.9	838.7	837.5	838.7	839.9	841.0	842.2	842.8
157.5°	863.7	863.2	862.2	861.2	860.2	859.2	860.2	861.2	862.2	863.2	863.7
160°	883.2	882.9	882.2	881.5	880.9	880.2	880.9	881.5	882.2	882.9	883.2
162.5°	901.1	900.5	899.4	898.2	897.1	895.9	897.1	898.2	899.4	900.5	901.1
165°	916.1	915.5	914.4	913.2	912.1	910.9	912.1	913.2	914.4	915.5	916.1
167.5°	928.8	928.3	927.3	926.3	925.3	924.3	925.3	926.3	927.3	928.3	928.8
170°	939.3	938.7	937.6	936.4	935.3	934.1	935.3	936.4	937.6	938.7	939.3
172.5°	946.8	946.2	945.1	943.9	942.8	941.6	942.8	943.9	945.1	946.2	946.8
175°	952.0	951.4	950.3	949.1	948.0	946.8	948.0	949.1	950.3	951.4	952.0
177.5°	955.0	954.4	953.3	952.1	951.0	949.8	951.0	952.1	953.3	954.4	955.0
180°	952.8	952.8	952.8	952.8	952.8	952.8	952.8	952.8	952.8	952.8	952.8

TEST NUMBER: P1032253

CATALOG NUMBER: S123RDIW-B340D755UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3
2.5°	497.0	498.8	497.0	493.4	497.0	499.2	501.5	505.1	506.9	506.9	509.5
5°	468.6	472.2	470.9	470.0	473.6	475.8	479.4	483.9	488.9	492.0	495.6
7.5°	443.4	445.7	447.9	447.9	451.5	456.5	461.9	467.3	473.6	478.1	480.8
10°	421.4	423.2	424.5	426.3	431.7	437.1	444.3	451.1	456.5	461.4	465.9
12.5°	400.3	403.0	406.1	407.5	411.5	418.3	425.0	433.1	441.6	446.6	451.1
15°	380.0	381.4	385.0	389.0	392.6	399.8	408.4	416.9	424.1	431.7	435.8
17.5°	359.3	359.8	369.2	367.0	378.7	385.4	389.9	398.0	409.7	416.0	422.3
20°	339.1	343.6	347.6	349.9	356.2	363.8	376.9	383.2	392.6	398.5	403.9
22.5°	323.4	330.1	330.1	335.5	338.6	345.8	355.3	367.4	377.8	381.8	389.5
25°	309.4	312.6	318.0	319.8	325.6	331.9	338.2	351.2	362.5	367.9	373.3
27.5°	291.4	295.5	302.7	302.7	310.3	317.1	324.7	333.3	344.5	352.1	358.0
30°	277.5	281.5	284.7	289.6	292.8	299.1	312.6	318.9	328.8	335.5	342.7
32.5°	264.4	267.6	270.3	275.7	279.3	286.5	293.7	304.9	313.5	319.8	327.4
35°	250.1	253.2	256.8	260.8	266.2	273.0	279.7	289.2	297.7	303.6	309.9
37.5°	236.6	238.8	244.2	246.9	251.4	257.7	266.2	276.1	283.8	288.3	294.6
40°	223.5	225.3	229.4	234.3	237.5	242.4	251.4	259.9	269.4	274.8	279.7
42.5°	209.6	211.8	215.4	220.4	225.3	230.7	235.7	245.6	254.1	258.6	264.0
45°	197.4	198.8	201.5	206.4	211.4	215.4	223.1	232.1	240.2	243.8	249.6
47.5°	183.0	184.4	188.4	190.7	196.1	201.5	209.1	218.1	225.3	228.9	234.3
50°	168.2	169.5	172.2	177.2	180.8	186.6	193.4	201.0	210.0	215.0	218.1
52.5°	153.8	156.5	158.8	162.8	167.3	173.1	179.4	186.6	194.3	199.2	202.8
55°	139.4	141.7	144.4	146.6	152.0	157.4	164.6	171.3	178.1	182.6	186.6
57.5°	123.2	126.4	129.1	133.6	137.6	142.1	150.2	155.6	163.7	166.9	170.4
60°	109.3	112.4	114.7	118.3	121.9	127.7	133.1	139.9	146.6	150.7	155.2
62.5°	97.6	98.9	100.3	103.9	107.5	112.9	118.3	125.0	132.2	134.5	138.1
65°	85.9	87.2	89.5	92.6	95.3	98.5	104.3	109.7	116.5	120.1	121.4
67.5°	76.0	77.4	77.8	80.1	82.3	85.9	89.0	94.4	100.7	103.0	105.7
70°	64.8	67.0	67.5	69.3	70.2	72.4	76.0	80.1	85.0	89.0	91.3
72.5°	51.7	54.9	55.8	58.5	59.8	62.1	64.8	67.9	71.1	72.9	74.7
75°	42.3	43.2	43.6	45.9	48.1	51.3	52.6	54.4	57.1	59.4	61.2
77.5°	35.1	35.5	36.0	36.0	36.4	38.2	40.9	43.2	45.0	45.9	47.2
80°	28.3	27.9	27.9	28.3	28.3	28.3	29.2	32.4	33.3	35.5	35.1
82.5°	22.0	21.1	21.6	21.1	21.1	21.1	21.1	21.6	21.6	22.9	23.8
85°	14.4	14.8	14.4	14.4	13.9	14.4	13.9	13.9	13.5	13.5	13.0
87.5°	7.6	8.1	7.6	7.6	7.2	7.6	7.2	7.2	6.7	6.7	5.8
90°	20.7	20.0	19.3	18.7	18.0	15.8	13.6	11.5	9.3	8.2	7.4
92.5°	33.4	32.9	32.4	31.9	31.4	30.4	29.4	28.4	27.4	26.9	26.4
95°	58.1	57.4	56.7	56.1	55.4	54.1	52.7	51.4	50.1	49.4	48.8
97.5°	84.2	83.3	82.5	81.6	80.8	79.8	78.8	77.8	76.8	76.3	75.9
100°	112.0	111.5	111.0	110.5	110.0	109.2	108.4	107.5	106.7	106.3	105.8
102.5°	145.0	144.5	144.0	143.5	143.0	141.8	140.6	139.5	138.3	137.7	137.5
105°	176.6	176.6	176.6	176.6	176.6	175.1	173.6	172.1	170.6	169.9	169.7
107.5°	213.1	212.6	212.1	211.6	211.1	210.4	209.8	209.1	208.4	208.1	208.0
110°	248.9	248.2	247.5	246.9	246.2	245.9	245.5	245.2	244.9	244.7	244.5

TEST NUMBER: P1032253

CATALOG NUMBER: S123RDIW-B340D755UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	284.8	283.9	283.1	282.2	281.4	281.4	281.4	281.4	281.4	281.4	281.3
115°	319.5	319.3	319.2	319.0	318.8	319.1	319.5	319.8	320.1	320.3	320.1
117.5°	355.5	355.5	355.5	355.5	355.5	355.8	356.2	356.5	356.8	357.0	356.9
120°	391.5	391.7	391.8	392.0	392.2	393.0	393.8	394.7	395.5	395.9	395.4
122.5°	427.6	428.1	428.6	429.1	429.6	429.9	430.3	430.6	430.9	431.1	430.8
125°	463.6	464.3	465.0	465.6	466.3	466.6	467.0	467.3	467.6	467.8	467.5
127.5°	499.0	500.0	501.0	502.0	503.0	503.3	503.7	504.0	504.3	504.5	504.0
130°	535.4	536.1	536.8	537.4	538.1	538.6	539.1	539.6	540.1	540.4	539.7
132.5°	570.0	570.8	571.7	572.5	573.3	573.6	574.0	574.3	574.6	574.8	574.1
135°	605.1	605.8	606.4	607.1	607.7	607.9	608.1	608.2	608.4	608.5	608.0
137.5°	638.8	639.7	640.5	641.4	642.2	641.7	641.2	640.7	640.2	639.9	639.5
140°	673.7	673.9	674.0	674.2	674.4	674.2	674.0	673.9	673.7	673.6	673.2
142.5°	705.1	705.3	705.4	705.6	705.8	705.5	705.1	704.8	704.5	704.3	703.9
145°	735.8	736.0	736.1	736.3	736.5	736.0	735.5	735.0	734.5	734.2	734.0
147.5°	765.7	765.7	765.7	765.7	765.7	765.2	764.7	764.2	763.7	763.4	763.1
150°	792.6	792.6	792.6	792.6	792.6	792.3	791.9	791.6	791.3	791.1	790.9
152.5°	817.9	817.6	817.3	816.9	816.6	816.4	816.2	816.1	815.9	815.8	815.6
155°	842.5	841.8	841.1	840.5	839.8	839.6	839.4	839.3	839.1	839.0	839.0
157.5°	863.4	862.7	862.0	861.4	860.7	860.5	860.4	860.2	860.1	860.0	860.1
160°	882.8	881.9	881.1	880.2	879.4	879.4	879.4	879.4	879.4	879.4	879.6
162.5°	900.7	899.9	899.0	898.2	897.4	897.2	897.0	896.9	896.7	896.6	896.9
165°	915.6	914.6	913.6	912.6	911.6	911.6	911.6	911.6	911.6	911.6	911.9
167.5°	928.3	927.3	926.3	925.3	924.3	924.1	924.0	923.8	923.7	923.6	923.9
170°	938.7	937.6	936.4	935.3	934.1	934.1	934.1	934.1	934.1	934.1	934.4
172.5°	946.3	945.3	944.3	943.3	942.3	942.3	942.3	942.3	942.3	942.3	942.6
175°	951.5	950.5	949.5	948.5	947.5	947.5	947.5	947.5	947.5	947.5	947.8
177.5°	954.5	953.5	952.5	951.5	950.5	950.5	950.5	950.5	950.5	950.5	950.8
180°	952.8	952.8	952.8	952.8	952.8	952.8	952.8	952.8	952.8	952.8	952.8

TEST NUMBER: P1032253

CATALOG NUMBER: S123RDIW-B340D755UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	525.3	525.3	525.3	525.3
2.5°	511.8	514.9	521.2	526.6
5°	501.0	506.0	515.4	524.8
7.5°	488.0	495.6	507.7	520.8
10°	475.4	485.3	500.1	515.4
12.5°	462.8	473.1	488.9	508.6
15°	447.9	458.7	477.6	501.5
17.5°	434.9	449.3	466.4	490.2
20°	421.0	431.7	453.8	479.0
22.5°	403.4	421.4	442.1	468.6
25°	389.5	405.2	425.9	456.0
27.5°	372.4	390.8	416.0	442.5
30°	358.4	373.7	397.1	429.0
32.5°	342.2	360.2	384.5	416.0
35°	327.9	343.1	366.1	398.0
37.5°	310.8	327.4	353.0	381.4
40°	295.9	312.1	336.4	362.9
42.5°	277.9	295.0	319.3	341.8
45°	263.5	279.3	298.6	319.3
47.5°	246.0	262.6	281.5	295.9
50°	230.3	245.6	260.4	272.5
52.5°	213.2	227.1	240.6	249.6
55°	197.4	208.2	219.0	225.3
57.5°	179.0	189.3	198.3	201.9
60°	162.8	171.3	177.2	181.2
62.5°	145.7	152.0	156.5	158.8
65°	129.1	133.6	135.8	138.1
67.5°	112.0	116.0	117.4	120.1
70°	94.0	98.5	99.4	100.7
72.5°	80.5	80.5	82.3	84.1
75°	64.3	65.2	66.1	66.1
77.5°	50.4	50.4	51.3	51.7
80°	36.9	37.3	37.3	36.9
82.5°	25.2	26.1	25.2	24.7
85°	13.9	15.7	14.8	14.8
87.5°	5.8	5.8	6.7	5.8
90°	5.7	4.0	2.4	0.7
92.5°	25.4	24.5	23.5	22.5
95°	47.7	46.5	45.4	44.2
97.5°	75.1	74.2	73.4	72.6
100°	104.8	103.8	102.8	101.8
102.5°	137.0	136.5	136.0	135.5
105°	169.4	169.1	168.7	168.4
107.5°	207.8	207.7	207.5	207.3
110°	244.2	243.9	243.5	243.2

TEST NUMBER: P1032253

CATALOG NUMBER: S123RDIW-B340D755UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	281.2	281.0	280.9	280.7
115°	319.6	319.1	318.6	318.1
117.5°	356.8	356.6	356.5	356.3
120°	394.4	393.4	392.4	391.4
122.5°	430.1	429.4	428.8	428.1
125°	467.0	466.5	466.0	465.5
127.5°	503.0	502.0	501.0	500.0
130°	538.4	537.1	535.7	534.4
132.5°	572.8	571.5	570.1	568.8
135°	607.0	606.0	605.0	604.0
137.5°	638.7	637.8	637.0	636.2
140°	672.4	671.5	670.7	669.9
142.5°	703.1	702.2	701.4	700.6
145°	733.7	733.4	733.0	732.7
147.5°	762.4	761.7	761.1	760.4
150°	790.6	790.3	789.9	789.6
152.5°	815.1	814.6	814.1	813.6
155°	839.0	839.0	839.0	839.0
157.5°	860.2	860.4	860.5	860.7
160°	879.9	880.2	880.6	880.9
162.5°	897.4	897.9	898.4	898.9
165°	912.4	912.9	913.4	913.9
167.5°	924.6	925.3	925.9	926.6
170°	935.1	935.8	936.4	937.1
172.5°	943.3	944.0	944.6	945.3
175°	948.5	949.2	949.8	950.5
177.5°	951.5	952.2	952.8	953.5
180°	952.8	952.8	952.8	952.8

(END OF REPORT)