

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032259

Luminaire Tested: S123RDIW-B340D755UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032259
REPORT IS A COMBINATION OF REPORTS P994359 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B340D755UB30-4F0-XX-W2A-F1
Description: Define 3 Regressed Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3928.0 lumens
Efficiency: N/A
Efficacy: 108.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 36.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032259

CATALOG NUMBER: S123RDIW-B340D755UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1032259

CATALOG NUMBER: S123RDIW-B340D755UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40
1	94	90	86	83	85	81	78	75	65	62	61	49	48	47	35	35	34
2	86	79	73	68	77	71	66	62	57	53	50	44	41	39	31	30	29
3	78	69	62	57	70	63	57	52	50	46	43	39	36	34	28	26	25
4	72	61	54	48	64	56	49	44	45	40	36	35	31	29	25	23	21
5	66	55	47	41	59	50	43	38	40	35	31	31	28	25	23	21	19
6	61	49	41	36	54	44	38	33	36	31	27	28	25	22	21	18	17
7	56	44	36	31	50	40	33	29	33	28	24	26	22	19	19	17	15
8	52	40	33	27	47	36	30	25	30	25	21	23	20	17	17	15	13
9	48	36	29	24	43	33	27	23	27	22	19	21	18	15	16	14	12
10	45	33	26	22	41	30	24	20	25	20	17	20	16	14	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6018	6018	6018
5°	6028	5804	5789
10°	5980	5586	5477
15°	5902	5316	5134
20°	5801	5023	4752
25°	5695	4719	4388
30°	5561	4394	3960
35°	5423	4075	3570
40°	5292	3729	3138
45°	5124	3391	2751
50°	4940	3029	2350
55°	4749	2643	1981
60°	4566	2247	1609
65°	4329	1840	1256
70°	4032	1391	897
75°	3606	943	711
80°	3078	656	499
85°	2305	354	262

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5124 cd/sqm

TEST NUMBER: P1032259

CATALOG NUMBER: S123RDIW-B340D755UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.6	1.3
10°-20°	146.2	3.7
20°-30°	210.5	5.4
30°-40°	237.1	6.0
40°-50°	226.7	5.8
50°-60°	185.6	4.7
60°-70°	125.1	3.2
70°-80°	62.8	1.6
80°-90°	18.4	0.5
90°-100°	61.9	1.6
100°-110°	187.3	4.8
110°-120°	318.8	8.1
120°-130°	419.4	10.7
130°-140°	471.4	12.0
140°-150°	463.4	11.8
150°-160°	390.2	9.9
160°-170°	259.7	6.6
170°-180°	91.0	2.3
0°-30°	409.2	10.4
0°-40°	646.3	16.5
0°-60°	1058.7	27.0
0°-90°	1265.0	32.2
90°-120°	567.9	14.5
90°-150°	1922.1	48.9
90°-180°	2663.0	67.8
0°-180°	3928.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	559	559	559	559	559	
5°	559	557	551	555	554	53
15°	533	528	516	513	510	150
25°	485	474	453	443	438	223
35°	420	404	375	356	348	263
45°	345	325	290	264	253	266
55°	262	240	201	175	166	235
65°	179	154	119	97	92	177
75°	95	73	48	44	43	101
85°	24	14	13	12	12	26
90°	1	8	18	21	23	5
95°	44	50	56	59	59	49
105°	170	171	178	178	180	182
115°	321	323	322	322	322	318
125°	470	472	470	467	464	419
135°	609	614	613	610	608	469
145°	739	741	743	742	739	462
155°	846	846	847	850	845	390
165°	922	920	920	924	919	260
175°	959	956	956	960	955	91
180°	961	961	961	961	961	

TEST NUMBER: P1032259

CATALOG NUMBER: S123RDIW-B340D755UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	559.1	559.1	559.1	559.1	559.1
2.5°	561.3	559.5	554.1	559.1	558.1
5°	559.1	556.8	551.3	555.4	554.5
7.5°	555.0	552.7	545.9	548.6	547.3
10°	549.5	546.4	538.2	538.6	536.4
12.5°	541.8	538.2	527.8	527.3	524.6
15°	533.2	528.2	515.5	513.3	510.1
17.5°	522.8	517.3	501.5	496.9	492.4
20°	511.0	503.7	486.5	480.6	475.2
22.5°	497.8	489.2	470.6	462.9	457.9
25°	485.1	473.8	453.0	443.4	438.4
27.5°	469.7	457.5	434.8	422.1	414.4
30°	453.9	440.3	414.9	399.5	392.2
32.5°	438.0	422.1	394.9	377.7	370.0
35°	419.9	403.5	375.4	355.9	347.8
37.5°	401.7	384.0	354.6	332.8	322.8
40°	384.5	364.5	332.3	308.8	298.3
42.5°	365.0	345.0	311.5	285.2	276.1
45°	345.0	324.6	289.7	263.9	253.0
47.5°	325.5	302.9	268.4	240.3	230.8
50°	303.8	282.5	245.7	217.6	207.2
52.5°	284.3	260.7	224.4	195.0	185.9
55°	262.1	239.9	201.3	175.0	165.9
57.5°	242.1	218.1	179.1	154.2	146.5
60°	221.3	196.3	158.7	134.2	126.5
62.5°	200.4	175.5	137.8	115.2	107.0
65°	179.1	154.2	118.8	96.6	91.6
67.5°	157.8	132.4	97.9	81.2	75.7
70°	136.9	112.4	80.7	64.8	59.8
72.5°	116.1	92.0	63.9	51.7	50.3
75°	94.8	73.0	48.1	43.5	42.6
77.5°	75.3	55.3	37.6	34.9	34.0
80°	56.7	38.1	28.6	27.2	26.3
82.5°	39.0	23.6	20.4	19.0	19.0
85°	24.0	14.1	12.7	11.8	11.8
87.5°	10.9	5.9	5.9	5.4	5.0
90°	0.8	8.3	18.1	21.1	22.6
92.5°	22.6	27.2	31.7	34.0	32.5
95°	44.5	49.8	55.9	58.9	58.9
97.5°	73.2	77.0	81.5	85.3	84.6
100°	102.7	107.2	111.0	113.2	114.8
102.5°	136.6	138.9	144.2	146.5	145.7
105°	169.9	171.4	178.2	178.2	179.7
107.5°	209.1	209.9	212.9	215.2	214.4
110°	245.4	246.9	248.4	251.4	249.9

TEST NUMBER: P1032259

CATALOG NUMBER: S123RDIW-B340D755UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	283.1	283.9	283.9	287.6	287.6
115°	320.9	323.1	321.6	322.4	321.6
117.5°	359.4	360.1	358.6	358.6	356.3
120°	394.8	399.4	395.6	394.8	393.3
122.5°	431.8	434.9	433.4	431.1	428.8
125°	469.6	471.9	470.3	467.3	464.3
127.5°	504.3	508.8	507.3	502.8	499.8
130°	539.0	545.1	542.8	539.8	534.5
132.5°	573.8	579.8	578.3	574.5	570.8
135°	609.3	613.8	613.0	610.0	608.5
137.5°	641.7	645.5	647.8	644.0	641.7
140°	675.7	679.5	680.2	679.5	674.2
142.5°	706.7	710.4	711.9	711.2	707.4
145°	739.1	740.6	742.9	742.1	739.1
147.5°	767.0	770.1	772.3	772.3	767.8
150°	796.5	798.0	799.5	799.5	795.0
152.5°	820.7	822.9	823.7	825.2	821.4
155°	846.3	846.3	847.1	850.1	844.8
157.5°	868.2	867.5	868.2	871.2	866.7
160°	888.6	887.1	887.1	890.9	887.8
162.5°	906.7	904.5	905.2	909.0	903.7
165°	921.8	919.6	919.6	924.1	918.8
167.5°	934.7	931.6	932.4	936.9	932.4
170°	945.2	942.2	942.2	947.5	942.2
172.5°	953.5	950.5	950.5	955.0	949.8
175°	958.8	955.8	955.8	960.3	955.0
177.5°	961.8	958.8	958.8	963.3	958.1
180°	961.1	961.1	961.1	961.1	961.1

(END OF REPORT)