

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032282

Luminaire Tested: S123RDIW-B560D1030UB35-4F0-XX-W2A-F

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032282
REPORT IS A COMBINATION OF REPORTS P994408 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B560D1030UB35-4F0-XX-W2A-F
Description: Define 3 Regressed Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6335.0 lumens
Efficiency: N/A
Efficacy: 114.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 55.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032282

CATALOG NUMBER: S123RDIW-B560D1030UB35-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1032282

CATALOG NUMBER: S123RDIW-B560D1030UB35-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41
1	94	90	87	83	85	82	78	76	65	63	61	50	49	48	37	36	35
2	86	79	73	68	77	72	67	62	57	54	51	45	42	40	33	31	30
3	79	70	63	57	71	63	57	52	51	47	43	40	37	34	29	27	26
4	72	62	54	48	65	56	49	44	45	41	37	35	32	29	26	24	22
5	66	55	47	41	59	50	43	38	40	36	32	32	28	26	24	21	20
6	61	49	41	36	55	45	38	33	36	31	28	29	25	22	21	19	17
7	56	44	37	31	51	40	34	29	33	28	24	26	23	20	20	17	15
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14
9	48	37	29	25	44	34	27	23	28	23	19	22	18	16	17	14	12
10	45	34	27	22	41	31	25	20	25	21	17	20	17	14	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10168	10168	10168
5°	10184	9808	9781
10°	10104	9440	9253
15°	9972	8983	8675
20°	9801	8487	8028
25°	9623	7972	7415
30°	9396	7425	6691
35°	9161	6886	6032
40°	8940	6301	5303
45°	8658	5730	4648
50°	8347	5119	3970
55°	8023	4466	3349
60°	7715	3796	2718
65°	7315	3108	2122
70°	6814	2351	1516
75°	6090	1592	1201
80°	5201	1107	842
85°	3900	599	441

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8658 cd/sqm

TEST NUMBER: P1032282

CATALOG NUMBER: S123RDIW-B560D1030UB35-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.8	1.4
10°-20°	247.0	3.9
20°-30°	355.7	5.6
30°-40°	400.5	6.3
40°-50°	383.1	6.0
50°-60°	313.6	5.0
60°-70°	211.5	3.3
70°-80°	106.1	1.7
80°-90°	30.5	0.5
90°-100°	48.6	0.8
100°-110°	234.8	3.7
110°-120°	575.4	9.1
120°-130°	730.4	11.5
130°-140°	780.3	12.3
140°-150°	729.6	11.5
150°-160°	588.5	9.3
160°-170°	379.8	6.0
170°-180°	130.9	2.1
0°-30°	691.5	10.9
0°-40°	1092.0	17.2
0°-60°	1788.8	28.2
0°-90°	2136.8	33.7
90°-120°	858.7	13.6
90°-150°	3099.0	48.9
90°-180°	4198.0	66.3
0°-180°	6335.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	945	945	945	945	945	
5°	945	941	932	938	937	90
15°	901	892	871	867	862	254
25°	820	801	765	749	741	377
35°	709	682	634	601	588	444
45°	583	548	490	446	428	450
55°	443	405	340	296	280	397
65°	303	260	201	163	155	299
75°	160	123	81	74	72	171
85°	41	24	22	20	20	44
90°	1	11	25	29	31	6
95°	62	20	32	39	39	75
105°	305	316	224	43	45	323
115°	572	578	587	598	602	565
125°	806	814	818	820	823	720
135°	1004	1010	1014	1017	1014	773
145°	1158	1165	1167	1169	1169	725
155°	1276	1274	1275	1280	1274	588
165°	1345	1342	1341	1350	1342	380
175°	1377	1372	1373	1380	1372	131
180°	1377	1377	1377	1377	1377	

TEST NUMBER: P1032282

CATALOG NUMBER: S123RDIW-B560D1030UB35-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	944.6	944.6	944.6	944.6	944.6
2.5°	948.4	945.4	936.2	944.6	943.1
5°	944.6	940.8	931.6	938.5	936.9
7.5°	937.7	933.9	922.4	927.0	924.7
10°	928.5	923.1	909.4	910.1	906.3
12.5°	915.5	909.4	891.7	891.0	886.4
15°	900.9	892.5	871.0	867.2	861.9
17.5°	883.3	874.1	847.3	839.6	832.0
20°	863.4	851.1	822.0	812.1	802.9
22.5°	841.2	826.6	795.2	782.2	773.8
25°	819.7	800.6	765.3	749.2	740.8
27.5°	793.7	773.0	734.7	713.2	700.2
30°	766.9	743.9	701.0	674.9	662.7
32.5°	740.0	713.2	667.3	638.2	625.1
35°	709.4	681.8	634.3	601.4	587.6
37.5°	678.8	648.9	599.1	562.3	545.5
40°	649.6	615.9	561.5	521.7	504.1
42.5°	616.7	583.0	526.3	481.9	466.6
45°	583.0	548.5	489.5	445.9	427.5
47.5°	550.1	511.7	453.5	406.0	389.9
50°	513.3	477.3	415.2	367.7	350.1
52.5°	480.3	440.5	379.2	329.4	314.1
55°	442.8	405.3	340.1	295.7	280.4
57.5°	409.1	368.5	302.6	260.5	247.4
60°	373.9	331.7	268.1	226.8	213.7
62.5°	338.6	296.5	232.9	194.6	180.8
65°	302.6	260.5	200.7	163.2	154.8
67.5°	266.6	223.7	165.5	137.1	127.9
70°	231.4	190.0	136.4	109.6	101.1
72.5°	196.1	155.5	108.0	87.3	85.0
75°	160.1	123.3	81.2	73.5	72.0
77.5°	127.2	93.5	63.6	59.0	57.5
80°	95.8	64.4	48.3	46.0	44.4
82.5°	65.9	39.8	34.5	32.2	32.2
85°	40.6	23.7	21.5	19.9	19.9
87.5°	18.4	10.0	10.0	9.2	8.4
90°	1.0	11.3	24.6	28.6	30.7
92.5°	23.5	17.4	26.6	33.8	34.8
95°	62.4	20.5	31.7	38.9	38.9
97.5°	113.6	84.9	32.7	40.9	41.9
100°	172.9	193.4	33.8	41.9	43.0
102.5°	240.4	253.7	75.7	41.9	44.0
105°	304.9	316.1	224.1	43.0	45.0
107.5°	373.4	382.6	398.0	240.4	106.4
110°	442.0	450.2	461.4	427.7	281.4

TEST NUMBER: P1032282

CATALOG NUMBER: S123RDIW-B560D1030UB35-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	507.5	514.6	525.9	535.1	533.0
115°	571.9	578.1	587.3	597.5	601.6
117.5°	635.4	642.5	647.6	655.8	656.8
120°	693.7	702.9	706.0	714.1	714.1
122.5°	753.0	760.2	764.3	769.4	770.4
125°	806.2	814.4	818.5	820.5	822.6
127.5°	859.4	867.6	872.7	875.8	873.7
130°	908.5	916.7	920.8	924.9	922.9
132.5°	955.6	963.8	966.8	970.9	967.9
135°	1003.7	1009.8	1013.9	1017.0	1013.9
137.5°	1044.6	1052.8	1054.8	1059.9	1057.9
140°	1085.5	1091.7	1094.7	1098.8	1096.8
142.5°	1123.4	1129.5	1132.6	1135.7	1132.6
145°	1158.2	1165.3	1167.4	1169.4	1169.4
147.5°	1191.9	1197.0	1199.1	1201.1	1196.0
150°	1222.6	1225.7	1227.7	1229.8	1226.7
152.5°	1250.2	1251.3	1252.3	1256.4	1251.3
155°	1275.8	1273.8	1274.8	1279.9	1273.8
157.5°	1296.3	1296.3	1295.3	1301.4	1293.2
160°	1314.7	1313.7	1312.7	1318.8	1311.6
162.5°	1332.1	1329.0	1328.0	1335.2	1329.0
165°	1345.4	1342.3	1341.3	1349.5	1342.3
167.5°	1356.7	1352.6	1352.6	1360.7	1352.6
170°	1365.9	1361.8	1361.8	1370.0	1361.8
172.5°	1372.0	1366.9	1367.9	1376.1	1366.9
175°	1377.1	1372.0	1373.0	1380.2	1372.0
177.5°	1379.2	1374.0	1375.1	1383.3	1373.0
180°	1377.1	1377.1	1377.1	1377.1	1377.1

(END OF REPORT)