

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032288

Luminaire Tested: S123RDIW-B560D1030UB50-4F0-XX-W2A-F

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032288
REPORT IS A COMBINATION OF REPORTS P994420 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B560D1030UB50-4F0-XX-W2A-F
Description: Define 3 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6065.0 lumens
Efficiency: N/A
Efficacy: 109.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 55.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032288

CATALOG NUMBER: S123RDIW-B560D1030UB50-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1032288

CATALOG NUMBER: S123RDIW-B560D1030UB50-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41
1	94	90	87	83	85	82	78	76	65	63	61	50	49	48	37	36	35
2	86	79	73	68	77	72	67	62	57	54	51	45	42	40	33	31	30
3	79	70	63	57	71	63	57	52	51	47	43	40	37	34	29	27	26
4	72	62	54	48	65	56	49	44	45	41	37	35	32	29	26	24	22
5	66	55	47	41	59	50	43	38	40	36	32	32	28	26	24	21	20
6	61	49	41	36	55	45	38	33	36	31	28	29	25	22	21	19	17
7	56	44	37	31	51	40	34	29	33	28	24	26	23	20	20	17	15
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14
9	48	37	29	25	44	34	27	23	28	23	19	22	18	16	17	14	12
10	45	34	27	22	41	31	25	20	25	21	17	20	17	14	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9734	9734	9734
5°	9750	9389	9364
10°	9673	9037	8858
15°	9547	8600	8305
20°	9383	8126	7685
25°	9213	7632	7099
30°	8996	7108	6406
35°	8771	6593	5774
40°	8559	6033	5077
45°	8288	5486	4450
50°	7991	4901	3801
55°	7681	4275	3206
60°	7385	3634	2602
65°	7003	2977	2032
70°	6523	2250	1451
75°	5831	1523	1149
80°	4978	1059	806
85°	3737	571	423

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 8288 cd/sqm

TEST NUMBER: P1032288

CATALOG NUMBER: S123RDIW-B560D1030UB50-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.0	1.4
10°-20°	236.5	3.9
20°-30°	340.5	5.6
30°-40°	383.4	6.3
40°-50°	366.8	6.0
50°-60°	300.2	5.0
60°-70°	202.4	3.3
70°-80°	101.5	1.7
80°-90°	29.2	0.5
90°-100°	46.5	0.8
100°-110°	224.8	3.7
110°-120°	550.8	9.1
120°-130°	699.3	11.5
130°-140°	747.0	12.3
140°-150°	698.6	11.5
150°-160°	563.5	9.3
160°-170°	363.6	6.0
170°-180°	125.3	2.1
0°-30°	662.0	10.9
0°-40°	1045.4	17.2
0°-60°	1712.5	28.2
0°-90°	2045.6	33.7
90°-120°	822.1	13.6
90°-150°	2967.0	48.9
90°-180°	4019.0	66.3
0°-180°	6065.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	904	904	904	904	904	
5°	904	901	892	898	897	86
15°	862	854	834	830	825	243
25°	785	766	733	717	709	361
35°	679	653	607	576	562	425
45°	558	525	469	427	409	431
55°	424	388	326	283	268	380
65°	290	249	192	156	148	287
75°	153	118	78	70	69	163
85°	39	23	20	19	19	43
90°	1	11	24	27	29	6
95°	60	20	30	37	37	71
105°	292	303	214	41	43	309
115°	548	553	562	572	576	541
125°	772	780	784	786	788	690
135°	961	967	971	974	971	740
145°	1109	1116	1118	1120	1120	694
155°	1222	1220	1220	1225	1220	563
165°	1288	1285	1284	1292	1285	364
175°	1318	1314	1314	1321	1314	125
180°	1318	1318	1318	1318	1318	

TEST NUMBER: P1032288

CATALOG NUMBER: S123RDIW-B560D1030UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	904.3	904.3	904.3	904.3	904.3
2.5°	908.0	905.0	896.2	904.3	902.8
5°	904.3	900.6	891.8	898.4	897.0
7.5°	897.7	894.0	883.0	887.4	885.2
10°	888.9	883.8	870.6	871.3	867.6
12.5°	876.4	870.6	853.7	853.0	848.6
15°	862.5	854.4	833.9	830.2	825.1
17.5°	845.6	836.8	811.2	803.8	796.5
20°	826.6	814.8	787.0	777.4	768.6
22.5°	805.3	791.4	761.3	748.8	740.8
25°	784.8	766.4	732.7	717.3	709.2
27.5°	759.8	740.0	703.4	682.8	670.3
30°	734.2	712.2	671.1	646.1	634.4
32.5°	708.5	682.8	638.8	610.9	598.5
35°	679.2	652.7	607.3	575.7	562.5
37.5°	649.8	621.2	573.5	538.3	522.2
40°	621.9	589.7	537.6	499.5	482.6
42.5°	590.4	558.1	503.9	461.3	446.7
45°	558.1	525.1	468.7	426.9	409.3
47.5°	526.6	489.9	434.2	388.7	373.3
50°	491.4	456.9	397.5	352.0	335.2
52.5°	459.9	421.7	363.0	315.4	300.7
55°	423.9	388.0	325.6	283.1	268.4
57.5°	391.6	352.8	289.7	249.4	236.9
60°	357.9	317.6	256.7	217.1	204.6
62.5°	324.2	283.8	223.0	186.3	173.1
65°	289.7	249.4	192.2	156.2	148.2
67.5°	255.2	214.2	158.4	131.3	122.5
70°	221.5	181.9	130.5	104.9	96.8
72.5°	187.8	148.9	103.4	83.6	81.4
75°	153.3	118.1	77.7	70.4	68.9
77.5°	121.7	89.5	60.9	56.5	55.0
80°	91.7	61.6	46.2	44.0	42.5
82.5°	63.1	38.1	33.0	30.8	30.8
85°	38.9	22.7	20.5	19.1	19.1
87.5°	17.6	9.5	9.5	8.8	8.1
90°	1.0	10.8	23.5	27.4	29.4
92.5°	22.5	16.7	25.5	32.3	33.3
95°	59.8	19.6	30.4	37.2	37.2
97.5°	108.7	81.3	31.3	39.2	40.2
100°	165.5	185.1	32.3	40.2	41.1
102.5°	230.2	242.9	72.5	40.2	42.1
105°	291.9	302.7	214.5	41.1	43.1
107.5°	357.5	366.3	381.0	230.2	101.9
110°	423.2	431.0	441.8	409.4	269.4

TEST NUMBER: P1032288

CATALOG NUMBER: S123RDIW-B560D1030UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	485.8	492.7	503.5	512.3	510.3
115°	547.6	553.4	562.2	572.0	576.0
117.5°	608.3	615.1	620.0	627.9	628.9
120°	664.1	672.9	675.9	683.7	683.7
122.5°	720.9	727.8	731.7	736.6	737.6
125°	771.9	779.7	783.6	785.6	787.5
127.5°	822.8	830.6	835.5	838.5	836.5
130°	869.8	877.7	881.6	885.5	883.5
132.5°	914.9	922.7	925.6	929.6	926.6
135°	960.9	966.8	970.7	973.6	970.7
137.5°	1000.1	1007.9	1009.9	1014.8	1012.8
140°	1039.3	1045.2	1048.1	1052.0	1050.0
142.5°	1075.5	1081.4	1084.3	1087.3	1084.3
145°	1108.8	1115.7	1117.6	1119.6	1119.6
147.5°	1141.1	1146.0	1148.0	1150.0	1145.1
150°	1170.5	1173.5	1175.4	1177.4	1174.4
152.5°	1197.0	1198.0	1198.9	1202.9	1198.0
155°	1221.5	1219.5	1220.5	1225.4	1219.5
157.5°	1241.1	1241.1	1240.1	1246.0	1238.1
160°	1258.7	1257.7	1256.7	1262.6	1255.7
162.5°	1275.3	1272.4	1271.4	1278.3	1272.4
165°	1288.1	1285.1	1284.2	1292.0	1285.1
167.5°	1298.8	1294.9	1294.9	1302.8	1294.9
170°	1307.7	1303.7	1303.7	1311.6	1303.7
172.5°	1313.5	1308.6	1309.6	1317.5	1308.6
175°	1318.4	1313.5	1314.5	1321.4	1313.5
177.5°	1320.4	1315.5	1316.5	1324.3	1314.5
180°	1318.4	1318.4	1318.4	1318.4	1318.4

(END OF REPORT)