

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031754

Luminaire Tested: S123DIW-B560D1535UB27-4F0-XX-W2A-A1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031754
REPORT IS A COMBINATION OF REPORTS P991642 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B560D1535UB27-4F0-XX-W2A-A1
Description: Define 3 Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7711.0 lumens
Efficiency: N/A
Efficacy: 101.2 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 76.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031754

CATALOG NUMBER: S123DIW-B560D1535UB27-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1031754

CATALOG NUMBER: S123DIW-B560D1535UB27-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	38	38	38
1	94	89	86	82	84	81	77	75	64	62	60	48	47	46	34	33	33
2	85	78	72	68	76	71	66	61	56	53	50	43	40	38	30	29	28
3	78	69	62	56	70	62	56	51	49	45	42	38	35	33	27	25	24
4	71	61	53	48	64	55	49	44	44	39	36	34	31	28	24	22	21
5	65	54	46	41	58	49	42	37	39	34	31	30	27	24	22	20	18
6	60	49	41	35	54	44	37	32	35	30	27	27	24	21	20	17	16
7	55	44	36	31	50	40	33	28	32	27	23	25	21	19	18	16	14
8	51	40	32	27	46	36	29	25	29	24	21	23	19	17	16	14	13
9	48	36	29	24	43	33	26	22	27	22	18	21	17	15	15	13	11
10	44	33	26	21	40	30	24	20	24	20	16	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8402	8402	8402	8402
5°	8408	9682	8432	7225
10°	8354	11716	8363	6310
15°	8239	13894	8307	5680
20°	8140	15996	8157	5226
25°	7992	16400	8010	4990
30°	7887	13549	7887	4835
35°	7756	9061	7707	4697
40°	7600	6542	7506	4488
45°	7403	5181	7189	4227
50°	6926	4400	6678	3971
55°	6400	3866	6141	3686
60°	5868	3366	5557	3387
65°	5284	2883	5028	2986
70°	4676	2393	4367	2517
75°	3998	1805	3739	1944
80°	3160	1204	2915	1276
85°	2180	554	1748	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 13551 cd/sqm

TEST NUMBER: P1031754

CATALOG NUMBER: S123DIW-B560D1535UB27-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.8	1.0
10°-20°	246.6	3.2
20°-30°	414.9	5.4
30°-40°	468.9	6.1
40°-50°	419.9	5.4
50°-60°	339.0	4.4
60°-70°	236.2	3.1
70°-80°	124.0	1.6
80°-90°	33.8	0.4
90°-100°	124.3	1.6
100°-110°	376.3	4.9
110°-120°	640.6	8.3
120°-130°	842.7	10.9
130°-140°	947.2	12.3
140°-150°	931.2	12.1
150°-160°	784.0	10.2
160°-170°	521.9	6.8
170°-180°	182.8	2.4
0°-30°	738.2	9.6
0°-40°	1207.1	15.7
0°-60°	1966.1	25.5
0°-90°	2360.1	30.6
90°-120°	1141.1	14.8
90°-150°	3862.3	50.1
90°-180°	5351.0	69.4
0°-180°	7711.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	781	781	781	781	781	
5°	780	927	782	692	780	74
15°	744	1380	750	564	744	210
25°	681	1638	682	498	681	314
35°	601	883	597	458	601	376
45°	498	476	484	389	498	381
55°	353	324	339	309	353	316
65°	219	210	208	218	219	218
75°	105	108	98	116	105	113
85°	23	25	18	23	23	26
90°	2	46	2	46	2	8
95°	90	118	90	118	90	99
105°	341	361	341	361	341	365
115°	645	646	645	646	645	638
125°	944	933	944	933	944	842
135°	1224	1223	1224	1223	1224	943
145°	1485	1485	1485	1485	1485	928
155°	1701	1698	1701	1698	1701	783
165°	1852	1846	1852	1846	1852	522
175°	1927	1919	1927	1919	1927	183
180°	1931	1931	1931	1931	1931	

TEST NUMBER: P1031754

CATALOG NUMBER: S123DIW-B560D1535UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6
2.5°	782.9	788.9	792.0	796.5	801.0	807.8	810.1	813.9	812.4	815.4	816.9
5°	779.9	790.4	799.5	810.9	821.5	829.0	836.6	848.7	857.8	859.3	866.1
7.5°	774.6	789.7	805.6	821.5	841.9	854.0	867.6	884.2	897.9	919.8	928.1
10°	767.7	788.9	811.6	833.6	861.5	880.5	897.1	925.1	953.1	975.8	996.9
12.5°	757.2	783.6	813.1	845.7	882.0	903.9	926.6	963.7	1006.0	1040.8	1063.5
15°	744.3	777.6	815.4	850.2	890.3	931.1	955.3	996.9	1057.5	1090.0	1148.2
17.5°	733.7	767.7	805.6	860.0	914.5	955.3	972.7	1049.1	1090.7	1145.2	1211.0
20°	717.1	760.2	808.6	863.1	933.4	958.4	993.9	1071.1	1122.5	1193.6	1274.5
22.5°	699.7	745.8	804.1	860.8	939.5	965.9	1014.3	1075.6	1157.3	1227.6	1316.9
25°	680.8	730.7	789.7	857.0	934.2	972.7	1018.1	1093.8	1182.3	1270.8	1353.2
27.5°	661.9	716.3	777.6	844.9	919.8	965.2	1010.6	1089.2	1202.7	1298.7	1403.9
30°	643.7	698.2	759.4	828.3	906.9	950.8	993.9	1092.2	1218.6	1326.7	1432.6
32.5°	624.0	680.0	744.3	801.8	881.2	928.1	976.5	1092.2	1228.4	1343.4	1440.2
35°	600.6	658.1	713.3	770.8	849.4	901.6	956.1	1084.7	1237.5	1348.7	1408.4
37.5°	577.9	628.6	676.2	732.2	814.6	870.6	933.4	1075.6	1232.9	1326.0	1342.6
40°	552.2	602.9	641.4	693.6	780.6	845.7	909.2	1063.5	1213.3	1272.3	1223.9
42.5°	527.2	567.3	600.6	651.3	745.8	809.4	878.2	1041.6	1174.7	1186.8	1077.9
45°	498.5	527.2	556.7	614.2	708.0	773.0	849.4	1009.8	1112.7	1077.9	940.2
47.5°	461.4	487.1	519.6	572.6	667.9	735.2	807.8	969.0	1022.7	950.0	799.5
50°	425.9	447.8	478.0	529.5	625.5	691.4	768.5	904.7	931.1	816.9	689.1
52.5°	390.3	406.9	436.4	487.9	583.9	647.5	717.8	838.9	823.7	701.2	587.7
55°	353.2	367.6	395.6	446.3	535.5	596.0	663.4	757.9	718.6	602.1	511.3
57.5°	316.9	332.1	360.8	403.2	487.1	546.1	599.8	674.0	615.0	521.9	441.7
60°	284.4	297.3	319.2	360.8	437.2	484.9	534.0	584.7	535.5	445.5	384.3
62.5°	250.4	262.5	282.9	320.7	386.5	428.9	468.2	509.8	455.4	389.5	335.1
65°	218.6	228.4	247.3	282.1	335.8	370.6	402.4	431.1	387.3	326.8	285.9
67.5°	189.9	198.2	214.1	245.1	290.5	315.4	341.1	365.3	328.3	279.9	245.1
70°	158.8	165.7	180.0	202.7	239.0	264.7	283.7	301.8	268.5	229.9	206.5
72.5°	131.6	138.4	147.5	170.9	195.9	211.8	232.2	242.0	223.1	191.4	167.9
75°	105.1	110.4	118.8	133.9	157.3	167.9	180.8	188.3	170.9	149.8	135.4
77.5°	82.4	84.7	90.8	101.4	117.2	129.3	139.2	143.7	131.6	118.0	105.9
80°	58.2	61.3	65.8	74.9	87.0	90.8	96.8	102.1	94.6	82.4	74.9
82.5°	38.6	42.4	44.6	48.4	56.0	60.5	62.0	66.6	59.8	55.2	52.2
85°	22.7	24.2	25.0	27.2	31.0	33.3	35.6	36.3	34.8	34.0	31.0
87.5°	11.3	11.3	11.3	12.9	13.6	15.1	15.9	15.9	15.9	15.1	14.4
90°	1.5	4.9	8.3	11.6	15.0	16.7	18.9	23.3	27.6	32.0	36.4
92.5°	45.5	47.5	49.5	51.6	53.6	54.6	55.6	57.6	59.7	61.7	63.7
95°	89.5	91.9	94.2	96.6	98.9	100.1	101.5	104.2	106.9	109.6	112.3
97.5°	147.2	148.9	150.5	152.2	153.9	154.7	155.7	157.7	159.8	161.8	163.8
100°	206.3	208.3	210.3	212.4	214.4	215.4	216.2	217.9	219.6	221.3	223.0
102.5°	274.6	275.6	276.6	277.6	278.6	279.1	280.3	282.7	285.0	287.4	289.8
105°	341.3	342.0	342.7	343.4	344.1	344.4	345.9	348.9	352.0	355.0	358.0
107.5°	420.2	420.5	420.9	421.2	421.5	421.7	422.4	423.7	425.1	426.4	427.8
110°	493.0	493.7	494.4	495.1	495.8	496.1	496.4	497.1	497.8	498.4	499.1

TEST NUMBER: P1031754

CATALOG NUMBER: S123DIW-B560D1535UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	568.9	569.2	569.6	569.9	570.2	570.4	570.4	570.4	570.4	570.4	570.4
115°	644.7	645.7	646.7	647.8	648.8	649.3	649.0	648.3	647.6	647.0	646.3
117.5°	722.1	722.4	722.8	723.1	723.4	723.6	723.3	722.6	721.9	721.3	720.6
120°	793.4	795.4	797.4	799.5	801.5	802.5	801.7	800.0	798.3	796.6	794.9
122.5°	867.7	869.1	870.4	871.8	873.1	873.8	873.5	872.8	872.1	871.5	870.8
125°	943.6	944.6	945.6	946.6	947.6	948.1	947.8	947.1	946.4	945.8	945.1
127.5°	1013.4	1015.4	1017.4	1019.5	1021.5	1022.5	1022.2	1021.5	1020.8	1020.1	1019.4
130°	1083.2	1085.9	1088.6	1091.3	1094.0	1095.3	1094.8	1093.8	1092.7	1091.7	1090.7
132.5°	1152.9	1155.6	1158.3	1161.0	1163.7	1165.1	1164.8	1164.1	1163.4	1162.7	1162.0
135°	1224.2	1226.2	1228.2	1230.3	1232.3	1233.3	1233.1	1232.8	1232.5	1232.1	1231.8
137.5°	1289.5	1291.2	1292.9	1294.6	1296.3	1297.1	1297.6	1298.6	1299.6	1300.6	1301.6
140°	1357.7	1359.4	1361.1	1362.8	1364.5	1365.3	1365.5	1365.8	1366.1	1366.5	1366.8
142.5°	1419.9	1421.6	1423.3	1425.0	1426.7	1427.5	1427.8	1428.5	1429.2	1429.9	1430.6
145°	1485.2	1485.9	1486.5	1487.2	1487.9	1488.2	1488.7	1489.7	1490.7	1491.7	1492.7
147.5°	1541.3	1542.7	1544.0	1545.4	1546.7	1547.4	1547.9	1548.9	1549.9	1550.9	1551.9
150°	1600.5	1601.2	1601.8	1602.5	1603.2	1603.5	1603.8	1604.5	1605.2	1605.8	1606.5
152.5°	1649.0	1650.0	1651.0	1652.1	1653.1	1653.6	1653.8	1654.1	1654.4	1654.8	1655.1
155°	1700.6	1700.6	1700.6	1700.6	1700.6	1700.6	1700.8	1701.1	1701.4	1701.8	1702.1
157.5°	1744.6	1744.3	1743.9	1743.6	1743.3	1743.1	1743.3	1743.6	1743.9	1744.3	1744.6
160°	1785.5	1784.8	1784.2	1783.5	1782.8	1782.5	1782.5	1782.5	1782.5	1782.5	1782.5
162.5°	1821.9	1820.9	1819.9	1818.9	1817.9	1817.4	1817.6	1817.9	1818.2	1818.6	1818.9
165°	1852.3	1851.3	1850.3	1849.2	1848.2	1847.7	1847.7	1847.7	1847.7	1847.7	1847.7
167.5°	1878.1	1876.7	1875.4	1874.0	1872.7	1872.0	1872.2	1872.5	1872.8	1873.2	1873.5
170°	1899.3	1897.9	1896.6	1895.2	1893.9	1893.2	1893.2	1893.2	1893.2	1893.2	1893.2
172.5°	1916.0	1914.6	1913.3	1911.9	1910.6	1909.9	1909.9	1909.9	1909.9	1909.9	1909.9
175°	1926.6	1925.2	1923.9	1922.5	1921.2	1920.5	1920.5	1920.5	1920.5	1920.5	1920.5
177.5°	1932.7	1931.3	1930.0	1928.6	1927.3	1926.6	1926.6	1926.6	1926.6	1926.6	1926.6
180°	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2

TEST NUMBER: P1031754

CATALOG NUMBER: S123DIW-B560D1535UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6
2.5°	822.2	823.7	829.0	832.8	840.4	839.6	839.6	838.9	836.6	840.4	842.6
5°	879.7	892.6	894.1	910.7	911.5	918.3	922.8	919.0	928.1	927.4	920.5
7.5°	950.8	968.2	976.5	992.4	1010.6	1006.0	1023.4	1026.4	1024.9	1032.5	1037.8
10°	1028.7	1059.0	1080.1	1109.6	1117.2	1121.7	1133.1	1142.9	1162.6	1147.5	1157.3
12.5°	1118.0	1139.9	1167.9	1214.8	1238.2	1253.4	1258.7	1265.5	1279.1	1270.8	1271.5
15°	1192.8	1222.3	1270.0	1328.2	1335.1	1354.0	1349.4	1390.3	1409.9	1380.4	1397.1
17.5°	1270.8	1310.1	1366.8	1417.5	1446.2	1459.1	1471.2	1510.5	1509.0	1504.5	1508.3
20°	1320.7	1385.0	1455.3	1522.6	1531.0	1540.8	1573.3	1590.0	1586.9	1599.8	1608.1
22.5°	1391.0	1459.1	1534.0	1578.6	1597.5	1608.9	1634.6	1645.2	1649.7	1652.7	1647.4
25°	1450.0	1522.6	1577.9	1617.2	1628.5	1634.6	1642.9	1645.9	1643.7	1638.4	1642.9
27.5°	1490.1	1548.4	1586.2	1604.3	1598.3	1588.4	1572.6	1562.0	1538.5	1527.2	1540.8
30°	1506.8	1532.5	1543.8	1513.6	1483.3	1459.1	1428.8	1372.9	1329.0	1341.9	1324.5
32.5°	1480.3	1463.6	1409.2	1331.3	1307.8	1268.5	1183.0	1117.2	1119.5	1084.7	1099.1
35°	1402.4	1326.7	1223.9	1105.9	1074.8	1053.7	959.9	945.5	915.2	882.7	891.8
37.5°	1264.7	1154.3	1029.5	942.5	896.3	850.2	797.2	765.5	747.3	733.7	744.3
40°	1096.8	962.1	859.3	781.4	742.0	712.5	676.2	644.5	624.0	621.8	625.5
42.5°	931.9	818.4	723.9	649.8	636.9	602.1	578.6	553.7	547.6	537.8	543.1
45°	788.9	696.6	618.7	558.2	543.1	534.0	505.3	489.4	482.6	476.5	485.6
47.5°	685.3	588.5	531.8	495.4	480.3	465.2	449.3	438.7	433.4	434.2	433.4
50°	585.5	514.4	464.4	436.4	427.4	416.8	403.9	397.1	394.8	388.0	393.3
52.5°	503.8	452.3	417.5	391.1	384.3	376.7	366.1	362.3	357.0	355.5	355.5
55°	438.0	397.9	369.9	352.5	344.2	338.1	332.1	327.5	323.7	323.7	323.7
57.5°	386.5	351.7	331.3	316.2	313.2	307.1	300.3	300.3	295.0	294.2	296.5
60°	342.7	311.6	295.8	282.9	278.4	276.8	270.0	270.0	268.5	264.7	267.8
62.5°	298.0	275.3	261.7	251.9	247.3	247.3	242.0	238.3	238.3	239.0	237.5
65°	257.2	240.5	228.4	220.9	218.6	215.6	214.8	211.8	209.5	210.3	209.5
67.5°	220.9	208.0	199.7	193.6	189.9	188.3	186.1	186.1	184.6	185.3	181.5
70°	188.3	175.5	168.7	162.6	161.1	161.1	158.1	158.8	157.3	159.6	158.1
72.5°	155.1	145.2	139.9	137.7	136.2	135.4	133.9	132.4	131.6	133.1	132.4
75°	125.6	117.2	113.5	111.9	110.4	110.4	109.7	108.9	108.2	108.2	108.2
77.5°	97.6	92.3	87.7	89.3	87.0	87.7	85.5	85.5	86.2	85.5	85.5
80°	71.9	68.1	68.1	66.6	63.5	65.1	65.1	62.8	62.0	63.5	61.3
82.5°	47.7	46.9	45.4	44.6	43.1	43.9	43.1	42.4	41.6	43.1	41.6
85°	28.0	28.0	27.2	25.7	27.2	26.5	25.7	25.7	25.0	25.0	25.0
87.5°	14.4	12.9	12.9	12.1	12.9	11.3	12.1	11.3	10.6	11.3	10.6
90°	37.8	39.1	40.5	41.8	42.5	42.8	43.5	44.2	44.8	45.5	44.8
92.5°	64.7	65.7	66.8	67.8	68.3	68.0	67.3	66.6	65.9	65.2	65.9
95°	113.6	115.0	116.3	117.6	118.3	118.3	118.3	118.3	118.3	118.3	118.3
97.5°	165.5	167.2	168.9	170.6	171.4	171.2	170.9	170.6	170.2	169.9	170.2
100°	224.0	225.0	226.1	227.1	227.6	227.9	228.6	229.3	229.9	230.6	229.9
102.5°	290.8	291.8	292.8	293.8	294.3	294.1	293.8	293.5	293.1	292.8	293.1
105°	358.0	358.0	358.0	358.0	358.0	358.3	359.0	359.7	360.4	361.1	360.4
107.5°	428.8	429.8	430.9	431.9	432.4	432.2	431.9	431.5	431.2	430.8	431.2
110°	500.5	501.8	503.2	504.5	505.2	504.9	504.2	503.5	502.8	502.1	502.8

TEST NUMBER: P1031754

CATALOG NUMBER: S123DIW-B560D1535UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	572.1	573.8	575.5	577.2	578.0	578.0	578.0	578.0	578.0	578.0	578.0
115°	646.6	647.0	647.3	647.6	647.8	647.6	647.3	647.0	646.6	646.3	646.6
117.5°	720.6	720.6	720.6	720.6	720.6	720.1	719.1	718.0	717.0	716.0	717.0
120°	794.6	794.2	793.9	793.6	793.4	793.1	792.4	791.7	791.1	790.4	791.1
122.5°	869.8	868.8	867.7	866.7	866.2	865.7	864.7	863.7	862.7	861.7	862.7
125°	943.7	942.4	941.0	939.7	939.0	938.3	937.0	935.7	934.3	933.0	934.3
127.5°	1017.4	1015.4	1013.3	1011.3	1010.3	1009.6	1008.3	1007.0	1005.6	1004.3	1005.6
130°	1089.4	1088.0	1086.7	1085.4	1084.7	1083.5	1081.2	1078.8	1076.5	1074.1	1076.5
132.5°	1160.3	1158.7	1157.0	1155.3	1154.5	1153.7	1152.0	1150.3	1148.6	1146.9	1148.6
135°	1230.5	1229.1	1227.8	1226.5	1225.8	1225.5	1224.8	1224.1	1223.4	1222.7	1223.4
137.5°	1299.9	1298.2	1296.5	1294.8	1294.0	1293.5	1292.5	1291.5	1290.5	1289.5	1290.5
140°	1366.5	1366.1	1365.8	1365.5	1365.3	1364.1	1361.8	1359.4	1357.1	1354.7	1357.1
142.5°	1430.2	1429.9	1429.5	1429.2	1429.0	1428.2	1426.5	1424.8	1423.1	1421.4	1423.1
145°	1492.4	1492.0	1491.7	1491.4	1491.2	1490.5	1489.2	1487.9	1486.5	1485.2	1486.5
147.5°	1551.9	1551.9	1551.9	1551.9	1551.9	1550.9	1548.9	1546.8	1544.8	1542.8	1544.8
150°	1606.5	1606.5	1606.5	1606.5	1606.5	1605.5	1603.5	1601.4	1599.4	1597.4	1599.4
152.5°	1655.8	1656.4	1657.1	1657.8	1658.1	1657.3	1655.6	1653.9	1652.2	1650.5	1652.2
155°	1703.5	1704.8	1706.2	1707.5	1708.2	1707.0	1704.6	1702.3	1699.9	1697.5	1699.9
157.5°	1745.9	1747.3	1748.6	1749.9	1750.6	1749.6	1747.6	1745.5	1743.5	1741.5	1743.5
160°	1784.2	1785.9	1787.6	1789.3	1790.1	1789.4	1788.1	1786.7	1785.4	1784.0	1785.4
162.5°	1820.6	1822.3	1824.0	1825.7	1826.5	1825.3	1823.0	1820.6	1818.3	1815.9	1818.3
165°	1849.7	1851.7	1853.8	1855.8	1856.8	1855.6	1853.3	1850.9	1848.6	1846.2	1848.6
167.5°	1875.5	1877.5	1879.6	1881.6	1882.6	1881.6	1879.6	1877.5	1875.5	1873.5	1875.5
170°	1895.6	1898.0	1900.3	1902.7	1903.9	1902.7	1900.3	1898.0	1895.6	1893.2	1895.6
172.5°	1911.9	1913.9	1916.0	1918.0	1919.0	1917.8	1915.5	1913.1	1910.8	1908.4	1910.8
175°	1922.5	1924.6	1926.6	1928.7	1929.7	1928.5	1926.1	1923.8	1921.4	1919.0	1921.4
177.5°	1928.6	1930.6	1932.7	1934.7	1935.7	1934.5	1932.2	1929.8	1927.5	1925.1	1927.5
180°	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2

TEST NUMBER: P1031754

CATALOG NUMBER: S123DIW-B560D1535UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6
2.5°	836.6	838.9	832.8	831.3	831.3	834.3	832.0	811.6	815.4	810.9	809.4
5°	928.9	924.3	918.3	915.2	911.5	900.9	900.1	876.7	872.1	857.0	850.2
7.5°	1030.2	1026.4	1008.3	1006.0	1004.5	994.7	969.7	944.7	926.6	909.2	892.6
10°	1146.0	1134.6	1126.3	1109.6	1101.3	1087.7	1055.2	1031.7	1000.7	974.2	939.5
12.5°	1285.1	1272.3	1244.3	1232.2	1221.6	1183.8	1151.2	1124.8	1064.3	1046.1	1003.0
15°	1387.2	1360.0	1357.0	1330.5	1329.0	1287.4	1225.4	1196.6	1149.7	1083.2	1038.5
17.5°	1497.7	1473.5	1454.6	1422.8	1418.3	1378.9	1333.5	1263.2	1211.8	1148.2	1091.5
20°	1578.6	1565.8	1533.2	1520.4	1493.9	1460.6	1413.7	1326.7	1263.9	1200.4	1130.8
22.5°	1642.9	1630.0	1604.3	1586.9	1571.8	1528.7	1472.7	1398.6	1312.4	1229.2	1157.3
25°	1642.2	1638.4	1627.8	1619.5	1608.1	1576.3	1529.4	1458.3	1362.3	1270.8	1170.9
27.5°	1549.1	1559.7	1577.9	1586.9	1584.7	1580.1	1553.7	1493.9	1407.7	1298.7	1186.8
30°	1355.5	1394.1	1428.1	1473.5	1487.1	1520.4	1535.5	1501.5	1432.6	1331.3	1207.2
32.5°	1124.0	1180.0	1254.1	1279.1	1322.2	1386.5	1458.3	1471.2	1428.1	1350.2	1220.1
35°	922.1	968.2	1025.7	1065.0	1103.6	1208.0	1298.7	1377.4	1391.8	1340.3	1217.1
37.5°	763.2	795.7	846.4	879.7	915.2	1004.5	1131.6	1233.7	1305.6	1307.1	1208.7
40°	648.2	662.6	706.5	730.7	764.7	841.9	955.3	1088.5	1193.6	1242.0	1186.8
42.5°	549.1	568.1	604.4	622.5	644.5	711.8	786.7	913.0	1043.1	1146.7	1146.0
45°	490.1	503.8	520.4	535.5	560.5	600.6	686.1	780.6	905.4	1022.7	1068.8
47.5°	438.0	450.8	467.5	472.0	488.6	526.5	578.6	661.1	777.6	894.1	981.1
50°	394.1	404.7	416.0	424.3	431.9	462.9	502.3	571.8	664.9	777.6	885.7
52.5°	360.0	367.6	377.4	382.0	388.8	411.5	441.7	493.2	569.6	672.4	777.6
55°	328.3	333.6	339.6	347.2	350.2	366.9	390.3	434.2	490.9	583.2	683.0
57.5°	298.8	301.0	304.8	309.4	313.2	327.5	347.9	377.4	427.4	498.5	593.0
60°	265.5	271.5	273.8	278.4	280.6	292.0	307.9	332.8	371.4	432.7	503.8
62.5°	237.5	241.3	245.1	247.3	252.6	256.4	269.3	292.0	323.7	369.1	433.4
65°	212.5	214.1	216.3	218.6	220.1	224.7	236.8	251.9	276.1	316.2	366.1
67.5°	183.8	185.3	188.3	189.1	190.6	196.7	203.5	216.3	236.8	267.0	307.9
70°	155.8	158.1	159.6	161.1	163.4	165.7	173.2	183.8	199.7	220.9	252.6
72.5°	131.6	133.9	133.9	135.4	134.6	137.7	145.2	152.8	163.4	180.8	208.8
75°	107.4	107.4	108.9	109.7	110.4	113.5	116.5	122.5	130.9	144.5	161.9
77.5°	84.7	84.0	85.5	85.5	85.5	87.7	90.8	93.8	99.1	108.9	122.5
80°	62.0	62.0	63.5	64.3	62.8	63.5	65.1	68.1	71.9	78.7	86.2
82.5°	40.8	43.9	43.1	43.9	43.1	44.6	45.4	46.1	47.7	50.7	56.0
85°	25.0	25.0	25.0	25.7	25.0	25.7	25.7	25.7	26.5	28.0	30.3
87.5°	10.6	10.6	10.6	11.3	10.6	10.6	11.3	10.6	11.3	11.3	12.1
90°	44.2	43.5	42.8	42.5	41.8	40.5	39.1	37.8	36.4	32.0	27.6
92.5°	66.6	67.3	68.0	68.3	67.8	66.8	65.7	64.7	63.7	61.7	59.7
95°	118.3	118.3	118.3	118.3	117.6	116.3	115.0	113.6	112.3	109.6	106.9
97.5°	170.6	170.9	171.2	171.4	170.6	168.9	167.2	165.5	163.8	161.8	159.8
100°	229.3	228.6	227.9	227.6	227.1	226.1	225.0	224.0	223.0	221.3	219.6
102.5°	293.5	293.8	294.1	294.3	293.8	292.8	291.8	290.8	289.8	287.4	285.0
105°	359.7	359.0	358.3	358.0	358.0	358.0	358.0	358.0	358.0	355.0	352.0
107.5°	431.5	431.9	432.2	432.4	431.9	430.9	429.8	428.8	427.8	426.4	425.1
110°	503.5	504.2	504.9	505.2	504.5	503.2	501.8	500.5	499.1	498.4	497.8

TEST NUMBER: P1031754

CATALOG NUMBER: S123DIW-B560D1535UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	578.0	578.0	578.0	578.0	577.2	575.5	573.8	572.1	570.4	570.4	570.4
115°	647.0	647.3	647.6	647.8	647.6	647.3	647.0	646.6	646.3	647.0	647.6
117.5°	718.0	719.1	720.1	720.6	720.6	720.6	720.6	720.6	720.6	721.3	721.9
120°	791.7	792.4	793.1	793.4	793.6	793.9	794.2	794.6	794.9	796.6	798.3
122.5°	863.7	864.7	865.7	866.2	866.7	867.7	868.8	869.8	870.8	871.5	872.1
125°	935.7	937.0	938.3	939.0	939.7	941.0	942.4	943.7	945.1	945.8	946.4
127.5°	1007.0	1008.3	1009.6	1010.3	1011.3	1013.3	1015.4	1017.4	1019.4	1020.1	1020.8
130°	1078.8	1081.2	1083.5	1084.7	1085.4	1086.7	1088.0	1089.4	1090.7	1091.7	1092.7
132.5°	1150.3	1152.0	1153.7	1154.5	1155.3	1157.0	1158.7	1160.3	1162.0	1162.7	1163.4
135°	1224.1	1224.8	1225.5	1225.8	1226.5	1227.8	1229.1	1230.5	1231.8	1232.1	1232.5
137.5°	1291.5	1292.5	1293.5	1294.0	1294.8	1296.5	1298.2	1299.9	1301.6	1300.6	1299.6
140°	1359.4	1361.8	1364.1	1365.3	1365.5	1365.8	1366.1	1366.5	1366.8	1366.5	1366.1
142.5°	1424.8	1426.5	1428.2	1429.0	1429.2	1429.5	1429.9	1430.2	1430.6	1429.9	1429.2
145°	1487.9	1489.2	1490.5	1491.2	1491.4	1491.7	1492.0	1492.4	1492.7	1491.7	1490.7
147.5°	1546.8	1548.9	1550.9	1551.9	1551.9	1551.9	1551.9	1551.9	1551.9	1550.9	1549.9
150°	1601.4	1603.5	1605.5	1606.5	1606.5	1606.5	1606.5	1606.5	1606.5	1605.8	1605.2
152.5°	1653.9	1655.6	1657.3	1658.1	1657.8	1657.1	1656.4	1655.8	1655.1	1654.8	1654.4
155°	1702.3	1704.6	1707.0	1708.2	1707.5	1706.2	1704.8	1703.5	1702.1	1701.8	1701.4
157.5°	1745.5	1747.6	1749.6	1750.6	1749.9	1748.6	1747.3	1745.9	1744.6	1744.3	1743.9
160°	1786.7	1788.1	1789.4	1790.1	1789.3	1787.6	1785.9	1784.2	1782.5	1782.5	1782.5
162.5°	1820.6	1823.0	1825.3	1826.5	1825.7	1824.0	1822.3	1820.6	1818.9	1818.6	1818.2
165°	1850.9	1853.3	1855.6	1856.8	1855.8	1853.8	1851.7	1849.7	1847.7	1847.7	1847.7
167.5°	1877.5	1879.6	1881.6	1882.6	1881.6	1879.6	1877.5	1875.5	1873.5	1873.2	1872.8
170°	1898.0	1900.3	1902.7	1903.9	1902.7	1900.3	1898.0	1895.6	1893.2	1893.2	1893.2
172.5°	1913.1	1915.5	1917.8	1919.0	1918.0	1916.0	1913.9	1911.9	1909.9	1909.9	1909.9
175°	1923.8	1926.1	1928.5	1929.7	1928.7	1926.6	1924.6	1922.5	1920.5	1920.5	1920.5
177.5°	1929.8	1932.2	1934.5	1935.7	1934.7	1932.7	1930.6	1928.6	1926.6	1926.6	1926.6
180°	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2

TEST NUMBER: P1031754

CATALOG NUMBER: S123DIW-B560D1535UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6
2.5°	801.8	799.5	799.5	798.0	793.5	785.1	784.4	785.9	781.4	776.8	770.0
5°	841.1	826.7	822.2	817.7	808.6	793.5	787.4	782.1	773.8	764.0	753.4
7.5°	874.4	854.0	847.9	839.6	821.5	800.3	786.7	775.3	764.0	750.4	737.5
10°	916.0	886.5	872.1	860.0	835.1	805.6	785.1	768.5	750.4	733.7	717.1
12.5°	962.9	915.2	910.7	881.2	852.5	808.6	783.6	759.4	735.2	714.8	697.4
15°	1002.2	950.0	931.1	911.5	856.2	801.8	777.6	750.4	722.4	700.4	674.7
17.5°	1027.2	984.1	944.0	917.5	860.0	811.6	764.7	733.7	704.2	674.0	652.8
20°	1057.5	994.7	959.9	924.3	867.6	804.1	757.2	718.6	682.3	655.0	629.3
22.5°	1087.7	1003.0	974.2	935.7	869.1	796.5	743.5	705.0	663.4	636.1	608.1
25°	1084.7	1015.1	967.4	934.9	854.0	789.7	727.7	682.3	643.7	608.9	580.9
27.5°	1087.0	1001.5	953.1	915.2	843.4	779.9	711.0	663.4	623.3	587.0	557.5
30°	1087.7	981.1	938.7	893.3	823.7	756.4	692.1	643.7	601.3	562.0	535.5
32.5°	1085.4	964.4	911.5	870.6	792.7	733.7	670.2	618.7	575.6	539.3	514.4
35°	1080.1	944.7	883.5	832.0	760.9	701.2	649.8	596.8	550.7	517.4	488.6
37.5°	1065.8	923.6	854.0	803.3	723.9	663.4	618.0	574.1	529.5	490.1	465.9
40°	1055.2	894.8	824.5	769.3	683.8	624.8	587.0	545.4	501.5	465.9	442.5
42.5°	1031.0	867.6	794.2	728.4	644.5	583.9	548.4	515.1	477.3	442.5	421.3
45°	991.6	838.1	757.2	690.6	601.3	543.9	511.3	484.1	450.8	417.5	396.4
47.5°	936.4	795.7	717.8	651.3	559.0	500.7	468.2	447.8	421.3	393.3	375.2
50°	876.7	749.6	677.7	611.9	518.1	461.4	429.6	410.7	393.3	367.6	350.2
52.5°	798.8	700.4	631.6	568.8	474.3	419.8	391.8	378.2	360.0	341.9	326.8
55°	723.1	636.9	580.2	520.4	431.1	380.5	353.2	338.9	328.3	313.2	301.0
57.5°	635.4	577.9	525.7	471.2	391.1	344.9	319.2	301.8	295.0	288.2	276.8
60°	554.4	510.6	468.2	422.8	349.5	307.9	282.9	269.3	262.5	257.9	250.4
62.5°	480.3	446.3	410.0	373.7	307.1	269.3	250.4	236.8	230.7	229.9	223.1
65°	409.2	385.0	355.5	320.0	267.8	234.5	216.3	208.0	201.2	201.2	195.9
67.5°	338.1	321.5	298.0	273.1	232.2	201.2	184.6	177.0	173.2	173.2	169.4
70°	281.4	270.0	248.9	226.9	191.4	167.9	155.1	148.3	146.0	146.7	143.7
72.5°	228.4	216.3	198.9	183.0	156.6	139.2	130.1	122.5	118.8	119.5	118.8
75°	177.0	170.9	155.8	143.7	122.5	110.4	102.1	98.3	95.3	96.1	94.6
77.5°	133.1	124.1	115.7	107.4	94.6	84.7	77.9	74.1	71.9	71.9	71.9
80°	90.8	89.3	82.4	77.9	67.3	59.8	54.5	53.7	51.4	51.4	51.4
82.5°	59.0	55.2	51.4	48.4	42.4	37.8	35.6	34.0	33.3	32.5	34.0
85°	32.5	30.3	28.7	25.7	23.4	21.2	18.9	18.2	17.4	18.2	17.4
87.5°	12.9	10.6	10.6	9.8	9.1	8.3	8.3	6.8	6.8	6.1	6.1
90°	23.3	18.9	16.7	15.0	11.6	8.3	4.9	1.5	4.9	8.3	11.6
92.5°	57.6	55.6	54.6	53.6	51.6	49.5	47.5	45.5	47.5	49.5	51.6
95°	104.2	101.5	100.1	98.9	96.6	94.2	91.9	89.5	91.9	94.2	96.6
97.5°	157.7	155.7	154.7	153.9	152.2	150.5	148.9	147.2	148.9	150.5	152.2
100°	217.9	216.2	215.4	214.4	212.4	210.3	208.3	206.3	208.3	210.3	212.4
102.5°	282.7	280.3	279.1	278.6	277.6	276.6	275.6	274.6	275.6	276.6	277.6
105°	348.9	345.9	344.4	344.1	343.4	342.7	342.0	341.3	342.0	342.7	343.4
107.5°	423.7	422.4	421.7	421.5	421.2	420.9	420.5	420.2	420.5	420.9	421.2
110°	497.1	496.4	496.1	495.8	495.1	494.4	493.7	493.0	493.7	494.4	495.1

TEST NUMBER: P1031754

CATALOG NUMBER: S123DIW-B560D1535UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	570.4	570.4	570.4	570.2	569.9	569.6	569.2	568.9	569.2	569.6	569.9
115°	648.3	649.0	649.3	648.8	647.8	646.7	645.7	644.7	645.7	646.7	647.8
117.5°	722.6	723.3	723.6	723.4	723.1	722.8	722.4	722.1	722.4	722.8	723.1
120°	800.0	801.7	802.5	801.5	799.5	797.4	795.4	793.4	795.4	797.4	799.5
122.5°	872.8	873.5	873.8	873.1	871.8	870.4	869.1	867.7	869.1	870.4	871.8
125°	947.1	947.8	948.1	947.6	946.6	945.6	944.6	943.6	944.6	945.6	946.6
127.5°	1021.5	1022.2	1022.5	1021.5	1019.5	1017.4	1015.4	1013.4	1015.4	1017.4	1019.5
130°	1093.8	1094.8	1095.3	1094.0	1091.3	1088.6	1085.9	1083.2	1085.9	1088.6	1091.3
132.5°	1164.1	1164.8	1165.1	1163.7	1161.0	1158.3	1155.6	1152.9	1155.6	1158.3	1161.0
135°	1232.8	1233.1	1233.3	1232.3	1230.3	1228.2	1226.2	1224.2	1226.2	1228.2	1230.3
137.5°	1298.6	1297.6	1297.1	1296.3	1294.6	1292.9	1291.2	1289.5	1291.2	1292.9	1294.6
140°	1365.8	1365.5	1365.3	1364.5	1362.8	1361.1	1359.4	1357.7	1359.4	1361.1	1362.8
142.5°	1428.5	1427.8	1427.5	1426.7	1425.0	1423.3	1421.6	1419.9	1421.6	1423.3	1425.0
145°	1489.7	1488.7	1488.2	1487.9	1487.2	1486.5	1485.9	1485.2	1485.9	1486.5	1487.2
147.5°	1548.9	1547.9	1547.4	1546.7	1545.4	1544.0	1542.7	1541.3	1542.7	1544.0	1545.4
150°	1604.5	1603.8	1603.5	1603.2	1602.5	1601.8	1601.2	1600.5	1601.2	1601.8	1602.5
152.5°	1654.1	1653.8	1653.6	1653.1	1652.1	1651.0	1650.0	1649.0	1650.0	1651.0	1652.1
155°	1701.1	1700.8	1700.6	1700.6	1700.6	1700.6	1700.6	1700.6	1700.6	1700.6	1700.6
157.5°	1743.6	1743.3	1743.1	1743.3	1743.6	1743.9	1744.3	1744.6	1744.3	1743.9	1743.6
160°	1782.5	1782.5	1782.5	1782.8	1783.5	1784.2	1784.8	1785.5	1784.8	1784.2	1783.5
162.5°	1817.9	1817.6	1817.4	1817.9	1818.9	1819.9	1820.9	1821.9	1820.9	1819.9	1818.9
165°	1847.7	1847.7	1847.7	1848.2	1849.2	1850.3	1851.3	1852.3	1851.3	1850.3	1849.2
167.5°	1872.5	1872.2	1872.0	1872.7	1874.0	1875.4	1876.7	1878.1	1876.7	1875.4	1874.0
170°	1893.2	1893.2	1893.2	1893.9	1895.2	1896.6	1897.9	1899.3	1897.9	1896.6	1895.2
172.5°	1909.9	1909.9	1909.9	1910.6	1911.9	1913.3	1914.6	1916.0	1914.6	1913.3	1911.9
175°	1920.5	1920.5	1920.5	1921.2	1922.5	1923.9	1925.2	1926.6	1925.2	1923.9	1922.5
177.5°	1926.6	1926.6	1926.6	1927.3	1928.6	1930.0	1931.3	1932.7	1931.3	1930.0	1928.6
180°	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2

TEST NUMBER: P1031754

CATALOG NUMBER: S123DIW-B560D1535UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6
2.5°	768.5	767.7	769.3	764.7	757.2	753.4	742.8	740.5	739.8	740.5	741.3
5°	747.3	746.6	744.3	736.7	727.7	720.9	708.0	707.2	702.7	698.2	700.4
7.5°	726.9	723.9	719.3	709.5	697.4	689.8	679.2	671.7	665.6	661.9	658.8
10°	706.5	701.9	697.4	684.5	669.4	658.1	645.2	639.2	632.4	629.3	626.3
12.5°	680.0	675.5	667.1	652.0	642.9	628.6	615.7	609.7	605.9	599.8	596.0
15°	658.8	649.8	645.2	629.3	610.4	608.9	585.5	583.9	576.4	576.4	570.3
17.5°	634.6	627.8	619.5	603.6	590.0	576.4	564.3	559.7	552.9	551.4	548.4
20°	611.2	602.1	599.1	583.2	568.8	552.2	539.3	534.8	531.8	528.7	531.0
22.5°	587.0	579.4	571.8	557.5	546.9	530.2	522.7	518.1	513.6	512.1	512.8
25°	563.5	556.7	549.1	534.8	523.4	509.8	503.0	500.7	498.5	498.5	497.7
27.5°	540.8	534.0	527.2	514.4	503.0	493.2	487.9	485.6	483.3	484.9	486.4
30°	517.4	511.3	505.3	493.9	484.9	475.8	472.8	471.2	470.5	474.3	474.3
32.5°	496.2	490.9	486.4	475.8	466.7	459.1	456.9	457.6	458.4	460.6	462.2
35°	474.3	470.5	465.9	456.9	449.3	442.5	443.3	443.3	444.8	448.5	451.6
37.5°	454.6	449.3	445.5	438.0	431.9	425.9	428.1	430.4	431.9	436.4	438.0
40°	431.1	428.9	425.9	418.3	413.0	412.2	413.0	414.5	417.5	419.8	422.1
42.5°	412.2	409.2	405.4	399.4	394.8	395.6	396.4	397.9	399.4	403.2	405.4
45°	391.1	388.8	385.8	380.5	376.7	377.4	378.2	378.2	379.7	384.3	385.8
47.5°	367.6	368.4	364.6	359.3	357.0	357.0	357.0	358.5	362.3	363.8	364.6
50°	344.9	343.4	342.7	337.4	335.8	335.1	335.8	336.6	341.9	341.1	343.4
52.5°	320.7	320.7	320.0	316.9	314.7	314.7	313.2	316.9	318.4	320.0	322.2
55°	297.3	295.0	294.2	292.7	289.7	288.9	290.5	295.0	296.5	298.0	300.3
57.5°	271.5	271.5	270.0	267.8	267.8	267.8	267.8	270.8	273.1	274.6	279.1
60°	248.1	245.1	242.8	242.8	242.8	242.0	246.6	246.6	251.1	251.9	253.4
62.5°	220.1	218.6	217.1	217.8	217.1	218.6	220.1	223.1	223.9	226.2	228.4
65°	193.6	193.6	192.1	196.7	193.6	193.6	197.4	197.4	198.9	201.2	204.2
67.5°	167.9	168.7	167.2	167.2	168.7	169.4	170.2	173.2	174.0	177.0	180.8
70°	141.4	143.0	143.7	142.2	143.7	145.2	146.7	147.5	150.5	152.0	154.3
72.5°	118.0	119.5	117.2	118.0	118.8	120.3	121.0	122.5	124.1	128.6	130.1
75°	94.6	93.8	93.0	96.1	94.6	97.6	98.3	98.3	99.8	103.6	105.1
77.5°	72.6	72.6	73.4	71.9	74.1	73.4	74.1	76.4	78.7	78.7	84.7
80°	50.7	52.2	52.2	52.2	52.9	53.7	52.2	56.0	56.7	56.7	59.0
82.5°	32.5	33.3	32.5	34.0	34.0	35.6	34.8	35.6	37.1	38.6	39.3
85°	17.4	17.4	18.9	18.9	18.2	18.9	18.2	18.9	20.4	20.4	21.2
87.5°	6.1	6.1	6.1	6.1	6.8	6.1	6.8	6.8	6.1	6.1	8.3
90°	15.0	16.7	18.9	23.3	27.6	32.0	36.4	37.8	39.1	40.5	41.8
92.5°	53.6	54.6	55.6	57.6	59.7	61.7	63.7	64.7	65.7	66.8	67.8
95°	98.9	100.1	101.5	104.2	106.9	109.6	112.3	113.6	115.0	116.3	117.6
97.5°	153.9	154.7	155.7	157.7	159.8	161.8	163.8	165.5	167.2	168.9	170.6
100°	214.4	215.4	216.2	217.9	219.6	221.3	223.0	224.0	225.0	226.1	227.1
102.5°	278.6	279.1	280.3	282.7	285.0	287.4	289.8	290.8	291.8	292.8	293.8
105°	344.1	344.4	345.9	348.9	352.0	355.0	358.0	358.0	358.0	358.0	358.0
107.5°	421.5	421.7	422.4	423.7	425.1	426.4	427.8	428.8	429.8	430.9	431.9
110°	495.8	496.1	496.4	497.1	497.8	498.4	499.1	500.5	501.8	503.2	504.5

TEST NUMBER: P1031754

CATALOG NUMBER: S123DIW-B560D1535UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	570.2	570.4	570.4	570.4	570.4	570.4	570.4	572.1	573.8	575.5	577.2
115°	648.8	649.3	649.0	648.3	647.6	647.0	646.3	646.6	647.0	647.3	647.6
117.5°	723.4	723.6	723.3	722.6	721.9	721.3	720.6	720.6	720.6	720.6	720.6
120°	801.5	802.5	801.7	800.0	798.3	796.6	794.9	794.6	794.2	793.9	793.6
122.5°	873.1	873.8	873.5	872.8	872.1	871.5	870.8	869.8	868.8	867.7	866.7
125°	947.6	948.1	947.8	947.1	946.4	945.8	945.1	943.7	942.4	941.0	939.7
127.5°	1021.5	1022.5	1022.2	1021.5	1020.8	1020.1	1019.4	1017.4	1015.4	1013.3	1011.3
130°	1094.0	1095.3	1094.8	1093.8	1092.7	1091.7	1090.7	1089.4	1088.0	1086.7	1085.4
132.5°	1163.7	1165.1	1164.8	1164.1	1163.4	1162.7	1162.0	1160.3	1158.7	1157.0	1155.3
135°	1232.3	1233.3	1233.1	1232.8	1232.5	1232.1	1231.8	1230.5	1229.1	1227.8	1226.5
137.5°	1296.3	1297.1	1297.6	1298.6	1299.6	1300.6	1301.6	1299.9	1298.2	1296.5	1294.8
140°	1364.5	1365.3	1365.5	1365.8	1366.1	1366.5	1366.8	1366.5	1366.1	1365.8	1365.5
142.5°	1426.7	1427.5	1427.8	1428.5	1429.2	1429.9	1430.6	1430.2	1429.9	1429.5	1429.2
145°	1487.9	1488.2	1488.7	1489.7	1490.7	1491.7	1492.7	1492.4	1492.0	1491.7	1491.4
147.5°	1546.7	1547.4	1547.9	1548.9	1549.9	1550.9	1551.9	1551.9	1551.9	1551.9	1551.9
150°	1603.2	1603.5	1603.8	1604.5	1605.2	1605.8	1606.5	1606.5	1606.5	1606.5	1606.5
152.5°	1653.1	1653.6	1653.8	1654.1	1654.4	1654.8	1655.1	1655.8	1656.4	1657.1	1657.8
155°	1700.6	1700.6	1700.8	1701.1	1701.4	1701.8	1702.1	1703.5	1704.8	1706.2	1707.5
157.5°	1743.3	1743.1	1743.3	1743.6	1743.9	1744.3	1744.6	1745.9	1747.3	1748.6	1749.9
160°	1782.8	1782.5	1782.5	1782.5	1782.5	1782.5	1782.5	1784.2	1785.9	1787.6	1789.3
162.5°	1817.9	1817.4	1817.6	1817.9	1818.2	1818.6	1818.9	1820.6	1822.3	1824.0	1825.7
165°	1848.2	1847.7	1847.7	1847.7	1847.7	1847.7	1847.7	1849.7	1851.7	1853.8	1855.8
167.5°	1872.7	1872.0	1872.2	1872.5	1872.8	1873.2	1873.5	1875.5	1877.5	1879.6	1881.6
170°	1893.9	1893.2	1893.2	1893.2	1893.2	1893.2	1893.2	1895.6	1898.0	1900.3	1902.7
172.5°	1910.6	1909.9	1909.9	1909.9	1909.9	1909.9	1909.9	1911.9	1913.9	1916.0	1918.0
175°	1921.2	1920.5	1920.5	1920.5	1920.5	1920.5	1920.5	1922.5	1924.6	1926.6	1928.7
177.5°	1927.3	1926.6	1926.6	1926.6	1926.6	1926.6	1926.6	1928.6	1930.6	1932.7	1934.7
180°	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2

TEST NUMBER: P1031754

CATALOG NUMBER: S123DIW-B560D1535UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6
2.5°	740.5	741.3	738.2	736.0	742.0	738.2	738.2	739.0	737.5	739.8	739.0
5°	698.9	699.7	694.4	695.9	692.9	692.1	691.4	695.9	695.1	694.4	695.9
7.5°	658.1	658.1	655.8	654.3	654.3	652.0	655.0	654.3	655.8	655.8	658.1
10°	624.0	625.5	621.8	618.0	617.2	618.0	618.0	618.7	619.5	624.8	624.0
12.5°	596.0	593.8	593.0	590.8	587.0	585.5	583.9	592.3	590.0	590.0	590.0
15°	565.0	570.3	569.6	562.8	561.3	564.3	562.8	562.8	570.3	569.6	568.8
17.5°	548.4	546.9	545.4	541.6	542.3	541.6	542.3	542.3	546.9	546.9	546.9
20°	529.5	526.5	526.5	524.9	524.9	522.7	525.7	526.5	529.5	529.5	530.2
22.5°	512.8	510.6	510.6	509.8	511.3	508.3	511.3	512.1	512.1	514.4	514.4
25°	498.5	497.0	497.0	498.5	498.5	498.5	498.5	501.5	499.2	500.0	499.2
27.5°	485.6	486.4	487.1	487.9	487.1	487.9	488.6	490.1	490.9	490.1	488.6
30°	473.5	475.8	476.5	476.5	478.0	478.8	479.6	479.6	480.3	478.0	479.6
32.5°	464.4	464.4	465.9	466.7	468.2	469.0	469.0	470.5	469.7	467.5	468.2
35°	451.6	451.6	454.6	456.1	458.4	457.6	458.4	458.4	459.1	457.6	455.4
37.5°	438.7	440.2	440.2	443.3	444.0	444.8	444.0	445.5	444.8	443.3	442.5
40°	423.6	422.8	423.6	425.9	426.6	426.6	426.6	428.1	428.1	428.1	427.4
42.5°	404.7	406.9	406.2	408.5	407.7	407.7	409.2	410.7	411.5	409.2	410.0
45°	386.5	386.5	388.0	388.0	388.8	388.8	391.8	390.3	391.8	390.3	391.1
47.5°	366.9	367.6	367.6	368.4	369.9	371.4	369.9	370.6	370.6	371.4	369.9
50°	344.9	344.9	346.4	348.7	351.7	350.2	349.5	352.5	350.2	350.2	348.7
52.5°	322.2	324.5	325.3	327.5	329.8	330.5	331.3	329.8	330.5	328.3	329.0
55°	300.3	301.0	304.1	306.3	308.6	308.6	307.9	308.6	309.4	306.3	306.3
57.5°	278.4	280.6	283.7	283.7	286.7	286.7	285.9	285.9	286.7	284.4	283.7
60°	254.9	257.2	261.0	261.0	265.5	266.3	264.7	263.2	263.2	261.0	261.7
62.5°	229.9	232.2	234.5	238.3	241.3	239.8	242.8	239.8	240.5	236.0	236.0
65°	208.0	208.8	212.5	216.3	216.3	217.8	216.3	217.1	214.8	214.8	211.8
67.5°	182.3	182.3	186.1	189.9	193.6	193.6	193.6	191.4	191.4	189.1	189.1
70°	159.6	158.8	162.6	164.9	167.2	167.9	166.4	165.7	164.1	161.9	161.1
72.5°	131.6	133.1	136.9	138.4	142.2	141.4	145.2	140.7	140.7	136.9	136.2
75°	106.7	108.2	111.9	114.2	116.5	116.5	118.8	116.5	113.5	111.9	111.2
77.5°	84.7	84.0	87.0	90.8	91.5	90.8	92.3	91.5	88.5	88.5	87.0
80°	60.5	62.8	65.8	65.1	68.1	67.3	67.3	65.8	65.8	63.5	65.1
82.5°	40.1	42.4	43.1	42.4	43.1	44.6	45.4	44.6	44.6	43.1	43.9
85°	21.2	21.2	22.7	23.4	22.7	22.7	23.4	25.7	24.2	22.7	24.2
87.5°	6.8	6.1	6.1	6.8	6.1	6.1	6.8	6.8	7.6	7.6	7.6
90°	42.5	42.8	43.5	44.2	44.8	45.5	44.8	44.2	43.5	42.8	42.5
92.5°	68.3	68.0	67.3	66.6	65.9	65.2	65.9	66.6	67.3	68.0	68.3
95°	118.3	118.3	118.3	118.3	118.3	118.3	118.3	118.3	118.3	118.3	118.3
97.5°	171.4	171.2	170.9	170.6	170.2	169.9	170.2	170.6	170.9	171.2	171.4
100°	227.6	227.9	228.6	229.3	229.9	230.6	229.9	229.3	228.6	227.9	227.6
102.5°	294.3	294.1	293.8	293.5	293.1	292.8	293.1	293.5	293.8	294.1	294.3
105°	358.0	358.3	359.0	359.7	360.4	361.1	360.4	359.7	359.0	358.3	358.0
107.5°	432.4	432.2	431.9	431.5	431.2	430.8	431.2	431.5	431.9	432.2	432.4
110°	505.2	504.9	504.2	503.5	502.8	502.1	502.8	503.5	504.2	504.9	505.2

TEST NUMBER: P1031754

CATALOG NUMBER: S123DIW-B560D1535UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	578.0	578.0	578.0	578.0	578.0	578.0	578.0	578.0	578.0	578.0	578.0
115°	647.8	647.6	647.3	647.0	646.6	646.3	646.6	647.0	647.3	647.6	647.8
117.5°	720.6	720.1	719.1	718.0	717.0	716.0	717.0	718.0	719.1	720.1	720.6
120°	793.4	793.1	792.4	791.7	791.1	790.4	791.1	791.7	792.4	793.1	793.4
122.5°	866.2	865.7	864.7	863.7	862.7	861.7	862.7	863.7	864.7	865.7	866.2
125°	939.0	938.3	937.0	935.7	934.3	933.0	934.3	935.7	937.0	938.3	939.0
127.5°	1010.3	1009.6	1008.3	1007.0	1005.6	1004.3	1005.6	1007.0	1008.3	1009.6	1010.3
130°	1084.7	1083.5	1081.2	1078.8	1076.5	1074.1	1076.5	1078.8	1081.2	1083.5	1084.7
132.5°	1154.5	1153.7	1152.0	1150.3	1148.6	1146.9	1148.6	1150.3	1152.0	1153.7	1154.5
135°	1225.8	1225.5	1224.8	1224.1	1223.4	1222.7	1223.4	1224.1	1224.8	1225.5	1225.8
137.5°	1294.0	1293.5	1292.5	1291.5	1290.5	1289.5	1290.5	1291.5	1292.5	1293.5	1294.0
140°	1365.3	1364.1	1361.8	1359.4	1357.1	1354.7	1357.1	1359.4	1361.8	1364.1	1365.3
142.5°	1429.0	1428.2	1426.5	1424.8	1423.1	1421.4	1423.1	1424.8	1426.5	1428.2	1429.0
145°	1491.2	1490.5	1489.2	1487.9	1486.5	1485.2	1486.5	1487.9	1489.2	1490.5	1491.2
147.5°	1551.9	1550.9	1548.9	1546.8	1544.8	1542.8	1544.8	1546.8	1548.9	1550.9	1551.9
150°	1606.5	1605.5	1603.5	1601.4	1599.4	1597.4	1599.4	1601.4	1603.5	1605.5	1606.5
152.5°	1658.1	1657.3	1655.6	1653.9	1652.2	1650.5	1652.2	1653.9	1655.6	1657.3	1658.1
155°	1708.2	1707.0	1704.6	1702.3	1699.9	1697.5	1699.9	1702.3	1704.6	1707.0	1708.2
157.5°	1750.6	1749.6	1747.6	1745.5	1743.5	1741.5	1743.5	1745.5	1747.6	1749.6	1750.6
160°	1790.1	1789.4	1788.1	1786.7	1785.4	1784.0	1785.4	1786.7	1788.1	1789.4	1790.1
162.5°	1826.5	1825.3	1823.0	1820.6	1818.3	1815.9	1818.3	1820.6	1823.0	1825.3	1826.5
165°	1856.8	1855.6	1853.3	1850.9	1848.6	1846.2	1848.6	1850.9	1853.3	1855.6	1856.8
167.5°	1882.6	1881.6	1879.6	1877.5	1875.5	1873.5	1875.5	1877.5	1879.6	1881.6	1882.6
170°	1903.9	1902.7	1900.3	1898.0	1895.6	1893.2	1895.6	1898.0	1900.3	1902.7	1903.9
172.5°	1919.0	1917.8	1915.5	1913.1	1910.8	1908.4	1910.8	1913.1	1915.5	1917.8	1919.0
175°	1929.7	1928.5	1926.1	1923.8	1921.4	1919.0	1921.4	1923.8	1926.1	1928.5	1929.7
177.5°	1935.7	1934.5	1932.2	1929.8	1927.5	1925.1	1927.5	1929.8	1932.2	1934.5	1935.7
180°	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2

TEST NUMBER: P1031754

CATALOG NUMBER: S123DIW-B560D1535UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6	780.6
2.5°	741.3	742.8	743.5	740.5	738.2	742.0	747.3	751.1	754.1	757.9	760.2
5°	697.4	702.7	702.7	704.2	706.5	710.3	720.1	726.9	733.0	737.5	741.3
7.5°	660.3	664.1	666.4	670.2	674.0	679.2	690.6	700.4	709.5	714.8	720.9
10°	627.1	630.1	633.9	636.1	642.9	650.5	664.9	673.2	683.8	692.1	699.7
12.5°	595.3	605.9	608.1	607.4	613.4	621.8	636.1	649.0	660.3	668.7	677.0
15°	572.6	576.4	580.9	580.2	593.0	595.3	607.4	622.5	637.6	642.9	650.5
17.5°	547.6	553.7	558.2	560.5	564.3	572.6	583.9	595.3	615.0	615.7	635.4
20°	528.0	534.0	537.0	540.1	542.3	552.2	562.0	574.9	590.8	599.1	609.7
22.5°	515.1	518.1	520.4	522.7	525.7	531.0	543.1	557.5	568.1	577.1	583.9
25°	500.0	503.0	506.0	507.5	509.8	512.8	521.9	533.3	548.4	554.4	561.3
27.5°	489.4	489.4	490.9	490.9	493.9	497.0	503.8	514.4	526.5	534.0	543.1
30°	478.0	477.3	478.0	477.3	476.5	481.1	487.1	496.2	504.5	513.6	519.6
32.5°	466.7	465.9	465.9	466.7	463.7	465.9	469.0	477.3	486.4	490.9	497.7
35°	454.6	453.1	453.1	453.1	451.6	450.1	453.1	460.6	466.7	472.8	478.0
37.5°	442.5	440.2	440.2	438.7	437.2	434.9	434.9	441.0	449.3	451.6	458.4
40°	425.9	425.9	424.3	423.6	422.1	420.6	418.3	423.6	431.1	433.4	438.7
42.5°	409.2	406.9	406.2	406.2	406.2	403.9	402.4	406.2	410.7	414.5	417.5
45°	390.3	388.8	389.5	388.8	387.3	386.5	385.8	387.3	392.6	394.1	397.9
47.5°	369.9	369.1	369.1	368.4	367.6	368.4	365.3	369.1	370.6	372.2	375.2
50°	348.7	347.9	347.2	346.4	346.4	347.2	346.4	346.4	349.5	351.0	354.0
52.5°	327.5	325.3	325.3	324.5	324.5	323.0	324.5	325.3	326.8	328.3	329.8
55°	304.8	304.8	302.6	302.6	301.0	301.0	301.8	301.0	304.1	305.6	305.6
57.5°	282.9	279.9	280.6	279.1	277.6	276.8	276.8	278.4	279.9	279.9	281.4
60°	259.4	256.4	255.7	252.6	254.2	251.9	252.6	252.6	255.7	254.2	255.7
62.5°	236.0	232.2	229.9	228.4	228.4	229.2	227.7	226.9	228.4	229.9	233.0
65°	211.0	208.8	206.5	204.2	204.2	203.5	205.0	202.7	202.0	202.7	204.2
67.5°	185.3	183.0	180.8	178.5	179.3	177.0	175.5	177.8	176.2	177.0	178.5
70°	160.4	158.8	154.3	152.8	152.0	152.8	152.0	150.5	152.8	152.0	152.8
72.5°	135.4	133.9	131.6	127.8	127.8	127.1	126.3	126.3	125.6	125.6	125.6
75°	111.2	108.2	105.9	105.1	103.6	102.9	102.1	100.6	101.4	102.1	100.6
77.5°	86.2	82.4	81.7	81.7	79.4	79.4	80.2	79.4	78.7	78.7	78.7
80°	63.5	60.5	60.5	59.0	57.5	57.5	57.5	57.5	56.7	56.0	56.7
82.5°	40.8	40.1	39.3	39.3	40.8	37.8	39.3	38.6	37.8	37.8	37.1
85°	22.7	23.4	22.7	23.4	21.9	22.7	22.7	22.7	21.9	22.7	21.2
87.5°	8.3	8.3	8.3	9.1	9.1	9.1	9.1	9.1	9.8	9.1	9.1
90°	41.8	40.5	39.1	37.8	36.4	32.0	27.6	23.3	18.9	16.7	15.0
92.5°	67.8	66.8	65.7	64.7	63.7	61.7	59.7	57.6	55.6	54.6	53.6
95°	117.6	116.3	115.0	113.6	112.3	109.6	106.9	104.2	101.5	100.1	98.9
97.5°	170.6	168.9	167.2	165.5	163.8	161.8	159.8	157.7	155.7	154.7	153.9
100°	227.1	226.1	225.0	224.0	223.0	221.3	219.6	217.9	216.2	215.4	214.4
102.5°	293.8	292.8	291.8	290.8	289.8	287.4	285.0	282.7	280.3	279.1	278.6
105°	358.0	358.0	358.0	358.0	358.0	355.0	352.0	348.9	345.9	344.4	344.1
107.5°	431.9	430.9	429.8	428.8	427.8	426.4	425.1	423.7	422.4	421.7	421.5
110°	504.5	503.2	501.8	500.5	499.1	498.4	497.8	497.1	496.4	496.1	495.8

TEST NUMBER: P1031754

CATALOG NUMBER: S123DIW-B560D1535UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	577.2	575.5	573.8	572.1	570.4	570.4	570.4	570.4	570.4	570.4	570.2
115°	647.6	647.3	647.0	646.6	646.3	647.0	647.6	648.3	649.0	649.3	648.8
117.5°	720.6	720.6	720.6	720.6	720.6	721.3	721.9	722.6	723.3	723.6	723.4
120°	793.6	793.9	794.2	794.6	794.9	796.6	798.3	800.0	801.7	802.5	801.5
122.5°	866.7	867.7	868.8	869.8	870.8	871.5	872.1	872.8	873.5	873.8	873.1
125°	939.7	941.0	942.4	943.7	945.1	945.8	946.4	947.1	947.8	948.1	947.6
127.5°	1011.3	1013.3	1015.4	1017.4	1019.4	1020.1	1020.8	1021.5	1022.2	1022.5	1021.5
130°	1085.4	1086.7	1088.0	1089.4	1090.7	1091.7	1092.7	1093.8	1094.8	1095.3	1094.0
132.5°	1155.3	1157.0	1158.7	1160.3	1162.0	1162.7	1163.4	1164.1	1164.8	1165.1	1163.7
135°	1226.5	1227.8	1229.1	1230.5	1231.8	1232.1	1232.5	1232.8	1233.1	1233.3	1232.3
137.5°	1294.8	1296.5	1298.2	1299.9	1301.6	1300.6	1299.6	1298.6	1297.6	1297.1	1296.3
140°	1365.5	1365.8	1366.1	1366.5	1366.8	1366.5	1366.1	1365.8	1365.5	1365.3	1364.5
142.5°	1429.2	1429.5	1429.9	1430.2	1430.6	1429.9	1429.2	1428.5	1427.8	1427.5	1426.7
145°	1491.4	1491.7	1492.0	1492.4	1492.7	1491.7	1490.7	1489.7	1488.7	1488.2	1487.9
147.5°	1551.9	1551.9	1551.9	1551.9	1551.9	1550.9	1549.9	1548.9	1547.9	1547.4	1546.7
150°	1606.5	1606.5	1606.5	1606.5	1606.5	1605.8	1605.2	1604.5	1603.8	1603.5	1603.2
152.5°	1657.8	1657.1	1656.4	1655.8	1655.1	1654.8	1654.4	1654.1	1653.8	1653.6	1653.1
155°	1707.5	1706.2	1704.8	1703.5	1702.1	1701.8	1701.4	1701.1	1700.8	1700.6	1700.6
157.5°	1749.9	1748.6	1747.3	1745.9	1744.6	1744.3	1743.9	1743.6	1743.3	1743.1	1743.3
160°	1789.3	1787.6	1785.9	1784.2	1782.5	1782.5	1782.5	1782.5	1782.5	1782.5	1782.8
162.5°	1825.7	1824.0	1822.3	1820.6	1818.9	1818.6	1818.2	1817.9	1817.6	1817.4	1817.9
165°	1855.8	1853.8	1851.7	1849.7	1847.7	1847.7	1847.7	1847.7	1847.7	1847.7	1848.2
167.5°	1881.6	1879.6	1877.5	1875.5	1873.5	1873.2	1872.8	1872.5	1872.2	1872.0	1872.7
170°	1902.7	1900.3	1898.0	1895.6	1893.2	1893.2	1893.2	1893.2	1893.2	1893.2	1893.9
172.5°	1918.0	1916.0	1913.9	1911.9	1909.9	1909.9	1909.9	1909.9	1909.9	1909.9	1910.6
175°	1928.7	1926.6	1924.6	1922.5	1920.5	1920.5	1920.5	1920.5	1920.5	1920.5	1921.2
177.5°	1934.7	1932.7	1930.6	1928.6	1926.6	1926.6	1926.6	1926.6	1926.6	1926.6	1927.3
180°	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2	1931.2

TEST NUMBER: P1031754

CATALOG NUMBER: S123DIW-B560D1535UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	780.6	780.6	780.6	780.6
2.5°	764.0	766.2	773.8	782.9
5°	748.8	754.9	765.5	779.9
7.5°	732.2	741.3	756.4	774.6
10°	713.3	726.1	745.1	767.7
12.5°	692.9	709.5	733.7	757.2
15°	680.0	696.6	718.6	744.3
17.5°	655.0	674.7	697.4	733.7
20°	629.3	651.3	680.8	717.1
22.5°	609.7	633.1	661.1	699.7
25°	586.2	610.4	640.7	680.8
27.5°	561.3	585.5	619.5	661.9
30°	542.3	565.8	598.3	643.7
32.5°	519.6	542.3	576.4	624.0
35°	493.9	519.6	552.2	600.6
37.5°	474.3	497.7	531.8	577.9
40°	453.1	473.5	506.8	552.2
42.5°	430.4	453.1	481.8	527.2
45°	409.2	425.9	455.4	498.5
47.5°	386.5	405.4	428.1	461.4
50°	362.3	378.2	403.2	425.9
52.5°	338.9	351.7	372.9	390.3
55°	313.9	326.8	342.7	353.2
57.5°	290.5	299.5	310.1	316.9
60°	261.7	270.8	277.6	284.4
62.5°	236.0	242.8	246.6	250.4
65°	209.5	213.3	215.6	218.6
67.5°	180.8	184.6	185.3	189.9
70°	154.3	155.1	156.6	158.8
72.5°	129.3	130.9	130.1	131.6
75°	103.6	105.1	103.6	105.1
77.5°	78.7	80.2	80.2	82.4
80°	56.7	57.5	58.2	58.2
82.5°	37.1	39.3	37.8	38.6
85°	21.2	21.9	21.9	22.7
87.5°	9.8	10.6	9.8	11.3
90°	11.6	8.3	4.9	1.5
92.5°	51.6	49.5	47.5	45.5
95°	96.6	94.2	91.9	89.5
97.5°	152.2	150.5	148.9	147.2
100°	212.4	210.3	208.3	206.3
102.5°	277.6	276.6	275.6	274.6
105°	343.4	342.7	342.0	341.3
107.5°	421.2	420.9	420.5	420.2
110°	495.1	494.4	493.7	493.0



TEST NUMBER: P1031754

CATALOG NUMBER: S123DIW-B560D1535UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	569.9	569.6	569.2	568.9
115°	647.8	646.7	645.7	644.7
117.5°	723.1	722.8	722.4	722.1
120°	799.5	797.4	795.4	793.4
122.5°	871.8	870.4	869.1	867.7
125°	946.6	945.6	944.6	943.6
127.5°	1019.5	1017.4	1015.4	1013.4
130°	1091.3	1088.6	1085.9	1083.2
132.5°	1161.0	1158.3	1155.6	1152.9
135°	1230.3	1228.2	1226.2	1224.2
137.5°	1294.6	1292.9	1291.2	1289.5
140°	1362.8	1361.1	1359.4	1357.7
142.5°	1425.0	1423.3	1421.6	1419.9
145°	1487.2	1486.5	1485.9	1485.2
147.5°	1545.4	1544.0	1542.7	1541.3
150°	1602.5	1601.8	1601.2	1600.5
152.5°	1652.1	1651.0	1650.0	1649.0
155°	1700.6	1700.6	1700.6	1700.6
157.5°	1743.6	1743.9	1744.3	1744.6
160°	1783.5	1784.2	1784.8	1785.5
162.5°	1818.9	1819.9	1820.9	1821.9
165°	1849.2	1850.3	1851.3	1852.3
167.5°	1874.0	1875.4	1876.7	1878.1
170°	1895.2	1896.6	1897.9	1899.3
172.5°	1911.9	1913.3	1914.6	1916.0
175°	1922.5	1923.9	1925.2	1926.6
177.5°	1928.6	1930.0	1931.3	1932.7
180°	1931.2	1931.2	1931.2	1931.2

(END OF REPORT)