

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032310

Luminaire Tested: S123RDIW-B560D1535UB27-4F0-XX-W2A-A

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032310
REPORT IS A COMBINATION OF REPORTS P994467 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B560D1535UB27-4F0-XX-W2A-A
Description: Define 3 Regressed Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8375.0 lumens
Efficiency: N/A
Efficacy: 109.9 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 76.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032310

CATALOG NUMBER: S123RDIW-B560D1535UB27-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1032310

CATALOG NUMBER: S123RDIW-B560D1535UB27-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	34	34	34
1	93	89	85	82	83	79	76	74	62	60	58	46	44	43	31	30	30
2	85	78	72	67	75	70	65	61	54	51	48	40	38	37	27	26	25
3	77	69	62	56	69	62	56	51	48	44	41	36	33	31	25	23	22
4	71	61	53	48	63	55	48	43	43	39	35	32	29	27	22	20	19
5	65	54	46	41	58	49	42	37	38	34	30	29	26	23	20	18	17
6	60	48	41	35	53	44	37	32	35	30	26	26	23	21	18	16	15
7	55	44	36	31	49	39	33	28	31	27	23	24	21	18	17	15	13
8	51	40	32	27	46	36	29	25	29	24	21	22	19	16	15	13	12
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	14	12	11
10	44	33	26	22	40	30	24	20	24	20	16	18	15	13	13	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9510	9510	9510	9510
5°	9518	10953	9542	8126
10°	9434	13222	9475	7098
15°	9336	15006	9336	6258
20°	9145	16186	9196	5551
25°	9004	15378	8987	5066
30°	8841	10655	8823	4590
35°	8645	6841	8606	4232
40°	8401	4831	8359	3876
45°	7977	3865	7965	3528
50°	7454	3234	7430	3122
55°	6867	2665	6811	2647
60°	6289	2203	6227	2251
65°	5613	1763	5649	1908
70°	4989	1225	5124	1543
75°	4230	909	4401	1186
80°	3366	603	3654	889
85°	2401	286	2613	554

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 12696 cd/sqm

TEST NUMBER: P1032310

CATALOG NUMBER: S123RDIW-B560D1535UB27-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.8	1.0
10°-20°	271.6	3.2
20°-30°	427.8	5.1
30°-40°	444.8	5.3
40°-50°	380.6	4.5
50°-60°	290.1	3.5
60°-70°	185.9	2.2
70°-80°	89.1	1.1
80°-90°	27.5	0.3
90°-100°	71.4	0.9
100°-110°	345.1	4.1
110°-120°	845.7	10.1
120°-130°	1073.6	12.8
130°-140°	1146.9	13.7
140°-150°	1072.5	12.8
150°-160°	865.1	10.3
160°-170°	558.3	6.7
170°-180°	192.4	2.3
0°-30°	786.1	9.4
0°-40°	1231.0	14.7
0°-60°	1901.6	22.7
0°-90°	2204.0	26.3
90°-120°	1262.2	15.1
90°-150°	4555.2	54.4
90°-180°	6171.0	73.7
0°-180°	8375.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	884	884	884	884	884	
5°	883	1049	885	778	883	84
15°	843	1491	843	622	843	237
25°	767	1536	766	506	767	353
35°	669	666	666	412	669	419
45°	537	356	536	324	537	414
55°	379	223	376	222	379	340
65°	232	129	234	139	232	232
75°	111	54	116	71	111	120
85°	25	13	27	25	25	28
90°	2	45	2	45	2	6
95°	92	57	92	57	92	110
105°	448	66	448	66	448	475
115°	841	884	841	884	841	830
125°	1185	1209	1185	1209	1185	1059
135°	1475	1490	1475	1490	1475	1136
145°	1702	1719	1702	1719	1702	1066
155°	1875	1872	1875	1872	1875	864
165°	1978	1973	1978	1973	1978	559
175°	2024	2017	2024	2017	2024	193
180°	2024	2024	2024	2024	2024	

TEST NUMBER: P1032310

CATALOG NUMBER: S123RDIW-B560D1535UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	885.8	891.8	896.4	899.4	907.0	911.5	915.3	922.1	922.1	923.6	926.6
5°	882.8	895.6	904.7	916.8	932.7	940.2	950.8	959.9	972.8	979.6	986.4
7.5°	876.0	894.1	913.0	931.2	954.6	969.7	980.3	1003.8	1020.4	1040.9	1056.7
10°	866.9	891.8	916.0	944.0	975.8	998.5	1014.4	1045.4	1077.2	1105.9	1130.1
12.5°	855.5	885.8	920.6	954.6	999.2	1021.9	1047.7	1086.2	1131.6	1167.9	1200.5
15°	843.4	878.2	917.6	959.2	1015.1	1046.9	1084.0	1130.9	1181.5	1233.7	1278.4
17.5°	824.5	868.4	912.3	972.8	1038.6	1057.5	1089.3	1153.6	1216.3	1263.2	1317.7
20°	805.6	854.8	910.0	964.5	1035.6	1079.4	1108.9	1177.0	1244.3	1301.1	1353.3
22.5°	788.2	839.6	897.1	966.0	1032.5	1076.4	1113.5	1184.6	1262.5	1326.0	1390.3
25°	767.0	823.0	886.5	951.6	1032.5	1065.8	1106.7	1189.1	1271.6	1344.9	1424.4
27.5°	744.3	801.1	863.8	930.4	1004.5	1053.7	1093.8	1182.3	1282.9	1361.6	1443.3
30°	721.6	779.9	840.4	900.2	983.4	1030.3	1076.4	1174.0	1289.0	1379.0	1441.8
32.5°	699.7	748.9	808.6	866.9	949.3	1000.8	1053.0	1165.7	1291.2	1366.9	1397.1
35°	669.4	720.9	769.3	831.3	914.5	965.2	1026.5	1164.9	1281.4	1328.3	1313.2
37.5°	641.5	684.6	730.7	785.9	871.4	937.2	1000.8	1145.2	1248.9	1251.9	1166.4
40°	610.4	646.0	684.6	742.8	835.1	900.2	969.0	1115.0	1189.9	1145.2	994.7
42.5°	574.9	606.7	636.9	693.6	794.3	866.9	941.0	1077.2	1104.4	1001.5	844.9
45°	537.1	562.8	590.8	650.5	751.1	823.0	897.1	1018.9	990.9	845.7	696.7
47.5°	497.7	519.7	546.9	601.4	705.0	778.4	848.7	935.7	864.6	708.8	584.0
50°	458.4	475.8	502.3	558.2	658.1	724.7	789.7	846.4	746.6	608.2	482.6
52.5°	419.8	433.4	460.7	508.3	605.1	668.7	715.6	737.5	636.2	502.3	419.1
55°	379.0	394.1	412.3	460.7	556.7	603.6	634.6	633.9	529.5	425.9	346.4
57.5°	339.6	353.3	369.1	417.6	495.5	527.2	553.7	540.9	441.8	348.7	297.3
60°	304.8	312.4	329.8	370.7	429.7	456.9	472.0	450.1	360.8	294.3	245.8
62.5°	267.0	274.6	289.0	327.5	363.8	378.2	391.1	363.1	298.0	239.8	210.3
65°	232.2	242.1	251.1	282.1	301.8	319.2	317.7	294.3	233.0	195.2	171.0
67.5°	202.0	205.7	213.3	232.2	241.3	254.2	254.9	228.4	187.6	158.9	144.5
70°	169.4	173.2	178.5	187.6	193.6	196.7	195.2	171.7	141.5	124.1	111.2
72.5°	141.5	140.7	144.5	144.5	150.5	149.8	145.2	127.1	107.4	93.0	85.5
75°	111.2	112.0	112.7	111.2	108.9	105.9	102.1	88.5	75.6	68.8	62.0
77.5°	87.0	85.5	86.2	80.9	77.9	74.9	69.6	62.8	52.2	50.7	47.7
80°	62.0	61.3	60.5	58.2	51.4	48.4	44.6	40.8	38.6	37.1	36.3
82.5°	41.6	41.6	40.1	35.6	31.8	29.5	28.7	27.2	25.0	25.0	24.2
85°	25.0	24.2	22.7	18.2	15.9	15.9	15.9	15.9	14.4	14.4	13.6
87.5°	9.8	9.1	6.8	6.8	6.1	6.1	6.1	5.3	5.3	4.5	4.5
90°	1.5	4.8	8.2	11.5	14.8	16.5	18.7	23.0	27.4	31.7	36.1
92.5°	34.6	32.6	30.6	28.6	26.6	25.6	27.1	30.1	33.1	36.1	39.1
95°	91.7	78.0	64.3	50.6	36.9	30.1	31.9	35.6	39.3	42.9	46.6
97.5°	166.9	157.5	148.2	138.8	129.5	124.8	116.3	99.2	82.2	65.1	48.1
100°	254.2	260.9	267.5	274.2	280.9	284.2	258.1	206.0	153.9	101.7	49.6
102.5°	353.4	357.8	362.1	366.5	370.8	373.0	343.9	285.8	227.6	169.5	111.3
105°	448.2	451.9	455.5	459.2	462.9	464.7	449.7	419.6	389.5	359.4	329.3
107.5°	548.9	551.9	554.9	557.9	560.9	562.4	564.9	569.9	575.0	580.0	585.0
110°	649.7	652.4	655.0	657.7	660.4	661.7	663.5	667.2	670.9	674.5	678.2

TEST NUMBER: P1032310

CATALOG NUMBER: S123RDIW-B560D1535UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	745.9	748.2	750.6	752.9	755.2	756.4	758.2	761.9	765.6	769.3	773.0
115°	840.7	842.7	844.7	846.7	848.7	849.7	851.2	854.2	857.2	860.2	863.2
117.5°	933.9	936.2	938.6	940.9	943.2	944.4	945.2	946.9	948.6	950.2	951.9
120°	1019.6	1022.6	1025.6	1028.7	1031.7	1033.2	1033.7	1034.7	1035.7	1036.7	1037.7
122.5°	1106.8	1109.2	1111.5	1113.9	1116.2	1117.4	1118.1	1119.4	1120.7	1122.1	1123.4
125°	1185.0	1187.7	1190.4	1193.1	1195.8	1197.1	1197.8	1199.1	1200.4	1201.8	1203.1
127.5°	1263.2	1265.9	1268.6	1271.3	1274.0	1275.3	1276.1	1277.8	1279.5	1281.1	1282.8
130°	1335.4	1338.1	1340.8	1343.5	1346.2	1347.5	1348.2	1349.5	1350.8	1352.2	1353.5
132.5°	1404.6	1407.3	1409.9	1412.6	1415.3	1416.6	1417.1	1418.1	1419.2	1420.2	1421.2
135°	1475.3	1477.3	1479.3	1481.3	1483.3	1484.3	1485.0	1486.3	1487.6	1489.0	1490.3
137.5°	1535.4	1538.1	1540.8	1543.5	1546.2	1547.5	1547.8	1548.5	1549.2	1549.8	1550.5
140°	1595.6	1597.6	1599.6	1601.6	1603.6	1604.6	1605.1	1606.1	1607.1	1608.1	1609.1
142.5°	1651.2	1653.2	1655.2	1657.3	1659.3	1660.3	1660.8	1661.8	1662.8	1663.8	1664.8
145°	1702.4	1704.7	1707.1	1709.4	1711.7	1712.9	1713.2	1713.9	1714.6	1715.2	1715.9
147.5°	1752.0	1753.7	1755.3	1757.0	1758.7	1759.5	1759.8	1760.5	1761.2	1761.8	1762.5
150°	1797.1	1798.1	1799.1	1800.1	1801.1	1801.6	1801.9	1802.6	1803.3	1803.9	1804.6
152.5°	1837.7	1838.0	1838.4	1838.7	1839.0	1839.2	1839.4	1839.7	1840.0	1840.4	1840.7
155°	1875.3	1874.6	1874.0	1873.3	1872.6	1872.3	1872.5	1872.8	1873.1	1873.5	1873.8
157.5°	1905.4	1905.4	1905.4	1905.4	1905.4	1905.4	1905.2	1904.9	1904.6	1904.2	1903.9
160°	1932.5	1932.2	1931.8	1931.5	1931.2	1931.0	1930.8	1930.5	1930.2	1929.8	1929.5
162.5°	1958.0	1957.0	1956.0	1955.0	1954.0	1953.5	1953.3	1953.0	1952.7	1952.3	1952.0
165°	1977.6	1976.6	1975.6	1974.6	1973.6	1973.1	1972.9	1972.6	1972.3	1971.9	1971.6
167.5°	1994.1	1992.8	1991.4	1990.1	1988.8	1988.1	1988.1	1988.1	1988.1	1988.1	1988.1
170°	2007.7	2006.3	2005.0	2003.6	2002.3	2001.6	2001.6	2001.6	2001.6	2001.6	2001.6
172.5°	2016.7	2015.0	2013.4	2011.7	2010.0	2009.2	2009.4	2009.7	2010.0	2010.4	2010.7
175°	2024.2	2022.5	2020.9	2019.2	2017.5	2016.7	2016.9	2017.2	2017.5	2017.9	2018.2
177.5°	2027.2	2025.5	2023.9	2022.2	2020.5	2019.7	2019.9	2020.2	2020.5	2020.9	2021.2
180°	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2

TEST NUMBER: P1032310

CATALOG NUMBER: S123RDIW-B560D1535UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	932.7	932.7	939.5	946.3	942.5	944.8	953.1	950.1	956.1	955.4	957.6
5°	1003.0	1011.4	1018.2	1032.5	1034.8	1032.5	1046.9	1050.7	1057.5	1049.2	1053.0
7.5°	1082.5	1099.9	1116.5	1137.7	1144.5	1146.0	1153.6	1164.2	1173.2	1156.6	1164.9
10°	1159.6	1186.1	1220.1	1239.0	1255.7	1261.7	1267.8	1274.6	1285.2	1295.0	1287.5
12.5°	1242.8	1281.4	1313.9	1348.0	1368.4	1366.1	1383.5	1388.1	1396.4	1398.6	1401.7
15°	1310.9	1365.4	1385.8	1436.5	1441.0	1456.1	1475.8	1493.2	1495.5	1490.9	1490.9
17.5°	1376.0	1422.9	1459.2	1500.0	1508.3	1521.2	1546.2	1554.5	1557.5	1556.7	1556.7
20°	1428.9	1459.9	1521.2	1555.2	1568.8	1585.5	1602.9	1613.5	1615.7	1618.8	1614.2
22.5°	1463.7	1510.6	1560.5	1588.5	1599.9	1605.9	1617.3	1620.3	1616.5	1617.3	1618.0
25°	1490.9	1537.1	1567.3	1574.9	1574.1	1566.6	1558.3	1543.9	1542.4	1536.3	1524.2
27.5°	1498.5	1515.9	1512.1	1481.1	1450.1	1447.1	1397.1	1369.9	1338.9	1343.4	1326.0
30°	1457.6	1435.0	1381.2	1302.6	1270.1	1217.1	1161.1	1102.9	1080.2	1055.2	1101.4
32.5°	1357.8	1276.9	1181.5	1079.4	1025.0	978.1	918.3	876.0	851.7	831.3	870.7
35°	1207.3	1080.9	954.6	857.8	813.2	770.8	714.8	693.6	663.4	666.4	670.2
37.5°	1013.6	874.4	779.1	683.8	654.3	636.9	596.1	563.5	553.0	549.9	549.9
40°	832.1	717.9	633.1	558.2	535.6	521.2	488.7	473.5	462.2	459.2	462.9
42.5°	688.4	590.8	525.0	475.0	459.2	441.0	427.4	408.5	406.2	400.9	407.7
45°	577.9	493.2	444.0	407.7	394.1	387.3	372.2	360.8	356.3	355.5	360.8
47.5°	490.2	424.4	381.2	358.5	348.0	341.2	328.3	323.8	319.2	320.7	318.5
50°	411.5	362.3	334.3	313.9	307.1	300.3	292.0	287.4	285.2	285.2	284.4
52.5°	353.3	312.4	294.3	275.3	272.3	268.5	259.5	256.4	252.6	251.9	254.9
55°	302.6	274.6	256.4	245.1	242.1	234.5	230.7	226.9	224.7	223.1	223.9
57.5°	258.7	237.5	225.4	215.6	210.3	207.3	200.5	199.7	198.2	198.2	197.4
60°	222.4	207.3	192.9	186.8	183.1	179.3	178.5	174.0	171.7	173.2	172.5
62.5°	188.4	176.2	167.9	161.1	158.9	155.8	153.6	152.0	149.8	150.5	150.5
65°	157.3	147.5	141.5	135.4	134.6	131.6	130.9	129.4	129.4	128.6	130.1
67.5°	129.4	122.5	117.2	113.5	111.2	112.0	108.9	106.7	106.7	105.9	108.2
70°	102.9	99.1	93.8	89.3	86.2	86.2	82.5	81.7	81.7	81.7	80.9
72.5°	79.4	72.6	70.3	68.8	68.8	68.8	67.3	67.3	66.6	67.3	66.6
75°	59.0	58.2	56.7	56.0	56.0	55.2	54.5	54.5	54.5	54.5	54.5
77.5°	46.1	46.1	44.6	43.9	43.9	43.9	43.1	43.1	42.4	42.4	42.4
80°	34.0	34.0	32.5	32.5	32.5	31.8	31.8	31.8	32.5	31.8	31.8
82.5°	23.4	23.4	22.7	23.4	22.7	21.9	21.9	21.9	21.2	21.9	21.9
85°	13.6	13.6	12.9	12.1	12.9	12.9	12.1	12.9	12.1	12.9	12.1
87.5°	5.3	4.5	4.5	4.5	3.8	4.5	3.8	3.8	4.5	3.8	4.5
90°	37.4	38.8	40.1	41.4	42.1	42.4	43.1	43.8	44.4	45.1	44.4
92.5°	41.4	43.8	46.1	48.4	49.6	49.8	50.1	50.4	50.8	51.1	50.8
95°	48.9	51.3	53.6	55.9	57.1	57.1	57.1	57.1	57.1	57.1	57.1
97.5°	50.8	53.5	56.2	58.9	60.2	60.4	60.7	61.0	61.4	61.7	61.4
100°	52.3	55.0	57.7	60.4	61.7	61.9	62.2	62.5	62.9	63.2	62.9
102.5°	100.3	89.3	78.2	67.2	61.7	62.0	62.7	63.4	64.0	64.7	64.0
105°	270.2	211.0	151.9	92.8	63.2	63.5	64.2	64.9	65.5	66.2	65.5
107.5°	533.5	482.1	430.6	379.1	353.4	331.5	287.7	244.0	200.2	156.4	200.2
110°	667.2	656.2	645.1	634.1	628.6	604.7	556.9	509.2	461.4	413.6	461.4

TEST NUMBER: P1032310

CATALOG NUMBER: S123RDIW-B560D1535UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	776.0	779.0	782.0	785.0	786.5	786.2	785.5	784.8	784.2	783.5	784.2
115°	866.6	869.9	873.3	876.6	878.3	879.0	880.3	881.6	883.0	884.3	883.0
117.5°	954.6	957.3	960.0	962.7	964.0	964.2	964.5	964.8	965.2	965.5	965.2
120°	1040.4	1043.0	1045.7	1048.4	1049.7	1049.7	1049.7	1049.7	1049.7	1049.7	1049.7
122.5°	1125.1	1126.7	1128.4	1130.1	1130.9	1131.1	1131.4	1131.7	1132.1	1132.4	1132.1
125°	1203.8	1204.4	1205.1	1205.8	1206.1	1206.4	1207.1	1207.8	1208.4	1209.1	1208.4
127.5°	1283.8	1284.8	1285.8	1286.8	1287.3	1287.0	1286.3	1285.6	1285.0	1284.3	1285.0
130°	1354.8	1356.2	1357.5	1358.8	1359.5	1359.2	1358.5	1357.8	1357.2	1356.5	1357.2
132.5°	1422.5	1423.9	1425.2	1426.5	1427.2	1426.7	1425.7	1424.7	1423.7	1422.7	1423.7
135°	1491.3	1492.3	1493.3	1494.3	1494.8	1494.3	1493.3	1492.3	1491.3	1490.3	1491.3
137.5°	1552.2	1553.8	1555.5	1557.2	1558.0	1557.7	1557.0	1556.3	1555.7	1555.0	1555.7
140°	1610.5	1611.8	1613.2	1614.5	1615.2	1614.9	1614.2	1613.5	1612.8	1612.1	1612.8
142.5°	1665.8	1666.8	1667.8	1668.8	1669.3	1668.8	1667.8	1666.8	1665.8	1664.8	1665.8
145°	1716.6	1717.2	1717.9	1718.6	1718.9	1718.9	1718.9	1718.9	1718.9	1718.9	1718.9
147.5°	1763.2	1763.8	1764.5	1765.2	1765.5	1764.7	1763.0	1761.3	1759.7	1758.0	1759.7
150°	1805.3	1805.9	1806.6	1807.3	1807.6	1807.1	1806.1	1805.1	1804.1	1803.1	1804.1
152.5°	1842.0	1843.4	1844.7	1846.0	1846.7	1845.9	1844.2	1842.5	1840.9	1839.2	1840.9
155°	1875.5	1877.1	1878.8	1880.5	1881.3	1880.3	1878.3	1876.3	1874.3	1872.3	1874.3
157.5°	1905.9	1907.9	1909.9	1911.9	1912.9	1911.6	1908.9	1906.2	1903.6	1900.9	1903.6
160°	1931.5	1933.5	1935.5	1937.5	1938.5	1937.3	1935.0	1932.7	1930.3	1928.0	1930.3
162.5°	1954.3	1956.7	1959.0	1961.3	1962.5	1961.5	1959.5	1957.5	1955.5	1953.5	1955.5
165°	1974.3	1976.9	1979.6	1982.3	1983.6	1982.4	1980.1	1977.8	1975.4	1973.1	1975.4
167.5°	1990.8	1993.4	1996.1	1998.8	2000.1	1998.8	1996.1	1993.4	1990.8	1988.1	1990.8
170°	2004.3	2007.0	2009.7	2012.4	2013.7	2012.4	2009.7	2007.0	2004.3	2001.6	2004.3
172.5°	2013.4	2016.0	2018.7	2021.4	2022.7	2021.2	2018.2	2015.2	2012.2	2009.2	2012.2
175°	2020.5	2022.9	2025.2	2027.5	2028.7	2027.4	2024.7	2022.0	2019.4	2016.7	2019.4
177.5°	2023.9	2026.5	2029.2	2031.9	2033.2	2031.5	2028.2	2024.9	2021.5	2018.2	2021.5
180°	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2

TEST NUMBER: P1032310

CATALOG NUMBER: S123RDIW-B560D1535UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	953.9	949.3	946.3	944.0	941.8	948.6	939.5	929.7	922.8	918.3	916.8
5°	1053.7	1043.9	1035.6	1028.7	1030.3	1030.3	1014.4	997.0	981.9	973.5	964.5
7.5°	1169.4	1158.9	1142.2	1138.4	1135.4	1116.5	1100.6	1068.8	1049.9	1031.0	1014.4
10°	1284.4	1270.8	1254.9	1249.6	1242.1	1218.6	1194.4	1153.6	1130.1	1095.3	1073.4
12.5°	1391.8	1375.2	1359.3	1355.5	1344.2	1323.8	1282.2	1239.8	1199.7	1162.6	1124.1
15°	1481.9	1477.3	1453.1	1438.0	1413.0	1385.0	1376.0	1318.5	1267.8	1229.2	1159.6
17.5°	1557.5	1536.3	1513.6	1503.8	1494.0	1461.4	1428.9	1369.9	1315.4	1258.7	1214.1
20°	1618.0	1594.6	1578.7	1564.3	1559.8	1522.7	1471.3	1419.1	1359.3	1295.8	1237.5
22.5°	1621.0	1618.0	1607.4	1599.1	1590.0	1565.8	1525.0	1459.9	1396.4	1326.8	1250.4
25°	1558.3	1553.7	1584.0	1576.4	1582.5	1573.4	1551.4	1497.0	1422.9	1341.2	1264.0
27.5°	1369.1	1415.3	1462.9	1479.6	1490.9	1523.5	1534.0	1503.8	1444.0	1357.0	1270.8
30°	1112.0	1173.2	1250.4	1292.0	1323.8	1384.3	1462.9	1472.8	1444.8	1375.2	1269.3
32.5°	872.9	928.9	990.9	1040.1	1082.5	1206.5	1312.4	1388.8	1402.4	1366.1	1273.1
35°	703.5	727.7	786.7	833.6	891.1	997.0	1121.8	1245.1	1328.3	1332.8	1261.7
37.5°	580.2	593.0	644.5	671.0	705.0	798.0	914.5	1075.6	1205.0	1266.3	1230.0
40°	480.3	509.8	539.3	554.5	578.7	643.0	754.9	881.2	1041.6	1155.1	1180.8
42.5°	416.8	429.7	448.6	469.7	484.9	540.9	615.7	731.5	876.0	1034.0	1105.1
45°	367.6	372.2	391.8	405.4	421.3	460.7	513.6	610.4	737.5	893.3	1014.4
47.5°	326.8	335.9	346.4	354.8	365.4	395.6	441.0	511.3	623.3	762.5	892.6
50°	290.5	295.8	309.4	313.2	320.7	341.9	376.7	430.4	522.7	633.9	768.5
52.5°	256.4	266.3	271.6	276.9	283.7	301.1	323.8	367.6	437.2	541.6	655.8
55°	230.0	233.0	240.5	245.1	250.4	262.5	282.1	314.7	369.1	452.3	560.5
57.5°	204.2	204.2	211.8	215.6	220.9	230.0	247.4	272.3	311.7	373.7	472.8
60°	177.0	177.8	183.8	188.4	189.9	198.9	213.3	233.0	263.2	308.6	389.6
62.5°	152.8	156.6	159.6	161.1	166.4	171.7	183.8	197.4	218.6	258.7	316.2
65°	132.4	133.1	135.4	136.9	139.2	145.2	154.3	163.4	181.5	211.0	257.9
67.5°	108.9	112.0	115.0	115.0	117.2	120.3	129.4	136.9	150.5	167.9	199.7
70°	81.7	83.2	87.7	90.0	93.0	98.3	102.9	107.4	118.0	130.9	155.1
72.5°	68.1	68.1	69.6	70.3	70.3	74.1	80.9	85.5	90.8	99.8	116.5
75°	54.5	54.5	56.7	56.0	57.5	59.0	59.8	62.8	65.8	72.6	82.5
77.5°	43.1	43.9	43.9	44.6	44.6	45.4	46.1	47.7	49.2	53.0	57.5
80°	31.8	32.5	32.5	33.3	33.3	34.0	34.8	35.6	37.1	38.6	40.8
82.5°	21.9	22.7	22.7	23.4	22.7	23.4	24.2	24.2	25.0	26.5	27.2
85°	12.9	12.9	13.6	12.9	12.9	12.9	13.6	13.6	14.4	16.6	16.6
87.5°	3.8	4.5	3.8	4.5	4.5	4.5	4.5	5.3	5.3	6.1	6.8
90°	43.8	43.1	42.4	42.1	41.4	40.1	38.8	37.4	36.1	31.7	27.4
92.5°	50.4	50.1	49.8	49.6	48.4	46.1	43.8	41.4	39.1	36.1	33.1
95°	57.1	57.1	57.1	57.1	55.9	53.6	51.3	48.9	46.6	42.9	39.3
97.5°	61.0	60.7	60.4	60.2	58.9	56.2	53.5	50.8	48.1	65.1	82.2
100°	62.5	62.2	61.9	61.7	60.4	57.7	55.0	52.3	49.6	101.7	153.9
102.5°	63.4	62.7	62.0	61.7	67.2	78.2	89.3	100.3	111.3	169.5	227.6
105°	64.9	64.2	63.5	63.2	92.8	151.9	211.0	270.2	329.3	359.4	389.5
107.5°	244.0	287.7	331.5	353.4	379.1	430.6	482.1	533.5	585.0	580.0	575.0
110°	509.2	556.9	604.7	628.6	634.1	645.1	656.2	667.2	678.2	674.5	670.9

TEST NUMBER: P1032310

CATALOG NUMBER: S123RDIW-B560D1535UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	784.8	785.5	786.2	786.5	785.0	782.0	779.0	776.0	773.0	769.3	765.6
115°	881.6	880.3	879.0	878.3	876.6	873.3	869.9	866.6	863.2	860.2	857.2
117.5°	964.8	964.5	964.2	964.0	962.7	960.0	957.3	954.6	951.9	950.2	948.6
120°	1049.7	1049.7	1049.7	1049.7	1048.4	1045.7	1043.0	1040.4	1037.7	1036.7	1035.7
122.5°	1131.7	1131.4	1131.1	1130.9	1130.1	1128.4	1126.7	1125.1	1123.4	1122.1	1120.7
125°	1207.8	1207.1	1206.4	1206.1	1205.8	1205.1	1204.4	1203.8	1203.1	1201.8	1200.4
127.5°	1285.6	1286.3	1287.0	1287.3	1286.8	1285.8	1284.8	1283.8	1282.8	1281.1	1279.5
130°	1357.8	1358.5	1359.2	1359.5	1358.8	1357.5	1356.2	1354.8	1353.5	1352.2	1350.8
132.5°	1424.7	1425.7	1426.7	1427.2	1426.5	1425.2	1423.9	1422.5	1421.2	1420.2	1419.2
135°	1492.3	1493.3	1494.3	1494.8	1494.3	1493.3	1492.3	1491.3	1490.3	1489.0	1487.6
137.5°	1556.3	1557.0	1557.7	1558.0	1557.2	1555.5	1553.8	1552.2	1550.5	1549.8	1549.2
140°	1613.5	1614.2	1614.9	1615.2	1614.5	1613.2	1611.8	1610.5	1609.1	1608.1	1607.1
142.5°	1666.8	1667.8	1668.8	1669.3	1668.8	1667.8	1666.8	1665.8	1664.8	1663.8	1662.8
145°	1718.9	1718.9	1718.9	1718.9	1718.6	1717.9	1717.2	1716.6	1715.9	1715.2	1714.6
147.5°	1761.3	1763.0	1764.7	1765.5	1765.2	1764.5	1763.8	1763.2	1762.5	1761.8	1761.2
150°	1805.1	1806.1	1807.1	1807.6	1807.3	1806.6	1805.9	1805.3	1804.6	1803.9	1803.3
152.5°	1842.5	1844.2	1845.9	1846.7	1846.0	1844.7	1843.4	1842.0	1840.7	1840.4	1840.0
155°	1876.3	1878.3	1880.3	1881.3	1880.5	1878.8	1877.1	1875.5	1873.8	1873.5	1873.1
157.5°	1906.2	1908.9	1911.6	1912.9	1911.9	1909.9	1907.9	1905.9	1903.9	1904.2	1904.6
160°	1932.7	1935.0	1937.3	1938.5	1937.5	1935.5	1933.5	1931.5	1929.5	1929.8	1930.2
162.5°	1957.5	1959.5	1961.5	1962.5	1961.3	1959.0	1956.7	1954.3	1952.0	1952.3	1952.7
165°	1977.8	1980.1	1982.4	1983.6	1982.3	1979.6	1976.9	1974.3	1971.6	1971.9	1972.3
167.5°	1993.4	1996.1	1998.8	2000.1	1998.8	1996.1	1993.4	1990.8	1988.1	1988.1	1988.1
170°	2007.0	2009.7	2012.4	2013.7	2012.4	2009.7	2007.0	2004.3	2001.6	2001.6	2001.6
172.5°	2015.2	2018.2	2021.2	2022.7	2021.4	2018.7	2016.0	2013.4	2010.7	2010.4	2010.0
175°	2022.0	2024.7	2027.4	2028.7	2027.5	2025.2	2022.9	2020.5	2018.2	2017.9	2017.5
177.5°	2024.9	2028.2	2031.5	2033.2	2031.9	2029.2	2026.5	2023.9	2021.2	2020.9	2020.5
180°	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2

TEST NUMBER: P1032310

CATALOG NUMBER: S123RDIW-B560D1535UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	914.5	910.7	907.0	907.0	898.6	891.1	887.3	888.8	884.3	878.2	872.2
5°	954.6	939.5	936.5	928.1	916.8	900.9	892.6	885.0	876.0	863.8	852.5
7.5°	991.7	972.0	961.4	953.1	931.2	909.2	891.1	879.0	863.1	844.9	831.3
10°	1040.1	1003.8	992.4	973.5	942.5	911.5	890.3	870.7	848.7	827.5	809.4
12.5°	1078.7	1037.1	1015.9	997.0	956.9	917.6	882.0	857.8	831.3	807.9	784.4
15°	1122.5	1075.6	1038.6	1015.9	965.2	917.6	877.5	843.4	813.9	785.2	764.8
17.5°	1143.7	1084.7	1068.1	1035.6	962.2	914.5	865.4	829.1	793.5	760.2	736.0
20°	1177.0	1108.2	1066.6	1044.6	979.6	909.2	851.7	810.1	773.1	737.5	711.8
22.5°	1179.3	1104.4	1077.2	1035.6	955.4	893.3	839.6	789.0	745.8	712.6	686.1
25°	1174.0	1097.6	1059.8	1026.5	959.9	884.3	815.4	765.5	723.2	684.6	653.6
27.5°	1171.7	1077.9	1042.4	1009.1	934.2	857.8	801.1	744.3	695.9	661.9	630.1
30°	1168.7	1056.7	1013.6	975.0	906.2	837.4	769.3	720.1	674.0	630.9	599.1
32.5°	1149.0	1028.0	984.1	943.3	869.1	800.3	746.6	694.4	644.5	604.4	575.6
35°	1143.0	1001.5	944.0	900.2	827.5	766.3	709.5	666.4	619.5	579.4	545.4
37.5°	1125.6	974.3	912.3	856.3	780.6	722.4	680.8	637.7	592.3	549.2	521.9
40°	1095.3	942.5	872.2	814.7	736.8	677.8	639.2	607.4	562.8	524.2	490.9
42.5°	1050.7	910.0	834.3	773.8	687.6	632.4	600.6	570.4	532.5	492.4	465.2
45°	999.2	866.9	796.5	729.2	641.5	587.7	554.5	536.3	501.5	467.5	435.7
47.5°	928.9	822.2	752.7	683.1	593.8	541.6	515.1	497.0	472.8	435.7	410.0
50°	840.4	764.8	698.9	636.9	546.9	497.0	470.5	456.9	436.5	410.0	385.0
52.5°	742.1	698.2	643.7	586.2	499.2	452.3	428.1	417.6	402.4	377.5	356.3
55°	643.0	624.1	587.0	530.3	449.3	410.7	389.6	375.9	364.6	346.4	328.3
57.5°	554.5	545.4	519.7	475.8	407.7	367.6	349.5	340.4	331.3	317.7	299.5
60°	462.9	472.8	446.3	424.4	362.3	327.5	311.7	301.8	297.3	285.2	273.8
62.5°	383.5	392.6	377.5	360.8	316.9	285.9	276.1	267.0	264.0	253.4	242.1
65°	311.7	323.0	311.7	302.6	276.1	250.4	238.3	233.7	230.7	223.9	214.8
67.5°	248.1	259.5	254.2	242.8	234.5	213.3	206.5	202.0	200.5	195.2	187.6
70°	186.8	202.7	204.2	197.4	189.9	180.0	175.5	174.0	170.2	165.7	161.1
72.5°	134.6	152.8	153.6	153.6	149.0	149.0	144.5	142.2	142.2	137.7	132.4
75°	99.1	111.2	112.7	114.2	116.5	118.8	115.7	115.7	115.0	110.4	108.2
77.5°	65.8	76.4	80.2	85.5	88.5	88.5	90.0	91.5	90.0	87.7	86.2
80°	42.4	49.9	54.5	57.5	62.0	64.3	66.6	67.3	65.8	65.1	62.8
82.5°	28.0	30.3	32.5	36.3	41.6	45.4	45.4	44.6	46.1	45.4	44.6
85°	15.9	17.4	18.2	18.9	21.9	25.7	26.5	27.2	28.7	27.2	25.7
87.5°	6.1	6.8	6.8	6.8	8.3	9.1	11.3	14.4	13.6	12.1	12.1
90°	23.0	18.7	16.5	14.8	11.5	8.2	4.8	1.5	4.8	8.2	11.5
92.5°	30.1	27.1	25.6	26.6	28.6	30.6	32.6	34.6	32.6	30.6	28.6
95°	35.6	31.9	30.1	36.9	50.6	64.3	78.0	91.7	78.0	64.3	50.6
97.5°	99.2	116.3	124.8	129.5	138.8	148.2	157.5	166.9	157.5	148.2	138.8
100°	206.0	258.1	284.2	280.9	274.2	267.5	260.9	254.2	260.9	267.5	274.2
102.5°	285.8	343.9	373.0	370.8	366.5	362.1	357.8	353.4	357.8	362.1	366.5
105°	419.6	449.7	464.7	462.9	459.2	455.5	451.9	448.2	451.9	455.5	459.2
107.5°	569.9	564.9	562.4	560.9	557.9	554.9	551.9	548.9	551.9	554.9	557.9
110°	667.2	663.5	661.7	660.4	657.7	655.0	652.4	649.7	652.4	655.0	657.7

TEST NUMBER: P1032310

CATALOG NUMBER: S123RDIW-B560D1535UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	761.9	758.2	756.4	755.2	752.9	750.6	748.2	745.9	748.2	750.6	752.9
115°	854.2	851.2	849.7	848.7	846.7	844.7	842.7	840.7	842.7	844.7	846.7
117.5°	946.9	945.2	944.4	943.2	940.9	938.6	936.2	933.9	936.2	938.6	940.9
120°	1034.7	1033.7	1033.2	1031.7	1028.7	1025.6	1022.6	1019.6	1022.6	1025.6	1028.7
122.5°	1119.4	1118.1	1117.4	1116.2	1113.9	1111.5	1109.2	1106.8	1109.2	1111.5	1113.9
125°	1199.1	1197.8	1197.1	1195.8	1193.1	1190.4	1187.7	1185.0	1187.7	1190.4	1193.1
127.5°	1277.8	1276.1	1275.3	1274.0	1271.3	1268.6	1265.9	1263.2	1265.9	1268.6	1271.3
130°	1349.5	1348.2	1347.5	1346.2	1343.5	1340.8	1338.1	1335.4	1338.1	1340.8	1343.5
132.5°	1418.1	1417.1	1416.6	1415.3	1412.6	1409.9	1407.3	1404.6	1407.3	1409.9	1412.6
135°	1486.3	1485.0	1484.3	1483.3	1481.3	1479.3	1477.3	1475.3	1477.3	1479.3	1481.3
137.5°	1548.5	1547.8	1547.5	1546.2	1543.5	1540.8	1538.1	1535.4	1538.1	1540.8	1543.5
140°	1606.1	1605.1	1604.6	1603.6	1601.6	1599.6	1597.6	1595.6	1597.6	1599.6	1601.6
142.5°	1661.8	1660.8	1660.3	1659.3	1657.3	1655.2	1653.2	1651.2	1653.2	1655.2	1657.3
145°	1713.9	1713.2	1712.9	1711.7	1709.4	1707.1	1704.7	1702.4	1704.7	1707.1	1709.4
147.5°	1760.5	1759.8	1759.5	1758.7	1757.0	1755.3	1753.7	1752.0	1753.7	1755.3	1757.0
150°	1802.6	1801.9	1801.6	1801.1	1800.1	1799.1	1798.1	1797.1	1798.1	1799.1	1800.1
152.5°	1839.7	1839.4	1839.2	1839.0	1838.7	1838.4	1838.0	1837.7	1838.0	1838.4	1838.7
155°	1872.8	1872.5	1872.3	1872.6	1873.3	1874.0	1874.6	1875.3	1874.6	1874.0	1873.3
157.5°	1904.9	1905.2	1905.4	1905.4	1905.4	1905.4	1905.4	1905.4	1905.4	1905.4	1905.4
160°	1930.5	1930.8	1931.0	1931.2	1931.5	1931.8	1932.2	1932.5	1932.2	1931.8	1931.5
162.5°	1953.0	1953.3	1953.5	1954.0	1955.0	1956.0	1957.0	1958.0	1957.0	1956.0	1955.0
165°	1972.6	1972.9	1973.1	1973.6	1974.6	1975.6	1976.6	1977.6	1976.6	1975.6	1974.6
167.5°	1988.1	1988.1	1988.1	1988.8	1990.1	1991.4	1992.8	1994.1	1992.8	1991.4	1990.1
170°	2001.6	2001.6	2001.6	2002.3	2003.6	2005.0	2006.3	2007.7	2006.3	2005.0	2003.6
172.5°	2009.7	2009.4	2009.2	2010.0	2011.7	2013.4	2015.0	2016.7	2015.0	2013.4	2011.7
175°	2017.2	2016.9	2016.7	2017.5	2019.2	2020.9	2022.5	2024.2	2022.5	2020.9	2019.2
177.5°	2020.2	2019.9	2019.7	2020.5	2022.2	2023.9	2025.5	2027.2	2025.5	2023.9	2022.2
180°	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2

TEST NUMBER: P1032310

CATALOG NUMBER: S123RDIW-B560D1535UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	872.2	868.4	866.9	863.1	854.0	848.0	841.2	836.6	837.4	833.6	835.9
5°	844.9	844.2	838.9	831.3	818.5	811.7	799.6	793.5	790.5	791.2	786.7
7.5°	822.2	815.4	811.7	799.6	787.4	773.1	763.2	757.9	753.4	748.9	745.8
10°	796.5	790.5	784.4	771.6	754.9	741.3	727.7	722.4	715.6	712.6	710.3
12.5°	769.3	765.5	757.9	742.8	723.9	711.0	695.2	692.1	683.1	677.0	675.5
15°	744.3	742.1	728.4	711.0	692.1	679.3	665.7	656.6	641.5	644.5	639.2
17.5°	717.9	708.0	699.7	676.3	667.2	647.5	631.6	627.1	616.5	609.7	602.9
20°	688.4	682.3	671.7	656.6	634.6	612.0	599.9	592.3	586.2	575.6	572.6
22.5°	660.4	652.8	643.7	624.1	605.1	586.2	569.6	562.8	555.2	547.7	543.1
25°	638.4	627.1	617.2	593.0	574.1	558.2	547.7	536.3	525.7	521.2	519.7
27.5°	604.4	597.6	587.7	565.1	547.7	530.3	520.4	512.9	501.5	496.2	491.7
30°	582.5	568.8	557.5	539.3	521.9	503.0	494.0	484.9	478.1	471.3	466.0
32.5°	553.0	542.4	533.3	515.1	497.7	480.3	470.5	456.9	453.1	447.8	441.8
35°	524.2	517.4	507.6	487.9	469.0	456.9	446.3	433.4	428.9	425.1	419.8
37.5°	497.0	487.1	480.3	461.4	444.8	430.4	422.1	411.5	408.5	403.9	400.2
40°	473.5	463.7	456.9	438.0	420.6	405.4	400.2	389.6	385.0	379.7	377.5
42.5°	447.1	438.7	429.7	416.0	397.9	382.8	372.2	366.1	360.1	357.8	353.3
45°	419.1	411.5	404.7	389.6	370.7	360.1	351.0	342.7	338.1	334.3	331.3
47.5°	394.9	388.1	379.0	362.3	347.2	337.4	328.3	320.0	315.4	310.9	307.1
50°	366.9	363.1	353.3	337.4	323.0	311.7	303.3	295.8	292.7	287.4	281.4
52.5°	341.9	335.1	326.8	313.9	301.1	287.4	276.1	271.6	266.3	263.2	257.9
55°	312.4	307.9	298.8	287.4	273.8	262.5	254.2	248.1	241.3	238.3	231.5
57.5°	287.4	279.1	274.6	260.2	247.4	236.0	230.0	223.9	216.3	211.8	208.8
60°	260.2	252.6	245.8	233.7	224.7	212.6	203.5	198.2	192.9	186.8	183.8
62.5°	233.7	227.7	219.4	209.5	198.2	188.4	181.5	174.0	171.0	164.9	162.6
65°	205.0	200.5	193.6	182.3	173.2	164.9	158.1	152.0	149.0	146.7	145.2
67.5°	179.3	173.2	168.7	158.9	149.0	142.2	138.4	134.6	130.9	128.6	126.3
70°	152.8	148.3	143.7	134.6	127.8	121.8	118.8	115.7	113.5	111.2	108.9
72.5°	125.6	123.3	118.8	112.7	107.4	102.9	100.6	96.8	94.6	90.8	89.3
75°	103.6	99.8	97.6	92.3	87.7	84.0	80.9	76.4	73.4	71.9	71.1
77.5°	81.7	80.2	77.2	72.6	70.3	66.6	62.0	60.5	59.0	59.0	58.2
80°	61.3	59.0	56.7	53.0	50.7	47.7	47.7	47.7	46.9	47.7	46.9
82.5°	41.6	40.1	38.6	36.3	35.6	35.6	36.3	36.3	36.3	36.3	36.3
85°	24.2	24.2	24.2	25.0	24.2	24.2	25.0	25.7	25.0	25.0	24.2
87.5°	11.3	11.3	12.1	12.1	12.9	12.9	12.9	12.9	12.9	12.9	13.6
90°	14.8	16.5	18.7	23.0	27.4	31.7	36.1	37.4	38.8	40.1	41.4
92.5°	26.6	25.6	27.1	30.1	33.1	36.1	39.1	41.4	43.8	46.1	48.4
95°	36.9	30.1	31.9	35.6	39.3	42.9	46.6	48.9	51.3	53.6	55.9
97.5°	129.5	124.8	116.3	99.2	82.2	65.1	48.1	50.8	53.5	56.2	58.9
100°	280.9	284.2	258.1	206.0	153.9	101.7	49.6	52.3	55.0	57.7	60.4
102.5°	370.8	373.0	343.9	285.8	227.6	169.5	111.3	100.3	89.3	78.2	67.2
105°	462.9	464.7	449.7	419.6	389.5	359.4	329.3	270.2	211.0	151.9	92.8
107.5°	560.9	562.4	564.9	569.9	575.0	580.0	585.0	533.5	482.1	430.6	379.1
110°	660.4	661.7	663.5	667.2	670.9	674.5	678.2	667.2	656.2	645.1	634.1

TEST NUMBER: P1032310

CATALOG NUMBER: S123RDIW-B560D1535UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	755.2	756.4	758.2	761.9	765.6	769.3	773.0	776.0	779.0	782.0	785.0
115°	848.7	849.7	851.2	854.2	857.2	860.2	863.2	866.6	869.9	873.3	876.6
117.5°	943.2	944.4	945.2	946.9	948.6	950.2	951.9	954.6	957.3	960.0	962.7
120°	1031.7	1033.2	1033.7	1034.7	1035.7	1036.7	1037.7	1040.4	1043.0	1045.7	1048.4
122.5°	1116.2	1117.4	1118.1	1119.4	1120.7	1122.1	1123.4	1125.1	1126.7	1128.4	1130.1
125°	1195.8	1197.1	1197.8	1199.1	1200.4	1201.8	1203.1	1203.8	1204.4	1205.1	1205.8
127.5°	1274.0	1275.3	1276.1	1277.8	1279.5	1281.1	1282.8	1283.8	1284.8	1285.8	1286.8
130°	1346.2	1347.5	1348.2	1349.5	1350.8	1352.2	1353.5	1354.8	1356.2	1357.5	1358.8
132.5°	1415.3	1416.6	1417.1	1418.1	1419.2	1420.2	1421.2	1422.5	1423.9	1425.2	1426.5
135°	1483.3	1484.3	1485.0	1486.3	1487.6	1489.0	1490.3	1491.3	1492.3	1493.3	1494.3
137.5°	1546.2	1547.5	1547.8	1548.5	1549.2	1549.8	1550.5	1552.2	1553.8	1555.5	1557.2
140°	1603.6	1604.6	1605.1	1606.1	1607.1	1608.1	1609.1	1610.5	1611.8	1613.2	1614.5
142.5°	1659.3	1660.3	1660.8	1661.8	1662.8	1663.8	1664.8	1665.8	1666.8	1667.8	1668.8
145°	1711.7	1712.9	1713.2	1713.9	1714.6	1715.2	1715.9	1716.6	1717.2	1717.9	1718.6
147.5°	1758.7	1759.5	1759.8	1760.5	1761.2	1761.8	1762.5	1763.2	1763.8	1764.5	1765.2
150°	1801.1	1801.6	1801.9	1802.6	1803.3	1803.9	1804.6	1805.3	1805.9	1806.6	1807.3
152.5°	1839.0	1839.2	1839.4	1839.7	1840.0	1840.4	1840.7	1842.0	1843.4	1844.7	1846.0
155°	1872.6	1872.3	1872.5	1872.8	1873.1	1873.5	1873.8	1875.5	1877.1	1878.8	1880.5
157.5°	1905.4	1905.4	1905.2	1904.9	1904.6	1904.2	1903.9	1905.9	1907.9	1909.9	1911.9
160°	1931.2	1931.0	1930.8	1930.5	1930.2	1929.8	1929.5	1931.5	1933.5	1935.5	1937.5
162.5°	1954.0	1953.5	1953.3	1953.0	1952.7	1952.3	1952.0	1954.3	1956.7	1959.0	1961.3
165°	1973.6	1973.1	1972.9	1972.6	1972.3	1971.9	1971.6	1974.3	1976.9	1979.6	1982.3
167.5°	1988.8	1988.1	1988.1	1988.1	1988.1	1988.1	1988.1	1990.8	1993.4	1996.1	1998.8
170°	2002.3	2001.6	2001.6	2001.6	2001.6	2001.6	2001.6	2004.3	2007.0	2009.7	2012.4
172.5°	2010.0	2009.2	2009.4	2009.7	2010.0	2010.4	2010.7	2013.4	2016.0	2018.7	2021.4
175°	2017.5	2016.7	2016.9	2017.2	2017.5	2017.9	2018.2	2020.5	2022.9	2025.2	2027.5
177.5°	2020.5	2019.7	2019.9	2020.2	2020.5	2020.9	2021.2	2023.9	2026.5	2029.2	2031.9
180°	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2

TEST NUMBER: P1032310

CATALOG NUMBER: S123RDIW-B560D1535UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	835.1	835.9	833.6	829.1	828.3	829.8	834.3	832.8	829.1	835.9	829.8
5°	789.0	785.2	783.7	785.2	780.6	778.4	782.9	780.6	782.9	783.7	785.9
7.5°	744.3	745.1	740.5	741.3	735.3	736.8	736.8	736.8	739.0	740.5	743.6
10°	705.8	707.3	702.0	702.7	698.2	695.2	697.4	702.0	702.0	702.0	703.5
12.5°	674.7	667.9	664.1	663.4	658.1	656.6	661.1	662.6	666.4	666.4	668.7
15°	636.2	634.6	631.6	631.6	618.8	621.8	623.3	628.6	636.2	630.1	631.6
17.5°	601.4	597.6	593.8	592.3	590.8	586.2	592.3	591.5	596.1	596.8	599.1
20°	570.4	567.3	559.8	560.5	562.0	555.2	559.0	559.0	563.5	568.1	573.4
22.5°	540.1	537.1	533.3	534.8	530.3	528.7	528.7	532.5	537.8	541.6	540.9
25°	516.6	511.3	509.1	506.8	504.5	506.1	503.8	507.6	511.3	513.6	511.3
27.5°	490.2	487.9	483.4	481.1	477.3	478.8	480.3	483.4	485.6	485.6	487.9
30°	464.5	461.4	459.9	457.6	457.6	454.6	455.4	458.4	460.7	462.9	466.0
32.5°	439.5	437.2	434.9	434.9	433.4	432.7	431.9	436.5	436.5	441.0	441.0
35°	419.1	415.3	415.3	411.5	413.0	412.3	410.7	413.8	414.5	417.6	416.8
37.5°	396.4	396.4	394.9	391.1	388.1	388.8	392.6	392.6	394.9	394.1	396.4
40°	373.7	372.2	372.2	369.9	369.1	368.4	369.1	369.9	373.7	372.9	373.7
42.5°	351.0	351.7	348.0	348.0	348.0	345.7	346.4	347.2	348.7	350.2	352.5
45°	329.0	327.5	326.8	325.3	323.8	324.5	323.8	326.8	326.0	327.5	329.8
47.5°	305.6	303.3	302.6	299.5	299.5	301.1	300.3	302.6	303.3	305.6	304.1
50°	282.9	279.9	277.6	278.4	273.8	275.3	275.3	277.6	279.9	280.6	282.1
52.5°	256.4	255.7	254.9	251.1	250.4	249.6	250.4	251.1	254.2	256.4	257.2
55°	230.7	230.0	225.4	223.9	221.6	221.6	223.1	223.9	229.2	230.0	233.0
57.5°	207.3	205.0	199.7	198.9	198.9	198.9	196.7	199.7	201.2	205.0	205.0
60°	181.5	181.5	177.0	177.0	177.8	177.0	177.0	177.8	177.8	180.8	182.3
62.5°	161.1	160.4	160.4	158.9	158.1	158.9	158.1	158.1	158.9	161.1	163.4
65°	143.0	142.2	141.5	140.7	139.2	139.2	139.9	141.5	141.5	143.0	143.7
67.5°	125.6	125.6	124.1	124.1	123.3	122.5	123.3	122.5	125.6	125.6	126.3
70°	108.2	107.4	105.1	104.4	102.1	102.9	102.9	105.1	105.9	107.4	108.9
72.5°	87.0	87.0	85.5	84.0	84.7	83.2	83.2	84.0	84.0	86.2	87.0
75°	71.9	70.3	69.6	70.3	69.6	71.1	69.6	69.6	71.1	71.1	71.1
77.5°	59.0	59.0	58.2	58.2	59.0	58.2	59.0	59.0	59.0	58.2	59.0
80°	48.4	47.7	47.7	47.7	46.9	46.9	46.9	46.9	46.9	46.9	46.9
82.5°	36.3	36.3	35.6	36.3	36.3	35.6	36.3	35.6	35.6	36.3	36.3
85°	24.2	25.7	24.2	24.2	25.0	25.0	25.7	25.0	25.7	24.2	25.0
87.5°	12.9	13.6	13.6	12.9	12.9	13.6	13.6	13.6	14.4	12.9	13.6
90°	42.1	42.4	43.1	43.8	44.4	45.1	44.4	43.8	43.1	42.4	42.1
92.5°	49.6	49.8	50.1	50.4	50.8	51.1	50.8	50.4	50.1	49.8	49.6
95°	57.1	57.1	57.1	57.1	57.1	57.1	57.1	57.1	57.1	57.1	57.1
97.5°	60.2	60.4	60.7	61.0	61.4	61.7	61.4	61.0	60.7	60.4	60.2
100°	61.7	61.9	62.2	62.5	62.9	63.2	62.9	62.5	62.2	61.9	61.7
102.5°	61.7	62.0	62.7	63.4	64.0	64.7	64.0	63.4	62.7	62.0	61.7
105°	63.2	63.5	64.2	64.9	65.5	66.2	65.5	64.9	64.2	63.5	63.2
107.5°	353.4	331.5	287.7	244.0	200.2	156.4	200.2	244.0	287.7	331.5	353.4
110°	628.6	604.7	556.9	509.2	461.4	413.6	461.4	509.2	556.9	604.7	628.6

TEST NUMBER: P1032310

CATALOG NUMBER: S123RDIW-B560D1535UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	786.5	786.2	785.5	784.8	784.2	783.5	784.2	784.8	785.5	786.2	786.5
115°	878.3	879.0	880.3	881.6	883.0	884.3	883.0	881.6	880.3	879.0	878.3
117.5°	964.0	964.2	964.5	964.8	965.2	965.5	965.2	964.8	964.5	964.2	964.0
120°	1049.7	1049.7	1049.7	1049.7	1049.7	1049.7	1049.7	1049.7	1049.7	1049.7	1049.7
122.5°	1130.9	1131.1	1131.4	1131.7	1132.1	1132.4	1132.1	1131.7	1131.4	1131.1	1130.9
125°	1206.1	1206.4	1207.1	1207.8	1208.4	1209.1	1208.4	1207.8	1207.1	1206.4	1206.1
127.5°	1287.3	1287.0	1286.3	1285.6	1285.0	1284.3	1285.0	1285.6	1286.3	1287.0	1287.3
130°	1359.5	1359.2	1358.5	1357.8	1357.2	1356.5	1357.2	1357.8	1358.5	1359.2	1359.5
132.5°	1427.2	1426.7	1425.7	1424.7	1423.7	1422.7	1423.7	1424.7	1425.7	1426.7	1427.2
135°	1494.8	1494.3	1493.3	1492.3	1491.3	1490.3	1491.3	1492.3	1493.3	1494.3	1494.8
137.5°	1558.0	1557.7	1557.0	1556.3	1555.7	1555.0	1555.7	1556.3	1557.0	1557.7	1558.0
140°	1615.2	1614.9	1614.2	1613.5	1612.8	1612.1	1612.8	1613.5	1614.2	1614.9	1615.2
142.5°	1669.3	1668.8	1667.8	1666.8	1665.8	1664.8	1665.8	1666.8	1667.8	1668.8	1669.3
145°	1718.9	1718.9	1718.9	1718.9	1718.9	1718.9	1718.9	1718.9	1718.9	1718.9	1718.9
147.5°	1765.5	1764.7	1763.0	1761.3	1759.7	1758.0	1759.7	1761.3	1763.0	1764.7	1765.5
150°	1807.6	1807.1	1806.1	1805.1	1804.1	1803.1	1804.1	1805.1	1806.1	1807.1	1807.6
152.5°	1846.7	1845.9	1844.2	1842.5	1840.9	1839.2	1840.9	1842.5	1844.2	1845.9	1846.7
155°	1881.3	1880.3	1878.3	1876.3	1874.3	1872.3	1874.3	1876.3	1878.3	1880.3	1881.3
157.5°	1912.9	1911.6	1908.9	1906.2	1903.6	1900.9	1903.6	1906.2	1908.9	1911.6	1912.9
160°	1938.5	1937.3	1935.0	1932.7	1930.3	1928.0	1930.3	1932.7	1935.0	1937.3	1938.5
162.5°	1962.5	1961.5	1959.5	1957.5	1955.5	1953.5	1955.5	1957.5	1959.5	1961.5	1962.5
165°	1983.6	1982.4	1980.1	1977.8	1975.4	1973.1	1975.4	1977.8	1980.1	1982.4	1983.6
167.5°	2000.1	1998.8	1996.1	1993.4	1990.8	1988.1	1990.8	1993.4	1996.1	1998.8	2000.1
170°	2013.7	2012.4	2009.7	2007.0	2004.3	2001.6	2004.3	2007.0	2009.7	2012.4	2013.7
172.5°	2022.7	2021.2	2018.2	2015.2	2012.2	2009.2	2012.2	2015.2	2018.2	2021.2	2022.7
175°	2028.7	2027.4	2024.7	2022.0	2019.4	2016.7	2019.4	2022.0	2024.7	2027.4	2028.7
177.5°	2033.2	2031.5	2028.2	2024.9	2021.5	2018.2	2021.5	2024.9	2028.2	2031.5	2033.2
180°	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2

TEST NUMBER: P1032310

CATALOG NUMBER: S123RDIW-B560D1535UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	835.9	838.9	835.9	829.8	835.9	839.6	843.4	849.5	852.5	852.5	857.0
5°	788.2	794.3	792.0	790.5	796.5	800.3	806.4	813.9	822.2	827.5	833.6
7.5°	745.8	749.6	753.4	753.4	759.5	767.8	776.9	785.9	796.5	804.1	808.6
10°	708.8	711.8	714.1	717.1	726.2	735.3	747.4	758.7	767.8	776.1	783.7
12.5°	673.2	677.8	683.1	685.3	692.1	703.5	714.8	728.4	742.8	751.1	758.7
15°	639.2	641.5	647.5	654.3	660.4	672.5	686.8	701.2	713.3	726.2	733.0
17.5°	604.4	605.1	621.0	617.2	636.9	648.3	655.8	669.4	689.1	699.7	710.3
20°	570.4	577.9	584.7	588.5	599.1	612.0	633.9	644.5	660.4	670.2	679.3
22.5°	543.9	555.2	555.2	564.3	569.6	581.7	597.6	618.0	635.4	642.2	655.1
25°	520.4	525.7	534.8	537.8	547.7	558.2	568.8	590.8	609.7	618.8	627.8
27.5°	490.2	497.0	509.1	509.1	521.9	533.3	546.1	560.5	579.4	592.3	602.1
30°	466.7	473.5	478.8	487.1	492.4	503.0	525.7	536.3	553.0	564.3	576.4
32.5°	444.8	450.1	454.6	463.7	469.7	481.8	494.0	512.9	527.2	537.8	550.7
35°	420.6	425.9	431.9	438.7	447.8	459.2	470.5	486.4	500.8	510.6	521.2
37.5°	397.9	401.7	410.7	415.3	422.8	433.4	447.8	464.5	477.3	484.9	495.5
40°	375.9	379.0	385.8	394.1	399.4	407.7	422.8	437.2	453.1	462.2	470.5
42.5°	352.5	356.3	362.3	370.7	379.0	388.1	396.4	413.0	427.4	434.9	444.0
45°	332.1	334.3	338.9	347.2	355.5	362.3	375.2	390.3	403.9	410.0	419.8
47.5°	307.9	310.1	316.9	320.7	329.8	338.9	351.7	366.9	379.0	385.0	394.1
50°	282.9	285.2	289.7	298.0	304.1	313.9	325.3	338.1	353.3	361.6	366.9
52.5°	258.7	263.2	267.0	273.8	281.4	291.2	301.8	313.9	326.8	335.1	341.2
55°	234.5	238.3	242.8	246.6	255.7	264.8	276.9	288.2	299.5	307.1	313.9
57.5°	207.3	212.6	217.1	224.7	231.5	239.0	252.6	261.7	275.3	280.6	286.7
60°	183.8	189.1	192.9	198.9	205.0	214.8	223.9	235.3	246.6	253.4	261.0
62.5°	164.1	166.4	168.7	174.7	180.8	189.9	198.9	210.3	222.4	226.2	232.2
65°	144.5	146.7	150.5	155.8	160.4	165.7	175.5	184.6	195.9	202.0	204.2
67.5°	127.8	130.1	130.9	134.6	138.4	144.5	149.8	158.9	169.4	173.2	177.8
70°	108.9	112.7	113.5	116.5	118.0	121.8	127.8	134.6	143.0	149.8	153.6
72.5°	87.0	92.3	93.8	98.3	100.6	104.4	108.9	114.2	119.5	122.5	125.6
75°	71.1	72.6	73.4	77.2	80.9	86.2	88.5	91.5	96.1	99.8	102.9
77.5°	59.0	59.8	60.5	60.5	61.3	64.3	68.8	72.6	75.6	77.2	79.4
80°	47.7	46.9	46.9	47.7	47.7	47.7	49.2	54.5	56.0	59.8	59.0
82.5°	37.1	35.6	36.3	35.6	35.6	35.6	35.6	36.3	36.3	38.6	40.1
85°	24.2	25.0	24.2	24.2	23.4	24.2	23.4	23.4	22.7	22.7	21.9
87.5°	12.9	13.6	12.9	12.9	12.1	12.9	12.1	12.1	11.3	11.3	9.8
90°	41.4	40.1	38.8	37.4	36.1	31.7	27.4	23.0	18.7	16.5	14.8
92.5°	48.4	46.1	43.8	41.4	39.1	36.1	33.1	30.1	27.1	25.6	26.6
95°	55.9	53.6	51.3	48.9	46.6	42.9	39.3	35.6	31.9	30.1	36.9
97.5°	58.9	56.2	53.5	50.8	48.1	65.1	82.2	99.2	116.3	124.8	129.5
100°	60.4	57.7	55.0	52.3	49.6	101.7	153.9	206.0	258.1	284.2	280.9
102.5°	67.2	78.2	89.3	100.3	111.3	169.5	227.6	285.8	343.9	373.0	370.8
105°	92.8	151.9	211.0	270.2	329.3	359.4	389.5	419.6	449.7	464.7	462.9
107.5°	379.1	430.6	482.1	533.5	585.0	580.0	575.0	569.9	564.9	562.4	560.9
110°	634.1	645.1	656.2	667.2	678.2	674.5	670.9	667.2	663.5	661.7	660.4

TEST NUMBER: P1032310

CATALOG NUMBER: S123RDIW-B560D1535UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	785.0	782.0	779.0	776.0	773.0	769.3	765.6	761.9	758.2	756.4	755.2
115°	876.6	873.3	869.9	866.6	863.2	860.2	857.2	854.2	851.2	849.7	848.7
117.5°	962.7	960.0	957.3	954.6	951.9	950.2	948.6	946.9	945.2	944.4	943.2
120°	1048.4	1045.7	1043.0	1040.4	1037.7	1036.7	1035.7	1034.7	1033.7	1033.2	1031.7
122.5°	1130.1	1128.4	1126.7	1125.1	1123.4	1122.1	1120.7	1119.4	1118.1	1117.4	1116.2
125°	1205.8	1205.1	1204.4	1203.8	1203.1	1201.8	1200.4	1199.1	1197.8	1197.1	1195.8
127.5°	1286.8	1285.8	1284.8	1283.8	1282.8	1281.1	1279.5	1277.8	1276.1	1275.3	1274.0
130°	1358.8	1357.5	1356.2	1354.8	1353.5	1352.2	1350.8	1349.5	1348.2	1347.5	1346.2
132.5°	1426.5	1425.2	1423.9	1422.5	1421.2	1420.2	1419.2	1418.1	1417.1	1416.6	1415.3
135°	1494.3	1493.3	1492.3	1491.3	1490.3	1489.0	1487.6	1486.3	1485.0	1484.3	1483.3
137.5°	1557.2	1555.5	1553.8	1552.2	1550.5	1549.8	1549.2	1548.5	1547.8	1547.5	1546.2
140°	1614.5	1613.2	1611.8	1610.5	1609.1	1608.1	1607.1	1606.1	1605.1	1604.6	1603.6
142.5°	1668.8	1667.8	1666.8	1665.8	1664.8	1663.8	1662.8	1661.8	1660.8	1660.3	1659.3
145°	1718.6	1717.9	1717.2	1716.6	1715.9	1715.2	1714.6	1713.9	1713.2	1712.9	1711.7
147.5°	1765.2	1764.5	1763.8	1763.2	1762.5	1761.8	1761.2	1760.5	1759.8	1759.5	1758.7
150°	1807.3	1806.6	1805.9	1805.3	1804.6	1803.9	1803.3	1802.6	1801.9	1801.6	1801.1
152.5°	1846.0	1844.7	1843.4	1842.0	1840.7	1840.4	1840.0	1839.7	1839.4	1839.2	1839.0
155°	1880.5	1878.8	1877.1	1875.5	1873.8	1873.5	1873.1	1872.8	1872.5	1872.3	1872.6
157.5°	1911.9	1909.9	1907.9	1905.9	1903.9	1904.2	1904.6	1904.9	1905.2	1905.4	1905.4
160°	1937.5	1935.5	1933.5	1931.5	1929.5	1929.8	1930.2	1930.5	1930.8	1931.0	1931.2
162.5°	1961.3	1959.0	1956.7	1954.3	1952.0	1952.3	1952.7	1953.0	1953.3	1953.5	1954.0
165°	1982.3	1979.6	1976.9	1974.3	1971.6	1971.9	1972.3	1972.6	1972.9	1973.1	1973.6
167.5°	1998.8	1996.1	1993.4	1990.8	1988.1	1988.1	1988.1	1988.1	1988.1	1988.1	1988.8
170°	2012.4	2009.7	2007.0	2004.3	2001.6	2001.6	2001.6	2001.6	2001.6	2001.6	2002.3
172.5°	2021.4	2018.7	2016.0	2013.4	2010.7	2010.4	2010.0	2009.7	2009.4	2009.2	2010.0
175°	2027.5	2025.2	2022.9	2020.5	2018.2	2017.9	2017.5	2017.2	2016.9	2016.7	2017.5
177.5°	2031.9	2029.2	2026.5	2023.9	2021.2	2020.9	2020.5	2020.2	2019.9	2019.7	2020.5
180°	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2

TEST NUMBER: P1032310

CATALOG NUMBER: S123RDIW-B560D1535UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	883.5	883.5	883.5	883.5
2.5°	860.8	866.1	876.7	885.8
5°	842.7	851.0	866.9	882.8
7.5°	820.7	833.6	854.0	876.0
10°	799.6	816.2	841.2	866.9
12.5°	778.4	795.8	822.2	855.5
15°	753.4	771.6	803.3	843.4
17.5°	731.5	755.7	784.4	824.5
20°	708.0	726.2	763.2	805.6
22.5°	678.5	708.8	743.6	788.2
25°	655.1	681.5	716.3	767.0
27.5°	626.3	657.3	699.7	744.3
30°	602.9	628.6	667.9	721.6
32.5°	575.6	605.9	646.8	699.7
35°	551.4	577.2	615.7	669.4
37.5°	522.7	550.7	593.8	641.5
40°	497.7	525.0	565.8	610.4
42.5°	467.5	496.2	537.1	574.9
45°	443.3	469.7	502.3	537.1
47.5°	413.8	441.8	473.5	497.7
50°	387.3	413.0	438.0	458.4
52.5°	358.5	382.0	404.7	419.8
55°	332.1	350.2	368.4	379.0
57.5°	301.1	318.5	333.6	339.6
60°	273.8	288.2	298.0	304.8
62.5°	245.1	255.7	263.2	267.0
65°	217.1	224.7	228.4	232.2
67.5°	188.4	195.2	197.4	202.0
70°	158.1	165.7	167.2	169.4
72.5°	135.4	135.4	138.4	141.5
75°	108.2	109.7	111.2	111.2
77.5°	84.7	84.7	86.2	87.0
80°	62.0	62.8	62.8	62.0
82.5°	42.4	43.9	42.4	41.6
85°	23.4	26.5	25.0	25.0
87.5°	9.8	9.8	11.3	9.8
90°	11.5	8.2	4.8	1.5
92.5°	28.6	30.6	32.6	34.6
95°	50.6	64.3	78.0	91.7
97.5°	138.8	148.2	157.5	166.9
100°	274.2	267.5	260.9	254.2
102.5°	366.5	362.1	357.8	353.4
105°	459.2	455.5	451.9	448.2
107.5°	557.9	554.9	551.9	548.9
110°	657.7	655.0	652.4	649.7



TEST NUMBER: P1032310

CATALOG NUMBER: S123RDIW-B560D1535UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	752.9	750.6	748.2	745.9
115°	846.7	844.7	842.7	840.7
117.5°	940.9	938.6	936.2	933.9
120°	1028.7	1025.6	1022.6	1019.6
122.5°	1113.9	1111.5	1109.2	1106.8
125°	1193.1	1190.4	1187.7	1185.0
127.5°	1271.3	1268.6	1265.9	1263.2
130°	1343.5	1340.8	1338.1	1335.4
132.5°	1412.6	1409.9	1407.3	1404.6
135°	1481.3	1479.3	1477.3	1475.3
137.5°	1543.5	1540.8	1538.1	1535.4
140°	1601.6	1599.6	1597.6	1595.6
142.5°	1657.3	1655.2	1653.2	1651.2
145°	1709.4	1707.1	1704.7	1702.4
147.5°	1757.0	1755.3	1753.7	1752.0
150°	1800.1	1799.1	1798.1	1797.1
152.5°	1838.7	1838.4	1838.0	1837.7
155°	1873.3	1874.0	1874.6	1875.3
157.5°	1905.4	1905.4	1905.4	1905.4
160°	1931.5	1931.8	1932.2	1932.5
162.5°	1955.0	1956.0	1957.0	1958.0
165°	1974.6	1975.6	1976.6	1977.6
167.5°	1990.1	1991.4	1992.8	1994.1
170°	2003.6	2005.0	2006.3	2007.7
172.5°	2011.7	2013.4	2015.0	2016.7
175°	2019.2	2020.9	2022.5	2024.2
177.5°	2022.2	2023.9	2025.5	2027.2
180°	2024.2	2024.2	2024.2	2024.2

(END OF REPORT)