

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031820

Luminaire Tested: S123DIW-B560D755UB30-4F0-XX-W2A-F

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031820
REPORT IS A COMBINATION OF REPORTS P991809 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B560D755UB30-4F0-XX-W2A-F
Description: Define 3 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5383.0 lumens
Efficiency: N/A
Efficacy: 114.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 47.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031820

CATALOG NUMBER: S123DIW-B560D755UB30-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1031820

CATALOG NUMBER: S123DIW-B560D755UB30-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50
1	96	92	88	84	88	84	81	78	69	67	65	56	55	53	44	43	42
2	88	80	74	69	80	73	68	64	61	57	54	49	47	44	38	37	35
3	80	70	63	57	73	65	58	53	54	49	45	43	40	37	34	32	30
4	73	62	54	48	66	57	50	45	48	42	38	39	35	32	30	28	26
5	67	55	47	41	61	51	44	39	43	37	33	35	31	28	27	25	22
6	62	50	42	36	56	46	39	33	38	33	29	31	27	24	25	22	20
7	57	45	37	31	52	41	34	29	35	29	25	28	24	21	23	20	17
8	53	41	33	28	48	37	31	26	32	26	22	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	31	25	21	27	22	18	22	18	15	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9550	9550	9550
5°	9574	9221	9207
10°	9488	8908	8817
15°	9356	8584	8392
20°	9205	8223	7971
25°	9009	7843	7521
30°	8795	7450	7048
35°	8571	7048	6578
40°	8336	6626	6115
45°	8078	6214	5632
50°	7815	5757	5147
55°	7478	5279	4656
60°	7131	4753	4133
65°	6805	4183	3588
70°	6334	3551	2951
75°	5660	2811	2291
80°	4886	1976	1620
85°	3813	1061	811

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8078 cd/sqm

TEST NUMBER: P1031820

CATALOG NUMBER: S123DIW-B560D755UB30-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.6	1.6
10°-20°	236.2	4.4
20°-30°	348.8	6.5
30°-40°	407.4	7.6
40°-50°	409.5	7.6
50°-60°	359.8	6.7
60°-70°	267.9	5.0
70°-80°	152.5	2.8
80°-90°	45.4	0.8
90°-100°	35.5	0.7
100°-110°	171.8	3.2
110°-120°	421.0	7.8
120°-130°	534.5	9.9
130°-140°	571.0	10.6
140°-150°	533.9	9.9
150°-160°	430.6	8.0
160°-170°	277.9	5.2
170°-180°	95.8	1.8
0°-30°	668.6	12.4
0°-40°	1076.0	20.0
0°-60°	1845.2	34.3
0°-90°	2311.0	42.9
90°-120°	628.3	11.7
90°-150°	2267.7	42.1
90°-180°	3072.0	57.1
0°-180°	5383.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	887	887	887	887	887	
5°	888	884	876	883	882	84
15°	845	842	832	838	834	238
25°	767	763	753	754	751	354
35°	664	659	649	645	641	415
45°	544	541	531	522	518	420
55°	413	412	402	394	390	370
65°	282	278	270	264	262	278
75°	149	146	143	140	137	159
85°	40	38	38	37	37	43
90°	1	8	18	21	22	5
95°	46	15	23	28	28	55
105°	223	231	164	31	33	237
115°	418	423	430	437	440	413
125°	590	596	599	600	602	527
135°	734	739	742	744	742	565
145°	848	853	854	856	856	531
155°	934	932	933	937	932	430
165°	984	982	982	988	982	278
175°	1008	1004	1005	1010	1004	96
180°	1008	1008	1008	1008	1008	

TEST NUMBER: P1031820

CATALOG NUMBER: S123DIW-B560D755UB30-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	887.2	887.2	887.2	887.2	887.2
2.5°	891.0	888.0	879.6	887.2	886.4
5°	888.0	884.2	875.8	883.4	881.9
7.5°	881.1	877.3	868.9	875.8	875.0
10°	871.9	868.1	858.2	865.1	863.6
12.5°	859.7	856.7	847.5	852.1	851.4
15°	845.2	842.2	832.3	838.4	833.8
17.5°	829.2	825.4	815.5	820.1	818.5
20°	810.9	806.3	796.4	799.5	797.2
22.5°	790.3	785.7	775.8	778.1	775.1
25°	767.4	762.9	752.9	753.7	751.4
27.5°	743.8	739.2	728.5	729.3	727.0
30°	717.8	714.0	703.4	703.4	698.0
32.5°	691.9	686.6	678.9	673.6	671.3
35°	663.7	659.1	649.2	644.6	640.8
37.5°	635.5	629.4	619.4	614.1	611.8
40°	605.7	601.1	590.5	584.3	581.3
42.5°	576.0	570.6	559.9	553.8	550.8
45°	543.9	540.9	530.9	521.8	518.0
47.5°	512.6	508.1	498.9	489.8	486.7
50°	480.6	476.8	466.9	458.5	453.9
52.5°	447.0	444.7	434.1	427.2	422.6
55°	412.7	411.9	402.0	393.6	389.8
57.5°	380.7	377.6	370.0	362.4	357.8
60°	345.6	344.8	335.7	328.8	325.0
62.5°	314.3	312.0	302.9	296.0	293.7
65°	281.5	277.7	270.1	263.9	261.7
67.5°	246.4	243.4	237.2	231.9	228.9
70°	215.1	210.5	206.0	200.6	196.8
72.5°	182.3	179.3	173.9	169.4	167.8
75°	148.8	145.7	143.4	139.6	137.3
77.5°	119.0	117.5	114.4	111.4	111.4
80°	90.0	87.7	86.2	85.4	85.4
82.5°	61.8	61.8	61.8	60.3	59.5
85°	39.7	38.1	38.1	36.6	36.6
87.5°	19.8	17.5	16.8	16.0	16.0
90°	0.7	8.2	18.0	21.0	22.5
92.5°	17.2	12.7	19.5	24.7	25.5
95°	45.7	15.0	23.2	28.4	28.4
97.5°	83.1	62.1	24.0	29.9	30.7
100°	126.5	141.5	24.7	30.7	31.4
102.5°	175.9	185.7	55.4	30.7	32.2
105°	223.1	231.3	164.0	31.4	32.9
107.5°	273.3	280.0	291.2	175.9	77.9
110°	323.4	329.4	337.6	312.9	205.9

TEST NUMBER: P1031820

CATALOG NUMBER: S123DIW-B560D755UB30-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	371.3	376.6	384.8	391.5	390.0
115°	418.5	423.0	429.7	437.2	440.2
117.5°	464.9	470.1	473.9	479.9	480.6
120°	507.6	514.3	516.6	522.6	522.6
122.5°	551.0	556.2	559.2	563.0	563.7
125°	589.9	595.9	598.9	600.4	601.9
127.5°	628.9	634.9	638.6	640.8	639.3
130°	664.8	670.8	673.8	676.8	675.3
132.5°	699.2	705.2	707.5	710.5	708.2
135°	734.4	738.9	741.9	744.2	741.9
137.5°	764.4	770.4	771.9	775.6	774.1
140°	794.3	798.8	801.1	804.0	802.5
142.5°	822.0	826.5	828.8	831.0	828.8
145°	847.5	852.7	854.2	855.7	855.7
147.5°	872.2	875.9	877.4	878.9	875.2
150°	894.6	896.9	898.4	899.9	897.6
152.5°	914.8	915.6	916.3	919.3	915.6
155°	933.6	932.1	932.8	936.6	932.1
157.5°	948.5	948.5	947.8	952.3	946.3
160°	962.0	961.3	960.5	965.0	959.8
162.5°	974.7	972.5	971.7	977.0	972.5
165°	984.5	982.2	981.5	987.5	982.2
167.5°	992.7	989.7	989.7	995.7	989.7
170°	999.4	996.4	996.4	1002.4	996.4
172.5°	1003.9	1000.2	1000.9	1006.9	1000.2
175°	1007.7	1003.9	1004.7	1009.9	1003.9
177.5°	1009.2	1005.4	1006.2	1012.2	1004.7
180°	1007.7	1007.7	1007.7	1007.7	1007.7

(END OF REPORT)