

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032416

Luminaire Tested: S123RDIW-B775D1535UB35-4F0-XX-W2A-F

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032416
REPORT IS A COMBINATION OF REPORTS P994716 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B775D1535UB35-4F0-XX-W2A-F
Description: Define 3 Regressed Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9200.0 lumens
Efficiency: N/A
Efficacy: 104.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 88.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032416

CATALOG NUMBER: S123RDIW-B775D1535UB35-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1032416

CATALOG NUMBER: S123RDIW-B775D1535UB35-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40
1	94	90	86	83	84	81	78	75	64	62	60	49	48	47	35	35	34
2	86	79	73	68	77	71	66	62	57	53	50	44	41	39	31	30	29
3	78	69	62	57	70	63	57	52	50	46	43	39	36	33	28	26	25
4	72	61	54	48	64	56	49	44	45	40	36	34	31	29	25	23	21
5	66	55	47	41	59	50	43	38	40	35	31	31	28	25	23	20	19
6	60	49	41	36	54	44	38	33	36	31	27	28	25	22	21	18	17
7	56	44	36	31	50	40	33	29	33	28	24	25	22	19	19	17	15
8	52	40	33	27	47	36	30	25	30	25	21	23	20	17	17	15	13
9	48	36	29	24	43	33	27	23	27	22	19	21	18	15	16	14	12
10	45	33	26	22	40	30	24	20	25	20	17	20	16	14	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14032	14032	14032
5°	14055	13535	13499
10°	13944	13026	12769
15°	13763	12397	11971
20°	13525	11713	11079
25°	13280	11002	10233
30°	12967	10246	9234
35°	12643	9503	8324
40°	12338	8697	7319
45°	11949	7908	6414
50°	11518	7065	5479
55°	11073	6164	4621
60°	10645	5239	3752
65°	10095	4290	2928
70°	9403	3244	2093
75°	8407	2197	1658
80°	7177	1527	1163
85°	5379	824	610

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11949 cd/sqm

TEST NUMBER: P1032416

CATALOG NUMBER: S123RDIW-B775D1535UB35-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.5	1.3
10°-20°	340.9	3.7
20°-30°	490.8	5.3
30°-40°	552.8	6.0
40°-50°	528.7	5.7
50°-60°	432.8	4.7
60°-70°	291.8	3.2
70°-80°	146.4	1.6
80°-90°	42.4	0.5
90°-100°	72.3	0.8
100°-110°	349.6	3.8
110°-120°	856.7	9.3
120°-130°	1087.5	11.8
130°-140°	1161.8	12.6
140°-150°	1086.4	11.8
150°-160°	876.3	9.5
160°-170°	565.5	6.1
170°-180°	194.9	2.1
0°-30°	954.3	10.4
0°-40°	1507.0	16.4
0°-60°	2468.6	26.8
0°-90°	2949.1	32.1
90°-120°	1278.6	13.9
90°-150°	4614.2	50.2
90°-180°	6251.0	67.9
0°-180°	9200.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1304	1304	1304	1304	1304	
5°	1304	1298	1286	1295	1293	124
15°	1243	1232	1202	1197	1189	350
25°	1131	1105	1056	1034	1022	520
35°	979	941	875	830	811	613
45°	805	757	676	615	590	621
55°	611	559	469	408	387	548
65°	418	360	277	225	214	413
75°	221	170	112	102	99	235
85°	56	33	30	28	28	61
90°	2	17	37	43	46	9
95°	93	30	47	58	58	111
105°	454	471	334	64	67	481
115°	852	861	874	890	896	841
125°	1200	1213	1219	1222	1225	1073
135°	1494	1504	1510	1514	1510	1151
145°	1724	1735	1738	1741	1741	1080
155°	1900	1897	1898	1906	1897	875
165°	2003	1999	1997	2009	1999	566
175°	2050	2043	2044	2055	2043	195
180°	2050	2050	2050	2050	2050	

TEST NUMBER: P1032416

CATALOG NUMBER: S123RDIW-B775D1535UB35-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1303.6	1303.6	1303.6	1303.6	1303.6
2.5°	1308.9	1304.6	1291.9	1303.6	1301.5
5°	1303.6	1298.3	1285.6	1295.1	1293.0
7.5°	1294.1	1288.8	1272.9	1279.3	1276.1
10°	1281.4	1274.0	1254.9	1256.0	1250.7
12.5°	1263.4	1254.9	1230.6	1229.6	1223.2
15°	1243.3	1231.7	1202.1	1196.8	1189.4
17.5°	1219.0	1206.3	1169.3	1158.7	1148.2
20°	1191.5	1174.6	1134.4	1120.7	1108.0
22.5°	1160.8	1140.8	1097.4	1079.4	1067.8
25°	1131.2	1104.8	1056.2	1034.0	1022.3
27.5°	1095.3	1066.8	1013.9	984.3	966.3
30°	1058.3	1026.6	967.4	931.4	914.5
32.5°	1021.3	984.3	920.9	880.7	862.7
35°	979.0	940.9	875.4	829.9	810.9
37.5°	936.7	895.5	826.8	776.0	752.8
40°	896.5	850.0	775.0	720.0	695.7
42.5°	851.1	804.6	726.3	665.0	643.9
45°	804.6	757.0	675.6	615.3	589.9
47.5°	759.1	706.2	625.9	560.3	538.1
50°	708.3	658.7	573.0	507.5	483.2
52.5°	662.9	607.9	523.3	454.6	433.5
55°	611.1	559.3	469.4	408.1	386.9
57.5°	564.6	508.5	417.6	359.5	341.5
60°	515.9	457.8	370.0	312.9	295.0
62.5°	467.3	409.2	321.4	268.5	249.5
65°	417.6	359.5	277.0	225.2	213.6
67.5°	367.9	308.7	228.4	189.2	176.6
70°	319.3	262.2	188.2	151.2	139.6
72.5°	270.7	214.6	149.1	120.5	117.4
75°	221.0	170.2	112.1	101.5	99.4
77.5°	175.5	129.0	87.8	81.4	79.3
80°	132.2	88.8	66.6	63.4	61.3
82.5°	90.9	55.0	47.6	44.4	44.4
85°	56.0	32.8	29.6	27.5	27.5
87.5°	25.4	13.7	13.7	12.7	11.6
90°	1.5	16.8	36.6	42.7	45.7
92.5°	35.0	25.9	39.6	50.3	51.8
95°	92.9	30.5	47.2	57.9	57.9
97.5°	169.1	126.4	48.7	60.9	62.5
100°	257.4	287.9	50.3	62.5	64.0
102.5°	358.0	377.8	112.7	62.5	65.5
105°	454.0	470.7	333.6	64.0	67.0
107.5°	556.0	569.7	592.6	358.0	158.4
110°	658.1	670.3	687.0	636.8	418.9

TEST NUMBER: P1032416

CATALOG NUMBER: S123RDIW-B775D1535UB35-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	755.6	766.2	783.0	796.7	793.7
115°	851.6	860.7	874.4	889.6	895.7
117.5°	946.0	956.7	964.3	976.5	978.0
120°	1032.8	1046.5	1051.1	1063.3	1063.3
122.5°	1121.2	1131.8	1137.9	1145.6	1147.1
125°	1200.4	1212.6	1218.7	1221.7	1224.8
127.5°	1279.6	1291.8	1299.4	1304.0	1300.9
130°	1352.7	1364.9	1371.0	1377.1	1374.1
132.5°	1422.8	1435.0	1439.6	1445.7	1441.1
135°	1494.4	1503.5	1509.6	1514.2	1509.6
137.5°	1555.3	1567.5	1570.6	1578.2	1575.1
140°	1616.3	1625.4	1630.0	1636.1	1633.0
142.5°	1672.6	1681.8	1686.3	1690.9	1686.3
145°	1724.4	1735.1	1738.1	1741.2	1741.2
147.5°	1774.7	1782.3	1785.4	1788.4	1780.8
150°	1820.4	1825.0	1828.0	1831.1	1826.5
152.5°	1861.5	1863.1	1864.6	1870.7	1863.1
155°	1899.6	1896.6	1898.1	1905.7	1896.6
157.5°	1930.1	1930.1	1928.6	1937.7	1925.5
160°	1957.5	1956.0	1954.5	1963.6	1952.9
162.5°	1983.4	1978.8	1977.3	1988.0	1978.8
165°	2003.2	1998.6	1997.1	2009.3	1998.6
167.5°	2020.0	2013.9	2013.9	2026.1	2013.9
170°	2033.7	2027.6	2027.6	2039.8	2027.6
172.5°	2042.8	2035.2	2036.7	2048.9	2035.2
175°	2050.4	2042.8	2044.3	2055.0	2042.8
177.5°	2053.5	2045.9	2047.4	2059.6	2044.3
180°	2050.4	2050.4	2050.4	2050.4	2050.4

(END OF REPORT)