

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031885

Luminaire Tested: S123DIW-B775D1320UB40-4F0-XX-W2A-A

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031885
REPORT IS A COMBINATION OF REPORTS P991953 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B775D1320UB40-4F0-XX-W2A-A
Description: Define 3 Direct/Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8512.0 lumens
Efficiency: N/A
Efficacy: 109.1 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 78
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031885

CATALOG NUMBER: S123DIW-B775D1320UB40-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1031885

CATALOG NUMBER: S123DIW-B775D1320UB40-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45
1	95	91	87	84	86	83	80	77	68	65	63	53	52	51	40	40	39
2	87	80	74	69	79	73	68	63	59	56	53	47	45	43	36	34	33
3	79	70	63	58	72	64	58	53	53	48	45	42	39	36	32	30	28
4	73	62	55	49	66	57	50	45	47	42	38	37	34	31	29	26	24
5	67	55	48	42	60	51	44	39	42	37	33	34	30	27	26	23	21
6	61	50	42	36	56	46	39	34	38	32	29	30	27	24	23	21	19
7	57	45	37	32	51	41	34	29	34	29	25	28	24	21	21	19	17
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	20	17	15
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	15	14
10	46	34	27	22	41	31	25	21	26	21	18	21	18	15	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11626	11626	11626	11626
5°	11634	13396	11668	9998
10°	11560	16210	11572	8730
15°	11400	19225	11493	7859
20°	11263	22134	11287	7231
25°	11059	22692	11084	6904
30°	10913	18748	10913	6689
35°	10732	12538	10665	6500
40°	10515	9051	10385	6210
45°	10243	7170	9947	5850
50°	9583	6088	9241	5495
55°	8857	5351	8496	5100
60°	8120	4658	7688	4685
65°	7313	3989	6957	4132
70°	6473	3311	6040	3485
75°	5535	2497	5177	2689
80°	4376	1667	4034	1768
85°	3016	765	2411	696

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 18751 cd/sqm

TEST NUMBER: P1031885

CATALOG NUMBER: S123DIW-B775D1320UB40-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.2	1.2
10°-20°	341.2	4.0
20°-30°	574.1	6.7
30°-40°	648.8	7.6
40°-50°	581.1	6.8
50°-60°	469.1	5.5
60°-70°	326.9	3.8
70°-80°	171.6	2.0
80°-90°	44.6	0.5
90°-100°	60.7	0.7
100°-110°	293.5	3.4
110°-120°	719.3	8.5
120°-130°	913.1	10.7
130°-140°	975.5	11.5
140°-150°	912.2	10.7
150°-160°	735.8	8.6
160°-170°	474.8	5.6
170°-180°	163.6	1.9
0°-30°	1021.5	12.0
0°-40°	1670.3	19.6
0°-60°	2720.4	32.0
0°-90°	3263.4	38.3
90°-120°	1073.6	12.6
90°-150°	3874.4	45.5
90°-180°	5249.0	61.7
0°-180°	8512.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1080	1080	1080	1080	1080	
5°	1079	1283	1082	958	1079	102
15°	1030	1910	1038	781	1030	291
25°	942	2267	944	690	942	435
35°	831	1221	826	633	831	520
45°	690	659	670	538	690	528
55°	489	448	469	427	489	438
65°	302	291	288	301	302	301
75°	146	150	136	161	146	156
85°	31	34	25	31	31	36
90°	1	38	1	38	1	7
95°	78	49	78	49	78	93
105°	381	56	381	56	381	404
115°	715	752	715	752	715	706
125°	1008	1028	1008	1028	1008	901
135°	1255	1268	1255	1268	1255	966
145°	1448	1462	1448	1462	1448	906
155°	1595	1592	1595	1592	1595	735
165°	1682	1678	1682	1678	1682	475
175°	1722	1715	1722	1715	1722	164
180°	1722	1722	1722	1722	1722	

TEST NUMBER: P1031885

CATALOG NUMBER: S123DIW-B775D1320UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1
2.5°	1083.3	1091.6	1095.8	1102.1	1108.4	1117.8	1120.9	1126.2	1124.1	1128.3	1130.4
5°	1079.1	1093.7	1106.3	1122.0	1136.6	1147.1	1157.6	1174.3	1186.9	1189.0	1198.4
7.5°	1071.8	1092.7	1114.7	1136.6	1164.9	1181.7	1200.5	1223.5	1242.4	1272.7	1284.2
10°	1062.3	1091.6	1123.0	1153.4	1192.1	1218.3	1241.3	1280.0	1318.8	1350.2	1379.5
12.5°	1047.7	1084.3	1125.1	1170.1	1220.4	1250.7	1282.1	1333.4	1392.0	1440.2	1471.6
15°	1029.9	1075.9	1128.3	1176.4	1231.9	1288.4	1321.9	1379.5	1463.2	1508.2	1588.8
17.5°	1015.2	1062.3	1114.7	1190.0	1265.4	1321.9	1346.0	1451.7	1509.2	1584.6	1675.7
20°	992.2	1051.9	1118.9	1194.2	1291.5	1326.1	1375.3	1482.0	1553.2	1651.6	1763.6
22.5°	968.1	1032.0	1112.6	1191.1	1299.9	1336.6	1403.5	1488.3	1601.4	1698.7	1822.2
25°	942.0	1011.1	1092.7	1185.8	1292.6	1346.0	1408.8	1513.4	1635.9	1758.3	1872.4
27.5°	915.8	991.2	1075.9	1169.1	1272.7	1335.5	1398.3	1507.2	1664.2	1797.1	1942.6
30°	890.7	966.0	1050.8	1146.1	1254.9	1315.6	1375.3	1511.3	1686.1	1835.8	1982.3
32.5°	863.5	940.9	1029.9	1109.4	1219.3	1284.2	1351.2	1511.3	1699.7	1858.8	1992.8
35°	831.0	910.6	987.0	1066.5	1175.4	1247.6	1322.9	1500.9	1712.3	1866.2	1948.8
37.5°	799.6	869.8	935.7	1013.1	1127.2	1204.7	1291.5	1488.3	1706.0	1834.8	1857.8
40°	764.0	834.2	887.5	959.8	1080.1	1170.1	1258.1	1471.6	1678.8	1760.4	1693.5
42.5°	729.5	785.0	831.0	901.2	1032.0	1119.9	1215.1	1441.2	1625.4	1642.2	1491.5
45°	689.7	729.5	770.3	849.9	979.7	1069.7	1175.4	1397.3	1539.6	1491.5	1301.0
47.5°	638.4	674.0	719.0	792.3	924.2	1017.3	1117.8	1340.7	1415.1	1314.6	1106.3
50°	589.3	619.6	661.5	732.6	865.6	956.6	1063.4	1251.8	1288.4	1130.4	953.5
52.5°	540.1	563.1	603.9	675.1	808.0	895.9	993.3	1160.7	1139.8	970.2	813.2
55°	488.8	508.7	547.4	617.5	741.0	824.7	917.9	1048.7	994.3	833.1	707.5
57.5°	438.5	459.5	499.2	557.9	674.0	755.7	830.0	932.6	850.9	722.2	611.2
60°	393.5	411.3	441.7	499.2	605.0	670.9	738.9	809.0	741.0	616.5	531.7
62.5°	346.4	363.2	391.4	443.8	534.8	593.4	647.9	705.4	630.1	539.0	463.7
65°	302.5	316.1	342.2	390.4	464.7	512.9	556.8	596.6	535.9	452.1	395.6
67.5°	262.7	274.2	296.2	339.1	401.9	436.4	472.0	505.5	454.2	387.3	339.1
70°	219.8	229.2	249.1	280.5	330.7	366.3	392.5	417.6	371.6	318.2	285.7
72.5°	182.1	191.5	204.1	236.5	271.1	293.1	321.3	334.9	308.8	264.8	232.4
75°	145.5	152.8	164.3	185.3	217.7	232.4	250.1	260.6	236.5	207.2	187.3
77.5°	114.1	117.2	125.6	140.2	162.2	179.0	192.6	198.9	182.1	163.3	146.5
80°	80.6	84.8	91.1	103.6	120.4	125.6	134.0	141.3	130.8	114.1	103.6
82.5°	53.4	58.6	61.8	67.0	77.5	83.7	85.8	92.1	82.7	76.4	72.2
85°	31.4	33.5	34.5	37.7	42.9	46.1	49.2	50.2	48.1	47.1	42.9
87.5°	15.7	15.7	15.7	17.8	18.8	20.9	22.0	22.0	22.0	20.9	19.9
90°	1.3	4.1	7.0	9.8	12.7	14.1	15.9	19.6	23.3	27.0	30.7
92.5°	29.4	27.7	26.0	24.3	22.6	21.7	23.0	25.6	28.1	30.7	33.3
95°	78.0	66.4	54.7	43.1	31.4	25.6	27.2	30.3	33.4	36.6	39.7
97.5°	142.0	134.0	126.1	118.1	110.2	106.2	98.9	84.4	69.9	55.4	40.9
100°	216.2	221.9	227.5	233.2	238.9	241.7	219.5	175.2	130.9	86.5	42.2
102.5°	300.6	304.3	308.0	311.7	315.4	317.2	292.5	243.0	193.6	144.1	94.7
105°	381.2	384.3	387.4	390.5	393.6	395.2	382.4	356.8	331.3	305.7	280.1
107.5°	466.9	469.5	472.0	474.6	477.1	478.4	480.5	484.8	489.1	493.3	497.6
110°	552.6	554.9	557.1	559.4	561.7	562.8	564.4	567.5	570.6	573.8	576.9

TEST NUMBER: P1031885

CATALOG NUMBER: S123DIW-B775D1320UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	634.4	636.4	638.4	640.4	642.4	643.4	645.0	648.1	651.2	654.3	657.4
115°	715.0	716.7	718.4	720.1	721.8	722.7	724.0	726.5	729.1	731.6	734.2
117.5°	794.3	796.3	798.3	800.3	802.3	803.3	804.0	805.4	806.9	808.3	809.7
120°	867.2	869.8	872.3	874.9	877.4	878.7	879.1	880.0	880.9	881.7	882.6
122.5°	941.4	943.4	945.4	947.4	949.4	950.4	951.0	952.1	953.2	954.4	955.5
125°	1007.9	1010.2	1012.4	1014.7	1017.0	1018.1	1018.7	1019.8	1021.0	1022.1	1023.3
127.5°	1074.4	1076.7	1079.0	1081.3	1083.6	1084.7	1085.4	1086.8	1088.3	1089.7	1091.1
130°	1135.8	1138.1	1140.4	1142.7	1145.0	1146.1	1146.7	1147.8	1148.9	1150.1	1151.2
132.5°	1194.7	1197.0	1199.2	1201.5	1203.8	1204.9	1205.3	1206.2	1207.0	1207.9	1208.7
135°	1254.8	1256.5	1258.2	1259.9	1261.6	1262.4	1263.0	1264.1	1265.3	1266.4	1267.6
137.5°	1305.9	1308.2	1310.5	1312.8	1315.1	1316.2	1316.5	1317.0	1317.6	1318.1	1318.7
140°	1357.1	1358.8	1360.5	1362.2	1363.9	1364.8	1365.2	1366.1	1366.9	1367.8	1368.6
142.5°	1404.4	1406.1	1407.8	1409.5	1411.2	1412.1	1412.5	1413.4	1414.2	1415.1	1415.9
145°	1447.9	1449.9	1451.9	1453.9	1455.9	1456.9	1457.2	1457.7	1458.3	1458.8	1459.4
147.5°	1490.1	1491.5	1492.9	1494.4	1495.8	1496.5	1496.8	1497.4	1497.9	1498.5	1499.1
150°	1528.5	1529.3	1530.2	1531.0	1531.9	1532.3	1532.6	1533.2	1533.7	1534.3	1534.9
152.5°	1563.0	1563.3	1563.6	1563.9	1564.2	1564.3	1564.4	1564.7	1565.0	1565.3	1565.6
155°	1595.0	1594.4	1593.9	1593.3	1592.8	1592.5	1592.6	1592.9	1593.2	1593.4	1593.7
157.5°	1620.6	1620.6	1620.6	1620.6	1620.6	1620.6	1620.5	1620.2	1619.9	1619.6	1619.3
160°	1643.6	1643.3	1643.0	1642.7	1642.4	1642.3	1642.2	1641.9	1641.6	1641.4	1641.1
162.5°	1665.4	1664.5	1663.7	1662.8	1661.9	1661.5	1661.4	1661.1	1660.8	1660.5	1660.2
165°	1682.0	1681.2	1680.3	1679.5	1678.6	1678.2	1678.1	1677.8	1677.5	1677.2	1676.9
167.5°	1696.1	1694.9	1693.8	1692.6	1691.5	1690.9	1690.9	1690.9	1690.9	1690.9	1690.9
170°	1707.6	1706.5	1705.3	1704.2	1703.1	1702.5	1702.5	1702.5	1702.5	1702.5	1702.5
172.5°	1715.2	1713.8	1712.4	1710.9	1709.5	1708.8	1708.9	1709.2	1709.5	1709.8	1710.1
175°	1721.6	1720.2	1718.8	1717.3	1715.9	1715.2	1715.3	1715.6	1715.9	1716.2	1716.5
177.5°	1724.2	1722.8	1721.4	1719.9	1718.5	1717.8	1717.9	1718.2	1718.5	1718.8	1719.1
180°	1721.6	1721.6	1721.6	1721.6	1721.6	1721.6	1721.6	1721.6	1721.6	1721.6	1721.6

TEST NUMBER: P1031885

CATALOG NUMBER: S123DIW-B775D1320UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1
2.5°	1137.7	1139.8	1147.1	1152.3	1162.8	1161.8	1161.8	1160.7	1157.6	1162.8	1166.0
5°	1217.2	1235.0	1237.1	1260.1	1261.2	1270.6	1276.9	1271.7	1284.2	1283.2	1273.8
7.5°	1315.6	1339.7	1351.2	1373.2	1398.3	1392.0	1416.1	1420.3	1418.2	1428.7	1436.0
10°	1423.4	1465.3	1494.6	1535.4	1545.9	1552.2	1567.9	1581.5	1608.7	1587.7	1601.4
12.5°	1546.9	1577.3	1616.0	1680.9	1713.3	1734.3	1741.6	1751.0	1769.9	1758.3	1759.4
15°	1650.5	1691.4	1757.3	1837.9	1847.3	1873.5	1867.2	1923.7	1950.9	1910.1	1933.1
17.5°	1758.3	1812.8	1891.3	1961.4	2001.2	2019.0	2035.7	2090.1	2088.0	2081.8	2087.0
20°	1827.4	1916.4	2013.7	2106.9	2118.4	2132.0	2177.0	2200.0	2195.8	2213.6	2225.1
22.5°	1924.8	2019.0	2122.6	2184.3	2210.5	2226.2	2261.8	2276.4	2282.7	2286.9	2279.6
25°	2006.4	2106.9	2183.3	2237.7	2253.4	2261.8	2273.3	2277.5	2274.3	2267.0	2273.3
27.5°	2061.9	2142.5	2194.8	2219.9	2211.5	2197.9	2176.0	2161.3	2128.9	2113.2	2132.0
30°	2084.9	2120.5	2136.2	2094.3	2052.5	2019.0	1977.1	1899.6	1838.9	1856.7	1832.7
32.5°	2048.3	2025.2	1949.9	1842.1	1809.6	1755.2	1636.9	1545.9	1549.0	1500.9	1520.8
35°	1940.5	1835.8	1693.5	1530.2	1487.3	1458.0	1328.2	1308.3	1266.4	1221.4	1234.0
37.5°	1750.0	1597.2	1424.5	1304.1	1240.3	1176.4	1103.2	1059.2	1034.1	1015.2	1029.9
40°	1517.6	1331.3	1189.0	1081.2	1026.7	985.9	935.7	891.7	863.5	860.3	865.6
42.5°	1289.5	1132.5	1001.6	899.1	881.3	833.1	800.7	766.1	757.8	744.2	751.5
45°	1091.6	964.0	856.1	772.4	751.5	738.9	699.2	677.2	667.8	659.4	671.9
47.5°	948.3	814.3	735.8	685.5	664.6	643.7	621.7	607.0	599.7	600.8	599.7
50°	810.1	711.7	642.6	603.9	591.3	576.7	558.9	549.5	546.3	536.9	544.3
52.5°	697.1	625.9	577.7	541.1	531.7	521.2	506.6	501.3	494.0	491.9	491.9
55°	606.0	550.5	511.8	487.7	476.2	467.8	459.5	453.2	448.0	448.0	448.0
57.5°	534.8	486.7	458.4	437.5	433.3	424.9	415.5	415.5	408.2	407.1	410.3
60°	474.1	431.2	409.2	391.4	385.2	383.1	373.6	373.6	371.6	366.3	370.5
62.5°	412.4	381.0	362.1	348.5	342.2	342.2	334.9	329.7	329.7	330.7	328.6
65°	355.9	332.8	316.1	305.6	302.5	298.3	297.2	293.1	289.9	291.0	289.9
67.5°	305.6	287.8	276.3	267.9	262.7	260.6	257.5	257.5	255.4	256.4	251.2
70°	260.6	242.8	233.4	225.0	222.9	222.9	218.7	219.8	217.7	220.8	218.7
72.5°	214.6	201.0	193.6	190.5	188.4	187.3	185.3	183.2	182.1	184.2	183.2
75°	173.7	162.2	157.0	154.9	152.8	152.8	151.8	150.7	149.7	149.7	149.7
77.5°	135.0	127.7	121.4	123.5	120.4	121.4	118.3	118.3	119.3	118.3	118.3
80°	99.4	94.2	94.2	92.1	87.9	90.0	90.0	86.9	85.8	87.9	84.8
82.5°	65.9	64.9	62.8	61.8	59.7	60.7	59.7	58.6	57.6	59.7	57.6
85°	38.7	38.7	37.7	35.6	37.7	36.6	35.6	35.6	34.5	34.5	34.5
87.5°	19.9	17.8	17.8	16.7	17.8	15.7	16.7	15.7	14.7	15.7	14.7
90°	31.8	33.0	34.1	35.2	35.8	36.1	36.7	37.2	37.8	38.4	37.8
92.5°	35.3	37.3	39.2	41.2	42.2	42.3	42.6	42.9	43.2	43.5	43.2
95°	41.7	43.7	45.6	47.6	48.6	48.6	48.6	48.6	48.6	48.6	48.6
97.5°	43.2	45.5	47.8	50.1	51.2	51.3	51.6	51.9	52.1	52.4	52.1
100°	44.5	46.7	49.0	51.3	52.4	52.5	52.8	53.1	53.4	53.7	53.4
102.5°	85.3	75.9	66.5	57.1	52.4	52.7	53.3	53.8	54.4	55.0	54.4
105°	229.8	179.5	129.2	78.9	53.7	54.0	54.6	55.1	55.7	56.3	55.7
107.5°	453.8	410.0	366.3	322.5	300.6	282.0	244.7	207.5	170.2	133.0	170.2
110°	567.5	558.1	548.8	539.4	534.7	514.4	473.7	433.0	392.4	351.7	392.4

TEST NUMBER: P1031885

CATALOG NUMBER: S123DIW-B775D1320UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	660.0	662.6	665.1	667.7	669.0	668.7	668.1	667.6	667.0	666.4	667.0
115°	737.0	739.9	742.7	745.6	747.0	747.6	748.7	749.8	751.0	752.1	751.0
117.5°	812.0	814.2	816.5	818.8	819.9	820.0	820.3	820.6	820.9	821.2	820.9
120°	884.9	887.1	889.4	891.7	892.8	892.8	892.8	892.8	892.8	892.8	892.8
122.5°	956.9	958.3	959.8	961.2	961.9	962.0	962.3	962.6	962.8	963.1	962.8
125°	1023.9	1024.4	1025.0	1025.5	1025.8	1026.1	1026.7	1027.2	1027.8	1028.4	1027.8
127.5°	1091.9	1092.8	1093.6	1094.5	1094.9	1094.6	1094.0	1093.5	1092.9	1092.3	1092.9
130°	1152.3	1153.5	1154.6	1155.7	1156.3	1156.0	1155.4	1154.9	1154.3	1153.7	1154.3
132.5°	1209.8	1211.0	1212.1	1213.2	1213.8	1213.4	1212.5	1211.7	1210.8	1210.0	1210.8
135°	1268.4	1269.3	1270.1	1271.0	1271.4	1271.0	1270.1	1269.3	1268.4	1267.6	1268.4
137.5°	1320.1	1321.5	1323.0	1324.4	1325.1	1324.8	1324.3	1323.7	1323.2	1322.6	1323.2
140°	1369.7	1370.9	1372.0	1373.1	1373.7	1373.4	1372.9	1372.3	1371.8	1371.2	1371.8
142.5°	1416.8	1417.6	1418.5	1419.4	1419.8	1419.4	1418.5	1417.6	1416.8	1415.9	1416.8
145°	1460.0	1460.6	1461.1	1461.7	1462.0	1462.0	1462.0	1462.0	1462.0	1462.0	1462.0
147.5°	1499.7	1500.2	1500.8	1501.3	1501.6	1500.9	1499.5	1498.0	1496.6	1495.2	1496.6
150°	1535.5	1536.1	1536.6	1537.2	1537.5	1537.1	1536.2	1535.3	1534.5	1533.6	1534.5
152.5°	1566.7	1567.9	1569.0	1570.1	1570.7	1570.0	1568.6	1567.1	1565.7	1564.3	1565.7
155°	1595.1	1596.5	1598.0	1599.4	1600.1	1599.3	1597.6	1595.9	1594.2	1592.5	1594.2
157.5°	1621.0	1622.7	1624.4	1626.1	1627.0	1625.9	1623.6	1621.3	1619.1	1616.8	1619.1
160°	1642.8	1644.5	1646.2	1647.9	1648.7	1647.7	1645.7	1643.8	1641.8	1639.8	1641.8
162.5°	1662.2	1664.2	1666.2	1668.2	1669.2	1668.3	1666.6	1664.9	1663.2	1661.5	1663.2
165°	1679.2	1681.4	1683.7	1686.0	1687.1	1686.1	1684.1	1682.2	1680.2	1678.2	1680.2
167.5°	1693.2	1695.5	1697.8	1700.1	1701.2	1700.1	1697.8	1695.5	1693.2	1690.9	1693.2
170°	1704.8	1707.0	1709.3	1711.6	1712.7	1711.6	1709.3	1707.0	1704.8	1702.5	1704.8
172.5°	1712.4	1714.7	1717.0	1719.3	1720.4	1719.1	1716.5	1714.0	1711.4	1708.8	1711.4
175°	1718.5	1720.5	1722.5	1724.5	1725.5	1724.4	1722.1	1719.8	1717.5	1715.2	1717.5
177.5°	1721.4	1723.6	1725.9	1728.2	1729.3	1727.9	1725.0	1722.2	1719.3	1716.5	1719.3
180°	1721.6	1721.6	1721.6	1721.6	1721.6	1721.6	1721.6	1721.6	1721.6	1721.6	1721.6

TEST NUMBER: P1031885

CATALOG NUMBER: S123DIW-B775D1320UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1
2.5°	1157.6	1160.7	1152.3	1150.3	1150.3	1154.4	1151.3	1123.0	1128.3	1122.0	1119.9
5°	1285.3	1279.0	1270.6	1266.4	1261.2	1246.5	1245.5	1213.1	1206.8	1185.8	1176.4
7.5°	1425.5	1420.3	1395.2	1392.0	1389.9	1376.3	1341.8	1307.2	1282.1	1258.1	1235.0
10°	1585.7	1570.0	1558.4	1535.4	1523.9	1505.1	1460.1	1427.6	1384.7	1348.1	1299.9
12.5°	1778.2	1760.4	1721.7	1705.0	1690.3	1638.0	1593.0	1556.3	1472.6	1447.5	1387.8
15°	1919.5	1881.9	1877.7	1841.0	1838.9	1781.4	1695.5	1655.8	1590.9	1498.8	1437.0
17.5°	2072.3	2038.8	2012.7	1968.7	1962.4	1908.0	1845.2	1747.9	1676.7	1588.8	1510.3
20°	2184.3	2166.5	2121.5	2103.7	2067.1	2021.1	1956.2	1835.8	1748.9	1661.0	1564.7
22.5°	2273.3	2255.5	2219.9	2195.8	2174.9	2115.3	2037.8	1935.2	1815.9	1700.8	1601.4
25°	2272.2	2267.0	2252.4	2240.8	2225.1	2181.2	2116.3	2017.9	1885.0	1758.3	1620.2
27.5°	2143.5	2158.2	2183.3	2195.8	2192.7	2186.4	2149.8	2067.1	1947.8	1797.1	1642.2
30°	1875.6	1928.9	1976.0	2038.8	2057.7	2103.7	2124.7	2077.6	1982.3	1842.1	1670.4
32.5°	1555.3	1632.8	1735.3	1769.9	1829.5	1918.5	2017.9	2035.7	1976.0	1868.2	1688.2
35°	1275.8	1339.7	1419.2	1473.7	1527.0	1671.5	1797.1	1905.9	1925.8	1854.6	1684.0
37.5°	1056.1	1101.1	1171.2	1217.2	1266.4	1389.9	1565.8	1707.1	1806.5	1808.6	1672.5
40°	897.0	916.9	977.6	1011.1	1058.1	1164.9	1321.9	1506.1	1651.6	1718.6	1642.2
42.5°	759.9	786.0	836.3	861.4	891.7	984.9	1088.5	1263.3	1443.3	1586.7	1585.7
45°	678.2	697.1	720.1	741.0	775.6	831.0	949.3	1080.1	1252.8	1415.1	1478.9
47.5°	606.0	623.8	646.8	653.1	676.1	728.5	800.7	914.8	1075.9	1237.1	1357.5
50°	545.3	560.0	575.6	587.2	597.6	640.5	695.0	791.3	920.0	1075.9	1225.6
52.5°	498.2	508.7	522.3	528.6	538.0	569.4	611.2	682.4	788.1	930.5	1075.9
55°	454.2	461.6	469.9	480.4	484.6	507.6	540.1	600.8	679.3	807.0	945.1
57.5°	413.4	416.6	421.8	428.1	433.3	453.2	481.5	522.3	591.3	689.7	820.6
60°	367.4	375.7	378.9	385.2	388.3	404.0	426.0	460.5	513.9	598.7	697.1
62.5°	328.6	333.9	339.1	342.2	349.6	354.8	372.6	404.0	448.0	510.8	599.7
65°	294.1	296.2	299.3	302.5	304.6	310.9	327.6	348.5	382.0	437.5	506.6
67.5°	254.3	256.4	260.6	261.7	263.8	272.1	281.5	299.3	327.6	369.5	426.0
70°	215.6	218.7	220.8	222.9	226.1	229.2	239.7	254.3	276.3	305.6	349.6
72.5°	182.1	185.3	185.3	187.3	186.3	190.5	201.0	211.4	226.1	250.1	288.9
75°	148.6	148.6	150.7	151.8	152.8	157.0	161.2	169.6	181.1	199.9	224.0
77.5°	117.2	116.2	118.3	118.3	118.3	121.4	125.6	129.8	137.1	150.7	169.6
80°	85.8	85.8	87.9	89.0	86.9	87.9	90.0	94.2	99.4	108.9	119.3
82.5°	56.5	60.7	59.7	60.7	59.7	61.8	62.8	63.8	65.9	70.1	77.5
85°	34.5	34.5	34.5	35.6	34.5	35.6	35.6	35.6	36.6	38.7	41.9
87.5°	14.7	14.7	14.7	15.7	14.7	14.7	15.7	14.7	15.7	15.7	16.7
90°	37.2	36.7	36.1	35.8	35.2	34.1	33.0	31.8	30.7	27.0	23.3
92.5°	42.9	42.6	42.3	42.2	41.2	39.2	37.3	35.3	33.3	30.7	28.1
95°	48.6	48.6	48.6	48.6	47.6	45.6	43.7	41.7	39.7	36.6	33.4
97.5°	51.9	51.6	51.3	51.2	50.1	47.8	45.5	43.2	40.9	55.4	69.9
100°	53.1	52.8	52.5	52.4	51.3	49.0	46.7	44.5	42.2	86.5	130.9
102.5°	53.8	53.3	52.7	52.4	57.1	66.5	75.9	85.3	94.7	144.1	193.6
105°	55.1	54.6	54.0	53.7	78.9	129.2	179.5	229.8	280.1	305.7	331.3
107.5°	207.5	244.7	282.0	300.6	322.5	366.3	410.0	453.8	497.6	493.3	489.1
110°	433.0	473.7	514.4	534.7	539.4	548.8	558.1	567.5	576.9	573.8	570.6

TEST NUMBER: P1031885

CATALOG NUMBER: S123DIW-B775D1320UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	667.6	668.1	668.7	669.0	667.7	665.1	662.6	660.0	657.4	654.3	651.2
115°	749.8	748.7	747.6	747.0	745.6	742.7	739.9	737.0	734.2	731.6	729.1
117.5°	820.6	820.3	820.0	819.9	818.8	816.5	814.2	812.0	809.7	808.3	806.9
120°	892.8	892.8	892.8	892.8	891.7	889.4	887.1	884.9	882.6	881.7	880.9
122.5°	962.6	962.3	962.0	961.9	961.2	959.8	958.3	956.9	955.5	954.4	953.2
125°	1027.2	1026.7	1026.1	1025.8	1025.5	1025.0	1024.4	1023.9	1023.3	1022.1	1021.0
127.5°	1093.5	1094.0	1094.6	1094.9	1094.5	1093.6	1092.8	1091.9	1091.1	1089.7	1088.3
130°	1154.9	1155.4	1156.0	1156.3	1155.7	1154.6	1153.5	1152.3	1151.2	1150.1	1148.9
132.5°	1211.7	1212.5	1213.4	1213.8	1213.2	1212.1	1211.0	1209.8	1208.7	1207.9	1207.0
135°	1269.3	1270.1	1271.0	1271.4	1271.0	1270.1	1269.3	1268.4	1267.6	1266.4	1265.3
137.5°	1323.7	1324.3	1324.8	1325.1	1324.4	1323.0	1321.5	1320.1	1318.7	1318.1	1317.6
140°	1372.3	1372.9	1373.4	1373.7	1373.1	1372.0	1370.9	1369.7	1368.6	1367.8	1366.9
142.5°	1417.6	1418.5	1419.4	1419.8	1419.4	1418.5	1417.6	1416.8	1415.9	1415.1	1414.2
145°	1462.0	1462.0	1462.0	1462.0	1461.7	1461.1	1460.6	1460.0	1459.4	1458.8	1458.3
147.5°	1498.0	1499.5	1500.9	1501.6	1501.3	1500.8	1500.2	1499.7	1499.1	1498.5	1497.9
150°	1535.3	1536.2	1537.1	1537.5	1537.2	1536.6	1536.1	1535.5	1534.9	1534.3	1533.7
152.5°	1567.1	1568.6	1570.0	1570.7	1570.1	1569.0	1567.9	1566.7	1565.6	1565.3	1565.0
155°	1595.9	1597.6	1599.3	1600.1	1599.4	1598.0	1596.5	1595.1	1593.7	1593.4	1593.2
157.5°	1621.3	1623.6	1625.9	1627.0	1626.1	1624.4	1622.7	1621.0	1619.3	1619.6	1619.9
160°	1643.8	1645.7	1647.7	1648.7	1647.9	1646.2	1644.5	1642.8	1641.1	1641.4	1641.6
162.5°	1664.9	1666.6	1668.3	1669.2	1668.2	1666.2	1664.2	1662.2	1660.2	1660.5	1660.8
165°	1682.2	1684.1	1686.1	1687.1	1686.0	1683.7	1681.4	1679.2	1676.9	1677.2	1677.5
167.5°	1695.5	1697.8	1700.1	1701.2	1700.1	1697.8	1695.5	1693.2	1690.9	1690.9	1690.9
170°	1707.0	1709.3	1711.6	1712.7	1711.6	1709.3	1707.0	1704.8	1702.5	1702.5	1702.5
172.5°	1714.0	1716.5	1719.1	1720.4	1719.3	1717.0	1714.7	1712.4	1710.1	1709.8	1709.5
175°	1719.8	1722.1	1724.4	1725.5	1724.5	1722.5	1720.5	1718.5	1716.5	1716.2	1715.9
177.5°	1722.2	1725.0	1727.9	1729.3	1728.2	1725.9	1723.6	1721.4	1719.1	1718.8	1718.5
180°	1721.6	1721.6	1721.6	1721.6	1721.6	1721.6	1721.6	1721.6	1721.6	1721.6	1721.6

TEST NUMBER: P1031885

CATALOG NUMBER: S123DIW-B775D1320UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1
2.5°	1109.4	1106.3	1106.3	1104.2	1097.9	1086.4	1085.4	1087.5	1081.2	1074.9	1065.5
5°	1163.9	1144.0	1137.7	1131.4	1118.9	1097.9	1089.5	1082.2	1070.7	1057.1	1042.4
7.5°	1209.9	1181.7	1173.3	1161.8	1136.6	1107.3	1088.5	1072.8	1057.1	1038.3	1020.5
10°	1267.5	1226.7	1206.8	1190.0	1155.5	1114.7	1086.4	1063.4	1038.3	1015.2	992.2
12.5°	1332.4	1266.4	1260.1	1219.3	1179.6	1118.9	1084.3	1050.8	1017.3	989.1	965.0
15°	1386.8	1314.6	1288.4	1261.2	1184.8	1109.4	1075.9	1038.3	999.5	969.2	933.6
17.5°	1421.3	1361.7	1306.2	1269.6	1190.0	1123.0	1058.1	1015.2	974.4	932.6	903.2
20°	1463.2	1376.3	1328.2	1279.0	1200.5	1112.6	1047.7	994.3	944.1	906.4	870.8
22.5°	1505.1	1387.8	1348.1	1294.7	1202.6	1102.1	1028.8	975.5	917.9	880.2	841.5
25°	1500.9	1404.6	1338.6	1293.6	1181.7	1092.7	1006.9	944.1	890.7	842.5	803.8
27.5°	1504.0	1385.7	1318.8	1266.4	1167.0	1079.1	983.8	917.9	862.4	812.2	771.4
30°	1505.1	1357.5	1298.9	1236.1	1139.8	1046.6	957.7	890.7	832.1	777.7	741.0
32.5°	1501.9	1334.5	1261.2	1204.7	1096.9	1015.2	927.3	856.1	796.5	746.3	711.7
35°	1494.6	1307.2	1222.5	1151.3	1052.9	970.2	899.1	825.8	762.0	715.9	676.1
37.5°	1474.7	1277.9	1181.7	1111.5	1001.6	917.9	855.1	794.4	732.6	678.2	644.7
40°	1460.1	1238.2	1140.8	1064.4	946.2	864.5	812.2	754.6	693.9	644.7	612.3
42.5°	1426.6	1200.5	1099.0	1007.9	891.7	808.0	758.8	712.8	660.4	612.3	583.0
45°	1372.1	1159.7	1047.7	955.6	832.1	752.5	707.5	669.8	623.8	577.7	548.4
47.5°	1295.7	1101.1	993.3	901.2	773.5	692.9	647.9	619.6	583.0	544.3	519.1
50°	1213.1	1037.2	937.8	846.7	716.9	638.4	594.5	568.3	544.3	508.7	484.6
52.5°	1105.2	969.2	873.9	787.1	656.2	580.9	542.2	523.3	498.2	473.1	452.1
55°	1000.6	881.3	802.8	720.1	596.6	526.5	488.8	468.9	454.2	433.3	416.6
57.5°	879.2	799.6	727.4	652.1	541.1	477.3	441.7	417.6	408.2	398.8	383.1
60°	767.2	706.5	647.9	585.1	483.5	426.0	391.4	372.6	363.2	356.9	346.4
62.5°	664.6	617.5	567.3	517.0	424.9	372.6	346.4	327.6	319.2	318.2	308.8
65°	566.2	532.7	491.9	442.7	370.5	324.5	299.3	287.8	278.4	278.4	271.1
67.5°	467.8	444.8	412.4	377.8	321.3	278.4	255.4	244.9	239.7	239.7	234.4
70°	389.3	373.6	344.3	314.0	264.8	232.4	214.6	205.1	202.0	203.0	198.9
72.5°	316.1	299.3	275.3	253.3	216.7	192.6	180.0	169.6	164.3	165.4	164.3
75°	244.9	236.5	215.6	198.9	169.6	152.8	141.3	136.1	131.9	132.9	130.8
77.5°	184.2	171.6	160.1	148.6	130.8	117.2	107.8	102.6	99.4	99.4	99.4
80°	125.6	123.5	114.1	107.8	93.2	82.7	75.4	74.3	71.2	71.2	71.2
82.5°	81.6	76.4	71.2	67.0	58.6	52.3	49.2	47.1	46.1	45.0	47.1
85°	45.0	41.9	39.8	35.6	32.4	29.3	26.2	25.1	24.1	25.1	24.1
87.5°	17.8	14.7	14.7	13.6	12.6	11.5	11.5	9.4	9.4	8.4	8.4
90°	19.6	15.9	14.1	12.7	9.8	7.0	4.1	1.3	4.1	7.0	9.8
92.5°	25.6	23.0	21.7	22.6	24.3	26.0	27.7	29.4	27.7	26.0	24.3
95°	30.3	27.2	25.6	31.4	43.1	54.7	66.4	78.0	66.4	54.7	43.1
97.5°	84.4	98.9	106.2	110.2	118.1	126.1	134.0	142.0	134.0	126.1	118.1
100°	175.2	219.5	241.7	238.9	233.2	227.5	221.9	216.2	221.9	227.5	233.2
102.5°	243.0	292.5	317.2	315.4	311.7	308.0	304.3	300.6	304.3	308.0	311.7
105°	356.8	382.4	395.2	393.6	390.5	387.4	384.3	381.2	384.3	387.4	390.5
107.5°	484.8	480.5	478.4	477.1	474.6	472.0	469.5	466.9	469.5	472.0	474.6
110°	567.5	564.4	562.8	561.7	559.4	557.1	554.9	552.6	554.9	557.1	559.4

TEST NUMBER: P1031885

CATALOG NUMBER: S123DIW-B775D1320UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	648.1	645.0	643.4	642.4	640.4	638.4	636.4	634.4	636.4	638.4	640.4
115°	726.5	724.0	722.7	721.8	720.1	718.4	716.7	715.0	716.7	718.4	720.1
117.5°	805.4	804.0	803.3	802.3	800.3	798.3	796.3	794.3	796.3	798.3	800.3
120°	880.0	879.1	878.7	877.4	874.9	872.3	869.8	867.2	869.8	872.3	874.9
122.5°	952.1	951.0	950.4	949.4	947.4	945.4	943.4	941.4	943.4	945.4	947.4
125°	1019.8	1018.7	1018.1	1017.0	1014.7	1012.4	1010.2	1007.9	1010.2	1012.4	1014.7
127.5°	1086.8	1085.4	1084.7	1083.6	1081.3	1079.0	1076.7	1074.4	1076.7	1079.0	1081.3
130°	1147.8	1146.7	1146.1	1145.0	1142.7	1140.4	1138.1	1135.8	1138.1	1140.4	1142.7
132.5°	1206.2	1205.3	1204.9	1203.8	1201.5	1199.2	1197.0	1194.7	1197.0	1199.2	1201.5
135°	1264.1	1263.0	1262.4	1261.6	1259.9	1258.2	1256.5	1254.8	1256.5	1258.2	1259.9
137.5°	1317.0	1316.5	1316.2	1315.1	1312.8	1310.5	1308.2	1305.9	1308.2	1310.5	1312.8
140°	1366.1	1365.2	1364.8	1363.9	1362.2	1360.5	1358.8	1357.1	1358.8	1360.5	1362.2
142.5°	1413.4	1412.5	1412.1	1411.2	1409.5	1407.8	1406.1	1404.4	1406.1	1407.8	1409.5
145°	1457.7	1457.2	1456.9	1455.9	1453.9	1451.9	1449.9	1447.9	1449.9	1451.9	1453.9
147.5°	1497.4	1496.8	1496.5	1495.8	1494.4	1492.9	1491.5	1490.1	1491.5	1492.9	1494.4
150°	1533.2	1532.6	1532.3	1531.9	1531.0	1530.2	1529.3	1528.5	1529.3	1530.2	1531.0
152.5°	1564.7	1564.4	1564.3	1564.2	1563.9	1563.6	1563.3	1563.0	1563.3	1563.6	1563.9
155°	1592.9	1592.6	1592.5	1592.8	1593.3	1593.9	1594.4	1595.0	1594.4	1593.9	1593.3
157.5°	1620.2	1620.5	1620.6	1620.6	1620.6	1620.6	1620.6	1620.6	1620.6	1620.6	1620.6
160°	1641.9	1642.2	1642.3	1642.4	1642.7	1643.0	1643.3	1643.6	1643.3	1643.0	1642.7
162.5°	1661.1	1661.4	1661.5	1661.9	1662.8	1663.7	1664.5	1665.4	1664.5	1663.7	1662.8
165°	1677.8	1678.1	1678.2	1678.6	1679.5	1680.3	1681.2	1682.0	1681.2	1680.3	1679.5
167.5°	1690.9	1690.9	1690.9	1691.5	1692.6	1693.8	1694.9	1696.1	1694.9	1693.8	1692.6
170°	1702.5	1702.5	1702.5	1703.1	1704.2	1705.3	1706.5	1707.6	1706.5	1705.3	1704.2
172.5°	1709.2	1708.9	1708.8	1709.5	1710.9	1712.4	1713.8	1715.2	1713.8	1712.4	1710.9
175°	1715.6	1715.3	1715.2	1715.9	1717.3	1718.8	1720.2	1721.6	1720.2	1718.8	1717.3
177.5°	1718.2	1717.9	1717.8	1718.5	1719.9	1721.4	1722.8	1724.2	1722.8	1721.4	1719.9
180°	1721.6	1721.6	1721.6	1721.6	1721.6	1721.6	1721.6	1721.6	1721.6	1721.6	1721.6

TEST NUMBER: P1031885

CATALOG NUMBER: S123DIW-B775D1320UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1
2.5°	1063.4	1062.3	1064.4	1058.1	1047.7	1042.4	1027.8	1024.7	1023.6	1024.7	1025.7
5°	1034.1	1033.0	1029.9	1019.4	1006.9	997.4	979.7	978.6	972.3	966.0	969.2
7.5°	1005.8	1001.6	995.4	981.7	965.0	954.5	939.9	929.4	921.0	915.8	911.6
10°	977.6	971.3	965.0	947.2	926.3	910.6	892.8	884.4	875.0	870.8	866.6
12.5°	940.9	934.6	923.1	902.2	889.6	869.8	852.0	843.6	838.4	830.0	824.7
15°	911.6	899.1	892.8	870.8	844.6	842.5	810.1	808.0	797.5	797.5	789.2
17.5°	878.1	868.7	857.2	835.2	816.4	797.5	780.8	774.5	765.1	763.0	758.8
20°	845.7	833.1	828.9	807.0	787.1	764.0	746.3	740.0	735.8	731.6	734.7
22.5°	812.2	801.7	791.3	771.4	756.7	733.7	723.2	716.9	710.7	708.6	709.6
25°	779.7	770.3	759.9	740.0	724.3	705.4	696.0	692.9	689.7	689.7	688.7
27.5°	748.3	738.9	729.5	711.7	696.0	682.4	675.1	671.9	668.8	670.9	673.0
30°	715.9	707.5	699.2	683.5	670.9	658.3	654.1	652.1	651.0	656.2	656.2
32.5°	686.6	679.3	673.0	658.3	645.8	635.3	632.2	633.2	634.3	637.4	639.5
35°	656.2	651.0	644.7	632.2	621.7	612.3	613.3	613.3	615.4	620.7	624.8
37.5°	629.0	621.7	616.5	606.0	597.6	589.3	592.4	595.5	597.6	603.9	606.0
40°	596.6	593.4	589.3	578.8	571.5	570.4	571.5	573.6	577.7	580.9	584.0
42.5°	570.4	566.2	561.0	552.6	546.3	547.4	548.4	550.5	552.6	557.9	561.0
45°	541.1	538.0	533.8	526.5	521.2	522.3	523.3	523.3	525.4	531.7	533.8
47.5°	508.7	509.7	504.5	497.2	494.0	494.0	494.0	496.1	501.3	503.4	504.5
50°	477.3	475.2	474.1	466.8	464.7	463.7	464.7	465.8	473.1	472.0	475.2
52.5°	443.8	443.8	442.7	438.5	435.4	435.4	433.3	438.5	440.6	442.7	445.9
55°	411.3	408.2	407.1	405.0	400.9	399.8	401.9	408.2	410.3	412.4	415.5
57.5°	375.7	375.7	373.6	370.5	370.5	370.5	370.5	374.7	377.8	379.9	386.2
60°	343.3	339.1	336.0	336.0	336.0	334.9	341.2	341.2	347.5	348.5	350.6
62.5°	304.6	302.5	300.4	301.4	300.4	302.5	304.6	308.8	309.8	312.9	316.1
65°	267.9	267.9	265.8	272.1	267.9	267.9	273.2	273.2	275.3	278.4	282.6
67.5°	232.4	233.4	231.3	231.3	233.4	234.4	235.5	239.7	240.7	244.9	250.1
70°	195.7	197.8	198.9	196.8	198.9	201.0	203.0	204.1	208.3	210.4	213.5
72.5°	163.3	165.4	162.2	163.3	164.3	166.4	167.5	169.6	171.6	177.9	180.0
75°	130.8	129.8	128.7	132.9	130.8	135.0	136.1	136.1	138.2	143.4	145.5
77.5°	100.5	100.5	101.5	99.4	102.6	101.5	102.6	105.7	108.9	108.9	117.2
80°	70.1	72.2	72.2	72.2	73.3	74.3	72.2	77.5	78.5	78.5	81.6
82.5°	45.0	46.1	45.0	47.1	47.1	49.2	48.1	49.2	51.3	53.4	54.4
85°	24.1	24.1	26.2	26.2	25.1	26.2	25.1	26.2	28.3	28.3	29.3
87.5°	8.4	8.4	8.4	8.4	9.4	8.4	9.4	9.4	8.4	8.4	11.5
90°	12.7	14.1	15.9	19.6	23.3	27.0	30.7	31.8	33.0	34.1	35.2
92.5°	22.6	21.7	23.0	25.6	28.1	30.7	33.3	35.3	37.3	39.2	41.2
95°	31.4	25.6	27.2	30.3	33.4	36.6	39.7	41.7	43.7	45.6	47.6
97.5°	110.2	106.2	98.9	84.4	69.9	55.4	40.9	43.2	45.5	47.8	50.1
100°	238.9	241.7	219.5	175.2	130.9	86.5	42.2	44.5	46.7	49.0	51.3
102.5°	315.4	317.2	292.5	243.0	193.6	144.1	94.7	85.3	75.9	66.5	57.1
105°	393.6	395.2	382.4	356.8	331.3	305.7	280.1	229.8	179.5	129.2	78.9
107.5°	477.1	478.4	480.5	484.8	489.1	493.3	497.6	453.8	410.0	366.3	322.5
110°	561.7	562.8	564.4	567.5	570.6	573.8	576.9	567.5	558.1	548.8	539.4

TEST NUMBER: P1031885

CATALOG NUMBER: S123DIW-B775D1320UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	642.4	643.4	645.0	648.1	651.2	654.3	657.4	660.0	662.6	665.1	667.7
115°	721.8	722.7	724.0	726.5	729.1	731.6	734.2	737.0	739.9	742.7	745.6
117.5°	802.3	803.3	804.0	805.4	806.9	808.3	809.7	812.0	814.2	816.5	818.8
120°	877.4	878.7	879.1	880.0	880.9	881.7	882.6	884.9	887.1	889.4	891.7
122.5°	949.4	950.4	951.0	952.1	953.2	954.4	955.5	956.9	958.3	959.8	961.2
125°	1017.0	1018.1	1018.7	1019.8	1021.0	1022.1	1023.3	1023.9	1024.4	1025.0	1025.5
127.5°	1083.6	1084.7	1085.4	1086.8	1088.3	1089.7	1091.1	1091.9	1092.8	1093.6	1094.5
130°	1145.0	1146.1	1146.7	1147.8	1148.9	1150.1	1151.2	1152.3	1153.5	1154.6	1155.7
132.5°	1203.8	1204.9	1205.3	1206.2	1207.0	1207.9	1208.7	1209.8	1211.0	1212.1	1213.2
135°	1261.6	1262.4	1263.0	1264.1	1265.3	1266.4	1267.6	1268.4	1269.3	1270.1	1271.0
137.5°	1315.1	1316.2	1316.5	1317.0	1317.6	1318.1	1318.7	1320.1	1321.5	1323.0	1324.4
140°	1363.9	1364.8	1365.2	1366.1	1366.9	1367.8	1368.6	1369.7	1370.9	1372.0	1373.1
142.5°	1411.2	1412.1	1412.5	1413.4	1414.2	1415.1	1415.9	1416.8	1417.6	1418.5	1419.4
145°	1455.9	1456.9	1457.2	1457.7	1458.3	1458.8	1459.4	1460.0	1460.6	1461.1	1461.7
147.5°	1495.8	1496.5	1496.8	1497.4	1497.9	1498.5	1499.1	1499.7	1500.2	1500.8	1501.3
150°	1531.9	1532.3	1532.6	1533.2	1533.7	1534.3	1534.9	1535.5	1536.1	1536.6	1537.2
152.5°	1564.2	1564.3	1564.4	1564.7	1565.0	1565.3	1565.6	1566.7	1567.9	1569.0	1570.1
155°	1592.8	1592.5	1592.6	1592.9	1593.2	1593.4	1593.7	1595.1	1596.5	1598.0	1599.4
157.5°	1620.6	1620.6	1620.5	1620.2	1619.9	1619.6	1619.3	1621.0	1622.7	1624.4	1626.1
160°	1642.4	1642.3	1642.2	1641.9	1641.6	1641.4	1641.1	1642.8	1644.5	1646.2	1647.9
162.5°	1661.9	1661.5	1661.4	1661.1	1660.8	1660.5	1660.2	1662.2	1664.2	1666.2	1668.2
165°	1678.6	1678.2	1678.1	1677.8	1677.5	1677.2	1676.9	1679.2	1681.4	1683.7	1686.0
167.5°	1691.5	1690.9	1690.9	1690.9	1690.9	1690.9	1690.9	1693.2	1695.5	1697.8	1700.1
170°	1703.1	1702.5	1702.5	1702.5	1702.5	1702.5	1702.5	1704.8	1707.0	1709.3	1711.6
172.5°	1709.5	1708.8	1708.9	1709.2	1709.5	1709.8	1710.1	1712.4	1714.7	1717.0	1719.3
175°	1715.9	1715.2	1715.3	1715.6	1715.9	1716.2	1716.5	1718.5	1720.5	1722.5	1724.5
177.5°	1718.5	1717.8	1717.9	1718.2	1718.5	1718.8	1719.1	1721.4	1723.6	1725.9	1728.2
180°	1721.6	1721.6	1721.6	1721.6	1721.6	1721.6	1721.6	1721.6	1721.6	1721.6	1721.6

TEST NUMBER: P1031885

CATALOG NUMBER: S123DIW-B775D1320UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1
2.5°	1024.7	1025.7	1021.5	1018.4	1026.7	1021.5	1021.5	1022.6	1020.5	1023.6	1022.6
5°	967.1	968.1	960.8	962.9	958.7	957.7	956.6	962.9	961.9	960.8	962.9
7.5°	910.6	910.6	907.4	905.3	905.3	902.2	906.4	905.3	907.4	907.4	910.6
10°	863.5	865.6	860.3	855.1	854.1	855.1	855.1	856.1	857.2	864.5	863.5
12.5°	824.7	821.6	820.6	817.4	812.2	810.1	808.0	819.5	816.4	816.4	816.4
15°	781.8	789.2	788.1	778.7	776.6	780.8	778.7	778.7	789.2	788.1	787.1
17.5°	758.8	756.7	754.6	749.4	750.4	749.4	750.4	750.4	756.7	756.7	756.7
20°	732.6	728.5	728.5	726.4	726.4	723.2	727.4	728.5	732.6	732.6	733.7
22.5°	709.6	706.5	706.5	705.4	707.5	703.3	707.5	708.6	708.6	711.7	711.7
25°	689.7	687.6	687.6	689.7	689.7	689.7	689.7	693.9	690.8	691.8	690.8
27.5°	671.9	673.0	674.0	675.1	674.0	675.1	676.1	678.2	679.3	678.2	676.1
30°	655.2	658.3	659.4	659.4	661.5	662.5	663.6	663.6	664.6	661.5	663.6
32.5°	642.6	642.6	644.7	645.8	647.9	648.9	648.9	651.0	650.0	646.8	647.9
35°	624.8	624.8	629.0	631.1	634.3	633.2	634.3	634.3	635.3	633.2	630.1
37.5°	607.0	609.1	609.1	613.3	614.4	615.4	614.4	616.5	615.4	613.3	612.3
40°	586.1	585.1	586.1	589.3	590.3	590.3	590.3	592.4	592.4	592.4	591.3
42.5°	560.0	563.1	562.0	565.2	564.1	564.1	566.2	568.3	569.4	566.2	567.3
45°	534.8	534.8	536.9	536.9	538.0	538.0	542.2	540.1	542.2	540.1	541.1
47.5°	507.6	508.7	508.7	509.7	511.8	513.9	511.8	512.9	512.9	513.9	511.8
50°	477.3	477.3	479.4	482.5	486.7	484.6	483.5	487.7	484.6	484.6	482.5
52.5°	445.9	449.0	450.1	453.2	456.3	457.4	458.4	456.3	457.4	454.2	455.3
55°	415.5	416.6	420.7	423.9	427.0	427.0	426.0	427.0	428.1	423.9	423.9
57.5°	385.2	388.3	392.5	392.5	396.7	396.7	395.6	395.6	396.7	393.5	392.5
60°	352.7	355.9	361.1	361.1	367.4	368.4	366.3	364.2	364.2	361.1	362.1
62.5°	318.2	321.3	324.5	329.7	333.9	331.8	336.0	331.8	332.8	326.6	326.6
65°	287.8	288.9	294.1	299.3	299.3	301.4	299.3	300.4	297.2	297.2	293.1
67.5°	252.2	252.2	257.5	262.7	267.9	267.9	267.9	264.8	264.8	261.7	261.7
70°	220.8	219.8	225.0	228.2	231.3	232.4	230.3	229.2	227.1	224.0	222.9
72.5°	182.1	184.2	189.4	191.5	196.8	195.7	201.0	194.7	194.7	189.4	188.4
75°	147.6	149.7	154.9	158.0	161.2	161.2	164.3	161.2	157.0	154.9	153.9
77.5°	117.2	116.2	120.4	125.6	126.6	125.6	127.7	126.6	122.5	122.5	120.4
80°	83.7	86.9	91.1	90.0	94.2	93.2	93.2	91.1	91.1	87.9	90.0
82.5°	55.5	58.6	59.7	58.6	59.7	61.8	62.8	61.8	61.8	59.7	60.7
85°	29.3	29.3	31.4	32.4	31.4	31.4	32.4	35.6	33.5	31.4	33.5
87.5°	9.4	8.4	8.4	9.4	8.4	8.4	9.4	9.4	10.5	10.5	10.5
90°	35.8	36.1	36.7	37.2	37.8	38.4	37.8	37.2	36.7	36.1	35.8
92.5°	42.2	42.3	42.6	42.9	43.2	43.5	43.2	42.9	42.6	42.3	42.2
95°	48.6	48.6	48.6	48.6	48.6	48.6	48.6	48.6	48.6	48.6	48.6
97.5°	51.2	51.3	51.6	51.9	52.1	52.4	52.1	51.9	51.6	51.3	51.2
100°	52.4	52.5	52.8	53.1	53.4	53.7	53.4	53.1	52.8	52.5	52.4
102.5°	52.4	52.7	53.3	53.8	54.4	55.0	54.4	53.8	53.3	52.7	52.4
105°	53.7	54.0	54.6	55.1	55.7	56.3	55.7	55.1	54.6	54.0	53.7
107.5°	300.6	282.0	244.7	207.5	170.2	133.0	170.2	207.5	244.7	282.0	300.6
110°	534.7	514.4	473.7	433.0	392.4	351.7	392.4	433.0	473.7	514.4	534.7

TEST NUMBER: P1031885

CATALOG NUMBER: S123DIW-B775D1320UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	669.0	668.7	668.1	667.6	667.0	666.4	667.0	667.6	668.1	668.7	669.0
115°	747.0	747.6	748.7	749.8	751.0	752.1	751.0	749.8	748.7	747.6	747.0
117.5°	819.9	820.0	820.3	820.6	820.9	821.2	820.9	820.6	820.3	820.0	819.9
120°	892.8	892.8	892.8	892.8	892.8	892.8	892.8	892.8	892.8	892.8	892.8
122.5°	961.9	962.0	962.3	962.6	962.8	963.1	962.8	962.6	962.3	962.0	961.9
125°	1025.8	1026.1	1026.7	1027.2	1027.8	1028.4	1027.8	1027.2	1026.7	1026.1	1025.8
127.5°	1094.9	1094.6	1094.0	1093.5	1092.9	1092.3	1092.9	1093.5	1094.0	1094.6	1094.9
130°	1156.3	1156.0	1155.4	1154.9	1154.3	1153.7	1154.3	1154.9	1155.4	1156.0	1156.3
132.5°	1213.8	1213.4	1212.5	1211.7	1210.8	1210.0	1210.8	1211.7	1212.5	1213.4	1213.8
135°	1271.4	1271.0	1270.1	1269.3	1268.4	1267.6	1268.4	1269.3	1270.1	1271.0	1271.4
137.5°	1325.1	1324.8	1324.3	1323.7	1323.2	1322.6	1323.2	1323.7	1324.3	1324.8	1325.1
140°	1373.7	1373.4	1372.9	1372.3	1371.8	1371.2	1371.8	1372.3	1372.9	1373.4	1373.7
142.5°	1419.8	1419.4	1418.5	1417.6	1416.8	1415.9	1416.8	1417.6	1418.5	1419.4	1419.8
145°	1462.0	1462.0	1462.0	1462.0	1462.0	1462.0	1462.0	1462.0	1462.0	1462.0	1462.0
147.5°	1501.6	1500.9	1499.5	1498.0	1496.6	1495.2	1496.6	1498.0	1499.5	1500.9	1501.6
150°	1537.5	1537.1	1536.2	1535.3	1534.5	1533.6	1534.5	1535.3	1536.2	1537.1	1537.5
152.5°	1570.7	1570.0	1568.6	1567.1	1565.7	1564.3	1565.7	1567.1	1568.6	1570.0	1570.7
155°	1600.1	1599.3	1597.6	1595.9	1594.2	1592.5	1594.2	1595.9	1597.6	1599.3	1600.1
157.5°	1627.0	1625.9	1623.6	1621.3	1619.1	1616.8	1619.1	1621.3	1623.6	1625.9	1627.0
160°	1648.7	1647.7	1645.7	1643.8	1641.8	1639.8	1641.8	1643.8	1645.7	1647.7	1648.7
162.5°	1669.2	1668.3	1666.6	1664.9	1663.2	1661.5	1663.2	1664.9	1666.6	1668.3	1669.2
165°	1687.1	1686.1	1684.1	1682.2	1680.2	1678.2	1680.2	1682.2	1684.1	1686.1	1687.1
167.5°	1701.2	1700.1	1697.8	1695.5	1693.2	1690.9	1693.2	1695.5	1697.8	1700.1	1701.2
170°	1712.7	1711.6	1709.3	1707.0	1704.8	1702.5	1704.8	1707.0	1709.3	1711.6	1712.7
172.5°	1720.4	1719.1	1716.5	1714.0	1711.4	1708.8	1711.4	1714.0	1716.5	1719.1	1720.4
175°	1725.5	1724.4	1722.1	1719.8	1717.5	1715.2	1717.5	1719.8	1722.1	1724.4	1725.5
177.5°	1729.3	1727.9	1725.0	1722.2	1719.3	1716.5	1719.3	1722.2	1725.0	1727.9	1729.3
180°	1721.6	1721.6	1721.6	1721.6	1721.6	1721.6	1721.6	1721.6	1721.6	1721.6	1721.6

TEST NUMBER: P1031885

CATALOG NUMBER: S123DIW-B775D1320UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1
2.5°	1025.7	1027.8	1028.8	1024.7	1021.5	1026.7	1034.1	1039.3	1043.5	1048.7	1051.9
5°	965.0	972.3	972.3	974.4	977.6	982.8	996.4	1005.8	1014.2	1020.5	1025.7
7.5°	913.7	918.9	922.1	927.3	932.6	939.9	955.6	969.2	981.7	989.1	997.4
10°	867.7	871.8	877.1	880.2	889.6	900.1	920.0	931.5	946.2	957.7	968.1
12.5°	823.7	838.4	841.5	840.4	848.8	860.3	880.2	898.0	913.7	925.2	936.7
15°	792.3	797.5	803.8	802.8	820.6	823.7	840.4	861.4	882.3	889.6	900.1
17.5°	757.8	766.1	772.4	775.6	780.8	792.3	808.0	823.7	850.9	852.0	879.2
20°	730.6	738.9	743.1	747.3	750.4	764.0	777.7	795.4	817.4	828.9	843.6
22.5°	712.8	716.9	720.1	723.2	727.4	734.7	751.5	771.4	786.0	798.6	808.0
25°	691.8	696.0	700.2	702.3	705.4	709.6	722.2	737.9	758.8	767.2	776.6
27.5°	677.2	677.2	679.3	679.3	683.5	687.6	697.1	711.7	728.5	738.9	751.5
30°	661.5	660.4	661.5	660.4	659.4	665.7	674.0	686.6	698.1	710.7	719.0
32.5°	645.8	644.7	644.7	645.8	641.6	644.7	648.9	660.4	673.0	679.3	688.7
35°	629.0	626.9	626.9	626.9	624.8	622.7	626.9	637.4	645.8	654.1	661.5
37.5°	612.3	609.1	609.1	607.0	605.0	601.8	601.8	610.2	621.7	624.8	634.3
40°	589.3	589.3	587.2	586.1	584.0	581.9	578.8	586.1	596.6	599.7	607.0
42.5°	566.2	563.1	562.0	562.0	562.0	558.9	556.8	562.0	568.3	573.6	577.7
45°	540.1	538.0	539.0	538.0	535.9	534.8	533.8	535.9	543.2	545.3	550.5
47.5°	511.8	510.8	510.8	509.7	508.7	509.7	505.5	510.8	512.9	514.9	519.1
50°	482.5	481.5	480.4	479.4	479.4	480.4	479.4	479.4	483.5	485.6	489.8
52.5°	453.2	450.1	450.1	449.0	449.0	446.9	449.0	450.1	452.1	454.2	456.3
55°	421.8	421.8	418.7	418.7	416.6	416.6	417.6	416.6	420.7	422.8	422.8
57.5°	391.4	387.3	388.3	386.2	384.1	383.1	383.1	385.2	387.3	387.3	389.3
60°	359.0	354.8	353.8	349.6	351.7	348.5	349.6	349.6	353.8	351.7	353.8
62.5°	326.6	321.3	318.2	316.1	316.1	317.1	315.0	314.0	316.1	318.2	322.4
65°	292.0	288.9	285.7	282.6	282.6	281.5	283.6	280.5	279.5	280.5	282.6
67.5°	256.4	253.3	250.1	247.0	248.1	244.9	242.8	246.0	243.9	244.9	247.0
70°	221.9	219.8	213.5	211.4	210.4	211.4	210.4	208.3	211.4	210.4	211.4
72.5°	187.3	185.3	182.1	176.9	176.9	175.8	174.8	174.8	173.7	173.7	173.7
75°	153.9	149.7	146.5	145.5	143.4	142.3	141.3	139.2	140.2	141.3	139.2
77.5°	119.3	114.1	113.0	113.0	109.9	109.9	110.9	109.9	108.9	108.9	108.9
80°	87.9	83.7	83.7	81.6	79.5	79.5	79.5	79.5	78.5	77.5	78.5
82.5°	56.5	55.5	54.4	54.4	56.5	52.3	54.4	53.4	52.3	52.3	51.3
85°	31.4	32.4	31.4	32.4	30.4	31.4	31.4	31.4	30.4	31.4	29.3
87.5°	11.5	11.5	11.5	12.6	12.6	12.6	12.6	12.6	13.6	12.6	12.6
90°	35.2	34.1	33.0	31.8	30.7	27.0	23.3	19.6	15.9	14.1	12.7
92.5°	41.2	39.2	37.3	35.3	33.3	30.7	28.1	25.6	23.0	21.7	22.6
95°	47.6	45.6	43.7	41.7	39.7	36.6	33.4	30.3	27.2	25.6	31.4
97.5°	50.1	47.8	45.5	43.2	40.9	55.4	69.9	84.4	98.9	106.2	110.2
100°	51.3	49.0	46.7	44.5	42.2	86.5	130.9	175.2	219.5	241.7	238.9
102.5°	57.1	66.5	75.9	85.3	94.7	144.1	193.6	243.0	292.5	317.2	315.4
105°	78.9	129.2	179.5	229.8	280.1	305.7	331.3	356.8	382.4	395.2	393.6
107.5°	322.5	366.3	410.0	453.8	497.6	493.3	489.1	484.8	480.5	478.4	477.1
110°	539.4	548.8	558.1	567.5	576.9	573.8	570.6	567.5	564.4	562.8	561.7

TEST NUMBER: P1031885

CATALOG NUMBER: S123DIW-B775D1320UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	667.7	665.1	662.6	660.0	657.4	654.3	651.2	648.1	645.0	643.4	642.4
115°	745.6	742.7	739.9	737.0	734.2	731.6	729.1	726.5	724.0	722.7	721.8
117.5°	818.8	816.5	814.2	812.0	809.7	808.3	806.9	805.4	804.0	803.3	802.3
120°	891.7	889.4	887.1	884.9	882.6	881.7	880.9	880.0	879.1	878.7	877.4
122.5°	961.2	959.8	958.3	956.9	955.5	954.4	953.2	952.1	951.0	950.4	949.4
125°	1025.5	1025.0	1024.4	1023.9	1023.3	1022.1	1021.0	1019.8	1018.7	1018.1	1017.0
127.5°	1094.5	1093.6	1092.8	1091.9	1091.1	1089.7	1088.3	1086.8	1085.4	1084.7	1083.6
130°	1155.7	1154.6	1153.5	1152.3	1151.2	1150.1	1148.9	1147.8	1146.7	1146.1	1145.0
132.5°	1213.2	1212.1	1211.0	1209.8	1208.7	1207.9	1207.0	1206.2	1205.3	1204.9	1203.8
135°	1271.0	1270.1	1269.3	1268.4	1267.6	1266.4	1265.3	1264.1	1263.0	1262.4	1261.6
137.5°	1324.4	1323.0	1321.5	1320.1	1318.7	1318.1	1317.6	1317.0	1316.5	1316.2	1315.1
140°	1373.1	1372.0	1370.9	1369.7	1368.6	1367.8	1366.9	1366.1	1365.2	1364.8	1363.9
142.5°	1419.4	1418.5	1417.6	1416.8	1415.9	1415.1	1414.2	1413.4	1412.5	1412.1	1411.2
145°	1461.7	1461.1	1460.6	1460.0	1459.4	1458.8	1458.3	1457.7	1457.2	1456.9	1455.9
147.5°	1501.3	1500.8	1500.2	1499.7	1499.1	1498.5	1497.9	1497.4	1496.8	1496.5	1495.8
150°	1537.2	1536.6	1536.1	1535.5	1534.9	1534.3	1533.7	1533.2	1532.6	1532.3	1531.9
152.5°	1570.1	1569.0	1567.9	1566.7	1565.6	1565.3	1565.0	1564.7	1564.4	1564.3	1564.2
155°	1599.4	1598.0	1596.5	1595.1	1593.7	1593.4	1593.2	1592.9	1592.6	1592.5	1592.8
157.5°	1626.1	1624.4	1622.7	1621.0	1619.3	1619.6	1619.9	1620.2	1620.5	1620.6	1620.6
160°	1647.9	1646.2	1644.5	1642.8	1641.1	1641.4	1641.6	1641.9	1642.2	1642.3	1642.4
162.5°	1668.2	1666.2	1664.2	1662.2	1660.2	1660.5	1660.8	1661.1	1661.4	1661.5	1661.9
165°	1686.0	1683.7	1681.4	1679.2	1676.9	1677.2	1677.5	1677.8	1678.1	1678.2	1678.6
167.5°	1700.1	1697.8	1695.5	1693.2	1690.9	1690.9	1690.9	1690.9	1690.9	1690.9	1691.5
170°	1711.6	1709.3	1707.0	1704.8	1702.5	1702.5	1702.5	1702.5	1702.5	1702.5	1703.1
172.5°	1719.3	1717.0	1714.7	1712.4	1710.1	1709.8	1709.5	1709.2	1708.9	1708.8	1709.5
175°	1724.5	1722.5	1720.5	1718.5	1716.5	1716.2	1715.9	1715.6	1715.3	1715.2	1715.9
177.5°	1728.2	1725.9	1723.6	1721.4	1719.1	1718.8	1718.5	1718.2	1717.9	1717.8	1718.5
180°	1721.6	1721.6	1721.6	1721.6	1721.6	1721.6	1721.6	1721.6	1721.6	1721.6	1721.6

TEST NUMBER: P1031885

CATALOG NUMBER: S123DIW-B775D1320UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1080.1	1080.1	1080.1	1080.1
2.5°	1057.1	1060.2	1070.7	1083.3
5°	1036.2	1044.5	1059.2	1079.1
7.5°	1013.1	1025.7	1046.6	1071.8
10°	987.0	1004.8	1030.9	1062.3
12.5°	958.7	981.7	1015.2	1047.7
15°	940.9	964.0	994.3	1029.9
17.5°	906.4	933.6	965.0	1015.2
20°	870.8	901.2	942.0	992.2
22.5°	843.6	876.0	914.8	968.1
25°	811.1	844.6	886.5	942.0
27.5°	776.6	810.1	857.2	915.8
30°	750.4	782.9	827.9	890.7
32.5°	719.0	750.4	797.5	863.5
35°	683.5	719.0	764.0	831.0
37.5°	656.2	688.7	735.8	799.6
40°	626.9	655.2	701.2	764.0
42.5°	595.5	626.9	666.7	729.5
45°	566.2	589.3	630.1	689.7
47.5°	534.8	561.0	592.4	638.4
50°	501.3	523.3	557.9	589.3
52.5°	468.9	486.7	516.0	540.1
55°	434.4	452.1	474.1	488.8
57.5°	401.9	414.5	429.1	438.5
60°	362.1	374.7	384.1	393.5
62.5°	326.6	336.0	341.2	346.4
65°	289.9	295.2	298.3	302.5
67.5°	250.1	255.4	256.4	262.7
70°	213.5	214.6	216.7	219.8
72.5°	179.0	181.1	180.0	182.1
75°	143.4	145.5	143.4	145.5
77.5°	108.9	110.9	110.9	114.1
80°	78.5	79.5	80.6	80.6
82.5°	51.3	54.4	52.3	53.4
85°	29.3	30.4	30.4	31.4
87.5°	13.6	14.7	13.6	15.7
90°	9.8	7.0	4.1	1.3
92.5°	24.3	26.0	27.7	29.4
95°	43.1	54.7	66.4	78.0
97.5°	118.1	126.1	134.0	142.0
100°	233.2	227.5	221.9	216.2
102.5°	311.7	308.0	304.3	300.6
105°	390.5	387.4	384.3	381.2
107.5°	474.6	472.0	469.5	466.9
110°	559.4	557.1	554.9	552.6

TEST NUMBER: P1031885

CATALOG NUMBER: S123DIW-B775D1320UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	640.4	638.4	636.4	634.4
115°	720.1	718.4	716.7	715.0
117.5°	800.3	798.3	796.3	794.3
120°	874.9	872.3	869.8	867.2
122.5°	947.4	945.4	943.4	941.4
125°	1014.7	1012.4	1010.2	1007.9
127.5°	1081.3	1079.0	1076.7	1074.4
130°	1142.7	1140.4	1138.1	1135.8
132.5°	1201.5	1199.2	1197.0	1194.7
135°	1259.9	1258.2	1256.5	1254.8
137.5°	1312.8	1310.5	1308.2	1305.9
140°	1362.2	1360.5	1358.8	1357.1
142.5°	1409.5	1407.8	1406.1	1404.4
145°	1453.9	1451.9	1449.9	1447.9
147.5°	1494.4	1492.9	1491.5	1490.1
150°	1531.0	1530.2	1529.3	1528.5
152.5°	1563.9	1563.6	1563.3	1563.0
155°	1593.3	1593.9	1594.4	1595.0
157.5°	1620.6	1620.6	1620.6	1620.6
160°	1642.7	1643.0	1643.3	1643.6
162.5°	1662.8	1663.7	1664.5	1665.4
165°	1679.5	1680.3	1681.2	1682.0
167.5°	1692.6	1693.8	1694.9	1696.1
170°	1704.2	1705.3	1706.5	1707.6
172.5°	1710.9	1712.4	1713.8	1715.2
175°	1717.3	1718.8	1720.2	1721.6
177.5°	1719.9	1721.4	1722.8	1724.2
180°	1721.6	1721.6	1721.6	1721.6

(END OF REPORT)