

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P992516

Luminaire Tested: S123DW-B1165DB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P992516
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-11)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DW-B1165DB2750-4F0-XX-W2A-F_5000K
Description: Define 3 Direct Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4585.0 lumens
Efficiency: N/A
Efficacy: 74.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 61.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P992516

CATALOG NUMBER: S123DW-B1165DB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P992516

CATALOG NUMBER: S123DW-B1165DB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	109	104	100	96	106	102	98	95	98	94	92	94	91	89	90	88	86	84			
2	99	91	84	79	97	89	83	78	86	80	76	82	78	74	79	76	72	70			
3	91	80	72	66	88	79	71	65	76	69	64	73	67	63	70	66	62	59			
4	83	71	62	56	81	70	62	55	67	60	55	65	59	54	63	58	53	51			
5	76	64	55	48	74	63	54	48	60	53	47	58	52	47	57	51	46	44			
6	71	57	49	42	69	56	48	42	55	47	42	53	46	41	51	46	41	39			
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	34			
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	31			
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	30	28			
10	54	40	33	27	52	40	32	27	39	32	27	38	32	27	37	31	27	25			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18963	18963	18963
5°	19051	18790	18921
10°	18924	18627	18743
15°	18703	18417	18450
20°	18444	18116	18133
25°	18099	17757	17721
30°	17716	17360	17228
35°	17318	16939	16720
40°	16901	16475	16219
45°	16442	16049	15658
50°	15980	15525	15093
55°	15379	14981	14527
60°	14772	14348	13892
65°	14238	13657	13234
70°	13445	12872	12299
75°	12285	11844	11341
80°	11077	10612	10519
85°	9732	9349	8979

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16442 cd/sqm

TEST NUMBER: P992516

CATALOG NUMBER: S123DW-B1165DB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.1	3.6
10°-20°	469.0	10.2
20°-30°	692.6	15.1
30°-40°	808.9	17.6
40°-50°	813.2	17.7
50°-60°	714.4	15.6
60°-70°	532.0	11.6
70°-80°	302.8	6.6
80°-90°	86.1	1.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1327.7	29.0
0°-40°	2136.6	46.6
0°-60°	3664.1	79.9
0°-90°	4585.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4585.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1762	1762	1762	1762	1762	
5°	1763	1756	1739	1754	1751	167
15°	1678	1672	1653	1665	1656	473
25°	1524	1515	1495	1497	1492	702
35°	1318	1309	1289	1280	1272	825
45°	1080	1074	1054	1036	1029	834
55°	820	818	798	782	774	734
65°	559	551	536	524	520	551
75°	295	289	285	277	273	316
85°	79	76	76	73	73	90
90°	0	0	0	0	0	

TEST NUMBER: P992516

CATALOG NUMBER: S123DW-B1165DB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1761.7	1761.7	1761.7	1761.7	1761.7
2.5°	1769.3	1763.2	1746.6	1761.7	1760.2
5°	1763.2	1755.7	1739.0	1754.2	1751.1
7.5°	1749.6	1742.0	1725.4	1739.0	1737.5
10°	1731.4	1723.9	1704.2	1717.8	1714.8
12.5°	1707.2	1701.1	1683.0	1692.0	1690.5
15°	1678.4	1672.4	1652.7	1664.8	1655.7
17.5°	1646.6	1639.0	1619.3	1628.4	1625.4
20°	1610.2	1601.2	1581.5	1587.5	1583.0
22.5°	1569.3	1560.3	1540.6	1545.1	1539.1
25°	1523.9	1514.8	1495.1	1496.6	1492.1
27.5°	1476.9	1467.9	1446.6	1448.2	1443.6
30°	1425.4	1417.9	1396.7	1396.7	1386.1
32.5°	1373.9	1363.3	1348.2	1337.6	1333.0
35°	1317.9	1308.8	1289.1	1280.0	1272.4
37.5°	1261.8	1249.7	1230.0	1219.4	1214.9
40°	1202.8	1193.7	1172.5	1160.3	1154.3
42.5°	1143.7	1133.1	1111.9	1099.8	1093.7
45°	1080.1	1074.0	1054.3	1036.1	1028.6
47.5°	1018.0	1008.9	990.7	972.5	966.5
50°	954.3	946.8	927.1	910.4	901.3
52.5°	887.7	883.1	861.9	848.3	839.2
55°	819.5	818.0	798.3	781.6	774.1
57.5°	755.9	749.8	734.7	719.5	710.4
60°	686.2	684.7	666.5	652.9	645.3
62.5°	624.1	619.6	601.4	587.7	583.2
65°	559.0	551.4	536.2	524.1	519.6
67.5°	489.3	483.2	471.1	460.5	454.4
70°	427.2	418.1	409.0	398.4	390.8
72.5°	362.0	356.0	345.4	336.3	333.3
75°	295.4	289.3	284.8	277.2	272.7
77.5°	236.3	233.3	227.2	221.2	221.2
80°	178.7	174.2	171.2	169.7	169.7
82.5°	122.7	122.7	122.7	119.7	118.2
85°	78.8	75.7	75.7	72.7	72.7
87.5°	39.4	34.8	33.3	31.8	31.8
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)