

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P982961

Luminaire Tested: S123IW-B1535UB2750-4F0-XX-W2A-1\_3000K

Issue Date: 5/2/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P982961  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 5/2/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S123IW-B1535UB2750-4F0-XX-W2A-1\_3000K  
Description: Define 3 Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5401.0 lumens  
Efficiency: N/A  
Efficacy: 103.5 lumens/watt  
Spacing Criteria (0/90/45): - / - / -  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Indirect

Input Watts (W): 52.2  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P982961

CATALOG NUMBER: S123IW-B1535UB2750-4F0-XX-W2A-1\_3000K

### Luminous Intensity Polar Plot



TEST NUMBER: P982961

CATALOG NUMBER: S123IW-B1535UB2750-4F0-XX-W2A-1\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |
|-----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|
| RF  | 20 |    |    |    | 20 |    |    |    | 20 |    |    |    | 20 |    |    |    | 20 |
| RC  | 80 |    |    |    | 70 |    |    |    | 50 |    |    |    | 30 |    |    |    | 10 |
| RW  | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 |
| RCR |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |
| 0   | 95 | 95 | 95 | 95 | 81 | 81 | 81 | 81 | 56 | 56 | 56 | 32 | 32 | 32 | 10 | 10 | 10 |
| 1   | 87 | 83 | 79 | 76 | 74 | 71 | 68 | 65 | 48 | 47 | 45 | 28 | 27 | 26 | 9  | 9  | 8  |
| 2   | 79 | 72 | 66 | 62 | 67 | 62 | 57 | 53 | 42 | 40 | 37 | 24 | 23 | 22 | 8  | 7  | 7  |
| 3   | 72 | 63 | 56 | 51 | 61 | 54 | 49 | 44 | 37 | 34 | 31 | 21 | 20 | 18 | 7  | 6  | 6  |
| 4   | 65 | 56 | 48 | 43 | 56 | 48 | 42 | 37 | 33 | 29 | 26 | 19 | 17 | 16 | 6  | 6  | 5  |
| 5   | 60 | 49 | 42 | 36 | 51 | 42 | 36 | 32 | 29 | 25 | 22 | 17 | 15 | 13 | 5  | 5  | 4  |
| 6   | 55 | 44 | 36 | 31 | 47 | 38 | 32 | 27 | 26 | 22 | 19 | 15 | 13 | 11 | 5  | 4  | 4  |
| 7   | 50 | 39 | 32 | 27 | 43 | 34 | 28 | 23 | 23 | 19 | 17 | 14 | 11 | 10 | 4  | 4  | 3  |
| 8   | 47 | 35 | 28 | 23 | 40 | 30 | 24 | 20 | 21 | 17 | 14 | 12 | 10 | 9  | 4  | 3  | 3  |
| 9   | 43 | 32 | 25 | 20 | 37 | 27 | 22 | 18 | 19 | 15 | 13 | 11 | 9  | 8  | 4  | 3  | 3  |
| 10  | 40 | 29 | 22 | 18 | 34 | 25 | 19 | 16 | 17 | 14 | 11 | 10 | 8  | 7  | 3  | 3  | 2  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0° | 45° | 90° |
|-----|----|-----|-----|
| 0°  | 0  | 0   | 0   |
| 5°  | 0  | 0   | 0   |
| 10° | 0  | 0   | 0   |
| 15° | 0  | 0   | 0   |
| 20° | 0  | 0   | 0   |
| 25° | 0  | 0   | 0   |
| 30° | 0  | 0   | 0   |
| 35° | 0  | 0   | 0   |
| 40° | 0  | 0   | 0   |
| 45° | 0  | 0   | 0   |
| 50° | 0  | 0   | 0   |
| 55° | 0  | 0   | 0   |
| 60° | 0  | 0   | 0   |
| 65° | 0  | 0   | 0   |
| 70° | 0  | 0   | 0   |
| 75° | 0  | 0   | 0   |
| 80° | 0  | 0   | 0   |
| 85° | 0  | 0   | 0   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 0°  
Luminance: 0 cd/sqm

TEST NUMBER: P982961

CATALOG NUMBER: S123IW-B1535UB2750-4F0-XX-W2A-1\_3000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 0.0    | 0.0       |
| 10°-20°   | 0.0    | 0.0       |
| 20°-30°   | 0.0    | 0.0       |
| 30°-40°   | 0.0    | 0.0       |
| 40°-50°   | 0.0    | 0.0       |
| 50°-60°   | 0.0    | 0.0       |
| 60°-70°   | 0.0    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 4.1    | 0.1       |
| 90°-100°  | 125.4  | 2.3       |
| 100°-110° | 379.5  | 7.0       |
| 110°-120° | 646.1  | 12.0      |
| 120°-130° | 849.9  | 15.7      |
| 130°-140° | 955.3  | 17.7      |
| 140°-150° | 939.2  | 17.4      |
| 150°-160° | 790.7  | 14.6      |
| 160°-170° | 526.4  | 9.7       |
| 170°-180° | 184.3  | 3.4       |
| 0°-30°    | 0.0    | 0.0       |
| 0°-40°    | 0.0    | 0.0       |
| 0°-60°    | 0.0    | 0.0       |
| 0°-90°    | 4.1    | 0.1       |
| 90°-120°  | 1150.9 | 21.3      |
| 90°-150°  | 3895.4 | 72.1      |
| 90°-180°  | 5397.0 | 99.9      |
| 0°-180°   | 5401.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|      | 0°   | 22.5° | 45°  | 67.5° | 90°  | Flux |
|------|------|-------|------|-------|------|------|
| 0°   | 0    | 0     | 0    | 0     | 0    |      |
| 5°   | 0    | 0     | 0    | 0     | 0    | 0    |
| 15°  | 0    | 0     | 0    | 0     | 0    | 0    |
| 25°  | 0    | 0     | 0    | 0     | 0    | 0    |
| 35°  | 0    | 0     | 0    | 0     | 0    | 0    |
| 45°  | 0    | 0     | 0    | 0     | 0    | 0    |
| 55°  | 0    | 0     | 0    | 0     | 0    | 0    |
| 65°  | 0    | 0     | 0    | 0     | 0    | 0    |
| 75°  | 0    | 0     | 0    | 0     | 0    | 0    |
| 85°  | 0    | 0     | 0    | 0     | 0    | 0    |
| 90°  | 2    | 17    | 37   | 43    | 46   | 7    |
| 95°  | 90   | 101   | 113  | 119   | 119  | 99   |
| 105° | 344  | 347   | 361  | 361   | 364  | 369  |
| 115° | 650  | 655   | 652  | 653   | 652  | 644  |
| 125° | 952  | 956   | 953  | 947   | 941  | 849  |
| 135° | 1235 | 1244  | 1242 | 1236  | 1233 | 951  |
| 145° | 1498 | 1501  | 1506 | 1504  | 1498 | 936  |
| 155° | 1715 | 1715  | 1717 | 1723  | 1712 | 790  |
| 165° | 1868 | 1864  | 1864 | 1873  | 1862 | 527  |
| 175° | 1943 | 1937  | 1937 | 1946  | 1936 | 185  |
| 180° | 1948 | 1948  | 1948 | 1948  | 1948 |      |



TEST NUMBER: P982961

CATALOG NUMBER: S123IW-B1535UB2750-4F0-XX-W2A-1\_3000K

**CANDELA DISTRIBUTION (FULL):**

|        | 0°    | 22.5° | 45°   | 67.5° | 90°   |
|--------|-------|-------|-------|-------|-------|
| 0°     | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 2.5°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 5°     | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 7.5°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 10°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 12.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 15°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 17.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 20°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 22.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 25°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 27.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 30°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 32.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 35°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 37.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 40°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 42.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 45°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 47.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 50°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 52.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 55°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 57.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 60°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 62.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 65°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 67.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 70°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 72.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 75°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 77.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 80°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 82.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 85°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 87.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 90°    | 1.5   | 16.8  | 36.7  | 42.8  | 45.9  |
| 92.5°  | 45.9  | 55.1  | 64.3  | 68.9  | 65.8  |
| 95°    | 90.3  | 101.0 | 113.2 | 119.3 | 119.3 |
| 97.5°  | 148.4 | 156.1 | 165.2 | 172.9 | 171.4 |
| 100°   | 208.1 | 217.3 | 224.9 | 229.5 | 232.6 |
| 102.5° | 276.9 | 281.5 | 292.2 | 296.8 | 295.3 |
| 105°   | 344.3 | 347.3 | 361.1 | 361.1 | 364.2 |
| 107.5° | 423.8 | 425.4 | 431.5 | 436.1 | 434.5 |
| 110°   | 497.3 | 500.3 | 503.4 | 509.5 | 506.4 |

TEST NUMBER: P982961

CATALOG NUMBER: S123IW-B1535UB2750-4F0-XX-W2A-1\_3000K

**CANDELA DISTRIBUTION (continued):**

|        | 0°     | 22.5°  | 45°    | 67.5°  | 90°    |
|--------|--------|--------|--------|--------|--------|
| 112.5° | 573.8  | 575.3  | 575.3  | 583.0  | 583.0  |
| 115°   | 650.3  | 654.9  | 651.8  | 653.3  | 651.8  |
| 117.5° | 728.3  | 729.8  | 726.8  | 726.8  | 722.2  |
| 120°   | 800.2  | 809.4  | 801.7  | 800.2  | 797.2  |
| 122.5° | 875.2  | 881.3  | 878.3  | 873.7  | 869.1  |
| 125°   | 951.7  | 956.3  | 953.2  | 947.1  | 941.0  |
| 127.5° | 1022.1 | 1031.3 | 1028.2 | 1019.0 | 1012.9 |
| 130°   | 1092.5 | 1104.7 | 1100.1 | 1094.0 | 1083.3 |
| 132.5° | 1162.8 | 1175.1 | 1172.0 | 1164.4 | 1156.7 |
| 135°   | 1234.8 | 1243.9 | 1242.4 | 1236.3 | 1233.2 |
| 137.5° | 1300.5 | 1308.2 | 1312.8 | 1305.1 | 1300.5 |
| 140°   | 1369.4 | 1377.0 | 1378.6 | 1377.0 | 1366.3 |
| 142.5° | 1432.1 | 1439.8 | 1442.8 | 1441.3 | 1433.7 |
| 145°   | 1497.9 | 1501.0 | 1505.6 | 1504.0 | 1497.9 |
| 147.5° | 1554.5 | 1560.7 | 1565.2 | 1565.2 | 1556.1 |
| 150°   | 1614.2 | 1617.3 | 1620.3 | 1620.3 | 1611.1 |
| 152.5° | 1663.2 | 1667.8 | 1669.3 | 1672.3 | 1664.7 |
| 155°   | 1715.2 | 1715.2 | 1716.7 | 1722.8 | 1712.1 |
| 157.5° | 1759.6 | 1758.0 | 1759.6 | 1765.7 | 1756.5 |
| 160°   | 1800.9 | 1797.8 | 1797.8 | 1805.5 | 1799.3 |
| 162.5° | 1837.6 | 1833.0 | 1834.5 | 1842.2 | 1831.5 |
| 165°   | 1868.2 | 1863.6 | 1863.6 | 1872.8 | 1862.1 |
| 167.5° | 1894.2 | 1888.1 | 1889.6 | 1898.8 | 1889.6 |
| 170°   | 1915.6 | 1909.5 | 1909.5 | 1920.2 | 1909.5 |
| 172.5° | 1932.5 | 1926.3 | 1926.3 | 1935.5 | 1924.8 |
| 175°   | 1943.2 | 1937.0 | 1937.0 | 1946.2 | 1935.5 |
| 177.5° | 1949.3 | 1943.2 | 1943.2 | 1952.3 | 1941.6 |
| 180°   | 1947.8 | 1947.8 | 1947.8 | 1947.8 | 1947.8 |



TEST NUMBER: P982961

CATALOG NUMBER: S123IW-B1535UB2750-4F0-XX-W2A-1\_3000K

**CIE UGR TABLE:**

| Reflectances:   |      |                  |      |      |      |      |                |      |      |      |      |
|-----------------|------|------------------|------|------|------|------|----------------|------|------|------|------|
| Ceiling         |      | 0.7              | 0.7  | 0.5  | 0.5  | 0.3  | 0.7            | 0.7  | 0.5  | 0.5  | 0.3  |
| Wall            |      | 0.5              | 0.3  | 0.5  | 0.3  | 0.3  | 0.5            | 0.3  | 0.5  | 0.3  | 0.3  |
| Reference plane |      | 0.2              | 0.2  | 0.2  | 0.2  | 0.2  | 0.2            | 0.2  | 0.2  | 0.2  | 0.2  |
| Room dimensions |      | Viewed crosswise |      |      |      |      | Viewed endwise |      |      |      |      |
| X=2H            | Y=2H | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
|                 | 3H   | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
|                 | 4H   | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
|                 | 6H   | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
|                 | 8H   | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
|                 | 12H  | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
| 4H              | 2H   | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
|                 | 3H   | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
|                 | 4H   | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
|                 | 6H   | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
|                 | 8H   | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
|                 | 12H  | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
| 8H              | 4H   | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
|                 | 6H   | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
|                 | 8H   | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
|                 | 12H  | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
| 12H             | 4H   | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
|                 | 6H   | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
|                 | 8H   | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |

END OF REPORT