

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P982967

Luminaire Tested: S123IW-B1535UB2750-4F0-XX-W2A_3500K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P982967
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123IW-B1535UB2750-4F0-XX-W2A_3500K
Description: Define 3 Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6255.0 lumens
Efficiency: N/A
Efficacy: 119.8 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 52.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P982967

CATALOG NUMBER: S123IW-B1535UB2750-4F0-XX-W2A_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P982967

CATALOG NUMBER: S123IW-B1535UB2750-4F0-XX-W2A_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P982967

CATALOG NUMBER: S123IW-B1535UB2750-4F0-XX-W2A_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	4.1	0.1
90°-100°	72.3	1.2
100°-110°	349.6	5.6
110°-120°	856.7	13.7
120°-130°	1087.5	17.4
130°-140°	1161.8	18.6
140°-150°	1086.4	17.4
150°-160°	876.3	14.0
160°-170°	565.5	9.0
170°-180°	194.9	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	4.1	0.1
90°-120°	1278.6	20.4
90°-150°	4614.2	73.8
90°-180°	6251.0	99.9
0°-180°	6255.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	2	17	37	43	46	5
95°	93	30	47	58	58	111
105°	454	471	334	64	67	481
115°	852	861	874	890	896	841
125°	1200	1213	1219	1222	1225	1073
135°	1494	1504	1510	1514	1510	1151
145°	1724	1735	1738	1741	1741	1080
155°	1900	1897	1898	1906	1897	875
165°	2003	1999	1997	2009	1999	566
175°	2050	2043	2044	2055	2043	195
180°	2050	2050	2050	2050	2050	

TEST NUMBER: P982967

CATALOG NUMBER: S123IW-B1535UB2750-4F0-XX-W2A_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.5	16.8	36.6	42.7	45.7
92.5°	35.0	25.9	39.6	50.3	51.8
95°	92.9	30.5	47.2	57.9	57.9
97.5°	169.1	126.4	48.7	60.9	62.5
100°	257.4	287.9	50.3	62.5	64.0
102.5°	358.0	377.8	112.7	62.5	65.5
105°	454.0	470.7	333.6	64.0	67.0
107.5°	556.0	569.7	592.6	358.0	158.4
110°	658.1	670.3	687.0	636.8	418.9

TEST NUMBER: P982967

CATALOG NUMBER: S123IW-B1535UB2750-4F0-XX-W2A_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	755.6	766.2	783.0	796.7	793.7
115°	851.6	860.7	874.4	889.6	895.7
117.5°	946.0	956.7	964.3	976.5	978.0
120°	1032.8	1046.5	1051.1	1063.3	1063.3
122.5°	1121.2	1131.8	1137.9	1145.6	1147.1
125°	1200.4	1212.6	1218.7	1221.7	1224.8
127.5°	1279.6	1291.8	1299.4	1304.0	1300.9
130°	1352.7	1364.9	1371.0	1377.1	1374.1
132.5°	1422.8	1435.0	1439.6	1445.7	1441.1
135°	1494.4	1503.5	1509.6	1514.2	1509.6
137.5°	1555.3	1567.5	1570.6	1578.2	1575.1
140°	1616.3	1625.4	1630.0	1636.1	1633.0
142.5°	1672.6	1681.8	1686.3	1690.9	1686.3
145°	1724.4	1735.1	1738.1	1741.2	1741.2
147.5°	1774.7	1782.3	1785.4	1788.4	1780.8
150°	1820.4	1825.0	1828.0	1831.1	1826.5
152.5°	1861.5	1863.1	1864.6	1870.7	1863.1
155°	1899.6	1896.6	1898.1	1905.7	1896.6
157.5°	1930.1	1930.1	1928.6	1937.7	1925.5
160°	1957.5	1956.0	1954.5	1963.6	1952.9
162.5°	1983.4	1978.8	1977.3	1988.0	1978.8
165°	2003.2	1998.6	1997.1	2009.3	1998.6
167.5°	2020.0	2013.9	2013.9	2026.1	2013.9
170°	2033.7	2027.6	2027.6	2039.8	2027.6
172.5°	2042.8	2035.2	2036.7	2048.9	2035.2
175°	2050.4	2042.8	2044.3	2055.0	2042.8
177.5°	2053.5	2045.9	2047.4	2059.6	2044.3
180°	2050.4	2050.4	2050.4	2050.4	2050.4



TEST NUMBER: P982967

CATALOG NUMBER: S123IW-B1535UB2750-4F0-XX-W2A_3500K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00

END OF REPORT