

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031964

Luminaire Tested: S123DIW-B775D755UB30-4F0-XX-W2A-F

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031964
REPORT IS A COMBINATION OF REPORTS P992139 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B775D755UB30-4F0-XX-W2A-F
Description: Define 3 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6260.0 lumens
Efficiency: N/A
Efficacy: 105.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 59.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031964

CATALOG NUMBER: S123DIW-B775D755UB30-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1031964

CATALOG NUMBER: S123DIW-B775D755UB30-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57
1	98	94	90	86	90	87	83	80	73	71	69	61	60	58	50	49	48
2	89	82	75	70	82	76	70	66	64	60	57	54	51	48	44	42	40
3	81	72	64	59	75	67	60	55	57	52	48	48	44	41	39	37	34
4	74	64	56	49	68	59	52	47	50	45	41	42	38	35	35	32	30
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26
6	63	51	43	37	58	47	40	35	41	35	31	34	30	27	29	25	23
7	58	46	38	32	54	43	36	30	37	31	27	31	27	24	26	23	20
8	54	42	34	28	50	39	32	27	34	28	24	29	24	21	24	21	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	21	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13177	13177	13177
5°	13209	12722	12703
10°	13092	12292	12165
15°	12910	11844	11580
20°	12701	11347	10999
25°	12431	10822	10378
30°	12136	10279	9725
35°	11827	9725	9076
40°	11503	9142	8438
45°	11146	8575	7771
50°	10783	7943	7102
55°	10319	7284	6424
60°	9838	6557	5702
65°	9389	5771	4949
70°	8740	4899	4072
75°	7809	3879	3161
80°	6743	2725	2236
85°	5254	1465	1119

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11146 cd/sqm

TEST NUMBER: P1031964

CATALOG NUMBER: S123DIW-B775D755UB30-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.4	1.8
10°-20°	325.9	5.2
20°-30°	481.3	7.7
30°-40°	562.1	9.0
40°-50°	565.1	9.0
50°-60°	496.4	7.9
60°-70°	369.7	5.9
70°-80°	210.4	3.4
80°-90°	61.8	1.0
90°-100°	35.5	0.6
100°-110°	171.8	2.7
110°-120°	421.0	6.7
120°-130°	534.5	8.5
130°-140°	571.0	9.1
140°-150°	533.9	8.5
150°-160°	430.6	6.9
160°-170°	277.9	4.4
170°-180°	95.8	1.5
0°-30°	922.6	14.7
0°-40°	1484.6	23.7
0°-60°	2546.1	40.7
0°-90°	3188.0	50.9
90°-120°	628.3	10.0
90°-150°	2267.7	36.2
90°-180°	3072.0	49.1
0°-180°	6260.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1224	1224	1224	1224	1224	
5°	1225	1220	1208	1219	1217	116
15°	1166	1162	1148	1157	1150	329
25°	1059	1053	1039	1040	1037	488
35°	916	910	896	890	884	573
45°	750	746	733	720	715	579
55°	570	568	555	543	538	510
65°	388	383	373	364	361	383
75°	205	201	198	193	190	219
85°	55	53	53	50	50	59
90°	1	8	18	21	22	6
95°	46	15	23	28	28	55
105°	223	231	164	31	33	237
115°	418	423	430	437	440	413
125°	590	596	599	600	602	527
135°	734	739	742	744	742	565
145°	848	853	854	856	856	531
155°	934	932	933	937	932	430
165°	984	982	982	988	982	278
175°	1008	1004	1005	1010	1004	96
180°	1008	1008	1008	1008	1008	

TEST NUMBER: P1031964

CATALOG NUMBER: S123DIW-B775D755UB30-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1224.2	1224.2	1224.2	1224.2	1224.2
2.5°	1229.4	1225.2	1213.7	1224.2	1223.1
5°	1225.2	1220.0	1208.4	1218.9	1216.8
7.5°	1215.8	1210.5	1198.9	1208.4	1207.3
10°	1203.1	1197.9	1184.2	1193.7	1191.5
12.5°	1186.3	1182.1	1169.4	1175.8	1174.7
15°	1166.3	1162.1	1148.4	1156.8	1150.5
17.5°	1144.2	1138.9	1125.2	1131.6	1129.4
20°	1118.9	1112.6	1098.9	1103.1	1100.0
22.5°	1090.5	1084.2	1070.5	1073.7	1069.4
25°	1058.9	1052.6	1038.9	1040.0	1036.8
27.5°	1026.3	1020.0	1005.2	1006.3	1003.1
30°	990.5	985.2	970.5	970.5	963.1
32.5°	954.7	947.3	936.8	929.5	926.3
35°	915.8	909.5	895.8	889.5	884.2
37.5°	876.8	868.4	854.7	847.3	844.2
40°	835.8	829.5	814.7	806.3	802.1
42.5°	794.7	787.3	772.6	764.2	760.0
45°	750.5	746.3	732.6	720.0	714.7
47.5°	707.4	701.0	688.4	675.8	671.6
50°	663.1	657.9	644.2	632.6	626.3
52.5°	616.8	613.7	598.9	589.5	583.1
55°	569.5	568.4	554.7	543.1	537.9
57.5°	525.3	521.0	510.5	500.0	493.7
60°	476.8	475.8	463.1	453.7	448.4
62.5°	433.7	430.5	417.9	408.4	405.3
65°	388.4	383.1	372.6	364.2	361.0
67.5°	340.0	335.8	327.4	320.0	315.8
70°	296.8	290.5	284.2	276.8	271.6
72.5°	251.6	247.4	240.0	233.7	231.6
75°	205.3	201.0	197.9	192.6	189.5
77.5°	164.2	162.1	157.9	153.7	153.7
80°	124.2	121.0	118.9	117.9	117.9
82.5°	85.3	85.3	85.3	83.2	82.1
85°	54.7	52.6	52.6	50.5	50.5
87.5°	27.4	24.2	23.2	22.1	22.1
90°	0.7	8.2	18.0	21.0	22.5
92.5°	17.2	12.7	19.5	24.7	25.5
95°	45.7	15.0	23.2	28.4	28.4
97.5°	83.1	62.1	24.0	29.9	30.7
100°	126.5	141.5	24.7	30.7	31.4
102.5°	175.9	185.7	55.4	30.7	32.2
105°	223.1	231.3	164.0	31.4	32.9
107.5°	273.3	280.0	291.2	175.9	77.9
110°	323.4	329.4	337.6	312.9	205.9



TEST NUMBER: P1031964

CATALOG NUMBER: S123DIW-B775D755UB30-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	371.3	376.6	384.8	391.5	390.0
115°	418.5	423.0	429.7	437.2	440.2
117.5°	464.9	470.1	473.9	479.9	480.6
120°	507.6	514.3	516.6	522.6	522.6
122.5°	551.0	556.2	559.2	563.0	563.7
125°	589.9	595.9	598.9	600.4	601.9
127.5°	628.9	634.9	638.6	640.8	639.3
130°	664.8	670.8	673.8	676.8	675.3
132.5°	699.2	705.2	707.5	710.5	708.2
135°	734.4	738.9	741.9	744.2	741.9
137.5°	764.4	770.4	771.9	775.6	774.1
140°	794.3	798.8	801.1	804.0	802.5
142.5°	822.0	826.5	828.8	831.0	828.8
145°	847.5	852.7	854.2	855.7	855.7
147.5°	872.2	875.9	877.4	878.9	875.2
150°	894.6	896.9	898.4	899.9	897.6
152.5°	914.8	915.6	916.3	919.3	915.6
155°	933.6	932.1	932.8	936.6	932.1
157.5°	948.5	948.5	947.8	952.3	946.3
160°	962.0	961.3	960.5	965.0	959.8
162.5°	974.7	972.5	971.7	977.0	972.5
165°	984.5	982.2	981.5	987.5	982.2
167.5°	992.7	989.7	989.7	995.7	989.7
170°	999.4	996.4	996.4	1002.4	996.4
172.5°	1003.9	1000.2	1000.9	1006.9	1000.2
175°	1007.7	1003.9	1004.7	1009.9	1003.9
177.5°	1009.2	1005.4	1006.2	1012.2	1004.7
180°	1007.7	1007.7	1007.7	1007.7	1007.7

(END OF REPORT)