

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P983003

Luminaire Tested: S123IW-B755UB2750-4F0-XX-W2A-1_4000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P983003
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123IW-B755UB2750-4F0-XX-W2A-1_4000K
Description: Define 3 Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2650.0 lumens
Efficiency: N/A
Efficacy: 114.2 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 23.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P983003

CATALOG NUMBER: S123IW-B755UB2750-4F0-XX-W2A-1_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P983003

CATALOG NUMBER: S123IW-B755UB2750-4F0-XX-W2A-1_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P983003

CATALOG NUMBER: S123IW-B755UB2750-4F0-XX-W2A-1_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.0	0.1
90°-100°	61.5	2.3
100°-110°	186.2	7.0
110°-120°	317.0	12.0
120°-130°	417.0	15.7
130°-140°	468.7	17.7
140°-150°	460.8	17.4
150°-160°	388.0	14.6
160°-170°	258.3	9.7
170°-180°	90.4	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.0	0.1
90°-120°	564.7	21.3
90°-150°	1911.3	72.1
90°-180°	2648.0	99.9
0°-180°	2650.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	8	18	21	22	3
95°	44	50	56	59	59	49
105°	169	170	177	177	179	181
115°	319	321	320	321	320	316
125°	467	469	468	465	462	416
135°	606	610	610	607	605	467
145°	735	736	739	738	735	459
155°	842	842	842	845	840	387
165°	917	914	914	919	914	259
175°	953	950	950	955	950	91
180°	956	956	956	956	956	

TEST NUMBER: P983003

CATALOG NUMBER: S123IW-B755UB2750-4F0-XX-W2A-1_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.8	8.3	18.0	21.0	22.5
92.5°	22.5	27.0	31.5	33.8	32.3
95°	44.3	49.5	55.6	58.6	58.6
97.5°	72.8	76.6	81.1	84.8	84.1
100°	102.1	106.6	110.4	112.6	114.1
102.5°	135.9	138.1	143.4	145.6	144.9
105°	168.9	170.4	177.2	177.2	178.7
107.5°	207.9	208.7	211.7	214.0	213.2
110°	244.0	245.5	247.0	250.0	248.5

TEST NUMBER: P983003

CATALOG NUMBER: S123IW-B755UB2750-4F0-XX-W2A-1_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	281.5	282.3	282.3	286.0	286.0
115°	319.1	321.3	319.8	320.6	319.8
117.5°	357.3	358.1	356.6	356.6	354.3
120°	392.6	397.1	393.4	392.6	391.1
122.5°	429.4	432.4	430.9	428.7	426.4
125°	466.9	469.2	467.7	464.7	461.7
127.5°	501.5	506.0	504.5	500.0	497.0
130°	536.0	542.0	539.8	536.8	531.5
132.5°	570.5	576.6	575.1	571.3	567.5
135°	605.8	610.3	609.6	606.6	605.1
137.5°	638.1	641.9	644.1	640.4	638.1
140°	671.9	675.6	676.4	675.6	670.4
142.5°	702.7	706.4	707.9	707.2	703.4
145°	735.0	736.5	738.7	738.0	735.0
147.5°	762.7	765.7	768.0	768.0	763.5
150°	792.0	793.5	795.0	795.0	790.5
152.5°	816.0	818.3	819.0	820.5	816.8
155°	841.6	841.6	842.3	845.3	840.1
157.5°	863.3	862.6	863.3	866.3	861.8
160°	883.6	882.1	882.1	885.8	882.8
162.5°	901.6	899.4	900.1	903.9	898.6
165°	916.6	914.4	914.4	918.9	913.6
167.5°	929.4	926.4	927.1	931.6	927.1
170°	939.9	936.9	936.9	942.2	936.9
172.5°	948.2	945.2	945.2	949.7	944.4
175°	953.4	950.4	950.4	954.9	949.7
177.5°	956.4	953.4	953.4	957.9	952.7
180°	955.7	955.7	955.7	955.7	955.7



TEST NUMBER: P983003

CATALOG NUMBER: S123IW-B755UB2750-4F0-XX-W2A-1_4000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00

END OF REPORT