

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P983006

Luminaire Tested: S123IW-B755UB2750-4F0-XX-W2A_3000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P983006
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123IW-B755UB2750-4F0-XX-W2A_3000K
Description: Define 3 Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3074.0 lumens
Efficiency: N/A
Efficacy: 132.5 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 23.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P983006

CATALOG NUMBER: S123IW-B755UB2750-4F0-XX-W2A_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P983006

CATALOG NUMBER: S123IW-B755UB2750-4F0-XX-W2A_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P983006

CATALOG NUMBER: S123IW-B755UB2750-4F0-XX-W2A_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.0	0.1
90°-100°	35.5	1.2
100°-110°	171.8	5.6
110°-120°	421.0	13.7
120°-130°	534.5	17.4
130°-140°	571.0	18.6
140°-150°	533.9	17.4
150°-160°	430.6	14.0
160°-170°	277.9	9.0
170°-180°	95.8	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.0	0.1
90°-120°	628.3	20.4
90°-150°	2267.7	73.8
90°-180°	3072.0	99.9
0°-180°	3074.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	8	18	21	22	3
95°	46	15	23	28	28	55
105°	223	231	164	31	33	237
115°	418	423	430	437	440	413
125°	590	596	599	600	602	527
135°	734	739	742	744	742	565
145°	848	853	854	856	856	531
155°	934	932	933	937	932	430
165°	984	982	982	988	982	278
175°	1008	1004	1005	1010	1004	96
180°	1008	1008	1008	1008	1008	

TEST NUMBER: P983006

CATALOG NUMBER: S123IW-B755UB2750-4F0-XX-W2A_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.7	8.2	18.0	21.0	22.5
92.5°	17.2	12.7	19.5	24.7	25.5
95°	45.7	15.0	23.2	28.4	28.4
97.5°	83.1	62.1	24.0	29.9	30.7
100°	126.5	141.5	24.7	30.7	31.4
102.5°	175.9	185.7	55.4	30.7	32.2
105°	223.1	231.3	164.0	31.4	32.9
107.5°	273.3	280.0	291.2	175.9	77.9
110°	323.4	329.4	337.6	312.9	205.9

TEST NUMBER: P983006

CATALOG NUMBER: S123IW-B755UB2750-4F0-XX-W2A_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	371.3	376.6	384.8	391.5	390.0
115°	418.5	423.0	429.7	437.2	440.2
117.5°	464.9	470.1	473.9	479.9	480.6
120°	507.6	514.3	516.6	522.6	522.6
122.5°	551.0	556.2	559.2	563.0	563.7
125°	589.9	595.9	598.9	600.4	601.9
127.5°	628.9	634.9	638.6	640.8	639.3
130°	664.8	670.8	673.8	676.8	675.3
132.5°	699.2	705.2	707.5	710.5	708.2
135°	734.4	738.9	741.9	744.2	741.9
137.5°	764.4	770.4	771.9	775.6	774.1
140°	794.3	798.8	801.1	804.0	802.5
142.5°	822.0	826.5	828.8	831.0	828.8
145°	847.5	852.7	854.2	855.7	855.7
147.5°	872.2	875.9	877.4	878.9	875.2
150°	894.6	896.9	898.4	899.9	897.6
152.5°	914.8	915.6	916.3	919.3	915.6
155°	933.6	932.1	932.8	936.6	932.1
157.5°	948.5	948.5	947.8	952.3	946.3
160°	962.0	961.3	960.5	965.0	959.8
162.5°	974.7	972.5	971.7	977.0	972.5
165°	984.5	982.2	981.5	987.5	982.2
167.5°	992.7	989.7	989.7	995.7	989.7
170°	999.4	996.4	996.4	1002.4	996.4
172.5°	1003.9	1000.2	1000.9	1006.9	1000.2
175°	1007.7	1003.9	1004.7	1009.9	1003.9
177.5°	1009.2	1005.4	1006.2	1012.2	1004.7
180°	1007.7	1007.7	1007.7	1007.7	1007.7



TEST NUMBER: P983006

CATALOG NUMBER: S123IW-B755UB2750-4F0-XX-W2A_3000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00

END OF REPORT