

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031991

Luminaire Tested: S123RDIW-B1000D1030UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031991
REPORT IS A COMBINATION OF REPORTS P993743 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B1000D1030UB30-4F0-XX-W2A-F1
Description: Define 3 Regressed Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7396.0 lumens
Efficiency: N/A
Efficacy: 94.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 78.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031991

CATALOG NUMBER: S123RDIW-B1000D1030UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1031991

CATALOG NUMBER: S123RDIW-B1000D1030UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57
1	98	94	90	87	91	87	84	81	74	72	70	62	60	59	51	50	49
2	90	83	77	72	83	77	71	67	65	61	58	55	52	50	45	43	42
3	82	73	66	60	76	68	61	56	58	53	49	49	45	42	40	38	36
4	75	65	57	51	69	60	53	48	52	46	42	44	40	37	36	33	31
5	69	58	50	44	64	54	47	41	46	41	37	39	35	32	33	30	27
6	64	52	44	38	59	48	41	36	42	36	32	36	31	28	30	27	24
7	59	47	39	34	55	44	37	32	38	32	28	33	28	25	27	24	22
8	55	43	35	30	51	40	33	28	35	29	25	30	25	22	25	22	19
9	51	39	32	27	47	37	30	25	32	27	23	27	23	20	23	20	18
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17957	17957	17957
5°	17987	17322	17276
10°	17845	16671	16343
15°	17614	15866	15321
20°	17310	14990	14179
25°	16997	14081	13097
30°	16594	13112	11818
35°	16180	12162	10653
40°	15791	11130	9366
45°	15292	10120	8209
50°	14741	9043	7011
55°	14171	7889	5914
60°	13625	6705	4801
65°	12921	5491	3747
70°	12033	4151	2678
75°	10758	2811	2122
80°	9180	1953	1489
85°	6887	1055	780

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15292 cd/sqm

TEST NUMBER: P1031991

CATALOG NUMBER: S123RDIW-B1000D1030UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.8	2.1
10°-20°	436.3	5.9
20°-30°	628.2	8.5
30°-40°	707.4	9.6
40°-50°	676.7	9.1
50°-60°	553.9	7.5
60°-70°	373.5	5.0
70°-80°	187.3	2.5
80°-90°	51.7	0.7
90°-100°	84.2	1.1
100°-110°	254.8	3.4
110°-120°	433.9	5.9
120°-130°	570.8	7.7
130°-140°	641.6	8.7
140°-150°	630.7	8.5
150°-160°	531.0	7.2
160°-170°	353.5	4.8
170°-180°	123.8	1.7
0°-30°	1221.3	16.5
0°-40°	1928.7	26.1
0°-60°	3159.3	42.7
0°-90°	3771.8	51.0
90°-120°	772.9	10.5
90°-150°	2615.9	35.4
90°-180°	3624.0	49.0
0°-180°	7396.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1668	1668	1668	1668	1668	
5°	1668	1662	1645	1658	1655	158
15°	1591	1576	1538	1532	1522	448
25°	1448	1414	1352	1323	1308	666
35°	1253	1204	1120	1062	1038	784
45°	1030	969	865	788	755	795
55°	782	716	601	522	495	701
65°	534	460	354	288	273	529
75°	283	218	143	130	127	301
85°	72	42	38	35	35	79
90°	1	11	25	29	31	9
95°	61	68	76	80	80	67
105°	231	233	242	242	244	247
115°	437	440	438	439	438	432
125°	639	642	640	636	632	570
135°	829	835	834	830	828	639
145°	1006	1008	1011	1010	1006	628
155°	1152	1152	1153	1157	1150	530
165°	1255	1252	1252	1258	1250	354
175°	1305	1301	1301	1307	1300	124
180°	1308	1308	1308	1308	1308	

TEST NUMBER: P1031991

CATALOG NUMBER: S123RDIW-B1000D1030UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1668.3	1668.3	1668.3	1668.3	1668.3
2.5°	1675.1	1669.7	1653.4	1668.3	1665.6
5°	1668.3	1661.5	1645.3	1657.5	1654.8
7.5°	1656.1	1649.4	1629.1	1637.2	1633.1
10°	1639.9	1630.4	1606.1	1607.4	1600.7
12.5°	1616.9	1606.1	1574.9	1573.6	1565.5
15°	1591.2	1576.3	1538.4	1531.6	1522.2
17.5°	1560.1	1543.8	1496.5	1482.9	1469.4
20°	1524.9	1503.2	1451.8	1434.2	1418.0
22.5°	1485.6	1459.9	1404.5	1381.5	1366.6
25°	1447.8	1413.9	1351.7	1323.3	1308.4
27.5°	1401.8	1365.2	1297.6	1259.7	1236.7
30°	1354.4	1313.8	1238.0	1192.0	1170.4
32.5°	1307.0	1259.7	1178.5	1127.1	1104.1
35°	1252.9	1204.2	1120.3	1062.1	1037.8
37.5°	1198.8	1146.0	1058.1	993.1	963.4
40°	1147.4	1087.8	991.8	921.4	890.3
42.5°	1089.2	1029.7	929.5	851.1	824.0
45°	1029.7	968.8	864.6	787.5	755.0
47.5°	971.5	903.8	801.0	717.1	688.7
50°	906.5	842.9	733.4	649.5	618.3
52.5°	848.4	778.0	669.8	581.8	554.7
55°	782.1	715.8	600.8	522.3	495.2
57.5°	722.5	650.8	534.5	460.0	437.0
60°	660.3	585.9	473.6	400.5	377.5
62.5°	598.0	523.6	411.3	343.7	319.3
65°	534.5	460.0	354.5	288.2	273.3
67.5°	470.9	395.1	292.3	242.2	226.0
70°	408.6	335.6	240.8	193.5	178.6
72.5°	346.4	274.7	190.8	154.2	150.2
75°	282.8	217.8	143.4	129.9	127.2
77.5°	224.6	165.1	112.3	104.2	101.5
80°	169.1	113.7	85.2	81.2	78.5
82.5°	116.4	70.4	60.9	56.8	56.8
85°	71.7	41.9	37.9	35.2	35.2
87.5°	32.5	17.6	17.6	16.2	14.9
90°	1.0	11.3	24.7	28.8	30.8
92.5°	30.8	37.0	43.2	46.2	44.2
95°	60.6	67.8	76.0	80.1	80.1
97.5°	99.7	104.8	111.0	116.1	115.1
100°	139.7	145.9	151.0	154.1	156.2
102.5°	186.0	189.1	196.3	199.3	198.3
105°	231.2	233.2	242.5	242.5	244.5
107.5°	284.6	285.6	289.8	292.8	291.8
110°	333.9	336.0	338.0	342.2	340.1



TEST NUMBER: P1031991

CATALOG NUMBER: S123RDIW-B1000D1030UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	385.3	386.3	386.3	391.5	391.5
115°	436.7	439.8	437.7	438.7	437.7
117.5°	489.1	490.1	488.1	488.1	485.0
120°	537.4	543.5	538.4	537.4	535.3
122.5°	587.7	591.8	589.8	586.7	583.6
125°	639.1	642.2	640.1	636.0	631.9
127.5°	686.4	692.5	690.5	684.3	680.2
130°	733.6	741.9	738.8	734.7	727.5
132.5°	780.9	789.1	787.1	781.9	776.8
135°	829.2	835.4	834.3	830.2	828.2
137.5°	873.4	878.5	881.6	876.5	873.4
140°	919.6	924.7	925.8	924.7	917.6
142.5°	961.7	966.9	968.9	967.9	962.8
145°	1005.9	1008.0	1011.1	1010.0	1005.9
147.5°	1043.9	1048.0	1051.1	1051.1	1045.0
150°	1084.0	1086.1	1088.1	1088.1	1082.0
152.5°	1116.9	1120.0	1121.0	1123.1	1117.9
155°	1151.8	1151.8	1152.8	1157.0	1149.8
157.5°	1181.6	1180.6	1181.6	1185.7	1179.6
160°	1209.4	1207.3	1207.3	1212.4	1208.3
162.5°	1234.0	1230.9	1232.0	1237.1	1229.9
165°	1254.6	1251.5	1251.5	1257.7	1250.5
167.5°	1272.0	1267.9	1269.0	1275.1	1269.0
170°	1286.4	1282.3	1282.3	1289.5	1282.3
172.5°	1297.7	1293.6	1293.6	1299.8	1292.6
175°	1304.9	1300.8	1300.8	1307.0	1299.8
177.5°	1309.0	1304.9	1304.9	1311.1	1303.9
180°	1308.0	1308.0	1308.0	1308.0	1308.0

(END OF REPORT)