

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032071

Luminaire Tested: S123RDIW-B1000D755UB35-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032071
REPORT IS A COMBINATION OF REPORTS P993925 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B1000D755UB35-4F0-XX-W2A-F1
Description: Define 3 Regressed Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6462.0 lumens
Efficiency: N/A
Efficacy: 92.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032071

CATALOG NUMBER: S123RDIW-B1000D755UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1032071

CATALOG NUMBER: S123RDIW-B1000D755UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64
1	100	96	92	89	93	90	86	83	78	75	73	67	65	64	57	56	55
2	91	84	78	73	85	79	74	69	69	65	61	59	56	54	51	49	47
3	84	74	67	61	78	70	63	58	61	56	52	53	49	46	45	43	40
4	77	66	58	52	71	62	55	50	54	49	45	47	43	40	41	38	35
5	71	59	51	45	66	56	48	43	49	43	39	43	38	35	37	33	31
6	65	53	45	39	61	50	43	38	44	38	34	39	34	31	34	30	27
7	60	48	40	35	56	45	38	33	40	34	30	35	31	27	31	27	24
8	56	44	36	31	52	41	34	30	37	31	27	32	28	24	28	25	22
9	52	40	33	28	49	38	31	26	34	28	24	30	25	22	26	23	20
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18034	18034	18034
5°	18063	17396	17349
10°	17922	16742	16411
15°	17688	15933	15385
20°	17384	15054	14239
25°	17069	14140	13153
30°	16664	13168	11868
35°	16249	12214	10698
40°	15859	11177	9406
45°	15356	10163	8244
50°	14804	9081	7042
55°	14231	7922	5939
60°	13683	6734	4821
65°	12974	5514	3763
70°	12086	4170	2690
75°	10803	2823	2130
80°	9218	1962	1494
85°	6916	1058	782

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15356 cd/sqm

TEST NUMBER: P1032071

CATALOG NUMBER: S123RDIW-B1000D755UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.5	2.4
10°-20°	438.1	6.8
20°-30°	630.8	9.8
30°-40°	710.4	11.0
40°-50°	679.5	10.5
50°-60°	556.3	8.6
60°-70°	375.0	5.8
70°-80°	188.1	2.9
80°-90°	51.2	0.8
90°-100°	62.2	1.0
100°-110°	188.1	2.9
110°-120°	320.2	5.0
120°-130°	421.3	6.5
130°-140°	473.5	7.3
140°-150°	465.5	7.2
150°-160°	391.9	6.1
160°-170°	260.9	4.0
170°-180°	91.4	1.4
0°-30°	1226.5	19.0
0°-40°	1936.9	30.0
0°-60°	3172.7	49.1
0°-90°	3787.1	58.6
90°-120°	570.5	8.8
90°-150°	1930.7	29.9
90°-180°	2675.0	41.4
0°-180°	6462.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1675	1675	1675	1675	1675	
5°	1675	1669	1652	1664	1662	159
15°	1598	1583	1545	1538	1529	450
25°	1454	1420	1357	1329	1314	669
35°	1258	1209	1125	1067	1042	788
45°	1034	973	868	791	758	798
55°	785	719	603	524	497	704
65°	537	462	356	289	274	531
75°	284	219	144	130	128	303
85°	72	42	38	35	35	79
90°	1	8	18	21	23	8
95°	45	50	56	59	59	49
105°	171	172	179	179	180	183
115°	322	325	323	324	323	319
125°	472	474	472	469	466	421
135°	612	617	616	613	611	472
145°	742	744	746	746	742	464
155°	850	850	851	854	849	391
165°	926	924	924	928	923	261
175°	963	960	960	965	959	92
180°	965	965	965	965	965	

TEST NUMBER: P1032071

CATALOG NUMBER: S123RDIW-B1000D755UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1675.4	1675.4	1675.4	1675.4	1675.4
2.5°	1682.2	1676.7	1660.4	1675.4	1672.7
5°	1675.4	1668.6	1652.3	1664.5	1661.8
7.5°	1663.2	1656.4	1636.0	1644.1	1640.1
10°	1646.9	1637.3	1612.9	1614.2	1607.4
12.5°	1623.8	1612.9	1581.6	1580.3	1572.1
15°	1597.9	1583.0	1544.9	1538.2	1528.6
17.5°	1566.7	1550.4	1502.8	1489.2	1475.6
20°	1531.4	1509.6	1458.0	1440.3	1424.0
22.5°	1492.0	1466.1	1410.4	1387.3	1372.4
25°	1453.9	1419.9	1357.4	1328.9	1314.0
27.5°	1407.7	1371.0	1303.1	1265.0	1241.9
30°	1360.1	1319.4	1243.3	1197.1	1175.4
32.5°	1312.6	1265.0	1183.5	1131.9	1108.8
35°	1258.2	1209.3	1125.1	1066.7	1042.2
37.5°	1203.9	1150.9	1062.6	997.4	967.5
40°	1152.3	1092.5	996.0	925.3	894.1
42.5°	1093.8	1034.0	933.5	854.7	827.5
45°	1034.0	972.9	868.3	790.8	758.2
47.5°	975.6	907.7	804.4	720.2	691.6
50°	910.4	846.5	736.5	652.2	621.0
52.5°	852.0	781.3	672.6	584.3	557.1
55°	785.4	718.8	603.3	524.5	497.3
57.5°	725.6	653.6	536.7	462.0	438.9
60°	663.1	588.4	475.6	402.2	379.1
62.5°	600.6	525.9	413.1	345.1	320.7
65°	536.7	462.0	356.0	289.4	274.5
67.5°	472.9	396.8	293.5	243.2	226.9
70°	410.4	337.0	241.9	194.3	179.4
72.5°	347.9	275.8	191.6	154.9	150.8
75°	284.0	218.8	144.0	130.4	127.7
77.5°	225.6	165.8	112.8	104.6	101.9
80°	169.8	114.1	85.6	81.5	78.8
82.5°	116.9	70.7	61.1	57.1	57.1
85°	72.0	42.1	38.0	35.3	35.3
87.5°	32.6	17.7	17.7	16.3	14.9
90°	0.8	8.3	18.2	21.2	22.8
92.5°	22.8	27.3	31.9	34.1	32.6
95°	44.7	50.1	56.1	59.2	59.2
97.5°	73.6	77.4	81.9	85.7	84.9
100°	103.1	107.7	111.5	113.8	115.3
102.5°	137.3	139.5	144.8	147.1	146.4
105°	170.6	172.1	179.0	179.0	180.5
107.5°	210.1	210.8	213.9	216.1	215.4
110°	246.5	248.0	249.5	252.5	251.0

TEST NUMBER: P1032071

CATALOG NUMBER: S123RDIW-B1000D755UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	284.4	285.1	285.1	288.9	288.9
115°	322.3	324.6	323.1	323.8	323.1
117.5°	361.0	361.7	360.2	360.2	358.0
120°	396.6	401.2	397.4	396.6	395.1
122.5°	433.8	436.8	435.3	433.0	430.8
125°	471.7	474.0	472.5	469.4	466.4
127.5°	506.6	511.1	509.6	505.1	502.0
130°	541.5	547.5	545.3	542.2	536.9
132.5°	576.4	582.4	580.9	577.1	573.3
135°	612.0	616.6	615.8	612.8	611.2
137.5°	644.6	648.4	650.7	646.9	644.6
140°	678.7	682.5	683.3	682.5	677.2
142.5°	709.8	713.6	715.1	714.4	710.6
145°	742.4	744.0	746.2	745.5	742.4
147.5°	770.5	773.5	775.8	775.8	771.3
150°	800.1	801.6	803.1	803.1	798.6
152.5°	824.3	826.6	827.4	828.9	825.1
155°	850.1	850.1	850.9	853.9	848.6
157.5°	872.1	871.4	872.1	875.2	870.6
160°	892.6	891.1	891.1	894.9	891.8
162.5°	910.8	908.5	909.3	913.1	907.8
165°	926.0	923.7	923.7	928.2	922.9
167.5°	938.9	935.8	936.6	941.1	936.6
170°	949.5	946.4	946.4	951.8	946.4
172.5°	957.8	954.8	954.8	959.3	954.0
175°	963.1	960.1	960.1	964.6	959.3
177.5°	966.2	963.1	963.1	967.7	962.4
180°	965.4	965.4	965.4	965.4	965.4

(END OF REPORT)