

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032500

Luminaire Tested: S124DIW-B1020D1560UB2750-4F0-XX-W2A-D_2700K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032500
REPORT IS A COMBINATION OF REPORTS P996769 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B1020D1560UB2750-4F0-XX-W2A-D_2700K
Description: Define 4 Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10428.0 lumens
Efficiency: N/A
Efficacy: 105.3 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 99
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032500

CATALOG NUMBER: S124DIW-B1020D1560UB2750-4F0-XX-W2A-D_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1032500

CATALOG NUMBER: S124DIW-B1020D1560UB2750-4F0-XX-W2A-D_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44
1	94	90	85	82	85	81	78	75	65	63	61	51	49	48	38	37	36
2	85	78	71	66	77	70	65	60	57	53	50	44	42	39	33	31	29
3	78	68	61	55	70	62	55	50	50	45	41	39	36	33	29	27	25
4	71	60	52	46	64	54	48	42	44	39	35	34	31	28	25	23	21
5	65	53	45	39	58	48	41	36	39	34	30	31	27	24	23	20	18
6	60	48	39	34	54	43	36	31	35	30	26	28	24	21	21	18	16
7	55	43	35	29	50	39	32	27	32	26	23	25	21	18	19	16	14
8	51	39	31	26	46	35	28	24	29	24	20	23	19	16	17	14	12
9	47	35	28	23	43	32	26	21	26	21	18	21	17	14	16	13	11
10	44	32	25	20	40	29	23	19	24	19	16	19	16	13	15	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9921	9921	9921
5°	9948	9663	9680
10°	9884	9472	9445
15°	9791	9259	9181
20°	9654	9027	8923
25°	9499	8772	8646
30°	9333	8519	8363
35°	9144	8261	8111
40°	8992	8012	7851
45°	8768	7780	7620
50°	8577	7515	7378
55°	8379	7260	7098
60°	8072	6942	6834
65°	7734	6601	6517
70°	7324	6209	6151
75°	6752	5776	5802
80°	6108	5332	5436
85°	5254	4887	5140

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8768 cd/sqm

TEST NUMBER: P1032500

CATALOG NUMBER: S124DIW-B1020D1560UB2750-4F0-XX-W2A-D_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.3	1.1
10°-20°	330.3	3.2
20°-30°	499.4	4.8
30°-40°	604.2	5.8
40°-50°	638.7	6.1
50°-60°	601.1	5.8
60°-70°	498.8	4.8
70°-80°	350.0	3.4
80°-90°	201.5	1.9
90°-100°	184.8	1.8
100°-110°	530.4	5.1
110°-120°	905.0	8.7
120°-130°	1107.6	10.6
130°-140°	1164.0	11.2
140°-150°	1077.9	10.3
150°-160°	867.0	8.3
160°-170°	559.1	5.4
170°-180°	192.7	1.8
0°-30°	945.0	9.1
0°-40°	1549.1	14.9
0°-60°	2789.0	26.7
0°-90°	3839.4	36.8
90°-120°	1620.2	15.5
90°-150°	4969.8	47.7
90°-180°	6589.0	63.2
0°-180°	10428.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1217	1217	1217	1217	1217	
5°	1218	1214	1204	1215	1214	116
15°	1168	1169	1165	1177	1176	329
25°	1068	1076	1080	1095	1097	492
35°	935	951	965	984	988	585
45°	779	805	831	854	861	602
55°	610	639	680	707	715	544
65°	422	466	512	546	557	419
75°	234	285	342	380	392	249
85°	72	129	191	232	245	75
90°	26	98	168	217	231	19
95°	101	95	152	198	212	117
105°	469	505	563	611	567	492
115°	861	878	920	953	962	848
125°	1204	1209	1240	1270	1280	1075
135°	1489	1488	1504	1528	1539	1148
145°	1716	1719	1719	1728	1737	1072
155°	1880	1881	1876	1882	1878	867
165°	1983	1975	1975	1987	1974	560
175°	2028	2019	2021	2034	2016	193
180°	2028	2028	2028	2028	2028	

TEST NUMBER: P1032500

CATALOG NUMBER: S124DIW-B1020D1560UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1216.6	1216.6	1216.6	1216.6	1216.6
2.5°	1222.1	1218.0	1207.1	1216.6	1215.3
5°	1218.0	1213.9	1204.4	1215.3	1213.9
7.5°	1209.8	1207.1	1198.9	1211.2	1209.8
10°	1198.9	1197.6	1190.7	1203.0	1201.6
12.5°	1183.9	1183.9	1179.8	1190.7	1190.7
15°	1167.6	1168.9	1164.9	1177.1	1175.8
17.5°	1145.8	1149.9	1148.5	1160.8	1159.4
20°	1122.6	1126.7	1128.1	1141.7	1141.7
22.5°	1096.7	1102.2	1104.9	1118.5	1121.3
25°	1068.1	1076.3	1080.4	1095.4	1096.7
27.5°	1036.8	1049.1	1054.5	1068.1	1069.5
30°	1005.5	1016.4	1025.9	1040.9	1043.6
32.5°	971.4	985.0	995.9	1013.6	1016.4
35°	934.6	951.0	964.6	983.7	987.7
37.5°	897.8	916.9	933.3	952.3	956.4
40°	862.4	880.1	899.2	919.6	925.1
42.5°	821.5	842.0	865.1	888.3	892.4
45°	779.3	805.2	831.1	854.2	861.0
47.5°	739.8	765.7	795.6	818.8	827.0
50°	696.2	726.2	756.1	783.4	791.6
52.5°	652.6	682.6	718.0	745.2	753.4
55°	610.4	639.0	679.8	707.1	715.3
57.5°	562.7	598.1	637.6	670.3	677.1
60°	516.4	551.8	596.7	628.1	639.0
62.5°	471.4	510.9	555.9	587.2	598.1
65°	422.3	465.9	512.3	546.3	557.2
67.5°	376.0	422.3	471.4	505.5	516.4
70°	328.3	374.7	426.4	463.2	472.8
72.5°	282.0	329.7	385.6	421.0	431.9
75°	234.3	284.7	342.0	380.1	392.4
77.5°	189.4	242.5	302.5	340.6	354.2
80°	148.5	203.0	262.9	303.8	314.7
82.5°	107.6	164.9	224.8	267.0	279.3
85°	72.2	129.4	190.7	231.6	245.2
87.5°	45.0	100.8	160.8	200.3	212.5
90°	26.4	97.5	168.3	216.9	230.8
92.5°	43.2	87.8	158.6	205.9	216.8
95°	101.1	94.6	151.9	197.8	211.6
97.5°	175.6	248.6	145.1	188.1	201.9
100°	263.8	326.5	170.2	181.3	192.4
102.5°	363.9	412.1	482.0	176.2	187.1
105°	468.9	505.2	563.2	610.9	567.2
107.5°	567.5	595.2	653.5	695.2	710.7
110°	666.2	689.9	746.7	781.0	796.5

TEST NUMBER: P1032500

CATALOG NUMBER: S124DIW-B1020D1560UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	761.9	787.4	835.3	863.8	880.8
115°	860.7	877.5	919.6	952.6	962.1
117.5°	950.2	964.4	1009.8	1036.9	1047.8
120°	1039.8	1050.0	1088.0	1118.3	1126.2
122.5°	1124.8	1127.8	1167.7	1196.4	1202.9
125°	1203.8	1208.6	1239.5	1270.0	1279.7
127.5°	1281.1	1281.4	1316.1	1339.2	1347.2
130°	1354.2	1354.3	1380.6	1406.7	1414.9
132.5°	1422.4	1424.1	1446.5	1471.2	1477.8
135°	1489.3	1487.8	1503.5	1528.3	1539.4
137.5°	1550.0	1548.7	1561.7	1585.1	1590.5
140°	1609.1	1610.9	1615.2	1637.5	1645.8
142.5°	1660.9	1667.0	1667.1	1685.2	1690.6
145°	1715.5	1718.7	1718.7	1728.4	1736.8
147.5°	1758.0	1765.7	1764.2	1767.1	1774.0
150°	1805.0	1809.7	1808.2	1808.2	1809.7
152.5°	1843.1	1847.6	1844.6	1847.6	1846.1
155°	1879.5	1881.0	1876.5	1882.5	1878.0
157.5°	1911.3	1911.3	1905.3	1912.9	1905.3
160°	1938.7	1934.1	1932.6	1941.7	1932.6
162.5°	1962.9	1956.9	1955.3	1964.4	1953.8
165°	1982.6	1975.1	1975.1	1987.2	1973.5
167.5°	1999.3	1991.7	1990.2	2003.9	1988.7
170°	2013.0	2003.9	2005.4	2017.5	2002.4
172.5°	2022.1	2013.0	2014.5	2026.6	2009.9
175°	2028.2	2019.0	2020.6	2034.2	2016.0
177.5°	2032.7	2022.1	2025.1	2037.3	2019.0
180°	2028.2	2028.2	2028.2	2028.2	2028.2

(END OF REPORT)