

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032516

Luminaire Tested: S124DIW-B1020D470UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032516
REPORT IS A COMBINATION OF REPORTS P996836 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B1020D470UB2750-4F0-XX-W2A-D_3000K
Description: Define 4 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6081.0 lumens
Efficiency: N/A
Efficacy: 101.4 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 60
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032516

CATALOG NUMBER: S124DIW-B1020D470UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1032516

CATALOG NUMBER: S124DIW-B1020D470UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	69	69	69
1	100	95	90	86	93	89	85	81	78	75	72	68	66	64	59	57	55
2	90	82	75	69	84	77	71	66	67	63	59	59	55	52	51	48	46
3	82	72	64	57	76	67	60	54	59	53	49	52	47	43	45	41	38
4	75	63	55	48	70	59	52	46	52	46	41	46	41	37	40	36	33
5	69	56	47	41	64	53	45	39	47	40	35	41	36	32	36	31	28
6	63	50	42	35	59	47	40	34	42	36	31	37	32	28	32	28	25
7	58	45	37	31	54	43	35	30	38	32	27	34	28	24	29	25	22
8	54	41	33	27	51	39	31	26	35	28	24	31	25	22	27	23	19
9	50	38	30	24	47	36	28	23	32	26	21	28	23	19	25	21	18
10	47	34	27	22	44	33	26	21	29	23	19	26	21	18	23	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10007	10007	10007
5°	10035	9746	9764
10°	9969	9555	9527
15°	9876	9339	9260
20°	9738	9106	9001
25°	9582	8848	8722
30°	9414	8593	8436
35°	9223	8333	8182
40°	9070	8082	7919
45°	8844	7847	7686
50°	8650	7580	7441
55°	8452	7323	7159
60°	8141	7003	6893
65°	7801	6658	6574
70°	7389	6263	6205
75°	6813	5825	5852
80°	6161	5378	5483
85°	5298	4930	5186

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8844 cd/sqm

TEST NUMBER: P1032516

CATALOG NUMBER: S124DIW-B1020D470UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.3	1.9
10°-20°	333.2	5.5
20°-30°	503.7	8.3
30°-40°	609.4	10.0
40°-50°	644.3	10.6
50°-60°	606.3	10.0
60°-70°	503.1	8.3
70°-80°	353.1	5.8
80°-90°	200.3	3.3
90°-100°	138.8	2.3
100°-110°	221.7	3.6
110°-120°	314.6	5.2
120°-130°	357.8	5.9
130°-140°	361.6	5.9
140°-150°	327.6	5.4
150°-160°	261.9	4.3
160°-170°	168.9	2.8
170°-180°	58.2	1.0
0°-30°	953.2	15.7
0°-40°	1562.6	25.7
0°-60°	2813.2	46.3
0°-90°	3869.8	63.6
90°-120°	675.2	11.1
90°-150°	1722.2	28.3
90°-180°	2211.0	36.4
0°-180°	6081.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1227	1227	1227	1227	1227	
5°	1229	1224	1215	1226	1224	117
15°	1178	1179	1175	1187	1186	332
25°	1077	1086	1090	1105	1106	496
35°	943	959	973	992	996	590
45°	786	812	838	862	868	608
55°	616	644	686	713	722	549
65°	426	470	517	551	562	422
75°	236	287	345	383	396	251
85°	73	131	192	234	247	76
90°	23	83	146	189	201	16
95°	43	73	130	170	182	45
105°	150	181	234	272	267	158
115°	266	280	323	354	364	262
125°	368	368	401	429	438	329
135°	452	451	463	486	495	349
145°	519	519	519	528	534	325
155°	568	568	567	569	567	262
165°	599	597	597	600	596	169
175°	613	610	610	614	609	58
180°	613	613	613	613	613	

TEST NUMBER: P1032516

CATALOG NUMBER: S124DIW-B1020D470UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1227.2	1227.2	1227.2	1227.2	1227.2
2.5°	1232.7	1228.6	1217.6	1227.2	1225.8
5°	1228.6	1224.4	1214.8	1225.8	1224.4
7.5°	1220.3	1217.6	1209.3	1221.7	1220.3
10°	1209.3	1208.0	1201.1	1213.4	1212.1
12.5°	1194.2	1194.2	1190.1	1201.1	1201.1
15°	1177.7	1179.1	1175.0	1187.3	1186.0
17.5°	1155.7	1159.9	1158.5	1170.8	1169.5
20°	1132.4	1136.5	1137.9	1151.6	1151.6
22.5°	1106.3	1111.8	1114.5	1128.2	1131.0
25°	1077.4	1085.6	1089.8	1104.9	1106.3
27.5°	1045.8	1058.2	1063.7	1077.4	1078.8
30°	1014.2	1025.2	1034.8	1049.9	1052.7
32.5°	979.8	993.6	1004.6	1022.4	1025.2
35°	942.7	959.2	973.0	992.2	996.3
37.5°	905.6	924.9	941.4	960.6	964.7
40°	869.9	887.8	907.0	927.6	933.1
42.5°	828.7	849.3	872.6	896.0	900.1
45°	786.1	812.2	838.3	861.6	868.5
47.5°	746.2	772.3	802.6	825.9	834.2
50°	702.2	732.5	762.7	790.2	798.4
52.5°	658.3	688.5	724.2	751.7	760.0
55°	615.7	644.5	685.7	713.2	721.5
57.5°	567.6	603.3	643.1	676.1	683.0
60°	520.8	556.6	601.9	633.5	644.5
62.5°	475.5	515.3	560.7	592.3	603.3
65°	426.0	470.0	516.7	551.1	562.1
67.5°	379.3	426.0	475.5	509.8	520.8
70°	331.2	377.9	430.1	467.2	476.9
72.5°	284.5	332.6	388.9	424.6	435.6
75°	236.4	287.2	344.9	383.4	395.8
77.5°	191.0	244.6	305.1	343.6	357.3
80°	149.8	204.8	265.2	306.5	317.4
82.5°	108.6	166.3	226.7	269.4	281.7
85°	72.8	130.6	192.4	233.6	247.4
87.5°	45.3	101.7	162.2	202.0	214.4
90°	23.4	83.4	146.1	188.7	200.6
92.5°	27.5	74.7	137.4	178.7	189.7
95°	43.1	72.8	129.7	169.5	182.3
97.5°	64.6	114.5	122.8	160.8	173.6
100°	90.2	134.2	124.6	153.9	164.0
102.5°	120.5	156.2	214.0	146.6	157.6
105°	150.3	180.6	233.7	272.2	266.6
107.5°	180.1	204.8	256.1	292.8	304.2
110°	209.0	229.5	280.4	312.9	325.3



TEST NUMBER: P1032516

CATALOG NUMBER: S124DIW-B1020D470UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	236.9	256.1	302.4	332.2	345.0
115°	265.7	279.5	323.0	354.2	363.8
117.5°	292.8	302.9	345.5	373.9	384.9
120°	318.9	324.9	364.2	392.6	402.7
122.5°	344.6	345.5	383.5	411.5	420.2
125°	367.5	367.9	401.4	428.9	437.5
127.5°	390.9	389.9	419.7	444.0	453.2
130°	411.9	411.0	434.4	459.6	467.8
132.5°	432.5	432.1	450.4	474.2	482.0
135°	451.8	451.3	462.8	485.7	494.9
137.5°	470.1	468.8	476.6	498.1	504.5
140°	488.0	487.6	489.8	509.1	516.4
142.5°	502.7	504.5	503.6	519.6	525.1
145°	519.2	519.2	519.2	527.8	534.2
147.5°	532.0	533.4	532.9	534.8	540.7
150°	546.2	546.7	546.2	546.2	546.7
152.5°	556.7	558.1	557.2	558.1	557.7
155°	567.7	568.2	566.8	568.7	567.3
157.5°	577.4	577.4	575.5	577.8	575.5
160°	585.6	584.2	583.8	586.5	583.8
162.5°	592.9	591.1	590.6	593.4	590.2
165°	598.9	596.6	596.6	600.3	596.1
167.5°	603.9	601.6	601.2	605.3	600.7
170°	608.1	605.3	605.8	609.4	604.9
172.5°	610.8	608.1	608.5	612.2	607.1
175°	612.6	609.9	610.4	614.5	609.0
177.5°	614.0	610.8	611.7	615.4	609.9
180°	612.6	612.6	612.6	612.6	612.6

(END OF REPORT)