

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032522

Luminaire Tested: S124DIW-B1020D470UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032522
REPORT IS A COMBINATION OF REPORTS P996844 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B1020D470UB2750-4F0-XX-W2A-F_3500K
Description: Define 4 Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6326.0 lumens
Efficiency: N/A
Efficacy: 105.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 60
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032522

CATALOG NUMBER: S124DIW-B1020D470UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1032522

CATALOG NUMBER: S124DIW-B1020D470UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74
1	102	98	94	90	96	93	89	86	83	80	78	74	72	70	66	64	63
2	93	85	79	74	88	81	75	70	73	68	64	65	61	58	58	55	53
3	85	75	67	61	80	71	64	59	64	59	54	57	53	49	51	48	45
4	78	67	58	52	73	63	56	50	57	51	46	51	46	42	46	42	39
5	72	59	51	45	67	57	49	43	51	45	40	46	41	37	41	37	34
6	66	53	45	39	62	51	43	38	46	40	35	42	36	32	38	33	30
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	34	30	27
8	57	44	36	31	54	42	35	30	38	32	28	35	30	26	32	27	24
9	53	40	33	27	50	39	31	27	35	29	25	32	27	23	29	25	22
10	50	37	30	25	47	36	29	24	33	27	22	30	25	21	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14045	14045	14045
5°	14058	13642	13658
10°	13938	13262	13170
15°	13739	12812	12620
20°	13483	12326	12049
25°	13196	11811	11436
30°	12849	11254	10762
35°	12491	10685	10110
40°	12116	10073	9418
45°	11723	9457	8771
50°	11289	8861	8053
55°	10818	8165	7341
60°	10334	7403	6598
65°	9781	6615	5762
70°	9145	5668	4866
75°	8193	4568	3897
80°	6984	3304	2741
85°	5421	1840	1476

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11723 cd/sqm

TEST NUMBER: P1032522

CATALOG NUMBER: S124DIW-B1020D470UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.3	2.6
10°-20°	457.4	7.2
20°-30°	673.1	10.6
30°-40°	782.5	12.4
40°-50°	782.4	12.4
50°-60°	684.3	10.8
60°-70°	508.0	8.0
70°-80°	288.3	4.6
80°-90°	83.8	1.3
90°-100°	20.4	0.3
100°-110°	134.5	2.1
110°-120°	256.8	4.1
120°-130°	326.0	5.2
130°-140°	348.8	5.5
140°-150°	326.1	5.2
150°-160°	263.0	4.2
160°-170°	169.6	2.7
170°-180°	58.5	0.9
0°-30°	1292.9	20.4
0°-40°	2075.4	32.8
0°-60°	3542.1	56.0
0°-90°	4422.3	69.9
90°-120°	411.7	6.5
90°-150°	1412.7	22.3
90°-180°	1904.0	30.1
0°-180°	6326.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1722	1722	1722	1722	1722	
5°	1721	1716	1700	1716	1713	163
15°	1638	1633	1612	1620	1616	462
25°	1484	1474	1455	1456	1451	683
35°	1277	1267	1248	1238	1231	798
45°	1042	1032	1010	995	991	803
55°	788	784	765	748	740	706
65°	534	527	513	500	493	529
75°	284	277	270	265	264	302
85°	74	74	72	72	70	80
90°	1	6	10	13	14	6
95°	25	10	10	13	13	31
105°	138	141	144	148	131	145
115°	259	260	260	260	260	255
125°	364	365	364	366	366	325
135°	451	450	452	453	454	347
145°	520	521	521	522	523	325
155°	570	571	569	571	570	263
165°	601	599	599	603	599	170
175°	615	612	613	617	612	59
180°	615	615	615	615	615	

TEST NUMBER: P1032522

CATALOG NUMBER: S124DIW-B1020D470UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1722.4	1722.4	1722.4	1722.4	1722.4
2.5°	1728.0	1723.8	1708.6	1722.4	1721.1
5°	1721.1	1715.5	1700.4	1715.5	1712.8
7.5°	1708.6	1703.1	1686.6	1699.0	1697.6
10°	1690.7	1685.2	1667.2	1678.3	1675.5
12.5°	1667.2	1661.7	1642.4	1654.8	1650.7
15°	1638.3	1632.7	1612.0	1620.3	1616.2
17.5°	1605.1	1598.2	1578.9	1584.4	1581.7
20°	1567.9	1561.0	1540.3	1544.4	1541.6
22.5°	1527.8	1518.2	1497.5	1505.8	1500.2
25°	1483.7	1474.0	1454.7	1456.1	1450.6
27.5°	1434.0	1424.3	1406.4	1403.6	1396.7
30°	1384.3	1373.3	1355.3	1349.8	1342.9
32.5°	1331.9	1322.2	1302.9	1296.0	1289.1
35°	1276.7	1267.0	1247.7	1238.0	1231.1
37.5°	1218.7	1210.4	1189.7	1180.0	1170.4
40°	1162.1	1151.1	1130.4	1116.6	1109.7
42.5°	1101.4	1095.9	1072.4	1055.8	1051.7
45°	1042.0	1032.4	1010.3	995.1	991.0
47.5°	979.9	973.0	952.3	935.8	924.7
50°	916.4	910.9	891.6	872.3	864.0
52.5°	854.3	847.4	826.7	810.2	799.1
55°	788.1	783.9	764.6	748.1	739.8
57.5°	726.0	721.8	702.5	685.9	677.7
60°	661.1	654.2	636.3	623.8	616.9
62.5°	597.6	592.1	572.8	561.7	554.8
65°	534.1	527.2	513.4	499.6	492.7
67.5°	469.3	463.7	449.9	436.1	434.8
70°	409.9	400.2	389.2	378.2	374.0
72.5°	346.4	336.8	328.5	320.2	316.1
75°	284.3	277.4	270.5	265.0	263.6
77.5°	223.6	220.8	213.9	212.5	208.4
80°	169.8	165.6	162.9	160.1	158.7
82.5°	117.3	115.9	115.9	114.6	113.2
85°	74.5	74.5	71.8	71.8	70.4
87.5°	35.9	34.5	33.1	33.1	33.1
90°	1.4	6.4	10.1	12.9	13.8
92.5°	6.9	6.0	9.7	12.4	12.4
95°	25.3	9.7	10.1	12.9	13.3
97.5°	48.3	58.4	10.1	12.4	12.9
100°	75.5	83.7	20.2	12.4	12.9
102.5°	105.8	111.4	116.9	13.3	13.3
105°	138.5	141.3	143.6	147.7	131.1
107.5°	168.4	169.8	173.0	175.3	177.2
110°	198.8	200.2	202.9	203.8	205.2

TEST NUMBER: P1032522

CATALOG NUMBER: S124DIW-B1020D470UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	228.2	231.0	231.9	231.5	233.3
115°	258.6	260.0	259.5	260.4	260.4
117.5°	285.8	287.6	289.0	288.5	288.5
120°	313.4	315.2	314.7	315.7	314.7
122.5°	339.1	340.1	341.0	341.4	340.5
125°	363.5	365.4	364.4	365.8	366.3
127.5°	387.0	387.5	389.8	389.3	388.8
130°	409.5	410.0	411.4	411.8	411.8
132.5°	430.2	431.2	433.0	433.5	433.0
135°	451.0	450.5	452.3	453.3	454.2
137.5°	469.4	469.4	471.7	472.6	472.1
140°	487.3	488.2	489.1	490.5	491.0
142.5°	503.4	505.3	505.7	506.6	506.6
145°	520.0	521.4	521.4	521.8	522.7
147.5°	532.9	535.6	535.2	535.6	536.1
150°	547.1	549.0	548.5	548.5	549.0
152.5°	559.1	560.5	559.5	560.5	560.0
155°	570.1	570.6	569.2	571.1	569.7
157.5°	579.8	579.8	578.0	580.3	578.0
160°	588.1	586.7	586.2	589.0	586.2
162.5°	595.4	593.6	593.1	595.9	592.7
165°	601.4	599.1	599.1	602.8	598.7
167.5°	606.5	604.2	603.7	607.9	603.3
170°	610.6	607.9	608.3	612.0	607.4
172.5°	613.4	610.6	611.1	614.8	609.7
175°	615.2	612.5	612.9	617.1	611.5
177.5°	616.6	613.4	614.3	618.0	612.5
180°	615.2	615.2	615.2	615.2	615.2

(END OF REPORT)