

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032111

Luminaire Tested: S123RDIW-B1165D1320UB40-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032111
REPORT IS A COMBINATION OF REPORTS P994016 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B1165D1320UB40-4F0-XX-W2A-A1
Description: Define 3 Regressed Direct/Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9110.0 lumens
Efficiency: N/A
Efficacy: 88.1 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 103.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032111

CATALOG NUMBER: S123RDIW-B1165D1320UB40-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1032111

CATALOG NUMBER: S123RDIW-B1165D1320UB40-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	94	91	87	91	87	84	81	74	72	70	62	60	59	51	50	49
2	90	83	77	72	83	77	72	68	65	62	59	55	52	50	45	43	42
3	83	73	66	61	76	68	62	57	58	54	50	49	46	43	41	38	36
4	76	65	58	52	70	61	54	49	52	47	43	44	40	37	37	34	32
5	70	59	51	45	64	55	48	42	47	42	37	40	36	33	33	30	28
6	64	53	45	39	59	49	42	37	42	37	33	36	32	29	30	27	25
7	60	48	40	35	55	45	38	33	39	33	29	33	29	26	28	25	22
8	55	43	36	31	51	41	34	29	35	30	26	30	26	23	26	22	20
9	52	40	32	28	48	37	31	26	32	27	23	28	24	21	24	21	18
10	48	37	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	19695	19695	19695	19695
5°	19710	22682	19760	16828
10°	19535	27382	19620	14698
15°	19335	31076	19335	12961
20°	18938	33520	19044	11497
25°	18648	31847	18611	10490
30°	18310	22066	18272	9507
35°	17904	14167	17823	8763
40°	17399	10004	17312	8026
45°	16517	8006	16495	7307
50°	15437	6697	15386	6466
55°	14220	5519	14108	5482
60°	13026	4562	12896	4662
65°	11625	3651	11702	3951
70°	10334	2537	10610	3194
75°	8760	1882	9118	2457
80°	6976	1248	7568	1841
85°	4966	590	5417	1146

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 26293 cd/sqm

TEST NUMBER: P1032111

CATALOG NUMBER: S123RDIW-B1165D1320UB40-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.7	2.0
10°-20°	562.5	6.2
20°-30°	885.9	9.7
30°-40°	921.2	10.1
40°-50°	788.1	8.7
50°-60°	600.8	6.6
60°-70°	384.9	4.2
70°-80°	184.4	2.0
80°-90°	52.0	0.6
90°-100°	105.7	1.2
100°-110°	320.0	3.5
110°-120°	544.7	6.0
120°-130°	716.6	7.9
130°-140°	805.5	8.8
140°-150°	791.9	8.7
150°-160°	666.7	7.3
160°-170°	443.9	4.9
170°-180°	155.4	1.7
0°-30°	1628.0	17.9
0°-40°	2549.2	28.0
0°-60°	3938.1	43.2
0°-90°	4559.5	50.0
90°-120°	970.5	10.7
90°-150°	3284.6	36.1
90°-180°	4551.0	50.0
0°-180°	9110.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1830	1830	1830	1830	1830	
5°	1828	2173	1833	1612	1828	173
15°	1747	3088	1747	1288	1747	491
25°	1588	3182	1585	1048	1588	732
35°	1386	1380	1380	854	1386	868
45°	1112	736	1111	672	1112	856
55°	785	462	779	459	785	703
65°	481	266	484	288	481	480
75°	230	113	240	147	230	249
85°	52	27	56	52	52	58
90°	1	39	1	39	1	8
95°	76	101	76	101	76	84
105°	290	307	290	307	290	311
115°	548	550	548	550	548	543
125°	802	793	802	793	802	716
135°	1041	1040	1041	1040	1041	802
145°	1263	1263	1263	1263	1263	789
155°	1446	1444	1446	1444	1446	666
165°	1575	1570	1575	1570	1575	444
175°	1638	1632	1638	1632	1638	156
180°	1642	1642	1642	1642	1642	

TEST NUMBER: P1032111

CATALOG NUMBER: S123RDIW-B1165D1320UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7
2.5°	1834.4	1846.9	1856.3	1862.6	1878.2	1887.6	1895.5	1909.6	1909.6	1912.7	1919.0
5°	1828.1	1854.7	1873.5	1898.6	1931.5	1947.2	1969.1	1987.9	2014.5	2028.6	2042.7
7.5°	1814.0	1851.6	1890.8	1928.4	1976.9	2008.3	2030.2	2078.8	2113.2	2155.5	2188.4
10°	1795.2	1846.9	1897.0	1955.0	2020.8	2067.8	2100.7	2164.9	2230.7	2290.2	2340.4
12.5°	1771.7	1834.4	1906.4	1976.9	2069.4	2116.3	2169.6	2249.5	2343.5	2418.7	2486.0
15°	1746.7	1818.7	1900.2	1986.3	2102.3	2168.0	2244.8	2341.9	2446.9	2555.0	2647.4
17.5°	1707.5	1798.3	1889.2	2014.5	2150.8	2190.0	2255.8	2388.9	2518.9	2616.1	2728.9
20°	1668.3	1770.2	1884.5	1997.3	2144.5	2235.4	2296.5	2437.5	2576.9	2694.4	2802.5
22.5°	1632.3	1738.8	1857.9	2000.4	2138.3	2229.1	2305.9	2453.1	2614.5	2746.1	2879.2
25°	1588.4	1704.4	1835.9	1970.7	2138.3	2207.2	2291.8	2462.5	2633.3	2785.2	2949.7
27.5°	1541.4	1658.9	1788.9	1926.8	2080.3	2182.1	2265.2	2448.4	2656.8	2819.7	2988.9
30°	1494.4	1615.1	1740.4	1864.1	2036.5	2133.6	2229.1	2431.2	2669.3	2855.7	2985.8
32.5°	1449.0	1550.8	1674.6	1795.2	1966.0	2072.5	2180.6	2414.0	2674.0	2830.7	2893.3
35°	1386.4	1492.9	1593.1	1721.6	1893.9	1998.9	2125.7	2412.4	2653.7	2750.8	2719.5
37.5°	1328.4	1417.7	1513.2	1627.6	1804.6	1940.9	2072.5	2371.7	2586.3	2592.6	2415.6
40°	1264.2	1337.8	1417.7	1538.3	1729.4	1864.1	2006.7	2309.0	2464.1	2371.7	2060.0
42.5°	1190.5	1256.3	1319.0	1436.5	1644.8	1795.2	1948.7	2230.7	2287.1	2074.1	1749.8
45°	1112.2	1165.5	1223.4	1347.2	1555.5	1704.4	1857.9	2110.1	2052.1	1751.4	1442.8
47.5°	1030.8	1076.2	1132.6	1245.4	1460.0	1611.9	1757.6	1937.8	1790.5	1467.8	1209.3
50°	949.3	985.3	1040.2	1156.1	1362.9	1500.7	1635.4	1752.9	1546.1	1259.5	999.4
52.5°	869.4	897.6	954.0	1052.7	1253.2	1384.8	1481.9	1527.3	1317.4	1040.2	867.8
55°	784.8	816.1	853.7	954.0	1152.9	1250.1	1314.3	1312.7	1096.6	881.9	717.5
57.5°	703.4	731.6	764.5	864.7	1026.1	1091.9	1146.7	1120.1	914.8	722.2	615.6
60°	631.3	647.0	683.0	767.6	889.8	946.2	977.5	932.1	747.2	609.4	509.1
62.5°	553.0	568.6	598.4	678.3	753.5	783.3	809.9	751.9	617.2	496.6	435.5
65°	480.9	501.3	520.1	584.3	625.0	661.1	657.9	609.4	482.5	404.2	354.0
67.5°	418.3	426.1	441.8	480.9	499.7	526.3	527.9	473.1	388.5	329.0	299.2
70°	350.9	358.7	369.7	388.5	401.0	407.3	404.2	355.6	292.9	256.9	230.3
72.5°	292.9	291.4	299.2	299.2	311.7	310.2	300.8	263.2	222.4	192.7	177.0
75°	230.3	231.8	233.4	230.3	225.6	219.3	211.5	183.3	156.7	142.6	128.5
77.5°	180.1	177.0	178.6	167.6	161.4	155.1	144.1	130.0	108.1	105.0	98.7
80°	128.5	126.9	125.3	120.6	106.5	100.3	92.4	84.6	79.9	76.8	75.2
82.5°	86.2	86.2	83.0	73.6	65.8	61.1	59.5	56.4	51.7	51.7	50.1
85°	51.7	50.1	47.0	37.6	32.9	32.9	32.9	32.9	29.8	29.8	28.2
87.5°	20.4	18.8	14.1	14.1	12.5	12.5	12.5	11.0	11.0	9.4	9.4
90°	1.3	4.2	7.0	9.9	12.8	14.2	16.1	19.8	23.5	27.3	31.0
92.5°	38.7	40.4	42.1	43.8	45.5	46.4	47.3	49.0	50.7	52.5	54.2
95°	76.1	78.1	80.1	82.1	84.1	85.1	86.3	88.6	90.9	93.2	95.5
97.5°	125.1	126.5	128.0	129.4	130.9	131.6	132.5	134.2	135.9	137.6	139.3
100°	175.5	177.2	178.9	180.6	182.3	183.2	183.9	185.3	186.8	188.2	189.6
102.5°	233.5	234.4	235.2	236.1	237.0	237.4	238.4	240.4	242.4	244.4	246.4
105°	290.3	290.9	291.5	292.0	292.6	292.9	294.2	296.8	299.3	301.9	304.5
107.5°	357.4	357.7	357.9	358.2	358.5	358.6	359.2	360.3	361.5	362.6	363.8
110°	419.3	419.9	420.5	421.0	421.6	421.9	422.2	422.7	423.3	423.8	424.4

TEST NUMBER: P1032111

CATALOG NUMBER: S123RDIW-B1165D1320UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	483.8	484.1	484.4	484.7	485.0	485.1	485.1	485.1	485.1	485.1	485.1
115°	548.3	549.2	550.0	550.9	551.8	552.2	551.9	551.3	550.8	550.2	549.6
117.5°	614.1	614.4	614.7	615.0	615.3	615.4	615.1	614.5	614.0	613.4	612.8
120°	674.7	676.4	678.2	679.9	681.6	682.5	681.8	680.3	678.9	677.4	676.0
122.5°	737.9	739.1	740.2	741.4	742.5	743.1	742.8	742.2	741.7	741.1	740.5
125°	802.4	803.3	804.1	805.0	805.9	806.3	806.0	805.4	804.9	804.3	803.7
127.5°	861.8	863.5	865.2	866.9	868.6	869.5	869.2	868.7	868.1	867.6	867.0
130°	921.1	923.4	925.7	928.0	930.3	931.5	931.1	930.2	929.3	928.5	927.6
132.5°	980.5	982.8	985.1	987.4	989.7	990.8	990.5	989.9	989.4	988.8	988.2
135°	1041.1	1042.8	1044.6	1046.3	1048.0	1048.9	1048.8	1048.5	1048.2	1047.9	1047.6
137.5°	1096.6	1098.0	1099.4	1100.9	1102.3	1103.0	1103.4	1104.3	1105.2	1106.0	1106.9
140°	1154.6	1156.0	1157.5	1158.9	1160.4	1161.1	1161.2	1161.5	1161.8	1162.1	1162.4
142.5°	1207.5	1208.9	1210.4	1211.8	1213.3	1214.0	1214.3	1214.9	1215.4	1216.0	1216.6
145°	1263.0	1263.6	1264.2	1264.7	1265.3	1265.6	1266.0	1266.9	1267.8	1268.6	1269.5
147.5°	1310.7	1311.9	1313.0	1314.2	1315.3	1315.9	1316.3	1317.2	1318.1	1318.9	1319.8
150°	1361.1	1361.7	1362.2	1362.8	1363.3	1363.6	1363.9	1364.5	1365.0	1365.6	1366.2
152.5°	1402.3	1403.2	1404.0	1404.9	1405.8	1406.2	1406.3	1406.6	1406.9	1407.2	1407.5
155°	1446.2	1446.2	1446.2	1446.2	1446.2	1446.2	1446.3	1446.6	1446.9	1447.2	1447.5
157.5°	1483.6	1483.3	1483.0	1482.7	1482.4	1482.3	1482.4	1482.7	1483.0	1483.3	1483.6
160°	1518.5	1517.9	1517.3	1516.8	1516.2	1515.9	1515.9	1515.9	1515.9	1515.9	1515.9
162.5°	1549.4	1548.5	1547.7	1546.8	1545.9	1545.5	1545.6	1545.9	1546.2	1546.5	1546.8
165°	1575.2	1574.3	1573.5	1572.6	1571.7	1571.3	1571.3	1571.3	1571.3	1571.3	1571.3
167.5°	1597.2	1596.0	1594.9	1593.7	1592.6	1592.0	1592.1	1592.4	1592.7	1593.0	1593.3
170°	1615.2	1614.1	1612.9	1611.8	1610.7	1610.1	1610.1	1610.1	1610.1	1610.1	1610.1
172.5°	1629.4	1628.2	1627.1	1625.9	1624.8	1624.2	1624.2	1624.2	1624.2	1624.2	1624.2
175°	1638.4	1637.3	1636.1	1635.0	1633.9	1633.3	1633.3	1633.3	1633.3	1633.3	1633.3
177.5°	1643.6	1642.4	1641.3	1640.1	1639.0	1638.4	1638.4	1638.4	1638.4	1638.4	1638.4
180°	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3

TEST NUMBER: P1032111

CATALOG NUMBER: S123RDIW-B1165D1320UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7
2.5°	1931.5	1931.5	1945.6	1959.7	1951.9	1956.6	1973.8	1967.5	1980.1	1978.5	1983.2
5°	2077.2	2094.4	2108.5	2138.3	2143.0	2138.3	2168.0	2175.9	2190.0	2172.7	2180.6
7.5°	2241.7	2277.7	2312.2	2356.0	2370.1	2373.3	2388.9	2410.9	2429.6	2395.2	2412.4
10°	2401.5	2456.3	2526.8	2565.9	2600.4	2612.9	2625.5	2639.6	2661.5	2681.9	2666.2
12.5°	2573.8	2653.7	2721.0	2791.5	2833.8	2829.1	2865.1	2874.5	2891.8	2896.5	2902.7
15°	2714.8	2827.5	2869.8	2974.8	2984.2	3015.5	3056.3	3092.3	3097.0	3087.6	3087.6
17.5°	2849.5	2946.6	3021.8	3106.4	3123.6	3150.2	3201.9	3219.2	3225.4	3223.9	3223.9
20°	2959.1	3023.4	3150.2	3220.7	3248.9	3283.4	3319.4	3341.4	3346.1	3352.3	3342.9
22.5°	3031.2	3128.3	3231.7	3289.7	3313.2	3325.7	3349.2	3355.5	3347.6	3349.2	3350.8
25°	3087.6	3183.1	3245.8	3261.5	3259.9	3244.2	3227.0	3197.2	3194.1	3181.6	3156.5
27.5°	3103.2	3139.3	3131.4	3067.2	3003.0	2996.7	2893.3	2836.9	2772.7	2782.1	2746.1
30°	3018.7	2971.7	2860.4	2697.5	2630.2	2520.5	2404.6	2284.0	2237.0	2185.3	2280.8
32.5°	2811.9	2644.3	2446.9	2235.4	2122.6	2025.5	1901.7	1814.0	1763.9	1721.6	1803.0
35°	2500.1	2238.5	1976.9	1776.4	1684.0	1596.3	1480.3	1436.5	1373.8	1380.1	1387.9
37.5°	2099.1	1810.9	1613.5	1416.1	1355.0	1319.0	1234.4	1167.0	1145.1	1138.8	1138.8
40°	1723.2	1486.6	1311.2	1156.1	1109.1	1079.3	1012.0	980.6	957.1	950.9	958.7
42.5°	1425.5	1223.4	1087.2	983.8	950.9	913.3	885.1	845.9	841.2	830.2	844.3
45°	1196.8	1021.4	919.5	844.3	816.1	802.1	770.7	747.2	737.8	736.3	747.2
47.5°	1015.1	878.8	789.5	742.5	720.6	706.5	679.9	670.5	661.1	664.2	659.5
50°	852.2	750.4	692.4	650.1	636.0	621.9	604.7	595.3	590.6	590.6	589.0
52.5°	731.6	647.0	609.4	570.2	563.9	556.1	537.3	531.0	523.2	521.6	527.9
55°	626.6	568.6	531.0	507.5	501.3	485.6	477.8	470.0	465.3	462.1	463.7
57.5°	535.7	491.9	466.8	446.5	435.5	429.2	415.1	413.6	410.4	410.4	408.9
60°	460.6	429.2	399.5	386.9	379.1	371.3	369.7	360.3	355.6	358.7	357.2
62.5°	390.1	365.0	347.8	333.7	329.0	322.7	318.0	314.9	310.2	311.7	311.7
65°	325.8	305.5	292.9	280.4	278.8	272.6	271.0	267.9	267.9	266.3	269.4
67.5°	267.9	253.8	242.8	235.0	230.3	231.8	225.6	220.9	220.9	219.3	224.0
70°	213.0	205.2	194.2	184.8	178.6	178.6	170.7	169.2	169.2	169.2	167.6
72.5°	164.5	150.4	145.7	142.6	142.6	142.6	139.4	139.4	137.9	139.4	137.9
75°	122.2	120.6	117.5	115.9	115.9	114.4	112.8	112.8	112.8	112.8	112.8
77.5°	95.6	95.6	92.4	90.9	90.9	90.9	89.3	89.3	87.7	87.7	87.7
80°	70.5	70.5	67.4	67.4	67.4	65.8	65.8	65.8	67.4	65.8	65.8
82.5°	48.6	48.6	47.0	48.6	47.0	45.4	45.4	45.4	43.9	45.4	45.4
85°	28.2	28.2	26.6	25.1	26.6	26.6	25.1	26.6	25.1	26.6	25.1
87.5°	11.0	9.4	9.4	9.4	7.8	9.4	7.8	7.8	9.4	7.8	9.4
90°	32.1	33.3	34.4	35.5	36.1	36.4	37.0	37.5	38.1	38.7	38.1
92.5°	55.1	55.9	56.8	57.7	58.1	57.8	57.2	56.7	56.1	55.5	56.1
95°	96.6	97.8	98.9	100.0	100.6	100.6	100.6	100.6	100.6	100.6	100.6
97.5°	140.7	142.2	143.6	145.1	145.8	145.7	145.4	145.1	144.8	144.5	144.8
100°	190.5	191.3	192.2	193.1	193.5	193.8	194.4	194.9	195.5	196.1	195.5
102.5°	247.3	248.1	249.0	249.9	250.3	250.2	249.9	249.6	249.3	249.0	249.3
105°	304.5	304.5	304.5	304.5	304.5	304.8	305.3	305.9	306.4	307.0	306.4
107.5°	364.7	365.5	366.4	367.3	367.7	367.6	367.3	367.0	366.7	366.4	366.7
110°	425.6	426.7	427.9	429.0	429.6	429.3	428.7	428.2	427.6	427.0	427.6

TEST NUMBER: P1032111

CATALOG NUMBER: S123RDIW-B1165D1320UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	486.5	487.9	489.4	490.8	491.5	491.5	491.5	491.5	491.5	491.5	491.5
115°	549.9	550.2	550.5	550.8	550.9	550.8	550.5	550.2	549.9	549.6	549.9
117.5°	612.8	612.8	612.8	612.8	612.8	612.4	611.5	610.6	609.8	608.9	609.8
120°	675.7	675.4	675.1	674.8	674.7	674.4	673.8	673.3	672.7	672.1	672.7
122.5°	739.7	738.8	738.0	737.1	736.7	736.3	735.4	734.5	733.7	732.8	733.7
125°	802.6	801.4	800.3	799.2	798.6	798.0	796.9	795.7	794.6	793.4	794.6
127.5°	865.3	863.5	861.8	860.1	859.2	858.6	857.5	856.4	855.2	854.1	855.2
130°	926.4	925.3	924.1	923.0	922.4	921.4	919.4	917.4	915.4	913.4	915.4
132.5°	986.8	985.4	983.9	982.5	981.8	981.1	979.6	978.2	976.7	975.3	976.7
135°	1046.4	1045.3	1044.1	1043.0	1042.4	1042.1	1041.5	1041.0	1040.4	1039.8	1040.4
137.5°	1105.5	1104.1	1102.6	1101.2	1100.5	1100.1	1099.2	1098.3	1097.5	1096.6	1097.5
140°	1162.1	1161.8	1161.5	1161.2	1161.1	1160.1	1158.1	1156.1	1154.1	1152.1	1154.1
142.5°	1216.3	1216.0	1215.7	1215.4	1215.3	1214.6	1213.1	1211.7	1210.2	1208.8	1210.2
145°	1269.2	1268.9	1268.6	1268.3	1268.2	1267.6	1266.5	1265.3	1264.2	1263.0	1264.2
147.5°	1319.8	1319.8	1319.8	1319.8	1319.8	1318.9	1317.2	1315.5	1313.7	1312.0	1313.7
150°	1366.2	1366.2	1366.2	1366.2	1366.2	1365.3	1363.6	1361.9	1360.2	1358.5	1360.2
152.5°	1408.1	1408.7	1409.2	1409.8	1410.1	1409.4	1407.9	1406.5	1405.0	1403.6	1405.0
155°	1448.7	1449.8	1451.0	1452.1	1452.7	1451.7	1449.7	1447.6	1445.6	1443.6	1445.6
157.5°	1484.8	1485.9	1487.1	1488.2	1488.8	1487.9	1486.2	1484.5	1482.7	1481.0	1482.7
160°	1517.3	1518.7	1520.2	1521.6	1522.3	1521.7	1520.6	1519.5	1518.3	1517.2	1518.3
162.5°	1548.2	1549.7	1551.1	1552.6	1553.3	1552.3	1550.3	1548.3	1546.3	1544.3	1546.3
165°	1573.0	1574.8	1576.5	1578.2	1579.1	1578.1	1576.1	1574.1	1572.1	1570.1	1572.1
167.5°	1595.0	1596.7	1598.4	1600.1	1601.0	1600.1	1598.4	1596.7	1595.0	1593.3	1595.0
170°	1612.1	1614.1	1616.1	1618.1	1619.1	1618.1	1616.1	1614.1	1612.1	1610.1	1612.1
172.5°	1625.9	1627.7	1629.4	1631.1	1632.0	1631.0	1629.0	1627.0	1625.0	1623.0	1625.0
175°	1635.0	1636.7	1638.4	1640.1	1641.0	1640.0	1638.0	1636.0	1634.0	1632.0	1634.0
177.5°	1640.1	1641.9	1643.6	1645.3	1646.2	1645.2	1643.2	1641.1	1639.1	1637.1	1639.1
180°	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3

TEST NUMBER: P1032111

CATALOG NUMBER: S123RDIW-B1165D1320UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7
2.5°	1975.4	1966.0	1959.7	1955.0	1950.3	1964.4	1945.6	1925.2	1911.1	1901.7	1898.6
5°	2182.1	2161.8	2144.5	2130.4	2133.6	2133.6	2100.7	2064.7	2033.3	2016.1	1997.3
7.5°	2421.8	2399.9	2365.4	2357.6	2351.3	2312.2	2279.3	2213.5	2174.3	2135.1	2100.7
10°	2659.9	2631.7	2598.8	2587.9	2572.2	2523.6	2473.5	2388.9	2340.4	2268.3	2222.9
12.5°	2882.4	2847.9	2815.0	2807.2	2783.7	2741.4	2655.2	2567.5	2484.5	2407.7	2327.8
15°	3068.8	3059.4	3009.3	2977.9	2926.2	2868.3	2849.5	2730.4	2625.5	2545.6	2401.5
17.5°	3225.4	3181.6	3134.6	3114.2	3093.8	3026.5	2959.1	2836.9	2724.2	2606.7	2514.2
20°	3350.8	3302.2	3269.3	3239.5	3230.1	3153.4	3046.9	2938.8	2815.0	2683.4	2562.8
22.5°	3357.0	3350.8	3328.8	3311.6	3292.8	3242.7	3158.1	3023.4	2891.8	2747.7	2589.4
25°	3227.0	3217.6	3280.3	3264.6	3277.1	3258.3	3212.9	3100.1	2946.6	2777.4	2617.6
27.5°	2835.4	2930.9	3029.6	3064.1	3087.6	3154.9	3176.9	3114.2	2990.5	2810.3	2631.7
30°	2302.8	2429.6	2589.4	2675.6	2741.4	2866.7	3029.6	3050.0	2992.0	2847.9	2628.6
32.5°	1807.7	1923.7	2052.1	2153.9	2241.7	2498.6	2717.9	2876.1	2904.3	2829.1	2636.4
35°	1456.8	1507.0	1629.2	1726.3	1845.3	2064.7	2323.1	2578.5	2750.8	2760.2	2612.9
37.5°	1201.5	1228.1	1334.7	1389.5	1460.0	1652.7	1893.9	2227.6	2495.4	2622.3	2547.1
40°	994.7	1055.8	1116.9	1148.2	1198.4	1331.5	1563.4	1825.0	2157.1	2392.1	2445.3
42.5°	863.1	889.8	928.9	972.8	1004.1	1120.1	1275.1	1514.8	1814.0	2141.4	2288.7
45°	761.3	770.7	811.4	839.6	872.5	954.0	1063.7	1264.2	1527.3	1850.0	2100.7
47.5°	676.7	695.5	717.5	734.7	756.6	819.3	913.3	1059.0	1290.8	1579.0	1848.5
50°	601.5	612.5	640.7	648.5	664.2	708.1	780.1	891.3	1082.5	1312.7	1591.6
52.5°	531.0	551.4	562.4	573.3	587.4	623.5	670.5	761.3	905.4	1121.6	1358.2
55°	476.2	482.5	498.1	507.5	518.5	543.6	584.3	651.7	764.5	936.8	1160.8
57.5°	423.0	423.0	438.6	446.5	457.4	476.2	512.2	563.9	645.4	773.9	979.1
60°	366.6	368.1	380.7	390.1	393.2	412.0	441.8	482.5	545.1	639.1	806.8
62.5°	316.4	324.3	330.5	333.7	344.6	355.6	380.7	408.9	452.7	535.7	654.8
65°	274.1	275.7	280.4	283.5	288.2	300.8	319.6	338.4	376.0	437.1	534.2
67.5°	225.6	231.8	238.1	238.1	242.8	249.1	267.9	283.5	311.7	347.8	413.6
70°	169.2	172.3	181.7	186.4	192.7	203.6	213.0	222.4	244.4	271.0	321.1
72.5°	141.0	141.0	144.1	145.7	145.7	153.5	167.6	177.0	188.0	206.8	241.2
75°	112.8	112.8	117.5	115.9	119.1	122.2	123.8	130.0	136.3	150.4	170.7
77.5°	89.3	90.9	90.9	92.4	92.4	94.0	95.6	98.7	101.8	109.7	119.1
80°	65.8	67.4	67.4	68.9	68.9	70.5	72.1	73.6	76.8	79.9	84.6
82.5°	45.4	47.0	47.0	48.6	47.0	48.6	50.1	50.1	51.7	54.8	56.4
85°	26.6	26.6	28.2	26.6	26.6	26.6	28.2	28.2	29.8	34.5	34.5
87.5°	7.8	9.4	7.8	9.4	9.4	9.4	9.4	11.0	11.0	12.5	14.1
90°	37.5	37.0	36.4	36.1	35.5	34.4	33.3	32.1	31.0	27.3	23.5
92.5°	56.7	57.2	57.8	58.1	57.7	56.8	55.9	55.1	54.2	52.5	50.7
95°	100.6	100.6	100.6	100.6	100.0	98.9	97.8	96.6	95.5	93.2	90.9
97.5°	145.1	145.4	145.7	145.8	145.1	143.6	142.2	140.7	139.3	137.6	135.9
100°	194.9	194.4	193.8	193.5	193.1	192.2	191.3	190.5	189.6	188.2	186.8
102.5°	249.6	249.9	250.2	250.3	249.9	249.0	248.1	247.3	246.4	244.4	242.4
105°	305.9	305.3	304.8	304.5	304.5	304.5	304.5	304.5	304.5	301.9	299.3
107.5°	367.0	367.3	367.6	367.7	367.3	366.4	365.5	364.7	363.8	362.6	361.5
110°	428.2	428.7	429.3	429.6	429.0	427.9	426.7	425.6	424.4	423.8	423.3

TEST NUMBER: P1032111

CATALOG NUMBER: S123RDIW-B1165D1320UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	491.5	491.5	491.5	491.5	490.8	489.4	487.9	486.5	485.1	485.1	485.1
115°	550.2	550.5	550.8	550.9	550.8	550.5	550.2	549.9	549.6	550.2	550.8
117.5°	610.6	611.5	612.4	612.8	612.8	612.8	612.8	612.8	612.8	613.4	614.0
120°	673.3	673.8	674.4	674.7	674.8	675.1	675.4	675.7	676.0	677.4	678.9
122.5°	734.5	735.4	736.3	736.7	737.1	738.0	738.8	739.7	740.5	741.1	741.7
125°	795.7	796.9	798.0	798.6	799.2	800.3	801.4	802.6	803.7	804.3	804.9
127.5°	856.4	857.5	858.6	859.2	860.1	861.8	863.5	865.3	867.0	867.6	868.1
130°	917.4	919.4	921.4	922.4	923.0	924.1	925.3	926.4	927.6	928.5	929.3
132.5°	978.2	979.6	981.1	981.8	982.5	983.9	985.4	986.8	988.2	988.8	989.4
135°	1041.0	1041.5	1042.1	1042.4	1043.0	1044.1	1045.3	1046.4	1047.6	1047.9	1048.2
137.5°	1098.3	1099.2	1100.1	1100.5	1101.2	1102.6	1104.1	1105.5	1106.9	1106.0	1105.2
140°	1156.1	1158.1	1160.1	1161.1	1161.2	1161.5	1161.8	1162.1	1162.4	1162.1	1161.8
142.5°	1211.7	1213.1	1214.6	1215.3	1215.4	1215.7	1216.0	1216.3	1216.6	1216.0	1215.4
145°	1265.3	1266.5	1267.6	1268.2	1268.3	1268.6	1268.9	1269.2	1269.5	1268.6	1267.8
147.5°	1315.5	1317.2	1318.9	1319.8	1319.8	1319.8	1319.8	1319.8	1319.8	1318.9	1318.1
150°	1361.9	1363.6	1365.3	1366.2	1366.2	1366.2	1366.2	1366.2	1366.2	1365.6	1365.0
152.5°	1406.5	1407.9	1409.4	1410.1	1409.8	1409.2	1408.7	1408.1	1407.5	1407.2	1406.9
155°	1447.6	1449.7	1451.7	1452.7	1452.1	1451.0	1449.8	1448.7	1447.5	1447.2	1446.9
157.5°	1484.5	1486.2	1487.9	1488.8	1488.2	1487.1	1485.9	1484.8	1483.6	1483.3	1483.0
160°	1519.5	1520.6	1521.7	1522.3	1521.6	1520.2	1518.7	1517.3	1515.9	1515.9	1515.9
162.5°	1548.3	1550.3	1552.3	1553.3	1552.6	1551.1	1549.7	1548.2	1546.8	1546.5	1546.2
165°	1574.1	1576.1	1578.1	1579.1	1578.2	1576.5	1574.8	1573.0	1571.3	1571.3	1571.3
167.5°	1596.7	1598.4	1600.1	1601.0	1600.1	1598.4	1596.7	1595.0	1593.3	1593.0	1592.7
170°	1614.1	1616.1	1618.1	1619.1	1618.1	1616.1	1614.1	1612.1	1610.1	1610.1	1610.1
172.5°	1627.0	1629.0	1631.0	1632.0	1631.1	1629.4	1627.7	1625.9	1624.2	1624.2	1624.2
175°	1636.0	1638.0	1640.0	1641.0	1640.1	1638.4	1636.7	1635.0	1633.3	1633.3	1633.3
177.5°	1641.1	1643.2	1645.2	1646.2	1645.3	1643.6	1641.9	1640.1	1638.4	1638.4	1638.4
180°	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3

TEST NUMBER: P1032111

CATALOG NUMBER: S123RDIW-B1165D1320UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7
2.5°	1893.9	1886.1	1878.2	1878.2	1861.0	1845.3	1837.5	1840.6	1831.2	1818.7	1806.2
5°	1976.9	1945.6	1939.3	1922.1	1898.6	1865.7	1848.5	1832.8	1814.0	1788.9	1765.5
7.5°	2053.7	2013.0	1991.0	1973.8	1928.4	1882.9	1845.3	1820.3	1787.4	1749.8	1721.6
10°	2153.9	2078.8	2055.3	2016.1	1951.9	1887.6	1843.8	1803.0	1757.6	1713.8	1676.2
12.5°	2233.8	2147.7	2103.8	2064.7	1981.6	1900.2	1826.5	1776.4	1721.6	1673.0	1624.5
15°	2324.7	2227.6	2150.8	2103.8	1998.9	1900.2	1817.1	1746.7	1685.6	1626.0	1583.7
17.5°	2368.6	2246.4	2211.9	2144.5	1992.6	1893.9	1792.1	1716.9	1643.3	1574.3	1524.2
20°	2437.5	2294.9	2208.8	2163.3	2028.6	1882.9	1763.9	1677.7	1601.0	1527.3	1474.1
22.5°	2442.2	2287.1	2230.7	2144.5	1978.5	1850.0	1738.8	1633.9	1544.6	1475.6	1420.8
25°	2431.2	2273.0	2194.7	2125.7	1987.9	1831.2	1688.7	1585.3	1497.6	1417.7	1353.5
27.5°	2426.5	2232.3	2158.6	2089.7	1934.6	1776.4	1658.9	1541.4	1441.2	1370.7	1304.9
30°	2420.3	2188.4	2099.1	2019.2	1876.7	1734.1	1593.1	1491.3	1395.8	1306.5	1240.7
32.5°	2379.5	2128.9	2038.0	1953.4	1799.9	1657.4	1546.1	1438.1	1334.7	1251.6	1192.1
35°	2367.0	2074.1	1955.0	1864.1	1713.8	1586.9	1469.4	1380.1	1283.0	1199.9	1129.5
37.5°	2331.0	2017.7	1889.2	1773.3	1616.6	1496.0	1409.9	1320.6	1226.6	1137.3	1080.9
40°	2268.3	1951.9	1806.2	1687.1	1525.8	1403.6	1323.7	1257.9	1165.5	1085.6	1016.7
42.5°	2175.9	1884.5	1727.9	1602.5	1424.0	1309.6	1243.8	1181.1	1102.8	1019.8	963.4
45°	2069.4	1795.2	1649.5	1510.1	1328.4	1217.2	1148.2	1110.7	1038.6	968.1	902.3
47.5°	1923.7	1702.8	1558.7	1414.6	1229.7	1121.6	1066.8	1029.2	979.1	902.3	849.0
50°	1740.4	1583.7	1447.5	1319.0	1132.6	1029.2	974.4	946.2	903.9	849.0	797.4
52.5°	1536.7	1445.9	1333.1	1214.0	1033.9	936.8	886.6	864.7	833.4	781.7	737.8
55°	1331.5	1292.4	1215.6	1098.1	930.5	850.6	806.8	778.6	755.1	717.5	679.9
57.5°	1148.2	1129.5	1076.2	985.3	844.3	761.3	723.7	704.9	686.1	657.9	620.3
60°	958.7	979.1	924.2	878.8	750.4	678.3	645.4	625.0	615.6	590.6	567.1
62.5°	794.2	813.0	781.7	747.2	656.4	592.1	571.8	553.0	546.7	524.8	501.3
65°	645.4	668.9	645.4	626.6	571.8	518.5	493.4	484.1	477.8	463.7	444.9
67.5°	513.8	537.3	526.3	502.8	485.6	441.8	427.7	418.3	415.1	404.2	388.5
70°	386.9	419.8	423.0	408.9	393.2	372.8	363.4	360.3	352.5	343.1	333.7
72.5°	278.8	316.4	318.0	318.0	308.6	308.6	299.2	294.5	294.5	285.1	274.1
75°	205.2	230.3	233.4	236.5	241.2	245.9	239.7	239.7	238.1	228.7	224.0
77.5°	136.3	158.2	166.0	177.0	183.3	183.3	186.4	189.5	186.4	181.7	178.6
80°	87.7	103.4	112.8	119.1	128.5	133.2	137.9	139.4	136.3	134.7	130.0
82.5°	58.0	62.7	67.4	75.2	86.2	94.0	94.0	92.4	95.6	94.0	92.4
85°	32.9	36.0	37.6	39.2	45.4	53.3	54.8	56.4	59.5	56.4	53.3
87.5°	12.5	14.1	14.1	14.1	17.2	18.8	23.5	29.8	28.2	25.1	25.1
90°	19.8	16.1	14.2	12.8	9.9	7.0	4.2	1.3	4.2	7.0	9.9
92.5°	49.0	47.3	46.4	45.5	43.8	42.1	40.4	38.7	40.4	42.1	43.8
95°	88.6	86.3	85.1	84.1	82.1	80.1	78.1	76.1	78.1	80.1	82.1
97.5°	134.2	132.5	131.6	130.9	129.4	128.0	126.5	125.1	126.5	128.0	129.4
100°	185.3	183.9	183.2	182.3	180.6	178.9	177.2	175.5	177.2	178.9	180.6
102.5°	240.4	238.4	237.4	237.0	236.1	235.2	234.4	233.5	234.4	235.2	236.1
105°	296.8	294.2	292.9	292.6	292.0	291.5	290.9	290.3	290.9	291.5	292.0
107.5°	360.3	359.2	358.6	358.5	358.2	357.9	357.7	357.4	357.7	357.9	358.2
110°	422.7	422.2	421.9	421.6	421.0	420.5	419.9	419.3	419.9	420.5	421.0

TEST NUMBER: P1032111

CATALOG NUMBER: S123RDIW-B1165D1320UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	485.1	485.1	485.1	485.0	484.7	484.4	484.1	483.8	484.1	484.4	484.7
115°	551.3	551.9	552.2	551.8	550.9	550.0	549.2	548.3	549.2	550.0	550.9
117.5°	614.5	615.1	615.4	615.3	615.0	614.7	614.4	614.1	614.4	614.7	615.0
120°	680.3	681.8	682.5	681.6	679.9	678.2	676.4	674.7	676.4	678.2	679.9
122.5°	742.2	742.8	743.1	742.5	741.4	740.2	739.1	737.9	739.1	740.2	741.4
125°	805.4	806.0	806.3	805.9	805.0	804.1	803.3	802.4	803.3	804.1	805.0
127.5°	868.7	869.2	869.5	868.6	866.9	865.2	863.5	861.8	863.5	865.2	866.9
130°	930.2	931.1	931.5	930.3	928.0	925.7	923.4	921.1	923.4	925.7	928.0
132.5°	989.9	990.5	990.8	989.7	987.4	985.1	982.8	980.5	982.8	985.1	987.4
135°	1048.5	1048.8	1048.9	1048.0	1046.3	1044.6	1042.8	1041.1	1042.8	1044.6	1046.3
137.5°	1104.3	1103.4	1103.0	1102.3	1100.9	1099.4	1098.0	1096.6	1098.0	1099.4	1100.9
140°	1161.5	1161.2	1161.1	1160.4	1158.9	1157.5	1156.0	1154.6	1156.0	1157.5	1158.9
142.5°	1214.9	1214.3	1214.0	1213.3	1211.8	1210.4	1208.9	1207.5	1208.9	1210.4	1211.8
145°	1266.9	1266.0	1265.6	1265.3	1264.7	1264.2	1263.6	1263.0	1263.6	1264.2	1264.7
147.5°	1317.2	1316.3	1315.9	1315.3	1314.2	1313.0	1311.9	1310.7	1311.9	1313.0	1314.2
150°	1364.5	1363.9	1363.6	1363.3	1362.8	1362.2	1361.7	1361.1	1361.7	1362.2	1362.8
152.5°	1406.6	1406.3	1406.2	1405.8	1404.9	1404.0	1403.2	1402.3	1403.2	1404.0	1404.9
155°	1446.6	1446.3	1446.2	1446.2	1446.2	1446.2	1446.2	1446.2	1446.2	1446.2	1446.2
157.5°	1482.7	1482.4	1482.3	1482.4	1482.7	1483.0	1483.3	1483.6	1483.3	1483.0	1482.7
160°	1515.9	1515.9	1515.9	1516.2	1516.8	1517.3	1517.9	1518.5	1517.9	1517.3	1516.8
162.5°	1545.9	1545.6	1545.5	1545.9	1546.8	1547.7	1548.5	1549.4	1548.5	1547.7	1546.8
165°	1571.3	1571.3	1571.3	1571.7	1572.6	1573.5	1574.3	1575.2	1574.3	1573.5	1572.6
167.5°	1592.4	1592.1	1592.0	1592.6	1593.7	1594.9	1596.0	1597.2	1596.0	1594.9	1593.7
170°	1610.1	1610.1	1610.1	1610.7	1611.8	1612.9	1614.1	1615.2	1614.1	1612.9	1611.8
172.5°	1624.2	1624.2	1624.2	1624.8	1625.9	1627.1	1628.2	1629.4	1628.2	1627.1	1625.9
175°	1633.3	1633.3	1633.3	1633.9	1635.0	1636.1	1637.3	1638.4	1637.3	1636.1	1635.0
177.5°	1638.4	1638.4	1638.4	1639.0	1640.1	1641.3	1642.4	1643.6	1642.4	1641.3	1640.1
180°	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3

TEST NUMBER: P1032111

CATALOG NUMBER: S123RDIW-B1165D1320UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7
2.5°	1806.2	1798.3	1795.2	1787.4	1768.6	1756.1	1742.0	1732.6	1734.1	1726.3	1731.0
5°	1749.8	1748.2	1737.3	1721.6	1695.0	1680.9	1655.8	1643.3	1637.0	1638.6	1629.2
7.5°	1702.8	1688.7	1680.9	1655.8	1630.7	1601.0	1580.6	1569.6	1560.2	1550.8	1544.6
10°	1649.5	1637.0	1624.5	1597.8	1563.4	1535.2	1507.0	1496.0	1481.9	1475.6	1470.9
12.5°	1593.1	1585.3	1569.6	1538.3	1499.1	1472.5	1439.6	1433.4	1414.6	1402.0	1398.9
15°	1541.4	1536.7	1508.5	1472.5	1433.4	1406.7	1378.5	1359.7	1328.4	1334.7	1323.7
17.5°	1486.6	1466.2	1449.0	1400.5	1381.7	1340.9	1308.0	1298.6	1276.7	1262.6	1248.5
20°	1425.5	1413.0	1391.1	1359.7	1314.3	1267.3	1242.2	1226.6	1214.0	1192.1	1185.8
22.5°	1367.6	1351.9	1333.1	1292.4	1253.2	1214.0	1179.6	1165.5	1149.8	1134.1	1124.8
25°	1322.1	1298.6	1278.3	1228.1	1189.0	1156.1	1134.1	1110.7	1088.7	1079.3	1076.2
27.5°	1251.6	1237.5	1217.2	1170.2	1134.1	1098.1	1077.8	1062.1	1038.6	1027.6	1018.2
30°	1206.2	1178.0	1154.5	1116.9	1080.9	1041.7	1022.9	1004.1	990.0	975.9	965.0
32.5°	1145.1	1123.2	1104.4	1066.8	1030.8	994.7	974.4	946.2	938.3	927.4	914.8
35°	1085.6	1071.5	1051.1	1010.4	971.2	946.2	924.2	897.6	888.2	880.4	869.4
37.5°	1029.2	1008.8	994.7	955.6	921.1	891.3	874.1	852.2	845.9	836.5	828.7
40°	980.6	960.3	946.2	907.0	871.0	839.6	828.7	806.8	797.4	786.4	781.7
42.5°	925.8	908.6	889.8	861.6	824.0	792.7	770.7	758.2	745.7	741.0	731.6
45°	867.8	852.2	838.1	806.8	767.6	745.7	726.9	709.6	700.2	692.4	686.1
47.5°	817.7	803.6	784.8	750.4	719.0	698.7	679.9	662.6	653.2	643.8	636.0
50°	759.8	751.9	731.6	698.7	668.9	645.4	628.2	612.5	606.2	595.3	582.7
52.5°	708.1	694.0	676.7	650.1	623.5	595.3	571.8	562.4	551.4	545.1	534.2
55°	647.0	637.6	618.8	595.3	567.1	543.6	526.3	513.8	499.7	493.4	479.4
57.5°	595.3	578.0	568.6	538.9	512.2	488.7	476.2	463.7	448.0	438.6	432.4
60°	538.9	523.2	509.1	484.1	465.3	440.2	421.4	410.4	399.5	386.9	380.7
62.5°	484.1	471.5	454.3	433.9	410.4	390.1	376.0	360.3	354.0	341.5	336.8
65°	424.5	415.1	401.0	377.5	358.7	341.5	327.4	314.9	308.6	303.9	300.8
67.5°	371.3	358.7	349.3	329.0	308.6	294.5	286.7	278.8	271.0	266.3	261.6
70°	316.4	307.0	297.6	278.8	264.7	252.2	245.9	239.7	235.0	230.3	225.6
72.5°	260.0	255.3	245.9	233.4	222.4	213.0	208.3	200.5	195.8	188.0	184.8
75°	214.6	206.8	202.1	191.1	181.7	173.9	167.6	158.2	152.0	148.8	147.3
77.5°	169.2	166.0	159.8	150.4	145.7	137.9	128.5	125.3	122.2	122.2	120.6
80°	126.9	122.2	117.5	109.7	105.0	98.7	98.7	98.7	97.1	98.7	97.1
82.5°	86.2	83.0	79.9	75.2	73.6	73.6	75.2	75.2	75.2	75.2	75.2
85°	50.1	50.1	50.1	51.7	50.1	50.1	51.7	53.3	51.7	51.7	50.1
87.5°	23.5	23.5	25.1	25.1	26.6	26.6	26.6	26.6	26.6	26.6	28.2
90°	12.8	14.2	16.1	19.8	23.5	27.3	31.0	32.1	33.3	34.4	35.5
92.5°	45.5	46.4	47.3	49.0	50.7	52.5	54.2	55.1	55.9	56.8	57.7
95°	84.1	85.1	86.3	88.6	90.9	93.2	95.5	96.6	97.8	98.9	100.0
97.5°	130.9	131.6	132.5	134.2	135.9	137.6	139.3	140.7	142.2	143.6	145.1
100°	182.3	183.2	183.9	185.3	186.8	188.2	189.6	190.5	191.3	192.2	193.1
102.5°	237.0	237.4	238.4	240.4	242.4	244.4	246.4	247.3	248.1	249.0	249.9
105°	292.6	292.9	294.2	296.8	299.3	301.9	304.5	304.5	304.5	304.5	304.5
107.5°	358.5	358.6	359.2	360.3	361.5	362.6	363.8	364.7	365.5	366.4	367.3
110°	421.6	421.9	422.2	422.7	423.3	423.8	424.4	425.6	426.7	427.9	429.0

TEST NUMBER: P1032111

CATALOG NUMBER: S123RDIW-B1165D1320UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	485.0	485.1	485.1	485.1	485.1	485.1	485.1	486.5	487.9	489.4	490.8
115°	551.8	552.2	551.9	551.3	550.8	550.2	549.6	549.9	550.2	550.5	550.8
117.5°	615.3	615.4	615.1	614.5	614.0	613.4	612.8	612.8	612.8	612.8	612.8
120°	681.6	682.5	681.8	680.3	678.9	677.4	676.0	675.7	675.4	675.1	674.8
122.5°	742.5	743.1	742.8	742.2	741.7	741.1	740.5	739.7	738.8	738.0	737.1
125°	805.9	806.3	806.0	805.4	804.9	804.3	803.7	802.6	801.4	800.3	799.2
127.5°	868.6	869.5	869.2	868.7	868.1	867.6	867.0	865.3	863.5	861.8	860.1
130°	930.3	931.5	931.1	930.2	929.3	928.5	927.6	926.4	925.3	924.1	923.0
132.5°	989.7	990.8	990.5	989.9	989.4	988.8	988.2	986.8	985.4	983.9	982.5
135°	1048.0	1048.9	1048.8	1048.5	1048.2	1047.9	1047.6	1046.4	1045.3	1044.1	1043.0
137.5°	1102.3	1103.0	1103.4	1104.3	1105.2	1106.0	1106.9	1105.5	1104.1	1102.6	1101.2
140°	1160.4	1161.1	1161.2	1161.5	1161.8	1162.1	1162.4	1162.1	1161.8	1161.5	1161.2
142.5°	1213.3	1214.0	1214.3	1214.9	1215.4	1216.0	1216.6	1216.3	1216.0	1215.7	1215.4
145°	1265.3	1265.6	1266.0	1266.9	1267.8	1268.6	1269.5	1269.2	1268.9	1268.6	1268.3
147.5°	1315.3	1315.9	1316.3	1317.2	1318.1	1318.9	1319.8	1319.8	1319.8	1319.8	1319.8
150°	1363.3	1363.6	1363.9	1364.5	1365.0	1365.6	1366.2	1366.2	1366.2	1366.2	1366.2
152.5°	1405.8	1406.2	1406.3	1406.6	1406.9	1407.2	1407.5	1408.1	1408.7	1409.2	1409.8
155°	1446.2	1446.2	1446.3	1446.6	1446.9	1447.2	1447.5	1448.7	1449.8	1451.0	1452.1
157.5°	1482.4	1482.3	1482.4	1482.7	1483.0	1483.3	1483.6	1484.8	1485.9	1487.1	1488.2
160°	1516.2	1515.9	1515.9	1515.9	1515.9	1515.9	1515.9	1517.3	1518.7	1520.2	1521.6
162.5°	1545.9	1545.5	1545.6	1545.9	1546.2	1546.5	1546.8	1548.2	1549.7	1551.1	1552.6
165°	1571.7	1571.3	1571.3	1571.3	1571.3	1571.3	1571.3	1573.0	1574.8	1576.5	1578.2
167.5°	1592.6	1592.0	1592.1	1592.4	1592.7	1593.0	1593.3	1595.0	1596.7	1598.4	1600.1
170°	1610.7	1610.1	1610.1	1610.1	1610.1	1610.1	1610.1	1612.1	1614.1	1616.1	1618.1
172.5°	1624.8	1624.2	1624.2	1624.2	1624.2	1624.2	1624.2	1625.9	1627.7	1629.4	1631.1
175°	1633.9	1633.3	1633.3	1633.3	1633.3	1633.3	1633.3	1635.0	1636.7	1638.4	1640.1
177.5°	1639.0	1638.4	1638.4	1638.4	1638.4	1638.4	1638.4	1640.1	1641.9	1643.6	1645.3
180°	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3

TEST NUMBER: P1032111

CATALOG NUMBER: S123RDIW-B1165D1320UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7
2.5°	1729.4	1731.0	1726.3	1716.9	1715.3	1718.5	1727.9	1724.7	1716.9	1731.0	1718.5
5°	1633.9	1626.0	1622.9	1626.0	1616.6	1611.9	1621.3	1616.6	1621.3	1622.9	1627.6
7.5°	1541.4	1543.0	1533.6	1535.2	1522.6	1525.8	1525.8	1525.8	1530.5	1533.6	1539.9
10°	1461.5	1464.7	1453.7	1455.3	1445.9	1439.6	1444.3	1453.7	1453.7	1453.7	1456.8
12.5°	1397.3	1383.2	1375.4	1373.8	1362.9	1359.7	1369.1	1372.3	1380.1	1380.1	1384.8
15°	1317.4	1314.3	1308.0	1308.0	1281.4	1287.7	1290.8	1301.8	1317.4	1304.9	1308.0
17.5°	1245.4	1237.5	1229.7	1226.6	1223.4	1214.0	1226.6	1225.0	1234.4	1236.0	1240.7
20°	1181.1	1174.9	1159.2	1160.8	1163.9	1149.8	1157.6	1157.6	1167.0	1176.4	1187.4
22.5°	1118.5	1112.2	1104.4	1107.5	1098.1	1095.0	1095.0	1102.8	1113.8	1121.6	1120.1
25°	1069.9	1059.0	1054.3	1049.6	1044.9	1048.0	1043.3	1051.1	1059.0	1063.7	1059.0
27.5°	1015.1	1010.4	1001.0	996.3	988.5	991.6	994.7	1001.0	1005.7	1005.7	1010.4
30°	961.8	955.6	952.4	947.7	947.7	941.5	943.0	949.3	954.0	958.7	965.0
32.5°	910.1	905.4	900.7	900.7	897.6	896.0	894.5	903.9	903.9	913.3	913.3
35°	867.8	860.0	860.0	852.2	855.3	853.7	850.6	856.9	858.4	864.7	863.1
37.5°	820.8	820.8	817.7	809.9	803.6	805.2	813.0	813.0	817.7	816.1	820.8
40°	773.9	770.7	770.7	766.0	764.5	762.9	764.5	766.0	773.9	772.3	773.9
42.5°	726.9	728.4	720.6	720.6	720.6	715.9	717.5	719.0	722.2	725.3	730.0
45°	681.4	678.3	676.7	673.6	670.5	672.0	670.5	676.7	675.2	678.3	683.0
47.5°	632.9	628.2	626.6	620.3	620.3	623.5	621.9	626.6	628.2	632.9	629.7
50°	585.9	579.6	574.9	576.5	567.1	570.2	570.2	574.9	579.6	581.2	584.3
52.5°	531.0	529.5	527.9	520.1	518.5	516.9	518.5	520.1	526.3	531.0	532.6
55°	477.8	476.2	466.8	463.7	459.0	459.0	462.1	463.7	474.7	476.2	482.5
57.5°	429.2	424.5	413.6	412.0	412.0	412.0	407.3	413.6	416.7	424.5	424.5
60°	376.0	376.0	366.6	366.6	368.1	366.6	366.6	368.1	368.1	374.4	377.5
62.5°	333.7	332.1	332.1	329.0	327.4	329.0	327.4	327.4	329.0	333.7	338.4
65°	296.1	294.5	292.9	291.4	288.2	288.2	289.8	292.9	292.9	296.1	297.6
67.5°	260.0	260.0	256.9	256.9	255.3	253.8	255.3	253.8	260.0	260.0	261.6
70°	224.0	222.4	217.7	216.2	211.5	213.0	213.0	217.7	219.3	222.4	225.6
72.5°	180.1	180.1	177.0	173.9	175.4	172.3	172.3	173.9	173.9	178.6	180.1
75°	148.8	145.7	144.1	145.7	144.1	147.3	144.1	144.1	147.3	147.3	147.3
77.5°	122.2	122.2	120.6	120.6	122.2	120.6	122.2	122.2	122.2	120.6	122.2
80°	100.3	98.7	98.7	98.7	97.1	97.1	97.1	97.1	97.1	97.1	97.1
82.5°	75.2	75.2	73.6	75.2	75.2	73.6	75.2	73.6	73.6	75.2	75.2
85°	50.1	53.3	50.1	50.1	51.7	51.7	53.3	51.7	53.3	50.1	51.7
87.5°	26.6	28.2	28.2	26.6	26.6	28.2	28.2	28.2	29.8	26.6	28.2
90°	36.1	36.4	37.0	37.5	38.1	38.7	38.1	37.5	37.0	36.4	36.1
92.5°	58.1	57.8	57.2	56.7	56.1	55.5	56.1	56.7	57.2	57.8	58.1
95°	100.6	100.6	100.6	100.6	100.6	100.6	100.6	100.6	100.6	100.6	100.6
97.5°	145.8	145.7	145.4	145.1	144.8	144.5	144.8	145.1	145.4	145.7	145.8
100°	193.5	193.8	194.4	194.9	195.5	196.1	195.5	194.9	194.4	193.8	193.5
102.5°	250.3	250.2	249.9	249.6	249.3	249.0	249.3	249.6	249.9	250.2	250.3
105°	304.5	304.8	305.3	305.9	306.4	307.0	306.4	305.9	305.3	304.8	304.5
107.5°	367.7	367.6	367.3	367.0	366.7	366.4	366.7	367.0	367.3	367.6	367.7
110°	429.6	429.3	428.7	428.2	427.6	427.0	427.6	428.2	428.7	429.3	429.6

TEST NUMBER: P1032111

CATALOG NUMBER: S123RDIW-B1165D1320UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	491.5	491.5	491.5	491.5	491.5	491.5	491.5	491.5	491.5	491.5	491.5
115°	550.9	550.8	550.5	550.2	549.9	549.6	549.9	550.2	550.5	550.8	550.9
117.5°	612.8	612.4	611.5	610.6	609.8	608.9	609.8	610.6	611.5	612.4	612.8
120°	674.7	674.4	673.8	673.3	672.7	672.1	672.7	673.3	673.8	674.4	674.7
122.5°	736.7	736.3	735.4	734.5	733.7	732.8	733.7	734.5	735.4	736.3	736.7
125°	798.6	798.0	796.9	795.7	794.6	793.4	794.6	795.7	796.9	798.0	798.6
127.5°	859.2	858.6	857.5	856.4	855.2	854.1	855.2	856.4	857.5	858.6	859.2
130°	922.4	921.4	919.4	917.4	915.4	913.4	915.4	917.4	919.4	921.4	922.4
132.5°	981.8	981.1	979.6	978.2	976.7	975.3	976.7	978.2	979.6	981.1	981.8
135°	1042.4	1042.1	1041.5	1041.0	1040.4	1039.8	1040.4	1041.0	1041.5	1042.1	1042.4
137.5°	1100.5	1100.1	1099.2	1098.3	1097.5	1096.6	1097.5	1098.3	1099.2	1100.1	1100.5
140°	1161.1	1160.1	1158.1	1156.1	1154.1	1152.1	1154.1	1156.1	1158.1	1160.1	1161.1
142.5°	1215.3	1214.6	1213.1	1211.7	1210.2	1208.8	1210.2	1211.7	1213.1	1214.6	1215.3
145°	1268.2	1267.6	1266.5	1265.3	1264.2	1263.0	1264.2	1265.3	1266.5	1267.6	1268.2
147.5°	1319.8	1318.9	1317.2	1315.5	1313.7	1312.0	1313.7	1315.5	1317.2	1318.9	1319.8
150°	1366.2	1365.3	1363.6	1361.9	1360.2	1358.5	1360.2	1361.9	1363.6	1365.3	1366.2
152.5°	1410.1	1409.4	1407.9	1406.5	1405.0	1403.6	1405.0	1406.5	1407.9	1409.4	1410.1
155°	1452.7	1451.7	1449.7	1447.6	1445.6	1443.6	1445.6	1447.6	1449.7	1451.7	1452.7
157.5°	1488.8	1487.9	1486.2	1484.5	1482.7	1481.0	1482.7	1484.5	1486.2	1487.9	1488.8
160°	1522.3	1521.7	1520.6	1519.5	1518.3	1517.2	1518.3	1519.5	1520.6	1521.7	1522.3
162.5°	1553.3	1552.3	1550.3	1548.3	1546.3	1544.3	1546.3	1548.3	1550.3	1552.3	1553.3
165°	1579.1	1578.1	1576.1	1574.1	1572.1	1570.1	1572.1	1574.1	1576.1	1578.1	1579.1
167.5°	1601.0	1600.1	1598.4	1596.7	1595.0	1593.3	1595.0	1596.7	1598.4	1600.1	1601.0
170°	1619.1	1618.1	1616.1	1614.1	1612.1	1610.1	1612.1	1614.1	1616.1	1618.1	1619.1
172.5°	1632.0	1631.0	1629.0	1627.0	1625.0	1623.0	1625.0	1627.0	1629.0	1631.0	1632.0
175°	1641.0	1640.0	1638.0	1636.0	1634.0	1632.0	1634.0	1636.0	1638.0	1640.0	1641.0
177.5°	1646.2	1645.2	1643.2	1641.1	1639.1	1637.1	1639.1	1641.1	1643.2	1645.2	1646.2
180°	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3

TEST NUMBER: P1032111

CATALOG NUMBER: S123RDIW-B1165D1320UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7
2.5°	1731.0	1737.3	1731.0	1718.5	1731.0	1738.8	1746.7	1759.2	1765.5	1765.5	1774.9
5°	1632.3	1644.8	1640.1	1637.0	1649.5	1657.4	1669.9	1685.6	1702.8	1713.8	1726.3
7.5°	1544.6	1552.4	1560.2	1560.2	1572.8	1590.0	1608.8	1627.6	1649.5	1665.2	1674.6
10°	1467.8	1474.1	1478.8	1485.0	1503.8	1522.6	1547.7	1571.2	1590.0	1607.2	1622.9
12.5°	1394.2	1403.6	1414.6	1419.3	1433.4	1456.8	1480.3	1508.5	1538.3	1555.5	1571.2
15°	1323.7	1328.4	1340.9	1355.0	1367.6	1392.6	1422.4	1452.2	1477.2	1503.8	1517.9
17.5°	1251.6	1253.2	1286.1	1278.3	1319.0	1342.5	1358.2	1386.4	1427.1	1449.0	1470.9
20°	1181.1	1196.8	1210.9	1218.7	1240.7	1267.3	1312.7	1334.7	1367.6	1387.9	1406.7
22.5°	1126.3	1149.8	1149.8	1168.6	1179.6	1204.6	1237.5	1279.8	1315.9	1330.0	1356.6
25°	1077.8	1088.7	1107.5	1113.8	1134.1	1156.1	1178.0	1223.4	1262.6	1281.4	1300.2
27.5°	1015.1	1029.2	1054.3	1054.3	1080.9	1104.4	1131.0	1160.8	1199.9	1226.6	1246.9
30°	966.5	980.6	991.6	1008.8	1019.8	1041.7	1088.7	1110.7	1145.1	1168.6	1193.7
32.5°	921.1	932.1	941.5	960.3	972.8	997.9	1022.9	1062.1	1091.9	1113.8	1140.4
35°	871.0	881.9	894.5	908.6	927.4	950.9	974.4	1007.3	1037.0	1057.4	1079.3
37.5°	824.0	831.8	850.6	860.0	875.7	897.6	927.4	961.8	988.5	1004.1	1026.1
40°	778.6	784.8	798.9	816.1	827.1	844.3	875.7	905.4	938.3	957.1	974.4
42.5°	730.0	737.8	750.4	767.6	784.8	803.6	820.8	855.3	885.1	900.7	919.5
45°	687.7	692.4	701.8	719.0	736.3	750.4	777.0	808.3	836.5	849.0	869.4
47.5°	637.6	642.3	656.4	664.2	683.0	701.8	728.4	759.8	784.8	797.4	816.1
50°	585.9	590.6	600.0	617.2	629.7	650.1	673.6	700.2	731.6	748.8	759.8
52.5°	535.7	545.1	553.0	567.1	582.7	603.1	625.0	650.1	676.7	694.0	706.5
55°	485.6	493.4	502.8	510.7	529.5	548.3	573.3	596.8	620.3	636.0	650.1
57.5°	429.2	440.2	449.6	465.3	479.4	495.0	523.2	542.0	570.2	581.2	593.7
60°	380.7	391.6	399.5	412.0	424.5	444.9	463.7	487.2	510.7	524.8	540.4
62.5°	339.9	344.6	349.3	361.9	374.4	393.2	412.0	435.5	460.6	468.4	480.9
65°	299.2	303.9	311.7	322.7	332.1	343.1	363.4	382.2	405.7	418.3	423.0
67.5°	264.7	269.4	271.0	278.8	286.7	299.2	310.2	329.0	350.9	358.7	368.1
70°	225.6	233.4	235.0	241.2	244.4	252.2	264.7	278.8	296.1	310.2	318.0
72.5°	180.1	191.1	194.2	203.6	208.3	216.2	225.6	236.5	247.5	253.8	260.0
75°	147.3	150.4	152.0	159.8	167.6	178.6	183.3	189.5	198.9	206.8	213.0
77.5°	122.2	123.8	125.3	125.3	126.9	133.2	142.6	150.4	156.7	159.8	164.5
80°	98.7	97.1	97.1	98.7	98.7	98.7	101.8	112.8	115.9	123.8	122.2
82.5°	76.8	73.6	75.2	73.6	73.6	73.6	73.6	75.2	75.2	79.9	83.0
85°	50.1	51.7	50.1	50.1	48.6	50.1	48.6	48.6	47.0	47.0	45.4
87.5°	26.6	28.2	26.6	26.6	25.1	26.6	25.1	25.1	23.5	23.5	20.4
90°	35.5	34.4	33.3	32.1	31.0	27.3	23.5	19.8	16.1	14.2	12.8
92.5°	57.7	56.8	55.9	55.1	54.2	52.5	50.7	49.0	47.3	46.4	45.5
95°	100.0	98.9	97.8	96.6	95.5	93.2	90.9	88.6	86.3	85.1	84.1
97.5°	145.1	143.6	142.2	140.7	139.3	137.6	135.9	134.2	132.5	131.6	130.9
100°	193.1	192.2	191.3	190.5	189.6	188.2	186.8	185.3	183.9	183.2	182.3
102.5°	249.9	249.0	248.1	247.3	246.4	244.4	242.4	240.4	238.4	237.4	237.0
105°	304.5	304.5	304.5	304.5	304.5	301.9	299.3	296.8	294.2	292.9	292.6
107.5°	367.3	366.4	365.5	364.7	363.8	362.6	361.5	360.3	359.2	358.6	358.5
110°	429.0	427.9	426.7	425.6	424.4	423.8	423.3	422.7	422.2	421.9	421.6

TEST NUMBER: P1032111

CATALOG NUMBER: S123RDIW-B1165D1320UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	490.8	489.4	487.9	486.5	485.1	485.1	485.1	485.1	485.1	485.1	485.0
115°	550.8	550.5	550.2	549.9	549.6	550.2	550.8	551.3	551.9	552.2	551.8
117.5°	612.8	612.8	612.8	612.8	612.8	613.4	614.0	614.5	615.1	615.4	615.3
120°	674.8	675.1	675.4	675.7	676.0	677.4	678.9	680.3	681.8	682.5	681.6
122.5°	737.1	738.0	738.8	739.7	740.5	741.1	741.7	742.2	742.8	743.1	742.5
125°	799.2	800.3	801.4	802.6	803.7	804.3	804.9	805.4	806.0	806.3	805.9
127.5°	860.1	861.8	863.5	865.3	867.0	867.6	868.1	868.7	869.2	869.5	868.6
130°	923.0	924.1	925.3	926.4	927.6	928.5	929.3	930.2	931.1	931.5	930.3
132.5°	982.5	983.9	985.4	986.8	988.2	988.8	989.4	989.9	990.5	990.8	989.7
135°	1043.0	1044.1	1045.3	1046.4	1047.6	1047.9	1048.2	1048.5	1048.8	1048.9	1048.0
137.5°	1101.2	1102.6	1104.1	1105.5	1106.9	1106.0	1105.2	1104.3	1103.4	1103.0	1102.3
140°	1161.2	1161.5	1161.8	1162.1	1162.4	1162.1	1161.8	1161.5	1161.2	1161.1	1160.4
142.5°	1215.4	1215.7	1216.0	1216.3	1216.6	1216.0	1215.4	1214.9	1214.3	1214.0	1213.3
145°	1268.3	1268.6	1268.9	1269.2	1269.5	1268.6	1267.8	1266.9	1266.0	1265.6	1265.3
147.5°	1319.8	1319.8	1319.8	1319.8	1319.8	1318.9	1318.1	1317.2	1316.3	1315.9	1315.3
150°	1366.2	1366.2	1366.2	1366.2	1366.2	1365.6	1365.0	1364.5	1363.9	1363.6	1363.3
152.5°	1409.8	1409.2	1408.7	1408.1	1407.5	1407.2	1406.9	1406.6	1406.3	1406.2	1405.8
155°	1452.1	1451.0	1449.8	1448.7	1447.5	1447.2	1446.9	1446.6	1446.3	1446.2	1446.2
157.5°	1488.2	1487.1	1485.9	1484.8	1483.6	1483.3	1483.0	1482.7	1482.4	1482.3	1482.4
160°	1521.6	1520.2	1518.7	1517.3	1515.9	1515.9	1515.9	1515.9	1515.9	1515.9	1516.2
162.5°	1552.6	1551.1	1549.7	1548.2	1546.8	1546.5	1546.2	1545.9	1545.6	1545.5	1545.9
165°	1578.2	1576.5	1574.8	1573.0	1571.3	1571.3	1571.3	1571.3	1571.3	1571.3	1571.7
167.5°	1600.1	1598.4	1596.7	1595.0	1593.3	1593.0	1592.7	1592.4	1592.1	1592.0	1592.6
170°	1618.1	1616.1	1614.1	1612.1	1610.1	1610.1	1610.1	1610.1	1610.1	1610.1	1610.7
172.5°	1631.1	1629.4	1627.7	1625.9	1624.2	1624.2	1624.2	1624.2	1624.2	1624.2	1624.8
175°	1640.1	1638.4	1636.7	1635.0	1633.3	1633.3	1633.3	1633.3	1633.3	1633.3	1633.9
177.5°	1645.3	1643.6	1641.9	1640.1	1638.4	1638.4	1638.4	1638.4	1638.4	1638.4	1639.0
180°	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3	1642.3

TEST NUMBER: P1032111

CATALOG NUMBER: S123RDIW-B1165D1320UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1829.7	1829.7	1829.7	1829.7
2.5°	1782.7	1793.6	1815.6	1834.4
5°	1745.1	1762.3	1795.2	1828.1
7.5°	1699.7	1726.3	1768.6	1814.0
10°	1655.8	1690.3	1742.0	1795.2
12.5°	1611.9	1648.0	1702.8	1771.7
15°	1560.2	1597.8	1663.6	1746.7
17.5°	1514.8	1564.9	1624.5	1707.5
20°	1466.2	1503.8	1580.6	1668.3
22.5°	1405.2	1467.8	1539.9	1632.3
25°	1356.6	1411.4	1483.5	1588.4
27.5°	1297.1	1361.3	1449.0	1541.4
30°	1248.5	1301.8	1383.2	1494.4
32.5°	1192.1	1254.8	1339.4	1449.0
35°	1142.0	1195.2	1275.1	1386.4
37.5°	1082.5	1140.4	1229.7	1328.4
40°	1030.8	1087.2	1171.7	1264.2
42.5°	968.1	1027.6	1112.2	1190.5
45°	918.0	972.8	1040.2	1112.2
47.5°	856.9	914.8	980.6	1030.8
50°	802.1	855.3	907.0	949.3
52.5°	742.5	791.1	838.1	869.4
55°	687.7	725.3	762.9	784.8
57.5°	623.5	659.5	690.8	703.4
60°	567.1	596.8	617.2	631.3
62.5°	507.5	529.5	545.1	553.0
65°	449.6	465.3	473.1	480.9
67.5°	390.1	404.2	408.9	418.3
70°	327.4	343.1	346.2	350.9
72.5°	280.4	280.4	286.7	292.9
75°	224.0	227.1	230.3	230.3
77.5°	175.4	175.4	178.6	180.1
80°	128.5	130.0	130.0	128.5
82.5°	87.7	90.9	87.7	86.2
85°	48.6	54.8	51.7	51.7
87.5°	20.4	20.4	23.5	20.4
90°	9.9	7.0	4.2	1.3
92.5°	43.8	42.1	40.4	38.7
95°	82.1	80.1	78.1	76.1
97.5°	129.4	128.0	126.5	125.1
100°	180.6	178.9	177.2	175.5
102.5°	236.1	235.2	234.4	233.5
105°	292.0	291.5	290.9	290.3
107.5°	358.2	357.9	357.7	357.4
110°	421.0	420.5	419.9	419.3

TEST NUMBER: P1032111

CATALOG NUMBER: S123RDIW-B1165D1320UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	484.7	484.4	484.1	483.8
115°	550.9	550.0	549.2	548.3
117.5°	615.0	614.7	614.4	614.1
120°	679.9	678.2	676.4	674.7
122.5°	741.4	740.2	739.1	737.9
125°	805.0	804.1	803.3	802.4
127.5°	866.9	865.2	863.5	861.8
130°	928.0	925.7	923.4	921.1
132.5°	987.4	985.1	982.8	980.5
135°	1046.3	1044.6	1042.8	1041.1
137.5°	1100.9	1099.4	1098.0	1096.6
140°	1158.9	1157.5	1156.0	1154.6
142.5°	1211.8	1210.4	1208.9	1207.5
145°	1264.7	1264.2	1263.6	1263.0
147.5°	1314.2	1313.0	1311.9	1310.7
150°	1362.8	1362.2	1361.7	1361.1
152.5°	1404.9	1404.0	1403.2	1402.3
155°	1446.2	1446.2	1446.2	1446.2
157.5°	1482.7	1483.0	1483.3	1483.6
160°	1516.8	1517.3	1517.9	1518.5
162.5°	1546.8	1547.7	1548.5	1549.4
165°	1572.6	1573.5	1574.3	1575.2
167.5°	1593.7	1594.9	1596.0	1597.2
170°	1611.8	1612.9	1614.1	1615.2
172.5°	1625.9	1627.1	1628.2	1629.4
175°	1635.0	1636.1	1637.3	1638.4
177.5°	1640.1	1641.3	1642.4	1643.6
180°	1642.3	1642.3	1642.3	1642.3

(END OF REPORT)