

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032561

Luminaire Tested: S124DIW-B1195D1340UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032561
REPORT IS A COMBINATION OF REPORTS P997034 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B1195D1340UB2750-4F0-XX-W2A-D_3000K
Description: Define 4 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10244.0 lumens
Efficiency: N/A
Efficacy: 99.1 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 103.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032561

CATALOG NUMBER: S124DIW-B1195D1340UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1032561

CATALOG NUMBER: S124DIW-B1195D1340UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	96	91	87	83	87	83	80	76	69	66	64	56	54	52	43	42	41
2	87	79	72	67	79	72	67	62	60	56	52	48	45	43	38	36	34
3	79	69	61	55	72	63	57	51	52	47	43	42	39	36	33	30	28
4	72	61	53	46	65	56	49	43	46	41	37	37	33	30	29	26	24
5	66	54	46	40	60	50	42	37	41	36	31	33	29	26	26	23	21
6	61	48	40	34	55	44	37	32	37	31	27	30	26	23	24	21	18
7	56	43	35	30	51	40	33	28	33	28	24	27	23	20	22	18	16
8	52	39	31	26	47	36	29	24	30	25	21	25	21	18	20	17	14
9	48	36	28	23	44	33	26	22	28	22	19	23	19	16	18	15	13
10	45	33	26	21	41	30	24	19	26	20	17	21	17	14	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11653	11653	11653
5°	11685	11349	11370
10°	11609	11126	11094
15°	11501	10875	10783
20°	11339	10603	10481
25°	11158	10303	10156
30°	10962	10006	9823
35°	10739	9702	9528
40°	10561	9411	9221
45°	10298	9137	8950
50°	10073	8827	8665
55°	9841	8527	8336
60°	9481	8155	8027
65°	9085	7753	7654
70°	8605	7294	7225
75°	7931	6784	6815
80°	7173	6263	6384
85°	6171	5740	6037

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10298 cd/sqm

TEST NUMBER: P1032561

CATALOG NUMBER: S124DIW-B1195D1340UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.4	1.3
10°-20°	387.9	3.8
20°-30°	586.6	5.7
30°-40°	709.6	6.9
40°-50°	750.2	7.3
50°-60°	706.0	6.9
60°-70°	585.9	5.7
70°-80°	411.1	4.0
80°-90°	235.3	2.3
90°-100°	195.5	1.9
100°-110°	481.4	4.7
110°-120°	792.8	7.7
120°-130°	958.0	9.4
130°-140°	1000.2	9.8
140°-150°	923.0	9.0
150°-160°	741.7	7.2
160°-170°	478.3	4.7
170°-180°	164.8	1.6
0°-30°	1109.9	10.8
0°-40°	1819.6	17.8
0°-60°	3275.8	32.0
0°-90°	4508.2	44.0
90°-120°	1469.8	14.3
90°-150°	4351.0	42.5
90°-180°	5736.0	56.0
0°-180°	10244.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1429	1429	1429	1429	1429	
5°	1431	1426	1415	1427	1426	136
15°	1371	1373	1368	1383	1381	386
25°	1255	1264	1269	1287	1288	578
35°	1098	1117	1133	1155	1160	687
45°	915	946	976	1003	1011	707
55°	717	750	798	830	840	639
65°	496	547	602	642	654	492
75°	275	334	402	446	461	292
85°	85	152	224	272	288	88
90°	30	108	187	241	256	21
95°	92	101	168	219	234	105
105°	405	445	510	562	528	425
115°	739	757	807	845	856	728
125°	1032	1035	1072	1107	1118	922
135°	1275	1274	1290	1318	1330	983
145°	1468	1470	1470	1481	1490	917
155°	1608	1609	1605	1610	1606	741
165°	1696	1690	1690	1700	1688	479
175°	1735	1727	1728	1740	1724	165
180°	1735	1735	1735	1735	1735	

TEST NUMBER: P1032561

CATALOG NUMBER: S124DIW-B1195D1340UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1429.0	1429.0	1429.0	1429.0	1429.0
2.5°	1435.4	1430.6	1417.8	1429.0	1427.4
5°	1430.6	1425.8	1414.6	1427.4	1425.8
7.5°	1421.0	1417.8	1408.2	1422.6	1421.0
10°	1408.2	1406.6	1398.6	1413.0	1411.4
12.5°	1390.6	1390.6	1385.8	1398.6	1398.6
15°	1371.4	1373.0	1368.2	1382.6	1381.0
17.5°	1345.8	1350.6	1349.0	1363.4	1361.8
20°	1318.6	1323.4	1325.0	1341.0	1341.0
22.5°	1288.2	1294.6	1297.8	1313.8	1317.0
25°	1254.6	1264.2	1269.0	1286.6	1288.2
27.5°	1217.8	1232.2	1238.6	1254.6	1256.2
30°	1181.0	1193.8	1205.0	1222.6	1225.8
32.5°	1140.9	1157.0	1169.8	1190.6	1193.8
35°	1097.7	1116.9	1132.9	1155.4	1160.2
37.5°	1054.5	1076.9	1096.1	1118.5	1123.3
40°	1012.9	1033.7	1056.1	1080.1	1086.5
42.5°	964.9	988.9	1016.1	1043.3	1048.1
45°	915.3	945.7	976.1	1003.3	1011.3
47.5°	868.9	899.3	934.5	961.7	971.3
50°	817.7	852.9	888.1	920.1	929.7
52.5°	766.5	801.7	843.3	875.3	884.9
55°	716.9	750.5	798.5	830.5	840.1
57.5°	660.9	702.5	748.9	787.3	795.3
60°	606.5	648.1	700.9	737.7	750.5
62.5°	553.7	600.1	652.9	689.7	702.5
65°	496.1	547.3	601.7	641.7	654.5
67.5°	441.7	496.1	553.7	593.7	606.5
70°	385.7	440.1	500.9	544.1	555.3
72.5°	331.2	387.3	452.9	494.5	507.3
75°	275.2	334.4	401.7	446.5	460.9
77.5°	222.4	284.8	355.2	400.1	416.1
80°	174.4	238.4	308.8	356.8	369.6
82.5°	126.4	193.6	264.0	313.6	328.0
85°	84.8	152.0	224.0	272.0	288.0
87.5°	52.8	118.4	188.8	235.2	249.6
90°	29.5	107.8	186.9	241.1	256.5
92.5°	43.5	96.9	176.0	228.6	241.4
95°	92.2	100.8	167.7	218.7	234.4
97.5°	155.4	230.4	159.7	207.8	223.5
100°	230.4	295.4	178.7	199.8	212.3
102.5°	316.1	366.8	443.2	192.8	205.6
105°	405.0	444.8	510.5	562.1	528.2
107.5°	489.3	520.4	585.5	632.0	648.4
110°	573.4	599.7	663.4	702.8	719.5

TEST NUMBER: P1032561

CATALOG NUMBER: S124DIW-B1195D1340UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	654.8	681.8	737.2	771.1	789.1
115°	738.9	757.2	807.1	844.8	856.0
117.5°	815.4	830.2	882.1	914.4	927.2
120°	891.7	901.7	946.8	981.4	991.6
122.5°	964.3	966.9	1012.7	1046.0	1054.6
125°	1031.5	1035.1	1072.5	1106.8	1117.7
127.5°	1097.7	1097.4	1135.9	1163.4	1173.3
130°	1159.7	1159.4	1188.9	1219.0	1228.6
132.5°	1218.1	1219.1	1243.5	1272.0	1280.3
135°	1274.9	1273.6	1290.0	1318.1	1330.3
137.5°	1326.8	1325.2	1338.1	1364.6	1371.4
140°	1377.4	1378.4	1382.6	1407.3	1416.6
142.5°	1421.2	1426.4	1426.1	1446.3	1452.7
145°	1467.9	1470.2	1470.2	1481.1	1490.1
147.5°	1504.2	1510.4	1509.1	1512.0	1519.7
150°	1544.5	1548.1	1546.8	1546.8	1548.1
152.5°	1576.6	1580.5	1577.9	1580.5	1579.2
155°	1607.7	1609.0	1605.1	1610.3	1606.4
157.5°	1635.0	1635.0	1629.8	1636.3	1629.8
160°	1658.3	1654.5	1653.2	1660.9	1653.2
162.5°	1679.1	1673.9	1672.6	1680.4	1671.3
165°	1696.0	1689.5	1689.5	1699.9	1688.2
167.5°	1710.3	1703.8	1702.5	1714.1	1701.2
170°	1721.9	1714.1	1715.4	1725.8	1712.8
172.5°	1729.7	1721.9	1723.2	1733.6	1719.3
175°	1734.9	1727.1	1728.4	1740.1	1724.5
177.5°	1738.8	1729.7	1732.3	1742.7	1727.1
180°	1734.9	1734.9	1734.9	1734.9	1734.9

(END OF REPORT)