

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032565

Luminaire Tested: S124DIW-B1195D1340UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032565
REPORT IS A COMBINATION OF REPORTS P997040 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B1195D1340UB2750-4F0-XX-W2A-F_2700K
Description: Define 4 Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10408.0 lumens
Efficiency: N/A
Efficacy: 100.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 103.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032565

CATALOG NUMBER: S124DIW-B1195D1340UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1032565

CATALOG NUMBER: S124DIW-B1195D1340UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55
1	98	93	89	86	90	86	83	80	72	70	68	60	58	57	49	47	46
2	89	81	75	70	81	75	70	65	63	60	56	53	50	47	43	41	39
3	81	71	64	58	74	66	60	55	56	51	47	47	43	40	38	35	33
4	74	63	55	49	68	59	52	46	50	44	40	42	38	34	34	31	29
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	31	27	25
6	63	51	42	37	57	47	40	34	40	34	30	34	29	26	28	24	22
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	20
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	18
9	50	38	30	25	46	35	28	24	30	25	21	26	22	18	21	18	16
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16146	16146	16146
5°	16159	15681	15700
10°	16022	15246	15139
15°	15792	14729	14506
20°	15499	14169	13850
25°	15168	13577	13145
30°	14770	12938	12371
35°	14357	12282	11622
40°	13928	11578	10826
45°	13476	10871	10081
50°	12977	10186	9257
55°	12435	9386	8438
60°	11879	8510	7585
65°	11244	7605	6624
70°	10512	6515	5593
75°	9418	5252	4480
80°	8024	3797	3151
85°	6236	2114	1696

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13476 cd/sqm

TEST NUMBER: P1032565

CATALOG NUMBER: S124DIW-B1195D1340UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.6	1.8
10°-20°	525.8	5.1
20°-30°	773.8	7.4
30°-40°	899.5	8.6
40°-50°	899.4	8.6
50°-60°	786.6	7.6
60°-70°	584.0	5.6
70°-80°	331.4	3.2
80°-90°	98.5	0.9
90°-100°	57.1	0.5
100°-110°	376.0	3.6
110°-120°	718.0	6.9
120°-130°	911.5	8.8
130°-140°	975.1	9.4
140°-150°	911.8	8.8
150°-160°	735.3	7.1
160°-170°	474.2	4.6
170°-180°	163.4	1.6
0°-30°	1486.2	14.3
0°-40°	2385.7	22.9
0°-60°	4071.7	39.1
0°-90°	5085.6	48.9
90°-120°	1151.1	11.1
90°-150°	3949.5	37.9
90°-180°	5322.0	51.1
0°-180°	10408.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1980	1980	1980	1980	1980	
5°	1978	1972	1955	1972	1969	188
15°	1883	1877	1853	1863	1858	531
25°	1706	1694	1672	1674	1667	785
35°	1468	1456	1434	1423	1415	918
45°	1198	1187	1161	1144	1139	923
55°	906	901	879	860	850	811
65°	614	606	590	574	566	608
75°	327	319	311	305	303	347
85°	86	86	82	82	81	92
90°	4	18	28	36	39	9
95°	71	27	28	36	37	87
105°	387	395	401	413	367	405
115°	723	727	726	728	728	712
125°	1016	1022	1019	1023	1024	908
135°	1261	1260	1265	1267	1270	971
145°	1454	1458	1458	1459	1462	908
155°	1594	1595	1591	1596	1593	735
165°	1682	1675	1675	1685	1674	475
175°	1720	1712	1714	1725	1710	164
180°	1720	1720	1720	1720	1720	

TEST NUMBER: P1032565

CATALOG NUMBER: S124DIW-B1195D1340UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1980.0	1980.0	1980.0	1980.0	1980.0
2.5°	1986.3	1981.6	1964.1	1980.0	1978.4
5°	1978.4	1972.0	1954.6	1972.0	1968.9
7.5°	1964.1	1957.8	1938.7	1953.0	1951.4
10°	1943.5	1937.1	1916.5	1929.2	1926.0
12.5°	1916.5	1910.2	1888.0	1902.2	1897.5
15°	1883.2	1876.9	1853.1	1862.6	1857.8
17.5°	1845.1	1837.2	1815.0	1821.3	1818.2
20°	1802.3	1794.4	1770.6	1775.3	1772.1
22.5°	1756.3	1745.2	1721.4	1730.9	1724.5
25°	1705.5	1694.4	1672.2	1673.8	1667.4
27.5°	1648.4	1637.3	1616.7	1613.5	1605.6
30°	1591.3	1578.6	1558.0	1551.6	1543.7
32.5°	1531.0	1519.9	1497.7	1489.7	1481.8
35°	1467.5	1456.4	1434.2	1423.1	1415.2
37.5°	1400.9	1391.4	1367.6	1356.5	1345.4
40°	1335.9	1323.2	1299.4	1283.5	1275.6
42.5°	1266.0	1259.7	1232.7	1213.7	1208.9
45°	1197.8	1186.7	1161.3	1143.9	1139.1
47.5°	1126.4	1118.5	1094.7	1075.7	1063.0
50°	1053.4	1047.1	1024.9	1002.7	993.2
52.5°	982.1	974.1	950.3	931.3	918.6
55°	905.9	901.1	878.9	859.9	850.4
57.5°	834.5	829.8	807.5	788.5	779.0
60°	759.9	752.0	731.4	717.1	709.2
62.5°	687.0	680.6	658.4	645.7	637.8
65°	614.0	606.1	590.2	574.3	566.4
67.5°	539.4	533.1	517.2	501.3	499.8
70°	471.2	460.1	447.4	434.7	429.9
72.5°	398.2	387.1	377.6	368.1	363.3
75°	326.8	318.9	311.0	304.6	303.0
77.5°	257.0	253.8	245.9	244.3	239.6
80°	195.1	190.4	187.2	184.0	182.4
82.5°	134.9	133.3	133.3	131.7	130.1
85°	85.7	85.7	82.5	82.5	80.9
87.5°	41.2	39.7	38.1	38.1	38.1
90°	3.9	18.0	28.3	36.0	38.6
92.5°	19.3	16.7	27.0	34.7	34.7
95°	70.8	27.0	28.3	36.0	37.3
97.5°	135.1	163.4	28.3	34.7	36.0
100°	211.0	234.1	56.6	34.7	36.0
102.5°	295.9	311.3	326.8	37.3	37.3
105°	387.2	395.0	401.4	413.0	366.7
107.5°	470.9	474.7	483.7	490.2	495.3
110°	555.8	559.6	567.3	569.9	573.8

TEST NUMBER: P1032565

CATALOG NUMBER: S124DIW-B1195D1340UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	638.1	645.8	648.4	647.1	652.3
115°	723.0	726.9	725.6	728.2	728.2
117.5°	798.9	804.1	807.9	806.6	806.6
120°	876.1	881.3	880.0	882.5	880.0
122.5°	948.2	950.7	953.3	954.6	952.0
125°	1016.3	1021.5	1018.9	1022.8	1024.1
127.5°	1081.9	1083.2	1089.7	1088.4	1087.1
130°	1145.0	1146.3	1150.1	1151.4	1151.4
132.5°	1202.9	1205.5	1210.6	1211.9	1210.6
135°	1260.8	1259.5	1264.6	1267.2	1269.8
137.5°	1312.2	1312.2	1318.7	1321.2	1320.0
140°	1362.4	1365.0	1367.6	1371.4	1372.7
142.5°	1407.4	1412.6	1413.9	1416.4	1416.4
145°	1453.7	1457.6	1457.6	1458.9	1461.5
147.5°	1489.8	1497.5	1496.2	1497.5	1498.8
150°	1529.6	1534.8	1533.5	1533.5	1534.8
152.5°	1563.1	1567.0	1564.4	1567.0	1565.7
155°	1594.0	1595.3	1591.4	1596.5	1592.7
157.5°	1621.0	1621.0	1615.8	1622.3	1615.8
160°	1644.1	1640.3	1639.0	1646.7	1639.0
162.5°	1664.7	1659.6	1658.3	1666.0	1657.0
165°	1681.5	1675.0	1675.0	1685.3	1673.7
167.5°	1695.6	1689.2	1687.9	1699.5	1686.6
170°	1707.2	1699.5	1700.8	1711.0	1698.2
172.5°	1714.9	1707.2	1708.5	1718.8	1704.6
175°	1720.1	1712.3	1713.6	1725.2	1709.8
177.5°	1723.9	1714.9	1717.5	1727.8	1712.3
180°	1720.1	1720.1	1720.1	1720.1	1720.1

(END OF REPORT)