

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032155

Luminaire Tested: S123RDIW-B1165D460UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032155
REPORT IS A COMBINATION OF REPORTS P994113 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B1165D460UB50-4F0-XX-W2A-F1
Description: Define 3 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5775.0 lumens
Efficiency: N/A
Efficacy: 77.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 74.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032155

CATALOG NUMBER: S123RDIW-B1165D460UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1032155

CATALOG NUMBER: S123RDIW-B1165D460UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77
1	103	99	95	92	98	94	91	88	85	83	80	77	75	73	69	68	66
2	95	87	81	76	90	83	78	73	75	71	67	68	65	62	61	59	57
3	87	77	70	64	82	74	67	62	67	62	57	61	56	53	55	52	49
4	80	69	61	55	75	66	58	53	60	54	49	54	50	46	49	46	42
5	73	62	53	47	69	59	51	46	54	48	43	49	44	40	45	41	37
6	68	55	47	41	64	53	46	40	49	42	38	45	39	35	41	36	33
7	63	50	42	37	60	48	41	36	44	38	34	41	35	31	37	33	30
8	59	46	38	33	56	44	37	32	41	34	30	37	32	28	34	30	27
9	55	42	35	29	52	41	33	29	37	31	27	35	29	26	32	27	24
10	51	39	32	27	49	37	31	26	35	29	25	32	27	23	30	25	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20106	20106	20106
5°	20139	19395	19343
10°	19980	18665	18298
15°	19721	17764	17154
20°	19381	16784	15875
25°	19030	15765	14664
30°	18581	14682	13231
35°	18116	13618	11928
40°	17681	12462	10487
45°	17122	11332	9191
50°	16505	10124	7851
55°	15865	8832	6623
60°	15255	7507	5376
65°	14465	6147	4195
70°	13473	4649	2999
75°	12043	3148	2376
80°	10282	2187	1667
85°	7713	1181	873

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17122 cd/sqm

TEST NUMBER: P1032155

CATALOG NUMBER: S123RDIW-B1165D460UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	175.6	3.0
10°-20°	488.5	8.5
20°-30°	703.3	12.2
30°-40°	792.1	13.7
40°-50°	757.6	13.1
50°-60°	620.2	10.7
60°-70°	418.1	7.2
70°-80°	209.7	3.6
80°-90°	56.0	1.0
90°-100°	36.1	0.6
100°-110°	109.3	1.9
110°-120°	186.0	3.2
120°-130°	244.7	4.2
130°-140°	275.0	4.8
140°-150°	270.4	4.7
150°-160°	227.7	3.9
160°-170°	151.6	2.6
170°-180°	53.1	0.9
0°-30°	1367.4	23.7
0°-40°	2159.5	37.4
0°-60°	3537.3	61.3
0°-90°	4221.2	73.1
90°-120°	331.4	5.7
90°-150°	1121.5	19.4
90°-180°	1554.0	26.9
0°-180°	5775.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1868	1868	1868	1868	1868	
5°	1868	1860	1842	1856	1853	177
15°	1782	1765	1722	1715	1704	502
25°	1621	1583	1513	1482	1465	746
35°	1403	1348	1254	1189	1162	878
45°	1153	1085	968	882	845	890
55°	876	801	673	585	554	785
65°	598	515	397	323	306	592
75°	317	244	161	145	142	337
85°	80	47	42	39	39	88
90°	0	5	11	12	13	7
95°	26	29	33	34	34	29
105°	99	100	104	104	105	106
115°	187	188	188	188	188	185
125°	274	275	274	273	271	244
135°	356	358	358	356	355	274
145°	431	432	434	433	431	269
155°	494	494	494	496	493	227
165°	538	536	536	539	536	152
175°	560	558	558	560	557	53
180°	561	561	561	561	561	

TEST NUMBER: P1032155

CATALOG NUMBER: S123RDIW-B1165D460UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1867.9	1867.9	1867.9	1867.9	1867.9
2.5°	1875.5	1869.5	1851.3	1867.9	1864.9
5°	1867.9	1860.4	1842.2	1855.8	1852.8
7.5°	1854.3	1846.7	1824.0	1833.1	1828.5
10°	1836.1	1825.5	1798.2	1799.8	1792.2
12.5°	1810.4	1798.2	1763.4	1761.9	1752.8
15°	1781.6	1764.9	1722.5	1714.9	1704.3
17.5°	1746.7	1728.6	1675.5	1660.4	1645.2
20°	1707.4	1683.1	1625.5	1605.8	1587.7
22.5°	1663.4	1634.6	1572.5	1546.8	1530.1
25°	1621.0	1583.1	1513.4	1481.6	1465.0
27.5°	1569.5	1528.6	1452.8	1410.4	1384.7
30°	1516.5	1471.0	1386.2	1334.7	1310.4
32.5°	1463.4	1410.4	1319.5	1262.0	1236.2
35°	1402.8	1348.3	1254.4	1189.2	1162.0
37.5°	1342.2	1283.2	1184.7	1112.0	1078.6
40°	1284.7	1218.0	1110.5	1031.7	996.8
42.5°	1219.5	1152.9	1040.8	952.9	922.6
45°	1152.9	1084.7	968.1	881.7	845.3
47.5°	1087.7	1012.0	896.9	802.9	771.1
50°	1015.0	943.8	821.1	727.2	692.3
52.5°	949.9	871.1	749.9	651.4	621.1
55°	875.6	801.4	672.6	584.8	554.5
57.5°	809.0	728.7	598.4	515.1	489.3
60°	739.3	656.0	530.2	448.4	422.7
62.5°	669.6	586.3	460.5	384.8	357.5
65°	598.4	515.1	396.9	322.7	306.0
67.5°	527.2	442.4	327.2	271.2	253.0
70°	457.5	375.7	269.7	216.6	200.0
72.5°	387.8	307.5	213.6	172.7	168.2
75°	316.6	243.9	160.6	145.4	142.4
77.5°	251.5	184.8	125.7	116.7	113.6
80°	189.4	127.3	95.4	90.9	87.9
82.5°	130.3	78.8	68.2	63.6	63.6
85°	80.3	47.0	42.4	39.4	39.4
87.5°	36.4	19.7	19.7	18.2	16.7
90°	0.4	4.8	10.6	12.3	13.2
92.5°	13.2	15.9	18.5	19.8	18.9
95°	26.0	29.1	32.6	34.4	34.4
97.5°	42.7	44.9	47.6	49.8	49.3
100°	59.9	62.6	64.8	66.1	67.0
102.5°	79.7	81.1	84.1	85.5	85.0
105°	99.1	100.0	104.0	104.0	104.8
107.5°	122.0	122.5	124.2	125.5	125.1
110°	143.2	144.0	144.9	146.7	145.8

TEST NUMBER: P1032155

CATALOG NUMBER: S123RDIW-B1165D460UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	165.2	165.6	165.6	167.8	167.8
115°	187.2	188.5	187.7	188.1	187.7
117.5°	209.7	210.1	209.2	209.2	207.9
120°	230.4	233.0	230.8	230.4	229.5
122.5°	252.0	253.7	252.9	251.5	250.2
125°	274.0	275.3	274.4	272.7	270.9
127.5°	294.3	296.9	296.0	293.4	291.6
130°	314.5	318.1	316.7	315.0	311.9
132.5°	334.8	338.3	337.4	335.2	333.0
135°	355.5	358.1	357.7	355.9	355.1
137.5°	374.4	376.6	378.0	375.8	374.4
140°	394.3	396.5	396.9	396.5	393.4
142.5°	412.3	414.5	415.4	415.0	412.8
145°	431.3	432.1	433.5	433.0	431.3
147.5°	447.6	449.3	450.6	450.6	448.0
150°	464.7	465.6	466.5	466.5	463.9
152.5°	478.8	480.2	480.6	481.5	479.3
155°	493.8	493.8	494.3	496.0	492.9
157.5°	506.6	506.2	506.6	508.4	505.7
160°	518.5	517.6	517.6	519.8	518.0
162.5°	529.1	527.7	528.2	530.4	527.3
165°	537.9	536.5	536.5	539.2	536.1
167.5°	545.4	543.6	544.0	546.7	544.0
170°	551.5	549.8	549.8	552.8	549.8
172.5°	556.4	554.6	554.6	557.3	554.2
175°	559.5	557.7	557.7	560.3	557.3
177.5°	561.2	559.5	559.5	562.1	559.0
180°	560.8	560.8	560.8	560.8	560.8

(END OF REPORT)