

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032575

Luminaire Tested: S124DIW-B1195D1560UB2750-4F0-XX-W2A-D_2700K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032575
REPORT IS A COMBINATION OF REPORTS P997099 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B1195D1560UB2750-4F0-XX-W2A-D_2700K
Description: Define 4 Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11111.0 lumens
Efficiency: N/A
Efficacy: 97.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 113.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032575

CATALOG NUMBER: S124DIW-B1195D1560UB2750-4F0-XX-W2A-D_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1032575

CATALOG NUMBER: S124DIW-B1195D1560UB2750-4F0-XX-W2A-D_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47
1	95	90	86	82	86	82	79	75	67	64	62	53	51	50	40	39	38
2	86	78	72	66	78	71	66	61	58	54	51	46	43	41	35	33	31
3	78	68	61	55	71	62	56	51	51	46	42	41	37	34	31	28	26
4	71	60	52	46	64	55	48	43	45	40	36	36	32	29	27	25	22
5	65	54	45	39	59	49	42	36	40	35	31	32	28	25	24	22	19
6	60	48	40	34	54	44	37	31	36	31	26	29	25	22	22	19	17
7	55	43	35	29	50	39	32	27	33	27	23	26	22	19	20	17	15
8	51	39	31	26	47	36	29	24	30	24	20	24	20	17	18	16	13
9	48	35	28	23	43	33	26	21	27	22	18	22	18	15	17	14	12
10	45	32	25	20	40	30	23	19	25	20	16	20	16	14	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11555	11555	11555
5°	11586	11254	11274
10°	11511	11032	11000
15°	11403	10783	10692
20°	11244	10513	10393
25°	11064	10216	10070
30°	10869	9922	9740
35°	10649	9621	9447
40°	10472	9331	9144
45°	10211	9060	8875
50°	9988	8752	8592
55°	9758	8456	8266
60°	9401	8086	7959
65°	9008	7688	7590
70°	8531	7233	7163
75°	7864	6726	6757
80°	7115	6210	6331
85°	6120	5691	5986

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10211 cd/sqm

TEST NUMBER: P1032575

CATALOG NUMBER: S124DIW-B1195D1560UB2750-4F0-XX-W2A-D_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.3	1.2
10°-20°	384.7	3.5
20°-30°	581.6	5.2
30°-40°	703.7	6.3
40°-50°	743.9	6.7
50°-60°	700.1	6.3
60°-70°	581.0	5.2
70°-80°	407.7	3.7
80°-90°	234.0	2.1
90°-100°	204.2	1.8
100°-110°	544.7	4.9
110°-120°	914.6	8.2
120°-130°	1113.1	10.0
130°-140°	1166.3	10.5
140°-150°	1078.4	9.7
150°-160°	867.0	7.8
160°-170°	559.1	5.0
170°-180°	192.7	1.7
0°-30°	1100.6	9.9
0°-40°	1804.2	16.2
0°-60°	3248.2	29.2
0°-90°	4470.9	40.2
90°-120°	1663.5	15.0
90°-150°	5021.3	45.2
90°-180°	6640.0	59.8
0°-180°	11111.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1417	1417	1417	1417	1417	
5°	1418	1414	1403	1415	1414	135
15°	1360	1361	1357	1371	1369	383
25°	1244	1254	1258	1276	1277	573
35°	1088	1108	1123	1146	1150	682
45°	908	938	968	995	1003	701
55°	711	744	792	824	833	633
65°	492	543	597	636	649	488
75°	273	332	398	443	457	290
85°	84	151	222	270	286	88
90°	30	110	190	246	261	22
95°	104	105	171	223	239	119
105°	471	512	578	631	589	494
115°	862	881	930	968	979	849
125°	1205	1209	1246	1281	1292	1076
135°	1490	1488	1506	1534	1546	1148
145°	1716	1719	1719	1730	1739	1072
155°	1880	1881	1876	1882	1878	867
165°	1983	1975	1975	1987	1974	560
175°	2028	2019	2021	2034	2016	193
180°	2028	2028	2028	2028	2028	

TEST NUMBER: P1032575

CATALOG NUMBER: S124DIW-B1195D1560UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1417.0	1417.0	1417.0	1417.0	1417.0
2.5°	1423.3	1418.5	1405.9	1417.0	1415.4
5°	1418.5	1413.8	1402.7	1415.4	1413.8
7.5°	1409.0	1405.9	1396.3	1410.6	1409.0
10°	1396.3	1394.7	1386.8	1401.1	1399.5
12.5°	1378.9	1378.9	1374.1	1386.8	1386.8
15°	1359.8	1361.4	1356.7	1370.9	1369.4
17.5°	1334.5	1339.2	1337.6	1351.9	1350.3
20°	1307.5	1312.2	1313.8	1329.7	1329.7
22.5°	1277.3	1283.7	1286.8	1302.7	1305.9
25°	1244.0	1253.5	1258.3	1275.7	1277.3
27.5°	1207.5	1221.8	1228.1	1244.0	1245.6
30°	1171.0	1183.7	1194.8	1212.3	1215.4
32.5°	1131.3	1147.2	1159.9	1180.5	1183.7
35°	1088.5	1107.5	1123.4	1145.6	1150.4
37.5°	1045.7	1067.9	1086.9	1109.1	1113.9
40°	1004.4	1025.0	1047.2	1071.1	1077.4
42.5°	956.8	980.6	1007.6	1034.6	1039.3
45°	907.6	937.8	967.9	994.9	1002.8
47.5°	861.6	891.7	926.7	953.6	963.2
50°	810.8	845.7	880.6	912.4	921.9
52.5°	760.0	795.0	836.2	867.9	877.5
55°	710.9	744.2	791.8	823.5	833.0
57.5°	655.3	696.6	742.6	780.7	788.6
60°	601.4	642.6	695.0	731.5	744.2
62.5°	549.0	595.0	647.4	683.9	696.6
65°	491.9	542.7	596.6	636.3	649.0
67.5°	437.9	491.9	549.0	588.7	601.4
70°	382.4	436.4	496.7	539.5	550.6
72.5°	328.5	384.0	449.0	490.3	503.0
75°	272.9	331.6	398.3	442.7	457.0
77.5°	220.6	282.4	352.3	396.7	412.6
80°	173.0	236.4	306.2	353.8	366.5
82.5°	125.4	192.0	261.8	311.0	325.3
85°	84.1	150.7	222.1	269.7	285.6
87.5°	52.4	117.4	187.2	233.3	247.5
90°	30.0	110.1	190.5	245.6	261.3
92.5°	46.6	99.0	179.5	233.0	245.7
95°	104.0	104.9	171.4	223.4	239.2
97.5°	178.3	257.8	163.5	212.4	228.1
100°	266.3	334.8	187.3	204.4	217.0
102.5°	366.4	419.5	498.0	197.9	210.6
105°	470.9	511.7	578.0	631.3	589.4
107.5°	569.5	601.1	667.2	714.5	731.6
110°	668.0	694.8	759.4	798.9	816.2

TEST NUMBER: P1032575

CATALOG NUMBER: S124DIW-B1195D1560UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	763.5	791.6	847.0	880.4	899.2
115°	862.0	880.9	930.2	968.1	979.2
117.5°	951.5	967.1	1019.2	1051.1	1063.8
120°	1040.9	1051.8	1096.3	1131.0	1140.7
122.5°	1125.9	1128.9	1174.9	1208.1	1216.1
125°	1204.7	1209.3	1245.8	1280.6	1291.6
127.5°	1282.0	1282.1	1321.3	1348.4	1358.0
130°	1354.9	1354.8	1384.7	1414.8	1424.3
132.5°	1423.1	1424.6	1449.6	1478.2	1486.1
135°	1489.8	1488.3	1505.5	1533.9	1546.4
137.5°	1550.5	1548.9	1562.8	1589.6	1596.1
140°	1609.6	1611.1	1615.7	1640.9	1650.3
142.5°	1661.1	1667.2	1667.1	1687.7	1694.0
145°	1715.7	1718.7	1718.7	1729.7	1739.1
147.5°	1758.2	1765.7	1764.2	1767.3	1775.1
150°	1805.2	1809.7	1808.2	1808.2	1809.7
152.5°	1843.1	1847.6	1844.6	1847.6	1846.1
155°	1879.5	1881.0	1876.5	1882.5	1878.0
157.5°	1911.3	1911.3	1905.3	1912.9	1905.3
160°	1938.7	1934.1	1932.6	1941.7	1932.6
162.5°	1962.9	1956.9	1955.3	1964.4	1953.8
165°	1982.6	1975.1	1975.1	1987.2	1973.5
167.5°	1999.3	1991.7	1990.2	2003.9	1988.7
170°	2013.0	2003.9	2005.4	2017.5	2002.4
172.5°	2022.1	2013.0	2014.5	2026.6	2009.9
175°	2028.2	2019.0	2020.6	2034.2	2016.0
177.5°	2032.7	2022.1	2025.1	2037.3	2019.0
180°	2028.2	2028.2	2028.2	2028.2	2028.2

(END OF REPORT)