

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032576

Luminaire Tested: S124DIW-B1195D1560UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032576
REPORT IS A COMBINATION OF REPORTS P997100 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B1195D1560UB2750-4F0-XX-W2A-D_3000K
Description: Define 4 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11206.9 lumens
Efficiency: N/A
Efficacy: 98.7 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 113.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032576

CATALOG NUMBER: S124DIW-B1195D1560UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1032576

CATALOG NUMBER: S124DIW-B1195D1560UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47
1	95	90	86	82	86	82	79	75	67	64	62	53	51	50	40	39	38
2	86	78	72	66	78	71	66	61	58	54	51	46	43	41	35	33	31
3	78	68	61	55	71	62	56	51	51	46	42	40	37	34	31	28	26
4	71	60	52	46	64	55	48	43	45	40	36	36	32	29	27	25	22
5	65	54	45	39	59	49	42	36	40	35	31	32	28	25	24	22	19
6	60	48	40	34	54	44	37	31	36	31	26	29	25	22	22	19	17
7	55	43	35	29	50	39	32	27	33	27	23	26	22	19	20	17	15
8	51	39	31	26	47	36	29	24	30	24	20	24	20	17	18	16	13
9	48	35	28	23	43	33	26	21	27	22	18	22	18	15	17	14	12
10	45	32	25	20	40	30	23	19	25	20	16	20	16	14	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11653	11653	11653
5°	11685	11349	11370
10°	11609	11126	11094
15°	11501	10875	10783
20°	11339	10603	10481
25°	11158	10303	10156
30°	10962	10006	9823
35°	10739	9702	9528
40°	10561	9411	9221
45°	10298	9137	8950
50°	10073	8827	8665
55°	9841	8527	8336
60°	9481	8155	8027
65°	9085	7753	7654
70°	8605	7294	7225
75°	7931	6784	6815
80°	7173	6263	6384
85°	6171	5740	6037

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10298 cd/sqm

TEST NUMBER: P1032576

CATALOG NUMBER: S124DIW-B1195D1560UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.4	1.2
10°-20°	387.9	3.5
20°-30°	586.6	5.2
30°-40°	709.6	6.3
40°-50°	750.2	6.7
50°-60°	706.0	6.3
60°-70°	585.9	5.2
70°-80°	411.1	3.7
80°-90°	236.0	2.1
90°-100°	205.9	1.8
100°-110°	549.4	4.9
110°-120°	922.6	8.2
120°-130°	1122.8	10.0
130°-140°	1176.5	10.5
140°-150°	1087.8	9.7
150°-160°	874.6	7.8
160°-170°	564.0	5.0
170°-180°	194.4	1.7
0°-30°	1109.9	9.9
0°-40°	1819.6	16.2
0°-60°	3275.8	29.2
0°-90°	4508.8	40.2
90°-120°	1677.9	15.0
90°-150°	5065.1	45.2
90°-180°	6698.0	59.8
0°-180°	11206.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1429	1429	1429	1429	1429	
5°	1431	1426	1415	1427	1426	136
15°	1371	1373	1368	1383	1381	386
25°	1255	1264	1269	1287	1288	578
35°	1098	1117	1133	1155	1160	687
45°	915	946	976	1003	1011	707
55°	717	750	798	830	840	639
65°	496	547	602	642	654	492
75°	275	334	402	446	461	292
85°	85	152	224	272	288	88
90°	30	111	192	248	264	22
95°	105	106	173	225	241	120
105°	475	516	583	637	594	498
115°	870	889	938	976	988	857
125°	1215	1220	1257	1292	1303	1086
135°	1503	1501	1519	1547	1560	1158
145°	1731	1734	1734	1745	1754	1082
155°	1896	1898	1893	1899	1894	874
165°	2000	1992	1992	2005	1991	565
175°	2046	2037	2038	2052	2034	195
180°	2046	2046	2046	2046	2046	

TEST NUMBER: P1032576

CATALOG NUMBER: S124DIW-B1195D1560UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1429.0	1429.0	1429.0	1429.0	1429.0
2.5°	1435.4	1430.6	1417.8	1429.0	1427.4
5°	1430.6	1425.8	1414.6	1427.4	1425.8
7.5°	1421.0	1417.8	1408.2	1422.6	1421.0
10°	1408.2	1406.6	1398.6	1413.0	1411.4
12.5°	1390.6	1390.6	1385.8	1398.6	1398.6
15°	1371.4	1373.0	1368.2	1382.6	1381.0
17.5°	1345.8	1350.6	1349.0	1363.4	1361.8
20°	1318.6	1323.4	1325.0	1341.0	1341.0
22.5°	1288.2	1294.6	1297.8	1313.8	1317.0
25°	1254.6	1264.2	1269.0	1286.6	1288.2
27.5°	1217.8	1232.2	1238.6	1254.6	1256.2
30°	1181.0	1193.8	1205.0	1222.6	1225.8
32.5°	1140.9	1157.0	1169.8	1190.6	1193.8
35°	1097.7	1116.9	1132.9	1155.4	1160.2
37.5°	1054.5	1076.9	1096.1	1118.5	1123.3
40°	1012.9	1033.7	1056.1	1080.1	1086.5
42.5°	964.9	988.9	1016.1	1043.3	1048.1
45°	915.3	945.7	976.1	1003.3	1011.3
47.5°	868.9	899.3	934.5	961.7	971.3
50°	817.7	852.9	888.1	920.1	929.7
52.5°	766.5	801.7	843.3	875.3	884.9
55°	716.9	750.5	798.5	830.5	840.1
57.5°	660.9	702.5	748.9	787.3	795.3
60°	606.5	648.1	700.9	737.7	750.5
62.5°	553.7	600.1	652.9	689.7	702.5
65°	496.1	547.3	601.7	641.7	654.5
67.5°	441.7	496.1	553.7	593.7	606.5
70°	385.7	440.1	500.9	544.1	555.3
72.5°	331.2	387.3	452.9	494.5	507.3
75°	275.2	334.4	401.7	446.5	460.9
77.5°	222.4	284.8	355.2	400.1	416.1
80°	174.4	238.4	308.8	356.8	369.6
82.5°	126.4	193.6	264.0	313.6	328.0
85°	84.8	152.0	224.0	272.0	288.0
87.5°	52.8	118.4	188.8	235.2	249.6
90°	30.2	111.0	192.1	247.6	263.5
92.5°	47.0	99.9	180.9	234.9	247.7
95°	105.0	105.7	172.9	225.2	241.2
97.5°	179.9	259.9	164.9	214.1	230.0
100°	268.6	337.7	188.9	206.1	218.8
102.5°	369.6	423.1	502.3	199.6	212.4
105°	475.0	516.2	583.0	636.8	594.5
107.5°	574.5	606.3	673.0	720.6	737.9
110°	673.9	700.8	766.0	805.9	823.3

TEST NUMBER: P1032576

CATALOG NUMBER: S124DIW-B1195D1560UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	770.2	798.6	854.4	888.1	907.0
115°	869.6	888.6	938.2	976.5	987.7
117.5°	959.9	975.6	1028.2	1060.3	1073.1
120°	1050.1	1061.0	1105.9	1140.9	1150.7
122.5°	1135.8	1138.8	1185.1	1218.6	1226.8
125°	1215.3	1219.8	1256.7	1291.7	1302.9
127.5°	1293.3	1293.3	1332.9	1360.2	1369.8
130°	1366.7	1366.6	1396.8	1427.2	1436.8
132.5°	1435.6	1437.0	1462.3	1491.1	1499.1
135°	1502.8	1501.3	1518.6	1547.3	1559.9
137.5°	1564.0	1562.4	1576.5	1603.5	1610.0
140°	1623.7	1625.2	1629.8	1655.2	1664.8
142.5°	1675.7	1681.8	1681.7	1702.4	1708.8
145°	1730.8	1733.7	1733.7	1744.9	1754.3
147.5°	1773.6	1781.2	1779.7	1782.8	1790.7
150°	1821.0	1825.6	1824.0	1824.0	1825.6
152.5°	1859.2	1863.8	1860.8	1863.8	1862.3
155°	1896.0	1897.5	1892.9	1899.0	1894.4
157.5°	1928.1	1928.1	1922.0	1929.6	1922.0
160°	1955.6	1951.0	1949.5	1958.7	1949.5
162.5°	1980.1	1974.0	1972.5	1981.6	1970.9
165°	2000.0	1992.4	1992.4	2004.6	1990.8
167.5°	2016.8	2009.2	2007.7	2021.4	2006.1
170°	2030.6	2021.4	2023.0	2035.2	2019.9
172.5°	2039.8	2030.6	2032.1	2044.4	2027.5
175°	2045.9	2036.7	2038.3	2052.0	2033.7
177.5°	2050.5	2039.8	2042.9	2055.1	2036.7
180°	2045.9	2045.9	2045.9	2045.9	2045.9

(END OF REPORT)