

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032167

Luminaire Tested: S123RDIW-B1165D755UB35-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032167
REPORT IS A COMBINATION OF REPORTS P994145 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B1165D755UB35-4F0-XX-W2A-F1
Description: Define 3 Regressed Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7084.0 lumens
Efficiency: N/A
Efficacy: 83.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 84.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032167

CATALOG NUMBER: S123RDIW-B1165D755UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1032167

CATALOG NUMBER: S123RDIW-B1165D755UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67
1	101	97	93	89	94	91	87	84	80	77	75	70	68	66	60	59	58
2	92	85	79	74	86	80	75	70	70	66	63	62	59	56	53	51	49
3	84	75	68	62	79	71	64	59	62	57	53	55	51	48	48	45	42
4	77	67	59	53	72	63	56	50	56	50	46	49	45	41	43	40	37
5	71	60	52	46	67	56	49	44	50	44	40	44	40	36	39	35	32
6	66	54	46	40	62	51	44	38	45	39	35	40	35	32	35	32	29
7	61	49	41	35	57	46	39	34	41	35	31	37	32	28	32	29	26
8	57	44	37	31	53	42	35	30	38	32	28	34	29	25	30	26	23
9	53	41	33	28	50	39	32	27	35	29	25	31	26	23	28	24	21
10	50	37	30	25	47	36	29	24	32	26	23	29	24	21	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20997	20997	20997
5°	21031	20254	20200
10°	20866	19492	19109
15°	20595	18551	17913
20°	20240	17528	16578
25°	19873	16464	15314
30°	19404	15332	13818
35°	18919	14221	12457
40°	18464	13014	10952
45°	17881	11834	9599
50°	17237	10573	8199
55°	16568	9223	6915
60°	15932	7839	5613
65°	15106	6420	4382
70°	14071	4854	3131
75°	12580	3287	2481
80°	10738	2285	1741
85°	8059	1234	911

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17881 cd/sqm

TEST NUMBER: P1032167

CATALOG NUMBER: S123RDIW-B1165D755UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.4	2.6
10°-20°	510.1	7.2
20°-30°	734.5	10.4
30°-40°	827.2	11.7
40°-50°	791.2	11.2
50°-60°	647.7	9.1
60°-70°	436.7	6.2
70°-80°	219.0	3.1
80°-90°	59.3	0.8
90°-100°	62.2	0.9
100°-110°	188.1	2.7
110°-120°	320.2	4.5
120°-130°	421.3	5.9
130°-140°	473.5	6.7
140°-150°	465.5	6.6
150°-160°	391.9	5.5
160°-170°	260.9	3.7
170°-180°	91.4	1.3
0°-30°	1428.0	20.2
0°-40°	2255.2	31.8
0°-60°	3694.0	52.1
0°-90°	4409.0	62.2
90°-120°	570.5	8.1
90°-150°	1930.7	27.3
90°-180°	2675.0	37.8
0°-180°	7084.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1951	1951	1951	1951	1951	
5°	1951	1943	1924	1938	1935	185
15°	1860	1843	1799	1791	1780	524
25°	1693	1653	1580	1547	1530	779
35°	1465	1408	1310	1242	1214	917
45°	1204	1133	1011	921	883	929
55°	914	837	702	611	579	820
65°	625	538	414	337	320	618
75°	331	255	168	152	149	352
85°	84	49	44	41	41	92
90°	1	8	18	21	23	9
95°	45	50	56	59	59	49
105°	171	172	179	179	180	183
115°	322	325	323	324	323	319
125°	472	474	472	469	466	421
135°	612	617	616	613	611	472
145°	742	744	746	746	742	464
155°	850	850	851	854	849	391
165°	926	924	924	928	923	261
175°	963	960	960	965	959	92
180°	965	965	965	965	965	

TEST NUMBER: P1032167

CATALOG NUMBER: S123RDIW-B1165D755UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1950.7	1950.7	1950.7	1950.7	1950.7
2.5°	1958.6	1952.3	1933.3	1950.7	1947.5
5°	1950.7	1942.8	1923.8	1938.1	1934.9
7.5°	1936.5	1928.6	1904.8	1914.3	1909.6
10°	1917.5	1906.4	1877.9	1879.5	1871.6
12.5°	1890.6	1877.9	1841.5	1840.0	1830.5
15°	1860.5	1843.1	1798.8	1790.9	1779.8
17.5°	1824.1	1805.2	1749.8	1734.0	1718.1
20°	1783.0	1757.7	1697.6	1677.0	1658.0
22.5°	1737.1	1707.1	1642.2	1615.3	1597.9
25°	1692.8	1653.3	1580.5	1547.3	1529.9
27.5°	1639.0	1596.3	1517.2	1472.9	1446.0
30°	1583.7	1536.2	1447.6	1393.8	1368.5
32.5°	1528.3	1472.9	1378.0	1317.9	1291.0
35°	1465.0	1408.1	1310.0	1241.9	1213.5
37.5°	1401.7	1340.0	1237.2	1161.2	1126.4
40°	1341.6	1272.0	1159.7	1077.4	1041.0
42.5°	1273.6	1204.0	1086.9	995.1	963.5
45°	1204.0	1132.8	1011.0	920.8	882.8
47.5°	1135.9	1056.8	936.6	838.5	805.3
50°	1060.0	985.6	857.5	759.4	723.0
52.5°	992.0	909.7	783.1	680.3	648.7
55°	914.4	836.9	702.4	610.7	579.0
57.5°	844.8	761.0	624.9	537.9	511.0
60°	772.1	685.0	553.7	468.3	441.4
62.5°	699.3	612.3	481.0	401.8	373.4
65°	624.9	537.9	414.5	337.0	319.6
67.5°	550.6	462.0	341.7	283.2	264.2
70°	477.8	392.4	281.6	226.2	208.8
72.5°	405.0	321.2	223.1	180.4	175.6
75°	330.7	254.7	167.7	151.9	148.7
77.5°	262.6	193.0	131.3	121.8	118.7
80°	197.8	132.9	99.7	94.9	91.8
82.5°	136.1	82.3	71.2	66.4	66.4
85°	83.9	49.0	44.3	41.1	41.1
87.5°	38.0	20.6	20.6	19.0	17.4
90°	0.8	8.3	18.2	21.2	22.8
92.5°	22.8	27.3	31.9	34.1	32.6
95°	44.7	50.1	56.1	59.2	59.2
97.5°	73.6	77.4	81.9	85.7	84.9
100°	103.1	107.7	111.5	113.8	115.3
102.5°	137.3	139.5	144.8	147.1	146.4
105°	170.6	172.1	179.0	179.0	180.5
107.5°	210.1	210.8	213.9	216.1	215.4
110°	246.5	248.0	249.5	252.5	251.0

TEST NUMBER: P1032167

CATALOG NUMBER: S123RDIW-B1165D755UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	284.4	285.1	285.1	288.9	288.9
115°	322.3	324.6	323.1	323.8	323.1
117.5°	361.0	361.7	360.2	360.2	358.0
120°	396.6	401.2	397.4	396.6	395.1
122.5°	433.8	436.8	435.3	433.0	430.8
125°	471.7	474.0	472.5	469.4	466.4
127.5°	506.6	511.1	509.6	505.1	502.0
130°	541.5	547.5	545.3	542.2	536.9
132.5°	576.4	582.4	580.9	577.1	573.3
135°	612.0	616.6	615.8	612.8	611.2
137.5°	644.6	648.4	650.7	646.9	644.6
140°	678.7	682.5	683.3	682.5	677.2
142.5°	709.8	713.6	715.1	714.4	710.6
145°	742.4	744.0	746.2	745.5	742.4
147.5°	770.5	773.5	775.8	775.8	771.3
150°	800.1	801.6	803.1	803.1	798.6
152.5°	824.3	826.6	827.4	828.9	825.1
155°	850.1	850.1	850.9	853.9	848.6
157.5°	872.1	871.4	872.1	875.2	870.6
160°	892.6	891.1	891.1	894.9	891.8
162.5°	910.8	908.5	909.3	913.1	907.8
165°	926.0	923.7	923.7	928.2	922.9
167.5°	938.9	935.8	936.6	941.1	936.6
170°	949.5	946.4	946.4	951.8	946.4
172.5°	957.8	954.8	954.8	959.3	954.0
175°	963.1	960.1	960.1	964.6	959.3
177.5°	966.2	963.1	963.1	967.7	962.4
180°	965.4	965.4	965.4	965.4	965.4

(END OF REPORT)