

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032182

Luminaire Tested: S123RDIW-B340D1030UB30-4F0-XX-W2A-F

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032182
REPORT IS A COMBINATION OF REPORTS P994182 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B340D1030UB30-4F0-XX-W2A-F
Description: Define 3 Regressed Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5446.0 lumens
Efficiency: N/A
Efficacy: 122.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 44.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032182

CATALOG NUMBER: S123RDIW-B340D1030UB30-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1032182

CATALOG NUMBER: S123RDIW-B340D1030UB30-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	68	68	68	49	49	49	32	32	32
1	92	88	84	81	82	78	75	72	60	58	56	43	42	41	28	27	27
2	84	77	71	66	74	68	64	60	53	50	47	38	36	35	25	24	23
3	76	68	61	55	68	60	54	50	47	43	39	34	31	29	22	21	20
4	70	60	52	47	62	53	47	42	41	37	34	30	27	25	20	18	17
5	64	53	45	40	57	48	41	36	37	32	29	27	24	22	18	16	15
6	59	48	40	34	52	43	36	31	33	29	25	24	21	19	16	14	13
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12
8	50	39	31	26	45	35	28	24	27	23	19	20	17	15	14	12	10
9	47	35	28	23	42	32	25	21	25	20	17	19	15	13	13	11	9
10	44	32	25	21	39	29	23	19	23	18	15	17	14	12	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6018	6018	6018
5°	6028	5804	5789
10°	5980	5586	5477
15°	5902	5316	5134
20°	5801	5023	4752
25°	5695	4719	4388
30°	5561	4394	3960
35°	5423	4075	3570
40°	5292	3729	3138
45°	5124	3391	2751
50°	4940	3029	2350
55°	4749	2643	1981
60°	4566	2247	1609
65°	4329	1840	1256
70°	4032	1391	897
75°	3606	943	711
80°	3078	656	499
85°	2305	354	262

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5124 cd/sqm

TEST NUMBER: P1032182

CATALOG NUMBER: S123RDIW-B340D1030UB30-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.6	1.0
10°-20°	146.2	2.7
20°-30°	210.5	3.9
30°-40°	237.1	4.4
40°-50°	226.7	4.2
50°-60°	185.6	3.4
60°-70°	125.1	2.3
70°-80°	62.8	1.2
80°-90°	19.2	0.4
90°-100°	48.4	0.9
100°-110°	233.8	4.3
110°-120°	572.9	10.5
120°-130°	727.3	13.4
130°-140°	776.9	14.3
140°-150°	726.5	13.3
150°-160°	586.0	10.8
160°-170°	378.2	6.9
170°-180°	130.3	2.4
0°-30°	409.2	7.5
0°-40°	646.3	11.9
0°-60°	1058.7	19.4
0°-90°	1265.7	23.2
90°-120°	855.0	15.7
90°-150°	3085.8	56.7
90°-180°	4180.0	76.8
0°-180°	5446.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	559	559	559	559	559	
5°	559	557	551	555	554	53
15°	533	528	516	513	510	150
25°	485	474	453	443	438	223
35°	420	404	375	356	348	263
45°	345	325	290	264	253	266
55°	262	240	201	175	166	235
65°	179	154	119	97	92	177
75°	95	73	48	44	43	101
85°	24	14	13	12	12	26
90°	1	11	24	28	31	5
95°	62	20	32	39	39	74
105°	304	315	223	43	45	322
115°	570	576	585	595	599	562
125°	803	811	815	817	819	717
135°	999	1006	1010	1013	1010	769
145°	1153	1160	1162	1164	1164	722
155°	1270	1268	1269	1274	1268	585
165°	1340	1337	1336	1344	1337	379
175°	1371	1366	1367	1374	1366	130
180°	1371	1371	1371	1371	1371	

TEST NUMBER: P1032182

CATALOG NUMBER: S123RDIW-B340D1030UB30-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	559.1	559.1	559.1	559.1	559.1
2.5°	561.3	559.5	554.1	559.1	558.1
5°	559.1	556.8	551.3	555.4	554.5
7.5°	555.0	552.7	545.9	548.6	547.3
10°	549.5	546.4	538.2	538.6	536.4
12.5°	541.8	538.2	527.8	527.3	524.6
15°	533.2	528.2	515.5	513.3	510.1
17.5°	522.8	517.3	501.5	496.9	492.4
20°	511.0	503.7	486.5	480.6	475.2
22.5°	497.8	489.2	470.6	462.9	457.9
25°	485.1	473.8	453.0	443.4	438.4
27.5°	469.7	457.5	434.8	422.1	414.4
30°	453.9	440.3	414.9	399.5	392.2
32.5°	438.0	422.1	394.9	377.7	370.0
35°	419.9	403.5	375.4	355.9	347.8
37.5°	401.7	384.0	354.6	332.8	322.8
40°	384.5	364.5	332.3	308.8	298.3
42.5°	365.0	345.0	311.5	285.2	276.1
45°	345.0	324.6	289.7	263.9	253.0
47.5°	325.5	302.9	268.4	240.3	230.8
50°	303.8	282.5	245.7	217.6	207.2
52.5°	284.3	260.7	224.4	195.0	185.9
55°	262.1	239.9	201.3	175.0	165.9
57.5°	242.1	218.1	179.1	154.2	146.5
60°	221.3	196.3	158.7	134.2	126.5
62.5°	200.4	175.5	137.8	115.2	107.0
65°	179.1	154.2	118.8	96.6	91.6
67.5°	157.8	132.4	97.9	81.2	75.7
70°	136.9	112.4	80.7	64.8	59.8
72.5°	116.1	92.0	63.9	51.7	50.3
75°	94.8	73.0	48.1	43.5	42.6
77.5°	75.3	55.3	37.6	34.9	34.0
80°	56.7	38.1	28.6	27.2	26.3
82.5°	39.0	23.6	20.4	19.0	19.0
85°	24.0	14.1	12.7	11.8	11.8
87.5°	10.9	5.9	5.9	5.4	5.0
90°	1.0	11.2	24.4	28.5	30.6
92.5°	23.4	17.3	26.5	33.6	34.6
95°	62.1	20.4	31.6	38.7	38.7
97.5°	113.1	84.6	32.6	40.7	41.8
100°	172.2	192.5	33.6	41.8	42.8
102.5°	239.4	252.6	75.4	41.8	43.8
105°	303.6	314.8	223.1	42.8	44.8
107.5°	371.8	381.0	396.3	239.4	105.9
110°	440.1	448.2	459.4	425.8	280.2

TEST NUMBER: P1032182

CATALOG NUMBER: S123RDIW-B340D1030UB30-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	505.3	512.4	523.6	532.8	530.8
115°	569.5	575.6	584.8	594.9	599.0
117.5°	632.6	639.8	644.9	653.0	654.0
120°	690.7	699.9	702.9	711.1	711.1
122.5°	749.8	756.9	761.0	766.1	767.1
125°	802.8	810.9	815.0	817.0	819.1
127.5°	855.7	863.9	869.0	872.0	870.0
130°	904.6	912.8	916.9	920.9	918.9
132.5°	951.5	959.6	962.7	966.8	963.7
135°	999.4	1005.5	1009.6	1012.6	1009.6
137.5°	1040.1	1048.3	1050.3	1055.4	1053.4
140°	1080.9	1087.0	1090.0	1094.1	1092.1
142.5°	1118.6	1124.7	1127.7	1130.8	1127.7
145°	1153.2	1160.3	1162.4	1164.4	1164.4
147.5°	1186.8	1191.9	1194.0	1196.0	1190.9
150°	1217.4	1220.4	1222.5	1224.5	1221.5
152.5°	1244.9	1245.9	1246.9	1251.0	1245.9
155°	1270.4	1268.3	1269.3	1274.4	1268.3
157.5°	1290.7	1290.7	1289.7	1295.8	1287.7
160°	1309.1	1308.1	1307.0	1313.1	1306.0
162.5°	1326.4	1323.3	1322.3	1329.4	1323.3
165°	1339.6	1336.6	1335.6	1343.7	1336.6
167.5°	1350.8	1346.8	1346.8	1354.9	1346.8
170°	1360.0	1355.9	1355.9	1364.1	1355.9
172.5°	1366.1	1361.0	1362.0	1370.2	1361.0
175°	1371.2	1366.1	1367.1	1374.3	1366.1
177.5°	1373.3	1368.2	1369.2	1377.3	1367.1
180°	1371.2	1371.2	1371.2	1371.2	1371.2

(END OF REPORT)