

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032198

Luminaire Tested: S123RDIW-B340D1320UB30-4F0-XX-W2A-A

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032198
REPORT IS A COMBINATION OF REPORTS P994223 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B340D1320UB30-4F0-XX-W2A-A
Description: Define 3 Regressed Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6601.0 lumens
Efficiency: N/A
Efficacy: 119.8 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 55.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032198

CATALOG NUMBER: S123RDIW-B340D1320UB30-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1032198

CATALOG NUMBER: S123RDIW-B340D1320UB30-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	100	100	100	100	88	88	88	88	67	67	67	47	47	47	29	29	29	29	29	29
1	91	87	84	80	81	77	74	72	59	57	55	41	40	39	26	25	25	25	25	17
2	83	76	71	66	73	68	63	59	52	48	46	37	35	33	23	22	21	21	21	15
3	76	67	60	55	67	60	54	49	46	42	39	33	30	28	20	19	18	18	18	13
4	70	60	52	47	61	53	47	42	41	36	33	29	26	24	18	17	16	16	16	11
5	64	53	45	40	56	47	41	36	36	32	28	26	23	21	17	15	14	14	14	10
6	59	47	40	34	52	42	36	31	33	28	25	24	21	18	15	13	12	12	12	9
7	54	43	35	30	48	38	32	27	29	25	22	21	18	16	14	12	11	11	11	8
8	50	39	31	26	44	34	28	24	27	22	19	19	17	14	13	11	10	10	10	7
9	47	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9	9	9	6
10	43	32	25	21	38	29	23	19	22	18	15	16	14	12	11	9	8	8	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5702	5702	5702	5702
5°	5707	6567	5721	4872
10°	5655	7927	5680	4255
15°	5598	8997	5598	3752
20°	5483	9704	5513	3329
25°	5399	9220	5389	3037
30°	5302	6389	5289	2753
35°	5184	4101	5159	2538
40°	5037	2896	5012	2324
45°	4782	2318	4775	2116
50°	4469	1939	4454	1872
55°	4117	1598	4084	1587
60°	3772	1321	3735	1349
65°	3365	1057	3387	1143
70°	2992	735	3072	925
75°	2537	546	2640	711
80°	2020	360	2193	533
85°	1441	171	1566	332

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 7612 cd/sqm

TEST NUMBER: P1032198

CATALOG NUMBER: S123RDIW-B340D1320UB30-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.0	0.8
10°-20°	162.8	2.5
20°-30°	256.5	3.9
30°-40°	266.7	4.0
40°-50°	228.2	3.5
50°-60°	173.9	2.6
60°-70°	111.4	1.7
70°-80°	53.4	0.8
80°-90°	17.5	0.3
90°-100°	61.1	0.9
100°-110°	295.2	4.5
110°-120°	723.4	11.0
120°-130°	918.4	13.9
130°-140°	981.1	14.9
140°-150°	917.4	13.9
150°-160°	740.0	11.2
160°-170°	477.5	7.2
170°-180°	164.6	2.5
0°-30°	471.3	7.1
0°-40°	738.0	11.2
0°-60°	1140.1	17.3
0°-90°	1322.5	20.0
90°-120°	1079.7	16.4
90°-150°	3896.5	59.0
90°-180°	5279.0	80.0
0°-180°	6601.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	530	530	530	530	530	
5°	529	629	531	467	529	50
15°	506	894	506	373	506	142
25°	460	921	459	303	460	212
35°	401	400	400	247	401	251
45°	322	213	322	195	322	248
55°	227	134	225	133	227	204
65°	139	77	140	83	139	139
75°	67	33	69	43	67	72
85°	15	8	16	15	15	17
90°	1	39	1	39	1	5
95°	78	49	78	49	78	94
105°	383	57	383	57	383	406
115°	719	756	719	756	719	710
125°	1014	1034	1014	1034	1014	906
135°	1262	1275	1262	1275	1262	972
145°	1456	1470	1456	1470	1456	912
155°	1604	1602	1604	1602	1604	739
165°	1692	1688	1692	1688	1692	478
175°	1732	1725	1732	1725	1732	165
180°	1732	1732	1732	1732	1732	

TEST NUMBER: P1032198

CATALOG NUMBER: S123RDIW-B340D1320UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7
2.5°	531.1	534.7	537.4	539.2	543.8	546.5	548.8	552.8	552.8	553.7	555.6
5°	529.3	537.0	542.4	549.7	559.2	563.7	570.1	575.5	583.2	587.3	591.4
7.5°	525.2	536.1	547.4	558.3	572.3	581.4	587.8	601.8	611.8	624.0	633.6
10°	519.7	534.7	549.2	566.0	585.0	598.6	608.2	626.8	645.8	663.0	677.6
12.5°	512.9	531.1	551.9	572.3	599.1	612.7	628.1	651.2	678.5	700.2	719.7
15°	505.7	526.5	550.1	575.1	608.6	627.7	649.9	678.0	708.4	739.7	766.4
17.5°	494.3	520.6	546.9	583.2	622.7	634.0	653.1	691.6	729.3	757.4	790.0
20°	483.0	512.5	545.6	578.2	620.9	647.2	664.9	705.7	746.0	780.0	811.3
22.5°	472.6	503.4	537.9	579.1	619.0	645.4	667.6	710.2	756.9	795.0	833.6
25°	459.9	493.4	531.5	570.5	619.0	639.0	663.5	712.9	762.4	806.4	854.0
27.5°	446.3	480.3	517.9	557.8	602.3	631.7	655.8	708.8	769.2	816.3	865.3
30°	432.7	467.6	503.9	539.7	589.6	617.7	645.4	703.9	772.8	826.8	864.4
32.5°	419.5	449.0	484.8	519.7	569.2	600.0	631.3	698.9	774.2	819.5	837.6
35°	401.4	432.2	461.2	498.4	548.3	578.7	615.4	698.4	768.3	796.4	787.3
37.5°	384.6	410.4	438.1	471.2	522.5	561.9	600.0	686.6	748.8	750.6	699.3
40°	366.0	387.3	410.4	445.4	500.7	539.7	581.0	668.5	713.4	686.6	596.4
42.5°	344.7	363.7	381.9	415.9	476.2	519.7	564.2	645.8	662.1	600.5	506.6
45°	322.0	337.4	354.2	390.0	450.3	493.4	537.9	610.9	594.1	507.0	417.7
47.5°	298.4	311.6	327.9	360.5	422.7	466.7	508.8	561.0	518.4	424.9	350.1
50°	274.8	285.3	301.1	334.7	394.6	434.5	473.5	507.5	447.6	364.6	289.3
52.5°	251.7	259.9	276.2	304.8	362.8	400.9	429.0	442.2	381.4	301.1	251.2
55°	227.2	236.3	247.2	276.2	333.8	361.9	380.5	380.0	317.5	255.3	207.7
57.5°	203.6	211.8	221.3	250.3	297.1	316.1	332.0	324.3	264.9	209.1	178.2
60°	182.8	187.3	197.7	222.2	257.6	273.9	283.0	269.8	216.3	176.4	147.4
62.5°	160.1	164.6	173.2	196.4	218.1	226.8	234.5	217.7	178.7	143.8	126.1
65°	139.2	145.1	150.6	169.2	181.0	191.4	190.5	176.4	139.7	117.0	102.5
67.5°	121.1	123.4	127.9	139.2	144.7	152.4	152.8	137.0	112.5	95.2	86.6
70°	101.6	103.9	107.0	112.5	116.1	117.9	117.0	102.9	84.8	74.4	66.7
72.5°	84.8	84.4	86.6	86.6	90.2	89.8	87.1	76.2	64.4	55.8	51.2
75°	66.7	67.1	67.6	66.7	65.3	63.5	61.2	53.1	45.4	41.3	37.2
77.5°	52.2	51.2	51.7	48.5	46.7	44.9	41.7	37.6	31.3	30.4	28.6
80°	37.2	36.7	36.3	34.9	30.8	29.0	26.8	24.5	23.1	22.2	21.8
82.5°	24.9	24.9	24.0	21.3	19.0	17.7	17.2	16.3	15.0	15.0	14.5
85°	15.0	14.5	13.6	10.9	9.5	9.5	9.5	9.5	8.6	8.6	8.2
87.5°	5.9	5.4	4.1	4.1	3.6	3.6	3.6	3.2	3.2	2.7	2.7
90°	1.3	4.2	7.0	9.9	12.8	14.2	16.1	19.8	23.5	27.2	30.9
92.5°	29.6	27.9	26.2	24.5	22.8	21.9	23.2	25.7	28.3	30.8	33.4
95°	78.5	66.8	55.0	43.3	31.6	25.7	27.3	30.4	33.6	36.7	39.9
97.5°	142.8	134.8	126.8	118.8	110.8	106.8	99.5	84.9	70.4	55.8	41.2
100°	217.4	223.1	228.8	234.5	240.2	243.1	220.8	176.2	131.7	87.1	42.5
102.5°	302.3	306.0	309.7	313.4	317.1	319.0	294.1	244.4	194.7	144.9	95.2
105°	383.3	386.5	389.6	392.8	395.9	397.5	384.6	358.9	333.2	307.4	281.7
107.5°	469.5	472.1	474.7	477.2	479.8	481.1	483.2	487.5	491.8	496.1	500.4
110°	555.7	558.0	560.3	562.6	564.9	566.0	567.6	570.7	573.9	577.0	580.2

TEST NUMBER: P1032198

CATALOG NUMBER: S123RDIW-B340D1320UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	638.0	640.0	642.0	644.1	646.1	647.1	648.7	651.8	654.9	658.1	661.2
115°	719.1	720.8	722.5	724.2	725.9	726.8	728.1	730.7	733.2	735.8	738.4
117.5°	798.8	800.8	802.8	804.8	806.8	807.8	808.5	810.0	811.4	812.9	814.3
120°	872.2	874.8	877.3	879.9	882.4	883.7	884.1	885.0	885.9	886.7	887.6
122.5°	946.8	948.8	950.8	952.8	954.8	955.8	956.4	957.5	958.6	959.8	960.9
125°	1013.7	1016.0	1018.3	1020.6	1022.9	1024.0	1024.6	1025.7	1026.8	1028.0	1029.1
127.5°	1080.6	1082.9	1085.2	1087.5	1089.8	1090.9	1091.6	1093.0	1094.5	1095.9	1097.3
130°	1142.3	1144.6	1146.9	1149.2	1151.5	1152.6	1153.2	1154.3	1155.4	1156.6	1157.7
132.5°	1201.5	1203.8	1206.1	1208.4	1210.7	1211.8	1212.2	1213.1	1213.9	1214.8	1215.6
135°	1261.9	1263.6	1265.4	1267.1	1268.8	1269.7	1270.3	1271.4	1272.5	1273.7	1274.8
137.5°	1313.4	1315.7	1318.0	1320.3	1322.6	1323.7	1324.0	1324.6	1325.1	1325.7	1326.3
140°	1364.9	1366.6	1368.3	1370.0	1371.7	1372.6	1373.0	1373.9	1374.7	1375.6	1376.4
142.5°	1412.4	1414.1	1415.9	1417.6	1419.3	1420.2	1420.6	1421.5	1422.3	1423.2	1424.0
145°	1456.2	1458.2	1460.2	1462.2	1464.2	1465.2	1465.5	1466.1	1466.6	1467.2	1467.8
147.5°	1498.6	1500.0	1501.5	1502.9	1504.4	1505.1	1505.4	1505.9	1506.5	1507.0	1507.6
150°	1537.2	1538.1	1538.9	1539.8	1540.7	1541.1	1541.4	1542.0	1542.5	1543.1	1543.7
152.5°	1572.0	1572.3	1572.5	1572.8	1573.1	1573.2	1573.3	1573.6	1573.9	1574.2	1574.5
155°	1604.1	1603.5	1602.9	1602.4	1601.8	1601.5	1601.6	1601.9	1602.2	1602.5	1602.8
157.5°	1629.8	1629.8	1629.8	1629.8	1629.8	1629.8	1629.7	1629.4	1629.1	1628.9	1628.6
160°	1653.0	1652.7	1652.4	1652.1	1651.8	1651.7	1651.6	1651.3	1651.0	1650.7	1650.4
162.5°	1674.9	1674.0	1673.2	1672.3	1671.4	1671.0	1670.9	1670.6	1670.3	1670.0	1669.7
165°	1691.6	1690.7	1689.9	1689.0	1688.1	1687.7	1687.6	1687.3	1687.0	1686.7	1686.4
167.5°	1705.7	1704.6	1703.4	1702.3	1701.2	1700.6	1700.6	1700.6	1700.6	1700.6	1700.6
170°	1717.3	1716.2	1715.0	1713.9	1712.8	1712.2	1712.2	1712.2	1712.2	1712.2	1712.2
172.5°	1725.0	1723.6	1722.2	1720.7	1719.3	1718.6	1718.7	1719.0	1719.3	1719.6	1719.9
175°	1731.5	1730.1	1728.6	1727.2	1725.7	1725.0	1725.1	1725.4	1725.7	1726.0	1726.3
177.5°	1734.0	1732.6	1731.2	1729.7	1728.3	1727.6	1727.7	1728.0	1728.3	1728.6	1728.9
180°	1731.5	1731.5	1731.5	1731.5	1731.5	1731.5	1731.5	1731.5	1731.5	1731.5	1731.5

TEST NUMBER: P1032198

CATALOG NUMBER: S123RDIW-B340D1320UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7
2.5°	559.2	559.2	563.3	567.3	565.1	566.4	571.4	569.6	573.2	572.8	574.2
5°	601.4	606.4	610.4	619.0	620.4	619.0	627.7	629.9	634.0	629.0	631.3
7.5°	649.0	659.4	669.4	682.1	686.2	687.1	691.6	698.0	703.4	693.4	698.4
10°	695.2	711.1	731.5	742.9	752.8	756.5	760.1	764.2	770.5	776.4	771.9
12.5°	745.1	768.3	787.8	808.2	820.4	819.1	829.5	832.2	837.2	838.6	840.4
15°	785.9	818.6	830.8	861.2	863.9	873.0	884.8	895.2	896.6	893.9	893.9
17.5°	824.9	853.1	874.8	899.3	904.3	912.0	927.0	932.0	933.8	933.3	933.3
20°	856.7	875.3	912.0	932.4	940.6	950.6	961.0	967.4	968.7	970.5	967.8
22.5°	877.6	905.7	935.6	952.4	959.2	962.8	969.6	971.4	969.2	969.6	970.1
25°	893.9	921.5	939.7	944.2	943.8	939.2	934.2	925.6	924.7	921.1	913.8
27.5°	898.4	908.8	906.6	888.0	869.4	867.6	837.6	821.3	802.7	805.4	795.0
30°	873.9	860.3	828.1	781.0	761.5	729.7	696.1	661.2	647.6	632.7	660.3
32.5°	814.1	765.5	708.4	647.2	614.5	586.4	550.6	525.2	510.7	498.4	522.0
35°	723.8	648.1	572.3	514.3	487.5	462.1	428.6	415.9	397.7	399.5	401.8
37.5°	607.7	524.3	467.1	410.0	392.3	381.9	357.4	337.9	331.5	329.7	329.7
40°	498.9	430.4	379.6	334.7	321.1	312.5	293.0	283.9	277.1	275.3	277.6
42.5°	412.7	354.2	314.7	284.8	275.3	264.4	256.2	244.9	243.5	240.4	244.4
45°	346.5	295.7	266.2	244.4	236.3	232.2	223.1	216.3	213.6	213.2	216.3
47.5°	293.9	254.4	228.6	215.0	208.6	204.5	196.8	194.1	191.4	192.3	190.9
50°	246.7	217.2	200.5	188.2	184.1	180.0	175.1	172.3	171.0	171.0	170.5
52.5°	211.8	187.3	176.4	165.1	163.3	161.0	155.6	153.7	151.5	151.0	152.8
55°	181.4	164.6	153.7	146.9	145.1	140.6	138.3	136.1	134.7	133.8	134.2
57.5°	155.1	142.4	135.1	129.3	126.1	124.3	120.2	119.7	118.8	118.8	118.4
60°	133.3	124.3	115.6	112.0	109.8	107.5	107.0	104.3	102.9	103.9	103.4
62.5°	112.9	105.7	100.7	96.6	95.2	93.4	92.1	91.2	89.8	90.2	90.2
65°	94.3	88.4	84.8	81.2	80.7	78.9	78.5	77.6	77.6	77.1	78.0
67.5°	77.6	73.5	70.3	68.0	66.7	67.1	65.3	63.9	63.9	63.5	64.9
70°	61.7	59.4	56.2	53.5	51.7	51.7	49.4	49.0	49.0	49.0	48.5
72.5°	47.6	43.5	42.2	41.3	41.3	41.3	40.4	40.4	39.9	40.4	39.9
75°	35.4	34.9	34.0	33.6	33.6	33.1	32.7	32.7	32.7	32.7	32.7
77.5°	27.7	27.7	26.8	26.3	26.3	26.3	25.9	25.9	25.4	25.4	25.4
80°	20.4	20.4	19.5	19.5	19.5	19.0	19.0	19.0	19.5	19.0	19.0
82.5°	14.1	14.1	13.6	14.1	13.6	13.2	13.2	13.2	12.7	13.2	13.2
85°	8.2	8.2	7.7	7.3	7.7	7.7	7.3	7.7	7.3	7.7	7.3
87.5°	3.2	2.7	2.7	2.7	2.3	2.7	2.3	2.3	2.7	2.3	2.7
90°	32.0	33.2	34.3	35.4	36.0	36.3	36.9	37.4	38.0	38.6	38.0
92.5°	35.4	37.4	39.5	41.5	42.5	42.6	42.9	43.2	43.4	43.7	43.4
95°	41.9	43.9	45.9	47.9	48.9	48.9	48.9	48.9	48.9	48.9	48.9
97.5°	43.5	45.8	48.1	50.4	51.5	51.6	51.9	52.2	52.4	52.7	52.4
100°	44.8	47.0	49.3	51.6	52.7	52.8	53.1	53.4	53.7	54.0	53.7
102.5°	85.8	76.3	66.9	57.4	52.7	53.0	53.6	54.1	54.7	55.3	54.7
105°	231.1	180.5	129.9	79.3	54.0	54.3	54.9	55.4	56.0	56.6	56.0
107.5°	456.4	412.4	368.3	324.3	302.3	283.6	246.1	208.7	171.2	133.8	171.2
110°	570.8	561.3	551.9	542.4	537.7	517.3	476.4	435.5	394.7	353.8	394.7

TEST NUMBER: P1032198

CATALOG NUMBER: S123RDIW-B340D1320UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	663.8	666.4	668.9	671.5	672.8	672.5	671.9	671.4	670.8	670.2	670.8
115°	741.2	744.1	746.9	749.8	751.2	751.8	752.9	754.1	755.2	756.4	755.2
117.5°	816.6	818.9	821.2	823.5	824.6	824.7	825.0	825.3	825.6	825.9	825.6
120°	889.9	892.2	894.5	896.8	897.9	897.9	897.9	897.9	897.9	897.9	897.9
122.5°	962.3	963.8	965.2	966.7	967.4	967.5	967.8	968.1	968.3	968.6	968.3
125°	1029.7	1030.3	1030.8	1031.4	1031.7	1032.0	1032.6	1033.1	1033.7	1034.3	1033.7
127.5°	1098.1	1099.0	1099.8	1100.7	1101.1	1100.8	1100.3	1099.7	1099.2	1098.6	1099.2
130°	1158.9	1160.0	1161.2	1162.3	1162.9	1162.6	1162.0	1161.5	1160.9	1160.3	1160.9
132.5°	1216.8	1217.9	1219.1	1220.2	1220.8	1220.4	1219.5	1218.6	1217.8	1216.9	1217.8
135°	1275.7	1276.5	1277.4	1278.3	1278.7	1278.3	1277.4	1276.5	1275.7	1274.8	1275.7
137.5°	1327.7	1329.1	1330.6	1332.0	1332.7	1332.4	1331.8	1331.3	1330.7	1330.1	1330.7
140°	1377.6	1378.7	1379.9	1381.0	1381.6	1381.3	1380.7	1380.2	1379.6	1379.0	1379.6
142.5°	1424.9	1425.7	1426.6	1427.5	1427.9	1427.5	1426.6	1425.7	1424.9	1424.0	1424.9
145°	1468.4	1468.9	1469.5	1470.0	1470.3	1470.3	1470.3	1470.3	1470.3	1470.3	1470.3
147.5°	1508.2	1508.8	1509.3	1509.9	1510.2	1509.5	1508.1	1506.6	1505.2	1503.8	1505.2
150°	1544.3	1544.8	1545.4	1545.9	1546.2	1545.8	1544.9	1544.1	1543.2	1542.4	1543.2
152.5°	1575.7	1576.8	1578.0	1579.1	1579.7	1579.0	1577.5	1576.1	1574.6	1573.2	1574.6
155°	1604.2	1605.7	1607.1	1608.6	1609.3	1608.4	1606.7	1605.0	1603.2	1601.5	1603.2
157.5°	1630.3	1632.0	1633.7	1635.4	1636.3	1635.2	1632.9	1630.6	1628.3	1626.0	1628.3
160°	1652.1	1653.8	1655.5	1657.2	1658.1	1657.1	1655.1	1653.1	1651.1	1649.1	1651.1
162.5°	1671.7	1673.7	1675.7	1677.7	1678.7	1677.8	1676.1	1674.4	1672.7	1671.0	1672.7
165°	1688.7	1691.0	1693.3	1695.6	1696.7	1695.7	1693.7	1691.7	1689.7	1687.7	1689.7
167.5°	1702.9	1705.2	1707.5	1709.8	1710.9	1709.8	1707.5	1705.2	1702.9	1700.6	1702.9
170°	1714.5	1716.8	1719.1	1721.4	1722.5	1721.4	1719.1	1716.8	1714.5	1712.2	1714.5
172.5°	1722.2	1724.5	1726.8	1729.1	1730.2	1728.9	1726.3	1723.8	1721.2	1718.6	1721.2
175°	1728.3	1730.3	1732.3	1734.3	1735.3	1734.2	1731.9	1729.6	1727.3	1725.0	1727.3
177.5°	1731.2	1733.5	1735.8	1738.1	1739.2	1737.8	1734.9	1732.0	1729.2	1726.3	1729.2
180°	1731.5	1731.5	1731.5	1731.5	1731.5	1731.5	1731.5	1731.5	1731.5	1731.5	1731.5

TEST NUMBER: P1032198

CATALOG NUMBER: S123RDIW-B340D1320UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7
2.5°	571.9	569.2	567.3	566.0	564.6	568.7	563.3	557.4	553.3	550.6	549.7
5°	631.7	625.9	620.9	616.8	617.7	617.7	608.2	597.7	588.7	583.7	578.2
7.5°	701.1	694.8	684.8	682.5	680.7	669.4	659.9	640.8	629.5	618.1	608.2
10°	770.1	761.9	752.4	749.2	744.7	730.6	716.1	691.6	677.6	656.7	643.5
12.5°	834.5	824.5	815.0	812.7	805.9	793.7	768.7	743.3	719.3	697.1	673.9
15°	888.4	885.7	871.2	862.1	847.2	830.4	824.9	790.5	760.1	737.0	695.2
17.5°	933.8	921.1	907.5	901.6	895.7	876.2	856.7	821.3	788.7	754.7	727.9
20°	970.1	956.0	946.5	937.9	935.2	912.9	882.1	850.8	815.0	776.9	742.0
22.5°	971.9	970.1	963.7	958.7	953.3	938.8	914.3	875.3	837.2	795.5	749.7
25°	934.2	931.5	949.7	945.1	948.8	943.3	930.2	897.5	853.1	804.1	757.8
27.5°	820.9	848.5	877.1	887.1	893.9	913.4	919.7	901.6	865.8	813.6	761.9
30°	666.7	703.4	749.7	774.6	793.7	829.9	877.1	883.0	866.2	824.5	761.0
32.5°	523.4	556.9	594.1	623.6	649.0	723.4	786.9	832.7	840.8	819.1	763.3
35°	421.8	436.3	471.7	499.8	534.2	597.7	672.6	746.5	796.4	799.1	756.5
37.5°	347.8	355.6	386.4	402.3	422.7	478.5	548.3	644.9	722.5	759.2	737.4
40°	288.0	305.7	323.4	332.4	346.9	385.5	452.6	528.3	624.5	692.5	707.9
42.5°	249.9	257.6	268.9	281.6	290.7	324.3	369.2	438.6	525.2	620.0	662.6
45°	220.4	223.1	234.9	243.1	252.6	276.2	307.9	366.0	442.2	535.6	608.2
47.5°	195.9	201.4	207.7	212.7	219.0	237.2	264.4	306.6	373.7	457.1	535.1
50°	174.2	177.3	185.5	187.8	192.3	205.0	225.9	258.1	313.4	380.0	460.8
52.5°	153.7	159.6	162.8	166.0	170.1	180.5	194.1	220.4	262.1	324.7	393.2
55°	137.9	139.7	144.2	146.9	150.1	157.4	169.2	188.7	221.3	271.2	336.1
57.5°	122.4	122.4	127.0	129.3	132.4	137.9	148.3	163.3	186.8	224.0	283.4
60°	106.1	106.6	110.2	112.9	113.8	119.3	127.9	139.7	157.8	185.0	233.6
62.5°	91.6	93.9	95.7	96.6	99.8	102.9	110.2	118.4	131.1	155.1	189.6
65°	79.4	79.8	81.2	82.1	83.4	87.1	92.5	98.0	108.8	126.5	154.6
67.5°	65.3	67.1	68.9	68.9	70.3	72.1	77.6	82.1	90.2	100.7	119.7
70°	49.0	49.9	52.6	54.0	55.8	59.0	61.7	64.4	70.7	78.5	93.0
72.5°	40.8	40.8	41.7	42.2	42.2	44.4	48.5	51.2	54.4	59.9	69.8
75°	32.7	32.7	34.0	33.6	34.5	35.4	35.8	37.6	39.5	43.5	49.4
77.5°	25.9	26.3	26.3	26.8	26.8	27.2	27.7	28.6	29.5	31.7	34.5
80°	19.0	19.5	19.5	20.0	20.0	20.4	20.9	21.3	22.2	23.1	24.5
82.5°	13.2	13.6	13.6	14.1	13.6	14.1	14.5	14.5	15.0	15.9	16.3
85°	7.7	7.7	8.2	7.7	7.7	7.7	8.2	8.2	8.6	10.0	10.0
87.5°	2.3	2.7	2.3	2.7	2.7	2.7	2.7	3.2	3.2	3.6	4.1
90°	37.4	36.9	36.3	36.0	35.4	34.3	33.2	32.0	30.9	27.2	23.5
92.5°	43.2	42.9	42.6	42.5	41.5	39.5	37.4	35.4	33.4	30.8	28.3
95°	48.9	48.9	48.9	48.9	47.9	45.9	43.9	41.9	39.9	36.7	33.6
97.5°	52.2	51.9	51.6	51.5	50.4	48.1	45.8	43.5	41.2	55.8	70.4
100°	53.4	53.1	52.8	52.7	51.6	49.3	47.0	44.8	42.5	87.1	131.7
102.5°	54.1	53.6	53.0	52.7	57.4	66.9	76.3	85.8	95.2	144.9	194.7
105°	55.4	54.9	54.3	54.0	79.3	129.9	180.5	231.1	281.7	307.4	333.2
107.5°	208.7	246.1	283.6	302.3	324.3	368.3	412.4	456.4	500.4	496.1	491.8
110°	435.5	476.4	517.3	537.7	542.4	551.9	561.3	570.8	580.2	577.0	573.9

TEST NUMBER: P1032198

CATALOG NUMBER: S123RDIW-B340D1320UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	671.4	671.9	672.5	672.8	671.5	668.9	666.4	663.8	661.2	658.1	654.9
115°	754.1	752.9	751.8	751.2	749.8	746.9	744.1	741.2	738.4	735.8	733.2
117.5°	825.3	825.0	824.7	824.6	823.5	821.2	818.9	816.6	814.3	812.9	811.4
120°	897.9	897.9	897.9	897.9	896.8	894.5	892.2	889.9	887.6	886.7	885.9
122.5°	968.1	967.8	967.5	967.4	966.7	965.2	963.8	962.3	960.9	959.8	958.6
125°	1033.1	1032.6	1032.0	1031.7	1031.4	1030.8	1030.3	1029.7	1029.1	1028.0	1026.8
127.5°	1099.7	1100.3	1100.8	1101.1	1100.7	1099.8	1099.0	1098.1	1097.3	1095.9	1094.5
130°	1161.5	1162.0	1162.6	1162.9	1162.3	1161.2	1160.0	1158.9	1157.7	1156.6	1155.4
132.5°	1218.6	1219.5	1220.4	1220.8	1220.2	1219.1	1217.9	1216.8	1215.6	1214.8	1213.9
135°	1276.5	1277.4	1278.3	1278.7	1278.3	1277.4	1276.5	1275.7	1274.8	1273.7	1272.5
137.5°	1331.3	1331.8	1332.4	1332.7	1332.0	1330.6	1329.1	1327.7	1326.3	1325.7	1325.1
140°	1380.2	1380.7	1381.3	1381.6	1381.0	1379.9	1378.7	1377.6	1376.4	1375.6	1374.7
142.5°	1425.7	1426.6	1427.5	1427.9	1427.5	1426.6	1425.7	1424.9	1424.0	1423.2	1422.3
145°	1470.3	1470.3	1470.3	1470.3	1470.0	1469.5	1468.9	1468.4	1467.8	1467.2	1466.6
147.5°	1506.6	1508.1	1509.5	1510.2	1509.9	1509.3	1508.8	1508.2	1507.6	1507.0	1506.5
150°	1544.1	1544.9	1545.8	1546.2	1545.9	1545.4	1544.8	1544.3	1543.7	1543.1	1542.5
152.5°	1576.1	1577.5	1579.0	1579.7	1579.1	1578.0	1576.8	1575.7	1574.5	1574.2	1573.9
155°	1605.0	1606.7	1608.4	1609.3	1608.6	1607.1	1605.7	1604.2	1602.8	1602.5	1602.2
157.5°	1630.6	1632.9	1635.2	1636.3	1635.4	1633.7	1632.0	1630.3	1628.6	1628.9	1629.1
160°	1653.1	1655.1	1657.1	1658.1	1657.2	1655.5	1653.8	1652.1	1650.4	1650.7	1651.0
162.5°	1674.4	1676.1	1677.8	1678.7	1677.7	1675.7	1673.7	1671.7	1669.7	1670.0	1670.3
165°	1691.7	1693.7	1695.7	1696.7	1695.6	1693.3	1691.0	1688.7	1686.4	1686.7	1687.0
167.5°	1705.2	1707.5	1709.8	1710.9	1709.8	1707.5	1705.2	1702.9	1700.6	1700.6	1700.6
170°	1716.8	1719.1	1721.4	1722.5	1721.4	1719.1	1716.8	1714.5	1712.2	1712.2	1712.2
172.5°	1723.8	1726.3	1728.9	1730.2	1729.1	1726.8	1724.5	1722.2	1719.9	1719.6	1719.3
175°	1729.6	1731.9	1734.2	1735.3	1734.3	1732.3	1730.3	1728.3	1726.3	1726.0	1725.7
177.5°	1732.0	1734.9	1737.8	1739.2	1738.1	1735.8	1733.5	1731.2	1728.9	1728.6	1728.3
180°	1731.5	1731.5	1731.5	1731.5	1731.5	1731.5	1731.5	1731.5	1731.5	1731.5	1731.5

TEST NUMBER: P1032198

CATALOG NUMBER: S123RDIW-B340D1320UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7
2.5°	548.3	546.0	543.8	543.8	538.8	534.2	532.0	532.9	530.2	526.5	522.9
5°	572.3	563.3	561.5	556.5	549.7	540.1	535.1	530.6	525.2	517.9	511.1
7.5°	594.6	582.8	576.4	571.4	558.3	545.1	534.2	527.0	517.5	506.6	498.4
10°	623.6	601.8	595.0	583.7	565.1	546.5	533.8	522.0	508.8	496.1	485.3
12.5°	646.7	621.8	609.1	597.7	573.7	550.1	528.8	514.3	498.4	484.4	470.3
15°	673.0	644.9	622.7	609.1	578.7	550.1	526.1	505.7	488.0	470.7	458.5
17.5°	685.7	650.3	640.4	620.9	576.9	548.3	518.8	497.1	475.7	455.8	441.3
20°	705.7	664.4	639.5	626.3	587.3	545.1	510.7	485.7	463.5	442.2	426.8
22.5°	707.0	662.1	645.8	620.9	572.8	535.6	503.4	473.0	447.2	427.2	411.3
25°	703.9	658.1	635.4	615.4	575.5	530.2	488.9	459.0	433.6	410.4	391.8
27.5°	702.5	646.3	624.9	605.0	560.1	514.3	480.3	446.3	417.2	396.8	377.8
30°	700.7	633.6	607.7	584.6	543.3	502.0	461.2	431.7	404.1	378.2	359.2
32.5°	688.9	616.3	590.0	565.5	521.1	479.8	447.6	416.3	386.4	362.4	345.1
35°	685.3	600.5	566.0	539.7	496.1	459.4	425.4	399.5	371.4	347.4	327.0
37.5°	674.8	584.1	546.9	513.4	468.0	433.1	408.2	382.3	355.1	329.3	312.9
40°	656.7	565.1	522.9	488.4	441.7	406.4	383.2	364.2	337.4	314.3	294.3
42.5°	629.9	545.6	500.2	463.9	412.2	379.1	360.1	342.0	319.3	295.2	278.9
45°	599.1	519.7	477.6	437.2	384.6	352.4	332.4	321.5	300.7	280.3	261.2
47.5°	556.9	493.0	451.2	409.5	356.0	324.7	308.8	298.0	283.4	261.2	245.8
50°	503.9	458.5	419.0	381.9	327.9	298.0	282.1	273.9	261.7	245.8	230.8
52.5°	444.9	418.6	385.9	351.5	299.3	271.2	256.7	250.3	241.3	226.3	213.6
55°	385.5	374.2	351.9	317.9	269.4	246.3	233.6	225.4	218.6	207.7	196.8
57.5°	332.4	327.0	311.6	285.3	244.4	220.4	209.5	204.1	198.6	190.5	179.6
60°	277.6	283.4	267.6	254.4	217.2	196.4	186.8	181.0	178.2	171.0	164.2
62.5°	229.9	235.4	226.3	216.3	190.0	171.4	165.5	160.1	158.3	151.9	145.1
65°	186.8	193.7	186.8	181.4	165.5	150.1	142.9	140.1	138.3	134.2	128.8
67.5°	148.8	155.6	152.4	145.6	140.6	127.9	123.8	121.1	120.2	117.0	112.5
70°	112.0	121.5	122.4	118.4	113.8	107.9	105.2	104.3	102.0	99.3	96.6
72.5°	80.7	91.6	92.1	92.1	89.3	89.3	86.6	85.3	85.3	82.5	79.4
75°	59.4	66.7	67.6	68.5	69.8	71.2	69.4	69.4	68.9	66.2	64.9
77.5°	39.5	45.8	48.1	51.2	53.1	53.1	54.0	54.9	54.0	52.6	51.7
80°	25.4	29.9	32.7	34.5	37.2	38.5	39.9	40.4	39.5	39.0	37.6
82.5°	16.8	18.1	19.5	21.8	24.9	27.2	27.2	26.8	27.7	27.2	26.8
85°	9.5	10.4	10.9	11.3	13.2	15.4	15.9	16.3	17.2	16.3	15.4
87.5°	3.6	4.1	4.1	4.1	5.0	5.4	6.8	8.6	8.2	7.3	7.3
90°	19.8	16.1	14.2	12.8	9.9	7.0	4.2	1.3	4.2	7.0	9.9
92.5°	25.7	23.2	21.9	22.8	24.5	26.2	27.9	29.6	27.9	26.2	24.5
95°	30.4	27.3	25.7	31.6	43.3	55.0	66.8	78.5	66.8	55.0	43.3
97.5°	84.9	99.5	106.8	110.8	118.8	126.8	134.8	142.8	134.8	126.8	118.8
100°	176.2	220.8	243.1	240.2	234.5	228.8	223.1	217.4	223.1	228.8	234.5
102.5°	244.4	294.1	319.0	317.1	313.4	309.7	306.0	302.3	306.0	309.7	313.4
105°	358.9	384.6	397.5	395.9	392.8	389.6	386.5	383.3	386.5	389.6	392.8
107.5°	487.5	483.2	481.1	479.8	477.2	474.7	472.1	469.5	472.1	474.7	477.2
110°	570.7	567.6	566.0	564.9	562.6	560.3	558.0	555.7	558.0	560.3	562.6

TEST NUMBER: P1032198

CATALOG NUMBER: S123RDIW-B340D1320UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	651.8	648.7	647.1	646.1	644.1	642.0	640.0	638.0	640.0	642.0	644.1
115°	730.7	728.1	726.8	725.9	724.2	722.5	720.8	719.1	720.8	722.5	724.2
117.5°	810.0	808.5	807.8	806.8	804.8	802.8	800.8	798.8	800.8	802.8	804.8
120°	885.0	884.1	883.7	882.4	879.9	877.3	874.8	872.2	874.8	877.3	879.9
122.5°	957.5	956.4	955.8	954.8	952.8	950.8	948.8	946.8	948.8	950.8	952.8
125°	1025.7	1024.6	1024.0	1022.9	1020.6	1018.3	1016.0	1013.7	1016.0	1018.3	1020.6
127.5°	1093.0	1091.6	1090.9	1089.8	1087.5	1085.2	1082.9	1080.6	1082.9	1085.2	1087.5
130°	1154.3	1153.2	1152.6	1151.5	1149.2	1146.9	1144.6	1142.3	1144.6	1146.9	1149.2
132.5°	1213.1	1212.2	1211.8	1210.7	1208.4	1206.1	1203.8	1201.5	1203.8	1206.1	1208.4
135°	1271.4	1270.3	1269.7	1268.8	1267.1	1265.4	1263.6	1261.9	1263.6	1265.4	1267.1
137.5°	1324.6	1324.0	1323.7	1322.6	1320.3	1318.0	1315.7	1313.4	1315.7	1318.0	1320.3
140°	1373.9	1373.0	1372.6	1371.7	1370.0	1368.3	1366.6	1364.9	1366.6	1368.3	1370.0
142.5°	1421.5	1420.6	1420.2	1419.3	1417.6	1415.9	1414.1	1412.4	1414.1	1415.9	1417.6
145°	1466.1	1465.5	1465.2	1464.2	1462.2	1460.2	1458.2	1456.2	1458.2	1460.2	1462.2
147.5°	1505.9	1505.4	1505.1	1504.4	1502.9	1501.5	1500.0	1498.6	1500.0	1501.5	1502.9
150°	1542.0	1541.4	1541.1	1540.7	1539.8	1538.9	1538.1	1537.2	1538.1	1538.9	1539.8
152.5°	1573.6	1573.3	1573.2	1573.1	1572.8	1572.5	1572.3	1572.0	1572.3	1572.5	1572.8
155°	1601.9	1601.6	1601.5	1601.8	1602.4	1602.9	1603.5	1604.1	1603.5	1602.9	1602.4
157.5°	1629.4	1629.7	1629.8	1629.8	1629.8	1629.8	1629.8	1629.8	1629.8	1629.8	1629.8
160°	1651.3	1651.6	1651.7	1651.8	1652.1	1652.4	1652.7	1653.0	1652.7	1652.4	1652.1
162.5°	1670.6	1670.9	1671.0	1671.4	1672.3	1673.2	1674.0	1674.9	1674.0	1673.2	1672.3
165°	1687.3	1687.6	1687.7	1688.1	1689.0	1689.9	1690.7	1691.6	1690.7	1689.9	1689.0
167.5°	1700.6	1700.6	1700.6	1701.2	1702.3	1703.4	1704.6	1705.7	1704.6	1703.4	1702.3
170°	1712.2	1712.2	1712.2	1712.8	1713.9	1715.0	1716.2	1717.3	1716.2	1715.0	1713.9
172.5°	1719.0	1718.7	1718.6	1719.3	1720.7	1722.2	1723.6	1725.0	1723.6	1722.2	1720.7
175°	1725.4	1725.1	1725.0	1725.7	1727.2	1728.6	1730.1	1731.5	1730.1	1728.6	1727.2
177.5°	1728.0	1727.7	1727.6	1728.3	1729.7	1731.2	1732.6	1734.0	1732.6	1731.2	1729.7
180°	1731.5	1731.5	1731.5	1731.5	1731.5	1731.5	1731.5	1731.5	1731.5	1731.5	1731.5

TEST NUMBER: P1032198

CATALOG NUMBER: S123RDIW-B340D1320UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7
2.5°	522.9	520.6	519.7	517.5	512.0	508.4	504.3	501.6	502.0	499.8	501.1
5°	506.6	506.1	502.9	498.4	490.7	486.6	479.4	475.7	473.9	474.4	471.7
7.5°	493.0	488.9	486.6	479.4	472.1	463.5	457.6	454.4	451.7	449.0	447.2
10°	477.6	473.9	470.3	462.6	452.6	444.4	436.3	433.1	429.0	427.2	425.9
12.5°	461.2	459.0	454.4	445.4	434.0	426.3	416.8	415.0	409.5	405.9	405.0
15°	446.3	444.9	436.7	426.3	415.0	407.3	399.1	393.7	384.6	386.4	383.2
17.5°	430.4	424.5	419.5	405.4	400.0	388.2	378.7	376.0	369.6	365.5	361.5
20°	412.7	409.1	402.7	393.7	380.5	366.9	359.6	355.1	351.5	345.1	343.3
22.5°	395.9	391.4	385.9	374.2	362.8	351.5	341.5	337.4	332.9	328.3	325.6
25°	382.8	376.0	370.1	355.6	344.2	334.7	328.3	321.5	315.2	312.5	311.6
27.5°	362.4	358.3	352.4	338.8	328.3	317.9	312.0	307.5	300.7	297.5	294.8
30°	349.2	341.0	334.2	323.4	312.9	301.6	296.1	290.7	286.6	282.5	279.4
32.5°	331.5	325.2	319.7	308.8	298.4	288.0	282.1	273.9	271.7	268.5	264.9
35°	314.3	310.2	304.3	292.5	281.2	273.9	267.6	259.9	257.1	254.9	251.7
37.5°	298.0	292.1	288.0	276.6	266.7	258.1	253.1	246.7	244.9	242.2	239.9
40°	283.9	278.0	273.9	262.6	252.2	243.1	239.9	233.6	230.8	227.7	226.3
42.5°	268.0	263.0	257.6	249.4	238.5	229.5	223.1	219.5	215.9	214.5	211.8
45°	251.2	246.7	242.6	233.6	222.2	215.9	210.4	205.4	202.7	200.5	198.6
47.5°	236.7	232.7	227.2	217.2	208.2	202.3	196.8	191.8	189.1	186.4	184.1
50°	220.0	217.7	211.8	202.3	193.7	186.8	181.9	177.3	175.5	172.3	168.7
52.5°	205.0	200.9	195.9	188.2	180.5	172.3	165.5	162.8	159.6	157.8	154.6
55°	187.3	184.6	179.1	172.3	164.2	157.4	152.4	148.8	144.7	142.9	138.8
57.5°	172.3	167.3	164.6	156.0	148.3	141.5	137.9	134.2	129.7	127.0	125.2
60°	156.0	151.5	147.4	140.1	134.7	127.4	122.0	118.8	115.6	112.0	110.2
62.5°	140.1	136.5	131.5	125.6	118.8	112.9	108.8	104.3	102.5	98.9	97.5
65°	122.9	120.2	116.1	109.3	103.9	98.9	94.8	91.2	89.3	88.0	87.1
67.5°	107.5	103.9	101.1	95.2	89.3	85.3	83.0	80.7	78.5	77.1	75.7
70°	91.6	88.9	86.2	80.7	76.6	73.0	71.2	69.4	68.0	66.7	65.3
72.5°	75.3	73.9	71.2	67.6	64.4	61.7	60.3	58.1	56.7	54.4	53.5
75°	62.1	59.9	58.5	55.3	52.6	50.3	48.5	45.8	44.0	43.1	42.6
77.5°	49.0	48.1	46.3	43.5	42.2	39.9	37.2	36.3	35.4	35.4	34.9
80°	36.7	35.4	34.0	31.7	30.4	28.6	28.6	28.6	28.1	28.6	28.1
82.5°	24.9	24.0	23.1	21.8	21.3	21.3	21.8	21.8	21.8	21.8	21.8
85°	14.5	14.5	14.5	15.0	14.5	14.5	15.0	15.4	15.0	15.0	14.5
87.5°	6.8	6.8	7.3	7.3	7.7	7.7	7.7	7.7	7.7	7.7	8.2
90°	12.8	14.2	16.1	19.8	23.5	27.2	30.9	32.0	33.2	34.3	35.4
92.5°	22.8	21.9	23.2	25.7	28.3	30.8	33.4	35.4	37.4	39.5	41.5
95°	31.6	25.7	27.3	30.4	33.6	36.7	39.9	41.9	43.9	45.9	47.9
97.5°	110.8	106.8	99.5	84.9	70.4	55.8	41.2	43.5	45.8	48.1	50.4
100°	240.2	243.1	220.8	176.2	131.7	87.1	42.5	44.8	47.0	49.3	51.6
102.5°	317.1	319.0	294.1	244.4	194.7	144.9	95.2	85.8	76.3	66.9	57.4
105°	395.9	397.5	384.6	358.9	333.2	307.4	281.7	231.1	180.5	129.9	79.3
107.5°	479.8	481.1	483.2	487.5	491.8	496.1	500.4	456.4	412.4	368.3	324.3
110°	564.9	566.0	567.6	570.7	573.9	577.0	580.2	570.8	561.3	551.9	542.4

TEST NUMBER: P1032198

CATALOG NUMBER: S123RDIW-B340D1320UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	646.1	647.1	648.7	651.8	654.9	658.1	661.2	663.8	666.4	668.9	671.5
115°	725.9	726.8	728.1	730.7	733.2	735.8	738.4	741.2	744.1	746.9	749.8
117.5°	806.8	807.8	808.5	810.0	811.4	812.9	814.3	816.6	818.9	821.2	823.5
120°	882.4	883.7	884.1	885.0	885.9	886.7	887.6	889.9	892.2	894.5	896.8
122.5°	954.8	955.8	956.4	957.5	958.6	959.8	960.9	962.3	963.8	965.2	966.7
125°	1022.9	1024.0	1024.6	1025.7	1026.8	1028.0	1029.1	1029.7	1030.3	1030.8	1031.4
127.5°	1089.8	1090.9	1091.6	1093.0	1094.5	1095.9	1097.3	1098.1	1099.0	1099.8	1100.7
130°	1151.5	1152.6	1153.2	1154.3	1155.4	1156.6	1157.7	1158.9	1160.0	1161.2	1162.3
132.5°	1210.7	1211.8	1212.2	1213.1	1213.9	1214.8	1215.6	1216.8	1217.9	1219.1	1220.2
135°	1268.8	1269.7	1270.3	1271.4	1272.5	1273.7	1274.8	1275.7	1276.5	1277.4	1278.3
137.5°	1322.6	1323.7	1324.0	1324.6	1325.1	1325.7	1326.3	1327.7	1329.1	1330.6	1332.0
140°	1371.7	1372.6	1373.0	1373.9	1374.7	1375.6	1376.4	1377.6	1378.7	1379.9	1381.0
142.5°	1419.3	1420.2	1420.6	1421.5	1422.3	1423.2	1424.0	1424.9	1425.7	1426.6	1427.5
145°	1464.2	1465.2	1465.5	1466.1	1466.6	1467.2	1467.8	1468.4	1468.9	1469.5	1470.0
147.5°	1504.4	1505.1	1505.4	1505.9	1506.5	1507.0	1507.6	1508.2	1508.8	1509.3	1509.9
150°	1540.7	1541.1	1541.4	1542.0	1542.5	1543.1	1543.7	1544.3	1544.8	1545.4	1545.9
152.5°	1573.1	1573.2	1573.3	1573.6	1573.9	1574.2	1574.5	1575.7	1576.8	1578.0	1579.1
155°	1601.8	1601.5	1601.6	1601.9	1602.2	1602.5	1602.8	1604.2	1605.7	1607.1	1608.6
157.5°	1629.8	1629.8	1629.7	1629.4	1629.1	1628.9	1628.6	1630.3	1632.0	1633.7	1635.4
160°	1651.8	1651.7	1651.6	1651.3	1651.0	1650.7	1650.4	1652.1	1653.8	1655.5	1657.2
162.5°	1671.4	1671.0	1670.9	1670.6	1670.3	1670.0	1669.7	1671.7	1673.7	1675.7	1677.7
165°	1688.1	1687.7	1687.6	1687.3	1687.0	1686.7	1686.4	1688.7	1691.0	1693.3	1695.6
167.5°	1701.2	1700.6	1700.6	1700.6	1700.6	1700.6	1700.6	1702.9	1705.2	1707.5	1709.8
170°	1712.8	1712.2	1712.2	1712.2	1712.2	1712.2	1712.2	1714.5	1716.8	1719.1	1721.4
172.5°	1719.3	1718.6	1718.7	1719.0	1719.3	1719.6	1719.9	1722.2	1724.5	1726.8	1729.1
175°	1725.7	1725.0	1725.1	1725.4	1725.7	1726.0	1726.3	1728.3	1730.3	1732.3	1734.3
177.5°	1728.3	1727.6	1727.7	1728.0	1728.3	1728.6	1728.9	1731.2	1733.5	1735.8	1738.1
180°	1731.5	1731.5	1731.5	1731.5	1731.5	1731.5	1731.5	1731.5	1731.5	1731.5	1731.5

TEST NUMBER: P1032198

CATALOG NUMBER: S123RDIW-B340D1320UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7
2.5°	500.7	501.1	499.8	497.1	496.6	497.5	500.2	499.3	497.1	501.1	497.5
5°	473.0	470.7	469.8	470.7	468.0	466.7	469.4	468.0	469.4	469.8	471.2
7.5°	446.3	446.7	444.0	444.4	440.8	441.7	441.7	441.7	443.1	444.0	445.8
10°	423.1	424.0	420.9	421.3	418.6	416.8	418.1	420.9	420.9	420.9	421.8
12.5°	404.5	400.5	398.2	397.7	394.6	393.7	396.4	397.3	399.5	399.5	400.9
15°	381.4	380.5	378.7	378.7	371.0	372.8	373.7	376.9	381.4	377.8	378.7
17.5°	360.5	358.3	356.0	355.1	354.2	351.5	355.1	354.6	357.4	357.8	359.2
20°	342.0	340.1	335.6	336.1	337.0	332.9	335.1	335.1	337.9	340.6	343.8
22.5°	323.8	322.0	319.7	320.6	317.9	317.0	317.0	319.3	322.5	324.7	324.3
25°	309.8	306.6	305.2	303.9	302.5	303.4	302.0	304.3	306.6	307.9	306.6
27.5°	293.9	292.5	289.8	288.4	286.2	287.1	288.0	289.8	291.2	291.2	292.5
30°	278.5	276.6	275.7	274.4	274.4	272.6	273.0	274.8	276.2	277.6	279.4
32.5°	263.5	262.1	260.8	260.8	259.9	259.4	259.0	261.7	261.7	264.4	264.4
35°	251.2	249.0	249.0	246.7	247.6	247.2	246.3	248.1	248.5	250.3	249.9
37.5°	237.6	237.6	236.7	234.5	232.7	233.1	235.4	235.4	236.7	236.3	237.6
40°	224.0	223.1	223.1	221.8	221.3	220.9	221.3	221.8	224.0	223.6	224.0
42.5°	210.4	210.9	208.6	208.6	208.6	207.3	207.7	208.2	209.1	210.0	211.3
45°	197.3	196.4	195.9	195.0	194.1	194.6	194.1	195.9	195.5	196.4	197.7
47.5°	183.2	181.9	181.4	179.6	179.6	180.5	180.0	181.4	181.9	183.2	182.3
50°	169.6	167.8	166.4	166.9	164.2	165.1	165.1	166.4	167.8	168.3	169.2
52.5°	153.7	153.3	152.8	150.6	150.1	149.7	150.1	150.6	152.4	153.7	154.2
55°	138.3	137.9	135.1	134.2	132.9	132.9	133.8	134.2	137.4	137.9	139.7
57.5°	124.3	122.9	119.7	119.3	119.3	119.3	117.9	119.7	120.6	122.9	122.9
60°	108.8	108.8	106.1	106.1	106.6	106.1	106.1	106.6	106.6	108.4	109.3
62.5°	96.6	96.1	96.1	95.2	94.8	95.2	94.8	94.8	95.2	96.6	98.0
65°	85.7	85.3	84.8	84.4	83.4	83.4	83.9	84.8	84.8	85.7	86.2
67.5°	75.3	75.3	74.4	74.4	73.9	73.5	73.9	73.5	75.3	75.3	75.7
70°	64.9	64.4	63.0	62.6	61.2	61.7	61.7	63.0	63.5	64.4	65.3
72.5°	52.2	52.2	51.2	50.3	50.8	49.9	49.9	50.3	50.3	51.7	52.2
75°	43.1	42.2	41.7	42.2	41.7	42.6	41.7	41.7	42.6	42.6	42.6
77.5°	35.4	35.4	34.9	34.9	35.4	34.9	35.4	35.4	35.4	34.9	35.4
80°	29.0	28.6	28.6	28.6	28.1	28.1	28.1	28.1	28.1	28.1	28.1
82.5°	21.8	21.8	21.3	21.8	21.8	21.3	21.8	21.3	21.3	21.8	21.8
85°	14.5	15.4	14.5	14.5	15.0	15.0	15.4	15.0	15.4	14.5	15.0
87.5°	7.7	8.2	8.2	7.7	7.7	8.2	8.2	8.2	8.6	7.7	8.2
90°	36.0	36.3	36.9	37.4	38.0	38.6	38.0	37.4	36.9	36.3	36.0
92.5°	42.5	42.6	42.9	43.2	43.4	43.7	43.4	43.2	42.9	42.6	42.5
95°	48.9	48.9	48.9	48.9	48.9	48.9	48.9	48.9	48.9	48.9	48.9
97.5°	51.5	51.6	51.9	52.2	52.4	52.7	52.4	52.2	51.9	51.6	51.5
100°	52.7	52.8	53.1	53.4	53.7	54.0	53.7	53.4	53.1	52.8	52.7
102.5°	52.7	53.0	53.6	54.1	54.7	55.3	54.7	54.1	53.6	53.0	52.7
105°	54.0	54.3	54.9	55.4	56.0	56.6	56.0	55.4	54.9	54.3	54.0
107.5°	302.3	283.6	246.1	208.7	171.2	133.8	171.2	208.7	246.1	283.6	302.3
110°	537.7	517.3	476.4	435.5	394.7	353.8	394.7	435.5	476.4	517.3	537.7

TEST NUMBER: P1032198

CATALOG NUMBER: S123RDIW-B340D1320UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	672.8	672.5	671.9	671.4	670.8	670.2	670.8	671.4	671.9	672.5	672.8
115°	751.2	751.8	752.9	754.1	755.2	756.4	755.2	754.1	752.9	751.8	751.2
117.5°	824.6	824.7	825.0	825.3	825.6	825.9	825.6	825.3	825.0	824.7	824.6
120°	897.9	897.9	897.9	897.9	897.9	897.9	897.9	897.9	897.9	897.9	897.9
122.5°	967.4	967.5	967.8	968.1	968.3	968.6	968.3	968.1	967.8	967.5	967.4
125°	1031.7	1032.0	1032.6	1033.1	1033.7	1034.3	1033.7	1033.1	1032.6	1032.0	1031.7
127.5°	1101.1	1100.8	1100.3	1099.7	1099.2	1098.6	1099.2	1099.7	1100.3	1100.8	1101.1
130°	1162.9	1162.6	1162.0	1161.5	1160.9	1160.3	1160.9	1161.5	1162.0	1162.6	1162.9
132.5°	1220.8	1220.4	1219.5	1218.6	1217.8	1216.9	1217.8	1218.6	1219.5	1220.4	1220.8
135°	1278.7	1278.3	1277.4	1276.5	1275.7	1274.8	1275.7	1276.5	1277.4	1278.3	1278.7
137.5°	1332.7	1332.4	1331.8	1331.3	1330.7	1330.1	1330.7	1331.3	1331.8	1332.4	1332.7
140°	1381.6	1381.3	1380.7	1380.2	1379.6	1379.0	1379.6	1380.2	1380.7	1381.3	1381.6
142.5°	1427.9	1427.5	1426.6	1425.7	1424.9	1424.0	1424.9	1425.7	1426.6	1427.5	1427.9
145°	1470.3	1470.3	1470.3	1470.3	1470.3	1470.3	1470.3	1470.3	1470.3	1470.3	1470.3
147.5°	1510.2	1509.5	1508.1	1506.6	1505.2	1503.8	1505.2	1506.6	1508.1	1509.5	1510.2
150°	1546.2	1545.8	1544.9	1544.1	1543.2	1542.4	1543.2	1544.1	1544.9	1545.8	1546.2
152.5°	1579.7	1579.0	1577.5	1576.1	1574.6	1573.2	1574.6	1576.1	1577.5	1579.0	1579.7
155°	1609.3	1608.4	1606.7	1605.0	1603.2	1601.5	1603.2	1605.0	1606.7	1608.4	1609.3
157.5°	1636.3	1635.2	1632.9	1630.6	1628.3	1626.0	1628.3	1630.6	1632.9	1635.2	1636.3
160°	1658.1	1657.1	1655.1	1653.1	1651.1	1649.1	1651.1	1653.1	1655.1	1657.1	1658.1
162.5°	1678.7	1677.8	1676.1	1674.4	1672.7	1671.0	1672.7	1674.4	1676.1	1677.8	1678.7
165°	1696.7	1695.7	1693.7	1691.7	1689.7	1687.7	1689.7	1691.7	1693.7	1695.7	1696.7
167.5°	1710.9	1709.8	1707.5	1705.2	1702.9	1700.6	1702.9	1705.2	1707.5	1709.8	1710.9
170°	1722.5	1721.4	1719.1	1716.8	1714.5	1712.2	1714.5	1716.8	1719.1	1721.4	1722.5
172.5°	1730.2	1728.9	1726.3	1723.8	1721.2	1718.6	1721.2	1723.8	1726.3	1728.9	1730.2
175°	1735.3	1734.2	1731.9	1729.6	1727.3	1725.0	1727.3	1729.6	1731.9	1734.2	1735.3
177.5°	1739.2	1737.8	1734.9	1732.0	1729.2	1726.3	1729.2	1732.0	1734.9	1737.8	1739.2
180°	1731.5	1731.5	1731.5	1731.5	1731.5	1731.5	1731.5	1731.5	1731.5	1731.5	1731.5

TEST NUMBER: P1032198

CATALOG NUMBER: S123RDIW-B340D1320UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7
2.5°	501.1	502.9	501.1	497.5	501.1	503.4	505.7	509.3	511.1	511.1	513.8
5°	472.6	476.2	474.8	473.9	477.6	479.8	483.4	488.0	493.0	496.1	499.8
7.5°	447.2	449.4	451.7	451.7	455.3	460.3	465.8	471.2	477.6	482.1	484.8
10°	424.9	426.8	428.1	429.9	435.4	440.8	448.1	454.9	460.3	465.3	469.8
12.5°	403.6	406.4	409.5	410.9	415.0	421.8	428.6	436.7	445.4	450.3	454.9
15°	383.2	384.6	388.2	392.3	395.9	403.2	411.8	420.4	427.7	435.4	439.5
17.5°	362.4	362.8	372.3	370.1	381.9	388.7	393.2	401.4	413.2	419.5	425.9
20°	342.0	346.5	350.6	352.8	359.2	366.9	380.0	386.4	395.9	401.8	407.3
22.5°	326.1	332.9	332.9	338.3	341.5	348.8	358.3	370.5	381.0	385.0	392.7
25°	312.0	315.2	320.6	322.5	328.3	334.7	341.0	354.2	365.5	371.0	376.4
27.5°	293.9	298.0	305.2	305.2	312.9	319.7	327.4	336.1	347.4	355.1	361.0
30°	279.8	283.9	287.1	292.1	295.2	301.6	315.2	321.5	331.5	338.3	345.6
32.5°	266.7	269.8	272.6	278.0	281.6	288.9	296.1	307.5	316.1	322.5	330.2
35°	252.2	255.3	259.0	263.0	268.5	275.3	282.1	291.6	300.2	306.1	312.5
37.5°	238.5	240.8	246.3	249.0	253.5	259.9	268.5	278.5	286.2	290.7	297.1
40°	225.4	227.2	231.3	236.3	239.5	244.4	253.5	262.1	271.7	277.1	282.1
42.5°	211.3	213.6	217.2	222.2	227.2	232.7	237.6	247.6	256.2	260.8	266.2
45°	199.1	200.5	203.2	208.2	213.2	217.2	224.9	234.0	242.2	245.8	251.7
47.5°	184.6	185.9	190.0	192.3	197.7	203.2	210.9	220.0	227.2	230.8	236.3
50°	169.6	171.0	173.7	178.7	182.3	188.2	195.0	202.7	211.8	216.8	220.0
52.5°	155.1	157.8	160.1	164.2	168.7	174.6	181.0	188.2	195.9	200.9	204.5
55°	140.6	142.9	145.6	147.8	153.3	158.7	166.0	172.8	179.6	184.1	188.2
57.5°	124.3	127.4	130.2	134.7	138.8	143.3	151.5	156.9	165.1	168.3	171.9
60°	110.2	113.4	115.6	119.3	122.9	128.8	134.2	141.0	147.8	151.9	156.5
62.5°	98.4	99.8	101.1	104.8	108.4	113.8	119.3	126.1	133.3	135.6	139.2
65°	86.6	88.0	90.2	93.4	96.1	99.3	105.2	110.7	117.5	121.1	122.4
67.5°	76.6	78.0	78.5	80.7	83.0	86.6	89.8	95.2	101.6	103.9	106.6
70°	65.3	67.6	68.0	69.8	70.7	73.0	76.6	80.7	85.7	89.8	92.1
72.5°	52.2	55.3	56.2	59.0	60.3	62.6	65.3	68.5	71.7	73.5	75.3
75°	42.6	43.5	44.0	46.3	48.5	51.7	53.1	54.9	57.6	59.9	61.7
77.5°	35.4	35.8	36.3	36.3	36.7	38.5	41.3	43.5	45.4	46.3	47.6
80°	28.6	28.1	28.1	28.6	28.6	28.6	29.5	32.7	33.6	35.8	35.4
82.5°	22.2	21.3	21.8	21.3	21.3	21.3	21.3	21.8	21.8	23.1	24.0
85°	14.5	15.0	14.5	14.5	14.1	14.5	14.1	14.1	13.6	13.6	13.2
87.5°	7.7	8.2	7.7	7.7	7.3	7.7	7.3	7.3	6.8	6.8	5.9
90°	35.4	34.3	33.2	32.0	30.9	27.2	23.5	19.8	16.1	14.2	12.8
92.5°	41.5	39.5	37.4	35.4	33.4	30.8	28.3	25.7	23.2	21.9	22.8
95°	47.9	45.9	43.9	41.9	39.9	36.7	33.6	30.4	27.3	25.7	31.6
97.5°	50.4	48.1	45.8	43.5	41.2	55.8	70.4	84.9	99.5	106.8	110.8
100°	51.6	49.3	47.0	44.8	42.5	87.1	131.7	176.2	220.8	243.1	240.2
102.5°	57.4	66.9	76.3	85.8	95.2	144.9	194.7	244.4	294.1	319.0	317.1
105°	79.3	129.9	180.5	231.1	281.7	307.4	333.2	358.9	384.6	397.5	395.9
107.5°	324.3	368.3	412.4	456.4	500.4	496.1	491.8	487.5	483.2	481.1	479.8
110°	542.4	551.9	561.3	570.8	580.2	577.0	573.9	570.7	567.6	566.0	564.9

TEST NUMBER: P1032198

CATALOG NUMBER: S123RDIW-B340D1320UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	671.5	668.9	666.4	663.8	661.2	658.1	654.9	651.8	648.7	647.1	646.1
115°	749.8	746.9	744.1	741.2	738.4	735.8	733.2	730.7	728.1	726.8	725.9
117.5°	823.5	821.2	818.9	816.6	814.3	812.9	811.4	810.0	808.5	807.8	806.8
120°	896.8	894.5	892.2	889.9	887.6	886.7	885.9	885.0	884.1	883.7	882.4
122.5°	966.7	965.2	963.8	962.3	960.9	959.8	958.6	957.5	956.4	955.8	954.8
125°	1031.4	1030.8	1030.3	1029.7	1029.1	1028.0	1026.8	1025.7	1024.6	1024.0	1022.9
127.5°	1100.7	1099.8	1099.0	1098.1	1097.3	1095.9	1094.5	1093.0	1091.6	1090.9	1089.8
130°	1162.3	1161.2	1160.0	1158.9	1157.7	1156.6	1155.4	1154.3	1153.2	1152.6	1151.5
132.5°	1220.2	1219.1	1217.9	1216.8	1215.6	1214.8	1213.9	1213.1	1212.2	1211.8	1210.7
135°	1278.3	1277.4	1276.5	1275.7	1274.8	1273.7	1272.5	1271.4	1270.3	1269.7	1268.8
137.5°	1332.0	1330.6	1329.1	1327.7	1326.3	1325.7	1325.1	1324.6	1324.0	1323.7	1322.6
140°	1381.0	1379.9	1378.7	1377.6	1376.4	1375.6	1374.7	1373.9	1373.0	1372.6	1371.7
142.5°	1427.5	1426.6	1425.7	1424.9	1424.0	1423.2	1422.3	1421.5	1420.6	1420.2	1419.3
145°	1470.0	1469.5	1468.9	1468.4	1467.8	1467.2	1466.6	1466.1	1465.5	1465.2	1464.2
147.5°	1509.9	1509.3	1508.8	1508.2	1507.6	1507.0	1506.5	1505.9	1505.4	1505.1	1504.4
150°	1545.9	1545.4	1544.8	1544.3	1543.7	1543.1	1542.5	1542.0	1541.4	1541.1	1540.7
152.5°	1579.1	1578.0	1576.8	1575.7	1574.5	1574.2	1573.9	1573.6	1573.3	1573.2	1573.1
155°	1608.6	1607.1	1605.7	1604.2	1602.8	1602.5	1602.2	1601.9	1601.6	1601.5	1601.8
157.5°	1635.4	1633.7	1632.0	1630.3	1628.6	1628.9	1629.1	1629.4	1629.7	1629.8	1629.8
160°	1657.2	1655.5	1653.8	1652.1	1650.4	1650.7	1651.0	1651.3	1651.6	1651.7	1651.8
162.5°	1677.7	1675.7	1673.7	1671.7	1669.7	1670.0	1670.3	1670.6	1670.9	1671.0	1671.4
165°	1695.6	1693.3	1691.0	1688.7	1686.4	1686.7	1687.0	1687.3	1687.6	1687.7	1688.1
167.5°	1709.8	1707.5	1705.2	1702.9	1700.6	1700.6	1700.6	1700.6	1700.6	1700.6	1701.2
170°	1721.4	1719.1	1716.8	1714.5	1712.2	1712.2	1712.2	1712.2	1712.2	1712.2	1712.8
172.5°	1729.1	1726.8	1724.5	1722.2	1719.9	1719.6	1719.3	1719.0	1718.7	1718.6	1719.3
175°	1734.3	1732.3	1730.3	1728.3	1726.3	1726.0	1725.7	1725.4	1725.1	1725.0	1725.7
177.5°	1738.1	1735.8	1733.5	1731.2	1728.9	1728.6	1728.3	1728.0	1727.7	1727.6	1728.3
180°	1731.5	1731.5	1731.5	1731.5	1731.5	1731.5	1731.5	1731.5	1731.5	1731.5	1731.5

TEST NUMBER: P1032198

CATALOG NUMBER: S123RDIW-B340D1320UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	529.7	529.7	529.7	529.7
2.5°	516.1	519.3	525.6	531.1
5°	505.2	510.2	519.7	529.3
7.5°	492.1	499.8	512.0	525.2
10°	479.4	489.3	504.3	519.7
12.5°	466.7	477.1	493.0	512.9
15°	451.7	462.6	481.6	505.7
17.5°	438.6	453.1	470.3	494.3
20°	424.5	435.4	457.6	483.0
22.5°	406.8	424.9	445.8	472.6
25°	392.7	408.6	429.5	459.9
27.5°	375.5	394.1	419.5	446.3
30°	361.5	376.9	400.5	432.7
32.5°	345.1	363.3	387.8	419.5
35°	330.6	346.0	369.2	401.4
37.5°	313.4	330.2	356.0	384.6
40°	298.4	314.7	339.2	366.0
42.5°	280.3	297.5	322.0	344.7
45°	265.8	281.6	301.1	322.0
47.5°	248.1	264.9	283.9	298.4
50°	232.2	247.6	262.6	274.8
52.5°	215.0	229.0	242.6	251.7
55°	199.1	210.0	220.9	227.2
57.5°	180.5	190.9	200.0	203.6
60°	164.2	172.8	178.7	182.8
62.5°	146.9	153.3	157.8	160.1
65°	130.2	134.7	137.0	139.2
67.5°	112.9	117.0	118.4	121.1
70°	94.8	99.3	100.2	101.6
72.5°	81.2	81.2	83.0	84.8
75°	64.9	65.8	66.7	66.7
77.5°	50.8	50.8	51.7	52.2
80°	37.2	37.6	37.6	37.2
82.5°	25.4	26.3	25.4	24.9
85°	14.1	15.9	15.0	15.0
87.5°	5.9	5.9	6.8	5.9
90°	9.9	7.0	4.2	1.3
92.5°	24.5	26.2	27.9	29.6
95°	43.3	55.0	66.8	78.5
97.5°	118.8	126.8	134.8	142.8
100°	234.5	228.8	223.1	217.4
102.5°	313.4	309.7	306.0	302.3
105°	392.8	389.6	386.5	383.3
107.5°	477.2	474.7	472.1	469.5
110°	562.6	560.3	558.0	555.7

TEST NUMBER: P1032198

CATALOG NUMBER: S123RDIW-B340D1320UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	644.1	642.0	640.0	638.0
115°	724.2	722.5	720.8	719.1
117.5°	804.8	802.8	800.8	798.8
120°	879.9	877.3	874.8	872.2
122.5°	952.8	950.8	948.8	946.8
125°	1020.6	1018.3	1016.0	1013.7
127.5°	1087.5	1085.2	1082.9	1080.6
130°	1149.2	1146.9	1144.6	1142.3
132.5°	1208.4	1206.1	1203.8	1201.5
135°	1267.1	1265.4	1263.6	1261.9
137.5°	1320.3	1318.0	1315.7	1313.4
140°	1370.0	1368.3	1366.6	1364.9
142.5°	1417.6	1415.9	1414.1	1412.4
145°	1462.2	1460.2	1458.2	1456.2
147.5°	1502.9	1501.5	1500.0	1498.6
150°	1539.8	1538.9	1538.1	1537.2
152.5°	1572.8	1572.5	1572.3	1572.0
155°	1602.4	1602.9	1603.5	1604.1
157.5°	1629.8	1629.8	1629.8	1629.8
160°	1652.1	1652.4	1652.7	1653.0
162.5°	1672.3	1673.2	1674.0	1674.9
165°	1689.0	1689.9	1690.7	1691.6
167.5°	1702.3	1703.4	1704.6	1705.7
170°	1713.9	1715.0	1716.2	1717.3
172.5°	1720.7	1722.2	1723.6	1725.0
175°	1727.2	1728.6	1730.1	1731.5
177.5°	1729.7	1731.2	1732.6	1734.0
180°	1731.5	1731.5	1731.5	1731.5

(END OF REPORT)