

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032213

Luminaire Tested: S123RDIW-B340D1320UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032213
REPORT IS A COMBINATION OF REPORTS P994245 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B340D1320UB50-4F0-XX-W2A-F1
Description: Define 3 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5619.0 lumens
Efficiency: N/A
Efficacy: 102.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 55.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032213

CATALOG NUMBER: S123RDIW-B340D1320UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1032213

CATALOG NUMBER: S123RDIW-B340D1320UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	100	100	100	100	89	89	89	89	68	68	68	48	48	48	30	30	30	30	30	22
1	92	87	84	81	81	78	75	72	59	57	55	42	41	40	27	26	26	26	26	19
2	83	76	71	66	74	68	63	59	52	49	46	37	35	34	24	23	22	22	22	16
3	76	67	60	55	67	60	54	49	46	42	39	33	31	29	21	20	19	19	19	13
4	70	59	52	46	61	53	47	42	41	36	33	29	27	24	19	17	16	16	16	12
5	64	53	45	40	56	47	41	36	36	32	28	26	23	21	17	15	14	14	14	10
6	59	47	40	34	52	42	36	31	33	28	25	24	21	18	15	14	12	12	12	9
7	54	43	35	30	48	38	32	27	30	25	22	22	19	16	14	12	11	11	11	8
8	50	38	31	26	44	34	28	24	27	22	19	20	17	14	13	11	10	10	10	7
9	47	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9	9	9	7
10	43	32	25	21	38	29	23	19	22	18	15	17	14	12	11	9	8	8	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5789	5789	5789
5°	5798	5584	5569
10°	5752	5374	5268
15°	5678	5114	4939
20°	5580	4832	4571
25°	5479	4539	4222
30°	5349	4227	3810
35°	5216	3921	3434
40°	5091	3588	3019
45°	4929	3262	2647
50°	4752	2915	2260
55°	4568	2543	1906
60°	4393	2162	1548
65°	4165	1770	1208
70°	3878	1338	864
75°	3469	906	684
80°	2959	630	480
85°	2219	340	250

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4929 cd/sqm

TEST NUMBER: P1032213

CATALOG NUMBER: S123RDIW-B340D1320UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.6	0.9
10°-20°	140.6	2.5
20°-30°	202.5	3.6
30°-40°	228.0	4.1
40°-50°	218.1	3.9
50°-60°	178.6	3.2
60°-70°	120.4	2.1
70°-80°	60.4	1.1
80°-90°	19.1	0.3
90°-100°	102.2	1.8
100°-110°	309.4	5.5
110°-120°	526.8	9.4
120°-130°	693.0	12.3
130°-140°	779.0	13.9
140°-150°	765.8	13.6
150°-160°	644.8	11.5
160°-170°	429.2	7.6
170°-180°	150.3	2.7
0°-30°	393.7	7.0
0°-40°	621.7	11.1
0°-60°	1018.4	18.1
0°-90°	1218.3	21.7
90°-120°	938.5	16.7
90°-150°	3176.3	56.5
90°-180°	4401.0	78.3
0°-180°	5619.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	538	538	538	538	538	
5°	538	536	530	534	533	51
15°	513	508	496	494	491	145
25°	467	456	436	427	422	215
35°	404	388	361	342	334	253
45°	332	312	279	254	243	256
55°	252	231	194	168	160	226
65°	172	148	114	93	88	171
75°	91	70	46	42	41	97
85°	23	14	12	11	11	25
90°	1	14	30	35	37	7
95°	74	82	92	97	97	81
105°	281	283	294	294	297	301
115°	530	534	532	533	532	525
125°	776	780	777	772	767	692
135°	1007	1014	1013	1008	1006	776
145°	1221	1224	1228	1226	1221	763
155°	1399	1399	1400	1405	1396	644
165°	1523	1520	1520	1527	1518	430
175°	1584	1580	1580	1587	1578	151
180°	1588	1588	1588	1588	1588	

TEST NUMBER: P1032213

CATALOG NUMBER: S123RDIW-B340D1320UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	537.8	537.8	537.8	537.8	537.8
2.5°	540.0	538.2	533.0	537.8	536.9
5°	537.8	535.6	530.4	534.3	533.4
7.5°	533.9	531.7	525.2	527.8	526.5
10°	528.6	525.6	517.7	518.2	516.0
12.5°	521.2	517.7	507.7	507.3	504.7
15°	512.9	508.1	495.9	493.8	490.7
17.5°	502.9	497.7	482.4	478.1	473.7
20°	491.6	484.6	468.0	462.3	457.1
22.5°	478.9	470.6	452.8	445.3	440.5
25°	466.7	455.8	435.7	426.6	421.8
27.5°	451.9	440.1	418.3	406.1	398.7
30°	436.6	423.5	399.1	384.3	377.3
32.5°	421.3	406.1	379.9	363.3	355.9
35°	403.9	388.2	361.2	342.4	334.5
37.5°	386.5	369.4	341.1	320.2	310.6
40°	369.9	350.7	319.7	297.0	287.0
42.5°	351.1	331.9	299.7	274.4	265.6
45°	331.9	312.3	278.7	253.9	243.4
47.5°	313.2	291.4	258.2	231.2	222.0
50°	292.2	271.7	236.4	209.4	199.3
52.5°	273.5	250.8	215.9	187.6	178.8
55°	252.1	230.7	193.7	168.4	159.6
57.5°	232.9	209.8	172.3	148.3	140.9
60°	212.9	188.9	152.7	129.1	121.7
62.5°	192.8	168.8	132.6	110.8	102.9
65°	172.3	148.3	114.3	92.9	88.1
67.5°	151.8	127.4	94.2	78.1	72.8
70°	131.7	108.2	77.6	62.4	57.6
72.5°	111.7	88.5	61.5	49.7	48.4
75°	91.2	70.2	46.2	41.9	41.0
77.5°	72.4	53.2	36.2	33.6	32.7
80°	54.5	36.6	27.5	26.2	25.3
82.5°	37.5	22.7	19.6	18.3	18.3
85°	23.1	13.5	12.2	11.3	11.3
87.5°	10.5	5.7	5.7	5.2	4.8
90°	1.2	13.7	29.9	34.9	37.4
92.5°	37.4	44.9	52.4	56.1	53.6
95°	73.6	82.3	92.3	97.3	97.3
97.5°	121.0	127.3	134.7	141.0	139.7
100°	169.7	177.2	183.4	187.1	189.6
102.5°	225.8	229.6	238.3	242.0	240.8
105°	280.7	283.2	294.4	294.4	296.9
107.5°	345.6	346.8	351.8	355.6	354.3
110°	405.5	408.0	410.5	415.5	413.0

TEST NUMBER: P1032213

CATALOG NUMBER: S123RDIW-B340D1320UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	467.9	469.1	469.1	475.3	475.3
115°	530.2	534.0	531.5	532.7	531.5
117.5°	593.9	595.1	592.6	592.6	588.9
120°	652.5	660.0	653.7	652.5	650.0
122.5°	713.6	718.6	716.1	712.4	708.6
125°	776.0	779.8	777.3	772.3	767.3
127.5°	833.4	840.9	838.4	830.9	825.9
130°	890.8	900.8	897.0	892.0	883.3
132.5°	948.2	958.2	955.7	949.4	943.2
135°	1006.8	1014.3	1013.1	1008.1	1005.6
137.5°	1060.5	1066.7	1070.5	1064.2	1060.5
140°	1116.6	1122.9	1124.1	1122.9	1114.1
142.5°	1167.8	1174.0	1176.5	1175.3	1169.0
145°	1221.4	1223.9	1227.7	1226.4	1221.4
147.5°	1267.6	1272.6	1276.3	1276.3	1268.8
150°	1316.2	1318.7	1321.2	1321.2	1313.7
152.5°	1356.2	1359.9	1361.1	1363.6	1357.4
155°	1398.6	1398.6	1399.8	1404.8	1396.1
157.5°	1434.8	1433.5	1434.8	1439.7	1432.3
160°	1468.4	1465.9	1465.9	1472.2	1467.2
162.5°	1498.4	1494.6	1495.9	1502.1	1493.4
165°	1523.3	1519.6	1519.6	1527.1	1518.3
167.5°	1544.5	1539.6	1540.8	1548.3	1540.8
170°	1562.0	1557.0	1557.0	1565.8	1557.0
172.5°	1575.7	1570.7	1570.7	1578.2	1569.5
175°	1584.5	1579.5	1579.5	1587.0	1578.2
177.5°	1589.5	1584.5	1584.5	1592.0	1583.2
180°	1588.2	1588.2	1588.2	1588.2	1588.2

(END OF REPORT)