

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032214

Luminaire Tested: S123RDIW-B340D1535UB27-4F0-XX-W2A-A

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032214
REPORT IS A COMBINATION OF REPORTS P994247 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B340D1535UB27-4F0-XX-W2A-A
Description: Define 3 Regressed Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7483.0 lumens
Efficiency: N/A
Efficacy: 114.8 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 65.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032214

CATALOG NUMBER: S123RDIW-B340D1535UB27-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1032214

CATALOG NUMBER: S123RDIW-B340D1535UB27-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	99	99	99	99	88	88	88	88	65	65	65	45	45	45	26	26	26
1	91	87	83	80	80	76	73	71	57	55	54	40	39	38	23	23	23
2	83	76	70	65	73	67	62	58	50	47	45	35	33	32	21	20	19
3	75	67	60	55	66	59	53	49	45	41	38	31	29	27	19	18	17
4	69	59	52	46	61	52	46	41	40	35	32	28	25	23	17	15	14
5	63	52	45	39	56	47	40	35	35	31	28	25	22	20	15	14	13
6	58	47	39	34	51	42	35	31	32	27	24	22	20	18	14	12	11
7	54	42	35	30	47	38	31	27	29	24	21	20	18	15	13	11	10
8	50	38	31	26	44	34	28	23	26	22	19	19	16	14	12	10	9
9	46	35	28	23	41	31	25	21	24	19	16	17	14	12	11	9	8
10	43	32	25	20	38	28	22	18	22	18	15	16	13	11	10	8	7

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5654	5654	5654	5654
5°	5658	6512	5673	4831
10°	5609	7861	5633	4220
15°	5551	8922	5551	3721
20°	5437	9623	5468	3301
25°	5353	9143	5343	3012
30°	5256	6335	5245	2729
35°	5140	4067	5117	2516
40°	4994	2872	4970	2304
45°	4742	2299	4736	2097
50°	4431	1922	4417	1856
55°	4082	1585	4050	1574
60°	3739	1310	3702	1338
65°	3338	1049	3360	1135
70°	2965	729	3045	918
75°	2514	541	2617	706
80°	2003	358	2172	529
85°	1422	168	1556	328

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 7549 cd/sqm

TEST NUMBER: P1032214

CATALOG NUMBER: S123RDIW-B340D1535UB27-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.6	0.7
10°-20°	161.5	2.2
20°-30°	254.3	3.4
30°-40°	264.5	3.5
40°-50°	226.3	3.0
50°-60°	172.5	2.3
60°-70°	110.5	1.5
70°-80°	52.9	0.7
80°-90°	17.9	0.2
90°-100°	71.4	1.0
100°-110°	345.1	4.6
110°-120°	845.7	11.3
120°-130°	1073.6	14.3
130°-140°	1146.9	15.3
140°-150°	1072.5	14.3
150°-160°	865.1	11.6
160°-170°	558.3	7.5
170°-180°	192.4	2.6
0°-30°	467.4	6.2
0°-40°	731.9	9.8
0°-60°	1130.6	15.1
0°-90°	1312.0	17.5
90°-120°	1262.2	16.9
90°-150°	4555.2	60.9
90°-180°	6171.0	82.5
0°-180°	7483.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	525	525	525	525	525	
5°	525	624	526	463	525	50
15°	502	886	502	370	502	141
25°	456	913	455	301	456	210
35°	398	396	396	245	398	249
45°	319	211	319	193	319	246
55°	225	133	224	132	225	202
65°	138	76	139	83	138	138
75°	66	32	69	42	66	71
85°	15	8	16	15	15	17
90°	2	45	2	45	2	6
95°	92	57	92	57	92	110
105°	448	66	448	66	448	475
115°	841	884	841	884	841	830
125°	1185	1209	1185	1209	1185	1059
135°	1475	1490	1475	1490	1475	1136
145°	1702	1719	1702	1719	1702	1066
155°	1875	1872	1875	1872	1875	864
165°	1978	1973	1978	1973	1978	559
175°	2024	2017	2024	2017	2024	193
180°	2024	2024	2024	2024	2024	

TEST NUMBER: P1032214

CATALOG NUMBER: S123RDIW-B340D1535UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3
2.5°	526.6	530.2	532.9	534.7	539.2	541.9	544.2	548.2	548.2	549.1	550.9
5°	524.8	532.5	537.9	545.1	554.5	559.0	565.3	570.7	578.4	582.4	586.5
7.5°	520.8	531.6	542.8	553.6	567.6	576.6	582.9	596.8	606.7	618.8	628.3
10°	515.4	530.2	544.6	561.3	580.2	593.6	603.1	621.5	640.4	657.5	671.9
12.5°	508.6	526.6	547.3	567.6	594.1	607.6	622.9	645.8	672.8	694.4	713.7
15°	501.5	522.1	545.5	570.3	603.5	622.4	644.5	672.4	702.5	733.5	760.1
17.5°	490.2	516.3	542.4	578.4	617.5	628.7	647.6	685.8	723.2	751.1	783.4
20°	479.0	508.2	541.0	573.4	615.7	641.8	659.3	699.8	739.8	773.5	804.6
22.5°	468.6	499.2	533.4	574.3	613.9	640.0	662.0	704.3	750.6	788.4	826.6
25°	456.0	489.3	527.1	565.8	613.9	633.7	658.0	707.0	756.0	799.6	846.8
27.5°	442.5	476.3	513.6	553.2	597.2	626.5	650.3	702.9	762.7	809.5	858.1
30°	429.0	463.7	499.7	535.2	584.7	612.5	640.0	698.0	766.3	819.9	857.2
32.5°	416.0	445.2	480.8	515.4	564.4	595.0	626.0	693.0	767.7	812.7	830.7
35°	398.0	428.6	457.4	494.3	543.7	573.9	610.3	692.6	761.8	789.7	780.7
37.5°	381.4	407.0	434.4	467.3	518.1	557.2	595.0	680.9	742.5	744.3	693.5
40°	362.9	384.1	407.0	441.6	496.5	535.2	576.1	662.9	707.4	680.9	591.4
42.5°	341.8	360.7	378.7	412.4	472.2	515.4	559.5	640.4	656.6	595.4	502.4
45°	319.3	334.6	351.2	386.8	446.6	489.3	533.4	605.8	589.2	502.8	414.2
47.5°	295.9	309.0	325.2	357.5	419.2	462.8	504.6	556.3	514.0	421.4	347.2
50°	272.5	282.9	298.6	331.9	391.3	430.8	469.5	503.3	443.9	361.6	286.9
52.5°	249.6	257.7	273.9	302.2	359.8	397.6	425.4	438.5	378.2	298.6	249.2
55°	225.3	234.3	245.1	273.9	331.0	358.9	377.3	376.9	314.8	253.2	206.0
57.5°	201.9	210.0	219.5	248.3	294.6	313.5	329.2	321.6	262.6	207.3	176.7
60°	181.2	185.7	196.1	220.4	255.4	271.6	280.6	267.6	214.5	174.9	146.2
62.5°	158.8	163.3	171.8	194.7	216.3	224.9	232.5	215.9	177.2	142.6	125.0
65°	138.1	143.9	149.3	167.8	179.4	189.8	188.9	174.9	138.5	116.0	101.6
67.5°	120.1	122.3	126.8	138.1	143.5	151.1	151.6	135.8	111.5	94.4	85.9
70°	100.7	103.0	106.1	111.5	115.1	116.9	116.0	102.1	84.1	73.8	66.1
72.5°	84.1	83.7	85.9	85.9	89.5	89.0	86.3	75.6	63.9	55.3	50.8
75°	66.1	66.6	67.0	66.1	64.8	63.0	60.7	52.6	45.0	40.9	36.9
77.5°	51.7	50.8	51.3	48.1	46.3	44.5	41.4	37.3	31.0	30.1	28.3
80°	36.9	36.4	36.0	34.6	30.6	28.8	26.5	24.3	22.9	22.0	21.6
82.5°	24.7	24.7	23.8	21.1	18.9	17.5	17.1	16.2	14.8	14.8	14.4
85°	14.8	14.4	13.5	10.8	9.4	9.4	9.4	9.4	8.5	8.5	8.1
87.5°	5.8	5.4	4.0	4.0	3.6	3.6	3.6	3.1	3.1	2.7	2.7
90°	1.5	4.8	8.2	11.5	14.8	16.5	18.7	23.0	27.4	31.7	36.1
92.5°	34.6	32.6	30.6	28.6	26.6	25.6	27.1	30.1	33.1	36.1	39.1
95°	91.7	78.0	64.3	50.6	36.9	30.1	31.9	35.6	39.3	42.9	46.6
97.5°	166.9	157.5	148.2	138.8	129.5	124.8	116.3	99.2	82.2	65.1	48.1
100°	254.2	260.9	267.5	274.2	280.9	284.2	258.1	206.0	153.9	101.7	49.6
102.5°	353.4	357.8	362.1	366.5	370.8	373.0	343.9	285.8	227.6	169.5	111.3
105°	448.2	451.9	455.5	459.2	462.9	464.7	449.7	419.6	389.5	359.4	329.3
107.5°	548.9	551.9	554.9	557.9	560.9	562.4	564.9	569.9	575.0	580.0	585.0
110°	649.7	652.4	655.0	657.7	660.4	661.7	663.5	667.2	670.9	674.5	678.2

TEST NUMBER: P1032214

CATALOG NUMBER: S123RDIW-B340D1535UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	745.9	748.2	750.6	752.9	755.2	756.4	758.2	761.9	765.6	769.3	773.0
115°	840.7	842.7	844.7	846.7	848.7	849.7	851.2	854.2	857.2	860.2	863.2
117.5°	933.9	936.2	938.6	940.9	943.2	944.4	945.2	946.9	948.6	950.2	951.9
120°	1019.6	1022.6	1025.6	1028.7	1031.7	1033.2	1033.7	1034.7	1035.7	1036.7	1037.7
122.5°	1106.8	1109.2	1111.5	1113.9	1116.2	1117.4	1118.1	1119.4	1120.7	1122.1	1123.4
125°	1185.0	1187.7	1190.4	1193.1	1195.8	1197.1	1197.8	1199.1	1200.4	1201.8	1203.1
127.5°	1263.2	1265.9	1268.6	1271.3	1274.0	1275.3	1276.1	1277.8	1279.5	1281.1	1282.8
130°	1335.4	1338.1	1340.8	1343.5	1346.2	1347.5	1348.2	1349.5	1350.8	1352.2	1353.5
132.5°	1404.6	1407.3	1409.9	1412.6	1415.3	1416.6	1417.1	1418.1	1419.2	1420.2	1421.2
135°	1475.3	1477.3	1479.3	1481.3	1483.3	1484.3	1485.0	1486.3	1487.6	1489.0	1490.3
137.5°	1535.4	1538.1	1540.8	1543.5	1546.2	1547.5	1547.8	1548.5	1549.2	1549.8	1550.5
140°	1595.6	1597.6	1599.6	1601.6	1603.6	1604.6	1605.1	1606.1	1607.1	1608.1	1609.1
142.5°	1651.2	1653.2	1655.2	1657.3	1659.3	1660.3	1660.8	1661.8	1662.8	1663.8	1664.8
145°	1702.4	1704.7	1707.1	1709.4	1711.7	1712.9	1713.2	1713.9	1714.6	1715.2	1715.9
147.5°	1752.0	1753.7	1755.3	1757.0	1758.7	1759.5	1759.8	1760.5	1761.2	1761.8	1762.5
150°	1797.1	1798.1	1799.1	1800.1	1801.1	1801.6	1801.9	1802.6	1803.3	1803.9	1804.6
152.5°	1837.7	1838.0	1838.4	1838.7	1839.0	1839.2	1839.4	1839.7	1840.0	1840.4	1840.7
155°	1875.3	1874.6	1874.0	1873.3	1872.6	1872.3	1872.5	1872.8	1873.1	1873.5	1873.8
157.5°	1905.4	1905.4	1905.4	1905.4	1905.4	1905.4	1905.2	1904.9	1904.6	1904.2	1903.9
160°	1932.5	1932.2	1931.8	1931.5	1931.2	1931.0	1930.8	1930.5	1930.2	1929.8	1929.5
162.5°	1958.0	1957.0	1956.0	1955.0	1954.0	1953.5	1953.3	1953.0	1952.7	1952.3	1952.0
165°	1977.6	1976.6	1975.6	1974.6	1973.6	1973.1	1972.9	1972.6	1972.3	1971.9	1971.6
167.5°	1994.1	1992.8	1991.4	1990.1	1988.8	1988.1	1988.1	1988.1	1988.1	1988.1	1988.1
170°	2007.7	2006.3	2005.0	2003.6	2002.3	2001.6	2001.6	2001.6	2001.6	2001.6	2001.6
172.5°	2016.7	2015.0	2013.4	2011.7	2010.0	2009.2	2009.4	2009.7	2010.0	2010.4	2010.7
175°	2024.2	2022.5	2020.9	2019.2	2017.5	2016.7	2016.9	2017.2	2017.5	2017.9	2018.2
177.5°	2027.2	2025.5	2023.9	2022.2	2020.5	2019.7	2019.9	2020.2	2020.5	2020.9	2021.2
180°	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2

TEST NUMBER: P1032214

CATALOG NUMBER: S123RDIW-B340D1535UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3
2.5°	554.5	554.5	558.6	562.6	560.4	561.7	566.7	564.9	568.5	568.0	569.4
5°	596.3	601.3	605.3	613.9	615.2	613.9	622.4	624.7	628.7	623.8	626.0
7.5°	643.6	653.9	663.8	676.4	680.4	681.3	685.8	692.1	697.5	687.6	692.6
10°	689.4	705.2	725.4	736.7	746.6	750.2	753.8	757.8	764.1	769.9	765.4
12.5°	738.9	761.8	781.2	801.4	813.6	812.2	822.6	825.3	830.2	831.6	833.4
15°	779.4	811.8	823.9	854.0	856.7	865.7	877.4	887.8	889.1	886.4	886.4
17.5°	818.1	846.0	867.5	891.8	896.8	904.4	919.3	924.2	926.0	925.6	925.6
20°	849.5	868.0	904.4	924.7	932.7	942.6	953.0	959.3	960.6	962.4	959.7
22.5°	870.2	898.1	927.8	944.4	951.2	954.8	961.5	963.3	961.1	961.5	962.0
25°	886.4	913.9	931.8	936.3	935.9	931.4	926.5	917.9	917.0	913.4	906.2
27.5°	890.9	901.3	899.0	880.6	862.1	860.3	830.7	814.5	796.0	798.7	788.4
30°	866.6	853.1	821.2	774.4	755.1	723.6	690.3	655.7	642.2	627.4	654.8
32.5°	807.3	759.2	702.5	641.8	609.4	581.5	546.0	520.8	506.4	494.3	517.6
35°	717.8	642.7	567.6	510.0	483.5	458.3	425.0	412.4	394.4	396.2	398.5
37.5°	602.6	519.9	463.2	406.6	389.0	378.7	354.4	335.1	328.8	327.0	327.0
40°	494.7	426.8	376.4	331.9	318.4	309.9	290.5	281.5	274.8	273.0	275.2
42.5°	409.3	351.2	312.1	282.4	273.0	262.2	254.1	242.9	241.5	238.4	242.4
45°	343.6	293.2	264.0	242.4	234.3	230.3	221.3	214.5	211.8	211.4	214.5
47.5°	291.4	252.3	226.7	213.2	206.9	202.8	195.2	192.5	189.8	190.7	189.3
50°	244.7	215.4	198.8	186.6	182.6	178.5	173.6	170.9	169.5	169.5	169.1
52.5°	210.0	185.7	174.9	163.7	161.9	159.7	154.3	152.5	150.2	149.8	151.6
55°	179.9	163.3	152.5	145.7	143.9	139.4	137.2	134.9	133.6	132.7	133.1
57.5°	153.8	141.2	134.0	128.2	125.0	123.2	119.2	118.7	117.8	117.8	117.4
60°	132.2	123.2	114.7	111.1	108.8	106.6	106.1	103.4	102.1	103.0	102.5
62.5°	112.0	104.8	99.8	95.8	94.4	92.6	91.3	90.4	89.0	89.5	89.5
65°	93.5	87.7	84.1	80.5	80.1	78.3	77.8	76.9	76.9	76.5	77.4
67.5°	76.9	72.9	69.7	67.5	66.1	66.6	64.8	63.4	63.4	63.0	64.3
70°	61.2	58.9	55.8	53.1	51.3	51.3	49.0	48.6	48.6	48.6	48.1
72.5°	47.2	43.2	41.8	40.9	40.9	40.9	40.0	40.0	39.6	40.0	39.6
75°	35.1	34.6	33.7	33.3	33.3	32.8	32.4	32.4	32.4	32.4	32.4
77.5°	27.4	27.4	26.5	26.1	26.1	26.1	25.6	25.6	25.2	25.2	25.2
80°	20.2	20.2	19.3	19.3	19.3	18.9	18.9	18.9	19.3	18.9	18.9
82.5°	13.9	13.9	13.5	13.9	13.5	13.0	13.0	13.0	12.6	13.0	13.0
85°	8.1	8.1	7.6	7.2	7.6	7.6	7.2	7.6	7.2	7.6	7.2
87.5°	3.1	2.7	2.7	2.7	2.2	2.7	2.2	2.2	2.7	2.2	2.7
90°	37.4	38.8	40.1	41.4	42.1	42.4	43.1	43.8	44.4	45.1	44.4
92.5°	41.4	43.8	46.1	48.4	49.6	49.8	50.1	50.4	50.8	51.1	50.8
95°	48.9	51.3	53.6	55.9	57.1	57.1	57.1	57.1	57.1	57.1	57.1
97.5°	50.8	53.5	56.2	58.9	60.2	60.4	60.7	61.0	61.4	61.7	61.4
100°	52.3	55.0	57.7	60.4	61.7	61.9	62.2	62.5	62.9	63.2	62.9
102.5°	100.3	89.3	78.2	67.2	61.7	62.0	62.7	63.4	64.0	64.7	64.0
105°	270.2	211.0	151.9	92.8	63.2	63.5	64.2	64.9	65.5	66.2	65.5
107.5°	533.5	482.1	430.6	379.1	353.4	331.5	287.7	244.0	200.2	156.4	200.2
110°	667.2	656.2	645.1	634.1	628.6	604.7	556.9	509.2	461.4	413.6	461.4

TEST NUMBER: P1032214

CATALOG NUMBER: S123RDIW-B340D1535UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	776.0	779.0	782.0	785.0	786.5	786.2	785.5	784.8	784.2	783.5	784.2
115°	866.6	869.9	873.3	876.6	878.3	879.0	880.3	881.6	883.0	884.3	883.0
117.5°	954.6	957.3	960.0	962.7	964.0	964.2	964.5	964.8	965.2	965.5	965.2
120°	1040.4	1043.0	1045.7	1048.4	1049.7	1049.7	1049.7	1049.7	1049.7	1049.7	1049.7
122.5°	1125.1	1126.7	1128.4	1130.1	1130.9	1131.1	1131.4	1131.7	1132.1	1132.4	1132.1
125°	1203.8	1204.4	1205.1	1205.8	1206.1	1206.4	1207.1	1207.8	1208.4	1209.1	1208.4
127.5°	1283.8	1284.8	1285.8	1286.8	1287.3	1287.0	1286.3	1285.6	1285.0	1284.3	1285.0
130°	1354.8	1356.2	1357.5	1358.8	1359.5	1359.2	1358.5	1357.8	1357.2	1356.5	1357.2
132.5°	1422.5	1423.9	1425.2	1426.5	1427.2	1426.7	1425.7	1424.7	1423.7	1422.7	1423.7
135°	1491.3	1492.3	1493.3	1494.3	1494.8	1494.3	1493.3	1492.3	1491.3	1490.3	1491.3
137.5°	1552.2	1553.8	1555.5	1557.2	1558.0	1557.7	1557.0	1556.3	1555.7	1555.0	1555.7
140°	1610.5	1611.8	1613.2	1614.5	1615.2	1614.9	1614.2	1613.5	1612.8	1612.1	1612.8
142.5°	1665.8	1666.8	1667.8	1668.8	1669.3	1668.8	1667.8	1666.8	1665.8	1664.8	1665.8
145°	1716.6	1717.2	1717.9	1718.6	1718.9	1718.9	1718.9	1718.9	1718.9	1718.9	1718.9
147.5°	1763.2	1763.8	1764.5	1765.2	1765.5	1764.7	1763.0	1761.3	1759.7	1758.0	1759.7
150°	1805.3	1805.9	1806.6	1807.3	1807.6	1807.1	1806.1	1805.1	1804.1	1803.1	1804.1
152.5°	1842.0	1843.4	1844.7	1846.0	1846.7	1845.9	1844.2	1842.5	1840.9	1839.2	1840.9
155°	1875.5	1877.1	1878.8	1880.5	1881.3	1880.3	1878.3	1876.3	1874.3	1872.3	1874.3
157.5°	1905.9	1907.9	1909.9	1911.9	1912.9	1911.6	1908.9	1906.2	1903.6	1900.9	1903.6
160°	1931.5	1933.5	1935.5	1937.5	1938.5	1937.3	1935.0	1932.7	1930.3	1928.0	1930.3
162.5°	1954.3	1956.7	1959.0	1961.3	1962.5	1961.5	1959.5	1957.5	1955.5	1953.5	1955.5
165°	1974.3	1976.9	1979.6	1982.3	1983.6	1982.4	1980.1	1977.8	1975.4	1973.1	1975.4
167.5°	1990.8	1993.4	1996.1	1998.8	2000.1	1998.8	1996.1	1993.4	1990.8	1988.1	1990.8
170°	2004.3	2007.0	2009.7	2012.4	2013.7	2012.4	2009.7	2007.0	2004.3	2001.6	2004.3
172.5°	2013.4	2016.0	2018.7	2021.4	2022.7	2021.2	2018.2	2015.2	2012.2	2009.2	2012.2
175°	2020.5	2022.9	2025.2	2027.5	2028.7	2027.4	2024.7	2022.0	2019.4	2016.7	2019.4
177.5°	2023.9	2026.5	2029.2	2031.9	2033.2	2031.5	2028.2	2024.9	2021.5	2018.2	2021.5
180°	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2

TEST NUMBER: P1032214

CATALOG NUMBER: S123RDIW-B340D1535UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3
2.5°	567.1	564.4	562.6	561.3	559.9	564.0	558.6	552.7	548.7	546.0	545.1
5°	626.5	620.6	615.7	611.6	612.5	612.5	603.1	592.7	583.8	578.8	573.4
7.5°	695.3	689.0	679.1	676.8	675.1	663.8	654.4	635.5	624.2	613.0	603.1
10°	763.6	755.6	746.1	743.0	738.5	724.5	710.1	685.8	671.9	651.2	638.2
12.5°	827.5	817.6	808.2	805.9	799.2	787.0	762.3	737.1	713.3	691.2	668.3
15°	881.0	878.3	863.9	854.9	840.1	823.5	818.1	783.9	753.8	730.8	689.4
17.5°	926.0	913.4	899.9	894.1	888.2	868.9	849.5	814.5	782.1	748.4	721.8
20°	962.0	948.0	938.6	930.1	927.4	905.3	874.7	843.7	808.2	770.4	735.8
22.5°	963.8	962.0	955.7	950.7	945.3	930.9	906.7	868.0	830.2	788.8	743.4
25°	926.5	923.8	941.7	937.2	940.8	935.4	922.4	890.0	846.0	797.4	751.5
27.5°	814.0	841.5	869.8	879.7	886.4	905.8	912.1	894.1	858.5	806.8	755.6
30°	661.1	697.5	743.4	768.1	787.0	823.0	869.8	875.6	859.0	817.6	754.7
32.5°	519.0	552.3	589.2	618.4	643.6	717.3	780.3	825.7	833.8	812.2	756.9
35°	418.3	432.6	467.7	495.6	529.8	592.7	667.0	740.3	789.7	792.4	750.2
37.5°	344.9	352.6	383.2	398.9	419.2	474.5	543.7	639.5	716.4	752.9	731.3
40°	285.6	303.1	320.7	329.7	344.0	382.3	448.8	523.9	619.3	686.7	702.0
42.5°	247.8	255.4	266.7	279.3	288.3	321.6	366.1	434.9	520.8	614.8	657.1
45°	218.6	221.3	233.0	241.1	250.5	273.9	305.4	362.9	438.5	531.1	603.1
47.5°	194.3	199.7	206.0	210.9	217.2	235.2	262.2	304.0	370.6	453.3	530.7
50°	172.7	175.8	183.9	186.2	190.7	203.3	224.0	255.9	310.8	376.9	456.9
52.5°	152.5	158.3	161.5	164.6	168.7	179.0	192.5	218.6	259.9	322.0	389.9
55°	136.7	138.5	143.0	145.7	148.9	156.1	167.8	187.1	219.5	268.9	333.3
57.5°	121.4	121.4	125.9	128.2	131.3	136.7	147.1	161.9	185.3	222.2	281.1
60°	105.2	105.7	109.3	112.0	112.9	118.3	126.8	138.5	156.5	183.5	231.6
62.5°	90.8	93.1	94.9	95.8	98.9	102.1	109.3	117.4	130.0	153.8	188.0
65°	78.7	79.2	80.5	81.4	82.8	86.3	91.7	97.1	107.9	125.5	153.4
67.5°	64.8	66.6	68.4	68.4	69.7	71.5	76.9	81.4	89.5	99.8	118.7
70°	48.6	49.5	52.2	53.5	55.3	58.5	61.2	63.9	70.2	77.8	92.2
72.5°	40.5	40.5	41.4	41.8	41.8	44.1	48.1	50.8	54.0	59.4	69.3
75°	32.4	32.4	33.7	33.3	34.2	35.1	35.5	37.3	39.1	43.2	49.0
77.5°	25.6	26.1	26.1	26.5	26.5	27.0	27.4	28.3	29.2	31.5	34.2
80°	18.9	19.3	19.3	19.8	19.8	20.2	20.7	21.1	22.0	22.9	24.3
82.5°	13.0	13.5	13.5	13.9	13.5	13.9	14.4	14.4	14.8	15.7	16.2
85°	7.6	7.6	8.1	7.6	7.6	7.6	8.1	8.1	8.5	9.9	9.9
87.5°	2.2	2.7	2.2	2.7	2.7	2.7	2.7	3.1	3.1	3.6	4.0
90°	43.8	43.1	42.4	42.1	41.4	40.1	38.8	37.4	36.1	31.7	27.4
92.5°	50.4	50.1	49.8	49.6	48.4	46.1	43.8	41.4	39.1	36.1	33.1
95°	57.1	57.1	57.1	57.1	55.9	53.6	51.3	48.9	46.6	42.9	39.3
97.5°	61.0	60.7	60.4	60.2	58.9	56.2	53.5	50.8	48.1	65.1	82.2
100°	62.5	62.2	61.9	61.7	60.4	57.7	55.0	52.3	49.6	101.7	153.9
102.5°	63.4	62.7	62.0	61.7	67.2	78.2	89.3	100.3	111.3	169.5	227.6
105°	64.9	64.2	63.5	63.2	92.8	151.9	211.0	270.2	329.3	359.4	389.5
107.5°	244.0	287.7	331.5	353.4	379.1	430.6	482.1	533.5	585.0	580.0	575.0
110°	509.2	556.9	604.7	628.6	634.1	645.1	656.2	667.2	678.2	674.5	670.9

TEST NUMBER: P1032214

CATALOG NUMBER: S123RDIW-B340D1535UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	784.8	785.5	786.2	786.5	785.0	782.0	779.0	776.0	773.0	769.3	765.6
115°	881.6	880.3	879.0	878.3	876.6	873.3	869.9	866.6	863.2	860.2	857.2
117.5°	964.8	964.5	964.2	964.0	962.7	960.0	957.3	954.6	951.9	950.2	948.6
120°	1049.7	1049.7	1049.7	1049.7	1048.4	1045.7	1043.0	1040.4	1037.7	1036.7	1035.7
122.5°	1131.7	1131.4	1131.1	1130.9	1130.1	1128.4	1126.7	1125.1	1123.4	1122.1	1120.7
125°	1207.8	1207.1	1206.4	1206.1	1205.8	1205.1	1204.4	1203.8	1203.1	1201.8	1200.4
127.5°	1285.6	1286.3	1287.0	1287.3	1286.8	1285.8	1284.8	1283.8	1282.8	1281.1	1279.5
130°	1357.8	1358.5	1359.2	1359.5	1358.8	1357.5	1356.2	1354.8	1353.5	1352.2	1350.8
132.5°	1424.7	1425.7	1426.7	1427.2	1426.5	1425.2	1423.9	1422.5	1421.2	1420.2	1419.2
135°	1492.3	1493.3	1494.3	1494.8	1494.3	1493.3	1492.3	1491.3	1490.3	1489.0	1487.6
137.5°	1556.3	1557.0	1557.7	1558.0	1557.2	1555.5	1553.8	1552.2	1550.5	1549.8	1549.2
140°	1613.5	1614.2	1614.9	1615.2	1614.5	1613.2	1611.8	1610.5	1609.1	1608.1	1607.1
142.5°	1666.8	1667.8	1668.8	1669.3	1668.8	1667.8	1666.8	1665.8	1664.8	1663.8	1662.8
145°	1718.9	1718.9	1718.9	1718.9	1718.6	1717.9	1717.2	1716.6	1715.9	1715.2	1714.6
147.5°	1761.3	1763.0	1764.7	1765.5	1765.2	1764.5	1763.8	1763.2	1762.5	1761.8	1761.2
150°	1805.1	1806.1	1807.1	1807.6	1807.3	1806.6	1805.9	1805.3	1804.6	1803.9	1803.3
152.5°	1842.5	1844.2	1845.9	1846.7	1846.0	1844.7	1843.4	1842.0	1840.7	1840.4	1840.0
155°	1876.3	1878.3	1880.3	1881.3	1880.5	1878.8	1877.1	1875.5	1873.8	1873.5	1873.1
157.5°	1906.2	1908.9	1911.6	1912.9	1911.9	1909.9	1907.9	1905.9	1903.9	1904.2	1904.6
160°	1932.7	1935.0	1937.3	1938.5	1937.5	1935.5	1933.5	1931.5	1929.5	1929.8	1930.2
162.5°	1957.5	1959.5	1961.5	1962.5	1961.3	1959.0	1956.7	1954.3	1952.0	1952.3	1952.7
165°	1977.8	1980.1	1982.4	1983.6	1982.3	1979.6	1976.9	1974.3	1971.6	1971.9	1972.3
167.5°	1993.4	1996.1	1998.8	2000.1	1998.8	1996.1	1993.4	1990.8	1988.1	1988.1	1988.1
170°	2007.0	2009.7	2012.4	2013.7	2012.4	2009.7	2007.0	2004.3	2001.6	2001.6	2001.6
172.5°	2015.2	2018.2	2021.2	2022.7	2021.4	2018.7	2016.0	2013.4	2010.7	2010.4	2010.0
175°	2022.0	2024.7	2027.4	2028.7	2027.5	2025.2	2022.9	2020.5	2018.2	2017.9	2017.5
177.5°	2024.9	2028.2	2031.5	2033.2	2031.9	2029.2	2026.5	2023.9	2021.2	2020.9	2020.5
180°	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2

TEST NUMBER: P1032214

CATALOG NUMBER: S123RDIW-B340D1535UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3
2.5°	543.7	541.5	539.2	539.2	534.3	529.8	527.5	528.4	525.7	522.1	518.5
5°	567.6	558.6	556.8	551.8	545.1	535.6	530.7	526.2	520.8	513.6	506.9
7.5°	589.6	577.9	571.6	566.7	553.6	540.6	529.8	522.6	513.1	502.4	494.3
10°	618.4	596.8	590.1	578.8	560.4	541.9	529.3	517.6	504.6	492.0	481.2
12.5°	641.3	616.6	604.0	592.7	568.9	545.5	524.4	510.0	494.3	480.3	466.4
15°	667.4	639.5	617.5	604.0	573.9	545.5	521.7	501.5	483.9	466.8	454.7
17.5°	680.0	644.9	635.0	615.7	572.1	543.7	514.5	492.9	471.8	452.0	437.6
20°	699.8	658.9	634.1	621.1	582.4	540.6	506.4	481.7	459.6	438.5	423.2
22.5°	701.1	656.6	640.4	615.7	568.0	531.1	499.2	469.1	443.4	423.6	407.9
25°	698.0	652.6	630.1	610.3	570.7	525.7	484.8	455.1	429.9	407.0	388.6
27.5°	696.6	640.9	619.7	599.9	555.4	510.0	476.3	442.5	413.8	393.5	374.6
30°	694.8	628.3	602.6	579.7	538.8	497.9	457.4	428.1	400.7	375.1	356.2
32.5°	683.1	611.2	585.1	560.8	516.7	475.8	443.9	412.9	383.2	359.3	342.2
35°	679.5	595.4	561.3	535.2	492.0	455.6	421.9	396.2	368.3	344.5	324.3
37.5°	669.2	579.3	542.4	509.1	464.1	429.5	404.8	379.1	352.1	326.5	310.3
40°	651.2	560.4	518.5	484.4	438.0	403.0	380.0	361.1	334.6	311.7	291.9
42.5°	624.7	541.0	496.1	460.1	408.8	376.0	357.1	339.1	316.6	292.8	276.6
45°	594.1	515.4	473.6	433.5	381.4	349.4	329.7	318.9	298.2	277.9	259.0
47.5°	552.3	488.9	447.5	406.1	353.0	322.0	306.3	295.5	281.1	259.0	243.8
50°	499.7	454.7	415.6	378.7	325.2	295.5	279.7	271.6	259.5	243.8	228.9
52.5°	441.2	415.1	382.7	348.5	296.8	268.9	254.5	248.3	239.3	224.4	211.8
55°	382.3	371.0	349.0	315.3	267.1	244.2	231.6	223.5	216.8	206.0	195.2
57.5°	329.7	324.3	309.0	282.9	242.4	218.6	207.8	202.4	197.0	188.9	178.1
60°	275.2	281.1	265.3	252.3	215.4	194.7	185.3	179.4	176.7	169.5	162.8
62.5°	228.0	233.4	224.4	214.5	188.4	170.0	164.2	158.8	157.0	150.7	143.9
65°	185.3	192.0	185.3	179.9	164.2	148.9	141.7	139.0	137.2	133.1	127.7
67.5°	147.5	154.3	151.1	144.4	139.4	126.8	122.8	120.1	119.2	116.0	111.5
70°	111.1	120.5	121.4	117.4	112.9	107.0	104.3	103.4	101.2	98.5	95.8
72.5°	80.1	90.8	91.3	91.3	88.6	88.6	85.9	84.6	84.6	81.9	78.7
75°	58.9	66.1	67.0	67.9	69.3	70.6	68.8	68.8	68.4	65.7	64.3
77.5°	39.1	45.4	47.7	50.8	52.6	52.6	53.5	54.4	53.5	52.2	51.3
80°	25.2	29.7	32.4	34.2	36.9	38.2	39.6	40.0	39.1	38.7	37.3
82.5°	16.6	18.0	19.3	21.6	24.7	27.0	27.0	26.5	27.4	27.0	26.5
85°	9.4	10.3	10.8	11.2	13.0	15.3	15.7	16.2	17.1	16.2	15.3
87.5°	3.6	4.0	4.0	4.0	4.9	5.4	6.7	8.5	8.1	7.2	7.2
90°	23.0	18.7	16.5	14.8	11.5	8.2	4.8	1.5	4.8	8.2	11.5
92.5°	30.1	27.1	25.6	26.6	28.6	30.6	32.6	34.6	32.6	30.6	28.6
95°	35.6	31.9	30.1	36.9	50.6	64.3	78.0	91.7	78.0	64.3	50.6
97.5°	99.2	116.3	124.8	129.5	138.8	148.2	157.5	166.9	157.5	148.2	138.8
100°	206.0	258.1	284.2	280.9	274.2	267.5	260.9	254.2	260.9	267.5	274.2
102.5°	285.8	343.9	373.0	370.8	366.5	362.1	357.8	353.4	357.8	362.1	366.5
105°	419.6	449.7	464.7	462.9	459.2	455.5	451.9	448.2	451.9	455.5	459.2
107.5°	569.9	564.9	562.4	560.9	557.9	554.9	551.9	548.9	551.9	554.9	557.9
110°	667.2	663.5	661.7	660.4	657.7	655.0	652.4	649.7	652.4	655.0	657.7

TEST NUMBER: P1032214

CATALOG NUMBER: S123RDIW-B340D1535UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	761.9	758.2	756.4	755.2	752.9	750.6	748.2	745.9	748.2	750.6	752.9
115°	854.2	851.2	849.7	848.7	846.7	844.7	842.7	840.7	842.7	844.7	846.7
117.5°	946.9	945.2	944.4	943.2	940.9	938.6	936.2	933.9	936.2	938.6	940.9
120°	1034.7	1033.7	1033.2	1031.7	1028.7	1025.6	1022.6	1019.6	1022.6	1025.6	1028.7
122.5°	1119.4	1118.1	1117.4	1116.2	1113.9	1111.5	1109.2	1106.8	1109.2	1111.5	1113.9
125°	1199.1	1197.8	1197.1	1195.8	1193.1	1190.4	1187.7	1185.0	1187.7	1190.4	1193.1
127.5°	1277.8	1276.1	1275.3	1274.0	1271.3	1268.6	1265.9	1263.2	1265.9	1268.6	1271.3
130°	1349.5	1348.2	1347.5	1346.2	1343.5	1340.8	1338.1	1335.4	1338.1	1340.8	1343.5
132.5°	1418.1	1417.1	1416.6	1415.3	1412.6	1409.9	1407.3	1404.6	1407.3	1409.9	1412.6
135°	1486.3	1485.0	1484.3	1483.3	1481.3	1479.3	1477.3	1475.3	1477.3	1479.3	1481.3
137.5°	1548.5	1547.8	1547.5	1546.2	1543.5	1540.8	1538.1	1535.4	1538.1	1540.8	1543.5
140°	1606.1	1605.1	1604.6	1603.6	1601.6	1599.6	1597.6	1595.6	1597.6	1599.6	1601.6
142.5°	1661.8	1660.8	1660.3	1659.3	1657.3	1655.2	1653.2	1651.2	1653.2	1655.2	1657.3
145°	1713.9	1713.2	1712.9	1711.7	1709.4	1707.1	1704.7	1702.4	1704.7	1707.1	1709.4
147.5°	1760.5	1759.8	1759.5	1758.7	1757.0	1755.3	1753.7	1752.0	1753.7	1755.3	1757.0
150°	1802.6	1801.9	1801.6	1801.1	1800.1	1799.1	1798.1	1797.1	1798.1	1799.1	1800.1
152.5°	1839.7	1839.4	1839.2	1839.0	1838.7	1838.4	1838.0	1837.7	1838.0	1838.4	1838.7
155°	1872.8	1872.5	1872.3	1872.6	1873.3	1874.0	1874.6	1875.3	1874.6	1874.0	1873.3
157.5°	1904.9	1905.2	1905.4	1905.4	1905.4	1905.4	1905.4	1905.4	1905.4	1905.4	1905.4
160°	1930.5	1930.8	1931.0	1931.2	1931.5	1931.8	1932.2	1932.5	1932.2	1931.8	1931.5
162.5°	1953.0	1953.3	1953.5	1954.0	1955.0	1956.0	1957.0	1958.0	1957.0	1956.0	1955.0
165°	1972.6	1972.9	1973.1	1973.6	1974.6	1975.6	1976.6	1977.6	1976.6	1975.6	1974.6
167.5°	1988.1	1988.1	1988.1	1988.8	1990.1	1991.4	1992.8	1994.1	1992.8	1991.4	1990.1
170°	2001.6	2001.6	2001.6	2002.3	2003.6	2005.0	2006.3	2007.7	2006.3	2005.0	2003.6
172.5°	2009.7	2009.4	2009.2	2010.0	2011.7	2013.4	2015.0	2016.7	2015.0	2013.4	2011.7
175°	2017.2	2016.9	2016.7	2017.5	2019.2	2020.9	2022.5	2024.2	2022.5	2020.9	2019.2
177.5°	2020.2	2019.9	2019.7	2020.5	2022.2	2023.9	2025.5	2027.2	2025.5	2023.9	2022.2
180°	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2

TEST NUMBER: P1032214

CATALOG NUMBER: S123RDIW-B340D1535UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3
2.5°	518.5	516.3	515.4	513.1	507.7	504.2	500.1	497.4	497.9	495.6	497.0
5°	502.4	501.9	498.8	494.3	486.6	482.6	475.4	471.8	470.0	470.4	467.7
7.5°	488.9	484.8	482.6	475.4	468.2	459.6	453.8	450.6	447.9	445.2	443.4
10°	473.6	470.0	466.4	458.7	448.8	440.7	432.6	429.5	425.4	423.6	422.3
12.5°	457.4	455.1	450.6	441.6	430.4	422.8	413.3	411.5	406.1	402.5	401.6
15°	442.5	441.2	433.1	422.8	411.5	403.9	395.8	390.4	381.4	383.2	380.0
17.5°	426.8	421.0	416.0	402.1	396.7	385.0	375.5	372.8	366.5	362.5	358.4
20°	409.3	405.7	399.4	390.4	377.3	363.8	356.6	352.1	348.5	342.2	340.4
22.5°	392.6	388.1	382.7	371.0	359.8	348.5	338.6	334.6	330.1	325.6	322.9
25°	379.6	372.8	367.0	352.6	341.3	331.9	325.6	318.9	312.6	309.9	309.0
27.5°	359.3	355.3	349.4	336.0	325.6	315.3	309.4	304.9	298.2	295.0	292.3
30°	346.3	338.2	331.5	320.7	310.3	299.1	293.7	288.3	284.2	280.2	277.0
32.5°	328.8	322.5	317.1	306.3	295.9	285.6	279.7	271.6	269.4	266.2	262.6
35°	311.7	307.6	301.8	290.1	278.8	271.6	265.3	257.7	255.0	252.8	249.6
37.5°	295.5	289.6	285.6	274.3	264.4	255.9	251.0	244.7	242.9	240.2	237.9
40°	281.5	275.7	271.6	260.4	250.1	241.1	237.9	231.6	228.9	225.8	224.4
42.5°	265.8	260.8	255.4	247.4	236.6	227.6	221.3	217.7	214.1	212.7	210.0
45°	249.2	244.7	240.6	231.6	220.4	214.1	208.7	203.7	201.0	198.8	197.0
47.5°	234.8	230.7	225.3	215.4	206.4	200.6	195.2	190.2	187.5	184.8	182.6
50°	218.1	215.9	210.0	200.6	192.0	185.3	180.3	175.8	174.0	170.9	167.3
52.5°	203.3	199.2	194.3	186.6	179.0	170.9	164.2	161.5	158.3	156.5	153.4
55°	185.7	183.0	177.6	170.9	162.8	156.1	151.1	147.5	143.5	141.7	137.6
57.5°	170.9	166.0	163.3	154.7	147.1	140.3	136.7	133.1	128.6	125.9	124.1
60°	154.7	150.2	146.2	139.0	133.6	126.4	121.0	117.8	114.7	111.1	109.3
62.5°	139.0	135.4	130.4	124.6	117.8	112.0	107.9	103.4	101.6	98.0	96.7
65°	121.9	119.2	115.1	108.4	103.0	98.0	94.0	90.4	88.6	87.2	86.3
67.5°	106.6	103.0	100.3	94.4	88.6	84.6	82.3	80.1	77.8	76.5	75.1
70°	90.8	88.1	85.4	80.1	76.0	72.4	70.6	68.8	67.5	66.1	64.8
72.5°	74.7	73.3	70.6	67.0	63.9	61.2	59.8	57.6	56.2	54.0	53.1
75°	61.6	59.4	58.0	54.9	52.2	49.9	48.1	45.4	43.6	42.7	42.3
77.5°	48.6	47.7	45.9	43.2	41.8	39.6	36.9	36.0	35.1	35.1	34.6
80°	36.4	35.1	33.7	31.5	30.1	28.3	28.3	28.3	27.9	28.3	27.9
82.5°	24.7	23.8	22.9	21.6	21.1	21.1	21.6	21.6	21.6	21.6	21.6
85°	14.4	14.4	14.4	14.8	14.4	14.4	14.8	15.3	14.8	14.8	14.4
87.5°	6.7	6.7	7.2	7.2	7.6	7.6	7.6	7.6	7.6	7.6	8.1
90°	14.8	16.5	18.7	23.0	27.4	31.7	36.1	37.4	38.8	40.1	41.4
92.5°	26.6	25.6	27.1	30.1	33.1	36.1	39.1	41.4	43.8	46.1	48.4
95°	36.9	30.1	31.9	35.6	39.3	42.9	46.6	48.9	51.3	53.6	55.9
97.5°	129.5	124.8	116.3	99.2	82.2	65.1	48.1	50.8	53.5	56.2	58.9
100°	280.9	284.2	258.1	206.0	153.9	101.7	49.6	52.3	55.0	57.7	60.4
102.5°	370.8	373.0	343.9	285.8	227.6	169.5	111.3	100.3	89.3	78.2	67.2
105°	462.9	464.7	449.7	419.6	389.5	359.4	329.3	270.2	211.0	151.9	92.8
107.5°	560.9	562.4	564.9	569.9	575.0	580.0	585.0	533.5	482.1	430.6	379.1
110°	660.4	661.7	663.5	667.2	670.9	674.5	678.2	667.2	656.2	645.1	634.1

TEST NUMBER: P1032214

CATALOG NUMBER: S123RDIW-B340D1535UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	755.2	756.4	758.2	761.9	765.6	769.3	773.0	776.0	779.0	782.0	785.0
115°	848.7	849.7	851.2	854.2	857.2	860.2	863.2	866.6	869.9	873.3	876.6
117.5°	943.2	944.4	945.2	946.9	948.6	950.2	951.9	954.6	957.3	960.0	962.7
120°	1031.7	1033.2	1033.7	1034.7	1035.7	1036.7	1037.7	1040.4	1043.0	1045.7	1048.4
122.5°	1116.2	1117.4	1118.1	1119.4	1120.7	1122.1	1123.4	1125.1	1126.7	1128.4	1130.1
125°	1195.8	1197.1	1197.8	1199.1	1200.4	1201.8	1203.1	1203.8	1204.4	1205.1	1205.8
127.5°	1274.0	1275.3	1276.1	1277.8	1279.5	1281.1	1282.8	1283.8	1284.8	1285.8	1286.8
130°	1346.2	1347.5	1348.2	1349.5	1350.8	1352.2	1353.5	1354.8	1356.2	1357.5	1358.8
132.5°	1415.3	1416.6	1417.1	1418.1	1419.2	1420.2	1421.2	1422.5	1423.9	1425.2	1426.5
135°	1483.3	1484.3	1485.0	1486.3	1487.6	1489.0	1490.3	1491.3	1492.3	1493.3	1494.3
137.5°	1546.2	1547.5	1547.8	1548.5	1549.2	1549.8	1550.5	1552.2	1553.8	1555.5	1557.2
140°	1603.6	1604.6	1605.1	1606.1	1607.1	1608.1	1609.1	1610.5	1611.8	1613.2	1614.5
142.5°	1659.3	1660.3	1660.8	1661.8	1662.8	1663.8	1664.8	1665.8	1666.8	1667.8	1668.8
145°	1711.7	1712.9	1713.2	1713.9	1714.6	1715.2	1715.9	1716.6	1717.2	1717.9	1718.6
147.5°	1758.7	1759.5	1759.8	1760.5	1761.2	1761.8	1762.5	1763.2	1763.8	1764.5	1765.2
150°	1801.1	1801.6	1801.9	1802.6	1803.3	1803.9	1804.6	1805.3	1805.9	1806.6	1807.3
152.5°	1839.0	1839.2	1839.4	1839.7	1840.0	1840.4	1840.7	1842.0	1843.4	1844.7	1846.0
155°	1872.6	1872.3	1872.5	1872.8	1873.1	1873.5	1873.8	1875.5	1877.1	1878.8	1880.5
157.5°	1905.4	1905.4	1905.2	1904.9	1904.6	1904.2	1903.9	1905.9	1907.9	1909.9	1911.9
160°	1931.2	1931.0	1930.8	1930.5	1930.2	1929.8	1929.5	1931.5	1933.5	1935.5	1937.5
162.5°	1954.0	1953.5	1953.3	1953.0	1952.7	1952.3	1952.0	1954.3	1956.7	1959.0	1961.3
165°	1973.6	1973.1	1972.9	1972.6	1972.3	1971.9	1971.6	1974.3	1976.9	1979.6	1982.3
167.5°	1988.8	1988.1	1988.1	1988.1	1988.1	1988.1	1988.1	1990.8	1993.4	1996.1	1998.8
170°	2002.3	2001.6	2001.6	2001.6	2001.6	2001.6	2001.6	2004.3	2007.0	2009.7	2012.4
172.5°	2010.0	2009.2	2009.4	2009.7	2010.0	2010.4	2010.7	2013.4	2016.0	2018.7	2021.4
175°	2017.5	2016.7	2016.9	2017.2	2017.5	2017.9	2018.2	2020.5	2022.9	2025.2	2027.5
177.5°	2020.5	2019.7	2019.9	2020.2	2020.5	2020.9	2021.2	2023.9	2026.5	2029.2	2031.9
180°	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2

TEST NUMBER: P1032214

CATALOG NUMBER: S123RDIW-B340D1535UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3
2.5°	496.5	497.0	495.6	492.9	492.5	493.4	496.1	495.2	492.9	497.0	493.4
5°	469.1	466.8	465.9	466.8	464.1	462.8	465.5	464.1	465.5	465.9	467.3
7.5°	442.5	443.0	440.3	440.7	437.1	438.0	438.0	438.0	439.4	440.3	442.1
10°	419.6	420.5	417.4	417.8	415.1	413.3	414.7	417.4	417.4	417.4	418.3
12.5°	401.2	397.1	394.9	394.4	391.3	390.4	393.1	394.0	396.2	396.2	397.6
15°	378.2	377.3	375.5	375.5	367.9	369.7	370.6	373.7	378.2	374.6	375.5
17.5°	357.5	355.3	353.0	352.1	351.2	348.5	352.1	351.7	354.4	354.8	356.2
20°	339.1	337.3	332.8	333.3	334.2	330.1	332.4	332.4	335.1	337.8	340.9
22.5°	321.1	319.3	317.1	318.0	315.3	314.4	314.4	316.6	319.8	322.0	321.6
25°	307.2	304.0	302.7	301.3	300.0	300.9	299.5	301.8	304.0	305.4	304.0
27.5°	291.4	290.1	287.4	286.0	283.8	284.7	285.6	287.4	288.7	288.7	290.1
30°	276.1	274.3	273.4	272.1	272.1	270.3	270.7	272.5	273.9	275.2	277.0
32.5°	261.3	259.9	258.6	258.6	257.7	257.2	256.8	259.5	259.5	262.2	262.2
35°	249.2	246.9	246.9	244.7	245.6	245.1	244.2	246.0	246.5	248.3	247.8
37.5°	235.7	235.7	234.8	232.5	230.7	231.2	233.4	233.4	234.8	234.3	235.7
40°	222.2	221.3	221.3	219.9	219.5	219.0	219.5	219.9	222.2	221.7	222.2
42.5°	208.7	209.1	206.9	206.9	206.9	205.5	206.0	206.4	207.3	208.2	209.6
45°	195.6	194.7	194.3	193.4	192.5	192.9	192.5	194.3	193.8	194.7	196.1
47.5°	181.7	180.3	179.9	178.1	178.1	179.0	178.5	179.9	180.3	181.7	180.8
50°	168.2	166.4	165.1	165.5	162.8	163.7	163.7	165.1	166.4	166.9	167.8
52.5°	152.5	152.0	151.6	149.3	148.9	148.4	148.9	149.3	151.1	152.5	152.9
55°	137.2	136.7	134.0	133.1	131.8	131.8	132.7	133.1	136.3	136.7	138.5
57.5°	123.2	121.9	118.7	118.3	118.3	118.3	116.9	118.7	119.6	121.9	121.9
60°	107.9	107.9	105.2	105.2	105.7	105.2	105.2	105.7	105.7	107.5	108.4
62.5°	95.8	95.3	95.3	94.4	94.0	94.4	94.0	94.0	94.4	95.8	97.1
65°	85.0	84.6	84.1	83.7	82.8	82.8	83.2	84.1	84.1	85.0	85.4
67.5°	74.7	74.7	73.8	73.8	73.3	72.9	73.3	72.9	74.7	74.7	75.1
70°	64.3	63.9	62.5	62.1	60.7	61.2	61.2	62.5	63.0	63.9	64.8
72.5°	51.7	51.7	50.8	49.9	50.4	49.5	49.5	49.9	49.9	51.3	51.7
75°	42.7	41.8	41.4	41.8	41.4	42.3	41.4	41.4	42.3	42.3	42.3
77.5°	35.1	35.1	34.6	34.6	35.1	34.6	35.1	35.1	35.1	34.6	35.1
80°	28.8	28.3	28.3	28.3	27.9	27.9	27.9	27.9	27.9	27.9	27.9
82.5°	21.6	21.6	21.1	21.6	21.6	21.1	21.6	21.1	21.1	21.6	21.6
85°	14.4	15.3	14.4	14.4	14.8	14.8	15.3	14.8	15.3	14.4	14.8
87.5°	7.6	8.1	8.1	7.6	7.6	8.1	8.1	8.1	8.5	7.6	8.1
90°	42.1	42.4	43.1	43.8	44.4	45.1	44.4	43.8	43.1	42.4	42.1
92.5°	49.6	49.8	50.1	50.4	50.8	51.1	50.8	50.4	50.1	49.8	49.6
95°	57.1	57.1	57.1	57.1	57.1	57.1	57.1	57.1	57.1	57.1	57.1
97.5°	60.2	60.4	60.7	61.0	61.4	61.7	61.4	61.0	60.7	60.4	60.2
100°	61.7	61.9	62.2	62.5	62.9	63.2	62.9	62.5	62.2	61.9	61.7
102.5°	61.7	62.0	62.7	63.4	64.0	64.7	64.0	63.4	62.7	62.0	61.7
105°	63.2	63.5	64.2	64.9	65.5	66.2	65.5	64.9	64.2	63.5	63.2
107.5°	353.4	331.5	287.7	244.0	200.2	156.4	200.2	244.0	287.7	331.5	353.4
110°	628.6	604.7	556.9	509.2	461.4	413.6	461.4	509.2	556.9	604.7	628.6

TEST NUMBER: P1032214

CATALOG NUMBER: S123RDIW-B340D1535UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	786.5	786.2	785.5	784.8	784.2	783.5	784.2	784.8	785.5	786.2	786.5
115°	878.3	879.0	880.3	881.6	883.0	884.3	883.0	881.6	880.3	879.0	878.3
117.5°	964.0	964.2	964.5	964.8	965.2	965.5	965.2	964.8	964.5	964.2	964.0
120°	1049.7	1049.7	1049.7	1049.7	1049.7	1049.7	1049.7	1049.7	1049.7	1049.7	1049.7
122.5°	1130.9	1131.1	1131.4	1131.7	1132.1	1132.4	1132.1	1131.7	1131.4	1131.1	1130.9
125°	1206.1	1206.4	1207.1	1207.8	1208.4	1209.1	1208.4	1207.8	1207.1	1206.4	1206.1
127.5°	1287.3	1287.0	1286.3	1285.6	1285.0	1284.3	1285.0	1285.6	1286.3	1287.0	1287.3
130°	1359.5	1359.2	1358.5	1357.8	1357.2	1356.5	1357.2	1357.8	1358.5	1359.2	1359.5
132.5°	1427.2	1426.7	1425.7	1424.7	1423.7	1422.7	1423.7	1424.7	1425.7	1426.7	1427.2
135°	1494.8	1494.3	1493.3	1492.3	1491.3	1490.3	1491.3	1492.3	1493.3	1494.3	1494.8
137.5°	1558.0	1557.7	1557.0	1556.3	1555.7	1555.0	1555.7	1556.3	1557.0	1557.7	1558.0
140°	1615.2	1614.9	1614.2	1613.5	1612.8	1612.1	1612.8	1613.5	1614.2	1614.9	1615.2
142.5°	1669.3	1668.8	1667.8	1666.8	1665.8	1664.8	1665.8	1666.8	1667.8	1668.8	1669.3
145°	1718.9	1718.9	1718.9	1718.9	1718.9	1718.9	1718.9	1718.9	1718.9	1718.9	1718.9
147.5°	1765.5	1764.7	1763.0	1761.3	1759.7	1758.0	1759.7	1761.3	1763.0	1764.7	1765.5
150°	1807.6	1807.1	1806.1	1805.1	1804.1	1803.1	1804.1	1805.1	1806.1	1807.1	1807.6
152.5°	1846.7	1845.9	1844.2	1842.5	1840.9	1839.2	1840.9	1842.5	1844.2	1845.9	1846.7
155°	1881.3	1880.3	1878.3	1876.3	1874.3	1872.3	1874.3	1876.3	1878.3	1880.3	1881.3
157.5°	1912.9	1911.6	1908.9	1906.2	1903.6	1900.9	1903.6	1906.2	1908.9	1911.6	1912.9
160°	1938.5	1937.3	1935.0	1932.7	1930.3	1928.0	1930.3	1932.7	1935.0	1937.3	1938.5
162.5°	1962.5	1961.5	1959.5	1957.5	1955.5	1953.5	1955.5	1957.5	1959.5	1961.5	1962.5
165°	1983.6	1982.4	1980.1	1977.8	1975.4	1973.1	1975.4	1977.8	1980.1	1982.4	1983.6
167.5°	2000.1	1998.8	1996.1	1993.4	1990.8	1988.1	1990.8	1993.4	1996.1	1998.8	2000.1
170°	2013.7	2012.4	2009.7	2007.0	2004.3	2001.6	2004.3	2007.0	2009.7	2012.4	2013.7
172.5°	2022.7	2021.2	2018.2	2015.2	2012.2	2009.2	2012.2	2015.2	2018.2	2021.2	2022.7
175°	2028.7	2027.4	2024.7	2022.0	2019.4	2016.7	2019.4	2022.0	2024.7	2027.4	2028.7
177.5°	2033.2	2031.5	2028.2	2024.9	2021.5	2018.2	2021.5	2024.9	2028.2	2031.5	2033.2
180°	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2

TEST NUMBER: P1032214

CATALOG NUMBER: S123RDIW-B340D1535UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3
2.5°	497.0	498.8	497.0	493.4	497.0	499.2	501.5	505.1	506.9	506.9	509.5
5°	468.6	472.2	470.9	470.0	473.6	475.8	479.4	483.9	488.9	492.0	495.6
7.5°	443.4	445.7	447.9	447.9	451.5	456.5	461.9	467.3	473.6	478.1	480.8
10°	421.4	423.2	424.5	426.3	431.7	437.1	444.3	451.1	456.5	461.4	465.9
12.5°	400.3	403.0	406.1	407.5	411.5	418.3	425.0	433.1	441.6	446.6	451.1
15°	380.0	381.4	385.0	389.0	392.6	399.8	408.4	416.9	424.1	431.7	435.8
17.5°	359.3	359.8	369.2	367.0	378.7	385.4	389.9	398.0	409.7	416.0	422.3
20°	339.1	343.6	347.6	349.9	356.2	363.8	376.9	383.2	392.6	398.5	403.9
22.5°	323.4	330.1	330.1	335.5	338.6	345.8	355.3	367.4	377.8	381.8	389.5
25°	309.4	312.6	318.0	319.8	325.6	331.9	338.2	351.2	362.5	367.9	373.3
27.5°	291.4	295.5	302.7	302.7	310.3	317.1	324.7	333.3	344.5	352.1	358.0
30°	277.5	281.5	284.7	289.6	292.8	299.1	312.6	318.9	328.8	335.5	342.7
32.5°	264.4	267.6	270.3	275.7	279.3	286.5	293.7	304.9	313.5	319.8	327.4
35°	250.1	253.2	256.8	260.8	266.2	273.0	279.7	289.2	297.7	303.6	309.9
37.5°	236.6	238.8	244.2	246.9	251.4	257.7	266.2	276.1	283.8	288.3	294.6
40°	223.5	225.3	229.4	234.3	237.5	242.4	251.4	259.9	269.4	274.8	279.7
42.5°	209.6	211.8	215.4	220.4	225.3	230.7	235.7	245.6	254.1	258.6	264.0
45°	197.4	198.8	201.5	206.4	211.4	215.4	223.1	232.1	240.2	243.8	249.6
47.5°	183.0	184.4	188.4	190.7	196.1	201.5	209.1	218.1	225.3	228.9	234.3
50°	168.2	169.5	172.2	177.2	180.8	186.6	193.4	201.0	210.0	215.0	218.1
52.5°	153.8	156.5	158.8	162.8	167.3	173.1	179.4	186.6	194.3	199.2	202.8
55°	139.4	141.7	144.4	146.6	152.0	157.4	164.6	171.3	178.1	182.6	186.6
57.5°	123.2	126.4	129.1	133.6	137.6	142.1	150.2	155.6	163.7	166.9	170.4
60°	109.3	112.4	114.7	118.3	121.9	127.7	133.1	139.9	146.6	150.7	155.2
62.5°	97.6	98.9	100.3	103.9	107.5	112.9	118.3	125.0	132.2	134.5	138.1
65°	85.9	87.2	89.5	92.6	95.3	98.5	104.3	109.7	116.5	120.1	121.4
67.5°	76.0	77.4	77.8	80.1	82.3	85.9	89.0	94.4	100.7	103.0	105.7
70°	64.8	67.0	67.5	69.3	70.2	72.4	76.0	80.1	85.0	89.0	91.3
72.5°	51.7	54.9	55.8	58.5	59.8	62.1	64.8	67.9	71.1	72.9	74.7
75°	42.3	43.2	43.6	45.9	48.1	51.3	52.6	54.4	57.1	59.4	61.2
77.5°	35.1	35.5	36.0	36.0	36.4	38.2	40.9	43.2	45.0	45.9	47.2
80°	28.3	27.9	27.9	28.3	28.3	28.3	29.2	32.4	33.3	35.5	35.1
82.5°	22.0	21.1	21.6	21.1	21.1	21.1	21.1	21.6	21.6	22.9	23.8
85°	14.4	14.8	14.4	14.4	13.9	14.4	13.9	13.9	13.5	13.5	13.0
87.5°	7.6	8.1	7.6	7.6	7.2	7.6	7.2	7.2	6.7	6.7	5.8
90°	41.4	40.1	38.8	37.4	36.1	31.7	27.4	23.0	18.7	16.5	14.8
92.5°	48.4	46.1	43.8	41.4	39.1	36.1	33.1	30.1	27.1	25.6	26.6
95°	55.9	53.6	51.3	48.9	46.6	42.9	39.3	35.6	31.9	30.1	36.9
97.5°	58.9	56.2	53.5	50.8	48.1	65.1	82.2	99.2	116.3	124.8	129.5
100°	60.4	57.7	55.0	52.3	49.6	101.7	153.9	206.0	258.1	284.2	280.9
102.5°	67.2	78.2	89.3	100.3	111.3	169.5	227.6	285.8	343.9	373.0	370.8
105°	92.8	151.9	211.0	270.2	329.3	359.4	389.5	419.6	449.7	464.7	462.9
107.5°	379.1	430.6	482.1	533.5	585.0	580.0	575.0	569.9	564.9	562.4	560.9
110°	634.1	645.1	656.2	667.2	678.2	674.5	670.9	667.2	663.5	661.7	660.4

TEST NUMBER: P1032214

CATALOG NUMBER: S123RDIW-B340D1535UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	785.0	782.0	779.0	776.0	773.0	769.3	765.6	761.9	758.2	756.4	755.2
115°	876.6	873.3	869.9	866.6	863.2	860.2	857.2	854.2	851.2	849.7	848.7
117.5°	962.7	960.0	957.3	954.6	951.9	950.2	948.6	946.9	945.2	944.4	943.2
120°	1048.4	1045.7	1043.0	1040.4	1037.7	1036.7	1035.7	1034.7	1033.7	1033.2	1031.7
122.5°	1130.1	1128.4	1126.7	1125.1	1123.4	1122.1	1120.7	1119.4	1118.1	1117.4	1116.2
125°	1205.8	1205.1	1204.4	1203.8	1203.1	1201.8	1200.4	1199.1	1197.8	1197.1	1195.8
127.5°	1286.8	1285.8	1284.8	1283.8	1282.8	1281.1	1279.5	1277.8	1276.1	1275.3	1274.0
130°	1358.8	1357.5	1356.2	1354.8	1353.5	1352.2	1350.8	1349.5	1348.2	1347.5	1346.2
132.5°	1426.5	1425.2	1423.9	1422.5	1421.2	1420.2	1419.2	1418.1	1417.1	1416.6	1415.3
135°	1494.3	1493.3	1492.3	1491.3	1490.3	1489.0	1487.6	1486.3	1485.0	1484.3	1483.3
137.5°	1557.2	1555.5	1553.8	1552.2	1550.5	1549.8	1549.2	1548.5	1547.8	1547.5	1546.2
140°	1614.5	1613.2	1611.8	1610.5	1609.1	1608.1	1607.1	1606.1	1605.1	1604.6	1603.6
142.5°	1668.8	1667.8	1666.8	1665.8	1664.8	1663.8	1662.8	1661.8	1660.8	1660.3	1659.3
145°	1718.6	1717.9	1717.2	1716.6	1715.9	1715.2	1714.6	1713.9	1713.2	1712.9	1711.7
147.5°	1765.2	1764.5	1763.8	1763.2	1762.5	1761.8	1761.2	1760.5	1759.8	1759.5	1758.7
150°	1807.3	1806.6	1805.9	1805.3	1804.6	1803.9	1803.3	1802.6	1801.9	1801.6	1801.1
152.5°	1846.0	1844.7	1843.4	1842.0	1840.7	1840.4	1840.0	1839.7	1839.4	1839.2	1839.0
155°	1880.5	1878.8	1877.1	1875.5	1873.8	1873.5	1873.1	1872.8	1872.5	1872.3	1872.6
157.5°	1911.9	1909.9	1907.9	1905.9	1903.9	1904.2	1904.6	1904.9	1905.2	1905.4	1905.4
160°	1937.5	1935.5	1933.5	1931.5	1929.5	1929.8	1930.2	1930.5	1930.8	1931.0	1931.2
162.5°	1961.3	1959.0	1956.7	1954.3	1952.0	1952.3	1952.7	1953.0	1953.3	1953.5	1954.0
165°	1982.3	1979.6	1976.9	1974.3	1971.6	1971.9	1972.3	1972.6	1972.9	1973.1	1973.6
167.5°	1998.8	1996.1	1993.4	1990.8	1988.1	1988.1	1988.1	1988.1	1988.1	1988.1	1988.8
170°	2012.4	2009.7	2007.0	2004.3	2001.6	2001.6	2001.6	2001.6	2001.6	2001.6	2002.3
172.5°	2021.4	2018.7	2016.0	2013.4	2010.7	2010.4	2010.0	2009.7	2009.4	2009.2	2010.0
175°	2027.5	2025.2	2022.9	2020.5	2018.2	2017.9	2017.5	2017.2	2016.9	2016.7	2017.5
177.5°	2031.9	2029.2	2026.5	2023.9	2021.2	2020.9	2020.5	2020.2	2019.9	2019.7	2020.5
180°	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2	2024.2

TEST NUMBER: P1032214

CATALOG NUMBER: S123RDIW-B340D1535UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	525.3	525.3	525.3	525.3
2.5°	511.8	514.9	521.2	526.6
5°	501.0	506.0	515.4	524.8
7.5°	488.0	495.6	507.7	520.8
10°	475.4	485.3	500.1	515.4
12.5°	462.8	473.1	488.9	508.6
15°	447.9	458.7	477.6	501.5
17.5°	434.9	449.3	466.4	490.2
20°	421.0	431.7	453.8	479.0
22.5°	403.4	421.4	442.1	468.6
25°	389.5	405.2	425.9	456.0
27.5°	372.4	390.8	416.0	442.5
30°	358.4	373.7	397.1	429.0
32.5°	342.2	360.2	384.5	416.0
35°	327.9	343.1	366.1	398.0
37.5°	310.8	327.4	353.0	381.4
40°	295.9	312.1	336.4	362.9
42.5°	277.9	295.0	319.3	341.8
45°	263.5	279.3	298.6	319.3
47.5°	246.0	262.6	281.5	295.9
50°	230.3	245.6	260.4	272.5
52.5°	213.2	227.1	240.6	249.6
55°	197.4	208.2	219.0	225.3
57.5°	179.0	189.3	198.3	201.9
60°	162.8	171.3	177.2	181.2
62.5°	145.7	152.0	156.5	158.8
65°	129.1	133.6	135.8	138.1
67.5°	112.0	116.0	117.4	120.1
70°	94.0	98.5	99.4	100.7
72.5°	80.5	80.5	82.3	84.1
75°	64.3	65.2	66.1	66.1
77.5°	50.4	50.4	51.3	51.7
80°	36.9	37.3	37.3	36.9
82.5°	25.2	26.1	25.2	24.7
85°	13.9	15.7	14.8	14.8
87.5°	5.8	5.8	6.7	5.8
90°	11.5	8.2	4.8	1.5
92.5°	28.6	30.6	32.6	34.6
95°	50.6	64.3	78.0	91.7
97.5°	138.8	148.2	157.5	166.9
100°	274.2	267.5	260.9	254.2
102.5°	366.5	362.1	357.8	353.4
105°	459.2	455.5	451.9	448.2
107.5°	557.9	554.9	551.9	548.9
110°	657.7	655.0	652.4	649.7

TEST NUMBER: P1032214

CATALOG NUMBER: S123RDIW-B340D1535UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	752.9	750.6	748.2	745.9
115°	846.7	844.7	842.7	840.7
117.5°	940.9	938.6	936.2	933.9
120°	1028.7	1025.6	1022.6	1019.6
122.5°	1113.9	1111.5	1109.2	1106.8
125°	1193.1	1190.4	1187.7	1185.0
127.5°	1271.3	1268.6	1265.9	1263.2
130°	1343.5	1340.8	1338.1	1335.4
132.5°	1412.6	1409.9	1407.3	1404.6
135°	1481.3	1479.3	1477.3	1475.3
137.5°	1543.5	1540.8	1538.1	1535.4
140°	1601.6	1599.6	1597.6	1595.6
142.5°	1657.3	1655.2	1653.2	1651.2
145°	1709.4	1707.1	1704.7	1702.4
147.5°	1757.0	1755.3	1753.7	1752.0
150°	1800.1	1799.1	1798.1	1797.1
152.5°	1838.7	1838.4	1838.0	1837.7
155°	1873.3	1874.0	1874.6	1875.3
157.5°	1905.4	1905.4	1905.4	1905.4
160°	1931.5	1931.8	1932.2	1932.5
162.5°	1955.0	1956.0	1957.0	1958.0
165°	1974.6	1975.6	1976.6	1977.6
167.5°	1990.1	1991.4	1992.8	1994.1
170°	2003.6	2005.0	2006.3	2007.7
172.5°	2011.7	2013.4	2015.0	2016.7
175°	2019.2	2020.9	2022.5	2024.2
177.5°	2022.2	2023.9	2025.5	2027.2
180°	2024.2	2024.2	2024.2	2024.2

(END OF REPORT)